

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938082

Luminaire Tested: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K

Issue Date: 12/17/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P938082  
REPORT IS A COMBINATION OF REPORTS P933599 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8150.3 lumens  
Efficiency: N/A  
Efficacy: 126.6 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P938082  
CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P938082

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	90	86	83	86	82	79	76	67	65	62	53	51	50	40	39	38	32
2	86	78	72	67	78	71	66	61	58	54	51	46	43	41	35	33	31	26
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26	21
4	71	60	52	46	64	55	48	42	45	40	35	35	32	29	27	24	22	18
5	65	53	45	39	59	49	41	36	40	34	30	31	27	24	24	21	19	15
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13
7	55	43	35	29	50	39	32	27	32	26	23	25	21	18	19	16	14	11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	26	21	17	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	18	24	19	16	19	15	13	15	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3798	3798	3798
5°	3707	4387	5105
10°	3358	6390	8463
15°	2850	8342	10219
20°	2317	9659	10414
25°	1931	10100	10204
30°	1627	10156	10184
35°	1436	9980	10448
40°	1249	9753	10720
45°	1128	9583	10762
50°	1033	9430	10583
55°	986	9209	10115
60°	1007	8792	9374
65°	1042	8165	8355
70°	1102	7106	7059
75°	1210	5779	5509
80°	1292	3994	3712
85°	1085	2109	1898

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 10762 cd/sqm



TEST NUMBER: P938082

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.9	0.6
10°-20°	234.6	2.9
20°-30°	410.4	5.0
30°-40°	528.3	6.5
40°-50°	590.2	7.2
50°-60°	565.2	6.9
60°-70°	448.0	5.5
70°-80°	263.4	3.2
80°-90°	76.1	0.9
90°-100°	374.5	4.6
100°-110°	984.7	12.1
110°-120°	1021.0	12.5
120°-130°	819.0	10.0
130°-140°	642.6	7.9
140°-150°	493.2	6.1
150°-160°	355.2	4.4
160°-170°	217.3	2.7
170°-180°	73.4	0.9
0°-30°	698.0	8.6
0°-40°	1226.4	15.0
0°-60°	2381.8	29.2
0°-90°	3169.2	38.9
90°-120°	2380.3	29.2
90°-150°	4335.1	53.2
90°-180°	4981.0	61.1
0°-180°	8150.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	399	428	482	545	565	37
15°	299	551	929	1127	1162	83
25°	191	625	1107	1156	1157	88
35°	129	598	1042	1102	1145	81
45°	88	476	921	1056	1103	68
55°	63	303	782	908	933	58
65°	50	161	580	653	662	50
75°	37	99	318	350	351	39
85°	13	30	79	87	88	14
90°	5	14	39	20	20	5
95°	50	194	645	333	226	55
105°	177	269	1089	1653	1542	188
115°	315	383	872	1739	1985	311
125°	438	491	793	1340	1581	389
135°	522	575	768	1082	1227	404
145°	606	645	759	923	995	380
155°	685	704	759	833	857	315
165°	739	749	759	788	798	209
175°	768	768	764	774	774	73
180°	768	768	768	768	768	



TEST NUMBER: P938082

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	409.3	409.3	411.9	413.2	415.8	417.2	419.8	422.4	430.4	431.7	434.3
5°	398.8	404.1	421.1	427.7	446.1	471.1	481.7	498.8	534.4	544.8	551.4
7.5°	383.0	394.8	436.9	447.5	493.5	559.4	586.9	623.8	680.4	708.1	730.4
10°	358.0	383.0	458.0	483.0	558.0	658.1	709.4	760.6	846.2	884.3	898.9
12.5°	330.4	371.1	480.4	514.5	622.5	768.6	830.5	887.0	984.4	1035.7	1043.6
15°	298.7	354.0	501.4	551.4	690.9	860.7	929.2	998.9	1089.7	1126.6	1135.7
17.5°	271.1	340.8	521.1	573.8	743.6	943.6	1013.3	1071.3	1145.0	1170.0	1176.6
20°	236.8	319.8	534.4	602.8	798.9	1004.2	1071.3	1116.0	1166.0	1181.9	1184.4
22.5°	211.8	297.4	542.2	613.2	835.6	1041.0	1097.6	1133.1	1167.3	1172.6	1173.9
25°	190.8	272.4	540.9	625.1	867.3	1063.3	1106.8	1133.1	1152.9	1155.5	1155.5
27.5°	171.1	244.8	535.6	627.8	890.9	1068.6	1102.9	1121.3	1130.5	1135.7	1135.7
30°	154.0	218.4	522.5	622.5	901.5	1063.3	1091.0	1100.2	1109.4	1117.3	1121.3
32.5°	140.8	193.4	502.8	611.9	902.8	1050.2	1069.9	1075.2	1088.3	1106.8	1113.4
35°	129.0	168.4	480.4	597.5	894.9	1029.2	1042.3	1047.6	1073.9	1101.6	1110.7
37.5°	117.1	150.0	451.4	572.5	883.1	1004.2	1013.3	1022.6	1063.3	1096.3	1106.8
40°	105.3	134.3	417.2	544.8	864.6	973.9	981.8	996.3	1050.2	1088.3	1098.9
42.5°	96.1	121.1	380.4	515.9	840.9	939.6	951.5	972.6	1034.4	1075.2	1087.0
45°	88.1	107.9	340.8	476.4	810.6	904.2	921.2	950.2	1016.0	1055.5	1066.0
47.5°	80.3	98.7	300.1	435.7	777.8	868.6	890.9	923.9	991.0	1029.2	1038.3
50°	73.7	89.5	259.3	392.2	742.2	830.5	856.8	890.9	959.4	994.9	1006.8
52.5°	68.4	81.6	221.1	348.8	701.5	790.9	821.2	856.8	921.2	955.5	963.3
55°	63.1	75.0	188.2	302.7	659.4	748.8	781.8	815.9	879.2	908.1	913.3
57.5°	60.6	69.7	160.6	259.3	614.6	701.5	738.3	769.9	829.1	851.5	856.8
60°	56.6	65.8	139.5	222.4	565.9	656.7	688.3	719.9	769.9	788.3	792.2
62.5°	52.7	63.1	123.7	186.8	515.9	604.1	635.6	664.6	706.8	719.9	725.2
65°	50.0	60.6	111.9	160.6	464.5	548.8	580.4	605.4	639.6	652.8	655.4
67.5°	47.4	57.9	102.7	138.1	413.2	493.5	517.2	540.9	567.2	580.4	581.7
70°	43.4	55.3	94.7	122.4	360.6	430.4	450.1	475.1	496.1	502.8	506.7
72.5°	40.8	51.3	89.5	110.6	306.7	369.8	388.2	402.7	421.1	427.7	427.7
75°	36.9	46.0	84.3	98.7	251.4	302.7	318.5	333.0	347.4	350.1	346.1
77.5°	32.9	40.8	72.4	82.9	196.1	239.5	252.7	260.6	272.4	275.1	276.4
80°	27.6	35.6	56.6	64.4	142.1	176.4	185.6	192.1	202.7	202.7	205.3
82.5°	21.0	27.6	40.8	46.0	96.1	121.1	129.0	133.0	139.5	139.5	139.5
85°	13.1	17.1	26.3	30.3	57.9	73.7	79.0	80.3	85.6	86.9	86.9
87.5°	6.6	9.2	17.1	18.4	30.3	38.1	38.1	40.8	40.8	39.4	38.1
90°	5.2	9.3	13.4	14.4	22.7	33.7	39.1	34.8	26.1	19.6	19.6
92.5°	20.6	55.7	90.7	99.5	139.9	193.8	220.7	193.4	138.9	98.0	94.1
95°	49.5	113.6	177.9	193.9	344.3	544.8	645.1	575.7	436.8	332.7	320.8
97.5°	85.6	142.1	198.8	212.9	463.7	798.1	965.3	921.4	833.7	767.8	745.4
100°	113.4	164.8	216.1	229.0	507.3	878.3	1063.8	1067.0	1073.5	1078.3	1051.5
102.5°	137.1	185.1	233.0	244.9	527.2	903.6	1091.7	1147.7	1259.5	1343.4	1320.5
105°	177.4	218.0	258.6	268.7	542.0	906.5	1088.6	1214.0	1464.7	1652.8	1640.4
107.5°	218.6	256.5	294.3	303.8	544.8	866.1	1026.8	1201.7	1551.4	1813.6	1816.6
110°	246.5	280.7	314.7	323.3	540.6	830.4	975.2	1170.7	1561.7	1855.0	1867.8



TEST NUMBER: P938082

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	273.8	306.4	338.8	347.0	540.7	799.1	928.3	1128.4	1528.6	1828.7	1848.4
115°	315.0	345.1	375.2	382.7	545.8	763.2	872.0	1064.7	1450.3	1739.4	1766.7
117.5°	355.9	383.2	410.5	417.2	556.0	740.9	833.4	1007.3	1355.2	1616.1	1646.4
120°	379.6	405.3	431.0	437.3	564.2	733.4	817.9	976.9	1294.7	1533.1	1562.6
122.5°	402.8	428.7	454.6	461.0	576.1	729.4	806.1	949.2	1235.4	1450.1	1479.2
125°	438.3	461.9	485.6	491.4	592.0	726.1	793.1	914.7	1157.8	1340.2	1367.0
127.5°	467.2	491.0	514.8	520.8	608.0	724.2	782.3	886.6	1095.5	1252.1	1274.7
130°	482.7	508.4	534.1	540.4	619.7	725.4	778.2	871.1	1057.0	1196.4	1217.2
132.5°	498.7	524.4	550.1	556.5	629.2	726.1	774.6	857.8	1024.2	1149.0	1167.6
135°	522.4	545.8	569.1	575.0	639.4	725.4	768.4	838.1	977.5	1082.0	1098.1
137.5°	546.6	569.7	592.9	598.7	654.9	729.9	767.3	826.2	944.0	1032.4	1045.5
140°	566.7	588.0	609.4	614.7	664.4	730.7	763.7	814.6	916.4	992.7	1005.1
142.5°	582.2	601.9	621.6	626.6	672.3	733.3	763.7	808.5	897.8	964.8	975.4
145°	606.0	623.1	640.3	644.6	682.6	733.3	758.6	795.1	868.2	923.1	931.2
147.5°	629.7	646.4	663.1	667.3	697.7	738.2	758.6	787.3	844.9	888.0	894.7
150°	645.1	660.2	675.4	679.2	705.7	740.9	758.6	782.9	831.5	867.9	873.3
152.5°	661.1	672.6	684.1	686.9	710.8	742.6	758.6	779.3	820.8	851.9	856.0
155°	684.8	693.3	701.8	703.9	722.1	746.4	758.6	775.1	808.1	832.9	835.5
157.5°	702.4	710.6	718.8	720.9	733.5	750.2	758.6	771.4	797.1	816.3	818.2
160°	714.2	720.6	727.1	728.7	738.6	751.9	758.6	769.5	791.5	808.1	809.2
162.5°	726.1	730.9	735.7	736.9	744.1	753.8	758.6	767.8	786.4	800.4	801.4
165°	738.9	743.3	747.7	748.8	752.1	756.4	758.6	765.2	778.5	788.4	789.5
167.5°	750.9	752.9	755.0	755.5	758.3	761.9	763.7	768.1	776.8	783.4	783.9
170°	758.6	760.6	762.7	763.2	763.4	763.6	763.7	768.1	776.8	783.4	783.4
172.5°	762.7	763.1	763.6	763.7	763.7	763.7	763.7	767.1	774.0	779.2	778.8
175°	768.4	768.4	768.4	768.4	766.8	764.7	763.7	765.9	770.2	773.5	773.5
177.5°	768.4	768.4	768.4	768.4	767.2	765.5	764.7	766.4	769.9	772.5	772.0
180°	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4



TEST NUMBER: P938082

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	409.3	409.3
2.5°	436.9	434.3
5°	561.9	564.6
7.5°	756.8	755.4
10°	941.0	952.8
12.5°	1075.2	1077.9
15°	1156.9	1162.0
17.5°	1188.4	1189.7
20°	1189.7	1187.0
22.5°	1175.3	1172.6
25°	1158.1	1156.9
27.5°	1142.3	1143.6
30°	1135.7	1139.7
32.5°	1135.7	1142.3
35°	1138.4	1145.0
37.5°	1137.0	1145.0
40°	1131.9	1141.0
42.5°	1117.3	1123.9
45°	1095.0	1102.9
47.5°	1066.0	1071.3
50°	1029.2	1034.4
52.5°	983.1	984.4
55°	927.8	933.1
57.5°	868.6	869.9
60°	802.8	806.8
62.5°	733.1	733.1
65°	659.4	661.9
67.5°	583.1	589.6
70°	505.4	506.7
72.5°	429.1	429.1
75°	350.1	351.4
77.5°	275.1	275.1
80°	204.0	205.3
82.5°	140.8	143.4
85°	88.1	88.1
87.5°	40.8	36.9
90°	19.6	19.6
92.5°	78.5	62.9
95°	273.6	226.4
97.5°	655.6	565.7
100°	944.5	837.4
102.5°	1228.8	1137.1
105°	1591.2	1541.9
107.5°	1828.6	1840.5
110°	1919.1	1970.4





TEST NUMBER: P938082

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	1927.2	2006.0
115°	1876.1	1985.4
117.5°	1767.7	1888.9
120°	1680.4	1798.2
122.5°	1595.3	1711.5
125°	1474.0	1581.1
127.5°	1364.9	1455.3
130°	1300.7	1384.1
132.5°	1242.3	1317.0
135°	1162.4	1226.8
137.5°	1098.3	1151.0
140°	1054.3	1103.6
142.5°	1017.8	1060.2
145°	963.2	995.3
147.5°	921.2	947.8
150°	894.9	916.4
152.5°	872.2	888.5
155°	846.3	857.1
157.5°	825.8	833.4
160°	813.5	817.9
162.5°	805.6	809.6
165°	793.9	798.3
167.5°	785.6	787.4
170°	783.4	783.4
172.5°	777.2	775.6
175°	773.5	773.5
177.5°	770.2	768.4
180°	768.4	768.4



TEST NUMBER: P938082  
 CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-4-2700K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.52	5.32	5.56	6.37	7.78	17.66	18.45	18.70	19.50	20.92
	3H	5.22	5.94	6.27	6.99	8.43	19.48	20.19	20.52	21.25	22.69
	4H	5.51	6.19	6.58	7.26	8.70	20.11	20.79	21.17	21.85	23.29
	6H	5.76	6.39	6.83	7.45	8.91	20.52	21.15	21.59	22.21	23.67
	8H	5.83	6.42	6.90	7.51	8.96	20.63	21.23	21.71	22.31	23.76
	12H	5.84	6.41	6.92	7.49	8.96	20.69	21.26	21.77	22.34	23.81
4H	2H	11.70	12.38	12.77	13.44	14.89	17.92	18.60	18.99	19.66	21.11
	3H	13.26	13.83	14.34	14.92	16.38	19.95	20.52	21.02	21.61	23.06
	4H	13.36	13.88	14.44	14.96	16.44	20.70	21.22	21.78	22.30	23.78
	6H	13.36	13.81	14.45	14.92	16.39	21.23	21.67	22.32	22.78	24.25
	8H	13.34	13.76	14.43	14.85	16.34	21.38	21.80	22.47	22.89	24.38
	12H	13.29	13.67	14.40	14.78	16.27	21.46	21.84	22.57	22.95	24.44
8H	4H	14.78	15.20	15.88	16.30	17.79	20.76	21.18	21.85	22.27	23.76
	6H	15.02	15.37	16.14	16.51	17.99	21.37	21.72	22.49	22.86	24.34
	8H	15.04	15.35	16.16	16.46	17.97	21.58	21.89	22.70	23.01	24.51
	12H	15.01	15.28	16.13	16.39	17.93	21.72	21.98	22.84	23.10	24.64
12H	4H	14.92	15.30	16.03	16.41	17.90	20.71	21.09	21.82	22.20	23.69
	6H	15.28	15.58	16.40	16.70	18.21	21.35	21.66	22.47	22.78	24.28
	8H	15.34	15.61	16.47	16.73	18.27	21.57	21.84	22.70	22.96	24.50