

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936388

Luminaire Tested: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936388  
REPORT IS A COMBINATION OF REPORTS P933446 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4990.1 lumens  
Efficiency: N/A  
Efficacy: 110.9 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936388  
CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P936388

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	71
1	102	97	93	89	96	92	88	85	82	79	77	74	71	69	66	64	62	62	62	62	58
2	92	84	77	71	87	79	73	68	71	66	62	64	60	57	57	54	51	51	51	51	48
3	83	73	65	58	79	69	62	56	62	56	51	56	51	47	50	46	43	43	43	43	39
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	40	36	36	36	36	33
5	69	57	48	41	65	54	46	40	49	42	37	44	38	34	39	34	31	31	31	31	28
6	64	51	42	35	60	48	40	34	43	37	32	39	33	29	35	30	27	27	27	27	24
7	59	45	37	31	55	43	35	30	39	32	27	35	30	25	32	27	23	23	23	23	21
8	54	41	33	27	51	39	31	26	36	29	24	32	26	22	29	24	21	21	21	21	18
9	51	37	29	24	48	36	28	23	32	26	21	29	24	20	26	22	18	18	18	18	16
10	47	34	26	21	45	33	25	21	30	23	19	27	22	18	24	20	16	16	16	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2846	2846	2846
5°	2779	3288	3825
10°	2520	4792	6341
15°	2140	6259	7657
20°	1742	7251	7804
25°	1453	7586	7645
30°	1224	7633	7631
35°	1082	7504	7828
40°	942	7336	8032
45°	853	7213	8063
50°	781	7102	7930
55°	748	6941	7578
60°	765	6633	7022
65°	794	6166	6260
70°	844	5374	5288
75°	932	4378	4127
80°	1012	3032	2781
85°	882	1605	1423

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 8063 cd/sqm



TEST NUMBER: P936388

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.5	1.2
10°-20°	263.7	5.3
20°-30°	461.3	9.2
30°-40°	593.8	11.9
40°-50°	663.2	13.3
50°-60°	635.2	12.7
60°-70°	503.4	10.1
70°-80°	296.0	5.9
80°-90°	83.1	1.7
90°-100°	107.6	2.2
100°-110°	282.9	5.7
110°-120°	293.3	5.9
120°-130°	235.3	4.7
130°-140°	184.6	3.7
140°-150°	141.7	2.8
150°-160°	102.0	2.0
160°-170°	62.4	1.3
170°-180°	21.1	0.4
0°-30°	784.5	15.7
0°-40°	1378.3	27.6
0°-60°	2676.8	53.6
0°-90°	3559.3	71.3
90°-120°	683.7	13.7
90°-150°	1245.2	25.0
90°-180°	1431.0	28.7
0°-180°	4990.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	460	460	460	460	460	
5°	448	481	541	612	634	41
15°	336	620	1044	1266	1306	93
25°	214	702	1244	1299	1300	99
35°	145	672	1172	1238	1287	90
45°	99	535	1035	1186	1240	77
55°	71	340	878	1020	1049	65
65°	56	180	652	734	744	56
75°	41	111	358	393	395	43
85°	15	34	89	98	99	16
90°	2	4	11	6	6	2
95°	14	56	185	96	65	16
105°	51	77	313	475	443	54
115°	90	110	250	500	570	89
125°	126	141	228	385	454	112
135°	150	165	221	311	352	116
145°	174	185	218	265	286	109
155°	197	202	218	239	246	90
165°	212	215	218	226	229	60
175°	221	221	219	222	222	21
180°	221	221	221	221	221	



TEST NUMBER: P936388

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	460.0	460.0	460.0	460.0	460.0	460.0	460.0	460.0	460.0	460.0	460.0
2.5°	460.0	460.0	462.9	464.4	467.4	468.8	471.8	474.8	483.6	485.1	488.1
5°	448.1	454.1	473.3	480.7	501.4	529.5	541.3	560.5	600.5	612.3	619.7
7.5°	430.4	443.7	491.0	502.9	554.6	628.6	659.6	701.0	764.6	795.7	820.8
10°	402.3	430.4	514.7	542.8	627.1	739.5	797.2	854.9	951.0	993.9	1010.2
12.5°	371.2	417.1	539.8	578.3	699.6	863.7	933.2	996.8	1106.3	1164.1	1172.9
15°	335.7	397.9	563.5	619.7	776.5	967.3	1044.2	1122.7	1224.7	1266.1	1276.5
17.5°	304.7	383.1	585.7	644.8	835.6	1060.4	1138.9	1204.0	1286.8	1314.9	1322.3
20°	266.2	359.4	600.5	677.4	897.8	1128.6	1204.0	1254.3	1310.5	1328.2	1331.2
22.5°	238.1	334.3	609.3	689.2	939.2	1170.0	1233.6	1273.5	1312.0	1317.9	1319.4
25°	214.5	306.2	607.9	702.5	974.7	1195.1	1243.9	1273.5	1295.7	1298.7	1298.7
27.5°	192.3	275.1	602.0	705.5	1001.3	1201.0	1239.5	1260.2	1270.6	1276.5	1276.5
30°	173.0	245.5	587.2	699.6	1013.1	1195.1	1226.2	1236.5	1246.9	1255.8	1260.2
32.5°	158.3	217.4	565.0	687.7	1014.6	1180.3	1202.5	1208.4	1223.2	1243.9	1251.3
35°	144.9	189.3	539.8	671.5	1005.7	1156.7	1171.5	1177.4	1207.0	1238.0	1248.4
37.5°	131.6	168.6	507.3	643.4	992.4	1128.6	1138.9	1149.3	1195.1	1232.1	1243.9
40°	118.3	150.9	468.8	612.3	971.7	1094.5	1103.3	1119.6	1180.3	1223.2	1235.1
42.5°	108.0	136.1	427.4	579.8	945.1	1056.0	1069.3	1093.0	1162.6	1208.4	1221.8
45°	99.1	121.3	383.1	535.4	911.1	1016.1	1035.3	1067.8	1141.9	1186.3	1198.1
47.5°	90.2	110.9	337.2	489.5	874.1	976.1	1001.3	1038.3	1113.7	1156.7	1167.0
50°	82.8	100.6	291.4	440.7	834.2	933.2	962.8	1001.3	1078.2	1118.1	1131.5
52.5°	76.9	91.7	248.5	391.9	788.3	888.9	922.9	962.8	1035.3	1073.8	1082.6
55°	71.0	84.3	211.5	340.2	741.0	841.6	878.5	917.0	988.0	1020.5	1026.4
57.5°	68.0	78.4	180.4	291.4	690.7	788.3	829.7	865.2	931.8	956.9	962.8
60°	63.6	74.0	156.8	250.0	636.0	738.0	773.5	809.0	865.2	885.9	890.4
62.5°	59.2	71.0	139.0	210.0	579.8	678.9	714.4	746.9	794.2	809.0	814.9
65°	56.2	68.0	125.7	180.4	522.1	616.7	652.2	680.3	718.8	733.6	736.5
67.5°	53.2	65.1	115.4	155.3	464.4	554.6	581.2	607.9	637.4	652.2	653.7
70°	48.8	62.1	106.5	137.5	405.2	483.6	505.8	533.9	557.6	565.0	569.4
72.5°	45.8	57.7	100.6	124.2	344.6	415.6	436.3	452.6	473.3	480.7	480.7
75°	41.4	51.8	94.7	110.9	282.5	340.2	357.9	374.2	390.5	393.4	389.0
77.5°	37.0	45.8	81.3	93.2	220.4	269.2	284.0	292.8	306.2	309.1	310.6
80°	31.1	39.9	63.6	72.5	159.7	198.2	208.5	215.9	227.8	227.8	230.7
82.5°	23.7	31.1	45.8	51.8	108.0	136.1	144.9	149.4	156.8	156.8	156.8
85°	14.8	19.2	29.6	34.0	65.1	82.8	88.7	90.2	96.1	97.6	97.6
87.5°	7.4	10.4	19.2	20.7	34.0	42.9	42.9	45.8	45.8	44.4	42.9
90°	1.5	2.7	3.8	4.1	6.5	9.7	11.2	10.0	7.5	5.6	5.6
92.5°	5.9	16.0	26.0	28.6	40.2	55.7	63.4	55.5	39.8	28.1	27.0
95°	14.2	32.6	51.1	55.7	98.9	156.5	185.3	165.4	125.4	95.5	92.2
97.5°	24.6	40.8	57.1	61.1	133.2	229.2	277.3	264.6	239.5	220.6	214.2
100°	32.6	47.3	62.1	65.8	145.7	252.3	305.6	306.4	308.3	309.7	302.0
102.5°	39.4	53.2	66.9	70.4	151.4	259.5	313.5	329.6	361.8	385.9	379.3
105°	51.0	62.6	74.2	77.2	155.7	260.3	312.7	348.6	420.7	474.8	471.2
107.5°	62.8	73.7	84.5	87.3	156.5	248.8	294.9	345.2	445.7	521.0	521.9
110°	70.8	80.7	90.4	92.9	155.3	238.5	280.1	336.3	448.6	532.8	536.5



TEST NUMBER: P936388

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	78.7	88.0	97.3	99.7	155.3	229.5	266.6	324.1	439.1	525.2	530.9
115°	90.5	99.2	107.8	109.9	156.8	219.2	250.4	305.9	416.6	499.6	507.5
117.5°	102.2	110.0	117.8	119.8	159.6	212.8	239.4	289.4	389.3	464.2	472.9
120°	109.1	116.4	123.7	125.6	162.1	210.7	235.0	280.6	371.9	440.4	448.9
122.5°	115.7	123.2	130.5	132.4	165.5	209.5	231.5	272.6	354.9	416.6	425.0
125°	125.9	132.7	139.5	141.2	170.1	208.6	227.9	262.8	332.7	385.0	392.7
127.5°	134.2	141.0	147.9	149.6	174.6	208.0	224.7	254.7	314.7	359.7	366.2
130°	138.6	146.0	153.3	155.2	178.0	208.3	223.5	250.2	303.6	343.6	349.6
132.5°	143.3	150.7	158.0	159.8	180.7	208.6	222.5	246.4	294.2	330.0	335.3
135°	150.1	156.8	163.5	165.2	183.7	208.4	220.8	240.8	280.8	310.8	315.4
137.5°	157.1	163.7	170.3	172.0	188.1	209.7	220.5	237.4	271.2	296.6	300.3
140°	162.8	168.9	175.0	176.6	190.9	209.9	219.4	234.0	263.3	285.2	288.7
142.5°	167.2	172.8	178.6	179.9	193.1	210.6	219.4	232.2	257.9	277.2	280.2
145°	174.0	179.0	183.9	185.2	196.1	210.6	217.9	228.4	249.4	265.1	267.4
147.5°	180.8	185.7	190.5	191.7	200.5	212.1	217.9	226.2	242.7	255.1	257.0
150°	185.3	189.6	194.0	195.1	202.7	212.9	217.9	224.9	238.8	249.3	250.8
152.5°	189.9	193.2	196.5	197.3	204.2	213.4	217.9	223.8	235.8	244.7	245.9
155°	196.7	199.2	201.6	202.2	207.5	214.5	217.9	222.6	232.1	239.2	240.0
157.5°	201.7	204.1	206.5	207.1	210.7	215.5	217.9	221.6	228.9	234.5	235.1
160°	205.2	207.1	208.8	209.3	212.2	216.0	217.9	221.1	227.4	232.1	232.4
162.5°	208.5	209.9	211.3	211.7	213.8	216.5	217.9	220.6	225.9	229.9	230.2
165°	212.3	213.5	214.8	215.0	216.0	217.3	217.9	219.8	223.6	226.5	226.8
167.5°	215.6	216.2	216.8	217.0	217.8	218.9	219.4	220.7	223.1	225.0	225.1
170°	217.9	218.5	219.1	219.2	219.3	219.4	219.4	220.7	223.1	225.0	225.0
172.5°	219.1	219.2	219.4	219.4	219.4	219.4	219.4	220.4	222.3	223.8	223.7
175°	220.8	220.8	220.8	220.8	220.3	219.7	219.4	220.0	221.3	222.2	222.2
177.5°	220.8	220.8	220.8	220.8	220.4	219.9	219.7	220.2	221.2	221.9	221.8
180°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8



TEST NUMBER: P936388

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	460.0	460.0
2.5°	491.0	488.1
5°	631.5	634.5
7.5°	850.4	848.9
10°	1057.5	1070.8
12.5°	1208.4	1211.4
15°	1300.1	1306.1
17.5°	1335.6	1337.1
20°	1337.1	1334.2
22.5°	1320.8	1317.9
25°	1301.6	1300.1
27.5°	1283.9	1285.3
30°	1276.5	1280.9
32.5°	1276.5	1283.9
35°	1279.4	1286.8
37.5°	1278.0	1286.8
40°	1272.0	1282.4
42.5°	1255.8	1263.2
45°	1230.6	1239.5
47.5°	1198.1	1204.0
50°	1156.7	1162.6
52.5°	1104.8	1106.3
55°	1042.7	1048.6
57.5°	976.1	977.6
60°	902.2	906.6
62.5°	823.8	823.8
65°	741.0	743.9
67.5°	655.2	662.6
70°	567.9	569.4
72.5°	482.2	482.2
75°	393.4	394.9
77.5°	309.1	309.1
80°	229.2	230.7
82.5°	158.3	161.2
85°	99.1	99.1
87.5°	45.8	41.4
90°	5.6	5.6
92.5°	22.5	18.0
95°	78.6	65.1
97.5°	188.3	162.5
100°	271.3	240.6
102.5°	353.0	326.7
105°	457.1	442.9
107.5°	525.2	528.7
110°	551.3	566.1





TEST NUMBER: P936388

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	553.5	576.2
115°	538.8	570.3
117.5°	507.8	542.6
120°	482.7	516.6
122.5°	458.3	491.6
125°	423.4	454.2
127.5°	392.1	418.1
130°	373.6	397.6
132.5°	356.8	378.3
135°	333.9	352.4
137.5°	315.5	330.6
140°	302.8	317.0
142.5°	292.3	304.6
145°	276.7	285.9
147.5°	264.6	272.2
150°	257.1	263.3
152.5°	250.5	255.3
155°	243.0	246.2
157.5°	237.2	239.4
160°	233.7	235.0
162.5°	231.4	232.6
165°	228.1	229.3
167.5°	225.7	226.2
170°	225.0	225.0
172.5°	223.2	222.8
175°	222.2	222.2
177.5°	221.3	220.8
180°	220.8	220.8



TEST NUMBER: P936388

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-6-3000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.37	7.53	7.11	8.30	9.22	19.54	20.69	20.28	21.46	22.39
	3H	7.10	8.14	7.85	8.92	9.88	21.39	22.44	22.15	23.21	24.17
	4H	7.41	8.40	8.18	9.19	10.15	22.05	23.03	22.82	23.82	24.79
	6H	7.68	8.59	8.46	9.39	10.37	22.49	23.40	23.28	24.20	25.18
	8H	7.75	8.62	8.55	9.44	10.42	22.62	23.49	23.41	24.30	25.29
	12H	7.78	8.61	8.58	9.42	10.44	22.69	23.52	23.50	24.33	25.35
4H	2H	13.62	14.60	14.39	15.39	16.36	19.85	20.83	20.62	21.62	22.59
	3H	15.21	16.04	16.00	16.86	17.84	21.92	22.74	22.70	23.56	24.55
	4H	15.32	16.07	16.12	16.89	17.91	22.69	23.45	23.50	24.27	25.28
	6H	15.35	16.00	16.17	16.85	17.86	23.24	23.90	24.06	24.74	25.76
	8H	15.33	15.94	16.16	16.79	17.82	23.41	24.02	24.24	24.87	25.90
	12H	15.30	15.86	16.15	16.72	17.76	23.52	24.07	24.36	24.93	25.97
8H	4H	16.78	17.40	17.61	18.24	19.27	22.78	23.39	23.60	24.23	25.26
	6H	17.04	17.55	17.89	18.43	19.47	23.42	23.93	24.27	24.81	25.84
	8H	17.06	17.52	17.93	18.39	19.44	23.64	24.09	24.50	24.97	26.02
	12H	17.05	17.44	17.91	18.32	19.42	23.79	24.19	24.66	25.06	26.17
12H	4H	16.94	17.49	17.79	18.36	19.40	22.74	23.30	23.59	24.16	25.20
	6H	17.30	17.76	18.17	18.63	19.68	23.40	23.86	24.27	24.74	25.78
	8H	17.39	17.79	18.25	18.66	19.76	23.65	24.05	24.51	24.92	26.02