

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937688

Luminaire Tested: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937688
REPORT IS A COMBINATION OF REPORTS P933575 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10646.8 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 87
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937688
CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P937688

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	96	91	87	84	88	84	80	77	69	67	65	56	55	53	44	43	42	36
2	87	79	73	68	79	73	67	63	60	56	53	49	46	43	38	36	34	30
3	79	69	62	56	72	63	57	52	53	48	44	43	39	36	33	31	29	24
4	72	61	53	46	65	56	49	43	46	41	37	38	34	30	29	27	24	20
5	66	54	46	39	60	49	42	37	41	36	31	33	29	26	26	23	21	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	20	18	15
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16	13
8	51	39	31	26	47	36	29	24	30	24	20	25	20	17	19	16	14	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10
10	44	32	25	20	41	30	23	19	25	20	16	21	16	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3759	3759	3759
5°	3671	4343	5053
10°	3329	6330	8377
15°	2828	8269	10115
20°	2301	9580	10310
25°	1919	10023	10100
30°	1618	10083	10081
35°	1430	9913	10342
40°	1245	9693	10611
45°	1126	9531	10652
50°	1032	9384	10476
55°	988	9171	10012
60°	1010	8764	9278
65°	1049	8148	8270
70°	1116	7101	6987
75°	1231	5785	5453
80°	1334	4007	3675
85°	1163	2121	1880

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10652 cd/sqm



TEST NUMBER: P937688

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.6	0.7
10°-20°	348.4	3.3
20°-30°	609.4	5.7
30°-40°	784.5	7.4
40°-50°	876.2	8.2
50°-60°	839.2	7.9
60°-70°	665.1	6.2
70°-80°	391.1	3.7
80°-90°	112.1	1.1
90°-100°	446.8	4.2
100°-110°	1174.7	11.0
110°-120°	1218.0	11.4
120°-130°	977.0	9.2
130°-140°	766.6	7.2
140°-150°	588.4	5.5
150°-160°	423.7	4.0
160°-170°	259.3	2.4
170°-180°	87.6	0.8
0°-30°	1036.4	9.7
0°-40°	1820.9	17.1
0°-60°	3536.4	33.2
0°-90°	4704.7	44.2
90°-120°	2839.5	26.7
90°-150°	5171.5	48.6
90°-180°	5942.0	55.8
0°-180°	10646.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	608	608	608	608	608	
5°	592	635	715	809	838	55
15°	444	819	1380	1673	1725	123
25°	283	928	1643	1716	1718	131
35°	192	887	1548	1636	1700	120
45°	131	707	1368	1567	1638	101
55°	94	449	1161	1348	1385	85
65°	74	238	862	969	983	74
75°	55	146	473	520	522	57
85°	20	45	117	129	131	21
90°	6	17	47	23	23	6
95°	59	231	770	397	270	66
105°	212	320	1299	1972	1839	224
115°	376	456	1040	2075	2368	371
125°	523	586	946	1599	1886	464
135°	623	686	917	1291	1464	482
145°	723	769	905	1101	1187	453
155°	817	840	905	994	1022	375
165°	882	893	905	941	952	249
175°	917	917	911	923	923	87
180°	917	917	917	917	917	



TEST NUMBER: P937688

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	607.7	607.7	607.7	607.7	607.7	607.7	607.7	607.7	607.7	607.7	607.7
2.5°	607.7	607.7	611.6	613.6	617.4	619.4	623.3	627.3	638.9	640.9	644.8
5°	592.1	599.9	625.3	635.1	662.4	699.6	715.1	740.6	793.3	809.0	818.8
7.5°	568.6	586.2	648.8	664.4	732.8	830.5	871.5	926.2	1010.3	1051.3	1084.5
10°	531.5	568.6	680.0	717.1	828.5	977.0	1053.2	1129.5	1256.5	1313.2	1334.6
12.5°	490.4	551.1	713.3	764.1	924.3	1141.2	1233.0	1317.0	1461.6	1537.9	1549.6
15°	443.6	525.6	744.5	818.8	1025.8	1278.0	1379.6	1483.1	1617.9	1672.7	1686.4
17.5°	402.6	506.1	773.8	852.0	1104.0	1401.1	1504.6	1590.6	1700.1	1737.1	1746.9
20°	351.7	474.9	793.3	895.0	1186.2	1490.9	1590.6	1657.1	1731.3	1754.8	1758.6
22.5°	314.6	441.6	805.1	910.6	1240.8	1545.7	1629.7	1682.4	1733.3	1741.1	1743.1
25°	283.4	404.5	803.1	928.2	1287.7	1578.9	1643.4	1682.4	1711.8	1715.6	1715.6
27.5°	254.0	363.4	795.3	932.1	1322.9	1586.7	1637.5	1664.9	1678.6	1686.4	1686.4
30°	228.7	324.4	775.8	924.3	1338.5	1578.9	1619.9	1633.6	1647.3	1658.9	1664.9
32.5°	209.1	287.2	746.4	908.6	1340.5	1559.4	1588.6	1596.4	1616.0	1643.4	1653.1
35°	191.5	250.1	713.3	887.1	1328.7	1528.1	1547.6	1555.4	1594.5	1635.6	1649.2
37.5°	173.9	222.7	670.3	850.0	1311.2	1490.9	1504.6	1518.3	1578.9	1627.7	1643.4
40°	156.3	199.3	619.4	809.0	1283.8	1446.0	1457.7	1479.2	1559.4	1616.0	1631.6
42.5°	142.7	179.7	564.7	766.0	1248.7	1395.2	1412.7	1444.0	1535.9	1596.4	1614.1
45°	130.9	160.2	506.1	707.4	1203.7	1342.4	1367.9	1410.9	1508.5	1567.1	1582.8
47.5°	119.2	146.5	445.6	646.8	1154.8	1289.7	1322.9	1371.7	1471.4	1528.1	1541.7
50°	109.4	132.9	384.9	582.3	1102.1	1233.0	1272.1	1322.9	1424.5	1477.2	1494.9
52.5°	101.7	121.2	328.2	517.8	1041.5	1174.4	1219.3	1272.1	1367.9	1418.7	1430.4
55°	93.8	111.4	279.4	449.4	979.0	1111.8	1160.7	1211.5	1305.3	1348.3	1356.1
57.5°	89.9	103.5	238.4	384.9	912.5	1041.5	1096.2	1143.2	1231.0	1264.2	1272.1
60°	84.0	97.7	207.2	330.2	840.3	975.1	1022.0	1068.8	1143.2	1170.5	1176.3
62.5°	78.2	93.8	183.7	277.5	766.0	896.9	943.8	986.8	1049.3	1068.8	1076.7
65°	74.2	89.9	166.1	238.4	689.8	814.8	861.8	898.8	949.7	969.2	973.1
67.5°	70.3	86.0	152.4	205.2	613.6	732.8	767.9	803.1	842.2	861.8	863.7
70°	64.5	82.0	140.7	181.7	535.4	638.9	668.3	705.4	736.6	746.4	752.3
72.5°	60.5	76.2	132.9	164.2	455.3	549.1	576.4	597.9	625.3	635.1	635.1
75°	54.7	68.4	125.0	146.5	373.2	449.4	472.9	494.4	515.9	519.8	513.9
77.5°	48.8	60.5	107.5	123.2	291.2	355.7	375.2	386.9	404.5	408.4	410.4
80°	41.0	52.8	84.0	95.7	211.0	261.9	275.5	285.2	300.9	300.9	304.9
82.5°	31.3	41.0	60.5	68.4	142.7	179.7	191.5	197.4	207.2	207.2	207.2
85°	19.5	25.4	39.0	45.0	86.0	109.4	117.2	119.2	127.0	129.0	129.0
87.5°	9.8	13.7	25.4	27.3	45.0	56.7	56.7	60.5	60.5	58.7	56.7
90°	6.1	11.0	16.0	17.3	27.1	40.2	46.7	41.5	31.2	23.4	23.4
92.5°	24.6	66.5	108.3	118.7	166.9	231.1	263.3	230.7	165.6	116.8	112.2
95°	59.1	135.6	212.2	231.3	410.8	650.0	769.6	686.7	521.0	396.8	382.7
97.5°	102.1	169.7	237.2	254.1	553.2	952.2	1151.6	1099.3	994.6	916.0	889.2
100°	135.4	196.6	257.8	273.1	605.1	1047.7	1269.1	1272.9	1280.6	1286.3	1254.4
102.5°	163.7	220.9	278.0	292.3	629.0	1077.9	1302.3	1369.1	1502.5	1602.5	1575.2
105°	211.6	260.0	308.4	320.5	646.6	1081.3	1298.7	1448.2	1747.3	1971.6	1956.9
107.5°	260.8	306.0	351.1	362.4	649.9	1033.1	1224.8	1433.4	1850.6	2163.6	2167.1
110°	294.0	334.7	375.6	385.7	644.9	990.5	1163.3	1396.5	1862.9	2212.8	2228.1



TEST NUMBER: P937688

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	326.7	365.5	404.4	414.0	645.1	953.3	1107.3	1346.0	1823.4	2181.4	2204.9
115°	375.9	411.7	447.4	456.4	651.1	910.5	1040.2	1270.2	1730.1	2075.0	2107.7
117.5°	424.5	457.0	489.5	497.6	663.1	883.8	994.1	1201.6	1616.6	1927.9	1964.1
120°	452.8	483.4	514.0	521.7	673.0	874.8	975.6	1165.3	1544.5	1828.9	1864.0
122.5°	480.5	511.3	542.3	550.0	687.1	870.0	961.5	1132.3	1473.8	1729.8	1764.5
125°	522.9	551.1	579.3	586.3	706.3	866.2	946.2	1091.2	1381.3	1598.9	1630.8
127.5°	557.4	585.8	614.3	621.4	725.3	863.9	933.2	1057.8	1306.8	1493.7	1520.6
130°	575.8	606.5	637.1	644.7	739.3	865.3	928.3	1039.1	1260.9	1427.2	1452.1
132.5°	594.9	625.5	656.1	663.8	750.5	866.2	924.0	1023.3	1221.8	1370.6	1392.9
135°	623.2	651.1	679.0	686.0	762.9	865.3	916.6	999.7	1165.9	1290.7	1309.9
137.5°	652.0	679.6	707.4	714.3	781.3	870.7	915.4	985.7	1126.2	1231.6	1247.3
140°	676.1	701.5	727.0	733.3	792.5	871.5	911.1	971.8	1093.2	1184.2	1198.9
142.5°	694.5	718.1	741.6	747.5	802.0	874.7	911.1	964.4	1071.0	1151.0	1163.6
145°	722.8	743.3	763.9	769.0	814.3	874.8	905.0	948.5	1035.8	1101.2	1110.7
147.5°	751.1	771.1	791.0	796.0	832.3	880.7	905.0	939.3	1007.9	1059.4	1067.2
150°	769.6	787.6	805.7	810.2	841.7	883.9	905.0	933.9	991.8	1035.3	1041.7
152.5°	788.7	802.4	816.0	819.5	848.0	885.9	905.0	929.7	979.2	1016.3	1021.1
155°	817.0	827.1	837.1	839.7	861.5	890.5	905.0	924.7	964.0	993.5	996.7
157.5°	837.9	847.8	857.5	860.0	875.0	895.0	905.0	920.2	950.9	973.9	976.1
160°	852.0	859.7	867.4	869.3	881.2	897.1	905.0	918.1	944.3	964.0	965.3
162.5°	866.2	871.9	877.6	879.1	887.7	899.2	905.0	916.0	938.2	954.7	955.9
165°	881.6	886.7	891.9	893.2	897.2	902.4	905.0	912.8	928.7	940.6	941.9
167.5°	895.7	898.1	900.6	901.2	904.5	908.9	911.1	916.3	926.6	934.4	935.0
170°	905.0	907.4	909.9	910.5	910.7	911.0	911.1	916.3	926.6	934.4	934.4
172.5°	909.9	910.4	911.0	911.1	911.1	911.1	911.1	915.2	923.4	929.5	929.0
175°	916.6	916.6	916.6	916.6	914.7	912.2	911.1	913.6	918.9	922.8	922.8
177.5°	916.6	916.6	916.6	916.6	915.2	913.3	912.3	914.4	918.5	921.5	920.9
180°	916.6	916.6	916.6	916.6	916.6	916.6	916.6	916.6	916.6	916.6	916.6



TEST NUMBER: P937688

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	607.7	607.7
2.5°	648.8	644.8
5°	834.4	838.3
7.5°	1123.5	1121.7
10°	1397.2	1414.7
12.5°	1596.4	1600.4
15°	1717.6	1725.4
17.5°	1764.5	1766.4
20°	1766.4	1762.6
22.5°	1744.9	1741.1
25°	1719.6	1717.6
27.5°	1696.1	1698.1
30°	1686.4	1692.2
32.5°	1686.4	1696.1
35°	1690.3	1700.1
37.5°	1688.3	1700.1
40°	1680.4	1694.1
42.5°	1658.9	1668.8
45°	1625.8	1637.5
47.5°	1582.8	1590.6
50°	1528.1	1535.9
52.5°	1459.7	1461.6
55°	1377.6	1385.4
57.5°	1289.7	1291.7
60°	1192.0	1197.8
62.5°	1088.4	1088.4
65°	979.0	982.8
67.5°	865.6	875.4
70°	750.3	752.3
72.5°	637.1	637.1
75°	519.8	521.7
77.5°	408.4	408.4
80°	302.9	304.9
82.5°	209.1	213.0
85°	130.9	130.9
87.5°	60.5	54.7
90°	23.4	23.4
92.5°	93.6	75.0
95°	326.4	270.1
97.5°	782.0	674.8
100°	1126.7	999.0
102.5°	1465.8	1356.4
105°	1898.1	1839.4
107.5°	2181.4	2195.6
110°	2289.4	2350.6



TEST NUMBER: P937688

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2299.0	2393.0
115°	2238.0	2368.5
117.5°	2108.8	2253.4
120°	2004.6	2145.1
122.5°	1903.2	2041.8
125°	1758.4	1886.1
127.5°	1628.4	1736.1
130°	1551.7	1651.2
132.5°	1482.1	1571.2
135°	1386.7	1463.5
137.5°	1310.2	1373.1
140°	1257.7	1316.5
142.5°	1214.3	1264.8
145°	1149.1	1187.3
147.5°	1099.0	1130.7
150°	1067.4	1093.2
152.5°	1040.5	1060.0
155°	1009.6	1022.4
157.5°	985.1	994.1
160°	970.5	975.6
162.5°	960.9	965.8
165°	947.2	952.3
167.5°	937.2	939.4
170°	934.4	934.4
172.5°	927.1	925.3
175°	922.8	922.8
177.5°	918.8	916.6
180°	916.6	916.6



TEST NUMBER: P937688
 CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-6-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.05	5.89	6.04	6.90	8.25	18.21	19.06	19.21	20.07	21.42
	3H	5.75	6.51	6.76	7.53	8.90	20.04	20.80	21.05	21.83	23.20
	4H	6.05	6.77	7.07	7.79	9.17	20.69	21.40	21.71	22.43	23.81
	6H	6.30	6.96	7.33	7.99	9.38	21.11	21.77	22.14	22.80	24.19
	8H	6.37	7.00	7.40	8.04	9.43	21.23	21.86	22.27	22.91	24.29
	12H	6.38	6.98	7.42	8.02	9.43	21.29	21.90	22.34	22.94	24.35
4H	2H	12.25	12.97	13.28	14.00	15.37	18.48	19.20	19.51	20.23	21.61
	3H	13.82	14.42	14.85	15.47	16.87	20.52	21.13	21.56	22.18	23.57
	4H	13.91	14.46	14.96	15.51	16.92	21.29	21.84	22.33	22.88	24.30
	6H	13.92	14.40	14.98	15.47	16.87	21.82	22.30	22.87	23.37	24.77
	8H	13.90	14.34	14.95	15.41	16.83	21.98	22.42	23.03	23.49	24.91
	12H	13.85	14.26	14.93	15.33	16.76	22.07	22.47	23.14	23.55	24.98
8H	4H	15.35	15.80	16.41	16.86	18.28	21.35	21.79	22.40	22.85	24.28
	6H	15.59	15.96	16.67	17.07	18.49	21.97	22.34	23.05	23.44	24.86
	8H	15.61	15.94	16.70	17.02	18.46	22.19	22.51	23.27	23.60	25.04
	12H	15.58	15.86	16.67	16.95	18.43	22.33	22.61	23.42	23.70	25.18
12H	4H	15.49	15.90	16.57	16.97	18.40	21.30	21.70	22.37	22.78	24.21
	6H	15.85	16.18	16.94	17.26	18.70	21.95	22.28	23.04	23.36	24.80
	8H	15.92	16.20	17.01	17.29	18.77	22.18	22.46	23.27	23.55	25.03