

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936793

Luminaire Tested: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936793
REPORT IS A COMBINATION OF REPORTS P933486 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8672.8 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936793
CATALOG NUMBER: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P936793

CATALOG NUMBER: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	98	94	89	86	91	87	83	80	75	72	69	63	61	59	53	51	50	45
2	89	81	74	69	82	75	70	65	65	60	56	55	51	49	45	43	41	37
3	81	71	63	57	74	66	59	53	56	51	47	48	44	40	40	37	34	30
4	73	62	54	47	68	58	50	45	50	44	39	42	38	34	35	32	29	25
5	67	55	46	40	62	51	44	38	44	38	33	37	33	29	31	28	25	21
6	62	49	40	34	57	46	38	32	39	33	29	33	29	25	28	24	21	18
7	57	44	36	30	52	41	34	28	35	29	25	30	25	22	25	22	19	16
8	53	40	32	26	49	37	30	25	32	26	22	27	23	19	23	19	16	14
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15	12
10	46	33	25	20	42	31	24	19	27	21	17	23	18	15	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2845	2845	2845
5°	2780	3289	3825
10°	2522	4794	6341
15°	2143	6264	7657
20°	1745	7258	7803
25°	1455	7596	7645
30°	1227	7644	7631
35°	1085	7517	7828
40°	946	7352	8032
45°	856	7231	8063
50°	785	7122	7930
55°	753	6963	7578
60°	770	6657	7023
65°	801	6192	6260
70°	854	5400	5288
75°	945	4403	4127
80°	1033	3054	2781
85°	918	1620	1423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8063 cd/sqm



TEST NUMBER: P936793

CATALOG NUMBER: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.3	0.9
10°-20°	351.6	4.1
20°-30°	615.0	7.1
30°-40°	791.7	9.1
40°-50°	884.3	10.2
50°-60°	847.0	9.8
60°-70°	671.2	7.7
70°-80°	394.7	4.6
80°-90°	112.0	1.3
90°-100°	295.2	3.4
100°-110°	776.1	8.9
110°-120°	804.7	9.3
120°-130°	645.5	7.4
130°-140°	506.5	5.8
140°-150°	388.8	4.5
150°-160°	280.0	3.2
160°-170°	171.3	2.0
170°-180°	57.9	0.7
0°-30°	1046.0	12.1
0°-40°	1837.7	21.2
0°-60°	3569.1	41.2
0°-90°	4746.9	54.7
90°-120°	1876.0	21.6
90°-150°	3416.8	39.4
90°-180°	3926.0	45.3
0°-180°	8672.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	613	613	613	613	613	
5°	598	641	722	816	846	55
15°	448	826	1392	1688	1741	125
25°	286	937	1659	1732	1734	132
35°	193	895	1562	1651	1716	121
45°	132	714	1380	1582	1653	102
55°	95	454	1172	1361	1398	86
65°	75	241	870	978	992	74
75°	55	148	477	525	526	58
85°	20	45	118	130	132	21
90°	4	11	31	16	16	5
95°	39	153	508	262	178	43
105°	140	212	858	1303	1215	148
115°	248	302	687	1371	1565	245
125°	346	387	625	1056	1246	307
135°	412	453	606	853	967	319
145°	478	508	598	728	784	299
155°	540	555	598	656	676	248
165°	582	590	598	622	629	164
175°	606	606	602	610	610	57
180°	606	606	606	606	606	



TEST NUMBER: P936793

CATALOG NUMBER: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	613.3	613.3	613.3	613.3	613.3	613.3	613.3	613.3	613.3	613.3	613.3
2.5°	613.3	613.3	617.2	619.2	623.2	625.1	629.1	633.0	644.8	646.8	650.8
5°	597.5	605.4	631.0	640.9	668.5	706.0	721.8	747.4	800.6	816.4	826.3
7.5°	573.9	591.6	654.7	670.5	739.5	838.1	879.5	934.7	1019.5	1060.9	1094.5
10°	536.4	573.9	686.3	723.7	836.1	986.0	1062.9	1139.9	1268.1	1325.3	1347.0
12.5°	495.0	556.1	719.8	771.1	932.8	1151.7	1244.4	1329.2	1475.2	1552.1	1563.9
15°	447.6	530.5	751.3	826.3	1035.3	1289.8	1392.3	1496.8	1632.9	1688.1	1701.9
17.5°	406.2	510.7	780.9	859.8	1114.2	1414.0	1518.5	1605.3	1715.7	1753.2	1763.1
20°	355.0	479.2	800.6	903.2	1197.1	1504.7	1605.3	1672.4	1747.3	1771.0	1774.9
22.5°	317.5	445.7	812.5	919.0	1252.3	1560.0	1644.7	1698.0	1749.3	1757.2	1759.1
25°	285.9	408.2	810.5	936.7	1299.6	1593.5	1658.6	1698.0	1727.6	1731.5	1731.5
27.5°	256.4	366.8	802.6	940.6	1335.1	1601.4	1652.6	1680.2	1694.0	1701.9	1701.9
30°	230.7	327.4	782.9	932.8	1350.9	1593.5	1634.9	1648.7	1662.5	1674.3	1680.2
32.5°	211.0	289.9	753.3	917.0	1352.9	1573.8	1603.3	1611.2	1630.9	1658.6	1668.4
35°	193.3	252.4	719.8	895.3	1341.1	1542.2	1561.9	1569.8	1609.3	1650.7	1664.5
37.5°	175.5	224.8	676.4	857.8	1323.3	1504.7	1518.5	1532.3	1593.5	1642.8	1658.6
40°	157.8	201.1	625.1	816.4	1295.7	1459.4	1471.2	1492.9	1573.8	1630.9	1646.7
42.5°	144.0	181.4	569.9	773.0	1260.2	1408.1	1425.9	1457.4	1550.1	1611.2	1629.0
45°	132.1	161.7	510.7	713.9	1214.9	1354.9	1380.5	1423.9	1522.5	1581.6	1597.4
47.5°	120.3	147.9	449.6	652.7	1165.6	1301.6	1335.1	1384.4	1485.0	1542.2	1556.0
50°	110.4	134.1	388.5	587.7	1112.2	1244.4	1283.9	1335.1	1437.7	1490.9	1508.7
52.5°	102.5	122.3	331.3	522.6	1051.1	1185.3	1230.6	1283.9	1380.5	1431.8	1443.6
55°	94.7	112.4	282.0	453.6	988.0	1122.2	1171.5	1222.7	1317.4	1360.8	1368.7
57.5°	90.7	104.5	240.6	388.5	920.9	1051.1	1106.3	1153.7	1242.5	1276.0	1283.9
60°	84.8	98.6	209.0	333.3	848.0	984.0	1031.4	1078.7	1153.7	1181.3	1187.2
62.5°	78.9	94.7	185.4	280.0	773.0	905.1	952.5	995.9	1059.0	1078.7	1086.6
65°	74.9	90.7	167.6	240.6	696.1	822.3	869.7	907.1	958.4	978.1	982.1
67.5°	71.0	86.8	153.8	207.1	619.2	739.5	775.0	810.5	849.9	869.7	871.6
70°	65.1	82.8	142.0	183.4	540.3	644.8	674.4	711.9	743.4	753.3	759.2
72.5°	61.1	76.9	134.1	165.6	459.5	554.1	581.7	603.4	631.0	640.9	640.9
75°	55.2	69.0	126.2	147.9	376.7	453.6	477.2	498.9	520.6	524.6	518.6
77.5°	49.3	61.1	108.5	124.2	293.8	358.9	378.6	390.5	408.2	412.1	414.1
80°	41.4	53.2	84.8	96.6	213.0	264.2	278.1	287.9	303.7	303.7	307.6
82.5°	31.6	41.4	61.1	69.0	144.0	181.4	193.3	199.2	209.0	209.0	209.0
85°	19.7	25.6	39.4	45.4	86.8	110.4	118.3	120.3	128.2	130.2	130.2
87.5°	9.9	13.8	25.6	27.6	45.4	57.2	57.2	61.1	61.1	59.2	57.2
90°	4.0	7.3	10.6	11.3	17.8	26.5	30.9	27.4	20.6	15.5	15.5
92.5°	16.3	43.9	71.6	78.5	110.3	152.7	173.9	152.4	109.4	77.2	74.1
95°	39.0	89.6	140.2	152.8	271.3	429.4	508.5	453.8	344.3	262.2	252.9
97.5°	67.4	112.0	156.7	167.8	365.5	629.1	760.9	726.3	657.1	605.2	587.5
100°	89.4	129.9	170.3	180.4	399.8	692.3	838.5	841.1	846.1	849.8	828.7
102.5°	108.2	145.9	183.6	193.1	415.5	712.2	860.5	904.6	992.7	1058.8	1040.7
105°	139.8	171.8	203.8	211.8	427.2	714.5	858.0	956.8	1154.5	1302.7	1292.9
107.5°	172.4	202.1	231.9	239.4	429.3	682.6	809.2	947.1	1222.7	1429.5	1431.9
110°	194.2	221.2	248.2	254.9	426.1	654.4	768.6	922.7	1230.8	1461.9	1472.1



TEST NUMBER: P936793

CATALOG NUMBER: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	215.8	241.5	267.1	273.5	426.2	629.9	731.6	889.3	1204.7	1441.2	1456.8
115°	248.4	272.0	295.7	301.6	430.2	601.7	687.3	839.3	1143.1	1370.9	1392.4
117.5°	280.4	301.9	323.4	328.8	438.2	583.9	656.8	793.9	1068.1	1273.8	1297.7
120°	299.2	319.4	339.7	344.7	444.7	578.0	644.6	769.9	1020.4	1208.3	1231.5
122.5°	317.4	337.8	358.2	363.3	454.0	574.8	635.3	748.1	973.8	1143.0	1165.8
125°	345.5	364.0	382.7	387.3	466.6	572.3	625.1	721.0	912.6	1056.4	1077.5
127.5°	368.3	387.0	405.7	410.5	479.2	570.8	616.5	698.9	863.4	986.9	1004.6
130°	380.4	400.6	420.9	426.0	488.4	571.7	613.3	686.6	833.1	942.9	959.4
132.5°	393.0	413.2	433.5	438.6	495.9	572.3	610.5	676.1	807.2	905.5	920.2
135°	411.8	430.2	448.5	453.2	503.9	571.7	605.6	660.5	770.4	852.7	865.4
137.5°	430.9	449.1	467.4	471.9	516.2	575.2	604.8	651.3	744.1	813.7	824.1
140°	446.7	463.5	480.3	484.5	523.7	575.8	602.0	642.1	722.2	782.4	792.1
142.5°	458.9	474.4	489.9	493.8	529.9	577.9	602.0	637.2	707.7	760.5	768.9
145°	477.6	491.1	504.7	508.1	538.1	578.0	597.9	626.7	684.4	727.6	733.9
147.5°	496.3	509.5	522.7	525.9	549.9	581.9	597.9	620.6	665.8	699.9	705.1
150°	508.5	520.4	532.3	535.3	556.2	584.0	597.9	617.0	655.4	684.1	688.3
152.5°	521.1	530.2	539.1	541.4	560.2	585.4	597.9	614.3	646.9	671.5	674.7
155°	539.7	546.4	553.1	554.8	569.2	588.3	597.9	610.9	636.9	656.4	658.5
157.5°	553.5	560.0	566.6	568.2	578.1	591.3	597.9	608.0	628.2	643.4	644.8
160°	562.9	568.0	573.1	574.3	582.2	592.7	597.9	606.6	623.8	636.9	637.7
162.5°	572.3	576.1	579.9	580.9	586.6	594.2	597.9	605.2	619.9	630.8	631.6
165°	582.4	585.9	589.2	590.1	592.7	596.1	597.9	603.1	613.6	621.5	622.4
167.5°	591.8	593.4	595.1	595.4	597.6	600.5	602.0	605.4	612.3	617.4	617.8
170°	597.9	599.5	601.2	601.6	601.7	601.9	602.0	605.4	612.3	617.4	617.4
172.5°	601.2	601.6	601.9	602.0	602.0	602.0	602.0	604.7	610.1	614.2	613.9
175°	605.6	605.6	605.6	605.6	604.4	602.7	602.0	603.6	607.1	609.6	609.6
177.5°	605.6	605.6	605.6	605.6	604.6	603.3	602.7	604.1	606.8	608.9	608.5
180°	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6



TEST NUMBER: P936793

CATALOG NUMBER: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	613.3	613.3
2.5°	654.7	650.8
5°	842.0	846.0
7.5°	1134.0	1132.0
10°	1410.1	1427.8
12.5°	1611.2	1615.2
15°	1733.5	1741.4
17.5°	1780.8	1782.8
20°	1782.8	1778.8
22.5°	1761.1	1757.2
25°	1735.5	1733.5
27.5°	1711.8	1713.8
30°	1701.9	1707.9
32.5°	1701.9	1711.8
35°	1705.9	1715.7
37.5°	1703.9	1715.7
40°	1696.0	1709.8
42.5°	1674.3	1684.2
45°	1640.8	1652.6
47.5°	1597.4	1605.3
50°	1542.2	1550.1
52.5°	1473.2	1475.2
55°	1390.4	1398.2
57.5°	1301.6	1303.6
60°	1203.0	1208.9
62.5°	1098.4	1098.4
65°	988.0	991.9
67.5°	873.6	883.5
70°	757.2	759.2
72.5°	642.9	642.9
75°	524.6	526.5
77.5°	412.1	412.1
80°	305.7	307.6
82.5°	211.0	214.9
85°	132.1	132.1
87.5°	61.1	55.2
90°	15.5	15.5
92.5°	61.8	49.6
95°	215.6	178.5
97.5°	516.7	445.9
100°	744.4	660.0
102.5°	968.4	896.2
105°	1254.1	1215.2
107.5°	1441.2	1450.6
110°	1512.5	1553.0



TEST NUMBER: P936793

CATALOG NUMBER: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1518.9	1581.1
115°	1478.6	1564.8
117.5°	1393.3	1488.9
120°	1324.4	1417.3
122.5°	1257.4	1349.0
125°	1161.8	1246.2
127.5°	1075.8	1147.0
130°	1025.1	1090.9
132.5°	979.2	1038.1
135°	916.2	967.0
137.5°	865.7	907.2
140°	830.9	869.8
142.5°	802.2	835.6
145°	759.2	784.5
147.5°	726.1	747.1
150°	705.3	722.2
152.5°	687.5	700.4
155°	667.0	675.5
157.5°	650.9	656.8
160°	641.2	644.6
162.5°	634.9	638.1
165°	625.7	629.2
167.5°	619.2	620.7
170°	617.4	617.4
172.5°	612.6	611.3
175°	609.6	609.6
177.5°	607.1	605.6
180°	605.6	605.6



TEST NUMBER: P936793

CATALOG NUMBER: SQ4-FB-050U-075D-B2750-1D-UNV-STD-W-8-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.06	6.01	5.97	6.94	8.14	18.24	19.19	19.15	20.12	21.32
	3H	5.77	6.62	6.69	7.57	8.79	20.08	20.94	21.00	21.88	23.10
	4H	6.07	6.88	7.01	7.83	9.06	20.73	21.54	21.67	22.49	23.72
	6H	6.33	7.07	7.27	8.03	9.27	21.17	21.91	22.11	22.87	24.11
	8H	6.40	7.11	7.35	8.08	9.32	21.29	22.00	22.24	22.97	24.22
	12H	6.42	7.10	7.38	8.06	9.33	21.36	22.04	22.32	23.00	24.27
4H	2H	12.29	13.09	13.22	14.04	15.27	18.52	19.33	19.46	20.28	21.51
	3H	13.86	14.54	14.81	15.51	16.76	20.58	21.25	21.53	22.23	23.48
	4H	13.96	14.58	14.92	15.55	16.82	21.35	21.97	22.31	22.94	24.21
	6H	13.98	14.51	14.95	15.51	16.77	21.89	22.43	22.86	23.42	24.69
	8H	13.95	14.46	14.93	15.44	16.73	22.06	22.56	23.03	23.55	24.83
	12H	13.92	14.37	14.91	15.37	16.66	22.15	22.61	23.15	23.61	24.90
8H	4H	15.41	15.91	16.39	16.90	18.19	21.42	21.92	22.39	22.90	24.19
	6H	15.66	16.07	16.66	17.10	18.39	22.05	22.46	23.05	23.49	24.78
	8H	15.68	16.04	16.69	17.06	18.36	22.27	22.64	23.28	23.65	24.95
	12H	15.65	15.97	16.66	16.98	18.33	22.42	22.74	23.43	23.75	25.10
12H	4H	15.56	16.01	16.55	17.02	18.31	21.37	21.83	22.37	22.83	24.12
	6H	15.92	16.29	16.93	17.30	18.60	22.03	22.40	23.04	23.42	24.72
	8H	15.99	16.31	17.01	17.33	18.67	22.27	22.59	23.28	23.60	24.95