

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938178

Luminaire Tested: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938178
REPORT IS A COMBINATION OF REPORTS P933592 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 26844.8 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 225.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938178
CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P938178

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	44	42	37	37	37	37
2	87	79	73	68	79	73	67	63	61	56	53	49	46	44	39	37	35	30	30	30	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25	25	25	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21	21	21	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	27	23	21	18	18	18	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	23	24	21	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	18	16	13	13	13	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12	12	12	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10	10	10	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4815	4815	4815
5°	4706	5567	6472
10°	4270	8116	10730
15°	3631	10607	12956
20°	2957	12294	13205
25°	2467	12869	12936
30°	2082	12953	12912
35°	1841	12741	13246
40°	1605	12466	13591
45°	1455	12264	13644
50°	1336	12084	13418
55°	1281	11819	12823
60°	1312	11305	11884
65°	1368	10522	10594
70°	1461	9182	8949
75°	1624	7493	6984
80°	1788	5203	4706
85°	1623	2765	2408

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13644 cd/sqm



TEST NUMBER: P938178

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.4	0.8
10°-20°	892.5	3.3
20°-30°	1561.1	5.8
30°-40°	2009.6	7.5
40°-50°	2244.7	8.4
50°-60°	2149.9	8.0
60°-70°	1703.8	6.3
70°-80°	1001.9	3.7
80°-90°	287.0	1.1
90°-100°	1112.3	4.1
100°-110°	2924.4	10.9
110°-120°	3032.3	11.3
120°-130°	2432.3	9.1
130°-140°	1908.5	7.1
140°-150°	1464.8	5.5
150°-160°	1054.9	3.9
160°-170°	645.5	2.4
170°-180°	218.1	0.8
0°-30°	2655.0	9.9
0°-40°	4664.6	17.4
0°-60°	9059.1	33.7
0°-90°	12051.7	44.9
90°-120°	7069.1	26.3
90°-150°	12874.7	48.0
90°-180°	14793.0	55.1
0°-180°	26844.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1557	1557	1557	1557	1557	
5°	1517	1627	1832	2072	2147	140
15°	1136	2097	3534	4285	4420	316
25°	726	2378	4210	4395	4400	334
35°	490	2272	3964	4190	4355	306
45°	335	1812	3504	4014	4195	259
55°	240	1151	2973	3454	3549	219
65°	190	611	2208	2483	2518	189
75°	140	376	1211	1332	1336	147
85°	50	115	300	330	335	53
90°	15	43	116	58	58	16
95°	147	576	1916	988	672	163
105°	527	798	3233	4908	4579	559
115°	936	1136	2590	5166	5896	924
125°	1302	1460	2356	3980	4696	1156
135°	1552	1708	2282	3213	3644	1200
145°	1800	1914	2253	2741	2956	1127
155°	2034	2090	2253	2473	2545	935
165°	2195	2224	2253	2342	2371	619
175°	2282	2282	2268	2297	2297	217
180°	2282	2282	2282	2282	2282	



TEST NUMBER: P938178
 CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1556.8	1556.8	1556.8	1556.8	1556.8	1556.8	1556.8	1556.8	1556.8	1556.8	1556.8
2.5°	1556.8	1556.8	1566.8	1571.8	1581.7	1586.8	1596.8	1606.8	1636.9	1641.9	1651.8
5°	1516.7	1536.7	1601.8	1626.8	1696.9	1792.1	1832.1	1897.2	2032.2	2072.4	2097.3
7.5°	1456.6	1501.7	1661.9	1701.9	1877.1	2127.4	2232.5	2372.7	2588.0	2693.1	2778.2
10°	1361.6	1456.6	1742.0	1837.0	2122.4	2502.8	2698.0	2893.2	3218.6	3363.7	3418.9
12.5°	1256.5	1411.6	1827.1	1957.2	2367.7	2923.3	3158.6	3373.8	3744.2	3939.5	3969.4
15°	1136.3	1346.5	1907.1	2097.3	2628.0	3273.7	3533.9	3799.3	4144.7	4284.9	4319.9
17.5°	1031.2	1296.5	1982.3	2182.4	2828.1	3589.0	3854.4	4074.5	4354.9	4450.0	4475.1
20°	901.0	1216.3	2032.2	2292.5	3038.5	3819.3	4074.5	4244.7	4435.0	4495.1	4505.0
22.5°	805.9	1131.2	2062.3	2332.6	3178.6	3959.5	4174.7	4309.8	4440.0	4460.0	4465.0
25°	725.8	1036.2	2057.3	2377.6	3298.7	4044.6	4209.7	4309.8	4384.9	4394.9	4394.9
27.5°	650.8	931.1	2037.3	2387.7	3388.8	4064.6	4194.7	4264.7	4299.8	4319.9	4319.9
30°	585.7	830.9	1987.2	2367.7	3428.8	4044.6	4149.7	4184.7	4219.8	4249.8	4264.7
32.5°	535.6	735.9	1912.1	2327.7	3433.8	3994.5	4069.6	4089.6	4139.6	4209.7	4234.8
35°	490.5	640.7	1827.1	2272.5	3403.9	3914.4	3964.4	3984.5	4084.6	4189.7	4224.7
37.5°	445.5	570.6	1716.9	2177.5	3358.8	3819.3	3854.4	3889.4	4044.6	4169.7	4209.7
40°	400.4	510.6	1586.8	2072.4	3288.7	3704.2	3734.2	3789.3	3994.5	4139.6	4179.7
42.5°	365.4	460.6	1446.7	1962.2	3198.6	3574.1	3619.1	3699.2	3934.4	4089.6	4134.7
45°	335.3	410.5	1296.5	1812.1	3083.4	3438.9	3503.9	3614.1	3864.3	4014.5	4054.5
47.5°	305.4	375.5	1141.3	1656.9	2958.3	3303.7	3388.8	3513.9	3769.3	3914.4	3949.4
50°	280.3	340.4	986.1	1491.7	2823.2	3158.6	3258.6	3388.8	3649.1	3784.3	3829.3
52.5°	260.3	310.4	841.0	1326.5	2668.0	3008.4	3123.5	3258.6	3503.9	3634.1	3664.1
55°	240.3	285.3	715.8	1151.3	2507.8	2848.2	2973.4	3103.5	3343.7	3453.9	3473.9
57.5°	230.2	265.3	610.7	986.1	2337.6	2668.0	2808.1	2928.3	3153.5	3238.6	3258.6
60°	215.2	250.2	530.6	846.0	2152.4	2497.8	2617.9	2738.1	2928.3	2998.3	3013.4
62.5°	200.3	240.3	470.5	710.8	1962.2	2297.6	2417.7	2527.8	2688.0	2738.1	2758.1
65°	190.2	230.2	425.5	610.7	1767.0	2087.4	2207.5	2302.6	2432.8	2482.7	2492.8
67.5°	180.2	220.3	390.5	525.6	1571.8	1877.1	1967.2	2057.3	2157.5	2207.5	2212.5
70°	165.2	210.2	360.4	465.5	1371.5	1636.9	1711.9	1807.0	1887.1	1912.1	1927.1
72.5°	155.2	195.2	340.4	420.4	1166.3	1406.6	1476.6	1531.8	1601.8	1626.8	1626.8
75°	140.1	175.2	320.4	375.5	956.0	1151.3	1211.4	1266.4	1321.4	1331.5	1316.5
77.5°	125.1	155.2	275.3	315.3	745.8	911.1	961.1	991.1	1036.2	1046.1	1051.2
80°	105.1	135.2	215.2	245.3	540.6	670.8	705.8	730.8	770.9	770.9	780.9
82.5°	80.1	105.1	155.2	175.2	365.4	460.6	490.5	505.5	530.6	530.6	530.6
85°	50.1	65.1	100.1	115.2	220.3	280.3	300.3	305.4	325.4	330.4	330.4
87.5°	25.0	35.0	65.1	70.1	115.2	145.1	145.1	155.2	155.2	150.2	145.1
90°	15.3	27.5	39.8	42.9	67.3	100.0	116.3	103.4	77.6	58.2	58.2
92.5°	61.2	165.4	269.6	295.6	415.6	575.5	655.5	574.4	412.4	291.0	279.4
95°	147.0	337.6	528.2	575.8	1022.5	1618.1	1915.9	1709.6	1297.2	987.9	952.8
97.5°	254.2	422.3	590.5	632.5	1377.3	2370.4	2867.0	2736.6	2475.9	2280.4	2213.7
100°	336.9	489.5	641.9	680.0	1506.5	2608.6	3159.5	3169.1	3188.1	3202.4	3123.0
102.5°	407.4	549.7	691.9	727.5	1565.8	2683.4	3242.3	3408.3	3740.5	3989.7	3921.6
105°	526.8	647.3	767.8	798.0	1609.6	2691.9	3233.0	3605.3	4350.0	4908.5	4871.9
107.5°	649.4	761.7	874.0	902.1	1617.8	2572.2	3049.3	3568.6	4607.3	5386.3	5395.2
110°	732.1	833.5	934.9	960.3	1605.5	2465.9	2896.1	3476.7	4637.9	5508.9	5547.0



TEST NUMBER: P938178

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	813.3	909.9	1006.5	1030.7	1606.0	2373.2	2756.8	3351.0	4539.4	5430.8	5489.4
115°	935.7	1024.8	1114.1	1136.4	1620.9	2266.8	2589.8	3162.3	4307.1	5165.9	5247.0
117.5°	1056.8	1137.7	1218.8	1239.0	1651.0	2200.3	2475.0	2991.6	4024.9	4799.7	4889.8
120°	1127.2	1203.4	1279.7	1298.8	1675.5	2177.9	2429.0	2901.1	3845.2	4553.2	4640.7
122.5°	1196.1	1273.0	1349.9	1369.2	1710.7	2166.1	2393.8	2818.9	3669.0	4306.7	4392.9
125°	1301.8	1371.9	1442.0	1459.6	1758.2	2156.4	2355.5	2716.5	3438.8	3980.4	4059.9
127.5°	1387.6	1458.4	1529.2	1546.8	1805.7	2150.8	2323.3	2633.3	3253.4	3718.5	3785.5
130°	1433.5	1509.8	1586.0	1605.0	1840.4	2154.2	2311.1	2587.1	3139.1	3553.1	3615.1
132.5°	1481.0	1557.2	1633.5	1652.5	1868.5	2156.4	2300.3	2547.4	3041.6	3412.3	3467.8
135°	1551.5	1620.9	1690.3	1707.7	1899.1	2154.4	2282.0	2489.0	2902.8	3213.2	3261.0
137.5°	1623.4	1692.2	1760.9	1778.1	1945.0	2167.6	2278.9	2453.9	2803.7	3066.1	3105.2
140°	1683.1	1746.4	1809.7	1825.6	1973.1	2169.8	2268.2	2419.2	2721.5	2948.1	2984.7
142.5°	1729.0	1787.6	1846.2	1860.8	1996.6	2177.7	2268.2	2400.9	2666.4	2865.5	2897.0
145°	1799.5	1850.6	1901.7	1914.4	2027.2	2177.7	2252.9	2361.5	2578.6	2741.4	2765.2
147.5°	1869.9	1919.6	1969.3	1981.8	2072.2	2192.7	2252.9	2338.3	2509.2	2637.3	2657.0
150°	1915.9	1960.9	2005.8	2017.1	2095.6	2200.5	2252.9	2325.1	2469.3	2577.5	2593.5
152.5°	1963.4	1997.4	2031.6	2040.0	2111.0	2205.6	2252.9	2314.5	2437.7	2530.1	2542.2
155°	2033.8	2059.1	2084.2	2090.5	2144.6	2216.8	2252.9	2301.9	2399.9	2473.4	2481.4
157.5°	2086.0	2110.4	2135.0	2141.1	2178.4	2228.1	2252.9	2291.0	2367.2	2424.4	2430.0
160°	2121.2	2140.2	2159.3	2164.1	2193.7	2233.2	2252.9	2285.5	2350.9	2399.9	2403.2
162.5°	2156.4	2170.7	2185.0	2188.5	2210.0	2238.6	2252.9	2280.5	2335.6	2377.0	2380.0
165°	2194.6	2207.6	2220.5	2223.7	2233.5	2246.4	2252.9	2272.6	2312.1	2341.7	2344.9
167.5°	2229.9	2236.1	2242.2	2243.6	2251.8	2262.8	2268.2	2281.1	2306.9	2326.4	2327.7
170°	2252.9	2259.0	2265.1	2266.6	2267.1	2267.8	2268.2	2281.1	2306.9	2326.4	2326.4
172.5°	2265.1	2266.5	2267.9	2268.2	2268.2	2268.2	2268.2	2278.4	2298.9	2314.1	2313.0
175°	2282.0	2282.0	2282.0	2282.0	2277.4	2271.3	2268.2	2274.7	2287.6	2297.3	2297.3
177.5°	2282.0	2282.0	2282.0	2282.0	2278.4	2273.6	2271.3	2276.4	2286.5	2294.2	2292.8
180°	2282.0	2282.0	2282.0	2282.0	2282.0	2282.0	2282.0	2282.0	2282.0	2282.0	2282.0



TEST NUMBER: P938178

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1556.8	1556.8
2.5°	1661.9	1651.8
5°	2137.5	2147.4
7.5°	2878.2	2873.2
10°	3579.0	3624.0
12.5°	4089.6	4099.6
15°	4399.9	4419.9
17.5°	4520.1	4525.0
20°	4525.0	4515.1
22.5°	4470.0	4460.0
25°	4405.0	4399.9
27.5°	4344.9	4349.9
30°	4319.9	4334.9
32.5°	4319.9	4344.9
35°	4329.8	4354.9
37.5°	4324.9	4354.9
40°	4304.9	4339.9
42.5°	4249.8	4274.8
45°	4164.7	4194.7
47.5°	4054.5	4074.5
50°	3914.4	3934.4
52.5°	3739.2	3744.2
55°	3529.0	3549.0
57.5°	3303.7	3308.7
60°	3053.4	3068.4
62.5°	2788.1	2788.1
65°	2507.8	2517.8
67.5°	2217.5	2242.6
70°	1922.2	1927.1
72.5°	1631.8	1631.8
75°	1331.5	1336.5
77.5°	1046.1	1046.1
80°	775.9	780.9
82.5°	535.6	545.7
85°	335.3	335.3
87.5°	155.2	140.1
90°	58.2	58.2
92.5°	233.1	186.8
95°	812.6	672.4
97.5°	1946.9	1680.0
100°	2805.1	2487.2
102.5°	3649.3	3377.0
105°	4725.6	4579.3
107.5°	5430.6	5466.0
110°	5699.5	5851.9



TEST NUMBER: P938178

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5723.4	5957.6
115°	5571.7	5896.4
117.5°	5249.9	5609.9
120°	4990.5	5340.4
122.5°	4738.0	5083.1
125°	4377.7	4695.6
127.5°	4053.7	4321.9
130°	3862.9	4110.6
132.5°	3689.6	3911.5
135°	3452.2	3643.5
137.5°	3261.8	3418.4
140°	3131.1	3277.5
142.5°	3022.9	3148.8
145°	2860.5	2955.8
147.5°	2736.0	2814.9
150°	2657.6	2721.6
152.5°	2590.5	2638.8
155°	2513.4	2545.4
157.5°	2452.5	2475.0
160°	2416.1	2429.0
162.5°	2392.2	2404.5
165°	2357.8	2370.8
167.5°	2333.2	2338.6
170°	2326.4	2326.4
172.5°	2308.1	2303.4
175°	2297.3	2297.3
177.5°	2287.4	2282.0
180°	2282.0	2282.0



TEST NUMBER: P938178
 CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.99	6.84	6.98	7.85	9.19	19.18	20.03	20.17	21.04	22.38
	3H	6.69	7.45	7.69	8.47	9.83	21.02	21.79	22.02	22.80	24.16
	4H	6.99	7.71	8.00	8.73	10.10	21.67	22.39	22.69	23.42	24.78
	6H	7.24	7.91	8.26	8.93	10.31	22.10	22.77	23.13	23.80	25.18
	8H	7.31	7.94	8.34	8.98	10.36	22.23	22.86	23.26	23.91	25.28
	12H	7.32	7.93	8.36	8.96	10.37	22.30	22.90	23.34	23.94	25.34
4H	2H	13.21	13.93	14.23	14.95	16.32	19.45	20.18	20.47	21.20	22.56
	3H	14.77	15.38	15.81	16.43	17.81	21.50	22.11	22.53	23.16	24.54
	4H	14.87	15.42	15.91	16.47	17.87	22.27	22.83	23.31	23.87	25.27
	6H	14.88	15.36	15.93	16.42	17.82	22.81	23.29	23.86	24.36	25.76
	8H	14.85	15.30	15.90	16.36	17.78	22.98	23.43	24.03	24.48	25.90
	12H	14.81	15.22	15.88	16.29	17.71	23.07	23.48	24.14	24.55	25.97
8H	4H	16.32	16.76	17.37	17.82	19.24	22.33	22.78	23.38	23.83	25.25
	6H	16.56	16.93	17.63	18.03	19.44	22.96	23.33	24.04	24.43	25.85
	8H	16.58	16.90	17.66	17.98	19.42	23.19	23.51	24.27	24.59	26.03
	12H	16.54	16.83	17.63	17.91	19.38	23.33	23.62	24.42	24.70	26.17
12H	4H	16.46	16.87	17.53	17.94	19.36	22.28	22.69	23.35	23.76	25.18
	6H	16.82	17.14	17.90	18.23	19.66	22.95	23.27	24.03	24.36	25.79
	8H	16.89	17.17	17.97	18.25	19.72	23.18	23.47	24.26	24.54	26.02