

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938183

Luminaire Tested: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938183
REPORT IS A COMBINATION OF REPORTS P933600 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8948.0 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938183
CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P938183

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	44	42	37
2	87	79	73	68	79	73	67	63	61	56	53	49	46	44	39	37	35	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	27	23	21	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	23	24	21	18	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	18	16	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4814	4814	4814
5°	4698	5560	6471
10°	4257	8099	10729
15°	3614	10575	12955
20°	2939	12245	13203
25°	2449	12805	12936
30°	2062	12876	12911
35°	1820	12651	13244
40°	1584	12363	13590
45°	1431	12149	13643
50°	1311	11955	13417
55°	1251	11673	12822
60°	1277	11146	11884
65°	1321	10351	10593
70°	1396	9008	8950
75°	1531	7327	6984
80°	1638	5064	4706
85°	1383	2672	2409

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13643 cd/sqm



TEST NUMBER: P938183

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.1	0.8
10°-20°	297.5	3.3
20°-30°	520.3	5.8
30°-40°	669.8	7.5
40°-50°	748.2	8.4
50°-60°	716.6	8.0
60°-70°	567.9	6.3
70°-80°	333.9	3.7
80°-90°	95.7	1.1
90°-100°	370.8	4.1
100°-110°	974.8	10.9
110°-120°	1010.8	11.3
120°-130°	810.8	9.1
130°-140°	636.2	7.1
140°-150°	488.3	5.5
150°-160°	351.6	3.9
160°-170°	215.2	2.4
170°-180°	72.7	0.8
0°-30°	884.9	9.9
0°-40°	1554.7	17.4
0°-60°	3019.5	33.7
0°-90°	4017.0	44.9
90°-120°	2356.4	26.3
90°-150°	4291.6	48.0
90°-180°	4931.0	55.1
0°-180°	8948.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	519	519	519	519	519	
5°	506	542	611	691	716	47
15°	379	699	1178	1428	1473	105
25°	242	792	1403	1465	1467	111
35°	164	757	1321	1396	1452	102
45°	112	604	1168	1338	1398	86
55°	80	384	991	1151	1183	73
65°	63	204	736	828	839	63
75°	47	125	404	444	446	49
85°	17	38	100	110	112	18
90°	5	14	39	19	19	5
95°	49	192	639	329	224	54
105°	176	266	1078	1636	1526	186
115°	312	379	863	1722	1966	308
125°	434	486	785	1327	1565	385
135°	517	569	761	1071	1214	400
145°	600	638	751	914	985	376
155°	678	697	751	824	848	312
165°	732	741	751	780	790	206
175°	761	761	756	766	766	72
180°	761	761	761	761	761	



TEST NUMBER: P938183

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8	518.8
2.5°	518.8	518.8	522.2	523.9	527.2	528.9	532.2	535.6	545.6	547.2	550.6
5°	505.5	512.2	533.9	542.2	565.6	597.3	610.6	632.3	677.4	690.7	699.1
7.5°	485.5	500.5	553.9	567.2	625.6	709.0	744.1	790.9	862.6	897.6	926.0
10°	453.8	485.5	580.6	612.3	707.4	834.2	899.2	964.3	1072.8	1121.2	1139.5
12.5°	418.8	470.5	609.0	652.3	789.2	974.4	1052.8	1124.5	1248.0	1313.1	1323.0
15°	378.7	448.8	635.7	699.1	875.9	1091.1	1177.9	1266.3	1381.5	1428.1	1439.9
17.5°	343.7	432.2	660.7	727.5	942.6	1196.2	1284.7	1358.1	1451.5	1483.2	1491.5
20°	300.3	405.4	677.4	764.2	1012.7	1273.0	1358.1	1414.8	1478.2	1498.2	1501.6
22.5°	268.6	377.0	687.3	777.5	1059.5	1319.7	1391.4	1436.5	1479.9	1486.6	1488.2
25°	242.0	345.4	685.8	792.4	1099.5	1348.1	1403.2	1436.5	1461.5	1464.9	1464.9
27.5°	216.9	310.3	679.1	795.8	1129.5	1354.8	1398.1	1421.5	1433.2	1439.9	1439.9
30°	195.2	277.0	662.4	789.2	1142.9	1348.1	1383.1	1394.8	1406.4	1416.5	1421.5
32.5°	178.6	245.2	637.4	775.8	1144.5	1331.4	1356.4	1363.0	1379.8	1403.2	1411.5
35°	163.5	213.6	609.0	757.4	1134.5	1304.7	1321.3	1328.0	1361.4	1396.5	1408.1
37.5°	148.5	190.2	572.3	725.8	1119.5	1273.0	1284.7	1296.4	1348.1	1389.8	1403.2
40°	133.5	170.2	528.9	690.7	1096.1	1234.6	1244.6	1263.0	1331.4	1379.8	1393.1
42.5°	121.8	153.5	482.2	654.0	1066.1	1191.3	1206.3	1233.0	1311.4	1363.0	1378.1
45°	111.8	136.9	432.2	603.9	1027.7	1146.2	1167.9	1204.6	1288.0	1338.1	1351.4
47.5°	101.8	125.1	380.4	552.3	986.0	1101.2	1129.5	1171.3	1256.3	1304.7	1316.4
50°	93.5	113.5	328.6	497.1	940.9	1052.8	1086.2	1129.5	1216.2	1261.3	1276.4
52.5°	86.8	103.4	280.3	442.1	889.3	1002.7	1041.1	1086.2	1167.9	1211.3	1221.3
55°	80.1	95.1	238.6	383.8	835.8	949.3	991.0	1034.4	1114.5	1151.2	1157.9
57.5°	76.7	88.4	203.5	328.6	779.1	889.3	936.0	976.0	1051.1	1079.5	1086.2
60°	71.8	83.4	176.9	282.0	717.4	832.6	872.6	912.6	976.0	999.4	1004.3
62.5°	66.8	80.1	156.9	236.9	654.0	765.8	805.9	842.5	896.0	912.6	919.2
65°	63.4	76.7	141.8	203.5	588.9	695.7	735.8	767.5	810.9	827.5	830.9
67.5°	60.0	73.5	130.2	175.2	523.9	625.6	655.7	685.8	719.1	735.8	737.4
70°	55.0	70.1	120.1	155.2	457.1	545.6	570.6	602.2	629.0	637.4	642.4
72.5°	51.8	65.1	113.5	140.1	388.8	468.8	492.2	510.6	533.9	542.2	542.2
75°	46.7	58.4	106.8	125.1	318.7	383.8	403.8	422.1	440.4	443.8	438.8
77.5°	41.7	51.8	91.8	105.1	248.6	303.7	320.4	330.3	345.4	348.6	350.3
80°	35.0	45.1	71.8	81.7	180.1	223.5	235.3	243.5	257.0	257.0	260.3
82.5°	26.7	35.0	51.8	58.4	121.8	153.5	163.5	168.5	176.9	176.9	176.9
85°	16.7	21.7	33.3	38.4	73.5	93.5	100.1	101.8	108.5	110.1	110.1
87.5°	8.4	11.6	21.7	23.4	38.4	48.4	48.4	51.8	51.8	50.1	48.4
90°	5.1	9.2	13.3	14.3	22.5	33.3	38.7	34.4	25.8	19.4	19.4
92.5°	20.4	55.1	89.8	98.5	138.5	191.9	218.5	191.5	137.5	97.0	93.2
95°	49.0	112.5	176.1	192.0	340.9	539.3	638.6	569.9	432.5	329.3	317.6
97.5°	84.7	140.7	196.8	210.8	459.1	790.1	955.6	912.1	825.3	760.1	737.9
100°	112.3	163.2	214.0	226.7	502.2	869.5	1053.1	1056.3	1062.7	1067.4	1040.9
102.5°	135.8	183.2	230.6	242.5	521.9	894.5	1080.8	1136.2	1246.9	1329.9	1307.2
105°	175.6	215.8	256.0	266.0	536.6	897.4	1077.7	1201.8	1450.0	1636.2	1623.9
107.5°	216.4	253.9	291.4	300.7	539.3	857.4	1016.5	1189.6	1535.8	1795.4	1798.4
110°	244.0	277.9	311.6	320.1	535.2	822.0	965.4	1158.9	1546.0	1836.3	1849.0



TEST NUMBER: P938183

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	271.1	303.3	335.4	343.5	535.3	791.1	919.0	1117.0	1513.2	1810.3	1829.8
115°	311.9	341.6	371.4	378.8	540.3	755.6	863.2	1054.0	1435.7	1722.0	1749.0
117.5°	352.3	379.3	406.3	413.0	550.4	733.5	825.0	997.1	1341.6	1599.9	1629.9
120°	375.8	401.2	426.6	433.0	558.6	726.0	809.7	967.1	1281.7	1517.7	1546.9
122.5°	398.7	424.4	450.0	456.4	570.3	722.0	798.0	939.7	1223.0	1435.5	1464.3
125°	433.9	457.3	480.7	486.5	586.1	718.8	785.2	905.5	1146.2	1326.8	1353.3
127.5°	462.5	486.1	509.7	515.6	601.9	716.9	774.4	877.7	1084.5	1239.5	1261.9
130°	477.8	503.3	528.7	535.0	613.5	718.1	770.4	862.4	1046.3	1184.4	1205.0
132.5°	493.7	519.1	544.6	550.9	622.9	718.8	766.8	849.1	1013.9	1137.4	1155.9
135°	517.2	540.3	563.4	569.2	633.0	718.1	760.7	829.7	967.7	1071.1	1087.1
137.5°	541.1	564.0	587.0	592.7	648.3	722.5	759.6	817.9	934.5	1022.0	1035.0
140°	561.0	582.1	603.2	608.6	657.8	723.3	756.1	806.4	907.2	982.7	995.0
142.5°	576.3	595.8	615.4	620.3	665.6	725.9	756.1	800.3	888.8	955.1	965.6
145°	599.9	616.8	633.9	638.1	675.7	725.9	750.9	787.1	859.5	913.8	921.8
147.5°	623.3	639.9	656.5	660.6	690.7	730.8	750.9	779.4	836.4	879.1	885.7
150°	638.6	653.6	668.6	672.4	698.6	733.5	750.9	775.0	823.1	859.2	864.5
152.5°	654.5	665.8	677.2	680.0	703.7	735.2	750.9	771.4	812.6	843.3	847.4
155°	678.0	686.4	694.7	696.8	714.8	738.9	750.9	767.3	799.9	824.5	827.2
157.5°	695.3	703.5	711.6	713.7	726.1	742.7	750.9	763.7	789.1	808.1	810.0
160°	707.1	713.4	719.8	721.4	731.2	744.3	750.9	761.8	783.6	799.9	801.0
162.5°	718.8	723.5	728.4	729.5	736.6	746.2	750.9	760.1	778.5	792.3	793.3
165°	731.5	735.9	740.2	741.3	744.5	748.8	750.9	757.5	770.7	780.5	781.6
167.5°	743.3	745.3	747.4	747.9	750.6	754.3	756.1	760.4	769.0	775.5	776.0
170°	750.9	753.0	755.1	755.6	755.8	756.0	756.1	760.4	769.0	775.5	775.5
172.5°	755.1	755.5	756.0	756.1	756.1	756.1	756.1	759.4	766.2	771.3	771.0
175°	760.7	760.7	760.7	760.7	759.1	757.1	756.1	758.2	762.5	765.7	765.7
177.5°	760.7	760.7	760.7	760.7	759.5	757.8	757.1	758.7	762.2	764.7	764.2
180°	760.7	760.7	760.7	760.7	760.7	760.7	760.7	760.7	760.7	760.7	760.7



TEST NUMBER: P938183

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	518.8	518.8
2.5°	553.9	550.6
5°	712.4	715.7
7.5°	959.4	957.7
10°	1192.9	1207.9
12.5°	1363.0	1366.4
15°	1466.6	1473.2
17.5°	1506.6	1508.3
20°	1508.3	1504.9
22.5°	1489.8	1486.6
25°	1468.2	1466.6
27.5°	1448.1	1449.8
30°	1439.9	1444.9
32.5°	1439.9	1448.1
35°	1443.2	1451.5
37.5°	1441.5	1451.5
40°	1434.8	1446.5
42.5°	1416.5	1424.8
45°	1388.1	1398.1
47.5°	1351.4	1358.1
50°	1304.7	1311.4
52.5°	1246.3	1248.0
55°	1176.2	1182.9
57.5°	1101.2	1102.8
60°	1017.7	1022.8
62.5°	929.3	929.3
65°	835.8	839.2
67.5°	739.1	747.5
70°	640.7	642.4
72.5°	543.9	543.9
75°	443.8	445.5
77.5°	348.6	348.6
80°	258.6	260.3
82.5°	178.6	181.8
85°	111.8	111.8
87.5°	51.8	46.7
90°	19.4	19.4
92.5°	77.7	62.3
95°	270.9	224.1
97.5°	649.0	560.0
100°	935.0	829.0
102.5°	1216.4	1125.7
105°	1575.2	1526.4
107.5°	1810.2	1822.0
110°	1899.8	1950.6



TEST NUMBER: P938183

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1907.8	1985.9
115°	1857.2	1965.5
117.5°	1750.0	1869.9
120°	1663.5	1780.1
122.5°	1579.3	1694.3
125°	1459.2	1565.2
127.5°	1351.2	1440.6
130°	1287.6	1370.2
132.5°	1229.8	1303.8
135°	1150.8	1214.5
137.5°	1087.3	1139.4
140°	1043.7	1092.5
142.5°	1007.6	1049.6
145°	953.6	985.3
147.5°	912.0	938.3
150°	885.9	907.2
152.5°	863.4	879.6
155°	837.8	848.5
157.5°	817.5	825.0
160°	805.4	809.7
162.5°	797.5	801.5
165°	785.9	790.3
167.5°	777.8	779.5
170°	775.5	775.5
172.5°	769.4	767.8
175°	765.7	765.7
177.5°	762.5	760.7
180°	760.7	760.7



TEST NUMBER: P938183
 CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-4-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.97	6.82	6.96	7.83	9.16	19.11	19.96	20.10	20.97	22.30
	3H	6.67	7.44	7.67	8.45	9.81	20.93	21.69	21.93	22.71	24.07
	4H	6.97	7.69	7.99	8.72	10.08	21.56	22.29	22.58	23.31	24.68
	6H	7.22	7.89	8.25	8.91	10.30	21.98	22.65	23.01	23.67	25.06
	8H	7.29	7.93	8.32	8.97	10.34	22.09	22.73	23.13	23.77	25.15
	12H	7.31	7.91	8.34	8.95	10.35	22.16	22.76	23.19	23.80	25.20
4H	2H	13.16	13.88	14.18	14.90	16.27	19.38	20.10	20.40	21.13	22.49
	3H	14.72	15.33	15.76	16.38	17.76	21.41	22.02	22.44	23.07	24.45
	4H	14.82	15.38	15.86	16.42	17.82	22.17	22.72	23.20	23.76	25.17
	6H	14.83	15.31	15.88	16.37	17.77	22.69	23.17	23.74	24.24	25.63
	8H	14.81	15.26	15.86	16.31	17.73	22.85	23.29	23.90	24.35	25.77
	12H	14.76	15.17	15.83	16.24	17.66	22.93	23.34	24.00	24.41	25.83
8H	4H	16.25	16.70	17.30	17.76	19.17	22.23	22.67	23.28	23.73	25.15
	6H	16.50	16.87	17.57	17.97	19.38	22.84	23.21	23.92	24.31	25.72
	8H	16.51	16.84	17.59	17.92	19.35	23.05	23.38	24.14	24.46	25.90
	12H	16.48	16.77	17.57	17.85	19.32	23.19	23.48	24.28	24.56	26.03
12H	4H	16.39	16.80	17.46	17.87	19.29	22.18	22.58	23.25	23.66	25.08
	6H	16.75	17.08	17.83	18.16	19.59	22.83	23.15	23.91	24.23	25.67
	8H	16.82	17.11	17.90	18.18	19.66	23.05	23.33	24.13	24.41	25.88