

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934079

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934079
REPORT IS A COMBINATION OF REPORTS P933681 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13340.2 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934079
CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79			79
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70	67			67
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59	56			56
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	47			47
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41			41
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38	35			35
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33	31			31
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30	27			27
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26	24			24
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24	22			22
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22	20			20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12557	12557	12557	12557
5°	12656	12676	12656	9967
10°	12575	12486	12575	8927
15°	12443	12216	12443	10200
20°	12188	11896	12188	10222
25°	11660	11428	11660	10005
30°	10976	11040	10976	9530
35°	9791	10549	9791	9007
40°	8163	9971	8163	8612
45°	7298	9295	7298	8158
50°	7759	8488	7759	7702
55°	7307	7619	7307	7438
60°	7542	6471	7542	6813
65°	6849	5349	6849	5979
70°	4754	4263	4754	5012
75°	4184	3151	4184	3773
80°	3397	2083	3397	2268
85°	1990	1103	1990	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 11178 cd/sqm



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.5	2.7
10°-20°	1040.5	7.8
20°-30°	1608.4	12.1
30°-40°	1920.1	14.4
40°-50°	1931.4	14.5
50°-60°	1680.5	12.6
60°-70°	1191.5	8.9
70°-80°	630.4	4.7
80°-90°	158.6	1.2
90°-100°	211.5	1.6
100°-110°	556.0	4.2
110°-120°	576.5	4.3
120°-130°	462.4	3.5
130°-140°	362.8	2.7
140°-150°	278.5	2.1
150°-160°	200.6	1.5
160°-170°	122.7	0.9
170°-180°	41.5	0.3
0°-30°	3015.4	22.6
0°-40°	4935.5	37.0
0°-60°	8547.4	64.1
0°-90°	10527.9	78.9
90°-120°	1343.9	10.1
90°-150°	2447.6	18.3
90°-180°	2812.0	21.1
0°-180°	13340.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	4060	4060	4060	4060	4060	
5°	4079	4206	4079	3307	4079	387
15°	3895	4167	3895	3480	3895	1096
25°	3430	3887	3430	3403	3430	1575
35°	2608	3468	2608	2961	2608	1613
45°	1682	2858	1682	2508	1682	1348
55°	1371	2109	1371	2059	1371	1260
65°	952	1271	952	1421	952	910
75°	361	603	361	722	361	380
85°	61	154	61	131	61	83
90°	3	11	3	11	3	5
95°	28	128	28	128	28	31
105°	100	870	100	870	100	106
115°	178	1121	178	1121	178	176
125°	248	893	248	893	248	220
135°	295	693	295	693	295	228
145°	342	562	342	562	342	214
155°	387	484	387	484	387	178
165°	417	451	417	451	417	118
175°	434	437	434	437	434	41
180°	434	434	434	434	434	



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7
2.5°	4094.3	4094.3	4117.4	4125.0	4125.0	4113.5	4102.0	4113.5	4148.1	4159.6	4155.8
5°	4079.0	4109.7	4152.0	4159.6	4167.3	4163.5	4155.8	4163.5	4201.9	4209.5	4213.4
7.5°	4048.2	4105.8	4159.6	4171.2	4182.7	4171.2	4167.3	4175.0	4213.4	4221.1	4221.1
10°	4009.8	4090.5	4152.0	4159.6	4171.2	4159.6	4159.6	4175.0	4213.4	4221.1	4224.9
12.5°	3956.0	4067.5	4125.0	4132.8	4148.1	4144.2	4140.4	4155.8	4194.2	4201.9	4201.9
15°	3894.6	4025.2	4079.0	4086.7	4113.5	4105.8	4105.8	4121.3	4163.5	4175.0	4171.2
17.5°	3810.1	3971.4	4032.9	4044.4	4063.6	4059.7	4063.6	4079.0	4117.4	4125.0	4128.9
20°	3714.1	3898.5	3971.4	3983.0	4002.2	4002.2	4002.2	4021.4	4059.7	4075.1	4075.1
22.5°	3583.5	3821.6	3898.5	3906.1	3929.2	3929.2	3936.9	3963.7	3998.3	4002.2	4002.2
25°	3429.9	3737.1	3802.5	3825.5	3848.5	3860.0	3871.5	3886.9	3898.5	3894.6	3898.5
27.5°	3268.5	3629.6	3714.1	3729.5	3760.2	3771.7	3787.0	3790.9	3794.7	3806.2	3798.6
30°	3088.0	3479.8	3606.5	3621.9	3671.8	3679.5	3664.2	3671.8	3691.0	3698.8	3706.4
32.5°	2884.4	3257.0	3495.2	3529.7	3575.8	3552.7	3549.0	3560.5	3591.2	3591.2	3598.9
35°	2608.0	3084.2	3391.5	3422.2	3456.7	3429.9	3445.2	3449.1	3468.2	3479.8	3476.0
37.5°	2304.5	2934.4	3283.9	3307.0	3333.8	3299.3	3322.3	3333.8	3349.3	3341.5	3341.5
40°	2035.7	2700.1	3157.2	3172.5	3195.6	3168.7	3191.7	3199.4	3207.1	3199.4	3195.6
42.5°	1836.0	2442.8	3022.7	3042.0	3026.6	3045.8	3053.4	3068.8	3057.3	3042.0	3042.0
45°	1682.3	2373.7	2876.8	2899.8	2876.8	2907.5	2919.0	2919.0	2884.4	2876.8	2873.0
47.5°	1632.4	2235.4	2730.8	2730.8	2719.3	2757.7	2777.0	2750.0	2715.4	2704.0	2704.0
50°	1628.5	2081.7	2531.1	2515.7	2569.5	2615.6	2596.4	2569.5	2542.7	2500.4	2500.4
52.5°	1478.7	1893.5	2273.8	2331.4	2415.9	2442.8	2412.0	2385.2	2339.1	2319.9	2304.5
55°	1371.1	1697.7	2039.5	2154.7	2243.0	2277.6	2220.0	2193.1	2124.0	2112.4	2104.8
57.5°	1348.2	1413.4	1824.4	1970.4	2077.9	2074.0	2039.5	1989.6	1931.9	1920.5	1916.6
60°	1236.7	1021.6	1593.9	1766.8	1878.2	1866.7	1836.0	1789.8	1736.1	1728.4	1720.7
62.5°	1121.5	741.3	1332.8	1528.7	1686.2	1682.3	1655.4	1586.3	1547.9	1528.7	1513.3
65°	952.5	622.2	948.7	1271.3	1497.9	1505.6	1448.0	1398.1	1355.8	1332.8	1328.9
67.5°	725.9	507.0	641.4	1060.1	1317.5	1309.7	1236.7	1213.7	1159.9	1148.4	1125.4
70°	537.7	338.0	445.5	860.4	1140.7	1121.5	1063.9	1037.0	987.1	960.2	944.9
72.5°	445.5	272.7	326.5	668.3	960.2	937.1	887.2	856.5	814.3	791.2	775.9
75°	361.0	288.1	249.6	495.4	779.7	764.3	718.2	687.5	652.9	622.2	626.1
77.5°	265.0	268.9	199.7	364.9	618.4	595.4	568.4	530.0	514.6	483.9	483.9
80°	199.7	211.2	149.8	249.6	445.5	445.5	422.5	395.6	368.7	353.4	353.4
82.5°	134.4	134.4	111.3	157.5	303.4	291.9	276.6	268.9	253.5	245.8	245.8
85°	61.4	76.8	69.1	96.0	165.1	172.9	172.9	165.1	161.3	153.6	157.5
87.5°	19.2	34.6	42.2	53.8	84.5	88.4	92.2	92.2	92.2	96.0	96.0
90°	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.7	14.7	11.0	11.0
92.5°	11.6	31.4	51.3	56.2	79.0	109.4	124.6	109.2	78.4	55.3	53.1
95°	27.9	64.1	100.4	109.5	194.4	307.7	364.2	325.0	246.6	187.8	181.1
97.5°	48.4	80.3	112.3	120.3	261.8	450.7	545.1	520.3	470.7	433.5	420.8
100°	64.1	93.0	122.0	129.3	286.4	495.9	600.7	602.5	606.1	608.8	593.7
102.5°	77.4	104.5	131.5	138.3	297.7	510.2	616.4	648.0	711.1	758.4	745.5
105°	100.2	123.1	145.9	151.6	306.0	511.7	614.6	685.4	826.9	933.1	926.2
107.5°	123.5	144.8	166.2	171.5	307.6	489.0	579.7	678.4	875.9	1024.0	1025.7
110°	139.1	158.4	177.7	182.6	305.2	468.8	550.6	661.0	881.7	1047.3	1054.6



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	154.7	173.0	191.4	195.9	305.3	451.2	524.1	637.1	863.0	1032.5	1043.6
115°	177.9	194.9	211.8	216.1	308.1	430.9	492.3	601.2	818.8	982.1	997.5
117.5°	200.9	216.3	231.7	235.6	313.9	418.3	470.5	568.8	765.2	912.5	929.7
120°	214.2	228.8	243.3	246.9	318.5	414.0	461.7	551.5	731.0	865.6	882.3
122.5°	227.4	242.1	256.6	260.3	325.2	411.7	455.0	535.9	697.5	818.7	835.1
125°	247.5	260.9	274.2	277.5	334.3	410.0	447.8	516.4	653.7	756.7	771.8
127.5°	263.8	277.2	290.7	294.1	343.3	408.9	441.7	500.6	618.5	706.9	719.7
130°	272.5	287.0	301.6	305.1	349.9	409.5	439.3	491.9	596.8	675.5	687.3
132.5°	281.6	296.0	310.6	314.1	355.2	410.0	437.3	484.3	578.3	648.7	659.3
135°	295.0	308.1	321.3	324.6	361.0	409.6	433.8	473.2	551.8	610.9	620.0
137.5°	308.6	321.7	334.7	338.0	369.8	412.1	433.2	466.5	532.9	582.9	590.3
140°	320.0	332.0	344.1	347.1	375.1	412.5	431.2	459.9	517.3	560.5	567.4
142.5°	328.7	339.8	351.0	353.8	379.6	414.0	431.2	456.4	506.9	544.8	550.8
145°	342.2	351.8	361.5	364.0	385.4	414.0	428.3	448.9	490.2	521.1	525.7
147.5°	355.5	364.9	374.4	376.7	393.9	416.9	428.3	444.6	477.0	501.4	505.1
150°	364.2	372.8	381.3	383.4	398.4	418.3	428.3	442.1	469.5	490.0	493.0
152.5°	373.3	379.8	386.1	387.8	401.3	419.3	428.3	440.0	463.5	481.0	483.3
155°	386.6	391.4	396.2	397.4	407.7	421.4	428.3	437.6	456.3	470.3	471.8
157.5°	396.5	401.2	405.9	407.1	414.2	423.5	428.3	435.6	450.0	460.9	461.9
160°	403.3	406.9	410.6	411.4	417.1	424.5	428.3	434.5	446.9	456.2	456.8
162.5°	410.0	412.7	415.4	416.1	420.2	425.6	428.3	433.5	444.0	451.8	452.4
165°	417.3	419.7	422.2	422.8	424.6	427.0	428.3	432.1	439.5	445.2	445.7
167.5°	423.9	425.1	426.3	426.6	428.1	430.1	431.2	433.6	438.6	442.3	442.5
170°	428.3	429.5	430.6	430.9	431.0	431.1	431.2	433.6	438.6	442.3	442.3
172.5°	430.6	430.9	431.1	431.2	431.2	431.2	431.2	433.1	437.0	439.9	439.7
175°	433.8	433.8	433.8	433.8	432.9	431.8	431.2	432.5	434.9	436.7	436.7
177.5°	433.8	433.8	433.8	433.8	433.1	432.3	431.8	432.8	434.7	436.1	435.9
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7
2.5°	4163.5	4152.0	4163.5	4155.8	4159.6	4148.1	4113.5	4102.0	4113.5	4125.0	4125.0
5°	4213.4	4205.8	4213.4	4213.4	4209.5	4201.9	4163.5	4155.8	4163.5	4167.3	4159.6
7.5°	4228.7	4217.3	4228.7	4221.1	4221.1	4213.4	4175.0	4167.3	4171.2	4182.7	4171.2
10°	4228.7	4217.3	4228.7	4224.9	4221.1	4213.4	4175.0	4159.6	4159.6	4171.2	4159.6
12.5°	4209.5	4201.9	4209.5	4201.9	4201.9	4194.2	4155.8	4140.4	4144.2	4148.1	4132.8
15°	4178.8	4167.3	4178.8	4171.2	4175.0	4163.5	4121.3	4105.8	4105.8	4113.5	4086.7
17.5°	4132.8	4117.4	4132.8	4128.9	4125.0	4117.4	4079.0	4063.6	4059.7	4063.6	4044.4
20°	4079.0	4067.5	4079.0	4075.1	4075.1	4059.7	4021.4	4002.2	4002.2	4002.2	3983.0
22.5°	3994.5	3983.0	3994.5	4002.2	4002.2	3998.3	3963.7	3936.9	3929.2	3929.2	3906.1
25°	3898.5	3886.9	3898.5	3898.5	3894.6	3898.5	3886.9	3871.5	3860.0	3848.5	3825.5
27.5°	3806.2	3798.6	3806.2	3798.6	3806.2	3794.7	3790.9	3787.0	3771.7	3760.2	3729.5
30°	3714.1	3706.4	3714.1	3706.4	3698.8	3691.0	3671.8	3664.2	3679.5	3671.8	3621.9
32.5°	3598.9	3591.2	3598.9	3598.9	3591.2	3591.2	3560.5	3549.0	3552.7	3575.8	3529.7
35°	3479.8	3468.2	3479.8	3476.0	3479.8	3468.2	3449.1	3445.2	3429.9	3456.7	3422.2
37.5°	3341.5	3330.0	3341.5	3341.5	3341.5	3349.3	3333.8	3322.3	3299.3	3333.8	3307.0
40°	3199.4	3184.0	3199.4	3195.6	3199.4	3207.1	3199.4	3191.7	3168.7	3195.6	3172.5
42.5°	3038.1	3034.2	3038.1	3042.0	3042.0	3057.3	3068.8	3053.4	3045.8	3026.6	3042.0
45°	2865.2	2857.6	2865.2	2873.0	2876.8	2884.4	2919.0	2919.0	2907.5	2876.8	2899.8
47.5°	2680.9	2661.7	2680.9	2704.0	2704.0	2715.4	2750.0	2777.0	2757.7	2719.3	2730.8
50°	2485.0	2488.9	2485.0	2500.4	2500.4	2542.7	2569.5	2596.4	2615.6	2569.5	2515.7
52.5°	2292.9	2289.2	2292.9	2304.5	2319.9	2339.1	2385.2	2412.0	2442.8	2415.9	2331.4
55°	2100.9	2108.6	2100.9	2104.8	2112.4	2124.0	2193.1	2220.0	2277.6	2243.0	2154.7
57.5°	1908.9	1897.4	1908.9	1916.6	1920.5	1931.9	1989.6	2039.5	2074.0	2077.9	1970.4
60°	1686.2	1670.7	1686.2	1720.7	1728.4	1736.1	1789.8	1836.0	1866.7	1878.2	1766.8
62.5°	1490.2	1463.4	1490.2	1513.3	1528.7	1547.9	1586.3	1655.4	1682.3	1686.2	1528.7
65°	1282.9	1271.3	1282.9	1328.9	1332.8	1355.8	1398.1	1448.0	1505.6	1497.9	1271.3
67.5°	1094.7	1094.7	1094.7	1125.4	1148.4	1159.9	1213.7	1236.7	1309.7	1317.5	1060.1
70°	921.8	917.9	921.8	944.9	960.2	987.1	1037.0	1063.9	1121.5	1140.7	860.4
72.5°	756.7	752.8	756.7	775.9	791.2	814.3	856.5	887.2	937.1	960.2	668.3
75°	610.7	603.0	610.7	626.1	622.2	652.9	687.5	718.2	764.3	779.7	495.4
77.5°	468.6	468.6	468.6	483.9	483.9	514.6	530.0	568.4	595.4	618.4	364.9
80°	349.5	345.6	349.5	353.4	353.4	368.7	395.6	422.5	445.5	445.5	249.6
82.5°	245.8	238.1	245.8	245.8	245.8	253.5	268.9	276.6	291.9	303.4	157.5
85°	153.6	153.6	153.6	157.5	153.6	161.3	165.1	172.9	172.9	165.1	96.0
87.5°	99.9	96.0	99.9	96.0	96.0	92.2	92.2	92.2	88.4	84.5	53.8
90°	11.0	11.0	11.0	11.0	11.0	14.7	19.7	22.1	19.0	12.8	8.1
92.5°	44.4	35.6	44.4	53.1	55.3	78.4	109.2	124.6	109.4	79.0	56.2
95°	154.5	127.8	154.5	181.1	187.8	246.6	325.0	364.2	307.7	194.4	109.5
97.5°	370.2	319.4	370.2	420.8	433.5	470.7	520.3	545.1	450.7	261.8	120.3
100°	533.3	472.9	533.3	593.7	608.8	606.1	602.5	600.7	495.9	286.4	129.3
102.5°	693.7	642.0	693.7	745.5	758.4	711.1	648.0	616.4	510.2	297.7	138.3
105°	898.4	870.5	898.4	926.2	933.1	826.9	685.4	614.6	511.7	306.0	151.6
107.5°	1032.5	1039.2	1032.5	1025.7	1024.0	875.9	678.4	579.7	489.0	307.6	171.5
110°	1083.5	1112.5	1083.5	1054.6	1047.3	881.7	661.0	550.6	468.8	305.2	182.6



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1088.1	1132.6	1088.1	1043.6	1032.5	863.0	637.1	524.1	451.2	305.3	195.9
115°	1059.2	1120.9	1059.2	997.5	982.1	818.8	601.2	492.3	430.9	308.1	216.1
117.5°	998.1	1066.5	998.1	929.7	912.5	765.2	568.8	470.5	418.3	313.9	235.6
120°	948.7	1015.2	948.7	882.3	865.6	731.0	551.5	461.7	414.0	318.5	246.9
122.5°	900.8	966.4	900.8	835.1	818.7	697.5	535.9	455.0	411.7	325.2	260.3
125°	832.2	892.6	832.2	771.8	756.7	653.7	516.4	447.8	410.0	334.3	277.5
127.5°	770.6	821.6	770.6	719.7	706.9	618.5	500.6	441.7	408.9	343.3	294.1
130°	734.4	781.5	734.4	687.3	675.5	596.8	491.9	439.3	409.5	349.9	305.1
132.5°	701.5	743.6	701.5	659.3	648.7	578.3	484.3	437.3	410.0	355.2	314.1
135°	656.3	692.6	656.3	620.0	610.9	551.8	473.2	433.8	409.6	361.0	324.6
137.5°	620.1	649.9	620.1	590.3	582.9	532.9	466.5	433.2	412.1	369.8	338.0
140°	595.3	623.1	595.3	567.4	560.5	517.3	459.9	431.2	412.5	375.1	347.1
142.5°	574.7	598.6	574.7	550.8	544.8	506.9	456.4	431.2	414.0	379.6	353.8
145°	543.8	561.9	543.8	525.7	521.1	490.2	448.9	428.3	414.0	385.4	364.0
147.5°	520.2	535.2	520.2	505.1	501.4	477.0	444.6	428.3	416.9	393.9	376.7
150°	505.2	517.3	505.2	493.0	490.0	469.5	442.1	428.3	418.3	398.4	383.4
152.5°	492.4	501.7	492.4	483.3	481.0	463.5	440.0	428.3	419.3	401.3	387.8
155°	477.8	483.9	477.8	471.8	470.3	456.3	437.6	428.3	421.4	407.7	397.4
157.5°	466.3	470.5	466.3	461.9	460.9	450.0	435.6	428.3	423.5	414.2	407.1
160°	459.3	461.7	459.3	456.8	456.2	446.9	434.5	428.3	424.5	417.1	411.4
162.5°	454.8	457.1	454.8	452.4	451.8	444.0	433.5	428.3	425.6	420.2	416.1
165°	448.3	450.7	448.3	445.7	445.2	439.5	432.1	428.3	427.0	424.6	422.8
167.5°	443.5	444.6	443.5	442.5	442.3	438.6	433.6	431.2	430.1	428.1	426.6
170°	442.3	442.3	442.3	442.3	442.3	438.6	433.6	431.2	431.1	431.0	430.9
172.5°	438.8	437.9	438.8	439.7	439.9	437.0	433.1	431.2	431.2	431.2	431.2
175°	436.7	436.7	436.7	436.7	436.7	434.9	432.5	431.2	431.8	432.9	433.8
177.5°	434.9	433.8	434.9	435.9	436.1	434.7	432.8	431.8	432.3	433.1	433.8
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7
2.5°	4117.4	4094.3	4094.3	4055.9	4040.5	4029.0	4009.8	3952.3	3936.9	3921.4	3944.5
5°	4152.0	4109.7	4079.0	4009.8	3952.3	3929.2	3856.2	3718.0	3625.7	3556.6	3518.2
7.5°	4159.6	4105.8	4048.2	3940.7	3802.5	3741.0	3518.2	3264.8	3195.6	3134.1	3095.7
10°	4152.0	4090.5	4009.8	3848.5	3522.0	3414.5	3191.7	3026.6	2984.3	2972.8	2984.3
12.5°	4125.0	4067.5	3956.0	3687.2	3230.2	3157.2	3026.6	2930.5	2922.9	2942.1	3045.8
15°	4079.0	4025.2	3894.6	3472.1	3068.8	3015.0	2922.9	2888.3	2930.5	3064.9	3376.1
17.5°	4032.9	3971.4	3810.1	3260.9	2946.0	2907.5	2842.2	2911.4	3149.4	3330.0	3433.7
20°	3971.4	3898.5	3714.1	3107.2	2857.6	2823.0	2792.3	3103.4	3283.9	3349.3	3406.8
22.5°	3898.5	3821.6	3583.5	2999.7	2765.4	2738.5	2757.7	3211.0	3283.9	3330.0	3380.0
25°	3802.5	3737.1	3429.9	2915.2	2692.5	2661.7	2734.7	3199.4	3241.7	3253.2	3353.0
27.5°	3714.1	3629.6	3268.5	2838.4	2604.1	2592.6	2753.9	3149.4	3180.3	3191.7	3299.3
30°	3606.5	3479.8	3088.0	2757.7	2511.9	2508.1	2757.7	3088.0	3080.4	3111.1	3218.6
32.5°	3495.2	3257.0	2884.4	2657.9	2423.6	2419.7	2730.8	2995.9	2988.2	3030.5	3111.1
35°	3391.5	3084.2	2608.0	2542.7	2312.2	2316.0	2665.5	2888.3	2892.2	2930.5	2980.5
37.5°	3283.9	2934.4	2304.5	2415.9	2204.7	2204.7	2577.2	2788.5	2780.7	2792.3	2861.5
40°	3157.2	2700.1	2035.7	2250.7	2104.8	2093.2	2469.7	2680.9	2654.0	2650.2	2746.2
42.5°	3022.7	2442.8	1836.0	2031.8	1989.6	1974.1	2339.1	2550.3	2500.4	2511.9	2634.8
45°	2876.8	2373.7	1682.3	1716.9	1870.5	1858.9	2196.9	2400.5	2365.9	2396.7	2523.5
47.5°	2730.8	2235.4	1632.4	1424.9	1743.7	1739.9	2039.5	2254.6	2235.4	2266.1	2400.5
50°	2531.1	2081.7	1628.5	1221.4	1601.7	1617.0	1851.3	2112.4	2112.4	2139.4	2281.4
52.5°	2273.8	1893.5	1478.7	1106.1	1436.4	1482.6	1686.2	1989.6	1997.2	2024.1	2150.9
55°	2039.5	1697.7	1371.1	1017.8	1240.6	1340.4	1524.8	1862.8	1878.2	1905.1	2020.3
57.5°	1824.4	1413.4	1348.2	914.2	1060.1	1156.1	1382.7	1739.9	1747.6	1770.7	1882.0
60°	1593.9	1021.6	1236.7	802.7	902.6	975.6	1252.1	1593.9	1620.8	1636.2	1732.2
62.5°	1332.8	741.3	1121.5	725.9	825.8	841.2	1144.6	1455.6	1490.2	1501.8	1559.4
65°	948.7	622.2	952.5	660.7	745.2	748.9	1029.4	1313.6	1344.3	1363.5	1405.7
67.5°	641.4	507.0	725.9	599.1	683.6	687.5	917.9	1148.4	1190.6	1206.0	1233.0
70°	445.5	338.0	537.7	533.9	614.5	622.2	798.9	998.7	1037.0	1048.6	1063.9
72.5°	326.5	272.7	445.5	480.1	541.6	549.2	676.0	829.7	868.0	879.6	887.2
75°	249.6	288.1	361.0	418.6	460.9	464.7	553.1	676.0	702.9	710.6	714.3
77.5°	199.7	268.9	265.0	338.0	376.4	368.7	434.0	522.4	545.4	545.4	545.4
80°	149.8	211.2	199.7	242.0	276.6	268.9	311.1	372.6	380.2	387.9	384.1
82.5°	111.3	134.4	134.4	153.6	184.4	176.6	207.4	242.0	242.0	242.0	249.6
85°	69.1	76.8	61.4	80.6	103.7	99.9	115.2	130.6	134.4	134.4	126.7
87.5°	42.2	34.6	19.2	30.7	46.1	46.1	53.8	57.7	53.8	53.8	53.8
90°	7.6	5.2	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.7	14.7
92.5°	51.3	31.4	11.6	31.4	51.3	56.2	79.0	109.4	124.6	109.2	78.4
95°	100.4	64.1	27.9	64.1	100.4	109.5	194.4	307.7	364.2	325.0	246.6
97.5°	112.3	80.3	48.4	80.3	112.3	120.3	261.8	450.7	545.1	520.3	470.7
100°	122.0	93.0	64.1	93.0	122.0	129.3	286.4	495.9	600.7	602.5	606.1
102.5°	131.5	104.5	77.4	104.5	131.5	138.3	297.7	510.2	616.4	648.0	711.1
105°	145.9	123.1	100.2	123.1	145.9	151.6	306.0	511.7	614.6	685.4	826.9
107.5°	166.2	144.8	123.5	144.8	166.2	171.5	307.6	489.0	579.7	678.4	875.9
110°	177.7	158.4	139.1	158.4	177.7	182.6	305.2	468.8	550.6	661.0	881.7



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	191.4	173.0	154.7	173.0	191.4	195.9	305.3	451.2	524.1	637.1	863.0
115°	211.8	194.9	177.9	194.9	211.8	216.1	308.1	430.9	492.3	601.2	818.8
117.5°	231.7	216.3	200.9	216.3	231.7	235.6	313.9	418.3	470.5	568.8	765.2
120°	243.3	228.8	214.2	228.8	243.3	246.9	318.5	414.0	461.7	551.5	731.0
122.5°	256.6	242.1	227.4	242.1	256.6	260.3	325.2	411.7	455.0	535.9	697.5
125°	274.2	260.9	247.5	260.9	274.2	277.5	334.3	410.0	447.8	516.4	653.7
127.5°	290.7	277.2	263.8	277.2	290.7	294.1	343.3	408.9	441.7	500.6	618.5
130°	301.6	287.0	272.5	287.0	301.6	305.1	349.9	409.5	439.3	491.9	596.8
132.5°	310.6	296.0	281.6	296.0	310.6	314.1	355.2	410.0	437.3	484.3	578.3
135°	321.3	308.1	295.0	308.1	321.3	324.6	361.0	409.6	433.8	473.2	551.8
137.5°	334.7	321.7	308.6	321.7	334.7	338.0	369.8	412.1	433.2	466.5	532.9
140°	344.1	332.0	320.0	332.0	344.1	347.1	375.1	412.5	431.2	459.9	517.3
142.5°	351.0	339.8	328.7	339.8	351.0	353.8	379.6	414.0	431.2	456.4	506.9
145°	361.5	351.8	342.2	351.8	361.5	364.0	385.4	414.0	428.3	448.9	490.2
147.5°	374.4	364.9	355.5	364.9	374.4	376.7	393.9	416.9	428.3	444.6	477.0
150°	381.3	372.8	364.2	372.8	381.3	383.4	398.4	418.3	428.3	442.1	469.5
152.5°	386.1	379.8	373.3	379.8	386.1	387.8	401.3	419.3	428.3	440.0	463.5
155°	396.2	391.4	386.6	391.4	396.2	397.4	407.7	421.4	428.3	437.6	456.3
157.5°	405.9	401.2	396.5	401.2	405.9	407.1	414.2	423.5	428.3	435.6	450.0
160°	410.6	406.9	403.3	406.9	410.6	411.4	417.1	424.5	428.3	434.5	446.9
162.5°	415.4	412.7	410.0	412.7	415.4	416.1	420.2	425.6	428.3	433.5	444.0
165°	422.2	419.7	417.3	419.7	422.2	422.8	424.6	427.0	428.3	432.1	439.5
167.5°	426.3	425.1	423.9	425.1	426.3	426.6	428.1	430.1	431.2	433.6	438.6
170°	430.6	429.5	428.3	429.5	430.6	430.9	431.0	431.1	431.2	433.6	438.6
172.5°	431.1	430.9	430.6	430.9	431.1	431.2	431.2	431.2	431.2	433.1	437.0
175°	433.8	433.8	433.8	433.8	433.8	433.8	432.9	431.8	431.2	432.5	434.9
177.5°	433.8	433.8	433.8	433.8	433.8	433.8	433.1	432.3	431.8	432.8	434.7
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934079
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7	4059.7
2.5°	3917.7	3906.1	3921.4	3879.2	3921.4	3906.1	3917.7	3944.5	3921.4	3936.9	3952.3
5°	3437.5	3418.3	3356.9	3307.0	3356.9	3418.3	3437.5	3518.2	3556.6	3625.7	3718.0
7.5°	3072.7	3057.3	3042.0	3011.2	3042.0	3057.3	3072.7	3095.7	3134.1	3195.6	3264.8
10°	2992.0	2995.9	3018.9	3015.0	3018.9	2995.9	2992.0	2984.3	2972.8	2984.3	3026.6
12.5°	3199.4	3233.9	3360.7	3353.0	3360.7	3233.9	3199.4	3045.8	2942.1	2922.9	2930.5
15°	3437.5	3449.1	3476.0	3479.8	3476.0	3449.1	3437.5	3376.1	3064.9	2930.5	2888.3
17.5°	3460.6	3464.5	3483.7	3483.7	3483.7	3464.5	3460.6	3433.7	3330.0	3149.4	2911.4
20°	3441.4	3449.1	3487.4	3495.2	3487.4	3449.1	3441.4	3406.8	3349.3	3283.9	3103.4
22.5°	3433.7	3449.1	3479.8	3476.0	3479.8	3449.1	3433.7	3380.0	3330.0	3283.9	3211.0
25°	3395.3	3395.3	3399.2	3402.9	3399.2	3395.3	3395.3	3353.0	3253.2	3241.7	3199.4
27.5°	3314.7	3322.3	3345.4	3341.5	3345.4	3322.3	3314.7	3299.3	3191.7	3180.3	3149.4
30°	3241.7	3233.9	3214.8	3199.4	3214.8	3233.9	3241.7	3218.6	3111.1	3080.4	3088.0
32.5°	3118.7	3099.5	3080.4	3068.8	3080.4	3099.5	3118.7	3111.1	3030.5	2988.2	2995.9
35°	2972.8	2976.7	2972.8	2961.3	2972.8	2976.7	2972.8	2980.5	2930.5	2892.2	2888.3
37.5°	2869.1	2876.8	2873.0	2857.6	2873.0	2876.8	2869.1	2861.5	2792.3	2780.7	2788.5
40°	2761.6	2765.4	2761.6	2750.0	2761.6	2765.4	2761.6	2746.2	2650.2	2654.0	2680.9
42.5°	2657.9	2654.0	2642.5	2634.8	2642.5	2654.0	2657.9	2634.8	2511.9	2500.4	2550.3
45°	2538.8	2542.7	2519.6	2508.1	2519.6	2542.7	2538.8	2523.5	2396.7	2365.9	2400.5
47.5°	2419.7	2419.7	2400.5	2389.0	2400.5	2419.7	2419.7	2400.5	2266.1	2235.4	2254.6
50°	2292.9	2289.2	2262.2	2258.4	2262.2	2289.2	2292.9	2281.4	2139.4	2112.4	2112.4
52.5°	2147.0	2147.0	2150.9	2158.5	2150.9	2147.0	2147.0	2150.9	2024.1	1997.2	1989.6
55°	2020.3	2024.1	2051.0	2058.6	2051.0	2024.1	2020.3	2020.3	1905.1	1878.2	1862.8
57.5°	1889.6	1889.6	1908.9	1908.9	1908.9	1889.6	1889.6	1882.0	1770.7	1747.6	1739.9
60°	1739.9	1747.6	1762.9	1759.1	1762.9	1747.6	1739.9	1732.2	1636.2	1620.8	1593.9
62.5°	1582.4	1590.1	1593.9	1586.3	1593.9	1590.1	1582.4	1559.4	1501.8	1490.2	1455.6
65°	1417.3	1424.9	1428.8	1421.1	1428.8	1424.9	1417.3	1405.7	1363.5	1344.3	1313.6
67.5°	1248.3	1244.4	1240.6	1255.9	1240.6	1244.4	1248.3	1233.0	1206.0	1190.6	1148.4
70°	1075.4	1075.4	1071.6	1079.3	1071.6	1075.4	1075.4	1063.9	1048.6	1037.0	998.7
72.5°	891.1	887.2	902.6	891.1	902.6	887.2	891.1	887.2	879.6	868.0	829.7
75°	710.6	718.2	710.6	722.1	710.6	718.2	710.6	714.3	710.6	702.9	676.0
77.5°	541.6	549.2	541.6	541.6	541.6	549.2	541.6	545.4	545.4	545.4	522.4
80°	384.1	380.2	380.2	376.4	380.2	380.2	384.1	384.1	387.9	380.2	372.6
82.5°	245.8	242.0	242.0	249.6	242.0	242.0	245.8	249.6	242.0	242.0	242.0
85°	134.4	138.3	130.6	130.6	130.6	138.3	134.4	126.7	134.4	134.4	130.6
87.5°	49.9	46.1	46.1	46.1	46.1	46.1	49.9	53.8	53.8	53.8	57.7
90°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	14.7	19.7	22.1	19.0
92.5°	55.3	53.1	44.4	35.6	44.4	53.1	55.3	78.4	109.2	124.6	109.4
95°	187.8	181.1	154.5	127.8	154.5	181.1	187.8	246.6	325.0	364.2	307.7
97.5°	433.5	420.8	370.2	319.4	370.2	420.8	433.5	470.7	520.3	545.1	450.7
100°	608.8	593.7	533.3	472.9	533.3	593.7	608.8	606.1	602.5	600.7	495.9
102.5°	758.4	745.5	693.7	642.0	693.7	745.5	758.4	711.1	648.0	616.4	510.2
105°	933.1	926.2	898.4	870.5	898.4	926.2	933.1	826.9	685.4	614.6	511.7
107.5°	1024.0	1025.7	1032.5	1039.2	1032.5	1025.7	1024.0	875.9	678.4	579.7	489.0
110°	1047.3	1054.6	1083.5	1112.5	1083.5	1054.6	1047.3	881.7	661.0	550.6	468.8



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1032.5	1043.6	1088.1	1132.6	1088.1	1043.6	1032.5	863.0	637.1	524.1	451.2
115°	982.1	997.5	1059.2	1120.9	1059.2	997.5	982.1	818.8	601.2	492.3	430.9
117.5°	912.5	929.7	998.1	1066.5	998.1	929.7	912.5	765.2	568.8	470.5	418.3
120°	865.6	882.3	948.7	1015.2	948.7	882.3	865.6	731.0	551.5	461.7	414.0
122.5°	818.7	835.1	900.8	966.4	900.8	835.1	818.7	697.5	535.9	455.0	411.7
125°	756.7	771.8	832.2	892.6	832.2	771.8	756.7	653.7	516.4	447.8	410.0
127.5°	706.9	719.7	770.6	821.6	770.6	719.7	706.9	618.5	500.6	441.7	408.9
130°	675.5	687.3	734.4	781.5	734.4	687.3	675.5	596.8	491.9	439.3	409.5
132.5°	648.7	659.3	701.5	743.6	701.5	659.3	648.7	578.3	484.3	437.3	410.0
135°	610.9	620.0	656.3	692.6	656.3	620.0	610.9	551.8	473.2	433.8	409.6
137.5°	582.9	590.3	620.1	649.9	620.1	590.3	582.9	532.9	466.5	433.2	412.1
140°	560.5	567.4	595.3	623.1	595.3	567.4	560.5	517.3	459.9	431.2	412.5
142.5°	544.8	550.8	574.7	598.6	574.7	550.8	544.8	506.9	456.4	431.2	414.0
145°	521.1	525.7	543.8	561.9	543.8	525.7	521.1	490.2	448.9	428.3	414.0
147.5°	501.4	505.1	520.2	535.2	520.2	505.1	501.4	477.0	444.6	428.3	416.9
150°	490.0	493.0	505.2	517.3	505.2	493.0	490.0	469.5	442.1	428.3	418.3
152.5°	481.0	483.3	492.4	501.7	492.4	483.3	481.0	463.5	440.0	428.3	419.3
155°	470.3	471.8	477.8	483.9	477.8	471.8	470.3	456.3	437.6	428.3	421.4
157.5°	460.9	461.9	466.3	470.5	466.3	461.9	460.9	450.0	435.6	428.3	423.5
160°	456.2	456.8	459.3	461.7	459.3	456.8	456.2	446.9	434.5	428.3	424.5
162.5°	451.8	452.4	454.8	457.1	454.8	452.4	451.8	444.0	433.5	428.3	425.6
165°	445.2	445.7	448.3	450.7	448.3	445.7	445.2	439.5	432.1	428.3	427.0
167.5°	442.3	442.5	443.5	444.6	443.5	442.5	442.3	438.6	433.6	431.2	430.1
170°	442.3	442.3	442.3	442.3	442.3	442.3	442.3	438.6	433.6	431.2	431.1
172.5°	439.9	439.7	438.8	437.9	438.8	439.7	439.9	437.0	433.1	431.2	431.2
175°	436.7	436.7	436.7	436.7	436.7	436.7	436.7	434.9	432.5	431.2	431.8
177.5°	436.1	435.9	434.9	433.8	434.9	435.9	436.1	434.7	432.8	431.8	432.3
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	4059.7	4059.7	4059.7	4059.7	4059.7
2.5°	4009.8	4029.0	4040.5	4055.9	4094.3
5°	3856.2	3929.2	3952.3	4009.8	4079.0
7.5°	3518.2	3741.0	3802.5	3940.7	4048.2
10°	3191.7	3414.5	3522.0	3848.5	4009.8
12.5°	3026.6	3157.2	3230.2	3687.2	3956.0
15°	2922.9	3015.0	3068.8	3472.1	3894.6
17.5°	2842.2	2907.5	2946.0	3260.9	3810.1
20°	2792.3	2823.0	2857.6	3107.2	3714.1
22.5°	2757.7	2738.5	2765.4	2999.7	3583.5
25°	2734.7	2661.7	2692.5	2915.2	3429.9
27.5°	2753.9	2592.6	2604.1	2838.4	3268.5
30°	2757.7	2508.1	2511.9	2757.7	3088.0
32.5°	2730.8	2419.7	2423.6	2657.9	2884.4
35°	2665.5	2316.0	2312.2	2542.7	2608.0
37.5°	2577.2	2204.7	2204.7	2415.9	2304.5
40°	2469.7	2093.2	2104.8	2250.7	2035.7
42.5°	2339.1	1974.1	1989.6	2031.8	1836.0
45°	2196.9	1858.9	1870.5	1716.9	1682.3
47.5°	2039.5	1739.9	1743.7	1424.9	1632.4
50°	1851.3	1617.0	1601.7	1221.4	1628.5
52.5°	1686.2	1482.6	1436.4	1106.1	1478.7
55°	1524.8	1340.4	1240.6	1017.8	1371.1
57.5°	1382.7	1156.1	1060.1	914.2	1348.2
60°	1252.1	975.6	902.6	802.7	1236.7
62.5°	1144.6	841.2	825.8	725.9	1121.5
65°	1029.4	748.9	745.2	660.7	952.5
67.5°	917.9	687.5	683.6	599.1	725.9
70°	798.9	622.2	614.5	533.9	537.7
72.5°	676.0	549.2	541.6	480.1	445.5
75°	553.1	464.7	460.9	418.6	361.0
77.5°	434.0	368.7	376.4	338.0	265.0
80°	311.1	268.9	276.6	242.0	199.7
82.5°	207.4	176.6	184.4	153.6	134.4
85°	115.2	99.9	103.7	80.6	61.4
87.5°	53.8	46.1	46.1	30.7	19.2
90°	12.8	8.1	7.6	5.2	2.9
92.5°	79.0	56.2	51.3	31.4	11.6
95°	194.4	109.5	100.4	64.1	27.9
97.5°	261.8	120.3	112.3	80.3	48.4
100°	286.4	129.3	122.0	93.0	64.1
102.5°	297.7	138.3	131.5	104.5	77.4
105°	306.0	151.6	145.9	123.1	100.2
107.5°	307.6	171.5	166.2	144.8	123.5
110°	305.2	182.6	177.7	158.4	139.1



TEST NUMBER: P934079

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	305.3	195.9	191.4	173.0	154.7
115°	308.1	216.1	211.8	194.9	177.9
117.5°	313.9	235.6	231.7	216.3	200.9
120°	318.5	246.9	243.3	228.8	214.2
122.5°	325.2	260.3	256.6	242.1	227.4
125°	334.3	277.5	274.2	260.9	247.5
127.5°	343.3	294.1	290.7	277.2	263.8
130°	349.9	305.1	301.6	287.0	272.5
132.5°	355.2	314.1	310.6	296.0	281.6
135°	361.0	324.6	321.3	308.1	295.0
137.5°	369.8	338.0	334.7	321.7	308.6
140°	375.1	347.1	344.1	332.0	320.0
142.5°	379.6	353.8	351.0	339.8	328.7
145°	385.4	364.0	361.5	351.8	342.2
147.5°	393.9	376.7	374.4	364.9	355.5
150°	398.4	383.4	381.3	372.8	364.2
152.5°	401.3	387.8	386.1	379.8	373.3
155°	407.7	397.4	396.2	391.4	386.6
157.5°	414.2	407.1	405.9	401.2	396.5
160°	417.1	411.4	410.6	406.9	403.3
162.5°	420.2	416.1	415.4	412.7	410.0
165°	424.6	422.8	422.2	419.7	417.3
167.5°	428.1	426.6	426.3	425.1	423.9
170°	431.0	430.9	430.6	429.5	428.3
172.5°	431.2	431.2	431.1	430.9	430.6
175°	432.9	433.8	433.8	433.8	433.8
177.5°	433.1	433.8	433.8	433.8	433.8
180°	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934079
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.94	17.14	16.60	17.81	18.60	18.79	19.99	19.45	20.67	21.45
	3H	16.44	17.52	17.11	18.20	19.03	20.17	21.24	20.84	21.93	22.75
	4H	16.65	17.66	17.34	18.36	19.20	20.63	21.65	21.32	22.35	23.18
	6H	16.78	17.72	17.49	18.43	19.28	20.94	21.88	21.65	22.58	23.43
	8H	16.79	17.69	17.51	18.42	19.27	21.02	21.92	21.74	22.65	23.50
	12H	16.77	17.63	17.50	18.35	19.23	21.08	21.93	21.80	22.65	23.53
4H	2H	17.02	18.03	17.71	18.73	19.57	19.24	20.25	19.94	20.95	21.79
	3H	18.07	18.92	18.78	19.66	20.51	20.78	21.63	21.49	22.36	23.22
	4H	18.36	19.13	19.09	19.87	20.75	21.33	22.09	22.05	22.83	23.72
	6H	18.51	19.17	19.25	19.94	20.83	21.72	22.38	22.46	23.15	24.04
	8H	18.52	19.14	19.27	19.90	20.81	21.83	22.46	22.58	23.22	24.12
	12H	18.50	19.06	19.27	19.85	20.76	21.91	22.47	22.68	23.25	24.16
8H	4H	18.85	19.47	19.60	20.23	21.13	21.48	22.10	22.23	22.86	23.76
	6H	19.12	19.64	19.90	20.44	21.35	21.93	22.45	22.71	23.25	24.16
	8H	19.17	19.63	19.96	20.43	21.35	22.09	22.55	22.88	23.35	24.28
	12H	19.17	19.57	19.96	20.37	21.35	22.21	22.61	23.00	23.41	24.39
12H	4H	18.87	19.43	19.64	20.21	21.12	21.46	22.02	22.23	22.80	23.71
	6H	19.19	19.65	19.98	20.45	21.37	21.93	22.39	22.73	23.20	24.12
	8H	19.27	19.67	20.06	20.47	21.45	22.11	22.52	22.91	23.31	24.29