

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934084

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934084
REPORT IS A COMBINATION OF REPORTS P933682 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4446.7 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 38.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934084
CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · - 135°-315°



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79		
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70	67		
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59	56		
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	47		
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41		
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38	35		
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33	31		
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30	27		
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26	24		
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24	22		
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12557	12557	12557	12557
5°	12638	12676	12638	9967
10°	12539	12486	12539	8927
15°	12388	12216	12388	10200
20°	12115	11895	12115	10221
25°	11571	11428	11571	10005
30°	10873	11040	10873	9530
35°	9678	10549	9678	9007
40°	8051	9971	8051	8612
45°	7180	9294	7180	8159
50°	7609	8489	7609	7702
55°	7140	7619	7140	7438
60°	7332	6471	7332	6812
65°	6616	5348	6616	5979
70°	4552	4263	4552	5013
75°	3945	3151	3945	3773
80°	3117	2083	3117	2269
85°	1689	1103	1689	937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 11024 cd/sqm



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	2.7
10°-20°	346.8	7.8
20°-30°	536.1	12.1
30°-40°	640.0	14.4
40°-50°	643.8	14.5
50°-60°	560.2	12.6
60°-70°	397.2	8.9
70°-80°	210.1	4.7
80°-90°	52.9	1.2
90°-100°	70.5	1.6
100°-110°	185.3	4.2
110°-120°	192.2	4.3
120°-130°	154.1	3.5
130°-140°	120.9	2.7
140°-150°	92.8	2.1
150°-160°	66.8	1.5
160°-170°	40.9	0.9
170°-180°	13.8	0.3
0°-30°	1005.1	22.6
0°-40°	1645.2	37.0
0°-60°	2849.1	64.1
0°-90°	3509.3	78.9
90°-120°	448.0	10.1
90°-150°	815.9	18.3
90°-180°	937.0	21.1
0°-180°	4446.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1353	1353	1353	1353	1353	
5°	1360	1402	1360	1102	1360	129
15°	1298	1389	1298	1160	1298	365
25°	1143	1296	1143	1134	1143	525
35°	869	1156	869	987	869	538
45°	561	952	561	836	561	449
55°	457	703	457	686	457	420
65°	318	424	318	474	318	303
75°	120	201	120	241	120	127
85°	20	51	20	44	20	28
90°	1	4	1	4	1	2
95°	9	43	9	43	9	10
105°	33	290	33	290	33	35
115°	59	374	59	374	59	59
125°	82	298	82	298	82	73
135°	98	231	98	231	98	76
145°	114	187	114	187	114	71
155°	129	161	129	161	129	59
165°	139	150	139	150	139	39
175°	145	146	145	146	145	14
180°	145	145	145	145	145	



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2
2.5°	1364.7	1364.7	1372.5	1375.0	1375.0	1371.1	1367.4	1371.1	1382.7	1386.5	1385.3
5°	1359.7	1369.9	1384.0	1386.5	1389.1	1387.8	1385.3	1387.8	1400.6	1403.2	1404.5
7.5°	1349.4	1368.6	1386.5	1390.4	1394.2	1390.4	1389.1	1391.7	1404.5	1407.0	1407.0
10°	1336.6	1363.5	1384.0	1386.5	1390.4	1386.5	1386.5	1391.7	1404.5	1407.0	1408.3
12.5°	1318.7	1355.8	1375.0	1377.6	1382.7	1381.4	1380.1	1385.3	1398.1	1400.6	1400.6
15°	1298.2	1341.8	1359.7	1362.2	1371.1	1368.6	1368.6	1373.8	1387.8	1391.7	1390.4
17.5°	1270.1	1323.8	1344.3	1348.2	1354.6	1353.2	1354.6	1359.7	1372.5	1375.0	1376.3
20°	1238.0	1299.5	1323.8	1327.6	1334.0	1334.0	1334.0	1340.4	1353.2	1358.3	1358.3
22.5°	1194.5	1273.8	1299.5	1302.0	1309.7	1309.7	1312.3	1321.2	1332.8	1334.0	1334.0
25°	1143.3	1245.7	1267.5	1275.2	1282.9	1286.6	1290.5	1295.6	1299.5	1298.2	1299.5
27.5°	1089.5	1209.9	1238.0	1243.1	1253.4	1257.3	1262.3	1263.7	1264.9	1268.7	1266.2
30°	1029.4	1159.9	1202.1	1207.3	1223.9	1226.5	1221.4	1223.9	1230.3	1233.0	1235.5
32.5°	961.4	1085.7	1165.0	1176.6	1192.0	1184.2	1183.0	1186.8	1197.1	1197.1	1199.6
35°	869.3	1028.1	1130.5	1140.7	1152.2	1143.3	1148.4	1149.7	1156.1	1159.9	1158.6
37.5°	768.1	978.1	1094.7	1102.3	1111.2	1099.7	1107.5	1111.2	1116.4	1113.9	1113.9
40°	678.6	900.0	1052.4	1057.5	1065.2	1056.2	1063.9	1066.5	1069.0	1066.5	1065.2
42.5°	612.0	814.3	1007.6	1014.0	1008.8	1015.2	1017.8	1023.0	1019.1	1014.0	1014.0
45°	560.8	791.2	958.9	966.6	958.9	969.2	973.0	973.0	961.4	958.9	957.7
47.5°	544.1	745.2	910.3	910.3	906.4	919.2	925.7	916.7	905.1	901.4	901.4
50°	542.8	693.9	843.7	838.6	856.5	871.9	865.5	856.5	847.6	833.4	833.4
52.5°	492.9	631.2	758.0	777.1	805.3	814.3	804.0	795.1	779.7	773.3	768.1
55°	457.1	565.9	679.9	718.2	747.7	759.2	740.0	731.0	708.0	704.2	701.6
57.5°	449.4	471.1	608.1	656.8	692.6	691.4	679.9	663.2	644.0	640.1	638.9
60°	412.2	340.5	531.3	589.0	626.1	622.2	612.0	596.6	578.7	576.2	573.6
62.5°	373.8	247.1	444.3	509.6	562.0	560.8	551.8	528.8	516.0	509.6	504.5
65°	317.5	207.4	316.2	423.7	499.3	501.8	482.7	466.0	451.9	444.3	442.9
67.5°	242.0	169.0	213.8	353.4	439.2	436.5	412.2	404.6	386.6	382.8	375.1
70°	179.3	112.7	148.5	286.8	380.2	373.8	354.7	345.6	329.1	320.1	314.9
72.5°	148.5	90.9	108.8	222.8	320.1	312.4	295.7	285.5	271.4	263.8	258.6
75°	120.3	96.0	83.2	165.1	259.9	254.8	239.4	229.2	217.6	207.4	208.7
77.5°	88.4	89.6	66.6	121.6	206.1	198.5	189.4	176.6	171.5	161.3	161.3
80°	66.6	70.4	49.9	83.2	148.5	148.5	140.8	131.9	122.9	117.8	117.8
82.5°	44.8	44.8	37.1	52.5	101.2	97.3	92.2	89.6	84.5	82.0	82.0
85°	20.4	25.6	23.1	32.0	55.0	57.7	57.7	55.0	53.8	51.2	52.5
87.5°	6.4	11.5	14.1	17.9	28.2	29.5	30.7	30.7	30.7	32.0	32.0
90°	1.0	1.7	2.5	2.7	4.3	6.3	7.4	6.6	4.9	3.7	3.7
92.5°	3.9	10.5	17.1	18.7	26.4	36.5	41.6	36.4	26.2	18.4	17.6
95°	9.3	21.4	33.5	36.5	64.8	102.5	121.4	108.3	82.2	62.6	60.4
97.5°	16.1	26.7	37.4	40.1	87.3	150.2	181.7	173.5	156.9	144.5	140.2
100°	21.3	31.0	40.7	43.1	95.4	165.3	200.2	200.8	202.0	202.9	197.9
102.5°	25.8	34.8	43.9	46.1	99.2	170.1	205.4	216.0	237.0	252.8	248.5
105°	33.4	41.1	48.6	50.6	102.0	170.5	204.8	228.5	275.7	311.0	308.7
107.5°	41.2	48.3	55.4	57.2	102.5	163.0	193.2	226.2	292.0	341.4	342.0
110°	46.4	52.8	59.2	60.9	101.7	156.3	183.5	220.4	293.9	349.1	351.6



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	51.6	57.7	63.8	65.3	101.7	150.4	174.7	212.4	287.7	344.2	347.9
115°	59.3	64.9	70.5	72.0	102.7	143.7	164.1	200.4	273.0	327.3	332.5
117.5°	67.0	72.1	77.2	78.5	104.7	139.4	156.9	189.6	255.0	304.2	309.9
120°	71.4	76.3	81.1	82.3	106.1	138.0	153.9	183.8	243.7	288.6	294.1
122.5°	75.8	80.6	85.5	86.7	108.3	137.2	151.6	178.6	232.5	272.9	278.3
125°	82.5	86.9	91.4	92.5	111.4	136.6	149.2	172.1	217.9	252.2	257.3
127.5°	87.9	92.4	96.9	98.1	114.4	136.2	147.2	166.9	206.2	235.7	239.9
130°	90.8	95.6	100.5	101.7	116.7	136.5	146.4	164.0	198.9	225.2	229.1
132.5°	93.9	98.7	103.6	104.7	118.4	136.6	145.7	161.4	192.7	216.3	219.8
135°	98.4	102.7	107.2	108.2	120.3	136.5	144.6	157.7	183.9	203.6	206.6
137.5°	102.9	107.3	111.6	112.7	123.3	137.3	144.4	155.4	177.6	194.3	196.8
140°	106.7	110.7	114.7	115.7	125.0	137.5	143.7	153.3	172.5	186.8	189.1
142.5°	109.6	113.3	117.0	117.9	126.6	138.0	143.7	152.1	169.0	181.6	183.6
145°	114.1	117.2	120.5	121.3	128.5	138.0	142.7	149.6	163.4	173.7	175.3
147.5°	118.5	121.6	124.8	125.6	131.3	139.0	142.7	148.2	159.0	167.2	168.4
150°	121.4	124.2	127.1	127.8	132.8	139.4	142.7	147.3	156.5	163.4	164.3
152.5°	124.4	126.6	128.7	129.3	133.7	139.7	142.7	146.6	154.5	160.4	161.1
155°	128.9	130.4	132.1	132.5	135.9	140.4	142.7	145.8	152.1	156.8	157.3
157.5°	132.2	133.7	135.3	135.7	138.0	141.2	142.7	145.2	150.0	153.6	154.0
160°	134.4	135.6	136.8	137.1	139.0	141.5	142.7	144.8	148.9	152.0	152.2
162.5°	136.6	137.5	138.5	138.7	140.0	141.9	142.7	144.5	148.0	150.6	150.8
165°	139.1	139.8	140.7	140.9	141.5	142.3	142.7	144.0	146.5	148.4	148.5
167.5°	141.3	141.7	142.1	142.2	142.6	143.3	143.7	144.5	146.1	147.4	147.5
170°	142.7	143.1	143.5	143.6	143.6	143.7	143.7	144.5	146.1	147.4	147.4
172.5°	143.5	143.6	143.7	143.7	143.7	143.7	143.7	144.4	145.6	146.6	146.5
175°	144.6	144.6	144.6	144.6	144.3	143.9	143.7	144.1	145.0	145.5	145.5
177.5°	144.6	144.6	144.6	144.6	144.4	144.1	143.9	144.2	144.9	145.4	145.3
180°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2
2.5°	1387.8	1384.0	1387.8	1385.3	1386.5	1382.7	1371.1	1367.4	1371.1	1375.0	1375.0
5°	1404.5	1401.9	1404.5	1404.5	1403.2	1400.6	1387.8	1385.3	1387.8	1389.1	1386.5
7.5°	1409.6	1405.7	1409.6	1407.0	1407.0	1404.5	1391.7	1389.1	1390.4	1394.2	1390.4
10°	1409.6	1405.7	1409.6	1408.3	1407.0	1404.5	1391.7	1386.5	1386.5	1390.4	1386.5
12.5°	1403.2	1400.6	1403.2	1400.6	1400.6	1398.1	1385.3	1380.1	1381.4	1382.7	1377.6
15°	1392.9	1389.1	1392.9	1390.4	1391.7	1387.8	1373.8	1368.6	1368.6	1371.1	1362.2
17.5°	1377.6	1372.5	1377.6	1376.3	1375.0	1372.5	1359.7	1354.6	1353.2	1354.6	1348.2
20°	1359.7	1355.8	1359.7	1358.3	1358.3	1353.2	1340.4	1334.0	1334.0	1334.0	1327.6
22.5°	1331.5	1327.6	1331.5	1334.0	1334.0	1332.8	1321.2	1312.3	1309.7	1309.7	1302.0
25°	1299.5	1295.6	1299.5	1299.5	1298.2	1299.5	1295.6	1290.5	1286.6	1282.9	1275.2
27.5°	1268.7	1266.2	1268.7	1266.2	1268.7	1264.9	1263.7	1262.3	1257.3	1253.4	1243.1
30°	1238.0	1235.5	1238.0	1235.5	1233.0	1230.3	1223.9	1221.4	1226.5	1223.9	1207.3
32.5°	1199.6	1197.1	1199.6	1199.6	1197.1	1197.1	1186.8	1183.0	1184.2	1192.0	1176.6
35°	1159.9	1156.1	1159.9	1158.6	1159.9	1156.1	1149.7	1148.4	1143.3	1152.2	1140.7
37.5°	1113.9	1110.0	1113.9	1113.9	1113.9	1116.4	1111.2	1107.5	1099.7	1111.2	1102.3
40°	1066.5	1061.3	1066.5	1065.2	1066.5	1069.0	1066.5	1063.9	1056.2	1065.2	1057.5
42.5°	1012.7	1011.4	1012.7	1014.0	1014.0	1019.1	1023.0	1017.8	1015.2	1008.8	1014.0
45°	955.0	952.5	955.0	957.7	958.9	961.4	973.0	973.0	969.2	958.9	966.6
47.5°	893.6	887.2	893.6	901.4	901.4	905.1	916.7	925.7	919.2	906.4	910.3
50°	828.3	829.7	828.3	833.4	833.4	847.6	856.5	865.5	871.9	856.5	838.6
52.5°	764.3	763.1	764.3	768.1	773.3	779.7	795.1	804.0	814.3	805.3	777.1
55°	700.3	702.9	700.3	701.6	704.2	708.0	731.0	740.0	759.2	747.7	718.2
57.5°	636.3	632.5	636.3	638.9	640.1	644.0	663.2	679.9	691.4	692.6	656.8
60°	562.0	556.9	562.0	573.6	576.2	578.7	596.6	612.0	622.2	626.1	589.0
62.5°	496.7	487.8	496.7	504.5	509.6	516.0	528.8	551.8	560.8	562.0	509.6
65°	427.6	423.7	427.6	442.9	444.3	451.9	466.0	482.7	501.8	499.3	423.7
67.5°	364.9	364.9	364.9	375.1	382.8	386.6	404.6	412.2	436.5	439.2	353.4
70°	307.3	306.0	307.3	314.9	320.1	329.1	345.6	354.7	373.8	380.2	286.8
72.5°	252.2	251.0	252.2	258.6	263.8	271.4	285.5	295.7	312.4	320.1	222.8
75°	203.6	201.0	203.6	208.7	207.4	217.6	229.2	239.4	254.8	259.9	165.1
77.5°	156.2	156.2	156.2	161.3	161.3	171.5	176.6	189.4	198.5	206.1	121.6
80°	116.5	115.2	116.5	117.8	117.8	122.9	131.9	140.8	148.5	148.5	83.2
82.5°	82.0	79.4	82.0	82.0	82.0	84.5	89.6	92.2	97.3	101.2	52.5
85°	51.2	51.2	51.2	52.5	51.2	53.8	55.0	57.7	57.7	55.0	32.0
87.5°	33.3	32.0	33.3	32.0	32.0	30.7	30.7	30.7	29.5	28.2	17.9
90°	3.7	3.7	3.7	3.7	3.7	4.9	6.6	7.4	6.3	4.3	2.7
92.5°	14.7	11.8	14.7	17.6	18.4	26.2	36.4	41.6	36.5	26.4	18.7
95°	51.6	42.6	51.6	60.4	62.6	82.2	108.3	121.4	102.5	64.8	36.5
97.5°	123.4	106.5	123.4	140.2	144.5	156.9	173.5	181.7	150.2	87.3	40.1
100°	177.8	157.7	177.8	197.9	202.9	202.0	200.8	200.2	165.3	95.4	43.1
102.5°	231.2	214.0	231.2	248.5	252.8	237.0	216.0	205.4	170.1	99.2	46.1
105°	299.5	290.2	299.5	308.7	311.0	275.7	228.5	204.8	170.5	102.0	50.6
107.5°	344.2	346.4	344.2	342.0	341.4	292.0	226.2	193.2	163.0	102.5	57.2
110°	361.1	370.8	361.1	351.6	349.1	293.9	220.4	183.5	156.3	101.7	60.9



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	362.7	377.5	362.7	347.9	344.2	287.7	212.4	174.7	150.4	101.7	65.3
115°	353.1	373.6	353.1	332.5	327.3	273.0	200.4	164.1	143.7	102.7	72.0
117.5°	332.7	355.5	332.7	309.9	304.2	255.0	189.6	156.9	139.4	104.7	78.5
120°	316.3	338.4	316.3	294.1	288.6	243.7	183.8	153.9	138.0	106.1	82.3
122.5°	300.2	322.1	300.2	278.3	272.9	232.5	178.6	151.6	137.2	108.3	86.7
125°	277.4	297.6	277.4	257.3	252.2	217.9	172.1	149.2	136.6	111.4	92.5
127.5°	256.9	273.8	256.9	239.9	235.7	206.2	166.9	147.2	136.2	114.4	98.1
130°	244.8	260.5	244.8	229.1	225.2	198.9	164.0	146.4	136.5	116.7	101.7
132.5°	233.8	247.9	233.8	219.8	216.3	192.7	161.4	145.7	136.6	118.4	104.7
135°	218.8	230.9	218.8	206.6	203.6	183.9	157.7	144.6	136.5	120.3	108.2
137.5°	206.7	216.7	206.7	196.8	194.3	177.6	155.4	144.4	137.3	123.3	112.7
140°	198.4	207.7	198.4	189.1	186.8	172.5	153.3	143.7	137.5	125.0	115.7
142.5°	191.6	199.5	191.6	183.6	181.6	169.0	152.1	143.7	138.0	126.6	117.9
145°	181.3	187.3	181.3	175.3	173.7	163.4	149.6	142.7	138.0	128.5	121.3
147.5°	173.4	178.4	173.4	168.4	167.2	159.0	148.2	142.7	139.0	131.3	125.6
150°	168.4	172.5	168.4	164.3	163.4	156.5	147.3	142.7	139.4	132.8	127.8
152.5°	164.1	167.2	164.1	161.1	160.4	154.5	146.6	142.7	139.7	133.7	129.3
155°	159.3	161.3	159.3	157.3	156.8	152.1	145.8	142.7	140.4	135.9	132.5
157.5°	155.4	156.9	155.4	154.0	153.6	150.0	145.2	142.7	141.2	138.0	135.7
160°	153.1	153.9	153.1	152.2	152.0	148.9	144.8	142.7	141.5	139.0	137.1
162.5°	151.6	152.3	151.6	150.8	150.6	148.0	144.5	142.7	141.9	140.0	138.7
165°	149.4	150.2	149.4	148.5	148.4	146.5	144.0	142.7	142.3	141.5	140.9
167.5°	147.8	148.2	147.8	147.5	147.4	146.1	144.5	143.7	143.3	142.6	142.2
170°	147.4	147.4	147.4	147.4	147.4	146.1	144.5	143.7	143.7	143.6	143.6
172.5°	146.2	145.9	146.2	146.5	146.6	145.6	144.4	143.7	143.7	143.7	143.7
175°	145.5	145.5	145.5	145.5	145.5	145.0	144.1	143.7	143.9	144.3	144.6
177.5°	145.0	144.6	145.0	145.3	145.4	144.9	144.2	143.9	144.1	144.4	144.6
180°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2
2.5°	1372.5	1364.7	1364.7	1351.9	1346.8	1343.0	1336.6	1317.5	1312.3	1307.2	1314.8
5°	1384.0	1369.9	1359.7	1336.6	1317.5	1309.7	1285.4	1239.4	1208.5	1185.6	1172.8
7.5°	1386.5	1368.6	1349.4	1313.6	1267.5	1247.0	1172.8	1088.3	1065.2	1044.7	1031.9
10°	1384.0	1363.5	1336.6	1282.9	1174.0	1138.2	1063.9	1008.8	994.8	990.9	994.8
12.5°	1375.0	1355.8	1318.7	1229.1	1076.8	1052.4	1008.8	976.8	974.3	980.7	1015.2
15°	1359.7	1341.8	1298.2	1157.4	1023.0	1005.0	974.3	962.8	976.8	1021.6	1125.4
17.5°	1344.3	1323.8	1270.1	1086.9	982.0	969.2	947.4	970.5	1049.8	1110.0	1144.6
20°	1323.8	1299.5	1238.0	1035.8	952.5	941.0	930.7	1034.5	1094.7	1116.4	1135.6
22.5°	1299.5	1273.8	1194.5	999.9	921.8	912.8	919.2	1070.4	1094.7	1110.0	1126.7
25°	1267.5	1245.7	1143.3	971.7	897.5	887.2	911.5	1066.5	1080.5	1084.4	1117.6
27.5°	1238.0	1209.9	1089.5	946.1	868.0	864.2	917.9	1049.8	1060.1	1063.9	1099.7
30°	1202.1	1159.9	1029.4	919.2	837.3	836.1	919.2	1029.4	1026.8	1037.0	1072.9
32.5°	1165.0	1085.7	961.4	886.0	807.9	806.6	910.3	998.7	996.0	1010.2	1037.0
35°	1130.5	1028.1	869.3	847.6	770.7	772.0	888.5	962.8	964.1	976.8	993.5
37.5°	1094.7	978.1	768.1	805.3	734.9	734.9	859.0	929.5	926.9	930.7	953.8
40°	1052.4	900.0	678.6	750.2	701.6	697.8	823.3	893.6	884.7	883.4	915.4
42.5°	1007.6	814.3	612.0	677.2	663.2	658.0	779.7	850.1	833.4	837.3	878.3
45°	958.9	791.2	560.8	572.3	623.5	619.7	732.3	800.2	788.7	798.9	841.2
47.5°	910.3	745.2	544.1	475.0	581.2	579.9	679.9	751.6	745.2	755.3	800.2
50°	843.7	693.9	542.8	407.2	533.9	539.0	617.1	704.2	704.2	713.1	760.5
52.5°	758.0	631.2	492.9	368.7	478.8	494.2	562.0	663.2	665.7	674.7	717.0
55°	679.9	565.9	457.1	339.2	413.6	446.8	508.2	620.9	626.1	635.0	673.5
57.5°	608.1	471.1	449.4	304.8	353.4	385.4	460.9	579.9	582.6	590.2	627.3
60°	531.3	340.5	412.2	267.5	300.9	325.2	417.3	531.3	540.3	545.4	577.4
62.5°	444.3	247.1	373.8	242.0	275.3	280.4	381.5	485.2	496.7	500.6	519.8
65°	316.2	207.4	317.5	220.3	248.4	249.6	343.1	437.9	448.1	454.5	468.6
67.5°	213.8	169.0	242.0	199.7	227.9	229.2	306.0	382.8	396.9	402.0	411.0
70°	148.5	112.7	179.3	178.0	204.8	207.4	266.3	332.9	345.6	349.5	354.7
72.5°	108.8	90.9	148.5	160.1	180.5	183.0	225.3	276.6	289.3	293.2	295.7
75°	83.2	96.0	120.3	139.5	153.6	154.9	184.4	225.3	234.3	236.8	238.1
77.5°	66.6	89.6	88.4	112.7	125.5	122.9	144.7	174.1	181.8	181.8	181.8
80°	49.9	70.4	66.6	80.6	92.2	89.6	103.7	124.2	126.7	129.3	128.0
82.5°	37.1	44.8	44.8	51.2	61.4	58.9	69.1	80.6	80.6	80.6	83.2
85°	23.1	25.6	20.4	26.8	34.6	33.3	38.4	43.5	44.8	44.8	42.2
87.5°	14.1	11.5	6.4	10.3	15.4	15.4	17.9	19.2	17.9	17.9	17.9
90°	2.5	1.7	1.0	1.7	2.5	2.7	4.3	6.3	7.4	6.6	4.9
92.5°	17.1	10.5	3.9	10.5	17.1	18.7	26.4	36.5	41.6	36.4	26.2
95°	33.5	21.4	9.3	21.4	33.5	36.5	64.8	102.5	121.4	108.3	82.2
97.5°	37.4	26.7	16.1	26.7	37.4	40.1	87.3	150.2	181.7	173.5	156.9
100°	40.7	31.0	21.3	31.0	40.7	43.1	95.4	165.3	200.2	200.8	202.0
102.5°	43.9	34.8	25.8	34.8	43.9	46.1	99.2	170.1	205.4	216.0	237.0
105°	48.6	41.1	33.4	41.1	48.6	50.6	102.0	170.5	204.8	228.5	275.7
107.5°	55.4	48.3	41.2	48.3	55.4	57.2	102.5	163.0	193.2	226.2	292.0
110°	59.2	52.8	46.4	52.8	59.2	60.9	101.7	156.3	183.5	220.4	293.9



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	63.8	57.7	51.6	57.7	63.8	65.3	101.7	150.4	174.7	212.4	287.7
115°	70.5	64.9	59.3	64.9	70.5	72.0	102.7	143.7	164.1	200.4	273.0
117.5°	77.2	72.1	67.0	72.1	77.2	78.5	104.7	139.4	156.9	189.6	255.0
120°	81.1	76.3	71.4	76.3	81.1	82.3	106.1	138.0	153.9	183.8	243.7
122.5°	85.5	80.6	75.8	80.6	85.5	86.7	108.3	137.2	151.6	178.6	232.5
125°	91.4	86.9	82.5	86.9	91.4	92.5	111.4	136.6	149.2	172.1	217.9
127.5°	96.9	92.4	87.9	92.4	96.9	98.1	114.4	136.2	147.2	166.9	206.2
130°	100.5	95.6	90.8	95.6	100.5	101.7	116.7	136.5	146.4	164.0	198.9
132.5°	103.6	98.7	93.9	98.7	103.6	104.7	118.4	136.6	145.7	161.4	192.7
135°	107.2	102.7	98.4	102.7	107.2	108.2	120.3	136.5	144.6	157.7	183.9
137.5°	111.6	107.3	102.9	107.3	111.6	112.7	123.3	137.3	144.4	155.4	177.6
140°	114.7	110.7	106.7	110.7	114.7	115.7	125.0	137.5	143.7	153.3	172.5
142.5°	117.0	113.3	109.6	113.3	117.0	117.9	126.6	138.0	143.7	152.1	169.0
145°	120.5	117.2	114.1	117.2	120.5	121.3	128.5	138.0	142.7	149.6	163.4
147.5°	124.8	121.6	118.5	121.6	124.8	125.6	131.3	139.0	142.7	148.2	159.0
150°	127.1	124.2	121.4	124.2	127.1	127.8	132.8	139.4	142.7	147.3	156.5
152.5°	128.7	126.6	124.4	126.6	128.7	129.3	133.7	139.7	142.7	146.6	154.5
155°	132.1	130.4	128.9	130.4	132.1	132.5	135.9	140.4	142.7	145.8	152.1
157.5°	135.3	133.7	132.2	133.7	135.3	135.7	138.0	141.2	142.7	145.2	150.0
160°	136.8	135.6	134.4	135.6	136.8	137.1	139.0	141.5	142.7	144.8	148.9
162.5°	138.5	137.5	136.6	137.5	138.5	138.7	140.0	141.9	142.7	144.5	148.0
165°	140.7	139.8	139.1	139.8	140.7	140.9	141.5	142.3	142.7	144.0	146.5
167.5°	142.1	141.7	141.3	141.7	142.1	142.2	142.6	143.3	143.7	144.5	146.1
170°	143.5	143.1	142.7	143.1	143.5	143.6	143.6	143.7	143.7	144.5	146.1
172.5°	143.7	143.6	143.5	143.6	143.7	143.7	143.7	143.7	143.7	144.4	145.6
175°	144.6	144.6	144.6	144.6	144.6	144.6	144.3	143.9	143.7	144.1	145.0
177.5°	144.6	144.6	144.6	144.6	144.6	144.6	144.4	144.1	143.9	144.2	144.9
180°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2	1353.2
2.5°	1305.9	1302.0	1307.2	1293.0	1307.2	1302.0	1305.9	1314.8	1307.2	1312.3	1317.5
5°	1145.8	1139.4	1119.0	1102.3	1119.0	1139.4	1145.8	1172.8	1185.6	1208.5	1239.4
7.5°	1024.2	1019.1	1014.0	1003.7	1014.0	1019.1	1024.2	1031.9	1044.7	1065.2	1088.3
10°	997.3	998.7	1006.3	1005.0	1006.3	998.7	997.3	994.8	990.9	994.8	1008.8
12.5°	1066.5	1078.0	1120.3	1117.6	1120.3	1078.0	1066.5	1015.2	980.7	974.3	976.8
15°	1145.8	1149.7	1158.6	1159.9	1158.6	1149.7	1145.8	1125.4	1021.6	976.8	962.8
17.5°	1153.5	1154.9	1161.2	1161.2	1161.2	1154.9	1153.5	1144.6	1110.0	1049.8	970.5
20°	1147.1	1149.7	1162.5	1165.0	1162.5	1149.7	1147.1	1135.6	1116.4	1094.7	1034.5
22.5°	1144.6	1149.7	1159.9	1158.6	1159.9	1149.7	1144.6	1126.7	1110.0	1094.7	1070.4
25°	1131.8	1131.8	1133.1	1134.3	1133.1	1131.8	1131.8	1117.6	1084.4	1080.5	1066.5
27.5°	1104.9	1107.5	1115.1	1113.9	1115.1	1107.5	1104.9	1099.7	1063.9	1060.1	1049.8
30°	1080.5	1078.0	1071.6	1066.5	1071.6	1078.0	1080.5	1072.9	1037.0	1026.8	1029.4
32.5°	1039.5	1033.1	1026.8	1023.0	1026.8	1033.1	1039.5	1037.0	1010.2	996.0	998.7
35°	990.9	992.3	990.9	987.1	990.9	992.3	990.9	993.5	976.8	964.1	962.8
37.5°	956.4	958.9	957.7	952.5	957.7	958.9	956.4	953.8	930.7	926.9	929.5
40°	920.6	921.8	920.6	916.7	920.6	921.8	920.6	915.4	883.4	884.7	893.6
42.5°	886.0	884.7	880.8	878.3	880.8	884.7	886.0	878.3	837.3	833.4	850.1
45°	846.2	847.6	839.8	836.1	839.8	847.6	846.2	841.2	798.9	788.7	800.2
47.5°	806.6	806.6	800.2	796.3	800.2	806.6	806.6	800.2	755.3	745.2	751.6
50°	764.3	763.1	754.1	752.8	754.1	763.1	764.3	760.5	713.1	704.2	704.2
52.5°	715.7	715.7	717.0	719.5	717.0	715.7	715.7	717.0	674.7	665.7	663.2
55°	673.5	674.7	683.6	686.2	683.6	674.7	673.5	673.5	635.0	626.1	620.9
57.5°	629.8	629.8	636.3	636.3	636.3	629.8	629.8	627.3	590.2	582.6	579.9
60°	579.9	582.6	587.6	586.3	587.6	582.6	579.9	577.4	545.4	540.3	531.3
62.5°	527.4	530.0	531.3	528.8	531.3	530.0	527.4	519.8	500.6	496.7	485.2
65°	472.4	475.0	476.3	473.7	476.3	475.0	472.4	468.6	454.5	448.1	437.9
67.5°	416.1	414.8	413.6	418.6	413.6	414.8	416.1	411.0	402.0	396.9	382.8
70°	358.4	358.4	357.2	359.8	357.2	358.4	358.4	354.7	349.5	345.6	332.9
72.5°	297.0	295.7	300.9	297.0	300.9	295.7	297.0	295.7	293.2	289.3	276.6
75°	236.8	239.4	236.8	240.7	236.8	239.4	236.8	238.1	236.8	234.3	225.3
77.5°	180.5	183.0	180.5	180.5	180.5	183.0	180.5	181.8	181.8	181.8	174.1
80°	128.0	126.7	126.7	125.5	126.7	126.7	128.0	128.0	129.3	126.7	124.2
82.5°	82.0	80.6	80.6	83.2	80.6	80.6	82.0	83.2	80.6	80.6	80.6
85°	44.8	46.1	43.5	43.5	43.5	46.1	44.8	42.2	44.8	44.8	43.5
87.5°	16.7	15.4	15.4	15.4	15.4	15.4	16.7	17.9	17.9	17.9	19.2
90°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	4.9	6.6	7.4	6.3
92.5°	18.4	17.6	14.7	11.8	14.7	17.6	18.4	26.2	36.4	41.6	36.5
95°	62.6	60.4	51.6	42.6	51.6	60.4	62.6	82.2	108.3	121.4	102.5
97.5°	144.5	140.2	123.4	106.5	123.4	140.2	144.5	156.9	173.5	181.7	150.2
100°	202.9	197.9	177.8	157.7	177.8	197.9	202.9	202.0	200.8	200.2	165.3
102.5°	252.8	248.5	231.2	214.0	231.2	248.5	252.8	237.0	216.0	205.4	170.1
105°	311.0	308.7	299.5	290.2	299.5	308.7	311.0	275.7	228.5	204.8	170.5
107.5°	341.4	342.0	344.2	346.4	344.2	342.0	341.4	292.0	226.2	193.2	163.0
110°	349.1	351.6	361.1	370.8	361.1	351.6	349.1	293.9	220.4	183.5	156.3



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	344.2	347.9	362.7	377.5	362.7	347.9	344.2	287.7	212.4	174.7	150.4
115°	327.3	332.5	353.1	373.6	353.1	332.5	327.3	273.0	200.4	164.1	143.7
117.5°	304.2	309.9	332.7	355.5	332.7	309.9	304.2	255.0	189.6	156.9	139.4
120°	288.6	294.1	316.3	338.4	316.3	294.1	288.6	243.7	183.8	153.9	138.0
122.5°	272.9	278.3	300.2	322.1	300.2	278.3	272.9	232.5	178.6	151.6	137.2
125°	252.2	257.3	277.4	297.6	277.4	257.3	252.2	217.9	172.1	149.2	136.6
127.5°	235.7	239.9	256.9	273.8	256.9	239.9	235.7	206.2	166.9	147.2	136.2
130°	225.2	229.1	244.8	260.5	244.8	229.1	225.2	198.9	164.0	146.4	136.5
132.5°	216.3	219.8	233.8	247.9	233.8	219.8	216.3	192.7	161.4	145.7	136.6
135°	203.6	206.6	218.8	230.9	218.8	206.6	203.6	183.9	157.7	144.6	136.5
137.5°	194.3	196.8	206.7	216.7	206.7	196.8	194.3	177.6	155.4	144.4	137.3
140°	186.8	189.1	198.4	207.7	198.4	189.1	186.8	172.5	153.3	143.7	137.5
142.5°	181.6	183.6	191.6	199.5	191.6	183.6	181.6	169.0	152.1	143.7	138.0
145°	173.7	175.3	181.3	187.3	181.3	175.3	173.7	163.4	149.6	142.7	138.0
147.5°	167.2	168.4	173.4	178.4	173.4	168.4	167.2	159.0	148.2	142.7	139.0
150°	163.4	164.3	168.4	172.5	168.4	164.3	163.4	156.5	147.3	142.7	139.4
152.5°	160.4	161.1	164.1	167.2	164.1	161.1	160.4	154.5	146.6	142.7	139.7
155°	156.8	157.3	159.3	161.3	159.3	157.3	156.8	152.1	145.8	142.7	140.4
157.5°	153.6	154.0	155.4	156.9	155.4	154.0	153.6	150.0	145.2	142.7	141.2
160°	152.0	152.2	153.1	153.9	153.1	152.2	152.0	148.9	144.8	142.7	141.5
162.5°	150.6	150.8	151.6	152.3	151.6	150.8	150.6	148.0	144.5	142.7	141.9
165°	148.4	148.5	149.4	150.2	149.4	148.5	148.4	146.5	144.0	142.7	142.3
167.5°	147.4	147.5	147.8	148.2	147.8	147.5	147.4	146.1	144.5	143.7	143.3
170°	147.4	147.4	147.4	147.4	147.4	147.4	147.4	146.1	144.5	143.7	143.7
172.5°	146.6	146.5	146.2	145.9	146.2	146.5	146.6	145.6	144.4	143.7	143.7
175°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.0	144.1	143.7	143.9
177.5°	145.4	145.3	145.0	144.6	145.0	145.3	145.4	144.9	144.2	143.9	144.1
180°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1353.2	1353.2	1353.2	1353.2	1353.2
2.5°	1336.6	1343.0	1346.8	1351.9	1364.7
5°	1285.4	1309.7	1317.5	1336.6	1359.7
7.5°	1172.8	1247.0	1267.5	1313.6	1349.4
10°	1063.9	1138.2	1174.0	1282.9	1336.6
12.5°	1008.8	1052.4	1076.8	1229.1	1318.7
15°	974.3	1005.0	1023.0	1157.4	1298.2
17.5°	947.4	969.2	982.0	1086.9	1270.1
20°	930.7	941.0	952.5	1035.8	1238.0
22.5°	919.2	912.8	921.8	999.9	1194.5
25°	911.5	887.2	897.5	971.7	1143.3
27.5°	917.9	864.2	868.0	946.1	1089.5
30°	919.2	836.1	837.3	919.2	1029.4
32.5°	910.3	806.6	807.9	886.0	961.4
35°	888.5	772.0	770.7	847.6	869.3
37.5°	859.0	734.9	734.9	805.3	768.1
40°	823.3	697.8	701.6	750.2	678.6
42.5°	779.7	658.0	663.2	677.2	612.0
45°	732.3	619.7	623.5	572.3	560.8
47.5°	679.9	579.9	581.2	475.0	544.1
50°	617.1	539.0	533.9	407.2	542.8
52.5°	562.0	494.2	478.8	368.7	492.9
55°	508.2	446.8	413.6	339.2	457.1
57.5°	460.9	385.4	353.4	304.8	449.4
60°	417.3	325.2	300.9	267.5	412.2
62.5°	381.5	280.4	275.3	242.0	373.8
65°	343.1	249.6	248.4	220.3	317.5
67.5°	306.0	229.2	227.9	199.7	242.0
70°	266.3	207.4	204.8	178.0	179.3
72.5°	225.3	183.0	180.5	160.1	148.5
75°	184.4	154.9	153.6	139.5	120.3
77.5°	144.7	122.9	125.5	112.7	88.4
80°	103.7	89.6	92.2	80.6	66.6
82.5°	69.1	58.9	61.4	51.2	44.8
85°	38.4	33.3	34.6	26.8	20.4
87.5°	17.9	15.4	15.4	10.3	6.4
90°	4.3	2.7	2.5	1.7	1.0
92.5°	26.4	18.7	17.1	10.5	3.9
95°	64.8	36.5	33.5	21.4	9.3
97.5°	87.3	40.1	37.4	26.7	16.1
100°	95.4	43.1	40.7	31.0	21.3
102.5°	99.2	46.1	43.9	34.8	25.8
105°	102.0	50.6	48.6	41.1	33.4
107.5°	102.5	57.2	55.4	48.3	41.2
110°	101.7	60.9	59.2	52.8	46.4



TEST NUMBER: P934084

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	101.7	65.3	63.8	57.7	51.6
115°	102.7	72.0	70.5	64.9	59.3
117.5°	104.7	78.5	77.2	72.1	67.0
120°	106.1	82.3	81.1	76.3	71.4
122.5°	108.3	86.7	85.5	80.6	75.8
125°	111.4	92.5	91.4	86.9	82.5
127.5°	114.4	98.1	96.9	92.4	87.9
130°	116.7	101.7	100.5	95.6	90.8
132.5°	118.4	104.7	103.6	98.7	93.9
135°	120.3	108.2	107.2	102.7	98.4
137.5°	123.3	112.7	111.6	107.3	102.9
140°	125.0	115.7	114.7	110.7	106.7
142.5°	126.6	117.9	117.0	113.3	109.6
145°	128.5	121.3	120.5	117.2	114.1
147.5°	131.3	125.6	124.8	121.6	118.5
150°	132.8	127.8	127.1	124.2	121.4
152.5°	133.7	129.3	128.7	126.6	124.4
155°	135.9	132.5	132.1	130.4	128.9
157.5°	138.0	135.7	135.3	133.7	132.2
160°	139.0	137.1	136.8	135.6	134.4
162.5°	140.0	138.7	138.5	137.5	136.6
165°	141.5	140.9	140.7	139.8	139.1
167.5°	142.6	142.2	142.1	141.7	141.3
170°	143.6	143.6	143.5	143.1	142.7
172.5°	143.7	143.7	143.7	143.6	143.5
175°	144.3	144.6	144.6	144.6	144.6
177.5°	144.4	144.6	144.6	144.6	144.6
180°	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P934084
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.92	17.12	16.58	17.80	18.58	18.72	19.92	19.38	20.59	21.38
	3H	16.42	17.50	17.10	18.19	19.01	20.08	21.15	20.75	21.84	22.66
	4H	16.63	17.64	17.32	18.34	19.18	20.53	21.55	21.23	22.25	23.08
	6H	16.76	17.70	17.47	18.41	19.26	20.82	21.76	21.53	22.47	23.32
	8H	16.77	17.67	17.49	18.40	19.25	20.90	21.80	21.62	22.53	23.38
	12H	16.76	17.61	17.48	18.33	19.21	20.95	21.80	21.68	22.53	23.41
4H	2H	16.98	18.00	17.68	18.70	19.53	19.17	20.18	19.87	20.88	21.72
	3H	18.04	18.89	18.75	19.62	20.48	20.69	21.54	21.41	22.28	23.13
	4H	18.33	19.10	19.06	19.84	20.72	21.23	22.00	21.96	22.74	23.62
	6H	18.48	19.14	19.22	19.91	20.80	21.61	22.27	22.35	23.04	23.93
	8H	18.49	19.11	19.24	19.87	20.78	21.72	22.34	22.47	23.10	24.00
	12H	18.47	19.03	19.24	19.82	20.73	21.78	22.34	22.56	23.13	24.04
8H	4H	18.81	19.43	19.56	20.19	21.09	21.38	22.00	22.13	22.77	23.67
	6H	19.08	19.60	19.86	20.40	21.31	21.82	22.34	22.61	23.14	24.05
	8H	19.13	19.59	19.92	20.39	21.31	21.97	22.43	22.77	23.24	24.16
	12H	19.13	19.53	19.92	20.33	21.31	22.08	22.49	22.88	23.28	24.26
12H	4H	18.83	19.39	19.60	20.17	21.08	21.36	21.92	22.13	22.71	23.62
	6H	19.14	19.60	19.94	20.41	21.33	21.82	22.28	22.62	23.09	24.01
	8H	19.23	19.63	20.02	20.42	21.41	22.00	22.40	22.79	23.19	24.18