

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934179

Luminaire Tested: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934179
REPORT IS A COMBINATION OF REPORTS P933685 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16295.7 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 148.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934179
CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · - 135°-315°



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	86	86	86	86	86	86	83
1	105	101	97	93	101	97	93	90	89	87	84	83	80	78	76	75	73	73	73	73	70
2	96	88	82	76	92	85	79	74	78	74	70	73	69	66	67	64	62	62	62	62	59
3	88	78	70	64	84	75	68	62	69	63	59	64	60	56	60	56	52	52	52	52	50
4	80	69	60	54	77	66	59	53	62	55	50	57	52	48	53	49	45	45	45	45	43
5	74	61	53	46	70	59	51	45	55	49	43	52	46	41	48	43	39	39	39	39	37
6	68	55	47	40	65	53	45	40	50	43	38	47	41	36	44	39	35	35	35	35	32
7	63	50	42	36	60	48	41	35	45	39	34	42	37	32	40	35	31	31	31	31	29
8	59	46	37	32	56	44	36	31	41	35	30	39	33	29	37	31	28	28	28	28	26
9	55	42	34	28	52	40	33	28	38	32	27	36	30	26	34	29	25	25	25	25	23
10	51	38	31	26	49	37	30	25	35	29	24	33	28	24	31	26	23	23	23	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16083	16083	16083	16083
5°	16209	16235	16209	12766
10°	16107	15992	16107	11433
15°	15937	15645	15937	13064
20°	15610	15235	15610	13092
25°	14934	14636	14934	12814
30°	14058	14139	14058	12205
35°	12539	13511	12539	11536
40°	10454	12771	10454	11030
45°	9347	11904	9347	10448
50°	9938	10871	9938	9865
55°	9359	9758	9359	9527
60°	9659	8287	9659	8726
65°	8772	6851	8772	7658
70°	6089	5460	6089	6419
75°	5359	4036	5359	4833
80°	4351	2668	4351	2905
85°	2550	1413	2550	1201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 14316 cd/sqm



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	469.4	2.9
10°-20°	1332.6	8.2
20°-30°	2060.0	12.6
30°-40°	2459.2	15.1
40°-50°	2473.6	15.2
50°-60°	2152.4	13.2
60°-70°	1526.1	9.4
70°-80°	807.4	5.0
80°-90°	202.7	1.2
90°-100°	211.5	1.3
100°-110°	556.0	3.4
110°-120°	576.5	3.5
120°-130°	462.4	2.8
130°-140°	362.8	2.2
140°-150°	278.5	1.7
150°-160°	200.6	1.2
160°-170°	122.7	0.8
170°-180°	41.5	0.3
0°-30°	3862.0	23.7
0°-40°	6321.2	38.8
0°-60°	10947.2	67.2
0°-90°	13483.3	82.7
90°-120°	1343.9	8.2
90°-150°	2447.6	15.0
90°-180°	2812.0	17.3
0°-180°	16295.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5200	5200	5200	5200	5200	
5°	5224	5387	5224	4236	5224	496
15°	4988	5337	4988	4457	4988	1403
25°	4393	4978	4393	4358	4393	2017
35°	3340	4442	3340	3793	3340	2066
45°	2155	3660	2155	3212	2155	1726
55°	1756	2701	1756	2637	1756	1614
65°	1220	1628	1220	1820	1220	1166
75°	462	772	462	925	462	486
85°	79	197	79	167	79	106
90°	3	11	3	11	3	6
95°	28	128	28	128	28	31
105°	100	870	100	870	100	106
115°	178	1121	178	1121	178	176
125°	248	893	248	893	248	220
135°	295	693	295	693	295	228
145°	342	562	342	562	342	214
155°	387	484	387	484	387	178
165°	417	451	417	451	417	118
175°	434	437	434	437	434	41
180°	434	434	434	434	434	



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5243.9	5243.9	5273.4	5283.3	5283.3	5268.5	5253.7	5268.5	5312.7	5327.6	5322.6
5°	5224.2	5263.6	5317.7	5327.6	5337.3	5332.4	5322.6	5332.4	5381.6	5391.5	5396.4
7.5°	5184.8	5258.7	5327.6	5342.3	5357.0	5342.3	5337.3	5347.2	5396.4	5406.2	5406.2
10°	5135.7	5239.0	5317.7	5327.6	5342.3	5327.6	5327.6	5347.2	5396.4	5406.2	5411.2
12.5°	5066.8	5209.4	5283.3	5293.1	5312.7	5307.8	5302.9	5322.6	5371.7	5381.6	5381.6
15°	4988.1	5155.4	5224.2	5234.1	5268.5	5258.7	5258.7	5278.3	5332.4	5347.2	5342.3
17.5°	4879.9	5086.5	5165.2	5180.0	5204.5	5199.7	5204.5	5224.2	5273.4	5283.3	5288.1
20°	4756.9	4993.0	5086.5	5101.2	5125.8	5125.8	5125.8	5150.4	5199.7	5219.3	5219.3
22.5°	4589.7	4894.6	4993.0	5002.9	5032.4	5032.4	5042.2	5076.6	5120.9	5125.8	5125.8
25°	4392.9	4786.4	4870.0	4899.6	4929.1	4943.8	4958.6	4978.2	4993.0	4988.1	4993.0
27.5°	4186.3	4648.7	4756.9	4776.6	4815.9	4830.7	4850.3	4855.3	4860.2	4874.9	4865.2
30°	3955.1	4456.8	4619.1	4638.8	4702.8	4712.6	4693.0	4702.8	4727.4	4737.2	4747.0
32.5°	3694.3	4171.5	4476.5	4520.8	4579.8	4550.3	4545.4	4560.1	4599.5	4599.5	4609.3
35°	3340.1	3950.1	4343.6	4383.0	4427.3	4392.9	4412.5	4417.5	4442.1	4456.8	4451.9
37.5°	2951.6	3758.3	4205.9	4235.5	4269.9	4225.6	4255.2	4269.9	4289.6	4279.7	4279.7
40°	2607.2	3458.2	4043.6	4063.3	4092.8	4058.4	4087.9	4097.7	4107.6	4097.7	4092.8
42.5°	2351.4	3128.6	3871.4	3896.1	3876.4	3900.9	3910.8	3930.5	3915.7	3896.1	3896.1
45°	2154.6	3040.0	3684.5	3714.0	3684.5	3723.9	3738.6	3738.6	3694.3	3684.5	3679.6
47.5°	2090.7	2863.0	3497.6	3497.6	3482.8	3532.0	3556.6	3522.1	3477.9	3463.1	3463.1
50°	2085.8	2666.2	3241.8	3222.1	3290.9	3350.0	3325.4	3290.9	3256.5	3202.4	3202.4
52.5°	1893.9	2425.2	2912.1	2986.0	3094.2	3128.6	3089.3	3054.9	2995.8	2971.2	2951.6
55°	1756.1	2174.3	2612.1	2759.7	2872.8	2917.1	2843.3	2808.8	2720.4	2705.5	2695.8
57.5°	1726.7	1810.3	2336.6	2523.6	2661.3	2656.4	2612.1	2548.2	2474.3	2459.6	2454.7
60°	1584.0	1308.5	2041.5	2262.8	2405.5	2390.7	2351.4	2292.4	2223.5	2213.7	2203.8
62.5°	1436.4	949.4	1707.0	1957.9	2159.5	2154.6	2120.2	2031.6	1982.5	1957.9	1938.2
65°	1220.0	796.9	1215.0	1628.3	1918.5	1928.3	1854.6	1790.6	1736.4	1707.0	1702.0
67.5°	929.8	649.3	821.5	1357.7	1687.3	1677.4	1584.0	1554.5	1485.6	1470.8	1441.3
70°	688.7	432.9	570.6	1101.9	1461.0	1436.4	1362.6	1328.2	1264.3	1229.8	1210.1
72.5°	570.6	349.2	418.1	855.9	1229.8	1200.3	1136.3	1097.0	1042.8	1013.4	993.7
75°	462.4	368.9	319.8	634.6	998.6	978.9	919.9	880.5	836.2	796.9	801.8
77.5°	339.4	344.4	255.8	467.3	792.0	762.5	728.0	678.9	659.2	619.9	619.9
80°	255.8	270.5	191.9	319.8	570.6	570.6	541.1	506.7	472.3	452.5	452.5
82.5°	172.2	172.2	142.6	201.6	388.7	373.8	354.2	344.4	324.7	314.8	314.8
85°	78.7	98.4	88.6	123.0	211.5	221.3	221.3	211.5	206.6	196.8	201.6
87.5°	24.6	44.3	54.1	68.9	108.2	113.2	118.0	118.0	118.0	123.0	123.0
90°	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.7	14.7	11.0	11.0
92.5°	11.6	31.4	51.3	56.2	79.0	109.4	124.6	109.2	78.4	55.3	53.1
95°	27.9	64.1	100.4	109.5	194.4	307.7	364.2	325.0	246.6	187.8	181.1
97.5°	48.4	80.3	112.3	120.3	261.8	450.7	545.1	520.3	470.7	433.5	420.8
100°	64.1	93.0	122.0	129.3	286.4	495.9	600.7	602.5	606.1	608.8	593.7
102.5°	77.4	104.5	131.5	138.3	297.7	510.2	616.4	648.0	711.1	758.4	745.5
105°	100.2	123.1	145.9	151.6	306.0	511.7	614.6	685.4	826.9	933.1	926.2
107.5°	123.5	144.8	166.2	171.5	307.6	489.0	579.7	678.4	875.9	1024.0	1025.7
110°	139.1	158.4	177.7	182.6	305.2	468.8	550.6	661.0	881.7	1047.3	1054.6



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	154.7	173.0	191.4	195.9	305.3	451.2	524.1	637.1	863.0	1032.5	1043.6
115°	177.9	194.9	211.8	216.1	308.1	430.9	492.3	601.2	818.8	982.1	997.5
117.5°	200.9	216.3	231.7	235.6	313.9	418.3	470.5	568.8	765.2	912.5	929.7
120°	214.2	228.8	243.3	246.9	318.5	414.0	461.7	551.5	731.0	865.6	882.3
122.5°	227.4	242.1	256.6	260.3	325.2	411.7	455.0	535.9	697.5	818.7	835.1
125°	247.5	260.9	274.2	277.5	334.3	410.0	447.8	516.4	653.7	756.7	771.8
127.5°	263.8	277.2	290.7	294.1	343.3	408.9	441.7	500.6	618.5	706.9	719.7
130°	272.5	287.0	301.6	305.1	349.9	409.5	439.3	491.9	596.8	675.5	687.3
132.5°	281.6	296.0	310.6	314.1	355.2	410.0	437.3	484.3	578.3	648.7	659.3
135°	295.0	308.1	321.3	324.6	361.0	409.6	433.8	473.2	551.8	610.9	620.0
137.5°	308.6	321.7	334.7	338.0	369.8	412.1	433.2	466.5	532.9	582.9	590.3
140°	320.0	332.0	344.1	347.1	375.1	412.5	431.2	459.9	517.3	560.5	567.4
142.5°	328.7	339.8	351.0	353.8	379.6	414.0	431.2	456.4	506.9	544.8	550.8
145°	342.2	351.8	361.5	364.0	385.4	414.0	428.3	448.9	490.2	521.1	525.7
147.5°	355.5	364.9	374.4	376.7	393.9	416.9	428.3	444.6	477.0	501.4	505.1
150°	364.2	372.8	381.3	383.4	398.4	418.3	428.3	442.1	469.5	490.0	493.0
152.5°	373.3	379.8	386.1	387.8	401.3	419.3	428.3	440.0	463.5	481.0	483.3
155°	386.6	391.4	396.2	397.4	407.7	421.4	428.3	437.6	456.3	470.3	471.8
157.5°	396.5	401.2	405.9	407.1	414.2	423.5	428.3	435.6	450.0	460.9	461.9
160°	403.3	406.9	410.6	411.4	417.1	424.5	428.3	434.5	446.9	456.2	456.8
162.5°	410.0	412.7	415.4	416.1	420.2	425.6	428.3	433.5	444.0	451.8	452.4
165°	417.3	419.7	422.2	422.8	424.6	427.0	428.3	432.1	439.5	445.2	445.7
167.5°	423.9	425.1	426.3	426.6	428.1	430.1	431.2	433.6	438.6	442.3	442.5
170°	428.3	429.5	430.6	430.9	431.0	431.1	431.2	433.6	438.6	442.3	442.3
172.5°	430.6	430.9	431.1	431.2	431.2	431.2	431.2	433.1	437.0	439.9	439.7
175°	433.8	433.8	433.8	433.8	432.9	431.8	431.2	432.5	434.9	436.7	436.7
177.5°	433.8	433.8	433.8	433.8	433.1	432.3	431.8	432.8	434.7	436.1	435.9
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5332.4	5317.7	5332.4	5322.6	5327.6	5312.7	5268.5	5253.7	5268.5	5283.3	5283.3
5°	5396.4	5386.6	5396.4	5396.4	5391.5	5381.6	5332.4	5322.6	5332.4	5337.3	5327.6
7.5°	5416.0	5401.3	5416.0	5406.2	5406.2	5396.4	5347.2	5337.3	5342.3	5357.0	5342.3
10°	5416.0	5401.3	5416.0	5411.2	5406.2	5396.4	5347.2	5327.6	5327.6	5342.3	5327.6
12.5°	5391.5	5381.6	5391.5	5381.6	5381.6	5371.7	5322.6	5302.9	5307.8	5312.7	5293.1
15°	5352.1	5337.3	5352.1	5342.3	5347.2	5332.4	5278.3	5258.7	5258.7	5268.5	5234.1
17.5°	5293.1	5273.4	5293.1	5288.1	5283.3	5273.4	5224.2	5204.5	5199.7	5204.5	5180.0
20°	5224.2	5209.4	5224.2	5219.3	5219.3	5199.7	5150.4	5125.8	5125.8	5125.8	5101.2
22.5°	5116.0	5101.2	5116.0	5125.8	5125.8	5120.9	5076.6	5042.2	5032.4	5032.4	5002.9
25°	4993.0	4978.2	4993.0	4993.0	4988.1	4993.0	4978.2	4958.6	4943.8	4929.1	4899.6
27.5°	4874.9	4865.2	4874.9	4865.2	4874.9	4860.2	4855.3	4850.3	4830.7	4815.9	4776.6
30°	4756.9	4747.0	4756.9	4747.0	4737.2	4727.4	4702.8	4693.0	4712.6	4702.8	4638.8
32.5°	4609.3	4599.5	4609.3	4609.3	4599.5	4599.5	4560.1	4545.4	4550.3	4579.8	4520.8
35°	4456.8	4442.1	4456.8	4451.9	4456.8	4442.1	4417.5	4412.5	4392.9	4427.3	4383.0
37.5°	4279.7	4265.0	4279.7	4279.7	4279.7	4289.6	4269.9	4255.2	4225.6	4269.9	4235.5
40°	4097.7	4078.0	4097.7	4092.8	4097.7	4107.6	4097.7	4087.9	4058.4	4092.8	4063.3
42.5°	3891.1	3886.2	3891.1	3896.1	3896.1	3915.7	3930.5	3910.8	3900.9	3876.4	3896.1
45°	3669.7	3659.9	3669.7	3679.6	3684.5	3694.3	3738.6	3738.6	3723.9	3684.5	3714.0
47.5°	3433.7	3409.0	3433.7	3463.1	3463.1	3477.9	3522.1	3556.6	3532.0	3482.8	3497.6
50°	3182.8	3187.6	3182.8	3202.4	3202.4	3256.5	3290.9	3325.4	3350.0	3290.9	3222.1
52.5°	2936.7	2931.9	2936.7	2951.6	2971.2	2995.8	3054.9	3089.3	3128.6	3094.2	2986.0
55°	2690.8	2700.7	2690.8	2695.8	2705.5	2720.4	2808.8	2843.3	2917.1	2872.8	2759.7
57.5°	2444.9	2430.1	2444.9	2454.7	2459.6	2474.3	2548.2	2612.1	2656.4	2661.3	2523.6
60°	2159.5	2139.8	2159.5	2203.8	2213.7	2223.5	2292.4	2351.4	2390.7	2405.5	2262.8
62.5°	1908.6	1874.2	1908.6	1938.2	1957.9	1982.5	2031.6	2120.2	2154.6	2159.5	1957.9
65°	1643.0	1628.3	1643.0	1702.0	1707.0	1736.4	1790.6	1854.6	1928.3	1918.5	1628.3
67.5°	1401.9	1401.9	1401.9	1441.3	1470.8	1485.6	1554.5	1584.0	1677.4	1687.3	1357.7
70°	1180.6	1175.7	1180.6	1210.1	1229.8	1264.3	1328.2	1362.6	1436.4	1461.0	1101.9
72.5°	969.1	964.2	969.1	993.7	1013.4	1042.8	1097.0	1136.3	1200.3	1229.8	855.9
75°	782.2	772.3	782.2	801.8	796.9	836.2	880.5	919.9	978.9	998.6	634.6
77.5°	600.1	600.1	600.1	619.9	619.9	659.2	678.9	728.0	762.5	792.0	467.3
80°	447.7	442.7	447.7	452.5	452.5	472.3	506.7	541.1	570.6	570.6	319.8
82.5°	314.8	304.9	314.8	314.8	314.8	324.7	344.4	354.2	373.8	388.7	201.6
85°	196.8	196.8	196.8	201.6	196.8	206.6	211.5	221.3	221.3	211.5	123.0
87.5°	127.9	123.0	127.9	123.0	123.0	118.0	118.0	118.0	113.2	108.2	68.9
90°	11.0	11.0	11.0	11.0	11.0	14.7	19.7	22.1	19.0	12.8	8.1
92.5°	44.4	35.6	44.4	53.1	55.3	78.4	109.2	124.6	109.4	79.0	56.2
95°	154.5	127.8	154.5	181.1	187.8	246.6	325.0	364.2	307.7	194.4	109.5
97.5°	370.2	319.4	370.2	420.8	433.5	470.7	520.3	545.1	450.7	261.8	120.3
100°	533.3	472.9	533.3	593.7	608.8	606.1	602.5	600.7	495.9	286.4	129.3
102.5°	693.7	642.0	693.7	745.5	758.4	711.1	648.0	616.4	510.2	297.7	138.3
105°	898.4	870.5	898.4	926.2	933.1	826.9	685.4	614.6	511.7	306.0	151.6
107.5°	1032.5	1039.2	1032.5	1025.7	1024.0	875.9	678.4	579.7	489.0	307.6	171.5
110°	1083.5	1112.5	1083.5	1054.6	1047.3	881.7	661.0	550.6	468.8	305.2	182.6



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1088.1	1132.6	1088.1	1043.6	1032.5	863.0	637.1	524.1	451.2	305.3	195.9
115°	1059.2	1120.9	1059.2	997.5	982.1	818.8	601.2	492.3	430.9	308.1	216.1
117.5°	998.1	1066.5	998.1	929.7	912.5	765.2	568.8	470.5	418.3	313.9	235.6
120°	948.7	1015.2	948.7	882.3	865.6	731.0	551.5	461.7	414.0	318.5	246.9
122.5°	900.8	966.4	900.8	835.1	818.7	697.5	535.9	455.0	411.7	325.2	260.3
125°	832.2	892.6	832.2	771.8	756.7	653.7	516.4	447.8	410.0	334.3	277.5
127.5°	770.6	821.6	770.6	719.7	706.9	618.5	500.6	441.7	408.9	343.3	294.1
130°	734.4	781.5	734.4	687.3	675.5	596.8	491.9	439.3	409.5	349.9	305.1
132.5°	701.5	743.6	701.5	659.3	648.7	578.3	484.3	437.3	410.0	355.2	314.1
135°	656.3	692.6	656.3	620.0	610.9	551.8	473.2	433.8	409.6	361.0	324.6
137.5°	620.1	649.9	620.1	590.3	582.9	532.9	466.5	433.2	412.1	369.8	338.0
140°	595.3	623.1	595.3	567.4	560.5	517.3	459.9	431.2	412.5	375.1	347.1
142.5°	574.7	598.6	574.7	550.8	544.8	506.9	456.4	431.2	414.0	379.6	353.8
145°	543.8	561.9	543.8	525.7	521.1	490.2	448.9	428.3	414.0	385.4	364.0
147.5°	520.2	535.2	520.2	505.1	501.4	477.0	444.6	428.3	416.9	393.9	376.7
150°	505.2	517.3	505.2	493.0	490.0	469.5	442.1	428.3	418.3	398.4	383.4
152.5°	492.4	501.7	492.4	483.3	481.0	463.5	440.0	428.3	419.3	401.3	387.8
155°	477.8	483.9	477.8	471.8	470.3	456.3	437.6	428.3	421.4	407.7	397.4
157.5°	466.3	470.5	466.3	461.9	460.9	450.0	435.6	428.3	423.5	414.2	407.1
160°	459.3	461.7	459.3	456.8	456.2	446.9	434.5	428.3	424.5	417.1	411.4
162.5°	454.8	457.1	454.8	452.4	451.8	444.0	433.5	428.3	425.6	420.2	416.1
165°	448.3	450.7	448.3	445.7	445.2	439.5	432.1	428.3	427.0	424.6	422.8
167.5°	443.5	444.6	443.5	442.5	442.3	438.6	433.6	431.2	430.1	428.1	426.6
170°	442.3	442.3	442.3	442.3	442.3	438.6	433.6	431.2	431.1	431.0	430.9
172.5°	438.8	437.9	438.8	439.7	439.9	437.0	433.1	431.2	431.2	431.2	431.2
175°	436.7	436.7	436.7	436.7	436.7	434.9	432.5	431.2	431.8	432.9	433.8
177.5°	434.9	433.8	434.9	435.9	436.1	434.7	432.8	431.8	432.3	433.1	433.8
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5273.4	5243.9	5243.9	5194.7	5175.0	5160.3	5135.7	5061.9	5042.2	5022.5	5052.1
5°	5317.7	5263.6	5224.2	5135.7	5061.9	5032.4	4938.9	4761.8	4643.7	4555.2	4506.0
7.5°	5327.6	5258.7	5184.8	5047.1	4870.0	4791.3	4506.0	4181.3	4092.8	4014.1	3964.9
10°	5317.7	5239.0	5135.7	4929.1	4510.9	4373.2	4087.9	3876.4	3822.2	3807.5	3822.2
12.5°	5283.3	5209.4	5066.8	4722.4	4137.0	4043.6	3876.4	3753.3	3743.5	3768.2	3900.9
15°	5224.2	5155.4	4988.1	4446.9	3930.5	3861.6	3743.5	3699.3	3753.3	3925.5	4324.0
17.5°	5165.2	5086.5	4879.9	4176.4	3773.1	3723.9	3640.2	3728.8	4033.8	4265.0	4397.8
20°	5086.5	4993.0	4756.9	3979.7	3659.9	3615.6	3576.3	3974.7	4205.9	4289.6	4363.3
22.5°	4993.0	4894.6	4589.7	3841.9	3541.9	3507.4	3532.0	4112.4	4205.9	4265.0	4328.9
25°	4870.0	4786.4	4392.9	3733.7	3448.4	3409.0	3502.5	4097.7	4151.8	4166.6	4294.5
27.5°	4756.9	4648.7	4186.3	3635.3	3335.2	3320.5	3527.1	4033.8	4073.1	4087.9	4225.6
30°	4619.1	4456.8	3955.1	3532.0	3217.2	3212.2	3532.0	3955.1	3945.2	3984.5	4122.3
32.5°	4476.5	4171.5	3694.3	3404.1	3104.0	3099.2	3497.6	3836.9	3827.2	3881.2	3984.5
35°	4343.6	3950.1	3340.1	3256.5	2961.4	2966.3	3414.0	3699.3	3704.2	3753.3	3817.3
37.5°	4205.9	3758.3	2951.6	3094.2	2823.7	2823.7	3300.8	3571.3	3561.6	3576.3	3664.9
40°	4043.6	3458.2	2607.2	2882.7	2695.8	2680.9	3163.1	3433.7	3399.2	3394.3	3517.3
42.5°	3871.4	3128.6	2351.4	2602.2	2548.2	2528.5	2995.8	3266.4	3202.4	3217.2	3374.5
45°	3684.5	3040.0	2154.6	2198.9	2395.7	2380.9	2813.8	3074.5	3030.3	3069.6	3231.9
47.5°	3497.6	2863.0	2090.7	1825.0	2233.4	2228.4	2612.1	2887.6	2863.0	2902.3	3074.5
50°	3241.8	2666.2	2085.8	1564.4	2051.3	2070.9	2371.0	2705.5	2705.5	2740.0	2922.0
52.5°	2912.1	2425.2	1893.9	1416.8	1839.7	1898.9	2159.5	2548.2	2558.0	2592.5	2754.8
55°	2612.1	2174.3	1756.1	1303.6	1588.9	1716.8	1952.9	2385.8	2405.5	2439.9	2587.5
57.5°	2336.6	1810.3	1726.7	1170.7	1357.7	1480.7	1770.9	2228.4	2238.3	2267.8	2410.4
60°	2041.5	1308.5	1584.0	1028.1	1156.0	1249.5	1603.7	2041.5	2075.9	2095.6	2218.5
62.5°	1707.0	949.4	1436.4	929.8	1057.7	1077.3	1465.9	1864.4	1908.6	1923.4	1997.2
65°	1215.0	796.9	1220.0	846.1	954.4	959.2	1318.3	1682.4	1721.7	1746.3	1800.4
67.5°	821.5	649.3	929.8	767.4	875.6	880.5	1175.7	1470.8	1524.9	1544.7	1579.1
70°	570.6	432.9	688.7	683.7	787.1	796.9	1023.2	1279.0	1328.2	1342.9	1362.6
72.5°	418.1	349.2	570.6	614.9	693.6	703.5	865.8	1062.5	1111.7	1126.5	1136.3
75°	319.8	368.9	462.4	536.1	590.3	595.3	708.3	865.8	900.2	910.1	914.9
77.5°	255.8	344.4	339.4	432.9	482.1	472.3	555.9	669.0	698.6	698.6	698.6
80°	191.9	270.5	255.8	309.9	354.2	344.4	398.5	477.1	487.0	496.8	492.0
82.5°	142.6	172.2	172.2	196.8	236.1	226.3	265.6	309.9	309.9	309.9	319.8
85°	88.6	98.4	78.7	103.3	132.8	127.9	147.6	167.2	172.2	172.2	162.3
87.5°	54.1	44.3	24.6	39.3	59.0	59.0	68.9	73.7	68.9	68.9	68.9
90°	7.6	5.2	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.7	14.7
92.5°	51.3	31.4	11.6	31.4	51.3	56.2	79.0	109.4	124.6	109.2	78.4
95°	100.4	64.1	27.9	64.1	100.4	109.5	194.4	307.7	364.2	325.0	246.6
97.5°	112.3	80.3	48.4	80.3	112.3	120.3	261.8	450.7	545.1	520.3	470.7
100°	122.0	93.0	64.1	93.0	122.0	129.3	286.4	495.9	600.7	602.5	606.1
102.5°	131.5	104.5	77.4	104.5	131.5	138.3	297.7	510.2	616.4	648.0	711.1
105°	145.9	123.1	100.2	123.1	145.9	151.6	306.0	511.7	614.6	685.4	826.9
107.5°	166.2	144.8	123.5	144.8	166.2	171.5	307.6	489.0	579.7	678.4	875.9
110°	177.7	158.4	139.1	158.4	177.7	182.6	305.2	468.8	550.6	661.0	881.7



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	191.4	173.0	154.7	173.0	191.4	195.9	305.3	451.2	524.1	637.1	863.0
115°	211.8	194.9	177.9	194.9	211.8	216.1	308.1	430.9	492.3	601.2	818.8
117.5°	231.7	216.3	200.9	216.3	231.7	235.6	313.9	418.3	470.5	568.8	765.2
120°	243.3	228.8	214.2	228.8	243.3	246.9	318.5	414.0	461.7	551.5	731.0
122.5°	256.6	242.1	227.4	242.1	256.6	260.3	325.2	411.7	455.0	535.9	697.5
125°	274.2	260.9	247.5	260.9	274.2	277.5	334.3	410.0	447.8	516.4	653.7
127.5°	290.7	277.2	263.8	277.2	290.7	294.1	343.3	408.9	441.7	500.6	618.5
130°	301.6	287.0	272.5	287.0	301.6	305.1	349.9	409.5	439.3	491.9	596.8
132.5°	310.6	296.0	281.6	296.0	310.6	314.1	355.2	410.0	437.3	484.3	578.3
135°	321.3	308.1	295.0	308.1	321.3	324.6	361.0	409.6	433.8	473.2	551.8
137.5°	334.7	321.7	308.6	321.7	334.7	338.0	369.8	412.1	433.2	466.5	532.9
140°	344.1	332.0	320.0	332.0	344.1	347.1	375.1	412.5	431.2	459.9	517.3
142.5°	351.0	339.8	328.7	339.8	351.0	353.8	379.6	414.0	431.2	456.4	506.9
145°	361.5	351.8	342.2	351.8	361.5	364.0	385.4	414.0	428.3	448.9	490.2
147.5°	374.4	364.9	355.5	364.9	374.4	376.7	393.9	416.9	428.3	444.6	477.0
150°	381.3	372.8	364.2	372.8	381.3	383.4	398.4	418.3	428.3	442.1	469.5
152.5°	386.1	379.8	373.3	379.8	386.1	387.8	401.3	419.3	428.3	440.0	463.5
155°	396.2	391.4	386.6	391.4	396.2	397.4	407.7	421.4	428.3	437.6	456.3
157.5°	405.9	401.2	396.5	401.2	405.9	407.1	414.2	423.5	428.3	435.6	450.0
160°	410.6	406.9	403.3	406.9	410.6	411.4	417.1	424.5	428.3	434.5	446.9
162.5°	415.4	412.7	410.0	412.7	415.4	416.1	420.2	425.6	428.3	433.5	444.0
165°	422.2	419.7	417.3	419.7	422.2	422.8	424.6	427.0	428.3	432.1	439.5
167.5°	426.3	425.1	423.9	425.1	426.3	426.6	428.1	430.1	431.2	433.6	438.6
170°	430.6	429.5	428.3	429.5	430.6	430.9	431.0	431.1	431.2	433.6	438.6
172.5°	431.1	430.9	430.6	430.9	431.1	431.2	431.2	431.2	431.2	433.1	437.0
175°	433.8	433.8	433.8	433.8	433.8	433.8	432.9	431.8	431.2	432.5	434.9
177.5°	433.8	433.8	433.8	433.8	433.8	433.8	433.1	432.3	431.8	432.8	434.7
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934179
 CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5017.6	5002.9	5022.5	4968.5	5022.5	5002.9	5017.6	5052.1	5022.5	5042.2	5061.9
5°	4402.7	4378.1	4299.4	4235.5	4299.4	4378.1	4402.7	4506.0	4555.2	4643.7	4761.8
7.5°	3935.4	3915.7	3896.1	3856.7	3896.1	3915.7	3935.4	3964.9	4014.1	4092.8	4181.3
10°	3832.1	3836.9	3866.5	3861.6	3866.5	3836.9	3832.1	3822.2	3807.5	3822.2	3876.4
12.5°	4097.7	4142.0	4304.3	4294.5	4304.3	4142.0	4097.7	3900.9	3768.2	3743.5	3753.3
15°	4402.7	4417.5	4451.9	4456.8	4451.9	4417.5	4402.7	4324.0	3925.5	3753.3	3699.3
17.5°	4432.2	4437.1	4461.8	4461.8	4461.8	4437.1	4432.2	4397.8	4265.0	4033.8	3728.8
20°	4407.6	4417.5	4466.7	4476.5	4466.7	4417.5	4407.6	4363.3	4289.6	4205.9	3974.7
22.5°	4397.8	4417.5	4456.8	4451.9	4456.8	4417.5	4397.8	4328.9	4265.0	4205.9	4112.4
25°	4348.6	4348.6	4353.5	4358.5	4353.5	4348.6	4348.6	4294.5	4166.6	4151.8	4097.7
27.5°	4245.3	4255.2	4284.6	4279.7	4284.6	4255.2	4245.3	4225.6	4087.9	4073.1	4033.8
30°	4151.8	4142.0	4117.4	4097.7	4117.4	4142.0	4151.8	4122.3	3984.5	3945.2	3955.1
32.5°	3994.4	3969.8	3945.2	3930.5	3945.2	3969.8	3994.4	3984.5	3881.2	3827.2	3836.9
35°	3807.5	3812.4	3807.5	3792.8	3807.5	3812.4	3807.5	3817.3	3753.3	3704.2	3699.3
37.5°	3674.6	3684.5	3679.6	3659.9	3679.6	3684.5	3674.6	3664.9	3576.3	3561.6	3571.3
40°	3536.9	3541.9	3536.9	3522.1	3536.9	3541.9	3536.9	3517.3	3394.3	3399.2	3433.7
42.5°	3404.1	3399.2	3384.4	3374.5	3384.4	3399.2	3404.1	3374.5	3217.2	3202.4	3266.4
45°	3251.6	3256.5	3227.0	3212.2	3227.0	3256.5	3251.6	3231.9	3069.6	3030.3	3074.5
47.5°	3099.2	3099.2	3074.5	3059.7	3074.5	3099.2	3099.2	3074.5	2902.3	2863.0	2887.6
50°	2936.7	2931.9	2897.4	2892.5	2897.4	2931.9	2936.7	2922.0	2740.0	2705.5	2705.5
52.5°	2749.8	2749.8	2754.8	2764.6	2754.8	2749.8	2749.8	2754.8	2592.5	2558.0	2548.2
55°	2587.5	2592.5	2626.9	2636.7	2626.9	2592.5	2587.5	2587.5	2439.9	2405.5	2385.8
57.5°	2420.3	2420.3	2444.9	2444.9	2444.9	2420.3	2420.3	2410.4	2267.8	2238.3	2228.4
60°	2228.4	2238.3	2258.0	2253.0	2258.0	2238.3	2228.4	2218.5	2095.6	2075.9	2041.5
62.5°	2026.8	2036.5	2041.5	2031.6	2041.5	2036.5	2026.8	1997.2	1923.4	1908.6	1864.4
65°	1815.2	1825.0	1830.0	1820.1	1830.0	1825.0	1815.2	1800.4	1746.3	1721.7	1682.4
67.5°	1598.8	1593.8	1588.9	1608.5	1588.9	1593.8	1598.8	1579.1	1544.7	1524.9	1470.8
70°	1377.3	1377.3	1372.5	1382.3	1372.5	1377.3	1377.3	1362.6	1342.9	1328.2	1279.0
72.5°	1141.3	1136.3	1156.0	1141.3	1156.0	1136.3	1141.3	1136.3	1126.5	1111.7	1062.5
75°	910.1	919.9	910.1	924.8	910.1	919.9	910.1	914.9	910.1	900.2	865.8
77.5°	693.6	703.5	693.6	693.6	693.6	703.5	693.6	698.6	698.6	698.6	669.0
80°	492.0	487.0	487.0	482.1	487.0	487.0	492.0	492.0	496.8	487.0	477.1
82.5°	314.8	309.9	309.9	319.8	309.9	309.9	314.8	319.8	309.9	309.9	309.9
85°	172.2	177.1	167.2	167.2	167.2	177.1	172.2	162.3	172.2	172.2	167.2
87.5°	64.0	59.0	59.0	59.0	59.0	59.0	64.0	68.9	68.9	68.9	73.7
90°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	14.7	19.7	22.1	19.0
92.5°	55.3	53.1	44.4	35.6	44.4	53.1	55.3	78.4	109.2	124.6	109.4
95°	187.8	181.1	154.5	127.8	154.5	181.1	187.8	246.6	325.0	364.2	307.7
97.5°	433.5	420.8	370.2	319.4	370.2	420.8	433.5	470.7	520.3	545.1	450.7
100°	608.8	593.7	533.3	472.9	533.3	593.7	608.8	606.1	602.5	600.7	495.9
102.5°	758.4	745.5	693.7	642.0	693.7	745.5	758.4	711.1	648.0	616.4	510.2
105°	933.1	926.2	898.4	870.5	898.4	926.2	933.1	826.9	685.4	614.6	511.7
107.5°	1024.0	1025.7	1032.5	1039.2	1032.5	1025.7	1024.0	875.9	678.4	579.7	489.0
110°	1047.3	1054.6	1083.5	1112.5	1083.5	1054.6	1047.3	881.7	661.0	550.6	468.8



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1032.5	1043.6	1088.1	1132.6	1088.1	1043.6	1032.5	863.0	637.1	524.1	451.2
115°	982.1	997.5	1059.2	1120.9	1059.2	997.5	982.1	818.8	601.2	492.3	430.9
117.5°	912.5	929.7	998.1	1066.5	998.1	929.7	912.5	765.2	568.8	470.5	418.3
120°	865.6	882.3	948.7	1015.2	948.7	882.3	865.6	731.0	551.5	461.7	414.0
122.5°	818.7	835.1	900.8	966.4	900.8	835.1	818.7	697.5	535.9	455.0	411.7
125°	756.7	771.8	832.2	892.6	832.2	771.8	756.7	653.7	516.4	447.8	410.0
127.5°	706.9	719.7	770.6	821.6	770.6	719.7	706.9	618.5	500.6	441.7	408.9
130°	675.5	687.3	734.4	781.5	734.4	687.3	675.5	596.8	491.9	439.3	409.5
132.5°	648.7	659.3	701.5	743.6	701.5	659.3	648.7	578.3	484.3	437.3	410.0
135°	610.9	620.0	656.3	692.6	656.3	620.0	610.9	551.8	473.2	433.8	409.6
137.5°	582.9	590.3	620.1	649.9	620.1	590.3	582.9	532.9	466.5	433.2	412.1
140°	560.5	567.4	595.3	623.1	595.3	567.4	560.5	517.3	459.9	431.2	412.5
142.5°	544.8	550.8	574.7	598.6	574.7	550.8	544.8	506.9	456.4	431.2	414.0
145°	521.1	525.7	543.8	561.9	543.8	525.7	521.1	490.2	448.9	428.3	414.0
147.5°	501.4	505.1	520.2	535.2	520.2	505.1	501.4	477.0	444.6	428.3	416.9
150°	490.0	493.0	505.2	517.3	505.2	493.0	490.0	469.5	442.1	428.3	418.3
152.5°	481.0	483.3	492.4	501.7	492.4	483.3	481.0	463.5	440.0	428.3	419.3
155°	470.3	471.8	477.8	483.9	477.8	471.8	470.3	456.3	437.6	428.3	421.4
157.5°	460.9	461.9	466.3	470.5	466.3	461.9	460.9	450.0	435.6	428.3	423.5
160°	456.2	456.8	459.3	461.7	459.3	456.8	456.2	446.9	434.5	428.3	424.5
162.5°	451.8	452.4	454.8	457.1	454.8	452.4	451.8	444.0	433.5	428.3	425.6
165°	445.2	445.7	448.3	450.7	448.3	445.7	445.2	439.5	432.1	428.3	427.0
167.5°	442.3	442.5	443.5	444.6	443.5	442.5	442.3	438.6	433.6	431.2	430.1
170°	442.3	442.3	442.3	442.3	442.3	442.3	442.3	438.6	433.6	431.2	431.1
172.5°	439.9	439.7	438.8	437.9	438.8	439.7	439.9	437.0	433.1	431.2	431.2
175°	436.7	436.7	436.7	436.7	436.7	436.7	436.7	434.9	432.5	431.2	431.8
177.5°	436.1	435.9	434.9	433.8	434.9	435.9	436.1	434.7	432.8	431.8	432.3
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5135.7	5160.3	5175.0	5194.7	5243.9
5°	4938.9	5032.4	5061.9	5135.7	5224.2
7.5°	4506.0	4791.3	4870.0	5047.1	5184.8
10°	4087.9	4373.2	4510.9	4929.1	5135.7
12.5°	3876.4	4043.6	4137.0	4722.4	5066.8
15°	3743.5	3861.6	3930.5	4446.9	4988.1
17.5°	3640.2	3723.9	3773.1	4176.4	4879.9
20°	3576.3	3615.6	3659.9	3979.7	4756.9
22.5°	3532.0	3507.4	3541.9	3841.9	4589.7
25°	3502.5	3409.0	3448.4	3733.7	4392.9
27.5°	3527.1	3320.5	3335.2	3635.3	4186.3
30°	3532.0	3212.2	3217.2	3532.0	3955.1
32.5°	3497.6	3099.2	3104.0	3404.1	3694.3
35°	3414.0	2966.3	2961.4	3256.5	3340.1
37.5°	3300.8	2823.7	2823.7	3094.2	2951.6
40°	3163.1	2680.9	2695.8	2882.7	2607.2
42.5°	2995.8	2528.5	2548.2	2602.2	2351.4
45°	2813.8	2380.9	2395.7	2198.9	2154.6
47.5°	2612.1	2228.4	2233.4	1825.0	2090.7
50°	2371.0	2070.9	2051.3	1564.4	2085.8
52.5°	2159.5	1898.9	1839.7	1416.8	1893.9
55°	1952.9	1716.8	1588.9	1303.6	1756.1
57.5°	1770.9	1480.7	1357.7	1170.7	1726.7
60°	1603.7	1249.5	1156.0	1028.1	1584.0
62.5°	1465.9	1077.3	1057.7	929.8	1436.4
65°	1318.3	959.2	954.4	846.1	1220.0
67.5°	1175.7	880.5	875.6	767.4	929.8
70°	1023.2	796.9	787.1	683.7	688.7
72.5°	865.8	703.5	693.6	614.9	570.6
75°	708.3	595.3	590.3	536.1	462.4
77.5°	555.9	472.3	482.1	432.9	339.4
80°	398.5	344.4	354.2	309.9	255.8
82.5°	265.6	226.3	236.1	196.8	172.2
85°	147.6	127.9	132.8	103.3	78.7
87.5°	68.9	59.0	59.0	39.3	24.6
90°	12.8	8.1	7.6	5.2	2.9
92.5°	79.0	56.2	51.3	31.4	11.6
95°	194.4	109.5	100.4	64.1	27.9
97.5°	261.8	120.3	112.3	80.3	48.4
100°	286.4	129.3	122.0	93.0	64.1
102.5°	297.7	138.3	131.5	104.5	77.4
105°	306.0	151.6	145.9	123.1	100.2
107.5°	307.6	171.5	166.2	144.8	123.5
110°	305.2	182.6	177.7	158.4	139.1



TEST NUMBER: P934179

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	305.3	195.9	191.4	173.0	154.7
115°	308.1	216.1	211.8	194.9	177.9
117.5°	313.9	235.6	231.7	216.3	200.9
120°	318.5	246.9	243.3	228.8	214.2
122.5°	325.2	260.3	256.6	242.1	227.4
125°	334.3	277.5	274.2	260.9	247.5
127.5°	343.3	294.1	290.7	277.2	263.8
130°	349.9	305.1	301.6	287.0	272.5
132.5°	355.2	314.1	310.6	296.0	281.6
135°	361.0	324.6	321.3	308.1	295.0
137.5°	369.8	338.0	334.7	321.7	308.6
140°	375.1	347.1	344.1	332.0	320.0
142.5°	379.6	353.8	351.0	339.8	328.7
145°	385.4	364.0	361.5	351.8	342.2
147.5°	393.9	376.7	374.4	364.9	355.5
150°	398.4	383.4	381.3	372.8	364.2
152.5°	401.3	387.8	386.1	379.8	373.3
155°	407.7	397.4	396.2	391.4	386.6
157.5°	414.2	407.1	405.9	401.2	396.5
160°	417.1	411.4	410.6	406.9	403.3
162.5°	420.2	416.1	415.4	412.7	410.0
165°	424.6	422.8	422.2	419.7	417.3
167.5°	428.1	426.6	426.3	425.1	423.9
170°	431.0	430.9	430.6	429.5	428.3
172.5°	431.2	431.2	431.1	430.9	430.6
175°	432.9	433.8	433.8	433.8	433.8
177.5°	433.1	433.8	433.8	433.8	433.8
180°	433.8	433.8	433.8	433.8	433.8



TEST NUMBER: P934179
 CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-STD-W-12-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.07	18.33	17.69	18.96	19.67	19.92	21.18	20.54	21.81	22.52
	3H	17.58	18.71	18.21	19.35	20.09	21.31	22.44	21.93	23.07	23.82
	4H	17.79	18.86	18.44	19.50	20.26	21.77	22.84	22.42	23.49	24.25
	6H	17.93	18.91	18.59	19.57	20.35	22.08	23.07	22.74	23.73	24.50
	8H	17.94	18.88	18.61	19.56	20.34	22.17	23.11	22.84	23.79	24.57
	12H	17.92	18.82	18.60	19.49	20.30	22.23	23.12	22.91	23.80	24.60
4H	2H	18.16	19.23	18.81	19.87	20.63	20.38	21.45	21.03	22.10	22.86
	3H	19.22	20.11	19.89	20.80	21.58	21.93	22.82	22.59	23.51	24.29
	4H	19.51	20.32	20.19	21.01	21.82	22.48	23.28	23.16	23.98	24.79
	6H	19.66	20.36	20.36	21.08	21.90	22.87	23.57	23.57	24.29	25.11
	8H	19.68	20.33	20.38	21.04	21.88	22.99	23.64	23.70	24.36	25.19
	12H	19.66	20.25	20.39	20.99	21.83	23.07	23.66	23.80	24.40	25.23
8H	4H	20.00	20.66	20.71	21.37	22.20	22.63	23.29	23.34	24.00	24.83
	6H	20.28	20.82	21.02	21.58	22.42	23.09	23.63	23.83	24.39	25.23
	8H	20.33	20.81	21.08	21.57	22.42	23.25	23.73	24.00	24.49	25.34
	12H	20.33	20.76	21.08	21.50	22.42	23.37	23.80	24.12	24.55	25.46
12H	4H	20.03	20.62	20.75	21.35	22.19	22.62	23.20	23.34	23.94	24.78
	6H	20.35	20.83	21.09	21.59	22.44	23.09	23.58	23.84	24.34	25.19
	8H	20.43	20.86	21.18	21.61	22.52	23.27	23.70	24.03	24.45	25.36