

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934389

Luminaire Tested: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934389
REPORT IS A COMBINATION OF REPORTS P933695 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6878.8 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934389
CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58		
1	100	95	91	88	93	89	86	83	77	75	72	66	64	63	56	55	54	49		
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45	41		
3	83	73	66	60	77	68	62	57	60	55	50	51	48	44	44	41	39	35		
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33	30		
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29	26		
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25	23		
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23	20		
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18		
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16		
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9504	9504	9504	9504
5°	9571	9594	9571	7544
10°	9504	9450	9504	6756
15°	9397	9245	9397	7721
20°	9197	9003	9197	7737
25°	8791	8649	8791	7572
30°	8268	8356	8268	7213
35°	7367	7984	7367	6817
40°	6136	7547	6136	6518
45°	5478	7035	5478	6174
50°	5816	6425	5816	5830
55°	5466	5767	5466	5630
60°	5628	4898	5628	5156
65°	5095	4048	5095	4526
70°	3520	3227	3520	3793
75°	3074	2385	3074	2856
80°	2461	1577	2461	1716
85°	1389	835	1389	710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 8402 cd/sqm



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.7	2.0
10°-20°	393.8	5.7
20°-30°	608.7	8.8
30°-40°	726.6	10.6
40°-50°	730.9	10.6
50°-60°	636.0	9.2
60°-70°	450.9	6.6
70°-80°	238.6	3.5
80°-90°	61.1	0.9
90°-100°	217.6	3.2
100°-110°	572.0	8.3
110°-120°	593.1	8.6
120°-130°	475.8	6.9
130°-140°	373.3	5.4
140°-150°	286.5	4.2
150°-160°	206.4	3.0
160°-170°	126.3	1.8
170°-180°	42.7	0.6
0°-30°	1141.1	16.6
0°-40°	1867.7	27.2
0°-60°	3234.6	47.0
0°-90°	3985.2	57.9
90°-120°	1382.8	20.1
90°-150°	2518.4	36.6
90°-180°	2894.0	42.1
0°-180°	6878.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1536	1536	1536	1536	1536	
5°	1544	1592	1544	1252	1544	146
15°	1474	1577	1474	1317	1474	415
25°	1298	1471	1298	1288	1298	596
35°	987	1312	987	1121	987	611
45°	637	1081	637	949	637	510
55°	519	798	519	779	519	477
65°	360	481	360	538	360	345
75°	137	228	137	273	137	144
85°	23	58	23	49	23	31
90°	3	11	3	11	3	3
95°	29	132	29	132	29	32
105°	103	896	103	896	103	109
115°	183	1153	183	1153	183	181
125°	255	918	255	918	255	226
135°	304	713	304	713	304	235
145°	352	578	352	578	352	221
155°	398	498	398	498	398	183
165°	429	464	429	464	429	121
175°	446	449	446	449	446	42
180°	446	446	446	446	446	



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3
2.5°	1549.4	1549.4	1558.2	1561.1	1561.1	1556.7	1552.3	1556.7	1569.8	1574.1	1572.7
5°	1543.6	1555.2	1571.2	1574.1	1577.0	1575.6	1572.7	1575.6	1590.1	1593.0	1594.5
7.5°	1532.0	1553.8	1574.1	1578.5	1582.9	1578.5	1577.0	1580.0	1594.5	1597.4	1597.4
10°	1517.5	1548.0	1571.2	1574.1	1578.5	1574.1	1574.1	1580.0	1594.5	1597.4	1598.8
12.5°	1497.1	1539.3	1561.1	1564.0	1569.8	1568.3	1566.9	1572.7	1587.2	1590.1	1590.1
15°	1473.8	1523.3	1543.6	1546.5	1556.7	1553.8	1553.8	1559.6	1575.6	1580.0	1578.5
17.5°	1441.9	1502.9	1526.2	1530.5	1537.8	1536.3	1537.8	1543.6	1558.2	1561.1	1562.5
20°	1405.5	1475.3	1502.9	1507.3	1514.5	1514.5	1514.5	1521.8	1536.3	1542.2	1542.2
22.5°	1356.1	1446.2	1475.3	1478.2	1486.9	1486.9	1489.8	1500.0	1513.1	1514.5	1514.5
25°	1298.0	1414.3	1439.0	1447.7	1456.4	1460.8	1465.1	1470.9	1475.3	1473.8	1475.3
27.5°	1236.9	1373.6	1405.5	1411.3	1423.0	1427.3	1433.2	1434.6	1436.1	1440.4	1437.5
30°	1168.6	1316.9	1364.8	1370.7	1389.5	1392.5	1386.6	1389.5	1396.8	1399.7	1402.6
32.5°	1091.6	1232.6	1322.7	1335.8	1353.2	1344.5	1343.0	1347.4	1359.0	1359.0	1361.9
35°	986.9	1167.2	1283.4	1295.1	1308.1	1298.0	1303.8	1305.2	1312.5	1316.9	1315.4
37.5°	872.1	1110.5	1242.7	1251.5	1261.6	1248.6	1257.3	1261.6	1267.5	1264.5	1264.5
40°	770.4	1021.8	1194.8	1200.6	1209.3	1199.1	1207.9	1210.8	1213.7	1210.8	1209.3
42.5°	694.8	924.4	1143.9	1151.2	1145.4	1152.6	1155.5	1161.3	1157.0	1151.2	1151.2
45°	636.6	898.3	1088.7	1097.4	1088.7	1100.3	1104.7	1104.7	1091.6	1088.7	1087.2
47.5°	617.7	845.9	1033.4	1033.4	1029.1	1043.6	1050.9	1040.7	1027.6	1023.3	1023.3
50°	616.3	787.8	957.9	952.0	972.4	989.8	982.6	972.4	962.2	946.2	946.2
52.5°	559.6	716.6	860.5	882.3	914.3	924.4	912.8	902.6	885.2	877.9	872.1
55°	518.9	642.4	771.8	815.4	848.8	861.9	840.1	829.9	803.8	799.4	796.5
57.5°	510.2	534.9	690.4	745.6	786.3	784.9	771.8	752.9	731.1	726.8	725.3
60°	468.0	386.6	603.2	668.6	710.8	706.4	694.8	677.3	657.0	654.1	651.2
62.5°	424.4	280.5	504.4	578.5	638.1	636.6	626.5	600.3	585.8	578.5	572.7
65°	360.5	235.5	359.0	481.1	566.9	569.8	548.0	529.1	513.1	504.4	502.9
67.5°	274.7	191.9	242.7	401.2	498.6	495.6	468.0	459.3	439.0	434.6	425.9
70°	203.5	127.9	168.6	325.6	431.7	424.4	402.6	392.4	373.5	363.4	357.6
72.5°	168.6	103.2	123.5	252.9	363.4	354.7	335.8	324.1	308.1	299.4	293.6
75°	136.6	109.0	94.5	187.5	295.1	289.2	271.8	260.2	247.1	235.5	236.9
77.5°	100.3	101.7	75.6	138.1	234.0	225.3	215.1	200.6	194.8	183.1	183.1
80°	75.6	79.9	56.7	94.5	168.6	168.6	159.9	149.7	139.5	133.7	133.7
82.5°	50.9	50.9	42.2	59.6	114.8	110.5	104.7	101.7	95.9	93.0	93.0
85°	23.3	29.1	26.2	36.3	62.5	65.4	65.4	62.5	61.0	58.1	59.6
87.5°	7.3	13.1	16.0	20.3	32.0	33.4	34.9	34.9	34.9	36.3	36.3
90°	3.0	5.4	7.8	8.4	13.2	19.6	22.8	20.3	15.1	11.3	11.3
92.5°	12.0	32.4	52.7	57.8	81.3	112.6	128.2	112.3	80.6	56.9	54.7
95°	28.8	66.0	103.3	112.6	200.0	316.6	374.8	334.5	253.8	193.2	186.3
97.5°	49.7	82.7	115.5	123.7	269.5	463.8	560.9	535.4	484.3	446.0	432.9
100°	65.9	95.7	125.6	133.0	294.7	510.3	618.0	619.9	623.6	626.5	611.0
102.5°	79.7	107.6	135.4	142.3	306.3	524.9	634.2	666.7	731.7	780.4	767.2
105°	103.1	126.6	150.2	156.1	314.8	526.6	632.4	705.2	850.9	960.2	953.0
107.5°	127.0	149.0	170.9	176.5	316.5	503.1	596.4	698.0	901.2	1053.6	1055.3
110°	143.2	163.0	182.9	187.8	314.1	482.4	566.5	680.0	907.3	1077.6	1085.1



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	159.1	178.0	196.9	201.6	314.1	464.2	539.2	655.5	888.0	1062.3	1073.7
115°	183.0	200.5	217.9	222.3	317.1	443.4	506.6	618.6	842.5	1010.5	1026.4
117.5°	206.7	222.6	238.4	242.3	323.0	430.4	484.1	585.2	787.3	938.9	956.5
120°	220.4	235.4	250.3	254.1	327.7	426.0	475.1	567.4	752.1	890.6	907.8
122.5°	234.0	249.0	264.1	267.8	334.6	423.6	468.2	551.4	717.7	842.4	859.3
125°	254.7	268.3	282.1	285.5	343.9	421.8	460.8	531.4	672.7	778.6	794.1
127.5°	271.4	285.3	299.1	302.6	353.2	420.7	454.5	515.1	636.3	727.3	740.4
130°	280.4	295.4	310.3	314.0	360.0	421.3	452.0	506.0	614.1	695.1	707.2
132.5°	289.7	304.7	319.6	323.3	365.5	421.8	450.0	498.4	595.0	667.4	678.3
135°	303.5	317.1	330.6	334.0	371.5	421.4	446.4	486.9	567.8	628.5	637.9
137.5°	317.5	331.0	344.4	347.8	380.4	423.9	445.7	479.9	548.4	599.7	607.4
140°	329.3	341.7	354.0	357.1	386.0	424.4	443.7	473.3	532.4	576.7	583.8
142.5°	338.2	349.6	361.0	364.0	390.5	426.0	443.7	469.7	521.5	560.5	566.7
145°	352.0	362.0	372.0	374.5	396.6	426.0	440.7	461.9	504.4	536.2	540.9
147.5°	365.8	375.5	385.3	387.7	405.3	428.9	440.7	457.4	490.8	515.9	519.8
150°	374.8	383.6	392.3	394.6	410.0	430.4	440.7	454.8	483.0	504.2	507.3
152.5°	384.0	390.7	397.4	399.0	412.9	431.4	440.7	452.7	476.8	494.9	497.2
155°	397.9	402.8	407.7	408.9	419.5	433.6	440.7	450.3	469.5	483.8	485.4
157.5°	408.0	412.8	417.6	418.8	426.1	435.9	440.7	448.2	463.1	474.2	475.3
160°	414.9	418.6	422.3	423.3	429.1	436.8	440.7	447.1	459.9	469.5	470.1
162.5°	421.8	424.6	427.4	428.1	432.3	437.9	440.7	446.1	456.9	464.9	465.5
165°	429.3	431.8	434.3	435.0	436.9	439.4	440.7	444.6	452.2	458.0	458.7
167.5°	436.1	437.3	438.6	438.9	440.5	442.6	443.7	446.2	451.3	455.0	455.3
170°	440.7	441.9	443.1	443.4	443.5	443.6	443.7	446.2	451.3	455.0	455.0
172.5°	443.1	443.4	443.6	443.7	443.7	443.7	443.7	445.6	449.6	452.6	452.4
175°	446.4	446.4	446.4	446.4	445.5	444.3	443.7	445.0	447.5	449.3	449.3
177.5°	446.4	446.4	446.4	446.4	445.7	444.8	444.3	445.3	447.3	448.7	448.5
180°	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3
2.5°	1575.6	1571.2	1575.6	1572.7	1574.1	1569.8	1556.7	1552.3	1556.7	1561.1	1561.1
5°	1594.5	1591.6	1594.5	1594.5	1593.0	1590.1	1575.6	1572.7	1575.6	1577.0	1574.1
7.5°	1600.3	1595.9	1600.3	1597.4	1597.4	1594.5	1580.0	1577.0	1578.5	1582.9	1578.5
10°	1600.3	1595.9	1600.3	1598.8	1597.4	1594.5	1580.0	1574.1	1574.1	1578.5	1574.1
12.5°	1593.0	1590.1	1593.0	1590.1	1590.1	1587.2	1572.7	1566.9	1568.3	1569.8	1564.0
15°	1581.4	1577.0	1581.4	1578.5	1580.0	1575.6	1559.6	1553.8	1553.8	1556.7	1546.5
17.5°	1564.0	1558.2	1564.0	1562.5	1561.1	1558.2	1543.6	1537.8	1536.3	1537.8	1530.5
20°	1543.6	1539.3	1543.6	1542.2	1542.2	1536.3	1521.8	1514.5	1514.5	1514.5	1507.3
22.5°	1511.6	1507.3	1511.6	1514.5	1514.5	1513.1	1500.0	1489.8	1486.9	1486.9	1478.2
25°	1475.3	1470.9	1475.3	1475.3	1473.8	1475.3	1470.9	1465.1	1460.8	1456.4	1447.7
27.5°	1440.4	1437.5	1440.4	1437.5	1440.4	1436.1	1434.6	1433.2	1427.3	1423.0	1411.3
30°	1405.5	1402.6	1405.5	1402.6	1399.7	1396.8	1389.5	1386.6	1392.5	1389.5	1370.7
32.5°	1361.9	1359.0	1361.9	1361.9	1359.0	1359.0	1347.4	1343.0	1344.5	1353.2	1335.8
35°	1316.9	1312.5	1316.9	1315.4	1316.9	1312.5	1305.2	1303.8	1298.0	1308.1	1295.1
37.5°	1264.5	1260.2	1264.5	1264.5	1264.5	1267.5	1261.6	1257.3	1248.6	1261.6	1251.5
40°	1210.8	1205.0	1210.8	1209.3	1210.8	1213.7	1210.8	1207.9	1199.1	1209.3	1200.6
42.5°	1149.7	1148.3	1149.7	1151.2	1151.2	1157.0	1161.3	1155.5	1152.6	1145.4	1151.2
45°	1084.3	1081.4	1084.3	1087.2	1088.7	1091.6	1104.7	1104.7	1100.3	1088.7	1097.4
47.5°	1014.5	1007.3	1014.5	1023.3	1023.3	1027.6	1040.7	1050.9	1043.6	1029.1	1033.4
50°	940.4	941.9	940.4	946.2	946.2	962.2	972.4	982.6	989.8	972.4	952.0
52.5°	867.7	866.3	867.7	872.1	877.9	885.2	902.6	912.8	924.4	914.3	882.3
55°	795.1	798.0	795.1	796.5	799.4	803.8	829.9	840.1	861.9	848.8	815.4
57.5°	722.4	718.0	722.4	725.3	726.8	731.1	752.9	771.8	784.9	786.3	745.6
60°	638.1	632.3	638.1	651.2	654.1	657.0	677.3	694.8	706.4	710.8	668.6
62.5°	564.0	553.8	564.0	572.7	578.5	585.8	600.3	626.5	636.6	638.1	578.5
65°	485.5	481.1	485.5	502.9	504.4	513.1	529.1	548.0	569.8	566.9	481.1
67.5°	414.2	414.2	414.2	425.9	434.6	439.0	459.3	468.0	495.6	498.6	401.2
70°	348.8	347.4	348.8	357.6	363.4	373.5	392.4	402.6	424.4	431.7	325.6
72.5°	286.3	284.9	286.3	293.6	299.4	308.1	324.1	335.8	354.7	363.4	252.9
75°	231.1	228.2	231.1	236.9	235.5	247.1	260.2	271.8	289.2	295.1	187.5
77.5°	177.3	177.3	177.3	183.1	183.1	194.8	200.6	215.1	225.3	234.0	138.1
80°	132.3	130.8	132.3	133.7	133.7	139.5	149.7	159.9	168.6	168.6	94.5
82.5°	93.0	90.1	93.0	93.0	93.0	95.9	101.7	104.7	110.5	114.8	59.6
85°	58.1	58.1	58.1	59.6	58.1	61.0	62.5	65.4	65.4	62.5	36.3
87.5°	37.8	36.3	37.8	36.3	36.3	34.9	34.9	34.9	33.4	32.0	20.3
90°	11.3	11.3	11.3	11.3	11.3	15.1	20.3	22.8	19.6	13.2	8.4
92.5°	45.5	36.5	45.5	54.7	56.9	80.6	112.3	128.2	112.6	81.3	57.8
95°	158.9	131.5	158.9	186.3	193.2	253.8	334.5	374.8	316.6	200.0	112.6
97.5°	380.8	328.7	380.8	432.9	446.0	484.3	535.4	560.9	463.8	269.5	123.7
100°	548.7	486.5	548.7	611.0	626.5	623.6	619.9	618.0	510.3	294.7	133.0
102.5°	713.9	660.6	713.9	767.2	780.4	731.7	666.7	634.2	524.9	306.3	142.3
105°	924.4	895.7	924.4	953.0	960.2	850.9	705.2	632.4	526.6	314.8	156.1
107.5°	1062.2	1069.2	1062.2	1055.3	1053.6	901.2	698.0	596.4	503.1	316.5	176.5
110°	1114.8	1144.7	1114.8	1085.1	1077.6	907.3	680.0	566.5	482.4	314.1	187.8



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1119.6	1165.3	1119.6	1073.7	1062.3	888.0	655.5	539.2	464.2	314.1	201.6
115°	1089.8	1153.4	1089.8	1026.4	1010.5	842.5	618.6	506.6	443.4	317.1	222.3
117.5°	1026.9	1097.4	1026.9	956.5	938.9	787.3	585.2	484.1	430.4	323.0	242.3
120°	976.2	1044.7	976.2	907.8	890.6	752.1	567.4	475.1	426.0	327.7	254.1
122.5°	926.8	994.3	926.8	859.3	842.4	717.7	551.4	468.2	423.6	334.6	267.8
125°	856.3	918.5	856.3	794.1	778.6	672.7	531.4	460.8	421.8	343.9	285.5
127.5°	792.9	845.5	792.9	740.4	727.3	636.3	515.1	454.5	420.7	353.2	302.6
130°	755.6	804.1	755.6	707.2	695.1	614.1	506.0	452.0	421.3	360.0	314.0
132.5°	721.7	765.1	721.7	678.3	667.4	595.0	498.4	450.0	421.8	365.5	323.3
135°	675.3	712.7	675.3	637.9	628.5	567.8	486.9	446.4	421.4	371.5	334.0
137.5°	638.1	668.7	638.1	607.4	599.7	548.4	479.9	445.7	423.9	380.4	347.8
140°	612.4	641.1	612.4	583.8	576.7	532.4	473.3	443.7	424.4	386.0	357.1
142.5°	591.3	615.9	591.3	566.7	560.5	521.5	469.7	443.7	426.0	390.5	364.0
145°	559.6	578.2	559.6	540.9	536.2	504.4	461.9	440.7	426.0	396.6	374.5
147.5°	535.2	550.6	535.2	519.8	515.9	490.8	457.4	440.7	428.9	405.3	387.7
150°	519.9	532.4	519.9	507.3	504.2	483.0	454.8	440.7	430.4	410.0	394.6
152.5°	506.7	516.2	506.7	497.2	494.9	476.8	452.7	440.7	431.4	412.9	399.0
155°	491.7	497.9	491.7	485.4	483.8	469.5	450.3	440.7	433.6	419.5	408.9
157.5°	479.8	484.1	479.8	475.3	474.2	463.1	448.2	440.7	435.9	426.1	418.8
160°	472.6	475.1	472.6	470.1	469.5	459.9	447.1	440.7	436.8	429.1	423.3
162.5°	467.9	470.4	467.9	465.5	464.9	456.9	446.1	440.7	437.9	432.3	428.1
165°	461.2	463.8	461.2	458.7	458.0	452.2	444.6	440.7	439.4	436.9	435.0
167.5°	456.4	457.5	456.4	455.3	455.0	451.3	446.2	443.7	442.6	440.5	438.9
170°	455.0	455.0	455.0	455.0	455.0	451.3	446.2	443.7	443.6	443.5	443.4
172.5°	451.5	450.6	451.5	452.4	452.6	449.6	445.6	443.7	443.7	443.7	443.7
175°	449.3	449.3	449.3	449.3	449.3	447.5	445.0	443.7	444.3	445.5	446.4
177.5°	447.5	446.4	447.5	448.5	448.7	447.3	445.3	444.3	444.8	445.7	446.4
180°	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3
2.5°	1558.2	1549.4	1549.4	1534.9	1529.1	1524.7	1517.5	1495.7	1489.8	1484.0	1492.7
5°	1571.2	1555.2	1543.6	1517.5	1495.7	1486.9	1459.3	1407.0	1372.1	1345.9	1331.4
7.5°	1574.1	1553.8	1532.0	1491.3	1439.0	1415.7	1331.4	1235.5	1209.3	1186.1	1171.5
10°	1571.2	1548.0	1517.5	1456.4	1332.9	1292.2	1207.9	1145.4	1129.4	1125.0	1129.4
12.5°	1561.1	1539.3	1497.1	1395.4	1222.4	1194.8	1145.4	1109.0	1106.1	1113.4	1152.6
15°	1543.6	1523.3	1473.8	1314.0	1161.3	1141.0	1106.1	1093.0	1109.0	1159.9	1277.6
17.5°	1526.2	1502.9	1441.9	1234.0	1114.8	1100.3	1075.6	1101.8	1191.9	1260.2	1299.4
20°	1502.9	1475.3	1405.5	1175.9	1081.4	1068.3	1056.7	1174.4	1242.7	1267.5	1289.3
22.5°	1475.3	1446.2	1356.1	1135.2	1046.5	1036.3	1043.6	1215.1	1242.7	1260.2	1279.1
25°	1439.0	1414.3	1298.0	1103.2	1018.9	1007.3	1034.9	1210.8	1226.8	1231.1	1268.9
27.5°	1405.5	1373.6	1236.9	1074.1	985.5	981.1	1042.2	1191.9	1203.5	1207.9	1248.6
30°	1364.8	1316.9	1168.6	1043.6	950.6	949.1	1043.6	1168.6	1165.7	1177.3	1218.0
32.5°	1322.7	1232.6	1091.6	1005.8	917.2	915.7	1033.4	1133.7	1130.8	1146.8	1177.3
35°	1283.4	1167.2	986.9	962.2	875.0	876.5	1008.7	1093.0	1094.5	1109.0	1127.9
37.5°	1242.7	1110.5	872.1	914.3	834.3	834.3	975.3	1055.2	1052.3	1056.7	1082.9
40°	1194.8	1021.8	770.4	851.8	796.5	792.2	934.6	1014.5	1004.4	1002.9	1039.3
42.5°	1143.9	924.4	694.8	768.9	752.9	747.1	885.2	965.1	946.2	950.6	997.1
45°	1088.7	898.3	636.6	649.7	707.9	703.5	831.4	908.4	895.4	907.0	954.9
47.5°	1033.4	845.9	617.7	539.2	659.9	658.4	771.8	853.2	845.9	857.6	908.4
50°	957.9	787.8	616.3	462.2	606.1	611.9	700.6	799.4	799.4	809.6	863.4
52.5°	860.5	716.6	559.6	418.6	543.6	561.1	638.1	752.9	755.8	766.0	814.0
55°	771.8	642.4	518.9	385.2	469.5	507.3	577.0	704.9	710.8	720.9	764.5
57.5°	690.4	534.9	510.2	345.9	401.2	437.5	523.3	658.4	661.3	670.1	712.2
60°	603.2	386.6	468.0	303.8	341.6	369.2	473.8	603.2	613.4	619.2	655.5
62.5°	504.4	280.5	424.4	274.7	312.5	318.3	433.1	550.9	564.0	568.3	590.1
65°	359.0	235.5	360.5	250.0	282.0	283.4	389.5	497.1	508.7	516.0	532.0
67.5°	242.7	191.9	274.7	226.7	258.7	260.2	347.4	434.6	450.6	456.4	466.6
70°	168.6	127.9	203.5	202.0	232.6	235.5	302.3	377.9	392.4	396.8	402.6
72.5°	123.5	103.2	168.6	181.7	204.9	207.9	255.8	314.0	328.5	332.9	335.8
75°	94.5	109.0	136.6	158.4	174.4	175.9	209.3	255.8	266.0	268.9	270.4
77.5°	75.6	101.7	100.3	127.9	142.4	139.5	164.2	197.7	206.4	206.4	206.4
80°	56.7	79.9	75.6	91.6	104.7	101.7	117.7	141.0	143.9	146.8	145.4
82.5°	42.2	50.9	50.9	58.1	69.8	66.9	78.5	91.6	91.6	91.6	94.5
85°	26.2	29.1	23.3	30.5	39.2	37.8	43.6	49.4	50.9	50.9	48.0
87.5°	16.0	13.1	7.3	11.6	17.4	17.4	20.3	21.8	20.3	20.3	20.3
90°	7.8	5.4	3.0	5.4	7.8	8.4	13.2	19.6	22.8	20.3	15.1
92.5°	52.7	32.4	12.0	32.4	52.7	57.8	81.3	112.6	128.2	112.3	80.6
95°	103.3	66.0	28.8	66.0	103.3	112.6	200.0	316.6	374.8	334.5	253.8
97.5°	115.5	82.7	49.7	82.7	115.5	123.7	269.5	463.8	560.9	535.4	484.3
100°	125.6	95.7	65.9	95.7	125.6	133.0	294.7	510.3	618.0	619.9	623.6
102.5°	135.4	107.6	79.7	107.6	135.4	142.3	306.3	524.9	634.2	666.7	731.7
105°	150.2	126.6	103.1	126.6	150.2	156.1	314.8	526.6	632.4	705.2	850.9
107.5°	170.9	149.0	127.0	149.0	170.9	176.5	316.5	503.1	596.4	698.0	901.2
110°	182.9	163.0	143.2	163.0	182.9	187.8	314.1	482.4	566.5	680.0	907.3



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	196.9	178.0	159.1	178.0	196.9	201.6	314.1	464.2	539.2	655.5	888.0
115°	217.9	200.5	183.0	200.5	217.9	222.3	317.1	443.4	506.6	618.6	842.5
117.5°	238.4	222.6	206.7	222.6	238.4	242.3	323.0	430.4	484.1	585.2	787.3
120°	250.3	235.4	220.4	235.4	250.3	254.1	327.7	426.0	475.1	567.4	752.1
122.5°	264.1	249.0	234.0	249.0	264.1	267.8	334.6	423.6	468.2	551.4	717.7
125°	282.1	268.3	254.7	268.3	282.1	285.5	343.9	421.8	460.8	531.4	672.7
127.5°	299.1	285.3	271.4	285.3	299.1	302.6	353.2	420.7	454.5	515.1	636.3
130°	310.3	295.4	280.4	295.4	310.3	314.0	360.0	421.3	452.0	506.0	614.1
132.5°	319.6	304.7	289.7	304.7	319.6	323.3	365.5	421.8	450.0	498.4	595.0
135°	330.6	317.1	303.5	317.1	330.6	334.0	371.5	421.4	446.4	486.9	567.8
137.5°	344.4	331.0	317.5	331.0	344.4	347.8	380.4	423.9	445.7	479.9	548.4
140°	354.0	341.7	329.3	341.7	354.0	357.1	386.0	424.4	443.7	473.3	532.4
142.5°	361.0	349.6	338.2	349.6	361.0	364.0	390.5	426.0	443.7	469.7	521.5
145°	372.0	362.0	352.0	362.0	372.0	374.5	396.6	426.0	440.7	461.9	504.4
147.5°	385.3	375.5	365.8	375.5	385.3	387.7	405.3	428.9	440.7	457.4	490.8
150°	392.3	383.6	374.8	383.6	392.3	394.6	410.0	430.4	440.7	454.8	483.0
152.5°	397.4	390.7	384.0	390.7	397.4	399.0	412.9	431.4	440.7	452.7	476.8
155°	407.7	402.8	397.9	402.8	407.7	408.9	419.5	433.6	440.7	450.3	469.5
157.5°	417.6	412.8	408.0	412.8	417.6	418.8	426.1	435.9	440.7	448.2	463.1
160°	422.3	418.6	414.9	418.6	422.3	423.3	429.1	436.8	440.7	447.1	459.9
162.5°	427.4	424.6	421.8	424.6	427.4	428.1	432.3	437.9	440.7	446.1	456.9
165°	434.3	431.8	429.3	431.8	434.3	435.0	436.9	439.4	440.7	444.6	452.2
167.5°	438.6	437.3	436.1	437.3	438.6	438.9	440.5	442.6	443.7	446.2	451.3
170°	443.1	441.9	440.7	441.9	443.1	443.4	443.5	443.6	443.7	446.2	451.3
172.5°	443.6	443.4	443.1	443.4	443.6	443.7	443.7	443.7	443.7	445.6	449.6
175°	446.4	446.4	446.4	446.4	446.4	446.4	445.5	444.3	443.7	445.0	447.5
177.5°	446.4	446.4	446.4	446.4	446.4	446.4	445.7	444.8	444.3	445.3	447.3
180°	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3	1536.3
2.5°	1482.6	1478.2	1484.0	1468.0	1484.0	1478.2	1482.6	1492.7	1484.0	1489.8	1495.7
5°	1300.9	1293.6	1270.4	1251.5	1270.4	1293.6	1300.9	1331.4	1345.9	1372.1	1407.0
7.5°	1162.8	1157.0	1151.2	1139.5	1151.2	1157.0	1162.8	1171.5	1186.1	1209.3	1235.5
10°	1132.3	1133.7	1142.5	1141.0	1142.5	1133.7	1132.3	1129.4	1125.0	1129.4	1145.4
12.5°	1210.8	1223.8	1271.8	1268.9	1271.8	1223.8	1210.8	1152.6	1113.4	1106.1	1109.0
15°	1300.9	1305.2	1315.4	1316.9	1315.4	1305.2	1300.9	1277.6	1159.9	1109.0	1093.0
17.5°	1309.6	1311.1	1318.3	1318.3	1318.3	1311.1	1309.6	1299.4	1260.2	1191.9	1101.8
20°	1302.3	1305.2	1319.8	1322.7	1319.8	1305.2	1302.3	1289.3	1267.5	1242.7	1174.4
22.5°	1299.4	1305.2	1316.9	1315.4	1316.9	1305.2	1299.4	1279.1	1260.2	1242.7	1215.1
25°	1284.9	1284.9	1286.3	1287.8	1286.3	1284.9	1284.9	1268.9	1231.1	1226.8	1210.8
27.5°	1254.4	1257.3	1266.0	1264.5	1266.0	1257.3	1254.4	1248.6	1207.9	1203.5	1191.9
30°	1226.8	1223.8	1216.6	1210.8	1216.6	1223.8	1226.8	1218.0	1177.3	1165.7	1168.6
32.5°	1180.2	1173.0	1165.7	1161.3	1165.7	1173.0	1180.2	1177.3	1146.8	1130.8	1133.7
35°	1125.0	1126.5	1125.0	1120.6	1125.0	1126.5	1125.0	1127.9	1109.0	1094.5	1093.0
37.5°	1085.8	1088.7	1087.2	1081.4	1087.2	1088.7	1085.8	1082.9	1056.7	1052.3	1055.2
40°	1045.1	1046.5	1045.1	1040.7	1045.1	1046.5	1045.1	1039.3	1002.9	1004.4	1014.5
42.5°	1005.8	1004.4	1000.0	997.1	1000.0	1004.4	1005.8	997.1	950.6	946.2	965.1
45°	960.8	962.2	953.5	949.1	953.5	962.2	960.8	954.9	907.0	895.4	908.4
47.5°	915.7	915.7	908.4	904.1	908.4	915.7	915.7	908.4	857.6	845.9	853.2
50°	867.7	866.3	856.1	854.7	856.1	866.3	867.7	863.4	809.6	799.4	799.4
52.5°	812.5	812.5	814.0	816.9	814.0	812.5	812.5	814.0	766.0	755.8	752.9
55°	764.5	766.0	776.2	779.1	776.2	766.0	764.5	764.5	720.9	710.8	704.9
57.5°	715.1	715.1	722.4	722.4	722.4	715.1	715.1	712.2	670.1	661.3	658.4
60°	658.4	661.3	667.2	665.7	667.2	661.3	658.4	655.5	619.2	613.4	603.2
62.5°	598.8	601.7	603.2	600.3	603.2	601.7	598.8	590.1	568.3	564.0	550.9
65°	536.3	539.2	540.7	537.8	540.7	539.2	536.3	532.0	516.0	508.7	497.1
67.5°	472.4	470.9	469.5	475.3	469.5	470.9	472.4	466.6	456.4	450.6	434.6
70°	407.0	407.0	405.5	408.4	405.5	407.0	407.0	402.6	396.8	392.4	377.9
72.5°	337.2	335.8	341.6	337.2	341.6	335.8	337.2	335.8	332.9	328.5	314.0
75°	268.9	271.8	268.9	273.3	268.9	271.8	268.9	270.4	268.9	266.0	255.8
77.5°	204.9	207.9	204.9	204.9	204.9	207.9	204.9	206.4	206.4	206.4	197.7
80°	145.4	143.9	143.9	142.4	143.9	143.9	145.4	145.4	146.8	143.9	141.0
82.5°	93.0	91.6	91.6	94.5	91.6	91.6	93.0	94.5	91.6	91.6	91.6
85°	50.9	52.3	49.4	49.4	49.4	52.3	50.9	48.0	50.9	50.9	49.4
87.5°	18.9	17.4	17.4	17.4	17.4	17.4	18.9	20.3	20.3	20.3	21.8
90°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	15.1	20.3	22.8	19.6
92.5°	56.9	54.7	45.5	36.5	45.5	54.7	56.9	80.6	112.3	128.2	112.6
95°	193.2	186.3	158.9	131.5	158.9	186.3	193.2	253.8	334.5	374.8	316.6
97.5°	446.0	432.9	380.8	328.7	380.8	432.9	446.0	484.3	535.4	560.9	463.8
100°	626.5	611.0	548.7	486.5	548.7	611.0	626.5	623.6	619.9	618.0	510.3
102.5°	780.4	767.2	713.9	660.6	713.9	767.2	780.4	731.7	666.7	634.2	524.9
105°	960.2	953.0	924.4	895.7	924.4	953.0	960.2	850.9	705.2	632.4	526.6
107.5°	1053.6	1055.3	1062.2	1069.2	1062.2	1055.3	1053.6	901.2	698.0	596.4	503.1
110°	1077.6	1085.1	1114.8	1144.7	1114.8	1085.1	1077.6	907.3	680.0	566.5	482.4



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1062.3	1073.7	1119.6	1165.3	1119.6	1073.7	1062.3	888.0	655.5	539.2	464.2
115°	1010.5	1026.4	1089.8	1153.4	1089.8	1026.4	1010.5	842.5	618.6	506.6	443.4
117.5°	938.9	956.5	1026.9	1097.4	1026.9	956.5	938.9	787.3	585.2	484.1	430.4
120°	890.6	907.8	976.2	1044.7	976.2	907.8	890.6	752.1	567.4	475.1	426.0
122.5°	842.4	859.3	926.8	994.3	926.8	859.3	842.4	717.7	551.4	468.2	423.6
125°	778.6	794.1	856.3	918.5	856.3	794.1	778.6	672.7	531.4	460.8	421.8
127.5°	727.3	740.4	792.9	845.5	792.9	740.4	727.3	636.3	515.1	454.5	420.7
130°	695.1	707.2	755.6	804.1	755.6	707.2	695.1	614.1	506.0	452.0	421.3
132.5°	667.4	678.3	721.7	765.1	721.7	678.3	667.4	595.0	498.4	450.0	421.8
135°	628.5	637.9	675.3	712.7	675.3	637.9	628.5	567.8	486.9	446.4	421.4
137.5°	599.7	607.4	638.1	668.7	638.1	607.4	599.7	548.4	479.9	445.7	423.9
140°	576.7	583.8	612.4	641.1	612.4	583.8	576.7	532.4	473.3	443.7	424.4
142.5°	560.5	566.7	591.3	615.9	591.3	566.7	560.5	521.5	469.7	443.7	426.0
145°	536.2	540.9	559.6	578.2	559.6	540.9	536.2	504.4	461.9	440.7	426.0
147.5°	515.9	519.8	535.2	550.6	535.2	519.8	515.9	490.8	457.4	440.7	428.9
150°	504.2	507.3	519.9	532.4	519.9	507.3	504.2	483.0	454.8	440.7	430.4
152.5°	494.9	497.2	506.7	516.2	506.7	497.2	494.9	476.8	452.7	440.7	431.4
155°	483.8	485.4	491.7	497.9	491.7	485.4	483.8	469.5	450.3	440.7	433.6
157.5°	474.2	475.3	479.8	484.1	479.8	475.3	474.2	463.1	448.2	440.7	435.9
160°	469.5	470.1	472.6	475.1	472.6	470.1	469.5	459.9	447.1	440.7	436.8
162.5°	464.9	465.5	467.9	470.4	467.9	465.5	464.9	456.9	446.1	440.7	437.9
165°	458.0	458.7	461.2	463.8	461.2	458.7	458.0	452.2	444.6	440.7	439.4
167.5°	455.0	455.3	456.4	457.5	456.4	455.3	455.0	451.3	446.2	443.7	442.6
170°	455.0	455.0	455.0	455.0	455.0	455.0	455.0	451.3	446.2	443.7	443.6
172.5°	452.6	452.4	451.5	450.6	451.5	452.4	452.6	449.6	445.6	443.7	443.7
175°	449.3	449.3	449.3	449.3	449.3	449.3	449.3	447.5	445.0	443.7	444.3
177.5°	448.7	448.5	447.5	446.4	447.5	448.5	448.7	447.3	445.3	444.3	444.8
180°	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1536.3	1536.3	1536.3	1536.3	1536.3
2.5°	1517.5	1524.7	1529.1	1534.9	1549.4
5°	1459.3	1486.9	1495.7	1517.5	1543.6
7.5°	1331.4	1415.7	1439.0	1491.3	1532.0
10°	1207.9	1292.2	1332.9	1456.4	1517.5
12.5°	1145.4	1194.8	1222.4	1395.4	1497.1
15°	1106.1	1141.0	1161.3	1314.0	1473.8
17.5°	1075.6	1100.3	1114.8	1234.0	1441.9
20°	1056.7	1068.3	1081.4	1175.9	1405.5
22.5°	1043.6	1036.3	1046.5	1135.2	1356.1
25°	1034.9	1007.3	1018.9	1103.2	1298.0
27.5°	1042.2	981.1	985.5	1074.1	1236.9
30°	1043.6	949.1	950.6	1043.6	1168.6
32.5°	1033.4	915.7	917.2	1005.8	1091.6
35°	1008.7	876.5	875.0	962.2	986.9
37.5°	975.3	834.3	834.3	914.3	872.1
40°	934.6	792.2	796.5	851.8	770.4
42.5°	885.2	747.1	752.9	768.9	694.8
45°	831.4	703.5	707.9	649.7	636.6
47.5°	771.8	658.4	659.9	539.2	617.7
50°	700.6	611.9	606.1	462.2	616.3
52.5°	638.1	561.1	543.6	418.6	559.6
55°	577.0	507.3	469.5	385.2	518.9
57.5°	523.3	437.5	401.2	345.9	510.2
60°	473.8	369.2	341.6	303.8	468.0
62.5°	433.1	318.3	312.5	274.7	424.4
65°	389.5	283.4	282.0	250.0	360.5
67.5°	347.4	260.2	258.7	226.7	274.7
70°	302.3	235.5	232.6	202.0	203.5
72.5°	255.8	207.9	204.9	181.7	168.6
75°	209.3	175.9	174.4	158.4	136.6
77.5°	164.2	139.5	142.4	127.9	100.3
80°	117.7	101.7	104.7	91.6	75.6
82.5°	78.5	66.9	69.8	58.1	50.9
85°	43.6	37.8	39.2	30.5	23.3
87.5°	20.3	17.4	17.4	11.6	7.3
90°	13.2	8.4	7.8	5.4	3.0
92.5°	81.3	57.8	52.7	32.4	12.0
95°	200.0	112.6	103.3	66.0	28.8
97.5°	269.5	123.7	115.5	82.7	49.7
100°	294.7	133.0	125.6	95.7	65.9
102.5°	306.3	142.3	135.4	107.6	79.7
105°	314.8	156.1	150.2	126.6	103.1
107.5°	316.5	176.5	170.9	149.0	127.0
110°	314.1	187.8	182.9	163.0	143.2



TEST NUMBER: P934389

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	314.1	201.6	196.9	178.0	159.1
115°	317.1	222.3	217.9	200.5	183.0
117.5°	323.0	242.3	238.4	222.6	206.7
120°	327.7	254.1	250.3	235.4	220.4
122.5°	334.6	267.8	264.1	249.0	234.0
125°	343.9	285.5	282.1	268.3	254.7
127.5°	353.2	302.6	299.1	285.3	271.4
130°	360.0	314.0	310.3	295.4	280.4
132.5°	365.5	323.3	319.6	304.7	289.7
135°	371.5	334.0	330.6	317.1	303.5
137.5°	380.4	347.8	344.4	331.0	317.5
140°	386.0	357.1	354.0	341.7	329.3
142.5°	390.5	364.0	361.0	349.6	338.2
145°	396.6	374.5	372.0	362.0	352.0
147.5°	405.3	387.7	385.3	375.5	365.8
150°	410.0	394.6	392.3	383.6	374.8
152.5°	412.9	399.0	397.4	390.7	384.0
155°	419.5	408.9	407.7	402.8	397.9
157.5°	426.1	418.8	417.6	412.8	408.0
160°	429.1	423.3	422.3	418.6	414.9
162.5°	432.3	428.1	427.4	424.6	421.8
165°	436.9	435.0	434.3	431.8	429.3
167.5°	440.5	438.9	438.6	437.3	436.1
170°	443.5	443.4	443.1	441.9	440.7
172.5°	443.7	443.7	443.6	443.4	443.1
175°	445.5	446.4	446.4	446.4	446.4
177.5°	445.7	446.4	446.4	446.4	446.4
180°	446.4	446.4	446.4	446.4	446.4



TEST NUMBER: P934389
 CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-STD-W-6-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.33	14.27	14.21	15.17	16.33	16.15	17.09	17.04	18.00	19.15
	3H	13.81	14.65	14.71	15.57	16.75	17.50	18.34	18.40	19.26	20.44
	4H	14.01	14.80	14.92	15.72	16.91	17.95	18.74	18.86	19.66	20.85
	6H	14.13	14.86	15.05	15.79	16.99	18.24	18.97	19.16	19.90	21.10
	8H	14.13	14.83	15.06	15.77	16.97	18.31	19.01	19.24	19.95	21.15
	12H	14.11	14.77	15.04	15.71	16.93	18.35	19.02	19.29	19.95	21.18
4H	2H	14.37	15.16	15.29	16.08	17.27	16.57	17.37	17.49	18.29	19.48
	3H	15.40	16.06	16.33	17.02	18.22	18.08	18.74	19.01	19.70	20.90
	4H	15.68	16.29	16.62	17.23	18.46	18.61	19.22	19.55	20.16	21.39
	6H	15.81	16.33	16.77	17.30	18.53	18.98	19.50	19.93	20.47	21.70
	8H	15.82	16.31	16.77	17.27	18.51	19.09	19.57	20.04	20.54	21.78
	12H	15.79	16.23	16.76	17.21	18.46	19.15	19.59	20.12	20.57	21.82
8H	4H	16.14	16.63	17.10	17.59	18.83	18.74	19.23	19.70	20.19	21.44
	6H	16.41	16.81	17.39	17.81	19.05	19.18	19.58	20.16	20.59	21.83
	8H	16.45	16.80	17.44	17.80	19.06	19.33	19.69	20.32	20.68	21.94
	12H	16.44	16.75	17.43	17.74	19.04	19.43	19.75	20.43	20.73	22.04
12H	4H	16.15	16.59	17.13	17.57	18.82	18.71	19.15	19.69	20.13	21.38
	6H	16.47	16.82	17.46	17.82	19.08	19.18	19.53	20.17	20.53	21.79
	8H	16.54	16.85	17.53	17.84	19.14	19.34	19.66	20.34	20.64	21.95