

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936289

Luminaire Tested: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936289
REPORT IS A COMBINATION OF REPORTS P933445 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3751.9 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936289
CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P936289

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	39	35	32	29
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1875	1875	1875
5°	1832	2167	2520
10°	1660	3158	4178
15°	1410	4124	5046
20°	1148	4779	5143
25°	958	4999	5038
30°	807	5029	5028
35°	713	4944	5158
40°	621	4835	5293
45°	562	4754	5314
50°	515	4681	5225
55°	493	4575	4994
60°	505	4372	4628
65°	523	4064	4125
70°	557	3541	3486
75°	614	2886	2721
80°	664	1998	1832
85°	584	1059	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5314 cd/sqm



TEST NUMBER: P936289

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	1.0
10°-20°	173.8	4.6
20°-30°	304.0	8.1
30°-40°	391.3	10.4
40°-50°	437.1	11.6
50°-60°	418.6	11.2
60°-70°	331.7	8.8
70°-80°	195.1	5.2
80°-90°	55.0	1.5
90°-100°	105.7	2.8
100°-110°	278.0	7.4
110°-120°	288.2	7.7
120°-130°	231.2	6.2
130°-140°	181.4	4.8
140°-150°	139.2	3.7
150°-160°	100.3	2.7
160°-170°	61.4	1.6
170°-180°	20.7	0.6
0°-30°	517.0	13.8
0°-40°	908.3	24.2
0°-60°	1764.0	47.0
0°-90°	2345.8	62.5
90°-120°	671.9	17.9
90°-150°	1223.8	32.6
90°-180°	1406.0	37.5
0°-180°	3751.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	303	303	303	303	303	
5°	295	317	357	404	418	27
15°	221	408	688	834	861	62
25°	141	463	820	856	857	65
35°	96	442	772	816	848	60
45°	65	353	682	782	817	51
55°	47	224	579	672	691	43
65°	37	119	430	483	490	37
75°	27	73	236	259	260	29
85°	10	22	58	64	65	10
90°	2	4	11	6	6	2
95°	14	55	182	94	64	16
105°	50	76	307	467	435	53
115°	89	108	246	491	560	88
125°	124	139	224	378	446	110
135°	148	162	217	305	346	114
145°	171	182	214	261	281	107
155°	193	199	214	235	242	89
165°	209	211	214	223	225	59
175°	217	217	216	218	218	21
180°	217	217	217	217	217	



TEST NUMBER: P936289

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	303.1	303.1	303.1	303.1	303.1	303.1	303.1	303.1	303.1	303.1	303.1
2.5°	303.1	303.1	305.0	306.0	308.0	309.0	311.0	312.9	318.7	319.7	321.6
5°	295.4	299.2	311.9	316.8	330.4	348.9	356.7	369.4	395.7	403.5	408.4
7.5°	283.6	292.4	323.5	331.4	365.5	414.2	434.7	462.0	503.9	524.4	541.0
10°	265.1	283.6	339.2	357.8	413.3	487.3	525.4	563.4	626.7	654.9	665.7
12.5°	244.7	274.9	355.7	381.1	461.1	569.2	615.0	657.0	729.1	767.1	772.9
15°	221.2	262.2	371.3	408.4	511.7	637.4	688.1	739.8	807.1	834.3	841.2
17.5°	200.8	252.4	386.0	425.0	550.7	698.8	750.5	793.4	848.0	866.5	871.3
20°	175.5	236.8	395.7	446.4	591.7	743.7	793.4	826.6	863.6	875.3	877.2
22.5°	156.9	220.3	401.6	454.2	618.9	770.9	812.9	839.2	864.5	868.4	869.4
25°	141.4	201.7	400.6	463.0	642.4	787.5	819.7	839.2	853.8	855.7	855.7
27.5°	126.7	181.3	396.7	464.9	659.9	791.5	816.8	830.4	837.2	841.2	841.2
30°	114.1	161.8	386.9	461.1	667.6	787.5	808.0	814.8	821.6	827.5	830.4
32.5°	104.3	143.3	372.3	453.2	668.6	777.8	792.4	796.3	806.0	819.7	824.6
35°	95.5	124.8	355.7	442.5	662.8	762.2	771.9	775.9	795.4	815.8	822.6
37.5°	86.7	111.1	334.3	424.0	654.0	743.7	750.5	757.4	787.5	811.9	819.7
40°	78.0	99.4	309.0	403.5	640.4	721.2	727.1	737.8	777.8	806.0	813.9
42.5°	71.1	89.6	281.7	382.1	622.8	695.9	704.7	720.3	766.1	796.3	805.0
45°	65.3	79.9	252.4	352.8	600.4	669.6	682.3	703.7	752.4	781.7	789.4
47.5°	59.5	73.1	222.2	322.6	576.1	643.3	659.9	684.2	733.9	762.2	769.0
50°	54.6	66.3	192.1	290.4	549.7	615.0	634.5	659.9	710.6	736.8	745.6
52.5°	50.7	60.5	163.8	258.3	519.5	585.8	608.2	634.5	682.3	707.7	713.5
55°	46.8	55.5	139.3	224.1	488.3	554.6	579.0	604.3	651.1	672.5	676.5
57.5°	44.9	51.6	118.9	192.1	455.1	519.5	546.8	570.2	614.1	630.6	634.5
60°	42.0	48.7	103.3	164.7	419.1	486.3	509.8	533.1	570.2	583.8	586.7
62.5°	39.0	46.8	91.7	138.4	382.1	447.4	470.7	492.3	523.4	533.1	537.0
65°	37.0	44.9	82.8	118.9	344.1	406.4	429.8	448.4	473.6	483.4	485.4
67.5°	35.1	42.9	76.1	102.3	306.0	365.5	383.0	400.6	420.1	429.8	430.8
70°	32.2	40.9	70.2	90.6	267.1	318.7	333.3	351.8	367.4	372.3	375.3
72.5°	30.2	38.0	66.3	81.9	227.1	273.8	287.5	298.3	311.9	316.8	316.8
75°	27.3	34.1	62.4	73.1	186.1	224.1	235.9	246.6	257.3	259.3	256.3
77.5°	24.3	30.2	53.6	61.4	145.3	177.4	187.1	193.0	201.7	203.7	204.7
80°	20.4	26.4	42.0	47.8	105.2	130.6	137.4	142.3	150.1	150.1	152.0
82.5°	15.6	20.4	30.2	34.1	71.1	89.6	95.5	98.5	103.3	103.3	103.3
85°	9.8	12.7	19.5	22.4	42.9	54.6	58.5	59.5	63.4	64.3	64.3
87.5°	4.8	6.8	12.7	13.7	22.4	28.3	28.3	30.2	30.2	29.3	28.3
90°	1.5	2.6	3.8	4.1	6.4	9.5	11.0	9.8	7.4	5.5	5.5
92.5°	5.8	15.7	25.6	28.1	39.5	54.7	62.3	54.6	39.1	27.6	26.6
95°	14.0	32.1	50.2	54.7	97.2	153.8	182.1	162.5	123.3	93.9	90.6
97.5°	24.1	40.1	56.1	60.1	130.9	225.3	272.5	260.1	235.4	216.8	210.5
100°	32.1	46.5	61.0	64.6	143.2	248.0	300.3	301.2	303.0	304.4	296.8
102.5°	38.8	52.3	65.8	69.2	148.8	255.0	308.1	323.9	355.5	379.3	372.8
105°	50.1	61.5	73.0	75.9	153.0	255.8	307.3	342.6	413.5	466.6	463.1
107.5°	61.7	72.4	83.0	85.8	153.8	244.5	289.8	339.2	438.0	512.0	512.9
110°	69.6	79.3	88.9	91.3	152.6	234.4	275.3	330.5	440.9	523.6	527.2



TEST NUMBER: P936289

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	77.3	86.5	95.6	98.0	152.6	225.6	262.0	318.5	431.5	516.2	521.7
115°	89.0	97.5	105.9	108.0	154.1	215.4	246.1	300.6	409.4	491.0	498.7
117.5°	100.5	108.1	115.8	117.7	156.9	209.1	235.3	284.4	382.6	456.2	464.7
120°	107.2	114.4	121.6	123.5	159.3	207.1	230.9	275.8	365.5	432.9	441.2
122.5°	113.7	121.0	128.3	130.1	162.6	205.9	227.5	267.9	348.7	409.4	417.6
125°	123.7	130.4	137.1	138.8	167.2	205.0	223.9	258.2	326.9	378.4	386.0
127.5°	131.9	138.6	145.4	147.0	171.6	204.5	220.8	250.3	309.3	353.5	359.9
130°	136.2	143.5	150.7	152.5	174.9	204.7	219.7	245.9	298.4	337.7	343.6
132.5°	140.8	148.1	155.2	157.1	177.6	205.0	218.7	242.2	289.1	324.3	329.6
135°	147.5	154.1	160.7	162.3	180.5	204.8	217.0	236.6	276.0	305.4	310.0
137.5°	154.4	160.9	167.3	169.0	184.9	206.1	216.7	233.3	266.6	291.5	295.2
140°	160.0	166.0	172.0	173.5	187.6	206.3	215.6	229.9	258.7	280.2	283.7
142.5°	164.3	169.9	175.5	176.8	189.7	207.0	215.6	228.2	253.5	272.4	275.4
145°	171.0	175.9	180.7	182.0	192.7	207.0	214.1	224.4	245.1	260.6	262.8
147.5°	177.7	182.5	187.2	188.4	197.0	208.4	214.1	222.3	238.5	250.7	252.5
150°	182.1	186.3	190.7	191.8	199.2	209.2	214.1	221.0	234.7	245.0	246.5
152.5°	186.6	189.8	193.1	193.9	200.7	209.7	214.1	220.0	231.7	240.5	241.7
155°	193.3	195.7	198.2	198.7	203.9	210.8	214.1	218.8	228.1	235.1	235.9
157.5°	198.3	200.6	202.9	203.5	207.1	211.8	214.1	217.7	225.0	230.4	231.0
160°	201.6	203.5	205.2	205.7	208.5	212.3	214.1	217.2	223.5	228.1	228.4
162.5°	204.9	206.3	207.7	208.0	210.1	212.8	214.1	216.8	222.0	226.0	226.3
165°	208.6	209.8	211.0	211.3	212.3	213.6	214.1	216.0	219.8	222.6	222.9
167.5°	211.9	212.5	213.1	213.3	214.1	215.1	215.6	216.9	219.3	221.1	221.2
170°	214.1	214.7	215.3	215.4	215.5	215.6	215.6	216.9	219.3	221.1	221.1
172.5°	215.3	215.4	215.6	215.6	215.6	215.6	215.6	216.6	218.5	220.0	219.9
175°	217.0	217.0	217.0	217.0	216.5	215.9	215.6	216.2	217.4	218.4	218.4
177.5°	217.0	217.0	217.0	217.0	216.6	216.1	215.9	216.4	217.3	218.1	218.0
180°	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0



TEST NUMBER: P936289

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	303.1	303.1
2.5°	323.5	321.6
5°	416.2	418.1
7.5°	560.5	559.5
10°	696.9	705.6
12.5°	796.3	798.3
15°	856.8	860.7
17.5°	880.1	881.1
20°	881.1	879.2
22.5°	870.4	868.4
25°	857.8	856.8
27.5°	846.0	847.0
30°	841.2	844.1
32.5°	841.2	846.0
35°	843.1	848.0
37.5°	842.2	848.0
40°	838.2	845.1
42.5°	827.5	832.4
45°	811.0	816.8
47.5°	789.4	793.4
50°	762.2	766.1
52.5°	728.1	729.1
55°	687.1	691.1
57.5°	643.3	644.3
60°	594.6	597.5
62.5°	542.9	542.9
65°	488.3	490.2
67.5°	431.8	436.6
70°	374.3	375.3
72.5°	317.7	317.7
75°	259.3	260.3
77.5°	203.7	203.7
80°	151.1	152.0
82.5°	104.3	106.2
85°	65.3	65.3
87.5°	30.2	27.3
90°	5.5	5.5
92.5°	22.1	17.7
95°	77.2	64.0
97.5°	185.1	159.7
100°	266.7	236.4
102.5°	346.9	321.0
105°	449.2	435.3
107.5°	516.2	519.6
110°	541.8	556.3



TEST NUMBER: P936289

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	544.0	566.3
115°	529.6	560.5
117.5°	499.0	533.2
120°	474.4	507.7
122.5°	450.4	483.1
125°	416.1	446.3
127.5°	385.4	410.9
130°	367.2	390.7
132.5°	350.7	371.8
135°	328.1	346.3
137.5°	310.1	324.9
140°	297.6	311.5
142.5°	287.3	299.3
145°	271.9	281.0
147.5°	260.1	267.5
150°	252.6	258.7
152.5°	246.2	250.9
155°	238.9	242.0
157.5°	233.1	235.3
160°	229.7	230.9
162.5°	227.4	228.6
165°	224.1	225.4
167.5°	221.8	222.3
170°	221.1	221.1
172.5°	219.4	219.0
175°	218.4	218.4
177.5°	217.4	217.0
180°	217.0	217.0



TEST NUMBER: P936289

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-STD-W-6-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.25	5.29	5.08	6.15	7.23	17.42	18.45	18.25	19.31	20.39
	3H	4.97	5.90	5.81	6.77	7.88	19.26	20.20	20.11	21.07	22.17
	4H	5.27	6.16	6.14	7.04	8.15	19.91	20.80	20.77	21.67	22.79
	6H	5.53	6.35	6.41	7.24	8.36	20.35	21.17	21.22	22.05	23.18
	8H	5.61	6.39	6.49	7.29	8.42	20.47	21.25	21.35	22.15	23.28
	12H	5.63	6.37	6.52	7.27	8.43	20.54	21.29	21.43	22.18	23.34
4H	2H	11.48	12.36	12.34	13.24	14.35	17.71	18.60	18.58	19.47	20.59
	3H	13.06	13.80	13.94	14.71	15.84	19.77	20.51	20.65	21.42	22.55
	4H	13.16	13.84	14.06	14.75	15.90	20.54	21.22	21.43	22.12	23.28
	6H	13.19	13.77	14.09	14.70	15.86	21.08	21.67	21.99	22.60	23.76
	8H	13.17	13.72	14.08	14.64	15.81	21.25	21.80	22.16	22.72	23.89
	12H	13.13	13.63	14.06	14.57	15.75	21.35	21.84	22.28	22.79	23.96
8H	4H	14.62	15.17	15.53	16.10	17.27	20.61	21.16	21.52	22.09	23.26
	6H	14.87	15.33	15.81	16.29	17.46	21.25	21.70	22.18	22.67	23.84
	8H	14.89	15.30	15.84	16.25	17.44	21.47	21.87	22.41	22.83	24.02
	12H	14.87	15.23	15.82	16.18	17.41	21.62	21.97	22.57	22.92	24.16
12H	4H	14.77	15.27	15.70	16.21	17.39	20.58	21.07	21.51	22.02	23.19
	6H	15.13	15.54	16.08	16.49	17.68	21.23	21.64	22.18	22.60	23.78
	8H	15.21	15.57	16.16	16.52	17.75	21.47	21.83	22.42	22.78	24.01