

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936384

Luminaire Tested: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936384
REPORT IS A COMBINATION OF REPORTS P933438 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3269.3 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 30
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936384
CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P936384

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	102	97	93	89	96	92	88	85	82	79	77	74	71	69	66	64	62	58
2	92	84	77	71	87	79	73	68	71	66	62	64	60	57	57	54	51	48
3	83	73	65	58	79	69	62	56	62	56	51	56	51	47	50	46	43	39
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	40	36	33
5	69	57	48	41	65	54	46	40	49	42	37	44	38	34	39	34	31	28
6	64	51	42	35	60	48	40	34	43	37	32	39	33	29	35	30	27	24
7	59	45	37	31	55	43	35	30	39	32	27	35	30	25	32	27	23	21
8	54	41	33	27	51	39	31	26	36	29	24	32	26	22	29	24	21	18
9	51	37	29	24	48	36	28	23	32	26	21	29	24	20	26	22	18	16
10	47	34	26	21	45	33	25	21	30	23	19	27	22	18	24	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2797	2797	2797
5°	2729	3230	3759
10°	2473	4704	6232
15°	2099	6142	7524
20°	1707	7112	7668
25°	1422	7437	7513
30°	1198	7478	7499
35°	1058	7348	7692
40°	919	7181	7893
45°	831	7056	7923
50°	761	6943	7792
55°	726	6780	7447
60°	742	6473	6902
65°	767	6011	6152
70°	812	5232	5198
75°	889	4255	4056
80°	950	2940	2734
85°	803	1551	1398

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7923 cd/sqm



TEST NUMBER: P936384

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	1.2
10°-20°	172.8	5.3
20°-30°	302.2	9.2
30°-40°	389.0	11.9
40°-50°	434.5	13.3
50°-60°	416.2	12.7
60°-70°	329.8	10.1
70°-80°	193.9	5.9
80°-90°	54.4	1.7
90°-100°	70.5	2.2
100°-110°	185.3	5.7
110°-120°	192.2	5.9
120°-130°	154.1	4.7
130°-140°	120.9	3.7
140°-150°	92.8	2.8
150°-160°	66.8	2.0
160°-170°	40.9	1.3
170°-180°	13.8	0.4
0°-30°	514.0	15.7
0°-40°	903.0	27.6
0°-60°	1753.7	53.6
0°-90°	2331.9	71.3
90°-120°	448.0	13.7
90°-150°	815.9	25.0
90°-180°	937.0	28.7
0°-180°	3269.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	301	301	301	301	301	
5°	294	315	355	401	416	27
15°	220	406	684	830	856	61
25°	140	460	815	851	852	65
35°	95	440	767	811	843	59
45°	65	351	678	777	812	50
55°	46	223	576	669	687	42
65°	37	118	427	481	487	37
75°	27	73	234	258	259	28
85°	10	22	58	64	65	10
90°	1	3	7	4	4	1
95°	9	36	121	63	43	10
105°	33	51	205	311	290	35
115°	59	72	164	327	374	59
125°	82	92	149	252	298	73
135°	98	108	145	204	231	76
145°	114	121	143	174	187	71
155°	129	132	143	157	161	59
165°	139	141	143	148	150	39
175°	145	145	144	146	146	14
180°	145	145	145	145	145	



TEST NUMBER: P936384

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4
2.5°	301.4	301.4	303.3	304.3	306.2	307.2	309.1	311.0	316.9	317.8	319.8
5°	293.6	297.5	310.1	314.9	328.5	346.9	354.7	367.3	393.4	401.2	406.0
7.5°	282.0	290.7	321.7	329.5	363.4	411.8	432.2	459.3	501.0	521.3	537.8
10°	263.6	282.0	337.2	355.6	410.9	484.5	522.3	560.1	623.1	651.2	661.8
12.5°	243.2	273.3	353.7	378.9	458.3	565.9	611.4	653.1	724.8	762.6	768.4
15°	220.0	260.7	369.2	406.0	508.7	633.7	684.1	735.5	802.3	829.5	836.2
17.5°	199.6	251.0	383.7	422.5	547.5	694.8	746.1	788.8	843.0	861.4	866.3
20°	174.4	235.5	393.4	443.8	588.2	739.3	788.8	821.7	858.5	870.2	872.1
22.5°	156.0	219.0	399.2	451.6	615.3	766.5	808.1	834.3	859.5	863.4	864.3
25°	140.5	200.6	398.3	460.3	638.6	783.0	814.9	834.3	848.8	850.8	850.8
27.5°	126.0	180.2	394.4	462.2	656.0	786.8	812.0	825.6	832.4	836.2	836.2
30°	113.4	160.9	384.7	458.3	663.8	783.0	803.3	810.1	816.9	822.7	825.6
32.5°	103.7	142.4	370.2	450.6	664.7	773.3	787.8	791.7	801.4	814.9	819.8
35°	95.0	124.0	353.7	439.9	658.9	757.8	767.4	771.3	790.7	811.1	817.8
37.5°	86.2	110.5	332.4	421.5	650.2	739.3	746.1	752.9	783.0	807.2	814.9
40°	77.5	98.8	307.2	401.2	636.6	717.1	722.9	733.5	773.3	801.4	809.1
42.5°	70.7	89.1	280.0	379.8	619.2	691.9	700.6	716.1	761.6	791.7	800.4
45°	64.9	79.5	251.0	350.8	596.9	665.7	678.3	699.6	748.1	777.1	784.9
47.5°	59.1	72.7	220.9	320.7	572.7	639.5	656.0	680.2	729.7	757.8	764.5
50°	54.3	65.9	190.9	288.8	546.5	611.4	630.8	656.0	706.4	732.6	741.3
52.5°	50.4	60.1	162.8	256.8	516.5	582.4	604.7	630.8	678.3	703.5	709.3
55°	46.5	55.2	138.6	222.9	485.5	551.4	575.6	600.8	647.3	668.6	672.5
57.5°	44.6	51.4	118.2	190.9	452.5	516.5	543.6	566.9	610.5	626.9	630.8
60°	41.7	48.4	102.7	163.8	416.7	483.5	506.8	530.0	566.9	580.4	583.3
62.5°	38.8	46.5	91.1	137.6	379.8	444.8	468.0	489.3	520.4	530.0	533.9
65°	36.8	44.6	82.4	118.2	342.1	404.1	427.3	445.7	470.9	480.6	482.6
67.5°	34.9	42.6	75.6	101.7	304.3	363.4	380.8	398.3	417.6	427.3	428.3
70°	32.0	40.7	69.8	90.1	265.5	316.9	331.4	349.8	365.3	370.2	373.1
72.5°	30.0	37.8	65.9	81.4	225.8	272.3	285.9	296.5	310.1	314.9	314.9
75°	27.1	33.9	62.0	72.7	185.1	222.9	234.5	245.2	255.8	257.8	254.8
77.5°	24.2	30.0	53.3	61.0	144.4	176.4	186.0	191.9	200.6	202.5	203.5
80°	20.3	26.2	41.7	47.5	104.7	129.8	136.6	141.5	149.2	149.2	151.2
82.5°	15.5	20.3	30.0	33.9	70.7	89.1	95.0	97.9	102.7	102.7	102.7
85°	9.7	12.6	19.4	22.3	42.6	54.3	58.1	59.1	63.0	64.0	64.0
87.5°	4.8	6.8	12.6	13.6	22.3	28.1	28.1	30.0	30.0	29.1	28.1
90°	1.0	1.7	2.5	2.7	4.3	6.3	7.4	6.6	4.9	3.7	3.7
92.5°	3.9	10.5	17.1	18.7	26.4	36.5	41.6	36.4	26.2	18.4	17.6
95°	9.3	21.4	33.5	36.5	64.8	102.5	121.4	108.3	82.2	62.6	60.4
97.5°	16.1	26.7	37.4	40.1	87.3	150.2	181.7	173.5	156.9	144.5	140.2
100°	21.3	31.0	40.7	43.1	95.4	165.3	200.2	200.8	202.0	202.9	197.9
102.5°	25.8	34.8	43.9	46.1	99.2	170.1	205.4	216.0	237.0	252.8	248.5
105°	33.4	41.1	48.6	50.6	102.0	170.5	204.8	228.5	275.7	311.0	308.7
107.5°	41.2	48.3	55.4	57.2	102.5	163.0	193.2	226.2	292.0	341.4	342.0
110°	46.4	52.8	59.2	60.9	101.7	156.3	183.5	220.4	293.9	349.1	351.6



TEST NUMBER: P936384

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	51.6	57.7	63.8	65.3	101.7	150.4	174.7	212.4	287.7	344.2	347.9
115°	59.3	64.9	70.5	72.0	102.7	143.7	164.1	200.4	273.0	327.3	332.5
117.5°	67.0	72.1	77.2	78.5	104.7	139.4	156.9	189.6	255.0	304.2	309.9
120°	71.4	76.3	81.1	82.3	106.1	138.0	153.9	183.8	243.7	288.6	294.1
122.5°	75.8	80.6	85.5	86.7	108.3	137.2	151.6	178.6	232.5	272.9	278.3
125°	82.5	86.9	91.4	92.5	111.4	136.6	149.2	172.1	217.9	252.2	257.3
127.5°	87.9	92.4	96.9	98.1	114.4	136.2	147.2	166.9	206.2	235.7	239.9
130°	90.8	95.6	100.5	101.7	116.7	136.5	146.4	164.0	198.9	225.2	229.1
132.5°	93.9	98.7	103.6	104.7	118.4	136.6	145.7	161.4	192.7	216.3	219.8
135°	98.4	102.7	107.2	108.2	120.3	136.5	144.6	157.7	183.9	203.6	206.6
137.5°	102.9	107.3	111.6	112.7	123.3	137.3	144.4	155.4	177.6	194.3	196.8
140°	106.7	110.7	114.7	115.7	125.0	137.5	143.7	153.3	172.5	186.8	189.1
142.5°	109.6	113.3	117.0	117.9	126.6	138.0	143.7	152.1	169.0	181.6	183.6
145°	114.1	117.2	120.5	121.3	128.5	138.0	142.7	149.6	163.4	173.7	175.3
147.5°	118.5	121.6	124.8	125.6	131.3	139.0	142.7	148.2	159.0	167.2	168.4
150°	121.4	124.2	127.1	127.8	132.8	139.4	142.7	147.3	156.5	163.4	164.3
152.5°	124.4	126.6	128.7	129.3	133.7	139.7	142.7	146.6	154.5	160.4	161.1
155°	128.9	130.4	132.1	132.5	135.9	140.4	142.7	145.8	152.1	156.8	157.3
157.5°	132.2	133.7	135.3	135.7	138.0	141.2	142.7	145.2	150.0	153.6	154.0
160°	134.4	135.6	136.8	137.1	139.0	141.5	142.7	144.8	148.9	152.0	152.2
162.5°	136.6	137.5	138.5	138.7	140.0	141.9	142.7	144.5	148.0	150.6	150.8
165°	139.1	139.8	140.7	140.9	141.5	142.3	142.7	144.0	146.5	148.4	148.5
167.5°	141.3	141.7	142.1	142.2	142.6	143.3	143.7	144.5	146.1	147.4	147.5
170°	142.7	143.1	143.5	143.6	143.6	143.7	143.7	144.5	146.1	147.4	147.4
172.5°	143.5	143.6	143.7	143.7	143.7	143.7	143.7	144.4	145.6	146.6	146.5
175°	144.6	144.6	144.6	144.6	144.3	143.9	143.7	144.1	145.0	145.5	145.5
177.5°	144.6	144.6	144.6	144.6	144.4	144.1	143.9	144.2	144.9	145.4	145.3
180°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P936384

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	301.4	301.4
2.5°	321.7	319.8
5°	413.8	415.7
7.5°	557.2	556.2
10°	692.8	701.6
12.5°	791.7	793.6
15°	851.8	855.6
17.5°	875.0	876.0
20°	876.0	874.0
22.5°	865.3	863.4
25°	852.7	851.8
27.5°	841.1	842.1
30°	836.2	839.2
32.5°	836.2	841.1
35°	838.2	843.0
37.5°	837.2	843.0
40°	833.3	840.1
42.5°	822.7	827.5
45°	806.2	812.0
47.5°	784.9	788.8
50°	757.8	761.6
52.5°	723.8	724.8
55°	683.1	687.0
57.5°	639.5	640.5
60°	591.1	594.0
62.5°	539.7	539.7
65°	485.5	487.4
67.5°	429.3	434.1
70°	372.1	373.1
72.5°	315.9	315.9
75°	257.8	258.7
77.5°	202.5	202.5
80°	150.2	151.2
82.5°	103.7	105.6
85°	64.9	64.9
87.5°	30.0	27.1
90°	3.7	3.7
92.5°	14.7	11.8
95°	51.6	42.6
97.5°	123.4	106.5
100°	177.8	157.7
102.5°	231.2	214.0
105°	299.5	290.2
107.5°	344.2	346.4
110°	361.1	370.8



TEST NUMBER: P936384

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	362.7	377.5
115°	353.1	373.6
117.5°	332.7	355.5
120°	316.3	338.4
122.5°	300.2	322.1
125°	277.4	297.6
127.5°	256.9	273.8
130°	244.8	260.5
132.5°	233.8	247.9
135°	218.8	230.9
137.5°	206.7	216.7
140°	198.4	207.7
142.5°	191.6	199.5
145°	181.3	187.3
147.5°	173.4	178.4
150°	168.4	172.5
152.5°	164.1	167.2
155°	159.3	161.3
157.5°	155.4	156.9
160°	153.1	153.9
162.5°	151.6	152.3
165°	149.4	150.2
167.5°	147.8	148.2
170°	147.4	147.4
172.5°	146.2	145.9
175°	145.5	145.5
177.5°	145.0	144.6
180°	144.6	144.6



TEST NUMBER: P936384

CATALOG NUMBER: SQ4-FB-025U-075D-B2750-1D-UNV-STD-W-4-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.30	7.46	7.04	8.23	9.15	19.44	20.60	20.18	21.37	22.29
	3H	7.03	8.07	7.78	8.85	9.81	21.29	22.33	22.04	23.11	24.07
	4H	7.34	8.33	8.11	9.12	10.08	21.94	22.92	22.71	23.71	24.68
	6H	7.61	8.52	8.39	9.32	10.30	22.37	23.28	23.16	24.08	25.06
	8H	7.68	8.55	8.48	9.37	10.35	22.49	23.36	23.29	24.18	25.16
	12H	7.71	8.54	8.51	9.35	10.36	22.56	23.39	23.37	24.20	25.22
4H	2H	13.53	14.51	14.30	15.30	16.27	19.75	20.74	20.53	21.53	22.49
	3H	15.13	15.95	15.91	16.77	17.76	21.81	22.64	22.60	23.46	24.45
	4H	15.23	15.99	16.04	16.81	17.82	22.58	23.33	23.38	24.16	25.17
	6H	15.26	15.92	16.08	16.76	17.78	23.12	23.78	23.94	24.63	25.64
	8H	15.25	15.86	16.07	16.70	17.73	23.29	23.90	24.11	24.74	25.77
	12H	15.22	15.77	16.06	16.63	17.67	23.39	23.94	24.23	24.80	25.84
8H	4H	16.69	17.31	17.52	18.15	19.18	22.67	23.28	23.49	24.12	25.15
	6H	16.95	17.46	17.80	18.34	19.37	23.30	23.81	24.15	24.69	25.72
	8H	16.97	17.43	17.84	18.30	19.35	23.51	23.97	24.38	24.85	25.89
	12H	16.95	17.35	17.82	18.23	19.33	23.66	24.06	24.53	24.93	26.04
12H	4H	16.85	17.40	17.69	18.26	19.30	22.63	23.19	23.48	24.05	25.09
	6H	17.21	17.66	18.07	18.54	19.59	23.28	23.74	24.15	24.62	25.67
	8H	17.29	17.69	18.16	18.56	19.67	23.52	23.92	24.39	24.79	25.89