

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937879

Luminaire Tested: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937879
REPORT IS A COMBINATION OF REPORTS P933589 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19237.6 lumens
Efficiency: N/A
Efficacy: 134.7 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 142.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937879
CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P937879

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24			24
1	92	88	84	80	81	78	75	72	60	58	56	44	42	41	28	28	27	20			20
2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	23	22	16			16
3	76	66	59	54	67	59	53	48	46	42	38	33	30	28	22	20	19	13			13
4	69	58	51	45	61	52	46	41	40	36	32	29	26	24	19	17	16	11			11
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13	10			10
6	58	46	38	33	51	41	34	29	32	27	23	23	20	17	15	13	12	8			8
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10	7			7
8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9	6			6
9	46	34	27	22	40	30	24	20	24	19	16	17	14	12	11	9	8	6			6
10	42	31	24	19	38	28	21	17	22	17	14	16	13	10	10	9	7	5			5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1876	1876	1876
5°	1833	2168	2521
10°	1663	3161	4179
15°	1414	4132	5047
20°	1152	4789	5143
25°	961	5012	5039
30°	811	5046	5029
35°	717	4963	5159
40°	626	4856	5294
45°	567	4777	5315
50°	520	4707	5227
55°	499	4603	4995
60°	511	4404	4629
65°	533	4099	4126
70°	568	3577	3486
75°	633	2918	2720
80°	697	2027	1833
85°	632	1077	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 5568 cd/sqm



TEST NUMBER: P937879

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.4	0.4
10°-20°	347.6	1.8
20°-30°	608.1	3.2
30°-40°	782.8	4.1
40°-50°	874.3	4.5
50°-60°	837.4	4.4
60°-70°	663.6	3.4
70°-80°	390.2	2.0
80°-90°	117.0	0.6
90°-100°	1093.2	5.7
100°-110°	2874.0	14.9
110°-120°	2980.0	15.5
120°-130°	2390.3	12.4
130°-140°	1875.6	9.7
140°-150°	1439.6	7.5
150°-160°	1036.7	5.4
160°-170°	634.3	3.3
170°-180°	214.3	1.1
0°-30°	1034.2	5.4
0°-40°	1816.9	9.4
0°-60°	3528.6	18.3
0°-90°	4699.5	24.4
90°-120°	6947.2	36.1
90°-150°	12652.7	65.8
90°-180°	14538.0	75.6
0°-180°	19237.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	606	606	606	606	606	
5°	591	634	714	807	836	55
15°	443	817	1377	1669	1722	123
25°	283	926	1640	1712	1714	130
35°	191	885	1544	1632	1696	119
45°	131	706	1365	1564	1634	101
55°	94	448	1158	1345	1382	85
65°	74	238	860	967	981	73
75°	55	146	472	519	520	57
85°	20	45	117	129	131	21
90°	15	42	114	57	57	14
95°	144	566	1883	971	661	160
105°	518	784	3177	4824	4500	549
115°	920	1117	2545	5077	5795	908
125°	1279	1434	2315	3912	4615	1136
135°	1525	1678	2243	3158	3581	1180
145°	1768	1881	2214	2694	2905	1108
155°	1999	2054	2214	2431	2502	918
165°	2157	2185	2214	2301	2330	609
175°	2243	2243	2229	2258	2258	213
180°	2243	2243	2243	2243	2243	



TEST NUMBER: P937879

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4
2.5°	606.4	606.4	610.3	612.2	616.1	618.0	622.0	625.9	637.6	639.5	643.4
5°	590.8	598.6	623.9	633.6	661.0	698.0	713.6	739.0	791.6	807.2	817.0
7.5°	567.3	584.9	647.3	662.9	731.2	828.7	869.6	924.2	1008.1	1048.9	1082.1
10°	530.3	567.3	678.5	715.6	826.7	974.9	1050.9	1126.9	1253.7	1310.3	1331.7
12.5°	489.3	549.8	711.6	762.3	922.2	1138.7	1230.3	1314.2	1458.4	1534.5	1546.1
15°	442.6	524.5	742.8	817.0	1023.7	1275.1	1376.6	1479.9	1614.5	1669.0	1682.7
17.5°	401.7	504.9	772.1	850.1	1101.7	1398.0	1501.3	1587.1	1696.3	1733.3	1743.1
20°	351.0	473.8	791.6	893.0	1183.5	1487.7	1587.1	1653.4	1727.5	1750.9	1754.8
22.5°	314.0	440.6	803.3	908.6	1238.1	1542.3	1626.1	1678.8	1729.5	1737.2	1739.2
25°	282.8	403.6	801.4	926.2	1284.9	1575.4	1639.7	1678.8	1708.0	1711.9	1711.9
27.5°	253.5	362.7	793.5	930.0	1320.0	1583.2	1633.9	1661.2	1674.8	1682.7	1682.7
30°	228.1	323.6	774.0	922.2	1335.6	1575.4	1616.4	1630.1	1643.6	1655.3	1661.2
32.5°	208.6	286.6	744.8	906.6	1337.5	1555.9	1585.2	1592.9	1612.4	1639.7	1649.5
35°	191.1	249.6	711.6	885.2	1325.9	1524.7	1544.2	1552.0	1591.0	1632.0	1645.6
37.5°	173.5	222.3	668.8	848.2	1308.2	1487.7	1501.3	1514.9	1575.4	1624.1	1639.7
40°	156.0	198.8	618.0	807.2	1281.0	1442.8	1454.6	1476.0	1555.9	1612.4	1628.0
42.5°	142.3	179.4	563.5	764.3	1245.9	1392.2	1409.7	1440.9	1532.5	1592.9	1610.5
45°	130.6	159.9	504.9	705.8	1201.1	1339.4	1364.8	1407.8	1505.2	1563.7	1579.3
47.5°	118.9	146.2	444.6	645.4	1152.3	1286.8	1320.0	1368.7	1468.1	1524.7	1538.4
50°	109.2	132.6	384.1	581.0	1099.6	1230.3	1269.3	1320.0	1421.4	1474.0	1491.6
52.5°	101.4	120.9	327.5	516.7	1039.3	1171.8	1216.7	1269.3	1364.8	1415.5	1427.2
55°	93.6	111.1	278.8	448.5	976.8	1109.4	1158.1	1208.8	1302.4	1345.4	1353.1
57.5°	89.7	103.3	237.9	384.1	910.6	1039.3	1093.8	1140.6	1228.3	1261.5	1269.3
60°	83.8	97.5	206.7	329.6	838.4	973.0	1019.8	1066.5	1140.6	1167.9	1173.7
62.5°	78.0	93.6	183.2	276.8	764.3	895.0	941.8	984.6	1047.0	1066.5	1074.3
65°	74.1	89.7	165.7	237.9	688.3	813.1	859.9	896.9	947.6	967.1	970.9
67.5°	70.2	85.8	152.0	204.7	612.2	731.2	766.3	801.4	840.3	859.9	861.8
70°	64.3	81.9	140.4	181.3	534.2	637.6	666.9	703.9	735.1	744.8	750.7
72.5°	60.5	76.1	132.6	163.8	454.3	547.9	575.2	596.6	623.9	633.6	633.6
75°	54.6	68.2	124.8	146.2	372.4	448.5	471.8	493.3	514.7	518.6	512.8
77.5°	48.7	60.5	107.3	122.9	290.5	354.8	374.3	386.0	403.6	407.5	409.4
80°	41.0	52.6	83.8	95.5	210.6	261.2	274.9	284.7	300.3	300.3	304.2
82.5°	31.2	41.0	60.5	68.2	142.3	179.4	191.1	196.9	206.7	206.7	206.7
85°	19.5	25.4	39.0	44.9	85.8	109.2	117.0	118.9	126.7	128.7	128.7
87.5°	9.8	13.7	25.4	27.3	44.9	56.6	56.6	60.5	60.5	58.5	56.6
90°	15.0	27.0	39.1	42.2	66.2	98.3	114.3	101.6	76.3	57.2	57.2
92.5°	60.2	162.5	264.9	290.5	408.4	565.6	644.2	564.5	405.3	286.0	274.6
95°	144.5	331.8	519.1	565.9	1004.9	1590.2	1882.9	1680.1	1274.8	970.8	936.3
97.5°	249.8	415.0	580.3	621.6	1353.6	2329.6	2817.6	2689.5	2433.3	2241.1	2175.5
100°	331.1	481.0	630.8	668.3	1480.5	2563.6	3105.1	3114.5	3133.2	3147.2	3069.1
102.5°	400.4	540.2	679.9	714.9	1538.8	2637.1	3186.4	3349.5	3676.0	3920.9	3854.0
105°	517.7	636.1	754.6	784.2	1581.9	2645.5	3177.3	3543.1	4275.0	4823.9	4787.9
107.5°	638.2	748.6	858.9	886.5	1589.9	2527.8	2996.7	3507.1	4527.8	5293.5	5302.2
110°	719.5	819.1	918.8	943.7	1577.8	2423.4	2846.1	3416.8	4558.0	5413.9	5451.4



TEST NUMBER: P937879

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	799.2	894.2	989.2	1012.9	1578.3	2332.3	2709.2	3293.2	4461.2	5337.2	5394.7
115°	919.6	1007.2	1094.9	1116.8	1592.9	2227.7	2545.2	3107.8	4232.9	5076.8	5156.5
117.5°	1038.6	1118.1	1197.8	1217.6	1622.5	2162.3	2432.3	2940.0	3955.5	4717.0	4805.5
120°	1107.8	1182.7	1257.7	1276.4	1646.6	2140.3	2387.1	2851.1	3778.9	4474.7	4560.7
122.5°	1175.5	1251.1	1326.7	1345.6	1681.2	2128.8	2352.5	2770.3	3605.7	4232.4	4317.2
125°	1279.4	1348.3	1417.2	1434.4	1727.9	2119.2	2314.8	2669.7	3379.5	3911.8	3989.9
127.5°	1363.7	1433.2	1502.8	1520.2	1774.5	2113.7	2283.3	2587.9	3197.3	3654.4	3720.3
130°	1408.8	1483.7	1558.6	1577.3	1808.6	2117.1	2271.2	2542.5	3085.0	3491.9	3552.7
132.5°	1455.4	1530.3	1605.3	1624.0	1836.3	2119.2	2260.7	2503.5	2989.2	3353.4	3408.0
135°	1524.7	1592.9	1661.2	1678.2	1866.4	2117.3	2242.7	2446.0	2852.7	3157.8	3204.8
137.5°	1595.5	1663.0	1730.5	1747.4	1911.4	2130.2	2239.6	2411.6	2755.4	3013.2	3051.7
140°	1654.1	1716.3	1778.5	1794.1	1939.1	2132.4	2229.1	2377.5	2674.5	2897.3	2933.3
142.5°	1699.2	1756.8	1814.4	1828.7	1962.1	2140.1	2229.1	2359.5	2620.5	2816.1	2847.0
145°	1768.5	1818.7	1868.9	1881.4	1992.3	2140.1	2214.1	2320.8	2534.1	2694.1	2717.6
147.5°	1837.7	1886.5	1935.4	1947.6	2036.5	2154.9	2214.1	2298.0	2465.9	2591.8	2611.2
150°	1882.9	1927.1	1971.2	1982.3	2059.5	2162.5	2214.1	2285.0	2426.8	2533.1	2548.8
152.5°	1929.6	1963.0	1996.5	2004.9	2074.6	2167.6	2214.1	2274.6	2395.7	2486.5	2498.4
155°	1998.8	2023.6	2048.3	2054.5	2107.7	2178.6	2214.1	2262.2	2358.5	2430.7	2438.6
157.5°	2050.0	2074.0	2098.2	2104.2	2140.8	2189.6	2214.1	2251.5	2326.4	2382.6	2388.1
160°	2084.6	2103.3	2122.1	2126.8	2155.8	2194.7	2214.1	2246.1	2310.4	2358.5	2361.7
162.5°	2119.2	2133.3	2147.3	2150.8	2171.9	2200.0	2214.1	2241.2	2295.4	2336.0	2339.0
165°	2156.8	2169.5	2182.2	2185.4	2195.0	2207.7	2214.1	2233.4	2272.2	2301.3	2304.5
167.5°	2191.5	2197.5	2203.5	2205.0	2213.0	2223.8	2229.1	2241.8	2267.2	2286.3	2287.6
170°	2214.1	2220.1	2226.1	2227.5	2228.0	2228.7	2229.1	2241.8	2267.2	2286.3	2286.3
172.5°	2226.1	2227.4	2228.8	2229.1	2229.1	2229.1	2229.1	2239.2	2259.2	2274.2	2273.1
175°	2242.7	2242.7	2242.7	2242.7	2238.1	2232.1	2229.1	2235.5	2248.2	2257.7	2257.7
177.5°	2242.7	2242.7	2242.7	2242.7	2239.2	2234.4	2232.1	2237.1	2247.1	2254.7	2253.3
180°	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7



TEST NUMBER: P937879

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	606.4	606.4
2.5°	647.3	643.4
5°	832.6	836.4
7.5°	1121.1	1119.2
10°	1394.1	1411.6
12.5°	1592.9	1596.8
15°	1713.9	1721.6
17.5°	1760.7	1762.6
20°	1762.6	1758.7
22.5°	1741.1	1737.2
25°	1715.8	1713.9
27.5°	1692.4	1694.4
30°	1682.7	1688.5
32.5°	1682.7	1692.4
35°	1686.5	1696.3
37.5°	1684.6	1696.3
40°	1676.8	1690.4
42.5°	1655.3	1665.1
45°	1622.2	1633.9
47.5°	1579.3	1587.1
50°	1524.7	1532.5
52.5°	1456.5	1458.4
55°	1374.6	1382.4
57.5°	1286.8	1288.8
60°	1189.4	1195.2
62.5°	1086.1	1086.1
65°	976.8	980.7
67.5°	863.8	873.5
70°	748.7	750.7
72.5°	635.7	635.7
75°	518.6	520.5
77.5°	407.5	407.5
80°	302.2	304.2
82.5°	208.6	212.5
85°	130.6	130.6
87.5°	60.5	54.6
90°	57.2	57.2
92.5°	229.1	183.6
95°	798.6	660.8
97.5°	1913.3	1651.1
100°	2756.7	2444.3
102.5°	3586.4	3318.8
105°	4644.1	4500.3
107.5°	5337.0	5371.7
110°	5601.2	5751.0



TEST NUMBER: P937879

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5624.8	5854.9
115°	5475.6	5794.7
117.5°	5159.3	5513.2
120°	4904.5	5248.3
122.5°	4656.3	4995.5
125°	4302.3	4614.7
127.5°	3983.8	4247.4
130°	3796.3	4039.8
132.5°	3626.0	3844.0
135°	3392.7	3580.6
137.5°	3205.5	3359.4
140°	3077.2	3221.0
142.5°	2970.8	3094.5
145°	2811.2	2904.9
147.5°	2688.8	2766.4
150°	2611.7	2674.6
152.5°	2545.9	2593.3
155°	2470.1	2501.5
157.5°	2410.2	2432.3
160°	2374.4	2387.1
162.5°	2351.0	2363.0
165°	2317.2	2330.0
167.5°	2292.9	2298.3
170°	2286.3	2286.3
172.5°	2268.3	2263.7
175°	2257.7	2257.7
177.5°	2248.0	2242.7
180°	2242.7	2242.7



TEST NUMBER: P937879

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-STD-W-12-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.18	0.87	1.33	2.01	3.60	13.37	14.06	14.52	15.20	16.79
	3H	0.87	1.49	2.03	2.63	4.24	15.20	15.82	16.36	16.97	18.57
	4H	1.16	1.75	2.32	2.89	4.51	15.84	16.43	17.01	17.58	19.19
	6H	1.40	1.94	2.57	3.09	4.71	16.27	16.81	17.44	17.96	19.58
	8H	1.47	1.98	2.64	3.14	4.76	16.39	16.90	17.56	18.06	19.68
	12H	1.48	1.96	2.65	3.12	4.76	16.45	16.94	17.63	18.10	19.74
4H	2H	7.38	7.97	8.55	9.11	10.73	13.63	14.21	14.79	15.36	16.97
	3H	8.93	9.42	10.11	10.59	12.22	15.66	16.15	16.83	17.32	18.94
	4H	9.02	9.47	10.20	10.63	12.27	16.42	16.87	17.60	18.03	19.68
	6H	9.02	9.41	10.20	10.59	12.22	16.96	17.34	18.14	18.52	20.16
	8H	8.99	9.35	10.17	10.53	12.18	17.12	17.48	18.30	18.65	20.30
	12H	8.94	9.27	10.14	10.45	12.11	17.20	17.53	18.40	18.71	20.37
8H	4H	10.45	10.81	11.63	11.99	13.64	16.47	16.83	17.65	18.00	19.65
	6H	10.69	10.98	11.89	12.20	13.85	17.09	17.39	18.29	18.61	20.25
	8H	10.70	10.96	11.91	12.15	13.82	17.31	17.57	18.52	18.76	20.43
	12H	10.66	10.89	11.87	12.08	13.78	17.45	17.68	18.66	18.87	20.57
12H	4H	10.59	10.92	11.79	12.10	13.76	16.41	16.74	17.61	17.92	19.58
	6H	10.94	11.20	12.15	12.40	14.06	17.07	17.33	18.28	18.53	20.19
	8H	11.00	11.23	12.21	12.42	14.12	17.30	17.52	18.51	18.72	20.41