

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934080

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934080
REPORT IS A COMBINATION OF REPORTS P933681 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13147.5 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934080
CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79			79
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70	67			67
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59	56			56
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	47			47
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41			41
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38	35			35
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33	31			31
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30	27			27
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26	24			24
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24	22			22
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22	20			20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12376	12376	12376	12376
5°	12473	12493	12473	9823
10°	12394	12306	12394	8798
15°	12264	12039	12264	10053
20°	12012	11724	12012	10074
25°	11492	11263	11492	9860
30°	10818	10880	10818	9392
35°	9649	10396	9649	8877
40°	8045	9827	8045	8488
45°	7193	9160	7193	8040
50°	7647	8365	7647	7591
55°	7201	7509	7201	7331
60°	7433	6377	7433	6715
65°	6750	5272	6750	5893
70°	4685	4201	4685	4940
75°	4124	3106	4124	3719
80°	3347	2053	3347	2235
85°	1960	1087	1960	924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 11016 cd/sqm



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.2	2.7
10°-20°	1025.5	7.8
20°-30°	1585.2	12.1
30°-40°	1892.4	14.4
40°-50°	1903.5	14.5
50°-60°	1656.2	12.6
60°-70°	1174.3	8.9
70°-80°	621.3	4.7
80°-90°	156.4	1.2
90°-100°	208.4	1.6
100°-110°	547.9	4.2
110°-120°	568.1	4.3
120°-130°	455.7	3.5
130°-140°	357.6	2.7
140°-150°	274.5	2.1
150°-160°	197.7	1.5
160°-170°	120.9	0.9
170°-180°	40.9	0.3
0°-30°	2971.8	22.6
0°-40°	4864.2	37.0
0°-60°	8423.9	64.1
0°-90°	10375.8	78.9
90°-120°	1324.5	10.1
90°-150°	2412.2	18.3
90°-180°	2772.0	21.1
0°-180°	13147.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	4001	4001	4001	4001	4001	
5°	4020	4145	4020	3259	4020	381
15°	3838	4107	3838	3430	3838	1080
25°	3380	3831	3380	3354	3380	1552
35°	2570	3418	2570	2918	2570	1590
45°	1658	2816	1658	2472	1658	1328
55°	1351	2078	1351	2029	1351	1242
65°	939	1253	939	1401	939	897
75°	356	594	356	712	356	374
85°	60	151	60	129	60	82
90°	3	11	3	11	3	5
95°	28	126	28	126	28	31
105°	99	858	99	858	99	105
115°	175	1105	175	1105	175	173
125°	244	880	244	880	244	217
135°	291	683	291	683	291	225
145°	337	554	337	554	337	211
155°	381	477	381	477	381	175
165°	411	444	411	444	411	116
175°	428	430	428	430	428	41
180°	428	428	428	428	428	



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1
2.5°	4035.2	4035.2	4057.9	4065.4	4065.4	4054.1	4042.7	4054.1	4088.2	4099.5	4095.7
5°	4020.1	4050.3	4092.0	4099.5	4107.1	4103.3	4095.7	4103.3	4141.2	4148.7	4152.5
7.5°	3989.7	4046.5	4099.5	4110.9	4122.3	4110.9	4107.1	4114.7	4152.5	4160.1	4160.1
10°	3951.9	4031.4	4092.0	4099.5	4110.9	4099.5	4099.5	4114.7	4152.5	4160.1	4163.9
12.5°	3898.9	4008.7	4065.4	4073.1	4088.2	4084.3	4080.6	4095.7	4133.6	4141.2	4141.2
15°	3838.3	3967.1	4020.1	4027.6	4054.1	4046.5	4046.5	4061.7	4103.3	4114.7	4110.9
17.5°	3755.1	3914.1	3974.6	3986.0	4004.9	4001.1	4004.9	4020.1	4057.9	4065.4	4069.3
20°	3660.4	3842.2	3914.1	3925.4	3944.3	3944.3	3944.3	3963.2	4001.1	4016.3	4016.3
22.5°	3531.7	3766.4	3842.2	3849.7	3872.4	3872.4	3880.0	3906.4	3940.5	3944.3	3944.3
25°	3380.3	3683.1	3747.5	3770.2	3792.9	3804.2	3815.6	3830.8	3842.2	3838.3	3842.2
27.5°	3221.3	3577.1	3660.4	3675.6	3705.9	3717.2	3732.3	3736.2	3739.9	3751.2	3743.7
30°	3043.4	3429.5	3554.4	3569.6	3618.8	3626.3	3611.2	3618.8	3637.7	3645.3	3652.9
32.5°	2842.7	3209.9	3444.7	3478.7	3524.1	3501.4	3497.7	3509.1	3539.3	3539.3	3546.9
35°	2570.3	3039.7	3342.5	3372.8	3406.8	3380.3	3395.4	3399.2	3418.1	3429.5	3425.8
37.5°	2271.2	2892.0	3236.5	3259.2	3285.7	3251.6	3274.3	3285.7	3300.9	3293.2	3293.2
40°	2006.3	2661.1	3111.6	3126.7	3149.4	3122.9	3145.6	3153.2	3160.8	3153.2	3149.4
42.5°	1809.4	2407.5	2979.0	2998.0	2982.8	3001.8	3009.3	3024.5	3013.1	2998.0	2998.0
45°	1658.0	2339.4	2835.2	2857.9	2835.2	2865.5	2876.8	2876.8	2842.7	2835.2	2831.5
47.5°	1608.8	2203.1	2691.4	2691.4	2680.0	2717.8	2736.8	2710.3	2676.2	2664.9	2664.9
50°	1605.0	2051.6	2494.6	2479.4	2532.4	2577.8	2558.9	2532.4	2505.9	2464.3	2464.3
52.5°	1457.3	1866.2	2240.9	2297.7	2381.0	2407.5	2377.2	2350.7	2305.3	2286.4	2271.2
55°	1351.3	1673.2	2010.0	2123.5	2210.6	2244.7	2187.9	2161.5	2093.3	2081.9	2074.4
57.5°	1328.7	1393.0	1798.1	1941.9	2047.9	2044.1	2010.0	1960.8	1904.0	1892.7	1888.9
60°	1218.9	1006.9	1570.9	1741.3	1851.1	1839.7	1809.4	1764.0	1711.0	1703.4	1695.8
62.5°	1105.3	730.6	1313.5	1506.6	1661.8	1658.0	1631.5	1563.3	1525.5	1506.6	1491.4
65°	938.8	613.2	934.9	1253.0	1476.2	1483.9	1427.1	1377.9	1336.2	1313.5	1309.7
67.5°	715.4	499.7	632.1	1044.8	1298.4	1290.8	1218.9	1196.1	1143.1	1131.8	1109.1
70°	529.9	333.1	439.1	847.9	1124.2	1105.3	1048.5	1022.0	972.9	946.3	931.2
72.5°	439.1	268.7	321.7	658.7	946.3	923.6	874.4	844.1	802.5	779.8	764.7
75°	355.8	283.9	246.0	488.3	768.4	753.3	707.8	677.6	643.5	613.2	617.0
77.5°	261.2	265.0	196.8	359.7	609.5	586.8	560.2	522.4	507.2	476.9	476.9
80°	196.8	208.2	147.6	246.0	439.1	439.1	416.4	389.9	363.4	348.3	348.3
82.5°	132.5	132.5	109.7	155.2	299.0	287.6	272.6	265.0	249.8	242.3	242.3
85°	60.5	75.7	68.1	94.6	162.7	170.4	170.4	162.7	159.0	151.4	155.2
87.5°	18.9	34.1	41.6	53.0	83.3	87.1	90.8	90.8	90.8	94.6	94.6
90°	2.9	5.2	7.4	8.0	12.6	18.7	21.8	19.4	14.5	10.9	10.9
92.5°	11.5	30.9	50.5	55.4	77.8	107.8	122.8	107.6	77.3	54.5	52.3
95°	27.5	63.2	98.9	107.9	191.6	303.2	359.0	320.3	243.0	185.1	178.5
97.5°	47.7	79.2	110.7	118.5	258.0	444.2	537.2	512.7	463.9	427.3	414.8
100°	63.1	91.7	120.2	127.4	282.3	488.8	592.0	593.8	597.4	600.0	585.1
102.5°	76.3	102.9	129.6	136.3	293.4	502.8	607.5	638.6	700.8	747.5	734.7
105°	98.7	121.3	143.8	149.5	301.6	504.3	605.8	675.5	815.0	919.7	912.8
107.5°	121.7	142.7	163.8	169.0	303.1	481.9	571.3	668.6	863.2	1009.2	1010.9
110°	137.1	156.1	175.1	179.9	300.8	462.0	542.6	651.4	869.0	1032.2	1039.3



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	152.4	170.5	188.6	193.1	300.9	444.6	516.6	627.9	850.5	1017.6	1028.5
115°	175.3	192.1	208.8	213.0	303.7	424.7	485.2	592.5	807.0	967.9	983.1
117.5°	198.0	213.2	228.3	232.2	309.3	412.3	463.7	560.6	754.2	899.3	916.2
120°	211.2	225.5	239.8	243.3	313.9	408.0	455.1	543.5	720.5	853.1	869.5
122.5°	224.1	238.6	252.9	256.5	320.5	405.8	448.5	528.1	687.4	806.9	823.0
125°	243.9	257.1	270.3	273.5	329.5	404.1	441.3	508.9	644.2	745.8	760.7
127.5°	260.0	273.2	286.5	289.8	338.4	403.0	435.3	493.4	609.6	696.7	709.3
130°	268.5	282.9	297.2	300.7	344.9	403.6	433.0	484.8	588.2	665.7	677.4
132.5°	277.5	291.8	306.1	309.6	350.1	404.1	431.0	477.3	569.9	639.4	649.8
135°	290.7	303.7	316.7	319.9	355.8	403.7	427.6	466.3	543.9	602.0	611.0
137.5°	304.2	317.1	329.9	333.1	364.4	406.2	427.0	459.7	525.2	574.4	581.8
140°	315.3	327.2	339.1	342.1	369.7	406.5	425.0	453.2	509.9	552.4	559.2
142.5°	323.9	334.9	345.9	348.7	374.1	408.0	425.0	449.8	499.6	536.9	542.8
145°	337.2	346.8	356.3	358.7	379.8	408.0	422.1	442.5	483.1	513.6	518.1
147.5°	350.4	359.7	369.0	371.3	388.2	410.8	422.1	438.2	470.1	494.1	497.8
150°	359.0	367.4	375.8	377.9	392.6	412.3	422.1	435.7	462.7	482.9	485.9
152.5°	367.9	374.3	380.6	382.2	395.5	413.2	422.1	433.7	456.8	474.1	476.4
155°	381.0	385.7	390.5	391.6	401.8	415.3	422.1	431.3	449.7	463.5	465.0
157.5°	390.8	395.4	400.0	401.2	408.2	417.4	422.1	429.3	443.5	454.2	455.2
160°	397.5	401.0	404.6	405.5	411.0	418.4	422.1	428.2	440.4	449.6	450.2
162.5°	404.1	406.7	409.4	410.1	414.1	419.4	422.1	427.3	437.6	445.3	445.9
165°	411.2	413.6	416.1	416.7	418.5	420.9	422.1	425.8	433.2	438.7	439.3
167.5°	417.8	419.0	420.1	420.4	421.9	423.9	425.0	427.4	432.2	435.9	436.1
170°	422.1	423.3	424.4	424.7	424.8	424.9	425.0	427.4	432.2	435.9	435.9
172.5°	424.4	424.7	424.9	425.0	425.0	425.0	425.0	426.9	430.7	433.6	433.4
175°	427.6	427.6	427.6	427.6	426.7	425.5	425.0	426.2	428.6	430.4	430.4
177.5°	427.6	427.6	427.6	427.6	426.9	426.0	425.5	426.5	428.4	429.8	429.6
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1
2.5°	4103.3	4092.0	4103.3	4095.7	4099.5	4088.2	4054.1	4042.7	4054.1	4065.4	4065.4
5°	4152.5	4145.0	4152.5	4152.5	4148.7	4141.2	4103.3	4095.7	4103.3	4107.1	4099.5
7.5°	4167.6	4156.4	4167.6	4160.1	4160.1	4152.5	4114.7	4107.1	4110.9	4122.3	4110.9
10°	4167.6	4156.4	4167.6	4163.9	4160.1	4152.5	4114.7	4099.5	4099.5	4110.9	4099.5
12.5°	4148.7	4141.2	4148.7	4141.2	4141.2	4133.6	4095.7	4080.6	4084.3	4088.2	4073.1
15°	4118.4	4107.1	4118.4	4110.9	4114.7	4103.3	4061.7	4046.5	4046.5	4054.1	4027.6
17.5°	4073.1	4057.9	4073.1	4069.3	4065.4	4057.9	4020.1	4004.9	4001.1	4004.9	3986.0
20°	4020.1	4008.7	4020.1	4016.3	4016.3	4001.1	3963.2	3944.3	3944.3	3944.3	3925.4
22.5°	3936.8	3925.4	3936.8	3944.3	3944.3	3940.5	3906.4	3880.0	3872.4	3872.4	3849.7
25°	3842.2	3830.8	3842.2	3842.2	3838.3	3842.2	3830.8	3815.6	3804.2	3792.9	3770.2
27.5°	3751.2	3743.7	3751.2	3743.7	3751.2	3739.9	3736.2	3732.3	3717.2	3705.9	3675.6
30°	3660.4	3652.9	3660.4	3652.9	3645.3	3637.7	3618.8	3611.2	3626.3	3618.8	3569.6
32.5°	3546.9	3539.3	3546.9	3546.9	3539.3	3539.3	3509.1	3497.7	3501.4	3524.1	3478.7
35°	3429.5	3418.1	3429.5	3425.8	3429.5	3418.1	3399.2	3395.4	3380.3	3406.8	3372.8
37.5°	3293.2	3281.9	3293.2	3293.2	3293.2	3300.9	3285.7	3274.3	3251.6	3285.7	3259.2
40°	3153.2	3138.0	3153.2	3149.4	3153.2	3160.8	3153.2	3145.6	3122.9	3149.4	3126.7
42.5°	2994.2	2990.4	2994.2	2998.0	2998.0	3013.1	3024.5	3009.3	3001.8	2982.8	2998.0
45°	2823.8	2816.3	2823.8	2831.5	2835.2	2842.7	2876.8	2876.8	2865.5	2835.2	2857.9
47.5°	2642.2	2623.3	2642.2	2664.9	2664.9	2676.2	2710.3	2736.8	2717.8	2680.0	2691.4
50°	2449.1	2452.9	2449.1	2464.3	2464.3	2505.9	2532.4	2558.9	2577.8	2532.4	2479.4
52.5°	2259.8	2256.1	2259.8	2271.2	2286.4	2305.3	2350.7	2377.2	2407.5	2381.0	2297.7
55°	2070.5	2078.2	2070.5	2074.4	2081.9	2093.3	2161.5	2187.9	2244.7	2210.6	2123.5
57.5°	1881.4	1870.0	1881.4	1888.9	1892.7	1904.0	1960.8	2010.0	2044.1	2047.9	1941.9
60°	1661.8	1646.6	1661.8	1695.8	1703.4	1711.0	1764.0	1809.4	1839.7	1851.1	1741.3
62.5°	1468.7	1442.2	1468.7	1491.4	1506.6	1525.5	1563.3	1631.5	1658.0	1661.8	1506.6
65°	1264.3	1253.0	1264.3	1309.7	1313.5	1336.2	1377.9	1427.1	1483.9	1476.2	1253.0
67.5°	1078.9	1078.9	1078.9	1109.1	1131.8	1143.1	1196.1	1218.9	1290.8	1298.4	1044.8
70°	908.5	904.7	908.5	931.2	946.3	972.9	1022.0	1048.5	1105.3	1124.2	847.9
72.5°	745.8	741.9	745.8	764.7	779.8	802.5	844.1	874.4	923.6	946.3	658.7
75°	601.8	594.3	601.8	617.0	613.2	643.5	677.6	707.8	753.3	768.4	488.3
77.5°	461.8	461.8	461.8	476.9	476.9	507.2	522.4	560.2	586.8	609.5	359.7
80°	344.5	340.6	344.5	348.3	348.3	363.4	389.9	416.4	439.1	439.1	246.0
82.5°	242.3	234.6	242.3	242.3	242.3	249.8	265.0	272.6	287.6	299.0	155.2
85°	151.4	151.4	151.4	155.2	151.4	159.0	162.7	170.4	170.4	162.7	94.6
87.5°	98.5	94.6	98.5	94.6	94.6	90.8	90.8	90.8	87.1	83.3	53.0
90°	10.9	10.9	10.9	10.9	10.9	14.5	19.4	21.8	18.7	12.6	8.0
92.5°	43.7	35.0	43.7	52.3	54.5	77.3	107.6	122.8	107.8	77.8	55.4
95°	152.2	126.0	152.2	178.5	185.1	243.0	320.3	359.0	303.2	191.6	107.9
97.5°	364.8	314.8	364.8	414.8	427.3	463.9	512.7	537.2	444.2	258.0	118.5
100°	525.6	466.0	525.6	585.1	600.0	597.4	593.8	592.0	488.8	282.3	127.4
102.5°	683.7	632.7	683.7	734.7	747.5	700.8	638.6	607.5	502.8	293.4	136.3
105°	885.4	858.0	885.4	912.8	919.7	815.0	675.5	605.8	504.3	301.6	149.5
107.5°	1017.6	1024.1	1017.6	1010.9	1009.2	863.2	668.6	571.3	481.9	303.1	169.0
110°	1067.9	1096.4	1067.9	1039.3	1032.2	869.0	651.4	542.6	462.0	300.8	179.9



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1072.4	1116.2	1072.4	1028.5	1017.6	850.5	627.9	516.6	444.6	300.9	193.1
115°	1043.9	1104.7	1043.9	983.1	967.9	807.0	592.5	485.2	424.7	303.7	213.0
117.5°	983.6	1051.1	983.6	916.2	899.3	754.2	560.6	463.7	412.3	309.3	232.2
120°	935.0	1000.6	935.0	869.5	853.1	720.5	543.5	455.1	408.0	313.9	243.3
122.5°	887.8	952.4	887.8	823.0	806.9	687.4	528.1	448.5	405.8	320.5	256.5
125°	820.2	879.7	820.2	760.7	745.8	644.2	508.9	441.3	404.1	329.5	273.5
127.5°	759.5	809.7	759.5	709.3	696.7	609.6	493.4	435.3	403.0	338.4	289.8
130°	723.8	770.2	723.8	677.4	665.7	588.2	484.8	433.0	403.6	344.9	300.7
132.5°	691.3	732.9	691.3	649.8	639.4	569.9	477.3	431.0	404.1	350.1	309.6
135°	646.8	682.6	646.8	611.0	602.0	543.9	466.3	427.6	403.7	355.8	319.9
137.5°	611.1	640.5	611.1	581.8	574.4	525.2	459.7	427.0	406.2	364.4	333.1
140°	586.7	614.1	586.7	559.2	552.4	509.9	453.2	425.0	406.5	369.7	342.1
142.5°	566.4	590.0	566.4	542.8	536.9	499.6	449.8	425.0	408.0	374.1	348.7
145°	535.9	553.8	535.9	518.1	513.6	483.1	442.5	422.1	408.0	379.8	358.7
147.5°	512.6	527.4	512.6	497.8	494.1	470.1	438.2	422.1	410.8	388.2	371.3
150°	497.9	509.9	497.9	485.9	482.9	462.7	435.7	422.1	412.3	392.6	377.9
152.5°	485.3	494.4	485.3	476.4	474.1	456.8	433.7	422.1	413.2	395.5	382.2
155°	470.9	476.9	470.9	465.0	463.5	449.7	431.3	422.1	415.3	401.8	391.6
157.5°	459.5	463.7	459.5	455.2	454.2	443.5	429.3	422.1	417.4	408.2	401.2
160°	452.7	455.1	452.7	450.2	449.6	440.4	428.2	422.1	418.4	411.0	405.5
162.5°	448.2	450.5	448.2	445.9	445.3	437.6	427.3	422.1	419.4	414.1	410.1
165°	441.8	444.2	441.8	439.3	438.7	433.2	425.8	422.1	420.9	418.5	416.7
167.5°	437.1	438.2	437.1	436.1	435.9	432.2	427.4	425.0	423.9	421.9	420.4
170°	435.9	435.9	435.9	435.9	435.9	432.2	427.4	425.0	424.9	424.8	424.7
172.5°	432.4	431.6	432.4	433.4	433.6	430.7	426.9	425.0	425.0	425.0	425.0
175°	430.4	430.4	430.4	430.4	430.4	428.6	426.2	425.0	425.5	426.7	427.6
177.5°	428.6	427.6	428.6	429.6	429.8	428.4	426.5	425.5	426.0	426.9	427.6
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1
2.5°	4057.9	4035.2	4035.2	3997.3	3982.2	3970.8	3951.9	3895.2	3880.0	3864.8	3887.5
5°	4092.0	4050.3	4020.1	3951.9	3895.2	3872.4	3800.5	3664.2	3573.3	3505.2	3467.4
7.5°	4099.5	4046.5	3989.7	3883.8	3747.5	3687.0	3467.4	3217.6	3149.4	3088.9	3050.9
10°	4092.0	4031.4	3951.9	3792.9	3471.1	3365.1	3145.6	2982.8	2941.2	2929.8	2941.2
12.5°	4065.4	4008.7	3898.9	3634.0	3183.5	3111.6	2982.8	2888.2	2880.7	2899.6	3001.8
15°	4020.1	3967.1	3838.3	3422.0	3024.5	2971.5	2880.7	2846.6	2888.2	3020.7	3327.3
17.5°	3974.6	3914.1	3755.1	3213.8	2903.4	2865.5	2801.1	2869.3	3103.9	3281.9	3384.1
20°	3914.1	3842.2	3660.4	3062.3	2816.3	2782.2	2751.9	3058.6	3236.5	3300.9	3357.6
22.5°	3842.2	3766.4	3531.7	2956.4	2725.5	2698.9	2717.8	3164.6	3236.5	3281.9	3331.1
25°	3747.5	3683.1	3380.3	2873.1	2653.6	2623.3	2695.2	3153.2	3194.9	3206.2	3304.6
27.5°	3660.4	3577.1	3221.3	2797.4	2566.5	2555.1	2714.1	3103.9	3134.3	3145.6	3251.6
30°	3554.4	3429.5	3043.4	2717.8	2475.6	2471.8	2717.8	3043.4	3035.8	3066.1	3172.1
32.5°	3444.7	3209.9	2842.7	2619.5	2388.6	2384.7	2691.4	2952.6	2945.0	2986.7	3066.1
35°	3342.5	3039.7	2570.3	2505.9	2278.8	2282.5	2627.0	2846.6	2850.4	2888.2	2937.4
37.5°	3236.5	2892.0	2271.2	2381.0	2172.8	2172.8	2539.9	2748.2	2740.6	2751.9	2820.1
40°	3111.6	2661.1	2006.3	2218.2	2074.4	2063.0	2434.0	2642.2	2615.6	2611.9	2706.6
42.5°	2979.0	2407.5	1809.4	2002.4	1960.8	1945.6	2305.3	2513.5	2464.3	2475.6	2596.7
45°	2835.2	2339.4	1658.0	1692.1	1843.4	1832.1	2165.2	2365.8	2331.7	2362.1	2487.0
47.5°	2691.4	2203.1	1608.8	1404.3	1718.5	1714.8	2010.0	2222.0	2203.1	2233.4	2365.8
50°	2494.6	2051.6	1605.0	1203.8	1578.5	1593.6	1824.5	2081.9	2081.9	2108.4	2248.5
52.5°	2240.9	1866.2	1457.3	1090.1	1415.7	1461.1	1661.8	1960.8	1968.4	1994.9	2119.8
55°	2010.0	1673.2	1351.3	1003.1	1222.7	1321.1	1502.8	1835.9	1851.1	1877.5	1991.1
57.5°	1798.1	1393.0	1328.7	900.9	1044.8	1139.4	1362.7	1714.8	1722.3	1745.1	1854.8
60°	1570.9	1006.9	1218.9	791.1	889.6	961.5	1234.1	1570.9	1597.4	1612.5	1707.2
62.5°	1313.5	730.6	1105.3	715.4	813.9	829.0	1128.0	1434.6	1468.7	1480.1	1536.9
65°	934.9	613.2	938.8	651.1	734.4	738.1	1014.5	1294.6	1324.9	1343.8	1385.4
67.5°	632.1	499.7	715.4	590.5	673.8	677.6	904.7	1131.8	1173.4	1188.6	1215.1
70°	439.1	333.1	529.9	526.2	605.7	613.2	787.4	984.2	1022.0	1033.4	1048.5
72.5°	321.7	268.7	439.1	473.2	533.7	541.3	666.2	817.7	855.5	866.9	874.4
75°	246.0	283.9	355.8	412.6	454.2	458.0	545.1	666.2	692.8	700.3	704.0
77.5°	196.8	265.0	261.2	333.1	370.9	363.4	427.7	514.8	537.5	537.5	537.5
80°	147.6	208.2	196.8	238.5	272.6	265.0	306.7	367.2	374.7	382.3	378.6
82.5°	109.7	132.5	132.5	151.4	181.7	174.1	204.4	238.5	238.5	238.5	246.0
85°	68.1	75.7	60.5	79.5	102.2	98.5	113.5	128.7	132.5	132.5	124.9
87.5°	41.6	34.1	18.9	30.3	45.5	45.5	53.0	56.8	53.0	53.0	53.0
90°	7.4	5.2	2.9	5.2	7.4	8.0	12.6	18.7	21.8	19.4	14.5
92.5°	50.5	30.9	11.5	30.9	50.5	55.4	77.8	107.8	122.8	107.6	77.3
95°	98.9	63.2	27.5	63.2	98.9	107.9	191.6	303.2	359.0	320.3	243.0
97.5°	110.7	79.2	47.7	79.2	110.7	118.5	258.0	444.2	537.2	512.7	463.9
100°	120.2	91.7	63.1	91.7	120.2	127.4	282.3	488.8	592.0	593.8	597.4
102.5°	129.6	102.9	76.3	102.9	129.6	136.3	293.4	502.8	607.5	638.6	700.8
105°	143.8	121.3	98.7	121.3	143.8	149.5	301.6	504.3	605.8	675.5	815.0
107.5°	163.8	142.7	121.7	142.7	163.8	169.0	303.1	481.9	571.3	668.6	863.2
110°	175.1	156.1	137.1	156.1	175.1	179.9	300.8	462.0	542.6	651.4	869.0



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	188.6	170.5	152.4	170.5	188.6	193.1	300.9	444.6	516.6	627.9	850.5
115°	208.8	192.1	175.3	192.1	208.8	213.0	303.7	424.7	485.2	592.5	807.0
117.5°	228.3	213.2	198.0	213.2	228.3	232.2	309.3	412.3	463.7	560.6	754.2
120°	239.8	225.5	211.2	225.5	239.8	243.3	313.9	408.0	455.1	543.5	720.5
122.5°	252.9	238.6	224.1	238.6	252.9	256.5	320.5	405.8	448.5	528.1	687.4
125°	270.3	257.1	243.9	257.1	270.3	273.5	329.5	404.1	441.3	508.9	644.2
127.5°	286.5	273.2	260.0	273.2	286.5	289.8	338.4	403.0	435.3	493.4	609.6
130°	297.2	282.9	268.5	282.9	297.2	300.7	344.9	403.6	433.0	484.8	588.2
132.5°	306.1	291.8	277.5	291.8	306.1	309.6	350.1	404.1	431.0	477.3	569.9
135°	316.7	303.7	290.7	303.7	316.7	319.9	355.8	403.7	427.6	466.3	543.9
137.5°	329.9	317.1	304.2	317.1	329.9	333.1	364.4	406.2	427.0	459.7	525.2
140°	339.1	327.2	315.3	327.2	339.1	342.1	369.7	406.5	425.0	453.2	509.9
142.5°	345.9	334.9	323.9	334.9	345.9	348.7	374.1	408.0	425.0	449.8	499.6
145°	356.3	346.8	337.2	346.8	356.3	358.7	379.8	408.0	422.1	442.5	483.1
147.5°	369.0	359.7	350.4	359.7	369.0	371.3	388.2	410.8	422.1	438.2	470.1
150°	375.8	367.4	359.0	367.4	375.8	377.9	392.6	412.3	422.1	435.7	462.7
152.5°	380.6	374.3	367.9	374.3	380.6	382.2	395.5	413.2	422.1	433.7	456.8
155°	390.5	385.7	381.0	385.7	390.5	391.6	401.8	415.3	422.1	431.3	449.7
157.5°	400.0	395.4	390.8	395.4	400.0	401.2	408.2	417.4	422.1	429.3	443.5
160°	404.6	401.0	397.5	401.0	404.6	405.5	411.0	418.4	422.1	428.2	440.4
162.5°	409.4	406.7	404.1	406.7	409.4	410.1	414.1	419.4	422.1	427.3	437.6
165°	416.1	413.6	411.2	413.6	416.1	416.7	418.5	420.9	422.1	425.8	433.2
167.5°	420.1	419.0	417.8	419.0	420.1	420.4	421.9	423.9	425.0	427.4	432.2
170°	424.4	423.3	422.1	423.3	424.4	424.7	424.8	424.9	425.0	427.4	432.2
172.5°	424.9	424.7	424.4	424.7	424.9	425.0	425.0	425.0	425.0	426.9	430.7
175°	427.6	427.6	427.6	427.6	427.6	427.6	426.7	425.5	425.0	426.2	428.6
177.5°	427.6	427.6	427.6	427.6	427.6	427.6	426.9	426.0	425.5	426.5	428.4
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P934080
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1	4001.1
2.5°	3861.1	3849.7	3864.8	3823.2	3864.8	3849.7	3861.1	3887.5	3864.8	3880.0	3895.2
5°	3387.9	3369.0	3308.4	3259.2	3308.4	3369.0	3387.9	3467.4	3505.2	3573.3	3664.2
7.5°	3028.3	3013.1	2998.0	2967.7	2998.0	3013.1	3028.3	3050.9	3088.9	3149.4	3217.6
10°	2948.8	2952.6	2975.3	2971.5	2975.3	2952.6	2948.8	2941.2	2929.8	2941.2	2982.8
12.5°	3153.2	3187.2	3312.1	3304.6	3312.1	3187.2	3153.2	3001.8	2899.6	2880.7	2888.2
15°	3387.9	3399.2	3425.8	3429.5	3425.8	3399.2	3387.9	3327.3	3020.7	2888.2	2846.6
17.5°	3410.6	3414.4	3433.3	3433.3	3433.3	3414.4	3410.6	3384.1	3281.9	3103.9	2869.3
20°	3391.7	3399.2	3437.0	3444.7	3437.0	3399.2	3391.7	3357.6	3300.9	3236.5	3058.6
22.5°	3384.1	3399.2	3429.5	3425.8	3429.5	3399.2	3384.1	3331.1	3281.9	3236.5	3164.6
25°	3346.2	3346.2	3350.0	3353.8	3350.0	3346.2	3346.2	3304.6	3206.2	3194.9	3153.2
27.5°	3266.8	3274.3	3297.0	3293.2	3297.0	3274.3	3266.8	3251.6	3145.6	3134.3	3103.9
30°	3194.9	3187.2	3168.3	3153.2	3168.3	3187.2	3194.9	3172.1	3066.1	3035.8	3043.4
32.5°	3073.7	3054.8	3035.8	3024.5	3035.8	3054.8	3073.7	3066.1	2986.7	2945.0	2952.6
35°	2929.8	2933.7	2929.8	2918.5	2929.8	2933.7	2929.8	2937.4	2888.2	2850.4	2846.6
37.5°	2827.7	2835.2	2831.5	2816.3	2831.5	2835.2	2827.7	2820.1	2751.9	2740.6	2748.2
40°	2721.7	2725.5	2721.7	2710.3	2721.7	2725.5	2721.7	2706.6	2611.9	2615.6	2642.2
42.5°	2619.5	2615.6	2604.3	2596.7	2604.3	2615.6	2619.5	2596.7	2475.6	2464.3	2513.5
45°	2502.1	2505.9	2483.2	2471.8	2483.2	2505.9	2502.1	2487.0	2362.1	2331.7	2365.8
47.5°	2384.7	2384.7	2365.8	2354.5	2365.8	2384.7	2384.7	2365.8	2233.4	2203.1	2222.0
50°	2259.8	2256.1	2229.5	2225.8	2229.5	2256.1	2259.8	2248.5	2108.4	2081.9	2081.9
52.5°	2116.0	2116.0	2119.8	2127.4	2119.8	2116.0	2116.0	2119.8	1994.9	1968.4	1960.8
55°	1991.1	1994.9	2021.4	2028.9	2021.4	1994.9	1991.1	1991.1	1877.5	1851.1	1835.9
57.5°	1862.3	1862.3	1881.4	1881.4	1881.4	1862.3	1862.3	1854.8	1745.1	1722.3	1714.8
60°	1714.8	1722.3	1737.4	1733.7	1737.4	1722.3	1714.8	1707.2	1612.5	1597.4	1570.9
62.5°	1559.5	1567.2	1570.9	1563.3	1570.9	1567.2	1559.5	1536.9	1480.1	1468.7	1434.6
65°	1396.8	1404.3	1408.1	1400.6	1408.1	1404.3	1396.8	1385.4	1343.8	1324.9	1294.6
67.5°	1230.2	1226.4	1222.7	1237.8	1222.7	1226.4	1230.2	1215.1	1188.6	1173.4	1131.8
70°	1059.9	1059.9	1056.1	1063.7	1056.1	1059.9	1059.9	1048.5	1033.4	1022.0	984.2
72.5°	878.2	874.4	889.6	878.2	889.6	874.4	878.2	874.4	866.9	855.5	817.7
75°	700.3	707.8	700.3	711.7	700.3	707.8	700.3	704.0	700.3	692.8	666.2
77.5°	533.7	541.3	533.7	533.7	533.7	541.3	533.7	537.5	537.5	537.5	514.8
80°	378.6	374.7	374.7	370.9	374.7	374.7	378.6	378.6	382.3	374.7	367.2
82.5°	242.3	238.5	238.5	246.0	238.5	238.5	242.3	246.0	238.5	238.5	238.5
85°	132.5	136.3	128.7	128.7	128.7	136.3	132.5	124.9	132.5	132.5	128.7
87.5°	49.2	45.5	45.5	45.5	45.5	45.5	49.2	53.0	53.0	53.0	56.8
90°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	14.5	19.4	21.8	18.7
92.5°	54.5	52.3	43.7	35.0	43.7	52.3	54.5	77.3	107.6	122.8	107.8
95°	185.1	178.5	152.2	126.0	152.2	178.5	185.1	243.0	320.3	359.0	303.2
97.5°	427.3	414.8	364.8	314.8	364.8	414.8	427.3	463.9	512.7	537.2	444.2
100°	600.0	585.1	525.6	466.0	525.6	585.1	600.0	597.4	593.8	592.0	488.8
102.5°	747.5	734.7	683.7	632.7	683.7	734.7	747.5	700.8	638.6	607.5	502.8
105°	919.7	912.8	885.4	858.0	885.4	912.8	919.7	815.0	675.5	605.8	504.3
107.5°	1009.2	1010.9	1017.6	1024.1	1017.6	1010.9	1009.2	863.2	668.6	571.3	481.9
110°	1032.2	1039.3	1067.9	1096.4	1067.9	1039.3	1032.2	869.0	651.4	542.6	462.0



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1017.6	1028.5	1072.4	1116.2	1072.4	1028.5	1017.6	850.5	627.9	516.6	444.6
115°	967.9	983.1	1043.9	1104.7	1043.9	983.1	967.9	807.0	592.5	485.2	424.7
117.5°	899.3	916.2	983.6	1051.1	983.6	916.2	899.3	754.2	560.6	463.7	412.3
120°	853.1	869.5	935.0	1000.6	935.0	869.5	853.1	720.5	543.5	455.1	408.0
122.5°	806.9	823.0	887.8	952.4	887.8	823.0	806.9	687.4	528.1	448.5	405.8
125°	745.8	760.7	820.2	879.7	820.2	760.7	745.8	644.2	508.9	441.3	404.1
127.5°	696.7	709.3	759.5	809.7	759.5	709.3	696.7	609.6	493.4	435.3	403.0
130°	665.7	677.4	723.8	770.2	723.8	677.4	665.7	588.2	484.8	433.0	403.6
132.5°	639.4	649.8	691.3	732.9	691.3	649.8	639.4	569.9	477.3	431.0	404.1
135°	602.0	611.0	646.8	682.6	646.8	611.0	602.0	543.9	466.3	427.6	403.7
137.5°	574.4	581.8	611.1	640.5	611.1	581.8	574.4	525.2	459.7	427.0	406.2
140°	552.4	559.2	586.7	614.1	586.7	559.2	552.4	509.9	453.2	425.0	406.5
142.5°	536.9	542.8	566.4	590.0	566.4	542.8	536.9	499.6	449.8	425.0	408.0
145°	513.6	518.1	535.9	553.8	535.9	518.1	513.6	483.1	442.5	422.1	408.0
147.5°	494.1	497.8	512.6	527.4	512.6	497.8	494.1	470.1	438.2	422.1	410.8
150°	482.9	485.9	497.9	509.9	497.9	485.9	482.9	462.7	435.7	422.1	412.3
152.5°	474.1	476.4	485.3	494.4	485.3	476.4	474.1	456.8	433.7	422.1	413.2
155°	463.5	465.0	470.9	476.9	470.9	465.0	463.5	449.7	431.3	422.1	415.3
157.5°	454.2	455.2	459.5	463.7	459.5	455.2	454.2	443.5	429.3	422.1	417.4
160°	449.6	450.2	452.7	455.1	452.7	450.2	449.6	440.4	428.2	422.1	418.4
162.5°	445.3	445.9	448.2	450.5	448.2	445.9	445.3	437.6	427.3	422.1	419.4
165°	438.7	439.3	441.8	444.2	441.8	439.3	438.7	433.2	425.8	422.1	420.9
167.5°	435.9	436.1	437.1	438.2	437.1	436.1	435.9	432.2	427.4	425.0	423.9
170°	435.9	435.9	435.9	435.9	435.9	435.9	435.9	432.2	427.4	425.0	424.9
172.5°	433.6	433.4	432.4	431.6	432.4	433.4	433.6	430.7	426.9	425.0	425.0
175°	430.4	430.4	430.4	430.4	430.4	430.4	430.4	428.6	426.2	425.0	425.5
177.5°	429.8	429.6	428.6	427.6	428.6	429.6	429.8	428.4	426.5	425.5	426.0
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	4001.1	4001.1	4001.1	4001.1	4001.1
2.5°	3951.9	3970.8	3982.2	3997.3	4035.2
5°	3800.5	3872.4	3895.2	3951.9	4020.1
7.5°	3467.4	3687.0	3747.5	3883.8	3989.7
10°	3145.6	3365.1	3471.1	3792.9	3951.9
12.5°	2982.8	3111.6	3183.5	3634.0	3898.9
15°	2880.7	2971.5	3024.5	3422.0	3838.3
17.5°	2801.1	2865.5	2903.4	3213.8	3755.1
20°	2751.9	2782.2	2816.3	3062.3	3660.4
22.5°	2717.8	2698.9	2725.5	2956.4	3531.7
25°	2695.2	2623.3	2653.6	2873.1	3380.3
27.5°	2714.1	2555.1	2566.5	2797.4	3221.3
30°	2717.8	2471.8	2475.6	2717.8	3043.4
32.5°	2691.4	2384.7	2388.6	2619.5	2842.7
35°	2627.0	2282.5	2278.8	2505.9	2570.3
37.5°	2539.9	2172.8	2172.8	2381.0	2271.2
40°	2434.0	2063.0	2074.4	2218.2	2006.3
42.5°	2305.3	1945.6	1960.8	2002.4	1809.4
45°	2165.2	1832.1	1843.4	1692.1	1658.0
47.5°	2010.0	1714.8	1718.5	1404.3	1608.8
50°	1824.5	1593.6	1578.5	1203.8	1605.0
52.5°	1661.8	1461.1	1415.7	1090.1	1457.3
55°	1502.8	1321.1	1222.7	1003.1	1351.3
57.5°	1362.7	1139.4	1044.8	900.9	1328.7
60°	1234.1	961.5	889.6	791.1	1218.9
62.5°	1128.0	829.0	813.9	715.4	1105.3
65°	1014.5	738.1	734.4	651.1	938.8
67.5°	904.7	677.6	673.8	590.5	715.4
70°	787.4	613.2	605.7	526.2	529.9
72.5°	666.2	541.3	533.7	473.2	439.1
75°	545.1	458.0	454.2	412.6	355.8
77.5°	427.7	363.4	370.9	333.1	261.2
80°	306.7	265.0	272.6	238.5	196.8
82.5°	204.4	174.1	181.7	151.4	132.5
85°	113.5	98.5	102.2	79.5	60.5
87.5°	53.0	45.5	45.5	30.3	18.9
90°	12.6	8.0	7.4	5.2	2.9
92.5°	77.8	55.4	50.5	30.9	11.5
95°	191.6	107.9	98.9	63.2	27.5
97.5°	258.0	118.5	110.7	79.2	47.7
100°	282.3	127.4	120.2	91.7	63.1
102.5°	293.4	136.3	129.6	102.9	76.3
105°	301.6	149.5	143.8	121.3	98.7
107.5°	303.1	169.0	163.8	142.7	121.7
110°	300.8	179.9	175.1	156.1	137.1



TEST NUMBER: P934080

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	300.9	193.1	188.6	170.5	152.4
115°	303.7	213.0	208.8	192.1	175.3
117.5°	309.3	232.2	228.3	213.2	198.0
120°	313.9	243.3	239.8	225.5	211.2
122.5°	320.5	256.5	252.9	238.6	224.1
125°	329.5	273.5	270.3	257.1	243.9
127.5°	338.4	289.8	286.5	273.2	260.0
130°	344.9	300.7	297.2	282.9	268.5
132.5°	350.1	309.6	306.1	291.8	277.5
135°	355.8	319.9	316.7	303.7	290.7
137.5°	364.4	333.1	329.9	317.1	304.2
140°	369.7	342.1	339.1	327.2	315.3
142.5°	374.1	348.7	345.9	334.9	323.9
145°	379.8	358.7	356.3	346.8	337.2
147.5°	388.2	371.3	369.0	359.7	350.4
150°	392.6	377.9	375.8	367.4	359.0
152.5°	395.5	382.2	380.6	374.3	367.9
155°	401.8	391.6	390.5	385.7	381.0
157.5°	408.2	401.2	400.0	395.4	390.8
160°	411.0	405.5	404.6	401.0	397.5
162.5°	414.1	410.1	409.4	406.7	404.1
165°	418.5	416.7	416.1	413.6	411.2
167.5°	421.9	420.4	420.1	419.0	417.8
170°	424.8	424.7	424.4	423.3	422.1
172.5°	425.0	425.0	424.9	424.7	424.4
175°	426.7	427.6	427.6	427.6	427.6
177.5°	426.9	427.6	427.6	427.6	427.6
180°	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P934080
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.89	17.09	16.55	17.76	18.55	18.74	19.94	19.40	20.62	21.40
	3H	16.39	17.47	17.06	18.15	18.98	20.12	21.19	20.79	21.88	22.70
	4H	16.60	17.61	17.29	18.31	19.15	20.58	21.59	21.27	22.29	23.13
	6H	16.73	17.67	17.44	18.38	19.23	20.89	21.82	21.59	22.53	23.38
	8H	16.74	17.64	17.46	18.37	19.22	20.97	21.87	21.69	22.60	23.45
	12H	16.72	17.58	17.45	18.30	19.18	21.03	21.88	21.75	22.60	23.48
4H	2H	16.96	17.98	17.66	18.68	19.51	19.19	20.20	19.88	20.90	21.74
	3H	18.02	18.87	18.73	19.61	20.46	20.73	21.58	21.44	22.31	23.17
	4H	18.31	19.08	19.04	19.82	20.70	21.28	22.04	22.00	22.78	23.67
	6H	18.46	19.12	19.20	19.89	20.78	21.67	22.33	22.41	23.10	23.99
	8H	18.47	19.09	19.22	19.85	20.76	21.78	22.41	22.53	23.17	24.07
	12H	18.45	19.01	19.22	19.80	20.71	21.86	22.42	22.63	23.20	24.11
8H	4H	18.80	19.42	19.55	20.18	21.08	21.43	22.05	22.18	22.81	23.71
	6H	19.07	19.59	19.85	20.39	21.30	21.88	22.40	22.66	23.20	24.11
	8H	19.12	19.58	19.91	20.38	21.30	22.04	22.50	22.83	23.30	24.23
	12H	19.12	19.52	19.91	20.32	21.30	22.16	22.56	22.95	23.36	24.34
12H	4H	18.82	19.38	19.59	20.16	21.07	21.41	21.97	22.18	22.75	23.66
	6H	19.14	19.60	19.93	20.40	21.32	21.88	22.34	22.68	23.15	24.07
	8H	19.22	19.62	20.01	20.42	21.40	22.06	22.47	22.86	23.26	24.24