

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937489

Luminaire Tested: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K

Issue Date: 12/17/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P937489  
REPORT IS A COMBINATION OF REPORTS P933573 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8188.0 lumens  
Efficiency: N/A  
Efficacy: 132.5 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 61.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937489  
CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P937489

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20					20					20					20	
RC	80				70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	37	37	37	29
1	93	88	84	81	83	79	76	73	62	60	58	46	45	44	32	31	30	30	30	30	23
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	28	26	25	25	25	25	19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21	21	21	21	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	18	18	18	18	13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	15	15	15	11
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13	13	13	13	10
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11	11	11	11	8
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10	10	10	10	7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	11	9	9	9	9	7
10	43	31	24	19	38	28	22	18	22	18	14	17	14	11	12	10	8	8	8	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1875	1875	1875
5°	1832	2167	2520
10°	1660	3158	4178
15°	1410	4124	5046
20°	1148	4779	5143
25°	958	4999	5038
30°	807	5029	5028
35°	713	4944	5158
40°	621	4835	5293
45°	562	4754	5314
50°	515	4681	5225
55°	493	4575	4994
60°	505	4372	4628
65°	523	4064	4125
70°	557	3541	3486
75°	614	2886	2721
80°	664	1998	1832
85°	584	1059	938

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 5314 cd/sqm



TEST NUMBER: P937489

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.2	0.5
10°-20°	173.8	2.1
20°-30°	304.0	3.7
30°-40°	391.3	4.8
40°-50°	437.1	5.3
50°-60°	418.6	5.1
60°-70°	331.7	4.1
70°-80°	195.1	2.4
80°-90°	57.6	0.7
90°-100°	439.1	5.4
100°-110°	1154.4	14.1
110°-120°	1197.0	14.6
120°-130°	960.2	11.7
130°-140°	753.4	9.2
140°-150°	578.2	7.1
150°-160°	416.4	5.1
160°-170°	254.8	3.1
170°-180°	86.1	1.1
0°-30°	517.0	6.3
0°-40°	908.3	11.1
0°-60°	1764.0	21.5
0°-90°	2348.4	28.7
90°-120°	2790.5	34.1
90°-150°	5082.3	62.1
90°-180°	5840.0	71.3
0°-180°	8188.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	303	303	303	303	303	
5°	295	317	357	404	418	27
15°	221	408	688	834	861	62
25°	141	463	820	856	857	65
35°	96	442	772	816	848	60
45°	65	353	682	782	817	51
55°	47	224	579	672	691	43
65°	37	119	430	483	490	37
75°	27	73	236	259	260	29
85°	10	22	58	64	65	10
90°	6	17	46	23	23	6
95°	58	227	756	390	265	64
105°	208	315	1276	1938	1808	220
115°	369	449	1022	2039	2328	365
125°	514	576	930	1571	1854	456
135°	612	674	901	1268	1438	474
145°	710	756	889	1082	1167	445
155°	803	825	889	976	1005	369
165°	866	878	889	924	936	244
175°	901	901	895	907	907	86
180°	901	901	901	901	901	



TEST NUMBER: P937489

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	303.1	303.1	303.1	303.1	303.1	303.1	303.1	303.1	303.1	303.1	303.1
2.5°	303.1	303.1	305.0	306.0	308.0	309.0	311.0	312.9	318.7	319.7	321.6
5°	295.4	299.2	311.9	316.8	330.4	348.9	356.7	369.4	395.7	403.5	408.4
7.5°	283.6	292.4	323.5	331.4	365.5	414.2	434.7	462.0	503.9	524.4	541.0
10°	265.1	283.6	339.2	357.8	413.3	487.3	525.4	563.4	626.7	654.9	665.7
12.5°	244.7	274.9	355.7	381.1	461.1	569.2	615.0	657.0	729.1	767.1	772.9
15°	221.2	262.2	371.3	408.4	511.7	637.4	688.1	739.8	807.1	834.3	841.2
17.5°	200.8	252.4	386.0	425.0	550.7	698.8	750.5	793.4	848.0	866.5	871.3
20°	175.5	236.8	395.7	446.4	591.7	743.7	793.4	826.6	863.6	875.3	877.2
22.5°	156.9	220.3	401.6	454.2	618.9	770.9	812.9	839.2	864.5	868.4	869.4
25°	141.4	201.7	400.6	463.0	642.4	787.5	819.7	839.2	853.8	855.7	855.7
27.5°	126.7	181.3	396.7	464.9	659.9	791.5	816.8	830.4	837.2	841.2	841.2
30°	114.1	161.8	386.9	461.1	667.6	787.5	808.0	814.8	821.6	827.5	830.4
32.5°	104.3	143.3	372.3	453.2	668.6	777.8	792.4	796.3	806.0	819.7	824.6
35°	95.5	124.8	355.7	442.5	662.8	762.2	771.9	775.9	795.4	815.8	822.6
37.5°	86.7	111.1	334.3	424.0	654.0	743.7	750.5	757.4	787.5	811.9	819.7
40°	78.0	99.4	309.0	403.5	640.4	721.2	727.1	737.8	777.8	806.0	813.9
42.5°	71.1	89.6	281.7	382.1	622.8	695.9	704.7	720.3	766.1	796.3	805.0
45°	65.3	79.9	252.4	352.8	600.4	669.6	682.3	703.7	752.4	781.7	789.4
47.5°	59.5	73.1	222.2	322.6	576.1	643.3	659.9	684.2	733.9	762.2	769.0
50°	54.6	66.3	192.1	290.4	549.7	615.0	634.5	659.9	710.6	736.8	745.6
52.5°	50.7	60.5	163.8	258.3	519.5	585.8	608.2	634.5	682.3	707.7	713.5
55°	46.8	55.5	139.3	224.1	488.3	554.6	579.0	604.3	651.1	672.5	676.5
57.5°	44.9	51.6	118.9	192.1	455.1	519.5	546.8	570.2	614.1	630.6	634.5
60°	42.0	48.7	103.3	164.7	419.1	486.3	509.8	533.1	570.2	583.8	586.7
62.5°	39.0	46.8	91.7	138.4	382.1	447.4	470.7	492.3	523.4	533.1	537.0
65°	37.0	44.9	82.8	118.9	344.1	406.4	429.8	448.4	473.6	483.4	485.4
67.5°	35.1	42.9	76.1	102.3	306.0	365.5	383.0	400.6	420.1	429.8	430.8
70°	32.2	40.9	70.2	90.6	267.1	318.7	333.3	351.8	367.4	372.3	375.3
72.5°	30.2	38.0	66.3	81.9	227.1	273.8	287.5	298.3	311.9	316.8	316.8
75°	27.3	34.1	62.4	73.1	186.1	224.1	235.9	246.6	257.3	259.3	256.3
77.5°	24.3	30.2	53.6	61.4	145.3	177.4	187.1	193.0	201.7	203.7	204.7
80°	20.4	26.4	42.0	47.8	105.2	130.6	137.4	142.3	150.1	150.1	152.0
82.5°	15.6	20.4	30.2	34.1	71.1	89.6	95.5	98.5	103.3	103.3	103.3
85°	9.8	12.7	19.5	22.4	42.9	54.6	58.5	59.5	63.4	64.3	64.3
87.5°	4.8	6.8	12.7	13.7	22.4	28.3	28.3	30.2	30.2	29.3	28.3
90°	6.0	10.9	15.7	17.0	26.6	39.5	45.9	40.8	30.6	23.0	23.0
92.5°	24.2	65.3	106.4	116.7	164.1	227.1	258.7	226.7	162.8	114.8	110.3
95°	58.0	133.2	208.5	227.3	403.7	638.8	756.3	674.9	512.0	389.9	376.1
97.5°	100.4	166.8	233.1	249.7	543.7	935.8	1131.8	1080.3	977.4	900.2	873.8
100°	133.0	193.2	253.4	268.4	594.7	1029.7	1247.2	1251.0	1258.5	1264.2	1232.8
102.5°	160.9	217.1	273.2	287.2	618.1	1059.3	1279.9	1345.5	1476.6	1574.9	1548.1
105°	207.9	255.5	303.1	315.0	635.5	1062.7	1276.3	1423.3	1717.2	1937.6	1923.2
107.5°	256.3	300.7	345.1	356.1	638.7	1015.3	1203.7	1408.7	1818.7	2126.3	2129.8
110°	289.0	329.0	369.1	379.1	633.8	973.5	1143.2	1372.4	1830.8	2174.6	2189.6



TEST NUMBER: P937489

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	321.0	359.2	397.4	406.9	634.0	936.8	1088.2	1322.8	1792.0	2143.8	2166.9
115°	369.4	404.6	439.7	448.6	639.8	894.8	1022.3	1248.3	1700.3	2039.3	2071.3
117.5°	417.2	449.1	481.1	489.1	651.7	868.5	976.9	1180.9	1588.8	1894.7	1930.2
120°	445.0	475.1	505.1	512.7	661.4	859.7	958.8	1145.2	1517.8	1797.4	1831.9
122.5°	472.2	502.5	532.9	540.5	675.3	855.0	945.0	1112.8	1448.4	1700.0	1734.1
125°	513.9	541.6	569.3	576.2	694.1	851.3	929.9	1072.4	1357.5	1571.3	1602.7
127.5°	547.8	575.7	603.7	610.7	712.8	849.0	917.2	1039.5	1284.3	1467.9	1494.4
130°	565.9	596.0	626.1	633.6	726.6	850.4	912.3	1021.2	1239.2	1402.6	1427.0
132.5°	584.6	614.7	644.8	652.3	737.6	851.3	908.0	1005.6	1200.7	1347.0	1368.9
135°	612.4	639.8	667.3	674.1	749.7	850.4	900.8	982.5	1145.8	1268.4	1287.3
137.5°	640.8	667.9	695.2	701.9	767.8	855.7	899.6	968.7	1106.8	1210.4	1225.8
140°	664.4	689.4	714.4	720.6	778.9	856.5	895.4	955.0	1074.3	1163.8	1178.2
142.5°	682.6	705.7	728.8	734.6	788.2	859.6	895.4	947.8	1052.5	1131.1	1143.5
145°	710.4	730.5	750.7	755.7	800.3	859.7	889.3	932.2	1017.9	1082.2	1091.6
147.5°	738.2	757.8	777.3	782.3	817.9	865.5	889.3	923.1	990.5	1041.1	1048.8
150°	756.3	774.0	791.8	796.2	827.2	868.6	889.3	917.8	974.7	1017.4	1023.7
152.5°	775.1	788.6	801.9	805.3	833.3	870.6	889.3	913.7	962.3	998.7	1003.5
155°	802.9	812.8	822.7	825.2	846.6	875.1	889.3	908.7	947.4	976.4	979.6
157.5°	823.5	833.1	842.7	845.2	859.9	879.6	889.3	904.4	934.5	957.1	959.3
160°	837.3	844.9	852.4	854.3	866.0	881.6	889.3	902.2	928.0	947.4	948.7
162.5°	851.3	856.9	862.5	864.0	872.4	883.7	889.3	900.2	922.0	938.3	939.4
165°	866.4	871.4	876.6	877.8	881.7	886.8	889.3	897.1	912.7	924.4	925.7
167.5°	880.2	882.7	885.1	885.7	888.9	893.2	895.4	900.5	910.7	918.3	918.9
170°	889.3	891.8	894.2	894.8	895.0	895.3	895.4	900.5	910.7	918.3	918.3
172.5°	894.2	894.7	895.3	895.4	895.4	895.4	895.4	899.4	907.5	913.5	913.0
175°	900.8	900.8	900.8	900.8	898.9	896.5	895.4	897.9	903.0	906.9	906.9
177.5°	900.8	900.8	900.8	900.8	899.4	897.6	896.6	898.7	902.6	905.6	905.0
180°	900.8	900.8	900.8	900.8	900.8	900.8	900.8	900.8	900.8	900.8	900.8



TEST NUMBER: P937489

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	303.1	303.1
2.5°	323.5	321.6
5°	416.2	418.1
7.5°	560.5	559.5
10°	696.9	705.6
12.5°	796.3	798.3
15°	856.8	860.7
17.5°	880.1	881.1
20°	881.1	879.2
22.5°	870.4	868.4
25°	857.8	856.8
27.5°	846.0	847.0
30°	841.2	844.1
32.5°	841.2	846.0
35°	843.1	848.0
37.5°	842.2	848.0
40°	838.2	845.1
42.5°	827.5	832.4
45°	811.0	816.8
47.5°	789.4	793.4
50°	762.2	766.1
52.5°	728.1	729.1
55°	687.1	691.1
57.5°	643.3	644.3
60°	594.6	597.5
62.5°	542.9	542.9
65°	488.3	490.2
67.5°	431.8	436.6
70°	374.3	375.3
72.5°	317.7	317.7
75°	259.3	260.3
77.5°	203.7	203.7
80°	151.1	152.0
82.5°	104.3	106.2
85°	65.3	65.3
87.5°	30.2	27.3
90°	23.0	23.0
92.5°	92.0	73.7
95°	320.7	265.4
97.5°	768.5	663.2
100°	1107.3	981.8
102.5°	1440.5	1333.1
105°	1865.4	1807.7
107.5°	2143.8	2157.8
110°	2249.9	2310.1





TEST NUMBER: P937489

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	2259.3	2351.8
115°	2199.4	2327.6
117.5°	2072.4	2214.6
120°	1970.1	2108.2
122.5°	1870.4	2006.6
125°	1728.1	1853.6
127.5°	1600.3	1706.1
130°	1524.9	1622.7
132.5°	1456.5	1544.1
135°	1362.8	1438.3
137.5°	1287.6	1349.4
140°	1236.1	1293.8
142.5°	1193.3	1243.0
145°	1129.3	1166.9
147.5°	1080.0	1111.2
150°	1049.0	1074.3
152.5°	1022.6	1041.7
155°	992.2	1004.8
157.5°	968.1	976.9
160°	953.8	958.8
162.5°	944.3	949.1
165°	930.8	935.9
167.5°	921.0	923.2
170°	918.3	918.3
172.5°	911.2	909.3
175°	906.9	906.9
177.5°	902.9	900.8
180°	900.8	900.8



TEST NUMBER: P937489  
 CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-6-3500K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.81	1.53	1.93	2.64	4.18	13.98	14.69	15.09	15.81	17.35
	3H	1.51	2.15	2.63	3.27	4.83	15.80	16.44	16.92	17.56	19.12
	4H	1.80	2.41	2.93	3.53	5.10	16.43	17.05	17.57	18.17	19.73
	6H	2.04	2.60	3.18	3.73	5.30	16.85	17.42	18.00	18.54	20.12
	8H	2.10	2.64	3.25	3.78	5.35	16.97	17.50	18.11	18.64	20.21
	12H	2.11	2.62	3.26	3.76	5.35	17.03	17.54	18.18	18.67	20.26
4H	2H	8.00	8.61	9.14	9.73	11.30	14.23	14.84	15.37	15.97	17.53
	3H	9.55	10.07	10.70	11.21	12.79	16.26	16.77	17.41	17.92	19.50
	4H	9.64	10.11	10.79	11.25	12.85	17.02	17.49	18.17	18.62	20.22
	6H	9.65	10.05	10.80	11.21	12.80	17.54	17.95	18.70	19.11	20.69
	8H	9.62	10.00	10.77	11.15	12.75	17.70	18.08	18.85	19.23	20.83
	12H	9.57	9.91	10.74	11.07	12.68	17.78	18.12	18.95	19.29	20.90
8H	4H	11.07	11.45	12.23	12.60	14.21	17.07	17.44	18.22	18.59	20.20
	6H	11.31	11.62	12.48	12.81	14.41	17.68	17.99	18.86	19.19	20.79
	8H	11.32	11.60	12.50	12.77	14.39	17.90	18.17	19.08	19.34	20.96
	12H	11.28	11.52	12.47	12.69	14.35	18.03	18.27	19.22	19.44	21.10
12H	4H	11.21	11.55	12.38	12.71	14.32	17.01	17.35	18.18	18.52	20.13
	6H	11.56	11.83	12.74	13.01	14.63	17.66	17.94	18.85	19.11	20.73
	8H	11.62	11.86	12.81	13.03	14.69	17.88	18.12	19.07	19.29	20.95