

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938079

Luminaire Tested: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938079
REPORT IS A COMBINATION OF REPORTS P933591 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23787.0 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 193.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938079
CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P938079

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	90	86	83	86	82	79	76	67	65	62	53	51	50	40	39	38	32
2	86	78	72	67	78	71	66	61	58	54	51	46	43	41	35	33	31	26
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26	21
4	71	60	52	46	64	55	48	42	45	40	35	35	32	29	27	24	22	18
5	65	53	45	39	59	49	41	36	40	34	30	31	27	24	24	21	19	15
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13
7	55	43	35	29	50	39	32	27	32	26	23	25	21	18	19	16	14	11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	26	21	17	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	18	24	19	16	19	15	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3695	3695	3695
5°	3611	4271	4966
10°	3276	6228	8233
15°	2785	8138	9941
20°	2269	9433	10132
25°	1893	9874	9926
30°	1597	9939	9907
35°	1413	9777	10163
40°	1232	9564	10428
45°	1117	9410	10469
50°	1025	9272	10295
55°	983	9069	9839
60°	1007	8674	9119
65°	1049	8073	8128
70°	1120	7046	6867
75°	1247	5750	5359
80°	1371	3993	3611
85°	1244	2121	1849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10469 cd/sqm



TEST NUMBER: P938079

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.5	0.6
10°-20°	684.8	2.9
20°-30°	1197.8	5.0
30°-40°	1541.9	6.5
40°-50°	1722.3	7.2
50°-60°	1649.5	6.9
60°-70°	1307.3	5.5
70°-80°	768.7	3.2
80°-90°	222.1	0.9
90°-100°	1093.2	4.6
100°-110°	2874.0	12.1
110°-120°	2980.0	12.5
120°-130°	2390.3	10.0
130°-140°	1875.6	7.9
140°-150°	1439.6	6.1
150°-160°	1036.7	4.4
160°-170°	634.3	2.7
170°-180°	214.3	0.9
0°-30°	2037.1	8.6
0°-40°	3579.0	15.0
0°-60°	6950.9	29.2
0°-90°	9248.9	38.9
90°-120°	6947.2	29.2
90°-150°	12652.7	53.2
90°-180°	14538.0	61.1
0°-180°	23787.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1194	1194	1194	1194	1194	
5°	1164	1248	1406	1590	1648	107
15°	872	1609	2712	3288	3391	243
25°	557	1824	3230	3372	3376	257
35°	376	1744	3042	3215	3341	235
45°	257	1390	2688	3080	3218	199
55°	184	883	2281	2650	2723	168
65°	146	469	1694	1905	1932	145
75°	108	288	930	1022	1026	113
85°	38	88	230	254	257	41
90°	15	42	114	57	57	15
95°	144	566	1883	971	661	160
105°	518	784	3177	4824	4500	549
115°	920	1117	2545	5077	5795	908
125°	1279	1434	2315	3912	4615	1136
135°	1525	1678	2243	3158	3581	1180
145°	1768	1881	2214	2694	2905	1108
155°	1999	2054	2214	2431	2502	918
165°	2157	2185	2214	2301	2330	609
175°	2243	2243	2229	2258	2258	213
180°	2243	2243	2243	2243	2243	



TEST NUMBER: P938079

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5
2.5°	1194.5	1194.5	1202.1	1206.0	1213.7	1217.5	1225.2	1232.9	1255.9	1259.8	1267.5
5°	1163.8	1179.1	1229.1	1248.3	1302.0	1375.0	1405.7	1455.6	1559.3	1590.0	1609.2
7.5°	1117.6	1152.2	1275.1	1305.8	1440.2	1632.3	1713.0	1820.5	1985.7	2066.3	2131.6
10°	1044.7	1117.6	1336.5	1409.5	1628.5	1920.4	2070.2	2220.0	2469.6	2580.9	2623.2
12.5°	964.1	1083.1	1401.9	1501.8	1816.7	2242.9	2423.5	2588.7	2872.9	3022.7	3045.7
15°	871.8	1033.1	1463.3	1609.2	2016.4	2511.8	2711.6	2915.1	3180.2	3287.6	3314.6
17.5°	791.2	994.8	1520.9	1674.5	2170.0	2753.8	2957.4	3126.4	3341.4	3414.4	3433.7
20°	691.3	933.3	1559.3	1759.0	2331.3	2930.4	3126.4	3256.9	3402.8	3449.0	3456.6
22.5°	618.3	868.0	1582.4	1789.7	2438.9	3038.0	3203.1	3306.9	3406.7	3422.1	3425.9
25°	556.9	795.1	1578.5	1824.3	2531.0	3103.3	3230.1	3306.9	3364.5	3372.1	3372.1
27.5°	499.3	714.3	1563.2	1832.0	2600.2	3118.6	3218.5	3272.3	3299.2	3314.6	3314.6
30°	449.3	637.6	1524.7	1816.7	2630.9	3103.3	3183.9	3210.9	3237.7	3260.8	3272.3
32.5°	411.0	564.5	1467.2	1786.0	2634.7	3064.9	3122.5	3137.9	3176.3	3230.1	3249.3
35°	376.4	491.6	1401.9	1743.7	2611.6	3003.4	3041.9	3057.2	3134.0	3214.7	3241.6
37.5°	341.9	437.9	1317.4	1670.7	2577.2	2930.4	2957.4	2984.2	3103.3	3199.3	3230.1
40°	307.3	391.8	1217.5	1590.0	2523.4	2842.2	2865.1	2907.4	3064.9	3176.3	3207.0
42.5°	280.3	353.4	1110.0	1505.5	2454.2	2742.3	2776.9	2838.3	3018.8	3137.9	3172.4
45°	257.4	314.9	994.8	1390.3	2365.9	2638.6	2688.5	2773.0	2965.0	3080.3	3111.0
47.5°	234.3	288.1	875.7	1271.3	2269.9	2534.9	2600.2	2696.1	2892.1	3003.4	3030.4
50°	215.1	261.1	756.6	1144.6	2166.2	2423.5	2500.3	2600.2	2799.9	2903.6	2938.2
52.5°	199.7	238.1	645.3	1017.8	2047.1	2308.3	2396.6	2500.3	2688.5	2788.4	2811.5
55°	184.4	218.9	549.2	883.3	1924.2	2185.4	2281.4	2381.2	2565.6	2650.1	2665.4
57.5°	176.6	203.6	468.6	756.6	1793.6	2047.1	2154.7	2246.8	2419.7	2484.9	2500.3
60°	165.1	192.1	407.1	649.0	1651.5	1916.5	2008.7	2100.9	2246.8	2300.6	2312.1
62.5°	153.6	184.4	361.0	545.4	1505.5	1762.9	1855.1	1939.6	2062.5	2100.9	2116.2
65°	145.9	176.6	326.5	468.6	1355.8	1601.6	1693.7	1766.8	1866.6	1905.0	1912.7
67.5°	138.3	169.0	299.6	403.3	1206.0	1440.2	1509.4	1578.5	1655.3	1693.7	1697.6
70°	126.7	161.3	276.6	357.2	1052.3	1255.9	1313.6	1386.5	1448.0	1467.2	1478.7
72.5°	119.1	149.8	261.1	322.6	894.9	1079.3	1133.1	1175.3	1229.1	1248.3	1248.3
75°	107.6	134.4	245.8	288.1	733.5	883.3	929.5	971.7	1014.0	1021.6	1010.1
77.5°	96.0	119.1	211.2	242.0	572.3	699.0	737.4	760.5	795.1	802.7	806.6
80°	80.6	103.7	165.1	188.2	414.8	514.6	541.6	560.8	591.5	591.5	599.1
82.5°	61.4	80.6	119.1	134.4	280.3	353.4	376.4	387.9	407.1	407.1	407.1
85°	38.4	49.9	76.8	88.4	169.0	215.1	230.4	234.3	249.6	253.5	253.5
87.5°	19.2	26.8	49.9	53.8	88.4	111.3	111.3	119.1	119.1	115.2	111.3
90°	15.0	27.0	39.1	42.2	66.2	98.3	114.3	101.6	76.3	57.2	57.2
92.5°	60.2	162.5	264.9	290.5	408.4	565.6	644.2	564.5	405.3	286.0	274.6
95°	144.5	331.8	519.1	565.9	1004.9	1590.2	1882.9	1680.1	1274.8	970.8	936.3
97.5°	249.8	415.0	580.3	621.6	1353.6	2329.6	2817.6	2689.5	2433.3	2241.1	2175.5
100°	331.1	481.0	630.8	668.3	1480.5	2563.6	3105.1	3114.5	3133.2	3147.2	3069.1
102.5°	400.4	540.2	679.9	714.9	1538.8	2637.1	3186.4	3349.5	3676.0	3920.9	3854.0
105°	517.7	636.1	754.6	784.2	1581.9	2645.5	3177.3	3543.1	4275.0	4823.9	4787.9
107.5°	638.2	748.6	858.9	886.5	1589.9	2527.8	2996.7	3507.1	4527.8	5293.5	5302.2
110°	719.5	819.1	918.8	943.7	1577.8	2423.4	2846.1	3416.8	4558.0	5413.9	5451.4



TEST NUMBER: P938079

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	799.2	894.2	989.2	1012.9	1578.3	2332.3	2709.2	3293.2	4461.2	5337.2	5394.7
115°	919.6	1007.2	1094.9	1116.8	1592.9	2227.7	2545.2	3107.8	4232.9	5076.8	5156.5
117.5°	1038.6	1118.1	1197.8	1217.6	1622.5	2162.3	2432.3	2940.0	3955.5	4717.0	4805.5
120°	1107.8	1182.7	1257.7	1276.4	1646.6	2140.3	2387.1	2851.1	3778.9	4474.7	4560.7
122.5°	1175.5	1251.1	1326.7	1345.6	1681.2	2128.8	2352.5	2770.3	3605.7	4232.4	4317.2
125°	1279.4	1348.3	1417.2	1434.4	1727.9	2119.2	2314.8	2669.7	3379.5	3911.8	3989.9
127.5°	1363.7	1433.2	1502.8	1520.2	1774.5	2113.7	2283.3	2587.9	3197.3	3654.4	3720.3
130°	1408.8	1483.7	1558.6	1577.3	1808.6	2117.1	2271.2	2542.5	3085.0	3491.9	3552.7
132.5°	1455.4	1530.3	1605.3	1624.0	1836.3	2119.2	2260.7	2503.5	2989.2	3353.4	3408.0
135°	1524.7	1592.9	1661.2	1678.2	1866.4	2117.3	2242.7	2446.0	2852.7	3157.8	3204.8
137.5°	1595.5	1663.0	1730.5	1747.4	1911.4	2130.2	2239.6	2411.6	2755.4	3013.2	3051.7
140°	1654.1	1716.3	1778.5	1794.1	1939.1	2132.4	2229.1	2377.5	2674.5	2897.3	2933.3
142.5°	1699.2	1756.8	1814.4	1828.7	1962.1	2140.1	2229.1	2359.5	2620.5	2816.1	2847.0
145°	1768.5	1818.7	1868.9	1881.4	1992.3	2140.1	2214.1	2320.8	2534.1	2694.1	2717.6
147.5°	1837.7	1886.5	1935.4	1947.6	2036.5	2154.9	2214.1	2298.0	2465.9	2591.8	2611.2
150°	1882.9	1927.1	1971.2	1982.3	2059.5	2162.5	2214.1	2285.0	2426.8	2533.1	2548.8
152.5°	1929.6	1963.0	1996.5	2004.9	2074.6	2167.6	2214.1	2274.6	2395.7	2486.5	2498.4
155°	1998.8	2023.6	2048.3	2054.5	2107.7	2178.6	2214.1	2262.2	2358.5	2430.7	2438.6
157.5°	2050.0	2074.0	2098.2	2104.2	2140.8	2189.6	2214.1	2251.5	2326.4	2382.6	2388.1
160°	2084.6	2103.3	2122.1	2126.8	2155.8	2194.7	2214.1	2246.1	2310.4	2358.5	2361.7
162.5°	2119.2	2133.3	2147.3	2150.8	2171.9	2200.0	2214.1	2241.2	2295.4	2336.0	2339.0
165°	2156.8	2169.5	2182.2	2185.4	2195.0	2207.7	2214.1	2233.4	2272.2	2301.3	2304.5
167.5°	2191.5	2197.5	2203.5	2205.0	2213.0	2223.8	2229.1	2241.8	2267.2	2286.3	2287.6
170°	2214.1	2220.1	2226.1	2227.5	2228.0	2228.7	2229.1	2241.8	2267.2	2286.3	2286.3
172.5°	2226.1	2227.4	2228.8	2229.1	2229.1	2229.1	2229.1	2239.2	2259.2	2274.2	2273.1
175°	2242.7	2242.7	2242.7	2242.7	2238.1	2232.1	2229.1	2235.5	2248.2	2257.7	2257.7
177.5°	2242.7	2242.7	2242.7	2242.7	2239.2	2234.4	2232.1	2237.1	2247.1	2254.7	2253.3
180°	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7



TEST NUMBER: P938079

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1194.5	1194.5
2.5°	1275.1	1267.5
5°	1640.0	1647.7
7.5°	2208.4	2204.6
10°	2746.1	2780.6
12.5°	3137.9	3145.6
15°	3376.0	3391.4
17.5°	3468.1	3472.0
20°	3472.0	3464.4
22.5°	3429.8	3422.1
25°	3379.9	3376.0
27.5°	3333.7	3337.6
30°	3314.6	3326.1
32.5°	3314.6	3333.7
35°	3322.2	3341.4
37.5°	3318.3	3341.4
40°	3303.0	3329.9
42.5°	3260.8	3280.0
45°	3195.5	3218.5
47.5°	3111.0	3126.4
50°	3003.4	3018.8
52.5°	2869.0	2872.9
55°	2707.7	2723.1
57.5°	2534.9	2538.7
60°	2342.8	2354.4
62.5°	2139.3	2139.3
65°	1924.2	1931.9
67.5°	1701.5	1720.7
70°	1474.8	1478.7
72.5°	1252.0	1252.0
75°	1021.6	1025.5
77.5°	802.7	802.7
80°	595.4	599.1
82.5°	411.0	418.6
85°	257.4	257.4
87.5°	119.1	107.6
90°	57.2	57.2
92.5°	229.1	183.6
95°	798.6	660.8
97.5°	1913.3	1651.1
100°	2756.7	2444.3
102.5°	3586.4	3318.8
105°	4644.1	4500.3
107.5°	5337.0	5371.7
110°	5601.2	5751.0



TEST NUMBER: P938079

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5624.8	5854.9
115°	5475.6	5794.7
117.5°	5159.3	5513.2
120°	4904.5	5248.3
122.5°	4656.3	4995.5
125°	4302.3	4614.7
127.5°	3983.8	4247.4
130°	3796.3	4039.8
132.5°	3626.0	3844.0
135°	3392.7	3580.6
137.5°	3205.5	3359.4
140°	3077.2	3221.0
142.5°	2970.8	3094.5
145°	2811.2	2904.9
147.5°	2688.8	2766.4
150°	2611.7	2674.6
152.5°	2545.9	2593.3
155°	2470.1	2501.5
157.5°	2410.2	2432.3
160°	2374.4	2387.1
162.5°	2351.0	2363.0
165°	2317.2	2330.0
167.5°	2292.9	2298.3
170°	2286.3	2286.3
172.5°	2268.3	2263.7
175°	2257.7	2257.7
177.5°	2248.0	2242.7
180°	2242.7	2242.7



TEST NUMBER: P938079
 CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-12-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.44	5.24	5.48	6.29	7.71	17.63	18.43	18.67	19.48	20.90
	3H	5.14	5.86	6.19	6.92	8.35	19.47	20.19	20.52	21.25	22.68
	4H	5.44	6.12	6.50	7.18	8.62	20.12	20.80	21.18	21.86	23.30
	6H	5.68	6.31	6.75	7.37	8.83	20.55	21.18	21.62	22.24	23.70
	8H	5.75	6.34	6.82	7.43	8.88	20.67	21.27	21.75	22.35	23.80
	12H	5.76	6.33	6.84	7.41	8.88	20.74	21.31	21.82	22.38	23.86
4H	2H	11.66	12.33	12.72	13.40	14.84	17.90	18.58	18.97	19.64	21.08
	3H	13.22	13.78	14.29	14.87	16.33	19.94	20.51	21.02	21.60	23.06
	4H	13.31	13.83	14.39	14.91	16.39	20.71	21.23	21.79	22.31	23.79
	6H	13.31	13.76	14.41	14.87	16.34	21.25	21.70	22.34	22.80	24.27
	8H	13.29	13.71	14.38	14.80	16.29	21.41	21.83	22.50	22.93	24.42
	12H	13.24	13.62	14.35	14.73	16.23	21.51	21.89	22.62	22.99	24.49
8H	4H	14.75	15.17	15.84	16.27	17.75	20.76	21.18	21.86	22.28	23.77
	6H	14.99	15.34	16.10	16.47	17.96	21.40	21.74	22.51	22.88	24.36
	8H	15.01	15.31	16.13	16.43	17.94	21.62	21.92	22.74	23.04	24.55
	12H	14.97	15.24	16.10	16.35	17.90	21.76	22.03	22.89	23.14	24.69
12H	4H	14.89	15.27	16.00	16.38	17.87	20.71	21.09	21.82	22.20	23.70
	6H	15.25	15.55	16.37	16.67	18.18	21.38	21.68	22.50	22.80	24.31
	8H	15.32	15.58	16.44	16.70	18.24	21.61	21.88	22.73	22.99	24.53