

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938279

Luminaire Tested: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938279
REPORT IS A COMBINATION OF REPORTS P933621 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 22214.3 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 166.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938279
CATALOG NUMBER: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P938279

CATALOG NUMBER: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21		
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	26	25	24	17		
2	83	75	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14		
3	75	66	59	53	66	59	53	48	45	40	37	32	29	27	20	18	17	12		
4	69	58	50	45	60	52	45	40	39	35	31	28	25	23	17	16	14	10		
5	63	51	44	38	55	46	39	34	35	30	27	25	22	19	15	14	12	8		
6	57	46	38	32	51	41	34	29	31	26	23	22	19	17	14	12	11	7		
7	53	41	33	28	47	37	30	25	28	23	20	20	17	14	12	11	9	6		
8	49	37	30	24	43	33	27	22	25	21	17	18	15	13	11	9	8	5		
9	45	34	26	21	40	30	24	19	23	18	15	16	13	11	10	9	7	5		
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	6	4		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1876	1876	1876
5°	1833	2168	2521
10°	1663	3161	4179
15°	1414	4132	5047
20°	1152	4789	5143
25°	961	5012	5039
30°	811	5046	5029
35°	717	4963	5159
40°	626	4856	5294
45°	567	4777	5315
50°	520	4707	5227
55°	499	4603	4995
60°	511	4404	4629
65°	533	4099	4126
70°	568	3577	3486
75°	633	2918	2720
80°	697	2027	1833
85°	632	1077	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 6718 cd/sqm



TEST NUMBER: P938279

CATALOG NUMBER: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.4	0.4
10°-20°	347.6	1.6
20°-30°	608.1	2.7
30°-40°	782.8	3.5
40°-50°	874.3	3.9
50°-60°	837.4	3.8
60°-70°	663.6	3.0
70°-80°	390.2	1.8
80°-90°	118.7	0.5
90°-100°	1316.9	5.9
100°-110°	3462.1	15.6
110°-120°	3589.9	16.2
120°-130°	2879.5	13.0
130°-140°	2259.4	10.2
140°-150°	1734.2	7.8
150°-160°	1248.9	5.6
160°-170°	764.1	3.4
170°-180°	258.2	1.2
0°-30°	1034.2	4.7
0°-40°	1816.9	8.2
0°-60°	3528.6	15.9
0°-90°	4701.2	21.2
90°-120°	8368.8	37.7
90°-150°	15241.9	68.6
90°-180°	17513.0	78.8
0°-180°	22214.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	606	606	606	606	606	
5°	591	634	714	807	836	55
15°	443	817	1377	1669	1722	123
25°	283	926	1640	1712	1714	130
35°	191	885	1544	1632	1696	119
45°	131	706	1365	1564	1634	101
55°	94	448	1158	1345	1382	85
65°	74	238	860	967	981	73
75°	55	146	472	519	520	57
85°	20	45	117	129	131	21
90°	18	51	138	69	69	16
95°	174	682	2268	1170	796	193
105°	624	945	3828	5811	5421	661
115°	1108	1345	3066	6116	6980	1094
125°	1541	1728	2789	4712	5559	1368
135°	1837	2022	2702	3804	4313	1421
145°	2130	2266	2667	3246	3499	1335
155°	2408	2475	2667	2928	3013	1106
165°	2598	2633	2667	2772	2807	733
175°	2702	2702	2685	2720	2720	256
180°	2702	2702	2702	2702	2702	



TEST NUMBER: P938279

CATALOG NUMBER: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4
2.5°	606.4	606.4	610.3	612.2	616.1	618.0	622.0	625.9	637.6	639.5	643.4
5°	590.8	598.6	623.9	633.6	661.0	698.0	713.6	739.0	791.6	807.2	817.0
7.5°	567.3	584.9	647.3	662.9	731.2	828.7	869.6	924.2	1008.1	1048.9	1082.1
10°	530.3	567.3	678.5	715.6	826.7	974.9	1050.9	1126.9	1253.7	1310.3	1331.7
12.5°	489.3	549.8	711.6	762.3	922.2	1138.7	1230.3	1314.2	1458.4	1534.5	1546.1
15°	442.6	524.5	742.8	817.0	1023.7	1275.1	1376.6	1479.9	1614.5	1669.0	1682.7
17.5°	401.7	504.9	772.1	850.1	1101.7	1398.0	1501.3	1587.1	1696.3	1733.3	1743.1
20°	351.0	473.8	791.6	893.0	1183.5	1487.7	1587.1	1653.4	1727.5	1750.9	1754.8
22.5°	314.0	440.6	803.3	908.6	1238.1	1542.3	1626.1	1678.8	1729.5	1737.2	1739.2
25°	282.8	403.6	801.4	926.2	1284.9	1575.4	1639.7	1678.8	1708.0	1711.9	1711.9
27.5°	253.5	362.7	793.5	930.0	1320.0	1583.2	1633.9	1661.2	1674.8	1682.7	1682.7
30°	228.1	323.6	774.0	922.2	1335.6	1575.4	1616.4	1630.1	1643.6	1655.3	1661.2
32.5°	208.6	286.6	744.8	906.6	1337.5	1555.9	1585.2	1592.9	1612.4	1639.7	1649.5
35°	191.1	249.6	711.6	885.2	1325.9	1524.7	1544.2	1552.0	1591.0	1632.0	1645.6
37.5°	173.5	222.3	668.8	848.2	1308.2	1487.7	1501.3	1514.9	1575.4	1624.1	1639.7
40°	156.0	198.8	618.0	807.2	1281.0	1442.8	1454.6	1476.0	1555.9	1612.4	1628.0
42.5°	142.3	179.4	563.5	764.3	1245.9	1392.2	1409.7	1440.9	1532.5	1592.9	1610.5
45°	130.6	159.9	504.9	705.8	1201.1	1339.4	1364.8	1407.8	1505.2	1563.7	1579.3
47.5°	118.9	146.2	444.6	645.4	1152.3	1286.8	1320.0	1368.7	1468.1	1524.7	1538.4
50°	109.2	132.6	384.1	581.0	1099.6	1230.3	1269.3	1320.0	1421.4	1474.0	1491.6
52.5°	101.4	120.9	327.5	516.7	1039.3	1171.8	1216.7	1269.3	1364.8	1415.5	1427.2
55°	93.6	111.1	278.8	448.5	976.8	1109.4	1158.1	1208.8	1302.4	1345.4	1353.1
57.5°	89.7	103.3	237.9	384.1	910.6	1039.3	1093.8	1140.6	1228.3	1261.5	1269.3
60°	83.8	97.5	206.7	329.6	838.4	973.0	1019.8	1066.5	1140.6	1167.9	1173.7
62.5°	78.0	93.6	183.2	276.8	764.3	895.0	941.8	984.6	1047.0	1066.5	1074.3
65°	74.1	89.7	165.7	237.9	688.3	813.1	859.9	896.9	947.6	967.1	970.9
67.5°	70.2	85.8	152.0	204.7	612.2	731.2	766.3	801.4	840.3	859.9	861.8
70°	64.3	81.9	140.4	181.3	534.2	637.6	666.9	703.9	735.1	744.8	750.7
72.5°	60.5	76.1	132.6	163.8	454.3	547.9	575.2	596.6	623.9	633.6	633.6
75°	54.6	68.2	124.8	146.2	372.4	448.5	471.8	493.3	514.7	518.6	512.8
77.5°	48.7	60.5	107.3	122.9	290.5	354.8	374.3	386.0	403.6	407.5	409.4
80°	41.0	52.6	83.8	95.5	210.6	261.2	274.9	284.7	300.3	300.3	304.2
82.5°	31.2	41.0	60.5	68.2	142.3	179.4	191.1	196.9	206.7	206.7	206.7
85°	19.5	25.4	39.0	44.9	85.8	109.2	117.0	118.9	126.7	128.7	128.7
87.5°	9.8	13.7	25.4	27.3	44.9	56.6	56.6	60.5	60.5	58.5	56.6
90°	18.1	32.7	47.2	50.8	79.7	118.4	137.8	122.5	91.9	68.9	68.9
92.5°	72.5	195.7	319.1	349.9	492.0	681.3	776.0	680.0	488.3	344.5	330.8
95°	174.0	399.6	625.3	681.7	1210.6	1915.7	2268.2	2024.0	1535.8	1169.5	1128.0
97.5°	301.0	500.0	699.0	748.8	1630.6	2806.3	3394.1	3239.9	2931.2	2699.7	2620.8
100°	398.8	579.4	759.9	805.0	1783.5	3088.1	3740.4	3751.7	3774.3	3791.2	3697.1
102.5°	482.3	650.7	819.1	861.2	1853.6	3176.8	3838.4	4035.0	4428.2	4723.2	4642.6
105°	623.7	766.4	909.0	944.7	1905.6	3186.8	3827.5	4268.3	5149.8	5811.0	5767.7
107.5°	768.8	901.8	1034.7	1067.9	1915.2	3045.0	3609.9	4224.7	5454.4	6376.7	6387.2
110°	866.7	986.7	1106.8	1136.8	1900.8	2919.3	3428.6	4116.0	5490.7	6521.8	6566.9



TEST NUMBER: P938279

CATALOG NUMBER: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	962.8	1077.2	1191.7	1220.3	1901.4	2809.5	3263.6	3967.1	5374.1	6429.3	6498.6
115°	1107.9	1213.4	1319.0	1345.4	1918.9	2683.6	3066.0	3743.7	5099.1	6115.6	6211.8
117.5°	1251.1	1346.9	1442.8	1466.8	1954.5	2604.8	2930.0	3541.6	4764.9	5682.3	5788.9
120°	1334.4	1424.7	1514.9	1537.5	1983.5	2578.2	2875.6	3434.4	4552.1	5390.4	5493.9
122.5°	1416.0	1507.1	1598.2	1620.9	2025.3	2564.4	2833.9	3337.1	4343.6	5098.5	5200.6
125°	1541.2	1624.1	1707.2	1727.9	2081.5	2552.9	2788.6	3216.1	4071.1	4712.2	4806.3
127.5°	1642.6	1726.5	1810.3	1831.2	2137.6	2546.2	2750.5	3117.6	3851.7	4402.3	4481.6
130°	1697.1	1787.3	1877.5	1900.1	2178.7	2550.2	2736.0	3062.7	3716.3	4206.4	4279.8
132.5°	1753.3	1843.5	1933.7	1956.3	2211.9	2552.8	2723.3	3015.8	3600.9	4039.7	4105.4
135°	1836.6	1918.8	2001.1	2021.6	2248.3	2550.5	2701.6	2946.5	3436.5	3803.9	3860.5
137.5°	1921.9	2003.3	2084.7	2105.1	2302.6	2566.1	2697.9	2905.0	3319.2	3629.9	3676.2
140°	1992.7	2067.6	2142.6	2161.3	2335.9	2568.7	2685.2	2864.1	3221.9	3490.2	3533.6
142.5°	2047.0	2116.3	2185.6	2202.9	2363.7	2578.0	2685.2	2842.4	3156.6	3392.4	3429.7
145°	2130.4	2190.9	2251.3	2266.4	2399.9	2578.0	2667.1	2795.6	3052.6	3245.5	3273.7
147.5°	2213.8	2272.6	2331.4	2346.1	2453.1	2595.8	2667.1	2768.2	2970.5	3122.2	3145.6
150°	2268.2	2321.4	2374.6	2387.9	2480.9	2605.1	2667.1	2752.5	2923.4	3051.5	3070.4
152.5°	2324.4	2364.7	2405.0	2415.0	2499.1	2611.1	2667.1	2740.0	2885.9	2995.3	3009.6
155°	2407.9	2437.7	2467.5	2474.9	2539.0	2624.3	2667.1	2725.1	2841.2	2928.2	2937.7
157.5°	2469.5	2498.5	2527.4	2534.7	2578.8	2637.6	2667.1	2712.2	2802.4	2870.2	2876.9
160°	2511.2	2533.7	2556.3	2561.9	2597.0	2643.7	2667.1	2705.7	2783.1	2841.1	2845.0
162.5°	2552.8	2569.8	2586.6	2590.9	2616.3	2650.1	2667.1	2699.7	2765.0	2814.0	2817.6
165°	2598.2	2613.5	2628.8	2632.7	2644.1	2659.4	2667.1	2690.4	2737.1	2772.2	2776.1
167.5°	2639.9	2647.2	2654.4	2656.2	2665.9	2678.8	2685.2	2700.5	2731.1	2754.1	2755.7
170°	2667.1	2674.3	2681.6	2683.5	2684.0	2684.8	2685.2	2700.5	2731.1	2754.1	2754.1
172.5°	2681.6	2683.2	2684.8	2685.2	2685.2	2685.2	2685.2	2697.3	2721.5	2739.7	2738.2
175°	2701.6	2701.6	2701.6	2701.6	2696.1	2688.9	2685.2	2692.9	2708.2	2719.7	2719.7
177.5°	2701.6	2701.6	2701.6	2701.6	2697.3	2691.7	2688.9	2694.9	2707.0	2716.0	2714.4
180°	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6



TEST NUMBER: P938279

CATALOG NUMBER: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	606.4	606.4
2.5°	647.3	643.4
5°	832.6	836.4
7.5°	1121.1	1119.2
10°	1394.1	1411.6
12.5°	1592.9	1596.8
15°	1713.9	1721.6
17.5°	1760.7	1762.6
20°	1762.6	1758.7
22.5°	1741.1	1737.2
25°	1715.8	1713.9
27.5°	1692.4	1694.4
30°	1682.7	1688.5
32.5°	1682.7	1692.4
35°	1686.5	1696.3
37.5°	1684.6	1696.3
40°	1676.8	1690.4
42.5°	1655.3	1665.1
45°	1622.2	1633.9
47.5°	1579.3	1587.1
50°	1524.7	1532.5
52.5°	1456.5	1458.4
55°	1374.6	1382.4
57.5°	1286.8	1288.8
60°	1189.4	1195.2
62.5°	1086.1	1086.1
65°	976.8	980.7
67.5°	863.8	873.5
70°	748.7	750.7
72.5°	635.7	635.7
75°	518.6	520.5
77.5°	407.5	407.5
80°	302.2	304.2
82.5°	208.6	212.5
85°	130.6	130.6
87.5°	60.5	54.6
90°	68.9	68.9
92.5°	276.0	221.2
95°	961.9	795.9
97.5°	2304.9	1989.0
100°	3320.9	2944.5
102.5°	4320.3	3997.9
105°	5594.5	5421.3
107.5°	6429.1	6471.0
110°	6747.4	6928.0



TEST NUMBER: P938279

CATALOG NUMBER: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	6775.8	7053.1
115°	6596.1	6980.5
117.5°	6215.2	6641.4
120°	5908.1	6322.3
122.5°	5609.3	6017.8
125°	5182.7	5559.1
127.5°	4799.2	5116.6
130°	4573.1	4866.4
132.5°	4368.0	4630.7
135°	4087.0	4313.4
137.5°	3861.6	4046.8
140°	3706.8	3880.1
142.5°	3578.7	3727.7
145°	3386.6	3499.3
147.5°	3239.1	3332.5
150°	3146.1	3221.9
152.5°	3066.8	3124.0
155°	2975.5	3013.4
157.5°	2903.4	2930.0
160°	2860.3	2875.6
162.5°	2832.1	2846.6
165°	2791.4	2806.7
167.5°	2762.1	2768.6
170°	2754.1	2754.1
172.5°	2732.6	2727.0
175°	2719.7	2719.7
177.5°	2708.0	2701.6
180°	2701.6	2701.6



TEST NUMBER: P938279
 CATALOG NUMBER: SQ4-FB-150U-050D-B2750-1D-UNV-STD-W-12-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.29	0.79	1.44	3.07	12.81	13.48	13.98	14.63	16.26
	3H	0.31	0.91	1.48	2.07	3.71	14.64	15.24	15.82	16.40	18.04
	4H	0.60	1.17	1.78	2.33	3.98	15.28	15.85	16.46	17.01	18.66
	6H	0.84	1.36	2.03	2.52	4.18	15.71	16.23	16.89	17.39	19.05
	8H	0.90	1.40	2.09	2.58	4.23	15.82	16.32	17.01	17.50	19.15
	12H	0.91	1.38	2.11	2.55	4.23	15.89	16.36	17.08	17.53	19.20
4H	2H	6.82	7.39	8.01	8.55	10.20	13.06	13.63	14.25	14.79	16.44
	3H	8.37	8.84	9.56	10.03	11.69	15.09	15.57	16.29	16.75	18.41
	4H	8.45	8.89	9.65	10.06	11.74	15.85	16.29	17.05	17.47	19.14
	6H	8.45	8.83	9.65	10.02	11.69	16.39	16.76	17.59	17.96	19.62
	8H	8.42	8.77	9.62	9.96	11.65	16.55	16.89	17.74	18.08	19.77
	12H	8.37	8.69	9.58	9.89	11.57	16.63	16.95	17.85	18.15	19.84
8H	4H	9.88	10.23	11.08	11.42	13.11	15.90	16.25	17.10	17.44	19.12
	6H	10.12	10.40	11.33	11.64	13.32	16.52	16.81	17.74	18.04	19.72
	8H	10.13	10.38	11.35	11.59	13.29	16.74	16.99	17.96	18.20	19.90
	12H	10.09	10.31	11.32	11.52	13.25	16.88	17.10	18.11	18.31	20.04
12H	4H	10.02	10.34	11.23	11.53	13.22	15.84	16.16	17.05	17.36	19.05
	6H	10.37	10.62	11.60	11.83	13.53	16.50	16.75	17.72	17.96	19.66
	8H	10.43	10.65	11.66	11.86	13.59	16.73	16.95	17.95	18.15	19.88