

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933890

Luminaire Tested: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933890
REPORT IS A COMBINATION OF REPORTS P933675 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4019.6 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933890
CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · - 135°-315°



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66			
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	62	61	60	55			
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46			
3	84	75	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39			
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	43	40	37	34			
5	71	59	50	44	66	56	48	43	50	44	39	44	39	35	39	35	32	29			
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	26			
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23			
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20			
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18			
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6282	6282	6282	6282
5°	6326	6341	6326	4986
10°	6281	6247	6281	4466
15°	6211	6111	6211	5103
20°	6079	5951	6079	5113
25°	5811	5717	5811	5005
30°	5465	5523	5465	4768
35°	4870	5277	4870	4506
40°	4055	4989	4055	4308
45°	3621	4649	3621	4081
50°	3843	4247	3843	3853
55°	3612	3811	3612	3721
60°	3719	3237	3719	3408
65°	3368	2676	3368	2992
70°	2326	2132	2326	2508
75°	2032	1576	2032	1888
80°	1624	1041	1624	1135
85°	918	552	918	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 5554 cd/sqm



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.7	2.3
10°-20°	260.3	6.5
20°-30°	402.3	10.0
30°-40°	480.3	11.9
40°-50°	483.1	12.0
50°-60°	420.3	10.5
60°-70°	298.0	7.4
70°-80°	157.7	3.9
80°-90°	40.1	1.0
90°-100°	104.2	2.6
100°-110°	274.0	6.8
110°-120°	284.1	7.1
120°-130°	227.9	5.7
130°-140°	178.8	4.4
140°-150°	137.2	3.4
150°-160°	98.8	2.5
160°-170°	60.5	1.5
170°-180°	20.4	0.5
0°-30°	754.2	18.8
0°-40°	1234.5	30.7
0°-60°	2137.9	53.2
0°-90°	2633.7	65.5
90°-120°	662.2	16.5
90°-150°	1206.1	30.0
90°-180°	1386.0	34.5
0°-180°	4019.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1016	1016	1016	1016	1016	
5°	1020	1052	1020	827	1020	97
15°	974	1042	974	870	974	274
25°	858	972	858	851	858	394
35°	652	868	652	741	652	404
45°	421	715	421	627	421	337
55°	343	527	343	515	343	315
65°	238	318	238	356	238	228
75°	90	151	90	181	90	95
85°	15	38	15	33	15	21
90°	1	5	1	5	1	2
95°	14	63	14	63	14	15
105°	49	429	49	429	49	52
115°	88	552	88	552	88	87
125°	122	440	122	440	122	108
135°	145	341	145	341	145	112
145°	169	277	169	277	169	106
155°	190	238	190	238	190	88
165°	206	222	206	222	206	58
175°	214	215	214	215	214	20
180°	214	214	214	214	214	



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5
2.5°	1024.1	1024.1	1029.9	1031.8	1031.8	1028.9	1026.1	1028.9	1037.6	1040.5	1039.5
5°	1020.2	1028.0	1038.6	1040.5	1042.4	1041.4	1039.5	1041.4	1051.0	1053.0	1053.9
7.5°	1012.6	1027.0	1040.5	1043.3	1046.2	1043.3	1042.4	1044.3	1053.9	1055.8	1055.8
10°	1002.9	1023.2	1038.6	1040.5	1043.3	1040.5	1040.5	1044.3	1053.9	1055.8	1056.8
12.5°	989.6	1017.4	1031.8	1033.7	1037.6	1036.7	1035.6	1039.5	1049.1	1051.0	1051.0
15°	974.2	1006.9	1020.2	1022.2	1028.9	1027.0	1027.0	1030.8	1041.4	1044.3	1043.3
17.5°	953.0	993.4	1008.8	1011.6	1016.4	1015.5	1016.4	1020.2	1029.9	1031.8	1032.7
20°	929.0	975.2	993.4	996.3	1001.0	1001.0	1001.0	1005.9	1015.5	1019.3	1019.3
22.5°	896.4	955.9	975.2	977.1	982.8	982.8	984.7	991.5	1000.1	1001.0	1001.0
25°	857.9	934.8	951.1	956.9	962.6	965.5	968.4	972.3	975.2	974.2	975.2
27.5°	817.6	907.8	929.0	932.8	940.6	943.4	947.3	948.2	949.2	952.0	950.1
30°	772.4	870.4	902.1	905.9	918.4	920.3	916.5	918.4	923.2	925.2	927.1
32.5°	721.5	814.7	874.2	882.9	894.5	888.6	887.7	890.5	898.3	898.3	900.2
35°	652.4	771.4	848.3	856.0	864.7	857.9	861.8	862.7	867.5	870.4	869.4
37.5°	576.4	734.0	821.4	827.1	833.9	825.2	831.0	833.9	837.7	835.8	835.8
40°	509.2	675.4	789.7	793.5	799.3	792.6	798.4	800.3	802.2	800.3	799.3
42.5°	459.3	611.0	756.1	760.8	757.0	761.8	763.8	767.6	764.8	760.8	760.8
45°	420.8	593.7	719.6	725.3	719.6	727.2	730.1	730.1	721.5	719.6	718.6
47.5°	408.3	559.2	683.1	683.1	680.2	689.8	694.6	687.9	679.2	676.3	676.3
50°	407.3	520.7	633.1	629.2	642.7	654.3	649.4	642.7	636.0	625.4	625.4
52.5°	369.9	473.6	568.7	583.1	604.3	611.0	603.4	596.6	585.0	580.3	576.4
55°	342.9	424.6	510.2	539.0	561.1	569.7	555.3	548.6	531.3	528.4	526.5
57.5°	337.2	353.5	456.3	492.9	519.7	518.8	510.2	497.7	483.2	480.4	479.4
60°	309.3	255.6	398.7	442.0	469.8	466.9	459.3	447.7	434.2	432.3	430.4
62.5°	280.5	185.5	333.4	382.4	421.7	420.8	414.1	396.8	387.2	382.4	378.6
65°	238.3	155.7	237.3	318.0	374.6	376.6	362.2	349.7	339.1	333.4	332.4
67.5°	181.5	126.8	160.4	265.2	329.6	327.6	309.3	303.6	290.1	287.3	281.5
70°	134.5	84.5	111.4	215.2	285.4	280.5	266.2	259.4	246.9	240.2	236.4
72.5°	111.4	68.2	81.7	167.1	240.2	234.5	221.9	214.2	203.7	197.9	194.1
75°	90.3	72.0	62.5	124.0	195.0	191.2	179.6	172.0	163.3	155.7	156.6
77.5°	66.3	67.2	49.9	91.3	154.7	148.9	142.2	132.6	128.7	121.1	121.1
80°	49.9	52.8	37.4	62.5	111.4	111.4	105.7	98.9	92.3	88.4	88.4
82.5°	33.6	33.6	27.9	39.3	75.9	73.1	69.1	67.2	63.4	61.5	61.5
85°	15.4	19.2	17.3	24.0	41.4	43.3	43.3	41.4	40.4	38.4	39.3
87.5°	4.8	8.7	10.6	13.5	21.1	22.1	23.0	23.0	23.0	24.0	24.0
90°	1.4	2.6	3.7	4.0	6.3	9.4	10.9	9.6	7.3	5.4	5.4
92.5°	5.7	15.5	25.2	27.7	39.0	54.0	61.4	53.8	38.6	27.2	26.2
95°	13.8	31.6	49.5	54.0	95.8	151.6	179.4	160.2	121.5	92.5	89.3
97.5°	23.8	39.5	55.3	59.2	129.0	222.0	268.5	256.3	232.0	213.6	207.4
100°	31.6	45.8	60.2	63.7	141.1	244.4	296.0	296.8	298.6	300.0	292.5
102.5°	38.2	51.6	64.8	68.2	146.7	251.4	303.7	319.3	350.4	373.8	367.4
105°	49.4	60.6	71.9	74.8	150.8	252.1	302.8	337.7	407.5	459.8	456.4
107.5°	60.8	71.3	81.8	84.5	151.6	240.9	285.6	334.3	431.7	504.6	505.5
110°	68.6	78.1	87.6	90.0	150.4	231.0	271.3	325.8	434.5	516.1	519.6



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	76.2	85.3	94.3	96.6	150.4	222.3	258.2	313.9	425.3	508.7	514.2
115°	87.7	96.1	104.4	106.5	151.8	212.3	242.6	296.2	403.5	483.9	491.5
117.5°	99.0	106.6	114.1	116.0	154.6	206.1	231.9	280.3	377.0	449.6	458.0
120°	105.6	112.8	119.9	121.7	157.0	204.1	227.6	271.8	360.2	426.6	434.8
122.5°	112.0	119.3	126.4	128.3	160.2	202.9	224.2	264.1	343.7	403.5	411.6
125°	122.0	128.5	135.1	136.8	164.7	202.1	220.7	254.5	322.2	372.9	380.4
127.5°	130.0	136.6	143.2	144.9	169.1	201.5	217.6	246.7	304.8	348.4	354.7
130°	134.3	141.4	148.5	150.3	172.4	201.8	216.5	242.4	294.0	332.8	338.6
132.5°	138.8	145.9	153.0	154.8	175.1	202.1	215.5	238.7	285.0	319.6	324.8
135°	145.4	151.8	158.3	160.0	177.9	201.9	213.8	233.2	272.0	301.0	305.5
137.5°	152.1	158.5	164.9	166.6	182.2	203.1	213.5	230.0	262.7	287.3	290.9
140°	157.7	163.6	169.5	171.0	184.9	203.3	212.5	226.6	255.0	276.2	279.6
142.5°	162.0	167.4	173.0	174.3	187.0	204.0	212.5	224.9	249.8	268.5	271.4
145°	168.6	173.3	178.1	179.3	189.9	204.0	211.1	221.2	241.5	256.8	259.0
147.5°	175.1	179.8	184.5	185.7	194.2	205.4	211.1	219.1	235.0	247.1	248.9
150°	179.4	183.6	187.9	189.0	196.3	206.2	211.1	217.8	231.3	241.4	243.0
152.5°	183.9	187.1	190.3	191.1	197.8	206.7	211.1	216.8	228.3	237.0	238.2
155°	190.5	192.9	195.3	195.9	200.9	207.7	211.1	215.6	224.8	231.7	232.4
157.5°	195.4	197.7	200.0	200.5	204.1	208.8	211.1	214.6	221.8	227.1	227.7
160°	198.7	200.5	202.3	202.7	205.5	209.2	211.1	214.1	220.2	224.8	225.1
162.5°	202.0	203.3	204.7	205.0	207.0	209.7	211.1	213.6	218.8	222.7	223.0
165°	205.6	206.8	208.0	208.3	209.2	210.5	211.1	212.9	216.6	219.4	219.6
167.5°	208.9	209.4	210.0	210.2	211.0	212.0	212.5	213.7	216.1	217.9	218.0
170°	211.1	211.6	212.2	212.3	212.4	212.5	212.5	213.7	216.1	217.9	217.9
172.5°	212.2	212.3	212.5	212.5	212.5	212.5	212.5	213.4	215.4	216.8	216.7
175°	213.8	213.8	213.8	213.8	213.3	212.8	212.5	213.1	214.3	215.3	215.3
177.5°	213.8	213.8	213.8	213.8	213.4	213.0	212.8	213.3	214.2	215.0	214.9
180°	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5
2.5°	1041.4	1038.6	1041.4	1039.5	1040.5	1037.6	1028.9	1026.1	1028.9	1031.8	1031.8
5°	1053.9	1051.9	1053.9	1053.9	1053.0	1051.0	1041.4	1039.5	1041.4	1042.4	1040.5
7.5°	1057.8	1054.9	1057.8	1055.8	1055.8	1053.9	1044.3	1042.4	1043.3	1046.2	1043.3
10°	1057.8	1054.9	1057.8	1056.8	1055.8	1053.9	1044.3	1040.5	1040.5	1043.3	1040.5
12.5°	1053.0	1051.0	1053.0	1051.0	1051.0	1049.1	1039.5	1035.6	1036.7	1037.6	1033.7
15°	1045.2	1042.4	1045.2	1043.3	1044.3	1041.4	1030.8	1027.0	1027.0	1028.9	1022.2
17.5°	1033.7	1029.9	1033.7	1032.7	1031.8	1029.9	1020.2	1016.4	1015.5	1016.4	1011.6
20°	1020.2	1017.4	1020.2	1019.3	1019.3	1015.5	1005.9	1001.0	1001.0	1001.0	996.3
22.5°	999.1	996.3	999.1	1001.0	1001.0	1000.1	991.5	984.7	982.8	982.8	977.1
25°	975.2	972.3	975.2	975.2	974.2	975.2	972.3	968.4	965.5	962.6	956.9
27.5°	952.0	950.1	952.0	950.1	952.0	949.2	948.2	947.3	943.4	940.6	932.8
30°	929.0	927.1	929.0	927.1	925.2	923.2	918.4	916.5	920.3	918.4	905.9
32.5°	900.2	898.3	900.2	900.2	898.3	898.3	890.5	887.7	888.6	894.5	882.9
35°	870.4	867.5	870.4	869.4	870.4	867.5	862.7	861.8	857.9	864.7	856.0
37.5°	835.8	833.0	835.8	835.8	835.8	837.7	833.9	831.0	825.2	833.9	827.1
40°	800.3	796.5	800.3	799.3	800.3	802.2	800.3	798.4	792.6	799.3	793.5
42.5°	759.9	758.9	759.9	760.8	760.8	764.8	767.6	763.8	761.8	757.0	760.8
45°	716.7	714.7	716.7	718.6	719.6	721.5	730.1	730.1	727.2	719.6	725.3
47.5°	670.6	665.7	670.6	676.3	676.3	679.2	687.9	694.6	689.8	680.2	683.1
50°	621.6	622.6	621.6	625.4	625.4	636.0	642.7	649.4	654.3	642.7	629.2
52.5°	573.6	572.6	573.6	576.4	580.3	585.0	596.6	603.4	611.0	604.3	583.1
55°	525.5	527.4	525.5	526.5	528.4	531.3	548.6	555.3	569.7	561.1	539.0
57.5°	477.5	474.6	477.5	479.4	480.4	483.2	497.7	510.2	518.8	519.7	492.9
60°	421.7	417.9	421.7	430.4	432.3	434.2	447.7	459.3	466.9	469.8	442.0
62.5°	372.7	366.1	372.7	378.6	382.4	387.2	396.8	414.1	420.8	421.7	382.4
65°	320.9	318.0	320.9	332.4	333.4	339.1	349.7	362.2	376.6	374.6	318.0
67.5°	273.8	273.8	273.8	281.5	287.3	290.1	303.6	309.3	327.6	329.6	265.2
70°	230.5	229.6	230.5	236.4	240.2	246.9	259.4	266.2	280.5	285.4	215.2
72.5°	189.3	188.3	189.3	194.1	197.9	203.7	214.2	221.9	234.5	240.2	167.1
75°	152.8	150.8	152.8	156.6	155.7	163.3	172.0	179.6	191.2	195.0	124.0
77.5°	117.2	117.2	117.2	121.1	121.1	128.7	132.6	142.2	148.9	154.7	91.3
80°	87.4	86.4	87.4	88.4	88.4	92.3	98.9	105.7	111.4	111.4	62.5
82.5°	61.5	59.6	61.5	61.5	61.5	63.4	67.2	69.1	73.1	75.9	39.3
85°	38.4	38.4	38.4	39.3	38.4	40.4	41.4	43.3	43.3	41.4	24.0
87.5°	25.0	24.0	25.0	24.0	24.0	23.0	23.0	23.0	22.1	21.1	13.5
90°	5.4	5.4	5.4	5.4	5.4	7.3	9.6	10.9	9.4	6.3	4.0
92.5°	21.8	17.5	21.8	26.2	27.2	38.6	53.8	61.4	54.0	39.0	27.7
95°	76.1	63.0	76.1	89.3	92.5	121.5	160.2	179.4	151.6	95.8	54.0
97.5°	182.4	157.4	182.4	207.4	213.6	232.0	256.3	268.5	222.0	129.0	59.2
100°	262.8	233.0	262.8	292.5	300.0	298.6	296.8	296.0	244.4	141.1	63.7
102.5°	341.9	316.4	341.9	367.4	373.8	350.4	319.3	303.7	251.4	146.7	68.2
105°	442.7	429.0	442.7	456.4	459.8	407.5	337.7	302.8	252.1	150.8	74.8
107.5°	508.7	512.1	508.7	505.5	504.6	431.7	334.3	285.6	240.9	151.6	84.5
110°	533.9	548.3	533.9	519.6	516.1	434.5	325.8	271.3	231.0	150.4	90.0



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	536.1	558.1	536.1	514.2	508.7	425.3	313.9	258.2	222.3	150.4	96.6
115°	521.9	552.4	521.9	491.5	483.9	403.5	296.2	242.6	212.3	151.8	106.5
117.5°	491.8	525.5	491.8	458.0	449.6	377.0	280.3	231.9	206.1	154.6	116.0
120°	467.6	500.3	467.6	434.8	426.6	360.2	271.8	227.6	204.1	157.0	121.7
122.5°	443.9	476.2	443.9	411.6	403.5	343.7	264.1	224.2	202.9	160.2	128.3
125°	410.1	439.9	410.1	380.4	372.9	322.2	254.5	220.7	202.1	164.7	136.8
127.5°	379.8	404.9	379.8	354.7	348.4	304.8	246.7	217.6	201.5	169.1	144.9
130°	361.8	385.1	361.8	338.6	332.8	294.0	242.4	216.5	201.8	172.4	150.3
132.5°	345.6	366.4	345.6	324.8	319.6	285.0	238.7	215.5	202.1	175.1	154.8
135°	323.4	341.3	323.4	305.5	301.0	272.0	233.2	213.8	201.9	177.9	160.0
137.5°	305.6	320.2	305.6	290.9	287.3	262.7	230.0	213.5	203.1	182.2	166.6
140°	293.3	307.0	293.3	279.6	276.2	255.0	226.6	212.5	203.3	184.9	171.0
142.5°	283.2	295.0	283.2	271.4	268.5	249.8	224.9	212.5	204.0	187.0	174.3
145°	268.0	277.0	268.0	259.0	256.8	241.5	221.2	211.1	204.0	189.9	179.3
147.5°	256.3	263.7	256.3	248.9	247.1	235.0	219.1	211.1	205.4	194.2	185.7
150°	249.0	255.0	249.0	243.0	241.4	231.3	217.8	211.1	206.2	196.3	189.0
152.5°	242.7	247.2	242.7	238.2	237.0	228.3	216.8	211.1	206.7	197.8	191.1
155°	235.4	238.5	235.4	232.4	231.7	224.8	215.6	211.1	207.7	200.9	195.9
157.5°	229.8	231.9	229.8	227.7	227.1	221.8	214.6	211.1	208.8	204.1	200.5
160°	226.3	227.6	226.3	225.1	224.8	220.2	214.1	211.1	209.2	205.5	202.7
162.5°	224.1	225.3	224.1	223.0	222.7	218.8	213.6	211.1	209.7	207.0	205.0
165°	220.9	222.1	220.9	219.6	219.4	216.6	212.9	211.1	210.5	209.2	208.3
167.5°	218.6	219.1	218.6	218.0	217.9	216.1	213.7	212.5	212.0	211.0	210.2
170°	217.9	217.9	217.9	217.9	217.9	216.1	213.7	212.5	212.5	212.4	212.3
172.5°	216.2	215.8	216.2	216.7	216.8	215.4	213.4	212.5	212.5	212.5	212.5
175°	215.3	215.3	215.3	215.3	215.3	214.3	213.1	212.5	212.8	213.3	213.8
177.5°	214.3	213.8	214.3	214.9	215.0	214.2	213.3	212.8	213.0	213.4	213.8
180°	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5
2.5°	1029.9	1024.1	1024.1	1014.5	1010.7	1007.8	1002.9	988.6	984.7	980.9	986.6
5°	1038.6	1028.0	1020.2	1002.9	988.6	982.8	964.6	930.0	906.9	889.6	880.0
7.5°	1040.5	1027.0	1012.6	985.7	951.1	935.7	880.0	816.6	799.3	784.0	774.3
10°	1038.6	1023.2	1002.9	962.6	881.0	854.1	798.4	757.0	746.4	743.6	746.4
12.5°	1031.8	1017.4	989.6	922.2	807.9	789.7	757.0	733.1	731.1	735.9	761.8
15°	1020.2	1006.9	974.2	868.5	767.6	754.2	731.1	722.5	733.1	766.7	844.5
17.5°	1008.8	993.4	953.0	815.7	736.9	727.2	710.9	728.2	787.8	833.0	858.8
20°	993.4	975.2	929.0	777.2	714.7	706.1	698.4	776.2	821.4	837.7	852.1
22.5°	975.2	955.9	896.4	750.3	691.7	685.0	689.8	803.2	821.4	833.0	845.5
25°	951.1	934.8	857.9	729.1	673.5	665.7	684.1	800.3	810.8	813.8	838.7
27.5°	929.0	907.8	817.6	709.9	651.4	648.4	688.8	787.8	795.5	798.4	825.2
30°	902.1	870.4	772.4	689.8	628.3	627.3	689.8	772.4	770.5	778.1	805.1
32.5°	874.2	814.7	721.5	664.8	606.2	605.3	683.1	749.4	747.5	758.0	778.1
35°	848.3	771.4	652.4	636.0	578.3	579.3	666.7	722.5	723.4	733.1	745.5
37.5°	821.4	734.0	576.4	604.3	551.4	551.4	644.6	697.4	695.5	698.4	715.8
40°	789.7	675.4	509.2	563.0	526.5	523.6	617.7	670.6	663.8	662.9	686.9
42.5°	756.1	611.0	459.3	508.3	497.7	493.8	585.0	637.9	625.4	628.3	659.0
45°	719.6	593.7	420.8	429.5	467.9	465.0	549.5	600.4	591.8	599.5	631.2
47.5°	683.1	559.2	408.3	356.4	436.1	435.2	510.2	563.9	559.2	566.8	600.4
50°	633.1	520.7	407.3	305.5	400.6	404.4	463.1	528.4	528.4	535.1	570.7
52.5°	568.7	473.6	369.9	276.7	359.3	370.8	421.7	497.7	499.6	506.3	538.0
55°	510.2	424.6	342.9	254.6	310.3	335.3	381.4	465.9	469.8	476.5	505.3
57.5°	456.3	353.5	337.2	228.6	265.2	289.2	345.9	435.2	437.1	442.9	470.7
60°	398.7	255.6	309.3	200.7	225.8	244.0	313.1	398.7	405.4	409.2	433.3
62.5°	333.4	185.5	280.5	181.5	206.6	210.4	286.3	364.1	372.7	375.6	390.0
65°	237.3	155.7	238.3	165.2	186.4	187.4	257.5	328.5	336.3	341.0	351.6
67.5°	160.4	126.8	181.5	149.8	171.0	172.0	229.6	287.3	297.9	301.7	308.4
70°	111.4	84.5	134.5	133.5	153.8	155.7	199.8	249.8	259.4	262.2	266.2
72.5°	81.7	68.2	111.4	120.0	135.4	137.4	169.1	207.5	217.2	220.0	221.9
75°	62.5	72.0	90.3	104.8	115.3	116.2	138.4	169.1	175.8	177.7	178.7
77.5°	49.9	67.2	66.3	84.5	94.2	92.3	108.6	130.6	136.4	136.4	136.4
80°	37.4	52.8	49.9	60.5	69.1	67.2	77.8	93.2	95.1	97.0	96.1
82.5°	27.9	33.6	33.6	38.4	46.1	44.2	51.9	60.5	60.5	60.5	62.5
85°	17.3	19.2	15.4	20.2	26.0	25.0	28.8	32.7	33.6	33.6	31.7
87.5°	10.6	8.7	4.8	7.6	11.6	11.6	13.5	14.4	13.5	13.5	13.5
90°	3.7	2.6	1.4	2.6	3.7	4.0	6.3	9.4	10.9	9.6	7.3
92.5°	25.2	15.5	5.7	15.5	25.2	27.7	39.0	54.0	61.4	53.8	38.6
95°	49.5	31.6	13.8	31.6	49.5	54.0	95.8	151.6	179.4	160.2	121.5
97.5°	55.3	39.5	23.8	39.5	55.3	59.2	129.0	222.0	268.5	256.3	232.0
100°	60.2	45.8	31.6	45.8	60.2	63.7	141.1	244.4	296.0	296.8	298.6
102.5°	64.8	51.6	38.2	51.6	64.8	68.2	146.7	251.4	303.7	319.3	350.4
105°	71.9	60.6	49.4	60.6	71.9	74.8	150.8	252.1	302.8	337.7	407.5
107.5°	81.8	71.3	60.8	71.3	81.8	84.5	151.6	240.9	285.6	334.3	431.7
110°	87.6	78.1	68.6	78.1	87.6	90.0	150.4	231.0	271.3	325.8	434.5



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	94.3	85.3	76.2	85.3	94.3	96.6	150.4	222.3	258.2	313.9	425.3
115°	104.4	96.1	87.7	96.1	104.4	106.5	151.8	212.3	242.6	296.2	403.5
117.5°	114.1	106.6	99.0	106.6	114.1	116.0	154.6	206.1	231.9	280.3	377.0
120°	119.9	112.8	105.6	112.8	119.9	121.7	157.0	204.1	227.6	271.8	360.2
122.5°	126.4	119.3	112.0	119.3	126.4	128.3	160.2	202.9	224.2	264.1	343.7
125°	135.1	128.5	122.0	128.5	135.1	136.8	164.7	202.1	220.7	254.5	322.2
127.5°	143.2	136.6	130.0	136.6	143.2	144.9	169.1	201.5	217.6	246.7	304.8
130°	148.5	141.4	134.3	141.4	148.5	150.3	172.4	201.8	216.5	242.4	294.0
132.5°	153.0	145.9	138.8	145.9	153.0	154.8	175.1	202.1	215.5	238.7	285.0
135°	158.3	151.8	145.4	151.8	158.3	160.0	177.9	201.9	213.8	233.2	272.0
137.5°	164.9	158.5	152.1	158.5	164.9	166.6	182.2	203.1	213.5	230.0	262.7
140°	169.5	163.6	157.7	163.6	169.5	171.0	184.9	203.3	212.5	226.6	255.0
142.5°	173.0	167.4	162.0	167.4	173.0	174.3	187.0	204.0	212.5	224.9	249.8
145°	178.1	173.3	168.6	173.3	178.1	179.3	189.9	204.0	211.1	221.2	241.5
147.5°	184.5	179.8	175.1	179.8	184.5	185.7	194.2	205.4	211.1	219.1	235.0
150°	187.9	183.6	179.4	183.6	187.9	189.0	196.3	206.2	211.1	217.8	231.3
152.5°	190.3	187.1	183.9	187.1	190.3	191.1	197.8	206.7	211.1	216.8	228.3
155°	195.3	192.9	190.5	192.9	195.3	195.9	200.9	207.7	211.1	215.6	224.8
157.5°	200.0	197.7	195.4	197.7	200.0	200.5	204.1	208.8	211.1	214.6	221.8
160°	202.3	200.5	198.7	200.5	202.3	202.7	205.5	209.2	211.1	214.1	220.2
162.5°	204.7	203.3	202.0	203.3	204.7	205.0	207.0	209.7	211.1	213.6	218.8
165°	208.0	206.8	205.6	206.8	208.0	208.3	209.2	210.5	211.1	212.9	216.6
167.5°	210.0	209.4	208.9	209.4	210.0	210.2	211.0	212.0	212.5	213.7	216.1
170°	212.2	211.6	211.1	211.6	212.2	212.3	212.4	212.5	212.5	213.7	216.1
172.5°	212.5	212.3	212.2	212.3	212.5	212.5	212.5	212.5	212.5	213.4	215.4
175°	213.8	213.8	213.8	213.8	213.8	213.8	213.3	212.8	212.5	213.1	214.3
177.5°	213.8	213.8	213.8	213.8	213.8	213.8	213.4	213.0	212.8	213.3	214.2
180°	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5	1015.5
2.5°	979.9	977.1	980.9	970.3	980.9	977.1	979.9	986.6	980.9	984.7	988.6
5°	859.9	855.0	839.6	827.1	839.6	855.0	859.9	880.0	889.6	906.9	930.0
7.5°	768.6	764.8	760.8	753.2	760.8	764.8	768.6	774.3	784.0	799.3	816.6
10°	748.4	749.4	755.1	754.2	755.1	749.4	748.4	746.4	743.6	746.4	757.0
12.5°	800.3	808.9	840.6	838.7	840.6	808.9	800.3	761.8	735.9	731.1	733.1
15°	859.9	862.7	869.4	870.4	869.4	862.7	859.9	844.5	766.7	733.1	722.5
17.5°	865.6	866.6	871.3	871.3	871.3	866.6	865.6	858.8	833.0	787.8	728.2
20°	860.8	862.7	872.3	874.2	872.3	862.7	860.8	852.1	837.7	821.4	776.2
22.5°	858.8	862.7	870.4	869.4	870.4	862.7	858.8	845.5	833.0	821.4	803.2
25°	849.3	849.3	850.2	851.2	850.2	849.3	849.3	838.7	813.8	810.8	800.3
27.5°	829.1	831.0	836.8	835.8	836.8	831.0	829.1	825.2	798.4	795.5	787.8
30°	810.8	808.9	804.1	800.3	804.1	808.9	810.8	805.1	778.1	770.5	772.4
32.5°	780.1	775.3	770.5	767.6	770.5	775.3	780.1	778.1	758.0	747.5	749.4
35°	743.6	744.5	743.6	740.7	743.6	744.5	743.6	745.5	733.1	723.4	722.5
37.5°	717.7	719.6	718.6	714.7	718.6	719.6	717.7	715.8	698.4	695.5	697.4
40°	690.8	691.7	690.8	687.9	690.8	691.7	690.8	686.9	662.9	663.8	670.6
42.5°	664.8	663.8	661.0	659.0	661.0	663.8	664.8	659.0	628.3	625.4	637.9
45°	635.1	636.0	630.2	627.3	630.2	636.0	635.1	631.2	599.5	591.8	600.4
47.5°	605.3	605.3	600.4	597.5	600.4	605.3	605.3	600.4	566.8	559.2	563.9
50°	573.6	572.6	565.8	564.9	565.8	572.6	573.6	570.7	535.1	528.4	528.4
52.5°	537.0	537.0	538.0	540.0	538.0	537.0	537.0	538.0	506.3	499.6	497.7
55°	505.3	506.3	513.0	514.9	513.0	506.3	505.3	505.3	476.5	469.8	465.9
57.5°	472.6	472.6	477.5	477.5	477.5	472.6	472.6	470.7	442.9	437.1	435.2
60°	435.2	437.1	440.9	440.0	440.9	437.1	435.2	433.3	409.2	405.4	398.7
62.5°	395.8	397.8	398.7	396.8	398.7	397.8	395.8	390.0	375.6	372.7	364.1
65°	354.5	356.4	357.4	355.5	357.4	356.4	354.5	351.6	341.0	336.3	328.5
67.5°	312.2	311.2	310.3	314.2	310.3	311.2	312.2	308.4	301.7	297.9	287.3
70°	269.0	269.0	268.1	270.0	268.1	269.0	269.0	266.2	262.2	259.4	249.8
72.5°	222.9	221.9	225.8	222.9	225.8	221.9	222.9	221.9	220.0	217.2	207.5
75°	177.7	179.6	177.7	180.6	177.7	179.6	177.7	178.7	177.7	175.8	169.1
77.5°	135.4	137.4	135.4	135.4	135.4	137.4	135.4	136.4	136.4	136.4	130.6
80°	96.1	95.1	95.1	94.2	95.1	95.1	96.1	96.1	97.0	95.1	93.2
82.5°	61.5	60.5	60.5	62.5	60.5	60.5	61.5	62.5	60.5	60.5	60.5
85°	33.6	34.6	32.7	32.7	32.7	34.6	33.6	31.7	33.6	33.6	32.7
87.5°	12.5	11.6	11.6	11.6	11.6	11.6	12.5	13.5	13.5	13.5	14.4
90°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	7.3	9.6	10.9	9.4
92.5°	27.2	26.2	21.8	17.5	21.8	26.2	27.2	38.6	53.8	61.4	54.0
95°	92.5	89.3	76.1	63.0	76.1	89.3	92.5	121.5	160.2	179.4	151.6
97.5°	213.6	207.4	182.4	157.4	182.4	207.4	213.6	232.0	256.3	268.5	222.0
100°	300.0	292.5	262.8	233.0	262.8	292.5	300.0	298.6	296.8	296.0	244.4
102.5°	373.8	367.4	341.9	316.4	341.9	367.4	373.8	350.4	319.3	303.7	251.4
105°	459.8	456.4	442.7	429.0	442.7	456.4	459.8	407.5	337.7	302.8	252.1
107.5°	504.6	505.5	508.7	512.1	508.7	505.5	504.6	431.7	334.3	285.6	240.9
110°	516.1	519.6	533.9	548.3	533.9	519.6	516.1	434.5	325.8	271.3	231.0



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	508.7	514.2	536.1	558.1	536.1	514.2	508.7	425.3	313.9	258.2	222.3
115°	483.9	491.5	521.9	552.4	521.9	491.5	483.9	403.5	296.2	242.6	212.3
117.5°	449.6	458.0	491.8	525.5	491.8	458.0	449.6	377.0	280.3	231.9	206.1
120°	426.6	434.8	467.6	500.3	467.6	434.8	426.6	360.2	271.8	227.6	204.1
122.5°	403.5	411.6	443.9	476.2	443.9	411.6	403.5	343.7	264.1	224.2	202.9
125°	372.9	380.4	410.1	439.9	410.1	380.4	372.9	322.2	254.5	220.7	202.1
127.5°	348.4	354.7	379.8	404.9	379.8	354.7	348.4	304.8	246.7	217.6	201.5
130°	332.8	338.6	361.8	385.1	361.8	338.6	332.8	294.0	242.4	216.5	201.8
132.5°	319.6	324.8	345.6	366.4	345.6	324.8	319.6	285.0	238.7	215.5	202.1
135°	301.0	305.5	323.4	341.3	323.4	305.5	301.0	272.0	233.2	213.8	201.9
137.5°	287.3	290.9	305.6	320.2	305.6	290.9	287.3	262.7	230.0	213.5	203.1
140°	276.2	279.6	293.3	307.0	293.3	279.6	276.2	255.0	226.6	212.5	203.3
142.5°	268.5	271.4	283.2	295.0	283.2	271.4	268.5	249.8	224.9	212.5	204.0
145°	256.8	259.0	268.0	277.0	268.0	259.0	256.8	241.5	221.2	211.1	204.0
147.5°	247.1	248.9	256.3	263.7	256.3	248.9	247.1	235.0	219.1	211.1	205.4
150°	241.4	243.0	249.0	255.0	249.0	243.0	241.4	231.3	217.8	211.1	206.2
152.5°	237.0	238.2	242.7	247.2	242.7	238.2	237.0	228.3	216.8	211.1	206.7
155°	231.7	232.4	235.4	238.5	235.4	232.4	231.7	224.8	215.6	211.1	207.7
157.5°	227.1	227.7	229.8	231.9	229.8	227.7	227.1	221.8	214.6	211.1	208.8
160°	224.8	225.1	226.3	227.6	226.3	225.1	224.8	220.2	214.1	211.1	209.2
162.5°	222.7	223.0	224.1	225.3	224.1	223.0	222.7	218.8	213.6	211.1	209.7
165°	219.4	219.6	220.9	222.1	220.9	219.6	219.4	216.6	212.9	211.1	210.5
167.5°	217.9	218.0	218.6	219.1	218.6	218.0	217.9	216.1	213.7	212.5	212.0
170°	217.9	217.9	217.9	217.9	217.9	217.9	217.9	216.1	213.7	212.5	212.5
172.5°	216.8	216.7	216.2	215.8	216.2	216.7	216.8	215.4	213.4	212.5	212.5
175°	215.3	215.3	215.3	215.3	215.3	215.3	215.3	214.3	213.1	212.5	212.8
177.5°	215.0	214.9	214.3	213.8	214.3	214.9	215.0	214.2	213.3	212.8	213.0
180°	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1015.5	1015.5	1015.5	1015.5	1015.5
2.5°	1002.9	1007.8	1010.7	1014.5	1024.1
5°	964.6	982.8	988.6	1002.9	1020.2
7.5°	880.0	935.7	951.1	985.7	1012.6
10°	798.4	854.1	881.0	962.6	1002.9
12.5°	757.0	789.7	807.9	922.2	989.6
15°	731.1	754.2	767.6	868.5	974.2
17.5°	710.9	727.2	736.9	815.7	953.0
20°	698.4	706.1	714.7	777.2	929.0
22.5°	689.8	685.0	691.7	750.3	896.4
25°	684.1	665.7	673.5	729.1	857.9
27.5°	688.8	648.4	651.4	709.9	817.6
30°	689.8	627.3	628.3	689.8	772.4
32.5°	683.1	605.3	606.2	664.8	721.5
35°	666.7	579.3	578.3	636.0	652.4
37.5°	644.6	551.4	551.4	604.3	576.4
40°	617.7	523.6	526.5	563.0	509.2
42.5°	585.0	493.8	497.7	508.3	459.3
45°	549.5	465.0	467.9	429.5	420.8
47.5°	510.2	435.2	436.1	356.4	408.3
50°	463.1	404.4	400.6	305.5	407.3
52.5°	421.7	370.8	359.3	276.7	369.9
55°	381.4	335.3	310.3	254.6	342.9
57.5°	345.9	289.2	265.2	228.6	337.2
60°	313.1	244.0	225.8	200.7	309.3
62.5°	286.3	210.4	206.6	181.5	280.5
65°	257.5	187.4	186.4	165.2	238.3
67.5°	229.6	172.0	171.0	149.8	181.5
70°	199.8	155.7	153.8	133.5	134.5
72.5°	169.1	137.4	135.4	120.0	111.4
75°	138.4	116.2	115.3	104.8	90.3
77.5°	108.6	92.3	94.2	84.5	66.3
80°	77.8	67.2	69.1	60.5	49.9
82.5°	51.9	44.2	46.1	38.4	33.6
85°	28.8	25.0	26.0	20.2	15.4
87.5°	13.5	11.6	11.6	7.6	4.8
90°	6.3	4.0	3.7	2.6	1.4
92.5°	39.0	27.7	25.2	15.5	5.7
95°	95.8	54.0	49.5	31.6	13.8
97.5°	129.0	59.2	55.3	39.5	23.8
100°	141.1	63.7	60.2	45.8	31.6
102.5°	146.7	68.2	64.8	51.6	38.2
105°	150.8	74.8	71.9	60.6	49.4
107.5°	151.6	84.5	81.8	71.3	60.8
110°	150.4	90.0	87.6	78.1	68.6



TEST NUMBER: P933890

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	150.4	96.6	94.3	85.3	76.2
115°	151.8	106.5	104.4	96.1	87.7
117.5°	154.6	116.0	114.1	106.6	99.0
120°	157.0	121.7	119.9	112.8	105.6
122.5°	160.2	128.3	126.4	119.3	112.0
125°	164.7	136.8	135.1	128.5	122.0
127.5°	169.1	144.9	143.2	136.6	130.0
130°	172.4	150.3	148.5	141.4	134.3
132.5°	175.1	154.8	153.0	145.9	138.8
135°	177.9	160.0	158.3	151.8	145.4
137.5°	182.2	166.6	164.9	158.5	152.1
140°	184.9	171.0	169.5	163.6	157.7
142.5°	187.0	174.3	173.0	167.4	162.0
145°	189.9	179.3	178.1	173.3	168.6
147.5°	194.2	185.7	184.5	179.8	175.1
150°	196.3	189.0	187.9	183.6	179.4
152.5°	197.8	191.1	190.3	187.1	183.9
155°	200.9	195.9	195.3	192.9	190.5
157.5°	204.1	200.5	200.0	197.7	195.4
160°	205.5	202.7	202.3	200.5	198.7
162.5°	207.0	205.0	204.7	203.3	202.0
165°	209.2	208.3	208.0	206.8	205.6
167.5°	211.0	210.2	210.0	209.4	208.9
170°	212.4	212.3	212.2	211.6	211.1
172.5°	212.5	212.5	212.5	212.3	212.2
175°	213.3	213.8	213.8	213.8	213.8
177.5°	213.4	213.8	213.8	213.8	213.8
180°	213.8	213.8	213.8	213.8	213.8



TEST NUMBER: P933890
 CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-STD-W-6-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.51	13.53	13.32	14.36	15.39	15.33	16.35	16.14	17.19	18.22
	3H	13.00	13.91	13.82	14.76	15.82	16.69	17.60	17.51	18.45	19.51
	4H	13.20	14.06	14.04	14.91	15.98	17.14	18.00	17.98	18.85	19.92
	6H	13.32	14.12	14.18	14.98	16.06	17.43	18.23	18.28	19.09	20.17
	8H	13.33	14.09	14.19	14.97	16.05	17.51	18.27	18.37	19.15	20.23
	12H	13.31	14.03	14.17	14.90	16.01	17.55	18.28	18.42	19.15	20.26
4H	2H	13.56	14.42	14.41	15.28	16.34	15.76	16.63	16.61	17.48	18.55
	3H	14.60	15.32	15.46	16.21	17.29	17.28	18.00	18.14	18.89	19.97
	4H	14.88	15.54	15.75	16.42	17.53	17.81	18.47	18.68	19.35	20.46
	6H	15.02	15.58	15.90	16.49	17.61	18.19	18.75	19.07	19.66	20.77
	8H	15.03	15.56	15.92	16.46	17.59	18.30	18.83	19.19	19.73	20.85
	12H	15.00	15.48	15.91	16.40	17.53	18.36	18.84	19.27	19.76	20.89
8H	4H	15.35	15.88	16.24	16.78	17.91	17.95	18.48	18.84	19.38	20.51
	6H	15.62	16.06	16.53	17.00	18.13	18.39	18.83	19.31	19.77	20.90
	8H	15.66	16.05	16.59	16.98	18.13	18.55	18.93	19.47	19.87	21.01
	12H	15.65	15.99	16.58	16.92	18.12	18.65	18.99	19.58	19.92	21.12
12H	4H	15.36	15.84	16.27	16.76	17.89	17.92	18.40	18.83	19.32	20.45
	6H	15.68	16.07	16.61	17.00	18.15	18.39	18.78	19.32	19.71	20.86
	8H	15.75	16.10	16.68	17.02	18.22	18.56	18.90	19.49	19.83	21.02