

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933980

Luminaire Tested: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933980
REPORT IS A COMBINATION OF REPORTS P933677 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10625.2 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933980
CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P933980

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	78	78	78	74
1	103	99	95	91	98	94	90	87	85	82	80	77	75	73	69	68	66	66	66	66	62
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	61	58	56	56	56	56	52
3	86	76	68	62	81	72	66	60	66	60	56	60	55	52	54	51	48	48	48	48	44
4	79	67	59	53	74	64	57	51	59	52	48	53	48	44	48	44	41	41	41	41	38
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	36	36	36	36	33
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	31	31	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	28	28	28	26
8	57	44	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	25	25	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	23	23	23	23	21
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	20	20	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9367	9367	9367	9367
5°	9440	9456	9440	7435
10°	9381	9314	9381	6659
15°	9282	9112	9282	7609
20°	9092	8873	9092	7625
25°	8698	8525	8698	7463
30°	8188	8235	8188	7108
35°	7303	7869	7303	6719
40°	6088	7438	6088	6424
45°	5444	6933	5444	6085
50°	5788	6332	5788	5745
55°	5451	5683	5451	5548
60°	5626	4827	5626	5082
65°	5109	3990	5109	4460
70°	3546	3180	3546	3739
75°	3121	2351	3121	2815
80°	2534	1554	2534	1692
85°	1484	823	1484	700

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 8338 cd/sqm



TEST NUMBER: P933980

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.4	2.6
10°-20°	776.2	7.3
20°-30°	1199.8	11.3
30°-40°	1432.3	13.5
40°-50°	1440.7	13.6
50°-60°	1253.5	11.8
60°-70°	888.8	8.4
70°-80°	470.2	4.4
80°-90°	118.7	1.1
90°-100°	208.4	2.0
100°-110°	547.9	5.2
110°-120°	568.1	5.3
120°-130°	455.7	4.3
130°-140°	357.6	3.4
140°-150°	274.5	2.6
150°-160°	197.7	1.9
160°-170°	120.9	1.1
170°-180°	40.9	0.4
0°-30°	2249.3	21.2
0°-40°	3681.6	34.6
0°-60°	6375.8	60.0
0°-90°	7853.6	73.9
90°-120°	1324.5	12.5
90°-150°	2412.2	22.7
90°-180°	2772.0	26.1
0°-180°	10625.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3028	3028	3028	3028	3028	
5°	3043	3137	3043	2467	3043	289
15°	2905	3109	2905	2596	2905	817
25°	2558	2900	2558	2538	2558	1175
35°	1945	2587	1945	2209	1945	1204
45°	1255	2132	1255	1871	1255	1005
55°	1023	1573	1023	1536	1023	940
65°	710	948	710	1060	710	679
75°	269	450	269	539	269	283
85°	46	115	46	97	46	62
90°	3	11	3	11	3	4
95°	28	126	28	126	28	31
105°	99	858	99	858	99	105
115°	175	1105	175	1105	175	173
125°	244	880	244	880	244	217
135°	291	683	291	683	291	225
145°	337	554	337	554	337	211
155°	381	477	381	477	381	175
165°	411	444	411	444	411	116
175°	428	430	428	430	428	41
180°	428	428	428	428	428	



TEST NUMBER: P933980
 CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4
2.5°	3054.2	3054.2	3071.4	3077.1	3077.1	3068.5	3059.9	3068.5	3094.3	3102.9	3100.0
5°	3042.7	3065.6	3097.2	3102.9	3108.6	3105.8	3100.0	3105.8	3134.4	3140.1	3143.0
7.5°	3019.8	3062.8	3102.9	3111.5	3120.1	3111.5	3108.6	3114.4	3143.0	3148.7	3148.7
10°	2991.2	3051.3	3097.2	3102.9	3111.5	3102.9	3102.9	3114.4	3143.0	3148.7	3151.6
12.5°	2951.0	3034.1	3077.1	3082.8	3094.3	3091.4	3088.6	3100.0	3128.7	3134.4	3134.4
15°	2905.2	3002.6	3042.7	3048.5	3068.5	3062.8	3062.8	3074.2	3105.8	3114.4	3111.5
17.5°	2842.2	2962.5	3008.3	3016.9	3031.3	3028.4	3031.3	3042.7	3071.4	3077.1	3080.0
20°	2770.6	2908.1	2962.5	2971.1	2985.4	2985.4	2985.4	2999.8	3028.4	3039.9	3039.9
22.5°	2673.1	2850.8	2908.1	2913.8	2931.0	2931.0	2936.7	2956.8	2982.6	2985.4	2985.4
25°	2558.5	2787.7	2836.4	2853.6	2870.8	2879.4	2888.0	2899.5	2908.1	2905.2	2908.1
27.5°	2438.1	2707.5	2770.6	2782.0	2804.9	2813.5	2825.0	2827.9	2830.7	2839.3	2833.6
30°	2303.5	2595.8	2690.3	2701.8	2739.0	2744.8	2733.3	2739.0	2753.4	2759.1	2764.8
32.5°	2151.6	2429.5	2607.2	2633.0	2667.4	2650.2	2647.4	2656.0	2678.9	2678.9	2684.6
35°	1945.3	2300.6	2529.9	2552.8	2578.6	2558.5	2570.0	2572.9	2587.2	2595.8	2592.9
37.5°	1719.0	2188.9	2449.6	2466.8	2486.8	2461.0	2478.2	2486.8	2498.3	2492.5	2492.5
40°	1518.4	2014.1	2355.0	2366.5	2383.7	2363.6	2380.8	2386.5	2392.3	2386.5	2383.7
42.5°	1369.5	1822.1	2254.8	2269.1	2257.6	2271.9	2277.7	2289.1	2280.5	2269.1	2269.1
45°	1254.9	1770.6	2145.9	2163.1	2145.9	2168.8	2177.4	2177.4	2151.6	2145.9	2143.0
47.5°	1217.6	1667.4	2037.0	2037.0	2028.4	2057.1	2071.4	2051.3	2025.6	2017.0	2017.0
50°	1214.8	1552.8	1888.0	1876.6	1916.7	1951.1	1936.7	1916.7	1896.6	1865.1	1865.1
52.5°	1103.0	1412.4	1696.1	1739.1	1802.1	1822.1	1799.2	1779.2	1744.8	1730.5	1719.0
55°	1022.8	1266.3	1521.3	1607.3	1673.2	1698.9	1656.0	1635.9	1584.3	1575.8	1570.0
57.5°	1005.6	1054.3	1360.9	1469.7	1550.0	1547.1	1521.3	1484.1	1441.1	1432.5	1429.6
60°	922.5	762.1	1189.0	1317.9	1401.0	1392.4	1369.5	1335.1	1295.0	1289.2	1283.5
62.5°	836.6	552.9	994.2	1140.3	1257.7	1254.9	1234.8	1183.2	1154.6	1140.3	1128.8
65°	710.5	464.1	707.7	948.3	1117.4	1123.1	1080.1	1042.9	1011.3	994.2	991.3
67.5°	541.5	378.2	478.5	790.7	982.7	977.0	922.5	905.3	865.2	856.6	839.4
70°	401.1	252.1	332.3	641.8	850.9	836.6	793.6	773.6	736.3	716.2	704.8
72.5°	332.3	203.4	243.5	498.5	716.2	699.1	661.8	638.9	607.4	590.2	578.7
75°	269.3	214.9	186.2	369.6	581.6	570.1	535.8	512.8	487.0	464.1	467.0
77.5°	197.7	200.5	149.0	272.2	461.3	444.1	424.0	395.4	383.9	361.0	361.0
80°	149.0	157.6	111.7	186.2	332.3	332.3	315.2	295.1	275.0	263.6	263.6
82.5°	100.3	100.3	83.1	117.5	226.3	217.7	206.3	200.5	189.1	183.4	183.4
85°	45.8	57.3	51.6	71.6	123.2	128.9	128.9	123.2	120.3	114.6	117.5
87.5°	14.3	25.8	31.5	40.1	63.0	65.9	68.8	68.8	68.8	71.6	71.6
90°	2.9	5.2	7.4	8.0	12.6	18.7	21.8	19.4	14.5	10.9	10.9
92.5°	11.5	30.9	50.5	55.4	77.8	107.8	122.8	107.6	77.3	54.5	52.3
95°	27.5	63.2	98.9	107.9	191.6	303.2	359.0	320.3	243.0	185.1	178.5
97.5°	47.7	79.2	110.7	118.5	258.0	444.2	537.2	512.7	463.9	427.3	414.8
100°	63.1	91.7	120.2	127.4	282.3	488.8	592.0	593.8	597.4	600.0	585.1
102.5°	76.3	102.9	129.6	136.3	293.4	502.8	607.5	638.6	700.8	747.5	734.7
105°	98.7	121.3	143.8	149.5	301.6	504.3	605.8	675.5	815.0	919.7	912.8
107.5°	121.7	142.7	163.8	169.0	303.1	481.9	571.3	668.6	863.2	1009.2	1010.9
110°	137.1	156.1	175.1	179.9	300.8	462.0	542.6	651.4	869.0	1032.2	1039.3



TEST NUMBER: P933980

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	152.4	170.5	188.6	193.1	300.9	444.6	516.6	627.9	850.5	1017.6	1028.5
115°	175.3	192.1	208.8	213.0	303.7	424.7	485.2	592.5	807.0	967.9	983.1
117.5°	198.0	213.2	228.3	232.2	309.3	412.3	463.7	560.6	754.2	899.3	916.2
120°	211.2	225.5	239.8	243.3	313.9	408.0	455.1	543.5	720.5	853.1	869.5
122.5°	224.1	238.6	252.9	256.5	320.5	405.8	448.5	528.1	687.4	806.9	823.0
125°	243.9	257.1	270.3	273.5	329.5	404.1	441.3	508.9	644.2	745.8	760.7
127.5°	260.0	273.2	286.5	289.8	338.4	403.0	435.3	493.4	609.6	696.7	709.3
130°	268.5	282.9	297.2	300.7	344.9	403.6	433.0	484.8	588.2	665.7	677.4
132.5°	277.5	291.8	306.1	309.6	350.1	404.1	431.0	477.3	569.9	639.4	649.8
135°	290.7	303.7	316.7	319.9	355.8	403.7	427.6	466.3	543.9	602.0	611.0
137.5°	304.2	317.1	329.9	333.1	364.4	406.2	427.0	459.7	525.2	574.4	581.8
140°	315.3	327.2	339.1	342.1	369.7	406.5	425.0	453.2	509.9	552.4	559.2
142.5°	323.9	334.9	345.9	348.7	374.1	408.0	425.0	449.8	499.6	536.9	542.8
145°	337.2	346.8	356.3	358.7	379.8	408.0	422.1	442.5	483.1	513.6	518.1
147.5°	350.4	359.7	369.0	371.3	388.2	410.8	422.1	438.2	470.1	494.1	497.8
150°	359.0	367.4	375.8	377.9	392.6	412.3	422.1	435.7	462.7	482.9	485.9
152.5°	367.9	374.3	380.6	382.2	395.5	413.2	422.1	433.7	456.8	474.1	476.4
155°	381.0	385.7	390.5	391.6	401.8	415.3	422.1	431.3	449.7	463.5	465.0
157.5°	390.8	395.4	400.0	401.2	408.2	417.4	422.1	429.3	443.5	454.2	455.2
160°	397.5	401.0	404.6	405.5	411.0	418.4	422.1	428.2	440.4	449.6	450.2
162.5°	404.1	406.7	409.4	410.1	414.1	419.4	422.1	427.3	437.6	445.3	445.9
165°	411.2	413.6	416.1	416.7	418.5	420.9	422.1	425.8	433.2	438.7	439.3
167.5°	417.8	419.0	420.1	420.4	421.9	423.9	425.0	427.4	432.2	435.9	436.1
170°	422.1	423.3	424.4	424.7	424.8	424.9	425.0	427.4	432.2	435.9	435.9
172.5°	424.4	424.7	424.9	425.0	425.0	425.0	425.0	426.9	430.7	433.6	433.4
175°	427.6	427.6	427.6	427.6	426.7	425.5	425.0	426.2	428.6	430.4	430.4
177.5°	427.6	427.6	427.6	427.6	426.9	426.0	425.5	426.5	428.4	429.8	429.6
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P933980

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4
2.5°	3105.8	3097.2	3105.8	3100.0	3102.9	3094.3	3068.5	3059.9	3068.5	3077.1	3077.1
5°	3143.0	3137.3	3143.0	3143.0	3140.1	3134.4	3105.8	3100.0	3105.8	3108.6	3102.9
7.5°	3154.5	3145.9	3154.5	3148.7	3148.7	3143.0	3114.4	3108.6	3111.5	3120.1	3111.5
10°	3154.5	3145.9	3154.5	3151.6	3148.7	3143.0	3114.4	3102.9	3102.9	3111.5	3102.9
12.5°	3140.1	3134.4	3140.1	3134.4	3134.4	3128.7	3100.0	3088.6	3091.4	3094.3	3082.8
15°	3117.2	3108.6	3117.2	3111.5	3114.4	3105.8	3074.2	3062.8	3062.8	3068.5	3048.5
17.5°	3082.8	3071.4	3082.8	3080.0	3077.1	3071.4	3042.7	3031.3	3028.4	3031.3	3016.9
20°	3042.7	3034.1	3042.7	3039.9	3039.9	3028.4	2999.8	2985.4	2985.4	2985.4	2971.1
22.5°	2979.7	2971.1	2979.7	2985.4	2985.4	2982.6	2956.8	2936.7	2931.0	2931.0	2913.8
25°	2908.1	2899.5	2908.1	2908.1	2905.2	2908.1	2899.5	2888.0	2879.4	2870.8	2853.6
27.5°	2839.3	2833.6	2839.3	2833.6	2839.3	2830.7	2827.9	2825.0	2813.5	2804.9	2782.0
30°	2770.6	2764.8	2770.6	2764.8	2759.1	2753.4	2739.0	2733.3	2744.8	2739.0	2701.8
32.5°	2684.6	2678.9	2684.6	2684.6	2678.9	2678.9	2656.0	2647.4	2650.2	2667.4	2633.0
35°	2595.8	2587.2	2595.8	2592.9	2595.8	2587.2	2572.9	2570.0	2558.5	2578.6	2552.8
37.5°	2492.5	2484.0	2492.5	2492.5	2492.5	2498.3	2486.8	2478.2	2461.0	2486.8	2466.8
40°	2386.5	2375.1	2386.5	2383.7	2386.5	2392.3	2386.5	2380.8	2363.6	2383.7	2366.5
42.5°	2266.2	2263.4	2266.2	2269.1	2269.1	2280.5	2289.1	2277.7	2271.9	2257.6	2269.1
45°	2137.3	2131.6	2137.3	2143.0	2145.9	2151.6	2177.4	2177.4	2168.8	2145.9	2163.1
47.5°	1999.8	1985.4	1999.8	2017.0	2017.0	2025.6	2051.3	2071.4	2057.1	2028.4	2037.0
50°	1853.7	1856.5	1853.7	1865.1	1865.1	1896.6	1916.7	1936.7	1951.1	1916.7	1876.6
52.5°	1710.4	1707.5	1710.4	1719.0	1730.5	1744.8	1779.2	1799.2	1822.1	1802.1	1739.1
55°	1567.2	1572.9	1567.2	1570.0	1575.8	1584.3	1635.9	1656.0	1698.9	1673.2	1607.3
57.5°	1423.9	1415.3	1423.9	1429.6	1432.5	1441.1	1484.1	1521.3	1547.1	1550.0	1469.7
60°	1257.7	1246.3	1257.7	1283.5	1289.2	1295.0	1335.1	1369.5	1392.4	1401.0	1317.9
62.5°	1111.6	1091.6	1111.6	1128.8	1140.3	1154.6	1183.2	1234.8	1254.9	1257.7	1140.3
65°	956.9	948.3	956.9	991.3	994.2	1011.3	1042.9	1080.1	1123.1	1117.4	948.3
67.5°	816.5	816.5	816.5	839.4	856.6	865.2	905.3	922.5	977.0	982.7	790.7
70°	687.6	684.7	687.6	704.8	716.2	736.3	773.6	793.6	836.6	850.9	641.8
72.5°	564.4	561.5	564.4	578.7	590.2	607.4	638.9	661.8	699.1	716.2	498.5
75°	455.5	449.8	455.5	467.0	464.1	487.0	512.8	535.8	570.1	581.6	369.6
77.5°	349.5	349.5	349.5	361.0	361.0	383.9	395.4	424.0	444.1	461.3	272.2
80°	260.7	257.8	260.7	263.6	263.6	275.0	295.1	315.2	332.3	332.3	186.2
82.5°	183.4	177.6	183.4	183.4	183.4	189.1	200.5	206.3	217.7	226.3	117.5
85°	114.6	114.6	114.6	117.5	114.6	120.3	123.2	128.9	128.9	123.2	71.6
87.5°	74.5	71.6	74.5	71.6	71.6	68.8	68.8	68.8	65.9	63.0	40.1
90°	10.9	10.9	10.9	10.9	10.9	14.5	19.4	21.8	18.7	12.6	8.0
92.5°	43.7	35.0	43.7	52.3	54.5	77.3	107.6	122.8	107.8	77.8	55.4
95°	152.2	126.0	152.2	178.5	185.1	243.0	320.3	359.0	303.2	191.6	107.9
97.5°	364.8	314.8	364.8	414.8	427.3	463.9	512.7	537.2	444.2	258.0	118.5
100°	525.6	466.0	525.6	585.1	600.0	597.4	593.8	592.0	488.8	282.3	127.4
102.5°	683.7	632.7	683.7	734.7	747.5	700.8	638.6	607.5	502.8	293.4	136.3
105°	885.4	858.0	885.4	912.8	919.7	815.0	675.5	605.8	504.3	301.6	149.5
107.5°	1017.6	1024.1	1017.6	1010.9	1009.2	863.2	668.6	571.3	481.9	303.1	169.0
110°	1067.9	1096.4	1067.9	1039.3	1032.2	869.0	651.4	542.6	462.0	300.8	179.9



TEST NUMBER: P933980

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1072.4	1116.2	1072.4	1028.5	1017.6	850.5	627.9	516.6	444.6	300.9	193.1
115°	1043.9	1104.7	1043.9	983.1	967.9	807.0	592.5	485.2	424.7	303.7	213.0
117.5°	983.6	1051.1	983.6	916.2	899.3	754.2	560.6	463.7	412.3	309.3	232.2
120°	935.0	1000.6	935.0	869.5	853.1	720.5	543.5	455.1	408.0	313.9	243.3
122.5°	887.8	952.4	887.8	823.0	806.9	687.4	528.1	448.5	405.8	320.5	256.5
125°	820.2	879.7	820.2	760.7	745.8	644.2	508.9	441.3	404.1	329.5	273.5
127.5°	759.5	809.7	759.5	709.3	696.7	609.6	493.4	435.3	403.0	338.4	289.8
130°	723.8	770.2	723.8	677.4	665.7	588.2	484.8	433.0	403.6	344.9	300.7
132.5°	691.3	732.9	691.3	649.8	639.4	569.9	477.3	431.0	404.1	350.1	309.6
135°	646.8	682.6	646.8	611.0	602.0	543.9	466.3	427.6	403.7	355.8	319.9
137.5°	611.1	640.5	611.1	581.8	574.4	525.2	459.7	427.0	406.2	364.4	333.1
140°	586.7	614.1	586.7	559.2	552.4	509.9	453.2	425.0	406.5	369.7	342.1
142.5°	566.4	590.0	566.4	542.8	536.9	499.6	449.8	425.0	408.0	374.1	348.7
145°	535.9	553.8	535.9	518.1	513.6	483.1	442.5	422.1	408.0	379.8	358.7
147.5°	512.6	527.4	512.6	497.8	494.1	470.1	438.2	422.1	410.8	388.2	371.3
150°	497.9	509.9	497.9	485.9	482.9	462.7	435.7	422.1	412.3	392.6	377.9
152.5°	485.3	494.4	485.3	476.4	474.1	456.8	433.7	422.1	413.2	395.5	382.2
155°	470.9	476.9	470.9	465.0	463.5	449.7	431.3	422.1	415.3	401.8	391.6
157.5°	459.5	463.7	459.5	455.2	454.2	443.5	429.3	422.1	417.4	408.2	401.2
160°	452.7	455.1	452.7	450.2	449.6	440.4	428.2	422.1	418.4	411.0	405.5
162.5°	448.2	450.5	448.2	445.9	445.3	437.6	427.3	422.1	419.4	414.1	410.1
165°	441.8	444.2	441.8	439.3	438.7	433.2	425.8	422.1	420.9	418.5	416.7
167.5°	437.1	438.2	437.1	436.1	435.9	432.2	427.4	425.0	423.9	421.9	420.4
170°	435.9	435.9	435.9	435.9	435.9	432.2	427.4	425.0	424.9	424.8	424.7
172.5°	432.4	431.6	432.4	433.4	433.6	430.7	426.9	425.0	425.0	425.0	425.0
175°	430.4	430.4	430.4	430.4	430.4	428.6	426.2	425.0	425.5	426.7	427.6
177.5°	428.6	427.6	428.6	429.6	429.8	428.4	426.5	425.5	426.0	426.9	427.6
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P933980
 CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4
2.5°	3071.4	3054.2	3054.2	3025.5	3014.1	3005.5	2991.2	2948.2	2936.7	2925.3	2942.5
5°	3097.2	3065.6	3042.7	2991.2	2948.2	2931.0	2876.6	2773.4	2704.7	2653.1	2624.4
7.5°	3102.9	3062.8	3019.8	2939.6	2836.4	2790.6	2624.4	2435.2	2383.7	2337.8	2309.2
10°	3097.2	3051.3	2991.2	2870.8	2627.3	2547.1	2380.8	2257.6	2226.1	2217.5	2226.1
12.5°	3077.1	3034.1	2951.0	2750.5	2409.5	2355.0	2257.6	2186.0	2180.3	2194.6	2271.9
15°	3042.7	3002.6	2905.2	2590.1	2289.1	2249.0	2180.3	2154.5	2186.0	2286.3	2518.3
17.5°	3008.3	2962.5	2842.2	2432.4	2197.5	2168.8	2120.1	2171.7	2349.3	2484.0	2561.4
20°	2962.5	2908.1	2770.6	2317.8	2131.6	2105.8	2082.9	2314.9	2449.6	2498.3	2541.4
22.5°	2908.1	2850.8	2673.1	2237.6	2062.8	2042.7	2057.1	2395.1	2449.6	2484.0	2521.2
25°	2836.4	2787.7	2558.5	2174.5	2008.4	1985.4	2039.9	2386.5	2418.1	2426.7	2501.1
27.5°	2770.6	2707.5	2438.1	2117.2	1942.5	1933.9	2054.2	2349.3	2372.2	2380.8	2461.0
30°	2690.3	2595.8	2303.5	2057.1	1873.7	1870.8	2057.1	2303.5	2297.7	2320.6	2400.9
32.5°	2607.2	2429.5	2151.6	1982.6	1807.8	1805.0	2037.0	2234.7	2229.0	2260.5	2320.6
35°	2529.9	2300.6	1945.3	1896.6	1724.7	1727.6	1988.3	2154.5	2157.3	2186.0	2223.2
37.5°	2449.6	2188.9	1719.0	1802.1	1644.5	1644.5	1922.4	2080.0	2074.3	2082.9	2134.4
40°	2355.0	2014.1	1518.4	1678.9	1570.0	1561.4	1842.2	1999.8	1979.7	1976.8	2048.5
42.5°	2254.8	1822.1	1369.5	1515.6	1484.1	1472.6	1744.8	1902.4	1865.1	1873.7	1965.4
45°	2145.9	1770.6	1254.9	1280.7	1395.3	1386.7	1638.8	1790.6	1764.8	1787.8	1882.3
47.5°	2037.0	1667.4	1217.6	1062.9	1300.7	1297.8	1521.3	1681.8	1667.4	1690.4	1790.6
50°	1888.0	1552.8	1214.8	911.1	1194.7	1206.2	1380.9	1575.8	1575.8	1595.8	1701.8
52.5°	1696.1	1412.4	1103.0	825.1	1071.5	1105.9	1257.7	1484.1	1489.8	1509.9	1604.4
55°	1521.3	1266.3	1022.8	759.2	925.4	999.9	1137.4	1389.5	1401.0	1421.0	1507.0
57.5°	1360.9	1054.3	1005.6	681.9	790.7	862.4	1031.4	1297.8	1303.6	1320.8	1403.8
60°	1189.0	762.1	922.5	598.8	673.3	727.7	934.0	1189.0	1209.0	1220.5	1292.1
62.5°	994.2	552.9	836.6	541.5	616.0	627.4	853.8	1085.8	1111.6	1120.2	1163.2
65°	707.7	464.1	710.5	492.8	555.8	558.7	767.8	979.8	1002.8	1017.1	1048.6
67.5°	478.5	378.2	541.5	446.9	510.0	512.8	684.7	856.6	888.2	899.6	919.7
70°	332.3	252.1	401.1	398.2	458.4	464.1	595.9	744.9	773.6	782.1	793.6
72.5°	243.5	203.4	332.3	358.1	404.0	409.7	504.2	618.8	647.5	656.1	661.8
75°	186.2	214.9	269.3	312.3	343.8	346.7	412.6	504.2	524.3	530.0	532.9
77.5°	149.0	200.5	197.7	252.1	280.8	275.0	323.7	389.6	406.8	406.8	406.8
80°	111.7	157.6	149.0	180.5	206.3	200.5	232.1	277.9	283.6	289.4	286.5
82.5°	83.1	100.3	100.3	114.6	137.5	131.8	154.7	180.5	180.5	180.5	186.2
85°	51.6	57.3	45.8	60.2	77.4	74.5	86.0	97.4	100.3	100.3	94.5
87.5°	31.5	25.8	14.3	22.9	34.4	34.4	40.1	43.0	40.1	40.1	40.1
90°	7.4	5.2	2.9	5.2	7.4	8.0	12.6	18.7	21.8	19.4	14.5
92.5°	50.5	30.9	11.5	30.9	50.5	55.4	77.8	107.8	122.8	107.6	77.3
95°	98.9	63.2	27.5	63.2	98.9	107.9	191.6	303.2	359.0	320.3	243.0
97.5°	110.7	79.2	47.7	79.2	110.7	118.5	258.0	444.2	537.2	512.7	463.9
100°	120.2	91.7	63.1	91.7	120.2	127.4	282.3	488.8	592.0	593.8	597.4
102.5°	129.6	102.9	76.3	102.9	129.6	136.3	293.4	502.8	607.5	638.6	700.8
105°	143.8	121.3	98.7	121.3	143.8	149.5	301.6	504.3	605.8	675.5	815.0
107.5°	163.8	142.7	121.7	142.7	163.8	169.0	303.1	481.9	571.3	668.6	863.2
110°	175.1	156.1	137.1	156.1	175.1	179.9	300.8	462.0	542.6	651.4	869.0



TEST NUMBER: P933980

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	188.6	170.5	152.4	170.5	188.6	193.1	300.9	444.6	516.6	627.9	850.5
115°	208.8	192.1	175.3	192.1	208.8	213.0	303.7	424.7	485.2	592.5	807.0
117.5°	228.3	213.2	198.0	213.2	228.3	232.2	309.3	412.3	463.7	560.6	754.2
120°	239.8	225.5	211.2	225.5	239.8	243.3	313.9	408.0	455.1	543.5	720.5
122.5°	252.9	238.6	224.1	238.6	252.9	256.5	320.5	405.8	448.5	528.1	687.4
125°	270.3	257.1	243.9	257.1	270.3	273.5	329.5	404.1	441.3	508.9	644.2
127.5°	286.5	273.2	260.0	273.2	286.5	289.8	338.4	403.0	435.3	493.4	609.6
130°	297.2	282.9	268.5	282.9	297.2	300.7	344.9	403.6	433.0	484.8	588.2
132.5°	306.1	291.8	277.5	291.8	306.1	309.6	350.1	404.1	431.0	477.3	569.9
135°	316.7	303.7	290.7	303.7	316.7	319.9	355.8	403.7	427.6	466.3	543.9
137.5°	329.9	317.1	304.2	317.1	329.9	333.1	364.4	406.2	427.0	459.7	525.2
140°	339.1	327.2	315.3	327.2	339.1	342.1	369.7	406.5	425.0	453.2	509.9
142.5°	345.9	334.9	323.9	334.9	345.9	348.7	374.1	408.0	425.0	449.8	499.6
145°	356.3	346.8	337.2	346.8	356.3	358.7	379.8	408.0	422.1	442.5	483.1
147.5°	369.0	359.7	350.4	359.7	369.0	371.3	388.2	410.8	422.1	438.2	470.1
150°	375.8	367.4	359.0	367.4	375.8	377.9	392.6	412.3	422.1	435.7	462.7
152.5°	380.6	374.3	367.9	374.3	380.6	382.2	395.5	413.2	422.1	433.7	456.8
155°	390.5	385.7	381.0	385.7	390.5	391.6	401.8	415.3	422.1	431.3	449.7
157.5°	400.0	395.4	390.8	395.4	400.0	401.2	408.2	417.4	422.1	429.3	443.5
160°	404.6	401.0	397.5	401.0	404.6	405.5	411.0	418.4	422.1	428.2	440.4
162.5°	409.4	406.7	404.1	406.7	409.4	410.1	414.1	419.4	422.1	427.3	437.6
165°	416.1	413.6	411.2	413.6	416.1	416.7	418.5	420.9	422.1	425.8	433.2
167.5°	420.1	419.0	417.8	419.0	420.1	420.4	421.9	423.9	425.0	427.4	432.2
170°	424.4	423.3	422.1	423.3	424.4	424.7	424.8	424.9	425.0	427.4	432.2
172.5°	424.9	424.7	424.4	424.7	424.9	425.0	425.0	425.0	425.0	426.9	430.7
175°	427.6	427.6	427.6	427.6	427.6	427.6	426.7	425.5	425.0	426.2	428.6
177.5°	427.6	427.6	427.6	427.6	427.6	427.6	426.9	426.0	425.5	426.5	428.4
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P933980
 CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4	3028.4
2.5°	2922.4	2913.8	2925.3	2893.7	2925.3	2913.8	2922.4	2942.5	2925.3	2936.7	2948.2
5°	2564.3	2549.9	2504.0	2466.8	2504.0	2549.9	2564.3	2624.4	2653.1	2704.7	2773.4
7.5°	2292.0	2280.5	2269.1	2246.2	2269.1	2280.5	2292.0	2309.2	2337.8	2383.7	2435.2
10°	2231.8	2234.7	2251.9	2249.0	2251.9	2234.7	2231.8	2226.1	2217.5	2226.1	2257.6
12.5°	2386.5	2412.3	2506.9	2501.1	2506.9	2412.3	2386.5	2271.9	2194.6	2180.3	2186.0
15°	2564.3	2572.9	2592.9	2595.8	2592.9	2572.9	2564.3	2518.3	2286.3	2186.0	2154.5
17.5°	2581.5	2584.3	2598.7	2598.7	2598.7	2584.3	2581.5	2561.4	2484.0	2349.3	2171.7
20°	2567.1	2572.9	2601.5	2607.2	2601.5	2572.9	2567.1	2541.4	2498.3	2449.6	2314.9
22.5°	2561.4	2572.9	2595.8	2592.9	2595.8	2572.9	2561.4	2521.2	2484.0	2449.6	2395.1
25°	2532.8	2532.8	2535.6	2538.5	2535.6	2532.8	2532.8	2501.1	2426.7	2418.1	2386.5
27.5°	2472.5	2478.2	2495.4	2492.5	2495.4	2478.2	2472.5	2461.0	2380.8	2372.2	2349.3
30°	2418.1	2412.3	2398.0	2386.5	2398.0	2412.3	2418.1	2400.9	2320.6	2297.7	2303.5
32.5°	2326.4	2312.1	2297.7	2289.1	2297.7	2312.1	2326.4	2320.6	2260.5	2229.0	2234.7
35°	2217.5	2220.4	2217.5	2208.9	2217.5	2220.4	2217.5	2223.2	2186.0	2157.3	2154.5
37.5°	2140.2	2145.9	2143.0	2131.6	2143.0	2145.9	2140.2	2134.4	2082.9	2074.3	2080.0
40°	2059.9	2062.8	2059.9	2051.3	2059.9	2062.8	2059.9	2048.5	1976.8	1979.7	1999.8
42.5°	1982.6	1979.7	1971.1	1965.4	1971.1	1979.7	1982.6	1965.4	1873.7	1865.1	1902.4
45°	1893.8	1896.6	1879.4	1870.8	1879.4	1896.6	1893.8	1882.3	1787.8	1764.8	1790.6
47.5°	1805.0	1805.0	1790.6	1782.0	1790.6	1805.0	1805.0	1790.6	1690.4	1667.4	1681.8
50°	1710.4	1707.5	1687.5	1684.6	1687.5	1707.5	1710.4	1701.8	1595.8	1575.8	1575.8
52.5°	1601.5	1601.5	1604.4	1610.1	1604.4	1601.5	1601.5	1604.4	1509.9	1489.8	1484.1
55°	1507.0	1509.9	1529.9	1535.6	1529.9	1509.9	1507.0	1507.0	1421.0	1401.0	1389.5
57.5°	1409.6	1409.6	1423.9	1423.9	1423.9	1409.6	1409.6	1403.8	1320.8	1303.6	1297.8
60°	1297.8	1303.6	1315.0	1312.2	1315.0	1303.6	1297.8	1292.1	1220.5	1209.0	1189.0
62.5°	1180.4	1186.1	1189.0	1183.2	1189.0	1186.1	1180.4	1163.2	1120.2	1111.6	1085.8
65°	1057.2	1062.9	1065.8	1060.0	1065.8	1062.9	1057.2	1048.6	1017.1	1002.8	979.8
67.5°	931.1	928.3	925.4	936.9	925.4	928.3	931.1	919.7	899.6	888.2	856.6
70°	802.2	802.2	799.3	805.1	799.3	802.2	802.2	793.6	782.1	773.6	744.9
72.5°	664.7	661.8	673.3	664.7	673.3	661.8	664.7	661.8	656.1	647.5	618.8
75°	530.0	535.8	530.0	538.6	530.0	535.8	530.0	532.9	530.0	524.3	504.2
77.5°	404.0	409.7	404.0	404.0	404.0	409.7	404.0	406.8	406.8	406.8	389.6
80°	286.5	283.6	283.6	280.8	283.6	283.6	286.5	286.5	289.4	283.6	277.9
82.5°	183.4	180.5	180.5	186.2	180.5	180.5	183.4	186.2	180.5	180.5	180.5
85°	100.3	103.1	97.4	97.4	97.4	103.1	100.3	94.5	100.3	100.3	97.4
87.5°	37.2	34.4	34.4	34.4	34.4	34.4	37.2	40.1	40.1	40.1	43.0
90°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	14.5	19.4	21.8	18.7
92.5°	54.5	52.3	43.7	35.0	43.7	52.3	54.5	77.3	107.6	122.8	107.8
95°	185.1	178.5	152.2	126.0	152.2	178.5	185.1	243.0	320.3	359.0	303.2
97.5°	427.3	414.8	364.8	314.8	364.8	414.8	427.3	463.9	512.7	537.2	444.2
100°	600.0	585.1	525.6	466.0	525.6	585.1	600.0	597.4	593.8	592.0	488.8
102.5°	747.5	734.7	683.7	632.7	683.7	734.7	747.5	700.8	638.6	607.5	502.8
105°	919.7	912.8	885.4	858.0	885.4	912.8	919.7	815.0	675.5	605.8	504.3
107.5°	1009.2	1010.9	1017.6	1024.1	1017.6	1010.9	1009.2	863.2	668.6	571.3	481.9
110°	1032.2	1039.3	1067.9	1096.4	1067.9	1039.3	1032.2	869.0	651.4	542.6	462.0



TEST NUMBER: P933980

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1017.6	1028.5	1072.4	1116.2	1072.4	1028.5	1017.6	850.5	627.9	516.6	444.6
115°	967.9	983.1	1043.9	1104.7	1043.9	983.1	967.9	807.0	592.5	485.2	424.7
117.5°	899.3	916.2	983.6	1051.1	983.6	916.2	899.3	754.2	560.6	463.7	412.3
120°	853.1	869.5	935.0	1000.6	935.0	869.5	853.1	720.5	543.5	455.1	408.0
122.5°	806.9	823.0	887.8	952.4	887.8	823.0	806.9	687.4	528.1	448.5	405.8
125°	745.8	760.7	820.2	879.7	820.2	760.7	745.8	644.2	508.9	441.3	404.1
127.5°	696.7	709.3	759.5	809.7	759.5	709.3	696.7	609.6	493.4	435.3	403.0
130°	665.7	677.4	723.8	770.2	723.8	677.4	665.7	588.2	484.8	433.0	403.6
132.5°	639.4	649.8	691.3	732.9	691.3	649.8	639.4	569.9	477.3	431.0	404.1
135°	602.0	611.0	646.8	682.6	646.8	611.0	602.0	543.9	466.3	427.6	403.7
137.5°	574.4	581.8	611.1	640.5	611.1	581.8	574.4	525.2	459.7	427.0	406.2
140°	552.4	559.2	586.7	614.1	586.7	559.2	552.4	509.9	453.2	425.0	406.5
142.5°	536.9	542.8	566.4	590.0	566.4	542.8	536.9	499.6	449.8	425.0	408.0
145°	513.6	518.1	535.9	553.8	535.9	518.1	513.6	483.1	442.5	422.1	408.0
147.5°	494.1	497.8	512.6	527.4	512.6	497.8	494.1	470.1	438.2	422.1	410.8
150°	482.9	485.9	497.9	509.9	497.9	485.9	482.9	462.7	435.7	422.1	412.3
152.5°	474.1	476.4	485.3	494.4	485.3	476.4	474.1	456.8	433.7	422.1	413.2
155°	463.5	465.0	470.9	476.9	470.9	465.0	463.5	449.7	431.3	422.1	415.3
157.5°	454.2	455.2	459.5	463.7	459.5	455.2	454.2	443.5	429.3	422.1	417.4
160°	449.6	450.2	452.7	455.1	452.7	450.2	449.6	440.4	428.2	422.1	418.4
162.5°	445.3	445.9	448.2	450.5	448.2	445.9	445.3	437.6	427.3	422.1	419.4
165°	438.7	439.3	441.8	444.2	441.8	439.3	438.7	433.2	425.8	422.1	420.9
167.5°	435.9	436.1	437.1	438.2	437.1	436.1	435.9	432.2	427.4	425.0	423.9
170°	435.9	435.9	435.9	435.9	435.9	435.9	435.9	432.2	427.4	425.0	424.9
172.5°	433.6	433.4	432.4	431.6	432.4	433.4	433.6	430.7	426.9	425.0	425.0
175°	430.4	430.4	430.4	430.4	430.4	430.4	430.4	428.6	426.2	425.0	425.5
177.5°	429.8	429.6	428.6	427.6	428.6	429.6	429.8	428.4	426.5	425.5	426.0
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P933980

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	3028.4	3028.4	3028.4	3028.4	3028.4
2.5°	2991.2	3005.5	3014.1	3025.5	3054.2
5°	2876.6	2931.0	2948.2	2991.2	3042.7
7.5°	2624.4	2790.6	2836.4	2939.6	3019.8
10°	2380.8	2547.1	2627.3	2870.8	2991.2
12.5°	2257.6	2355.0	2409.5	2750.5	2951.0
15°	2180.3	2249.0	2289.1	2590.1	2905.2
17.5°	2120.1	2168.8	2197.5	2432.4	2842.2
20°	2082.9	2105.8	2131.6	2317.8	2770.6
22.5°	2057.1	2042.7	2062.8	2237.6	2673.1
25°	2039.9	1985.4	2008.4	2174.5	2558.5
27.5°	2054.2	1933.9	1942.5	2117.2	2438.1
30°	2057.1	1870.8	1873.7	2057.1	2303.5
32.5°	2037.0	1805.0	1807.8	1982.6	2151.6
35°	1988.3	1727.6	1724.7	1896.6	1945.3
37.5°	1922.4	1644.5	1644.5	1802.1	1719.0
40°	1842.2	1561.4	1570.0	1678.9	1518.4
42.5°	1744.8	1472.6	1484.1	1515.6	1369.5
45°	1638.8	1386.7	1395.3	1280.7	1254.9
47.5°	1521.3	1297.8	1300.7	1062.9	1217.6
50°	1380.9	1206.2	1194.7	911.1	1214.8
52.5°	1257.7	1105.9	1071.5	825.1	1103.0
55°	1137.4	999.9	925.4	759.2	1022.8
57.5°	1031.4	862.4	790.7	681.9	1005.6
60°	934.0	727.7	673.3	598.8	922.5
62.5°	853.8	627.4	616.0	541.5	836.6
65°	767.8	558.7	555.8	492.8	710.5
67.5°	684.7	512.8	510.0	446.9	541.5
70°	595.9	464.1	458.4	398.2	401.1
72.5°	504.2	409.7	404.0	358.1	332.3
75°	412.6	346.7	343.8	312.3	269.3
77.5°	323.7	275.0	280.8	252.1	197.7
80°	232.1	200.5	206.3	180.5	149.0
82.5°	154.7	131.8	137.5	114.6	100.3
85°	86.0	74.5	77.4	60.2	45.8
87.5°	40.1	34.4	34.4	22.9	14.3
90°	12.6	8.0	7.4	5.2	2.9
92.5°	77.8	55.4	50.5	30.9	11.5
95°	191.6	107.9	98.9	63.2	27.5
97.5°	258.0	118.5	110.7	79.2	47.7
100°	282.3	127.4	120.2	91.7	63.1
102.5°	293.4	136.3	129.6	102.9	76.3
105°	301.6	149.5	143.8	121.3	98.7
107.5°	303.1	169.0	163.8	142.7	121.7
110°	300.8	179.9	175.1	156.1	137.1



TEST NUMBER: P933980

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	300.9	193.1	188.6	170.5	152.4
115°	303.7	213.0	208.8	192.1	175.3
117.5°	309.3	232.2	228.3	213.2	198.0
120°	313.9	243.3	239.8	225.5	211.2
122.5°	320.5	256.5	252.9	238.6	224.1
125°	329.5	273.5	270.3	257.1	243.9
127.5°	338.4	289.8	286.5	273.2	260.0
130°	344.9	300.7	297.2	282.9	268.5
132.5°	350.1	309.6	306.1	291.8	277.5
135°	355.8	319.9	316.7	303.7	290.7
137.5°	364.4	333.1	329.9	317.1	304.2
140°	369.7	342.1	339.1	327.2	315.3
142.5°	374.1	348.7	345.9	334.9	323.9
145°	379.8	358.7	356.3	346.8	337.2
147.5°	388.2	371.3	369.0	359.7	350.4
150°	392.6	377.9	375.8	367.4	359.0
152.5°	395.5	382.2	380.6	374.3	367.9
155°	401.8	391.6	390.5	385.7	381.0
157.5°	408.2	401.2	400.0	395.4	390.8
160°	411.0	405.5	404.6	401.0	397.5
162.5°	414.1	410.1	409.4	406.7	404.1
165°	418.5	416.7	416.1	413.6	411.2
167.5°	421.9	420.4	420.1	419.0	417.8
170°	424.8	424.7	424.4	423.3	422.1
172.5°	425.0	425.0	424.9	424.7	424.4
175°	426.7	427.6	427.6	427.6	427.6
177.5°	426.9	427.6	427.6	427.6	427.6
180°	427.6	427.6	427.6	427.6	427.6



TEST NUMBER: P933980
 CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.55	15.68	15.27	16.42	17.30	17.40	18.53	18.12	19.27	20.15
	3H	15.05	16.06	15.78	16.81	17.72	18.77	19.79	19.51	20.54	21.45
	4H	15.25	16.20	16.00	16.97	17.89	19.23	20.19	19.99	20.95	21.88
	6H	15.38	16.26	16.15	17.03	17.97	19.54	20.42	20.30	21.19	22.13
	8H	15.39	16.23	16.17	17.02	17.96	19.62	20.46	20.40	21.25	22.19
	12H	15.37	16.17	16.15	16.95	17.92	19.67	20.47	20.46	21.26	22.23
4H	2H	15.62	16.57	16.38	17.33	18.26	17.84	18.80	18.60	19.56	20.48
	3H	16.67	17.47	17.44	18.26	19.21	19.38	20.17	20.15	20.97	21.91
	4H	16.96	17.68	17.74	18.48	19.45	19.92	20.64	20.71	21.44	22.41
	6H	17.10	17.72	17.90	18.54	19.52	20.31	20.93	21.11	21.75	22.73
	8H	17.11	17.69	17.92	18.51	19.50	20.42	21.01	21.23	21.82	22.82
	12H	17.09	17.62	17.92	18.45	19.45	20.50	21.02	21.32	21.86	22.86
8H	4H	17.44	18.02	18.24	18.84	19.83	20.07	20.65	20.87	21.47	22.46
	6H	17.71	18.19	18.54	19.05	20.04	20.52	21.00	21.35	21.86	22.86
	8H	17.75	18.18	18.60	19.04	20.05	20.68	21.11	21.52	21.96	22.97
	12H	17.75	18.13	18.60	18.98	20.04	20.79	21.17	21.64	22.02	23.08
12H	4H	17.46	17.98	18.28	18.82	19.82	20.04	20.57	20.87	21.41	22.41
	6H	17.77	18.20	18.62	19.06	20.07	20.52	20.95	21.36	21.81	22.81
	8H	17.85	18.23	18.70	19.08	20.14	20.70	21.08	21.54	21.92	22.99