

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934085

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934085
REPORT IS A COMBINATION OF REPORTS P933682 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4382.5 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 38.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934085
CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79			79
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70	67			67
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59	56			56
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	47			47
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41			41
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38	35			35
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33	31			31
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30	27			27
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26	24			24
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24	22			22
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22	20			20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12376	12376	12376	12376
5°	12455	12493	12455	9823
10°	12358	12306	12358	8798
15°	12209	12039	12209	10052
20°	11940	11723	11940	10074
25°	11404	11263	11404	9860
30°	10715	10880	10715	9392
35°	9538	10397	9538	8877
40°	7935	9827	7935	8487
45°	7076	9161	7076	8041
50°	7500	8366	7500	7591
55°	7037	7510	7037	7331
60°	7227	6376	7227	6715
65°	6523	5271	6523	5893
70°	4486	4202	4486	4940
75°	3889	3106	3889	3719
80°	3070	2052	3070	2236
85°	1673	1086	1673	924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 10866 cd/sqm



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.4	2.7
10°-20°	341.8	7.8
20°-30°	528.4	12.1
30°-40°	630.8	14.4
40°-50°	634.5	14.5
50°-60°	552.1	12.6
60°-70°	391.4	8.9
70°-80°	207.1	4.7
80°-90°	52.1	1.2
90°-100°	69.5	1.6
100°-110°	182.7	4.2
110°-120°	189.4	4.3
120°-130°	151.9	3.5
130°-140°	119.2	2.7
140°-150°	91.5	2.1
150°-160°	65.9	1.5
160°-170°	40.3	0.9
170°-180°	13.6	0.3
0°-30°	990.6	22.6
0°-40°	1621.4	37.0
0°-60°	2808.0	64.1
0°-90°	3458.6	78.9
90°-120°	441.5	10.1
90°-150°	804.1	18.3
90°-180°	924.0	21.1
0°-180°	4382.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1334	1334	1334	1334	1334	
5°	1340	1382	1340	1086	1340	127
15°	1279	1369	1279	1143	1279	360
25°	1127	1277	1127	1118	1127	517
35°	857	1139	857	973	857	530
45°	553	939	553	824	553	443
55°	450	693	450	676	450	414
65°	313	418	313	467	313	299
75°	119	198	119	237	119	125
85°	20	50	20	43	20	27
90°	1	4	1	4	1	2
95°	9	42	9	42	9	10
105°	33	286	33	286	33	35
115°	58	368	58	368	58	58
125°	81	293	81	293	81	72
135°	97	228	97	228	97	75
145°	112	185	112	185	112	70
155°	127	159	127	159	127	58
165°	137	148	137	148	137	39
175°	142	143	142	143	142	14
180°	142	142	142	142	142	



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1345.0	1345.0	1352.7	1355.1	1355.1	1351.3	1347.6	1351.3	1362.7	1366.5	1365.3
5°	1340.1	1350.1	1364.0	1366.5	1369.0	1367.8	1365.3	1367.8	1380.4	1382.9	1384.2
7.5°	1329.9	1348.8	1366.5	1370.3	1374.1	1370.3	1369.0	1371.6	1384.2	1386.7	1386.7
10°	1317.3	1343.8	1364.0	1366.5	1370.3	1366.5	1366.5	1371.6	1384.2	1386.7	1388.0
12.5°	1299.7	1336.2	1355.1	1357.7	1362.7	1361.4	1360.2	1365.3	1377.9	1380.4	1380.4
15°	1279.4	1322.4	1340.1	1342.5	1351.3	1348.8	1348.8	1353.9	1367.8	1371.6	1370.3
17.5°	1251.7	1304.7	1324.9	1328.7	1335.0	1333.7	1335.0	1340.1	1352.7	1355.1	1356.4
20°	1220.1	1280.8	1304.7	1308.4	1314.7	1314.7	1314.7	1321.1	1333.7	1338.7	1338.7
22.5°	1177.2	1255.4	1280.8	1283.2	1290.8	1290.8	1293.4	1302.1	1313.5	1314.7	1314.7
25°	1126.8	1227.7	1249.1	1256.8	1264.3	1268.0	1271.9	1276.9	1280.8	1279.4	1280.8
27.5°	1073.8	1192.4	1220.1	1225.2	1235.3	1239.1	1244.1	1245.4	1246.7	1250.4	1247.9
30°	1014.5	1143.1	1184.8	1189.8	1206.3	1208.7	1203.8	1206.3	1212.6	1215.1	1217.6
32.5°	947.6	1070.0	1148.2	1159.6	1174.7	1167.1	1165.9	1169.7	1179.8	1179.8	1182.3
35°	856.7	1013.3	1114.2	1124.2	1135.6	1126.8	1131.8	1133.1	1139.4	1143.1	1141.9
37.5°	757.0	964.0	1078.9	1086.4	1095.2	1083.8	1091.5	1095.2	1100.3	1097.8	1097.8
40°	668.8	887.0	1037.2	1042.2	1049.8	1041.0	1048.5	1051.1	1053.6	1051.1	1049.8
42.5°	603.2	802.5	993.0	999.3	994.3	1000.6	1003.1	1008.2	1004.4	999.3	999.3
45°	552.7	779.8	945.1	952.6	945.1	955.2	958.9	958.9	947.6	945.1	943.8
47.5°	536.2	734.4	897.1	897.1	893.3	905.9	912.3	903.4	892.1	888.3	888.3
50°	535.0	683.9	831.5	826.5	844.1	859.3	853.0	844.1	835.3	821.4	821.4
52.5°	485.8	622.1	747.0	765.9	793.7	802.5	792.4	783.6	768.4	762.1	757.0
55°	450.5	557.7	670.0	707.8	736.9	748.2	729.3	720.5	697.7	694.0	691.4
57.5°	442.9	464.3	599.4	647.3	682.6	681.4	670.0	653.6	634.7	630.9	629.6
60°	406.3	335.6	523.6	580.4	617.0	613.2	603.2	588.0	570.3	567.8	565.3
62.5°	368.4	243.5	437.9	502.2	553.9	552.7	543.9	521.1	508.5	502.2	497.2
65°	313.0	204.4	311.6	417.6	492.1	494.6	475.7	459.3	445.4	437.9	436.5
67.5°	238.5	166.6	210.7	348.3	432.8	430.2	406.3	398.7	381.0	377.2	369.7
70°	176.7	111.1	146.4	282.7	374.7	368.4	349.5	340.6	324.3	315.4	310.4
72.5°	146.4	89.6	107.2	219.6	315.4	307.9	291.5	281.3	267.5	260.0	254.9
75°	118.6	94.6	82.0	162.7	256.1	251.1	236.0	225.9	214.5	204.4	205.7
77.5°	87.1	88.3	65.6	119.9	203.1	195.6	186.7	174.1	169.0	159.0	159.0
80°	65.6	69.4	49.2	82.0	146.4	146.4	138.8	130.0	121.1	116.1	116.1
82.5°	44.1	44.1	36.6	51.8	99.7	95.9	90.8	88.3	83.3	80.8	80.8
85°	20.2	25.2	22.7	31.5	54.2	56.8	56.8	54.2	53.0	50.4	51.8
87.5°	6.3	11.4	13.8	17.7	27.8	29.0	30.3	30.3	30.3	31.5	31.5
90°	1.0	1.7	2.5	2.7	4.2	6.2	7.3	6.5	4.9	3.6	3.6
92.5°	3.8	10.3	16.8	18.4	26.0	36.0	41.0	35.9	25.8	18.1	17.4
95°	9.2	21.1	33.0	36.0	63.9	101.0	119.7	106.8	81.0	61.7	59.5
97.5°	15.9	26.4	36.9	39.5	86.0	148.0	179.1	170.9	154.6	142.4	138.2
100°	21.0	30.6	40.1	42.5	94.1	162.9	197.3	197.9	199.1	200.0	195.0
102.5°	25.4	34.3	43.3	45.5	97.8	167.6	202.5	212.9	233.6	249.2	244.9
105°	32.9	40.5	47.9	49.9	100.6	168.1	201.9	225.2	271.7	306.6	304.3
107.5°	40.6	47.6	54.6	56.3	101.0	160.6	190.4	222.9	287.7	336.4	337.0
110°	45.7	52.0	58.4	60.0	100.3	154.0	180.9	217.2	289.7	344.1	346.5



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	50.8	56.8	62.8	64.4	100.3	148.2	172.2	209.3	283.5	339.2	342.8
115°	58.4	64.0	69.5	71.0	101.2	141.6	161.8	197.5	269.0	322.6	327.7
117.5°	66.0	71.1	76.1	77.4	103.1	137.4	154.6	186.9	251.4	299.8	305.4
120°	70.4	75.2	79.9	81.1	104.6	136.0	151.7	181.2	240.2	284.4	289.8
122.5°	74.7	79.5	84.2	85.5	106.8	135.2	149.5	176.0	229.1	268.9	274.3
125°	81.3	85.7	90.1	91.2	109.8	134.7	147.1	169.6	214.8	248.6	253.6
127.5°	86.6	91.1	95.5	96.6	112.8	134.3	145.1	164.5	203.2	232.3	236.5
130°	89.5	94.3	99.0	100.3	115.0	134.6	144.3	161.6	196.1	221.9	225.8
132.5°	92.5	97.3	102.1	103.2	116.7	134.7	143.6	159.1	189.9	213.2	216.6
135°	96.9	101.2	105.6	106.7	118.6	134.6	142.5	155.4	181.3	200.6	203.6
137.5°	101.4	105.7	110.0	111.1	121.5	135.3	142.3	153.2	175.1	191.5	194.0
140°	105.1	109.1	113.1	114.0	123.2	135.5	141.6	151.1	170.0	184.1	186.4
142.5°	108.0	111.6	115.3	116.2	124.7	136.0	141.6	149.9	166.6	179.0	181.0
145°	112.4	115.6	118.8	119.6	126.6	136.0	140.7	147.5	161.0	171.2	172.8
147.5°	116.8	119.9	123.0	123.8	129.4	136.9	140.7	146.0	156.7	164.7	166.0
150°	119.7	122.4	125.3	126.0	130.8	137.4	140.7	145.2	154.2	161.0	162.0
152.5°	122.6	124.7	126.8	127.4	131.8	137.7	140.7	144.5	152.2	158.1	158.8
155°	127.0	128.5	130.2	130.5	133.9	138.4	140.7	143.7	149.9	154.5	155.0
157.5°	130.3	131.8	133.3	133.7	136.0	139.1	140.7	143.1	147.8	151.4	151.7
160°	132.5	133.6	134.8	135.1	136.9	139.4	140.7	142.7	146.8	149.8	150.0
162.5°	134.7	135.5	136.5	136.7	138.0	139.8	140.7	142.4	145.8	148.4	148.6
165°	137.0	137.8	138.7	138.9	139.4	140.3	140.7	141.9	144.4	146.2	146.4
167.5°	139.2	139.6	140.0	140.1	140.6	141.2	141.6	142.4	144.0	145.3	145.4
170°	140.7	141.1	141.4	141.5	141.5	141.6	141.6	142.4	144.0	145.3	145.3
172.5°	141.4	141.5	141.6	141.6	141.6	141.6	141.6	142.3	143.5	144.5	144.4
175°	142.5	142.5	142.5	142.5	142.2	141.8	141.6	142.0	142.9	143.4	143.4
177.5°	142.5	142.5	142.5	142.5	142.3	142.0	141.8	142.1	142.8	143.2	143.2
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1367.8	1364.0	1367.8	1365.3	1366.5	1362.7	1351.3	1347.6	1351.3	1355.1	1355.1
5°	1384.2	1381.7	1384.2	1384.2	1382.9	1380.4	1367.8	1365.3	1367.8	1369.0	1366.5
7.5°	1389.2	1385.4	1389.2	1386.7	1386.7	1384.2	1371.6	1369.0	1370.3	1374.1	1370.3
10°	1389.2	1385.4	1389.2	1388.0	1386.7	1384.2	1371.6	1366.5	1366.5	1370.3	1366.5
12.5°	1382.9	1380.4	1382.9	1380.4	1380.4	1377.9	1365.3	1360.2	1361.4	1362.7	1357.7
15°	1372.8	1369.0	1372.8	1370.3	1371.6	1367.8	1353.9	1348.8	1348.8	1351.3	1342.5
17.5°	1357.7	1352.7	1357.7	1356.4	1355.1	1352.7	1340.1	1335.0	1333.7	1335.0	1328.7
20°	1340.1	1336.2	1340.1	1338.7	1338.7	1333.7	1321.1	1314.7	1314.7	1314.7	1308.4
22.5°	1312.3	1308.4	1312.3	1314.7	1314.7	1313.5	1302.1	1293.4	1290.8	1290.8	1283.2
25°	1280.8	1276.9	1280.8	1280.8	1279.4	1280.8	1276.9	1271.9	1268.0	1264.3	1256.8
27.5°	1250.4	1247.9	1250.4	1247.9	1250.4	1246.7	1245.4	1244.1	1239.1	1235.3	1225.2
30°	1220.1	1217.6	1220.1	1217.6	1215.1	1212.6	1206.3	1203.8	1208.7	1206.3	1189.8
32.5°	1182.3	1179.8	1182.3	1182.3	1179.8	1179.8	1169.7	1165.9	1167.1	1174.7	1159.6
35°	1143.1	1139.4	1143.1	1141.9	1143.1	1139.4	1133.1	1131.8	1126.8	1135.6	1124.2
37.5°	1097.8	1094.0	1097.8	1097.8	1097.8	1100.3	1095.2	1091.5	1083.8	1095.2	1086.4
40°	1051.1	1046.0	1051.1	1049.8	1051.1	1053.6	1051.1	1048.5	1041.0	1049.8	1042.2
42.5°	998.1	996.8	998.1	999.3	999.3	1004.4	1008.2	1003.1	1000.6	994.3	999.3
45°	941.2	938.8	941.2	943.8	945.1	947.6	958.9	958.9	955.2	945.1	952.6
47.5°	880.7	874.4	880.7	888.3	888.3	892.1	903.4	912.3	905.9	893.3	897.1
50°	816.3	817.7	816.3	821.4	821.4	835.3	844.1	853.0	859.3	844.1	826.5
52.5°	753.3	752.1	753.3	757.0	762.1	768.4	783.6	792.4	802.5	793.7	765.9
55°	690.2	692.8	690.2	691.4	694.0	697.7	720.5	729.3	748.2	736.9	707.8
57.5°	627.1	623.3	627.1	629.6	630.9	634.7	653.6	670.0	681.4	682.6	647.3
60°	553.9	548.8	553.9	565.3	567.8	570.3	588.0	603.2	613.2	617.0	580.4
62.5°	489.5	480.7	489.5	497.2	502.2	508.5	521.1	543.9	552.7	553.9	502.2
65°	421.4	417.6	421.4	436.5	437.9	445.4	459.3	475.7	494.6	492.1	417.6
67.5°	359.7	359.7	359.7	369.7	377.2	381.0	398.7	406.3	430.2	432.8	348.3
70°	302.8	301.6	302.8	310.4	315.4	324.3	340.6	349.5	368.4	374.7	282.7
72.5°	248.6	247.3	248.6	254.9	260.0	267.5	281.3	291.5	307.9	315.4	219.6
75°	200.6	198.1	200.6	205.7	204.4	214.5	225.9	236.0	251.1	256.1	162.7
77.5°	153.9	153.9	153.9	159.0	159.0	169.0	174.1	186.7	195.6	203.1	119.9
80°	114.8	113.5	114.8	116.1	116.1	121.1	130.0	138.8	146.4	146.4	82.0
82.5°	80.8	78.2	80.8	80.8	80.8	83.3	88.3	90.8	95.9	99.7	51.8
85°	50.4	50.4	50.4	51.8	50.4	53.0	54.2	56.8	56.8	54.2	31.5
87.5°	32.9	31.5	32.9	31.5	31.5	30.3	30.3	30.3	29.0	27.8	17.7
90°	3.6	3.6	3.6	3.6	3.6	4.9	6.5	7.3	6.2	4.2	2.7
92.5°	14.5	11.7	14.5	17.4	18.1	25.8	35.9	41.0	36.0	26.0	18.4
95°	50.8	42.0	50.8	59.5	61.7	81.0	106.8	119.7	101.0	63.9	36.0
97.5°	121.6	105.0	121.6	138.2	142.4	154.6	170.9	179.1	148.0	86.0	39.5
100°	175.2	155.4	175.2	195.0	200.0	199.1	197.9	197.3	162.9	94.1	42.5
102.5°	227.9	210.9	227.9	244.9	249.2	233.6	212.9	202.5	167.6	97.8	45.5
105°	295.2	286.0	295.2	304.3	306.6	271.7	225.2	201.9	168.1	100.6	49.9
107.5°	339.2	341.4	339.2	337.0	336.4	287.7	222.9	190.4	160.6	101.0	56.3
110°	355.9	365.5	355.9	346.5	344.1	289.7	217.2	180.9	154.0	100.3	60.0



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	357.5	372.1	357.5	342.8	339.2	283.5	209.3	172.2	148.2	100.3	64.4
115°	348.0	368.2	348.0	327.7	322.6	269.0	197.5	161.8	141.6	101.2	71.0
117.5°	327.9	350.4	327.9	305.4	299.8	251.4	186.9	154.6	137.4	103.1	77.4
120°	311.7	333.5	311.7	289.8	284.4	240.2	181.2	151.7	136.0	104.6	81.1
122.5°	295.9	317.4	295.9	274.3	268.9	229.1	176.0	149.5	135.2	106.8	85.5
125°	273.4	293.3	273.4	253.6	248.6	214.8	169.6	147.1	134.7	109.8	91.2
127.5°	253.2	269.9	253.2	236.5	232.3	203.2	164.5	145.1	134.3	112.8	96.6
130°	241.2	256.7	241.2	225.8	221.9	196.1	161.6	144.3	134.6	115.0	100.3
132.5°	230.4	244.3	230.4	216.6	213.2	189.9	159.1	143.6	134.7	116.7	103.2
135°	215.6	227.6	215.6	203.6	200.6	181.3	155.4	142.5	134.6	118.6	106.7
137.5°	203.7	213.5	203.7	194.0	191.5	175.1	153.2	142.3	135.3	121.5	111.1
140°	195.5	204.7	195.5	186.4	184.1	170.0	151.1	141.6	135.5	123.2	114.0
142.5°	188.8	196.6	188.8	181.0	179.0	166.6	149.9	141.6	136.0	124.7	116.2
145°	178.7	184.6	178.7	172.8	171.2	161.0	147.5	140.7	136.0	126.6	119.6
147.5°	170.8	175.8	170.8	166.0	164.7	156.7	146.0	140.7	136.9	129.4	123.8
150°	166.0	170.0	166.0	162.0	161.0	154.2	145.2	140.7	137.4	130.8	126.0
152.5°	161.8	164.8	161.8	158.8	158.1	152.2	144.5	140.7	137.7	131.8	127.4
155°	157.0	159.0	157.0	155.0	154.5	149.9	143.7	140.7	138.4	133.9	130.5
157.5°	153.2	154.6	153.2	151.7	151.4	147.8	143.1	140.7	139.1	136.0	133.7
160°	150.9	151.7	150.9	150.0	149.8	146.8	142.7	140.7	139.4	136.9	135.1
162.5°	149.4	150.1	149.4	148.6	148.4	145.8	142.4	140.7	139.8	138.0	136.7
165°	147.3	148.0	147.3	146.4	146.2	144.4	141.9	140.7	140.3	139.4	138.9
167.5°	145.6	146.0	145.6	145.4	145.3	144.0	142.4	141.6	141.2	140.6	140.1
170°	145.3	145.3	145.3	145.3	145.3	144.0	142.4	141.6	141.6	141.5	141.5
172.5°	144.1	143.8	144.1	144.4	144.5	143.5	142.3	141.6	141.6	141.6	141.6
175°	143.4	143.4	143.4	143.4	143.4	142.9	142.0	141.6	141.8	142.2	142.5
177.5°	142.9	142.5	142.9	143.2	143.2	142.8	142.1	141.8	142.0	142.3	142.5
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1352.7	1345.0	1345.0	1332.4	1327.4	1323.6	1317.3	1298.4	1293.4	1288.3	1295.8
5°	1364.0	1350.1	1340.1	1317.3	1298.4	1290.8	1266.8	1221.4	1191.1	1168.4	1155.8
7.5°	1366.5	1348.8	1329.9	1294.6	1249.1	1229.0	1155.8	1072.6	1049.8	1029.6	1017.0
10°	1364.0	1343.8	1317.3	1264.3	1157.1	1121.7	1048.5	994.3	980.4	976.6	980.4
12.5°	1355.1	1336.2	1299.7	1211.3	1061.2	1037.2	994.3	962.7	960.3	966.6	1000.6
15°	1340.1	1322.4	1279.4	1140.7	1008.2	990.5	960.3	948.9	962.7	1006.9	1109.1
17.5°	1324.9	1304.7	1251.7	1071.2	967.8	955.2	933.7	956.4	1034.6	1094.0	1128.0
20°	1304.7	1280.8	1220.1	1020.8	938.8	927.4	917.3	1019.6	1078.9	1100.3	1119.2
22.5°	1280.8	1255.4	1177.2	985.5	908.5	899.6	905.9	1054.9	1078.9	1094.0	1110.4
25°	1249.1	1227.7	1126.8	957.7	884.5	874.4	898.4	1051.1	1064.9	1068.7	1101.5
27.5°	1220.1	1192.4	1073.8	932.5	855.5	851.7	904.7	1034.6	1044.8	1048.5	1083.8
30°	1184.8	1143.1	1014.5	905.9	825.2	824.0	905.9	1014.5	1011.9	1022.0	1057.4
32.5°	1148.2	1070.0	947.6	873.2	796.2	794.9	897.1	984.2	981.6	995.6	1022.0
35°	1114.2	1013.3	856.7	835.3	759.6	760.8	875.6	948.9	950.1	962.7	979.2
37.5°	1078.9	964.0	757.0	793.7	724.3	724.3	846.6	916.0	913.6	917.3	940.0
40°	1037.2	887.0	668.8	739.4	691.4	687.7	811.4	880.7	871.9	870.7	902.2
42.5°	993.0	802.5	603.2	667.4	653.6	648.5	768.4	837.8	821.4	825.2	865.6
45°	945.1	779.8	552.7	564.0	614.4	610.7	721.7	788.6	777.3	787.4	829.0
47.5°	897.1	734.4	536.2	468.1	572.8	571.6	670.0	740.7	734.4	744.4	788.6
50°	831.5	683.9	535.0	401.3	526.2	531.2	608.1	694.0	694.0	702.8	749.5
52.5°	747.0	622.1	485.8	363.4	471.9	487.0	553.9	653.6	656.1	665.0	706.6
55°	670.0	557.7	450.5	334.3	407.6	440.4	500.9	612.0	617.0	625.8	663.7
57.5°	599.4	464.3	442.9	300.3	348.3	379.8	454.2	571.6	574.1	581.7	618.3
60°	523.6	335.6	406.3	263.7	296.5	320.5	411.3	523.6	532.5	537.5	569.1
62.5°	437.9	243.5	368.4	238.5	271.3	276.4	376.0	478.2	489.5	493.4	512.3
65°	311.6	204.4	313.0	217.1	244.8	246.0	338.2	431.6	441.6	447.9	461.8
67.5°	210.7	166.6	238.5	196.8	224.6	225.9	301.6	377.2	391.2	396.2	405.0
70°	146.4	111.1	176.7	175.4	201.9	204.4	262.4	328.0	340.6	344.5	349.5
72.5°	107.2	89.6	146.4	157.8	177.9	180.4	222.0	272.6	285.2	289.0	291.5
75°	82.0	94.6	118.6	137.5	151.4	152.7	181.7	222.0	230.9	233.4	234.6
77.5°	65.6	88.3	87.1	111.1	123.7	121.1	142.6	171.6	179.2	179.2	179.2
80°	49.2	69.4	65.6	79.5	90.8	88.3	102.2	122.4	124.9	127.4	126.2
82.5°	36.6	44.1	44.1	50.4	60.5	58.1	68.1	79.5	79.5	79.5	82.0
85°	22.7	25.2	20.2	26.5	34.1	32.9	37.8	42.9	44.1	44.1	41.6
87.5°	13.8	11.4	6.3	10.1	15.2	15.2	17.7	18.9	17.7	17.7	17.7
90°	2.5	1.7	1.0	1.7	2.5	2.7	4.2	6.2	7.3	6.5	4.9
92.5°	16.8	10.3	3.8	10.3	16.8	18.4	26.0	36.0	41.0	35.9	25.8
95°	33.0	21.1	9.2	21.1	33.0	36.0	63.9	101.0	119.7	106.8	81.0
97.5°	36.9	26.4	15.9	26.4	36.9	39.5	86.0	148.0	179.1	170.9	154.6
100°	40.1	30.6	21.0	30.6	40.1	42.5	94.1	162.9	197.3	197.9	199.1
102.5°	43.3	34.3	25.4	34.3	43.3	45.5	97.8	167.6	202.5	212.9	233.6
105°	47.9	40.5	32.9	40.5	47.9	49.9	100.6	168.1	201.9	225.2	271.7
107.5°	54.6	47.6	40.6	47.6	54.6	56.3	101.0	160.6	190.4	222.9	287.7
110°	58.4	52.0	45.7	52.0	58.4	60.0	100.3	154.0	180.9	217.2	289.7



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	62.8	56.8	50.8	56.8	62.8	64.4	100.3	148.2	172.2	209.3	283.5
115°	69.5	64.0	58.4	64.0	69.5	71.0	101.2	141.6	161.8	197.5	269.0
117.5°	76.1	71.1	66.0	71.1	76.1	77.4	103.1	137.4	154.6	186.9	251.4
120°	79.9	75.2	70.4	75.2	79.9	81.1	104.6	136.0	151.7	181.2	240.2
122.5°	84.2	79.5	74.7	79.5	84.2	85.5	106.8	135.2	149.5	176.0	229.1
125°	90.1	85.7	81.3	85.7	90.1	91.2	109.8	134.7	147.1	169.6	214.8
127.5°	95.5	91.1	86.6	91.1	95.5	96.6	112.8	134.3	145.1	164.5	203.2
130°	99.0	94.3	89.5	94.3	99.0	100.3	115.0	134.6	144.3	161.6	196.1
132.5°	102.1	97.3	92.5	97.3	102.1	103.2	116.7	134.7	143.6	159.1	189.9
135°	105.6	101.2	96.9	101.2	105.6	106.7	118.6	134.6	142.5	155.4	181.3
137.5°	110.0	105.7	101.4	105.7	110.0	111.1	121.5	135.3	142.3	153.2	175.1
140°	113.1	109.1	105.1	109.1	113.1	114.0	123.2	135.5	141.6	151.1	170.0
142.5°	115.3	111.6	108.0	111.6	115.3	116.2	124.7	136.0	141.6	149.9	166.6
145°	118.8	115.6	112.4	115.6	118.8	119.6	126.6	136.0	140.7	147.5	161.0
147.5°	123.0	119.9	116.8	119.9	123.0	123.8	129.4	136.9	140.7	146.0	156.7
150°	125.3	122.4	119.7	122.4	125.3	126.0	130.8	137.4	140.7	145.2	154.2
152.5°	126.8	124.7	122.6	124.7	126.8	127.4	131.8	137.7	140.7	144.5	152.2
155°	130.2	128.5	127.0	128.5	130.2	130.5	133.9	138.4	140.7	143.7	149.9
157.5°	133.3	131.8	130.3	131.8	133.3	133.7	136.0	139.1	140.7	143.1	147.8
160°	134.8	133.6	132.5	133.6	134.8	135.1	136.9	139.4	140.7	142.7	146.8
162.5°	136.5	135.5	134.7	135.5	136.5	136.7	138.0	139.8	140.7	142.4	145.8
165°	138.7	137.8	137.0	137.8	138.7	138.9	139.4	140.3	140.7	141.9	144.4
167.5°	140.0	139.6	139.2	139.6	140.0	140.1	140.6	141.2	141.6	142.4	144.0
170°	141.4	141.1	140.7	141.1	141.4	141.5	141.5	141.6	141.6	142.4	144.0
172.5°	141.6	141.5	141.4	141.5	141.6	141.6	141.6	141.6	141.6	142.3	143.5
175°	142.5	142.5	142.5	142.5	142.5	142.5	142.2	141.8	141.6	142.0	142.9
177.5°	142.5	142.5	142.5	142.5	142.5	142.5	142.3	142.0	141.8	142.1	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1287.1	1283.2	1288.3	1274.4	1288.3	1283.2	1287.1	1295.8	1288.3	1293.4	1298.4
5°	1129.3	1123.0	1102.8	1086.4	1102.8	1123.0	1129.3	1155.8	1168.4	1191.1	1221.4
7.5°	1009.4	1004.4	999.3	989.2	999.3	1004.4	1009.4	1017.0	1029.6	1049.8	1072.6
10°	982.9	984.2	991.8	990.5	991.8	984.2	982.9	980.4	976.6	980.4	994.3
12.5°	1051.1	1062.4	1104.1	1101.5	1104.1	1062.4	1051.1	1000.6	966.6	960.3	962.7
15°	1129.3	1133.1	1141.9	1143.1	1141.9	1133.1	1129.3	1109.1	1006.9	962.7	948.9
17.5°	1136.8	1138.2	1144.5	1144.5	1144.5	1138.2	1136.8	1128.0	1094.0	1034.6	956.4
20°	1130.5	1133.1	1145.7	1148.2	1145.7	1133.1	1130.5	1119.2	1100.3	1078.9	1019.6
22.5°	1128.0	1133.1	1143.1	1141.9	1143.1	1133.1	1128.0	1110.4	1094.0	1078.9	1054.9
25°	1115.4	1115.4	1116.7	1117.9	1116.7	1115.4	1115.4	1101.5	1068.7	1064.9	1051.1
27.5°	1088.9	1091.5	1099.0	1097.8	1099.0	1091.5	1088.9	1083.8	1048.5	1044.8	1034.6
30°	1064.9	1062.4	1056.1	1051.1	1056.1	1062.4	1064.9	1057.4	1022.0	1011.9	1014.5
32.5°	1024.5	1018.2	1011.9	1008.2	1011.9	1018.2	1024.5	1022.0	995.6	981.6	984.2
35°	976.6	977.9	976.6	972.9	976.6	977.9	976.6	979.2	962.7	950.1	948.9
37.5°	942.6	945.1	943.8	938.8	943.8	945.1	942.6	940.0	917.3	913.6	916.0
40°	907.2	908.5	907.2	903.4	907.2	908.5	907.2	902.2	870.7	871.9	880.7
42.5°	873.2	871.9	868.1	865.6	868.1	871.9	873.2	865.6	825.2	821.4	837.8
45°	834.0	835.3	827.7	824.0	827.7	835.3	834.0	829.0	787.4	777.3	788.6
47.5°	794.9	794.9	788.6	784.8	788.6	794.9	794.9	788.6	744.4	734.4	740.7
50°	753.3	752.1	743.2	741.9	743.2	752.1	753.3	749.5	702.8	694.0	694.0
52.5°	705.4	705.4	706.6	709.1	706.6	705.4	705.4	706.6	665.0	656.1	653.6
55°	663.7	665.0	673.8	676.3	673.8	665.0	663.7	663.7	625.8	617.0	612.0
57.5°	620.8	620.8	627.1	627.1	627.1	620.8	620.8	618.3	581.7	574.1	571.6
60°	571.6	574.1	579.1	577.9	579.1	574.1	571.6	569.1	537.5	532.5	523.6
62.5°	519.8	522.4	523.6	521.1	523.6	522.4	519.8	512.3	493.4	489.5	478.2
65°	465.6	468.1	469.4	466.9	469.4	468.1	465.6	461.8	447.9	441.6	431.6
67.5°	410.1	408.8	407.6	412.6	407.6	408.8	410.1	405.0	396.2	391.2	377.2
70°	353.3	353.3	352.0	354.6	352.0	353.3	353.3	349.5	344.5	340.6	328.0
72.5°	292.7	291.5	296.5	292.7	296.5	291.5	292.7	291.5	289.0	285.2	272.6
75°	233.4	236.0	233.4	237.2	233.4	236.0	233.4	234.6	233.4	230.9	222.0
77.5°	177.9	180.4	177.9	177.9	177.9	180.4	177.9	179.2	179.2	179.2	171.6
80°	126.2	124.9	124.9	123.7	124.9	124.9	126.2	126.2	127.4	124.9	122.4
82.5°	80.8	79.5	79.5	82.0	79.5	79.5	80.8	82.0	79.5	79.5	79.5
85°	44.1	45.5	42.9	42.9	42.9	45.5	44.1	41.6	44.1	44.1	42.9
87.5°	16.4	15.2	15.2	15.2	15.2	15.2	16.4	17.7	17.7	17.7	18.9
90°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.9	6.5	7.3	6.2
92.5°	18.1	17.4	14.5	11.7	14.5	17.4	18.1	25.8	35.9	41.0	36.0
95°	61.7	59.5	50.8	42.0	50.8	59.5	61.7	81.0	106.8	119.7	101.0
97.5°	142.4	138.2	121.6	105.0	121.6	138.2	142.4	154.6	170.9	179.1	148.0
100°	200.0	195.0	175.2	155.4	175.2	195.0	200.0	199.1	197.9	197.3	162.9
102.5°	249.2	244.9	227.9	210.9	227.9	244.9	249.2	233.6	212.9	202.5	167.6
105°	306.6	304.3	295.2	286.0	295.2	304.3	306.6	271.7	225.2	201.9	168.1
107.5°	336.4	337.0	339.2	341.4	339.2	337.0	336.4	287.7	222.9	190.4	160.6
110°	344.1	346.5	355.9	365.5	355.9	346.5	344.1	289.7	217.2	180.9	154.0



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	339.2	342.8	357.5	372.1	357.5	342.8	339.2	283.5	209.3	172.2	148.2
115°	322.6	327.7	348.0	368.2	348.0	327.7	322.6	269.0	197.5	161.8	141.6
117.5°	299.8	305.4	327.9	350.4	327.9	305.4	299.8	251.4	186.9	154.6	137.4
120°	284.4	289.8	311.7	333.5	311.7	289.8	284.4	240.2	181.2	151.7	136.0
122.5°	268.9	274.3	295.9	317.4	295.9	274.3	268.9	229.1	176.0	149.5	135.2
125°	248.6	253.6	273.4	293.3	273.4	253.6	248.6	214.8	169.6	147.1	134.7
127.5°	232.3	236.5	253.2	269.9	253.2	236.5	232.3	203.2	164.5	145.1	134.3
130°	221.9	225.8	241.2	256.7	241.2	225.8	221.9	196.1	161.6	144.3	134.6
132.5°	213.2	216.6	230.4	244.3	230.4	216.6	213.2	189.9	159.1	143.6	134.7
135°	200.6	203.6	215.6	227.6	215.6	203.6	200.6	181.3	155.4	142.5	134.6
137.5°	191.5	194.0	203.7	213.5	203.7	194.0	191.5	175.1	153.2	142.3	135.3
140°	184.1	186.4	195.5	204.7	195.5	186.4	184.1	170.0	151.1	141.6	135.5
142.5°	179.0	181.0	188.8	196.6	188.8	181.0	179.0	166.6	149.9	141.6	136.0
145°	171.2	172.8	178.7	184.6	178.7	172.8	171.2	161.0	147.5	140.7	136.0
147.5°	164.7	166.0	170.8	175.8	170.8	166.0	164.7	156.7	146.0	140.7	136.9
150°	161.0	162.0	166.0	170.0	166.0	162.0	161.0	154.2	145.2	140.7	137.4
152.5°	158.1	158.8	161.8	164.8	161.8	158.8	158.1	152.2	144.5	140.7	137.7
155°	154.5	155.0	157.0	159.0	157.0	155.0	154.5	149.9	143.7	140.7	138.4
157.5°	151.4	151.7	153.2	154.6	153.2	151.7	151.4	147.8	143.1	140.7	139.1
160°	149.8	150.0	150.9	151.7	150.9	150.0	149.8	146.8	142.7	140.7	139.4
162.5°	148.4	148.6	149.4	150.1	149.4	148.6	148.4	145.8	142.4	140.7	139.8
165°	146.2	146.4	147.3	148.0	147.3	146.4	146.2	144.4	141.9	140.7	140.3
167.5°	145.3	145.4	145.6	146.0	145.6	145.4	145.3	144.0	142.4	141.6	141.2
170°	145.3	145.3	145.3	145.3	145.3	145.3	145.3	144.0	142.4	141.6	141.6
172.5°	144.5	144.4	144.1	143.8	144.1	144.4	144.5	143.5	142.3	141.6	141.6
175°	143.4	143.4	143.4	143.4	143.4	143.4	143.4	142.9	142.0	141.6	141.8
177.5°	143.2	143.2	142.9	142.5	142.9	143.2	143.2	142.8	142.1	141.8	142.0
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1317.3	1323.6	1327.4	1332.4	1345.0
5°	1266.8	1290.8	1298.4	1317.3	1340.1
7.5°	1155.8	1229.0	1249.1	1294.6	1329.9
10°	1048.5	1121.7	1157.1	1264.3	1317.3
12.5°	994.3	1037.2	1061.2	1211.3	1299.7
15°	960.3	990.5	1008.2	1140.7	1279.4
17.5°	933.7	955.2	967.8	1071.2	1251.7
20°	917.3	927.4	938.8	1020.8	1220.1
22.5°	905.9	899.6	908.5	985.5	1177.2
25°	898.4	874.4	884.5	957.7	1126.8
27.5°	904.7	851.7	855.5	932.5	1073.8
30°	905.9	824.0	825.2	905.9	1014.5
32.5°	897.1	794.9	796.2	873.2	947.6
35°	875.6	760.8	759.6	835.3	856.7
37.5°	846.6	724.3	724.3	793.7	757.0
40°	811.4	687.7	691.4	739.4	668.8
42.5°	768.4	648.5	653.6	667.4	603.2
45°	721.7	610.7	614.4	564.0	552.7
47.5°	670.0	571.6	572.8	468.1	536.2
50°	608.1	531.2	526.2	401.3	535.0
52.5°	553.9	487.0	471.9	363.4	485.8
55°	500.9	440.4	407.6	334.3	450.5
57.5°	454.2	379.8	348.3	300.3	442.9
60°	411.3	320.5	296.5	263.7	406.3
62.5°	376.0	276.4	271.3	238.5	368.4
65°	338.2	246.0	244.8	217.1	313.0
67.5°	301.6	225.9	224.6	196.8	238.5
70°	262.4	204.4	201.9	175.4	176.7
72.5°	222.0	180.4	177.9	157.8	146.4
75°	181.7	152.7	151.4	137.5	118.6
77.5°	142.6	121.1	123.7	111.1	87.1
80°	102.2	88.3	90.8	79.5	65.6
82.5°	68.1	58.1	60.5	50.4	44.1
85°	37.8	32.9	34.1	26.5	20.2
87.5°	17.7	15.2	15.2	10.1	6.3
90°	4.2	2.7	2.5	1.7	1.0
92.5°	26.0	18.4	16.8	10.3	3.8
95°	63.9	36.0	33.0	21.1	9.2
97.5°	86.0	39.5	36.9	26.4	15.9
100°	94.1	42.5	40.1	30.6	21.0
102.5°	97.8	45.5	43.3	34.3	25.4
105°	100.6	49.9	47.9	40.5	32.9
107.5°	101.0	56.3	54.6	47.6	40.6
110°	100.3	60.0	58.4	52.0	45.7



TEST NUMBER: P934085

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	100.3	64.4	62.8	56.8	50.8
115°	101.2	71.0	69.5	64.0	58.4
117.5°	103.1	77.4	76.1	71.1	66.0
120°	104.6	81.1	79.9	75.2	70.4
122.5°	106.8	85.5	84.2	79.5	74.7
125°	109.8	91.2	90.1	85.7	81.3
127.5°	112.8	96.6	95.5	91.1	86.6
130°	115.0	100.3	99.0	94.3	89.5
132.5°	116.7	103.2	102.1	97.3	92.5
135°	118.6	106.7	105.6	101.2	96.9
137.5°	121.5	111.1	110.0	105.7	101.4
140°	123.2	114.0	113.1	109.1	105.1
142.5°	124.7	116.2	115.3	111.6	108.0
145°	126.6	119.6	118.8	115.6	112.4
147.5°	129.4	123.8	123.0	119.9	116.8
150°	130.8	126.0	125.3	122.4	119.7
152.5°	131.8	127.4	126.8	124.7	122.6
155°	133.9	130.5	130.2	128.5	127.0
157.5°	136.0	133.7	133.3	131.8	130.3
160°	136.9	135.1	134.8	133.6	132.5
162.5°	138.0	136.7	136.5	135.5	134.7
165°	139.4	138.9	138.7	137.8	137.0
167.5°	140.6	140.1	140.0	139.6	139.2
170°	141.5	141.5	141.4	141.1	140.7
172.5°	141.6	141.6	141.6	141.5	141.4
175°	142.2	142.5	142.5	142.5	142.5
177.5°	142.3	142.5	142.5	142.5	142.5
180°	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P934085
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-4-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.87	17.07	16.53	17.75	18.53	18.67	19.86	19.33	20.54	21.33
	3H	16.37	17.45	17.05	18.14	18.96	20.03	21.10	20.70	21.79	22.61
	4H	16.58	17.59	17.27	18.29	19.13	20.48	21.49	21.17	22.19	23.03
	6H	16.71	17.65	17.42	18.36	19.21	20.77	21.71	21.48	22.42	23.27
	8H	16.72	17.62	17.44	18.35	19.20	20.85	21.75	21.57	22.48	23.33
	12H	16.71	17.56	17.43	18.28	19.16	20.90	21.75	21.62	22.48	23.35
4H	2H	16.93	17.95	17.63	18.65	19.48	19.12	20.13	19.81	20.83	21.67
	3H	17.99	18.84	18.70	19.57	20.43	20.64	21.49	21.35	22.23	23.08
	4H	18.28	19.05	19.01	19.79	20.67	21.18	21.95	21.91	22.69	23.57
	6H	18.43	19.09	19.17	19.86	20.75	21.56	22.22	22.30	22.99	23.88
	8H	18.44	19.06	19.19	19.82	20.73	21.66	22.29	22.42	23.05	23.95
	12H	18.42	18.98	19.19	19.77	20.68	21.73	22.29	22.50	23.08	23.99
8H	4H	18.76	19.38	19.51	20.14	21.04	21.33	21.95	22.08	22.71	23.62
	6H	19.03	19.55	19.81	20.35	21.26	21.77	22.29	22.55	23.09	24.00
	8H	19.08	19.54	19.87	20.34	21.26	21.92	22.38	22.72	23.19	24.11
	12H	19.08	19.48	19.87	20.28	21.26	22.03	22.44	22.83	23.23	24.21
12H	4H	18.78	19.34	19.55	20.12	21.03	21.31	21.87	22.08	22.66	23.56
	6H	19.09	19.55	19.89	20.36	21.28	21.77	22.23	22.57	23.04	23.96
	8H	19.18	19.58	19.97	20.37	21.36	21.95	22.35	22.74	23.14	24.12