

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933981

Luminaire Tested: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933981
REPORT IS A COMBINATION OF REPORTS P933677 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10391.6 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933981
CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	78	78	78	74
1	103	99	95	91	98	94	90	87	85	82	80	77	75	73	69	68	66	66	66	66	62
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	61	58	56	56	56	56	52
3	86	76	68	62	81	72	66	60	66	60	56	60	55	52	54	51	48	48	48	48	44
4	79	67	59	53	74	64	57	51	59	52	48	53	48	44	48	44	41	41	41	41	38
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	36	36	36	36	33
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	31	31	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	28	28	28	26
8	57	44	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	25	25	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	23	23	23	23	21
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	20	20	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9161	9161	9161	9161
5°	9233	9248	9233	7271
10°	9175	9109	9175	6513
15°	9078	8912	9078	7442
20°	8892	8678	8892	7457
25°	8507	8337	8507	7299
30°	8008	8054	8008	6952
35°	7142	7696	7142	6571
40°	5955	7274	5955	6283
45°	5324	6781	5324	5951
50°	5660	6192	5660	5619
55°	5331	5558	5331	5427
60°	5502	4721	5502	4970
65°	4997	3902	4997	4362
70°	3468	3110	3468	3657
75°	3053	2299	3053	2753
80°	2478	1520	2478	1655
85°	1452	805	1452	684

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 8155 cd/sqm



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.4	2.6
10°-20°	759.1	7.3
20°-30°	1173.4	11.3
30°-40°	1400.8	13.5
40°-50°	1409.0	13.6
50°-60°	1226.0	11.8
60°-70°	869.2	8.4
70°-80°	459.9	4.4
80°-90°	116.1	1.1
90°-100°	203.8	2.0
100°-110°	535.9	5.2
110°-120°	555.7	5.3
120°-130°	445.7	4.3
130°-140°	349.7	3.4
140°-150°	268.4	2.6
150°-160°	193.3	1.9
160°-170°	118.3	1.1
170°-180°	40.0	0.4
0°-30°	2199.9	21.2
0°-40°	3600.6	34.6
0°-60°	6235.6	60.0
0°-90°	7680.9	73.9
90°-120°	1295.4	12.5
90°-150°	2359.2	22.7
90°-180°	2711.0	26.1
0°-180°	10391.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2962	2962	2962	2962	2962	
5°	2976	3068	2976	2412	2976	282
15°	2841	3040	2841	2539	2841	799
25°	2502	2836	2502	2483	2502	1149
35°	1903	2530	1903	2160	1903	1177
45°	1227	2085	1227	1830	1227	983
55°	1000	1538	1000	1502	1000	919
65°	695	928	695	1037	695	664
75°	263	440	263	527	263	277
85°	45	112	45	95	45	61
90°	3	11	3	11	3	4
95°	27	123	27	123	27	30
105°	97	839	97	839	97	102
115°	172	1080	172	1080	172	169
125°	238	860	238	860	238	212
135°	284	668	284	668	284	220
145°	330	542	330	542	330	207
155°	373	466	373	466	373	171
165°	402	434	402	434	402	114
175°	418	421	418	421	418	40
180°	418	418	418	418	418	



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8
2.5°	2987.0	2987.0	3003.8	3009.4	3009.4	3001.0	2992.6	3001.0	3026.3	3034.7	3031.9
5°	2975.8	2998.2	3029.1	3034.7	3040.3	3037.5	3031.9	3037.5	3065.5	3071.1	3073.9
7.5°	2953.4	2995.4	3034.7	3043.1	3051.5	3043.1	3040.3	3045.9	3073.9	3079.5	3079.5
10°	2925.4	2984.2	3029.1	3034.7	3043.1	3034.7	3034.7	3045.9	3073.9	3079.5	3082.3
12.5°	2886.2	2967.4	3009.4	3015.0	3026.3	3023.5	3020.6	3031.9	3059.9	3065.5	3065.5
15°	2841.3	2936.6	2975.8	2981.4	3001.0	2995.4	2995.4	3006.6	3037.5	3045.9	3043.1
17.5°	2779.7	2897.4	2942.2	2950.6	2964.6	2961.8	2964.6	2975.8	3003.8	3009.4	3012.2
20°	2709.6	2844.1	2897.4	2905.8	2919.8	2919.8	2919.8	2933.8	2961.8	2973.0	2973.0
22.5°	2614.4	2788.1	2844.1	2849.7	2866.5	2866.5	2872.1	2891.8	2917.0	2919.8	2919.8
25°	2502.3	2726.4	2774.1	2790.9	2807.7	2816.1	2824.5	2835.7	2844.1	2841.3	2844.1
27.5°	2384.5	2648.0	2709.6	2720.8	2743.3	2751.7	2762.9	2765.7	2768.5	2776.9	2771.3
30°	2252.8	2538.7	2631.2	2642.4	2678.8	2684.4	2673.2	2678.8	2692.8	2698.4	2704.0
32.5°	2104.3	2376.1	2549.9	2575.1	2608.8	2591.9	2589.1	2597.5	2620.0	2620.0	2625.6
35°	1902.6	2250.0	2474.3	2496.7	2521.9	2502.3	2513.5	2516.3	2530.3	2538.7	2535.9
37.5°	1681.2	2140.7	2395.7	2412.5	2432.1	2406.9	2423.7	2432.1	2443.3	2437.7	2437.7
40°	1485.1	1969.8	2303.2	2314.5	2331.3	2311.6	2328.5	2334.1	2339.7	2334.1	2331.3
42.5°	1339.4	1782.1	2205.2	2219.2	2208.0	2222.0	2227.6	2238.8	2230.4	2219.2	2219.2
45°	1227.3	1731.6	2098.7	2115.5	2098.7	2121.1	2129.5	2129.5	2104.3	2098.7	2095.9
47.5°	1190.9	1630.8	1992.2	1992.2	1983.8	2011.8	2025.8	2006.2	1981.0	1972.6	1972.6
50°	1188.0	1518.7	1846.5	1835.3	1874.5	1908.2	1894.2	1874.5	1854.9	1824.1	1824.1
52.5°	1078.8	1381.4	1658.8	1700.8	1762.5	1782.1	1759.7	1740.0	1706.4	1692.4	1681.2
55°	1000.3	1238.5	1487.9	1571.9	1636.4	1661.6	1619.6	1599.9	1549.5	1541.1	1535.5
57.5°	983.5	1031.1	1331.0	1437.4	1515.9	1513.1	1487.9	1451.4	1409.4	1401.0	1398.2
60°	902.2	745.3	1162.8	1288.9	1370.2	1361.8	1339.4	1305.7	1266.5	1260.9	1255.3
62.5°	818.2	540.8	972.3	1115.2	1230.1	1227.3	1207.7	1157.2	1129.2	1115.2	1104.0
65°	694.9	453.9	692.1	927.5	1092.8	1098.4	1056.4	1019.9	989.1	972.3	969.5
67.5°	529.6	369.9	467.9	773.4	961.1	955.5	902.2	885.4	846.2	837.8	821.0
70°	392.3	246.6	325.0	627.6	832.2	818.2	776.2	756.5	720.1	700.5	689.3
72.5°	325.0	198.9	238.2	487.5	700.5	683.7	647.3	624.8	594.0	577.2	566.0
75°	263.4	210.2	182.1	361.5	568.8	557.6	524.0	501.6	476.3	453.9	456.7
77.5°	193.3	196.1	145.7	266.2	451.1	434.3	414.7	386.7	375.5	353.1	353.1
80°	145.7	154.1	109.3	182.1	325.0	325.0	308.2	288.6	269.0	257.8	257.8
82.5°	98.1	98.1	81.3	114.9	221.4	213.0	201.7	196.1	184.9	179.3	179.3
85°	44.8	56.0	50.4	70.0	120.5	126.1	126.1	120.5	117.7	112.1	114.9
87.5°	14.0	25.2	30.8	39.2	61.6	64.4	67.2	67.2	67.2	70.0	70.0
90°	2.8	5.0	7.3	7.8	12.3	18.3	21.3	19.0	14.2	10.6	10.6
92.5°	11.2	30.3	49.4	54.2	76.1	105.4	120.1	105.3	75.6	53.3	51.2
95°	26.9	61.8	96.8	105.5	187.4	296.5	351.1	313.3	237.7	181.0	174.6
97.5°	46.6	77.4	108.3	115.9	252.4	434.4	525.4	501.5	453.7	417.9	405.6
100°	61.7	89.7	117.6	124.6	276.1	478.0	579.0	580.8	584.2	586.8	572.3
102.5°	74.6	100.7	126.7	133.3	286.9	491.8	594.1	624.6	685.4	731.0	718.5
105°	96.6	118.6	140.7	146.2	295.0	493.2	592.4	660.6	797.1	899.4	892.7
107.5°	119.0	139.5	160.2	165.3	296.5	471.3	558.7	653.9	844.2	987.1	988.6
110°	134.1	152.7	171.3	176.0	294.2	451.9	530.7	637.1	849.8	1009.5	1016.5



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	149.1	166.7	184.5	188.9	294.3	434.9	505.2	614.1	831.8	995.2	1005.9
115°	171.5	187.8	204.2	208.3	297.0	415.3	474.6	579.5	789.2	946.6	961.5
117.5°	193.6	208.5	223.3	227.1	302.5	403.2	453.6	548.3	737.6	879.5	896.1
120°	206.5	220.5	234.5	238.0	307.0	399.0	445.1	531.5	704.6	834.3	850.4
122.5°	219.2	233.3	247.3	250.9	313.5	396.9	438.6	516.5	672.3	789.1	804.9
125°	238.5	251.4	264.3	267.5	322.2	395.2	431.6	497.7	630.1	729.4	743.9
127.5°	254.2	267.2	280.2	283.5	330.9	394.1	425.7	482.5	596.2	681.4	693.7
130°	262.6	276.7	290.7	294.1	337.3	394.7	423.5	474.1	575.3	651.1	662.5
132.5°	271.4	285.3	299.3	302.8	342.4	395.2	421.5	466.8	557.4	625.3	635.5
135°	284.3	297.0	309.7	312.9	348.0	394.8	418.2	456.1	531.9	588.8	597.6
137.5°	297.5	310.1	322.6	325.8	356.4	397.2	417.6	449.6	513.7	561.8	569.0
140°	308.4	320.0	331.7	334.6	361.6	397.6	415.6	443.3	498.7	540.2	547.0
142.5°	316.8	327.6	338.3	341.0	365.8	399.0	415.6	439.9	488.6	525.1	530.9
145°	329.8	339.1	348.5	350.8	371.5	399.0	412.8	432.7	472.5	502.3	506.7
147.5°	342.7	351.7	360.9	363.1	379.7	401.8	412.8	428.5	459.8	483.3	486.9
150°	351.1	359.3	367.5	369.6	384.0	403.2	412.8	426.1	452.5	472.3	475.2
152.5°	359.8	366.0	372.2	373.8	386.8	404.1	412.8	424.1	446.7	463.6	465.9
155°	372.7	377.2	381.9	383.0	392.9	406.2	412.8	421.8	439.8	453.3	454.8
157.5°	382.2	386.7	391.3	392.4	399.2	408.3	412.8	419.8	433.7	444.2	445.2
160°	388.7	392.2	395.7	396.6	402.0	409.2	412.8	418.8	430.8	439.7	440.3
162.5°	395.2	397.8	400.4	401.1	405.0	410.2	412.8	417.9	428.0	435.5	436.1
165°	402.2	404.5	406.9	407.5	409.3	411.6	412.8	416.5	423.7	429.1	429.6
167.5°	408.6	409.7	410.9	411.1	412.6	414.6	415.6	418.0	422.7	426.3	426.6
170°	412.8	413.9	415.1	415.3	415.4	415.5	415.6	418.0	422.7	426.3	426.3
172.5°	415.1	415.3	415.5	415.6	415.6	415.6	415.6	417.5	421.2	424.0	423.8
175°	418.2	418.2	418.2	418.2	417.3	416.2	415.6	416.8	419.2	421.0	421.0
177.5°	418.2	418.2	418.2	418.2	417.5	416.7	416.2	417.1	419.0	420.4	420.1
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8
2.5°	3037.5	3029.1	3037.5	3031.9	3034.7	3026.3	3001.0	2992.6	3001.0	3009.4	3009.4
5°	3073.9	3068.3	3073.9	3073.9	3071.1	3065.5	3037.5	3031.9	3037.5	3040.3	3034.7
7.5°	3085.1	3076.7	3085.1	3079.5	3079.5	3073.9	3045.9	3040.3	3043.1	3051.5	3043.1
10°	3085.1	3076.7	3085.1	3082.3	3079.5	3073.9	3045.9	3034.7	3034.7	3043.1	3034.7
12.5°	3071.1	3065.5	3071.1	3065.5	3065.5	3059.9	3031.9	3020.6	3023.5	3026.3	3015.0
15°	3048.7	3040.3	3048.7	3043.1	3045.9	3037.5	3006.6	2995.4	2995.4	3001.0	2981.4
17.5°	3015.0	3003.8	3015.0	3012.2	3009.4	3003.8	2975.8	2964.6	2961.8	2964.6	2950.6
20°	2975.8	2967.4	2975.8	2973.0	2973.0	2961.8	2933.8	2919.8	2919.8	2919.8	2905.8
22.5°	2914.2	2905.8	2914.2	2919.8	2919.8	2917.0	2891.8	2872.1	2866.5	2866.5	2849.7
25°	2844.1	2835.7	2844.1	2844.1	2841.3	2844.1	2835.7	2824.5	2816.1	2807.7	2790.9
27.5°	2776.9	2771.3	2776.9	2771.3	2776.9	2768.5	2765.7	2762.9	2751.7	2743.3	2720.8
30°	2709.6	2704.0	2709.6	2704.0	2698.4	2692.8	2678.8	2673.2	2684.4	2678.8	2642.4
32.5°	2625.6	2620.0	2625.6	2625.6	2620.0	2620.0	2597.5	2589.1	2591.9	2608.8	2575.1
35°	2538.7	2530.3	2538.7	2535.9	2538.7	2530.3	2516.3	2513.5	2502.3	2521.9	2496.7
37.5°	2437.7	2429.3	2437.7	2437.7	2437.7	2443.3	2432.1	2423.7	2406.9	2432.1	2412.5
40°	2334.1	2322.9	2334.1	2331.3	2334.1	2339.7	2334.1	2328.5	2311.6	2331.3	2314.5
42.5°	2216.4	2213.6	2216.4	2219.2	2219.2	2230.4	2238.8	2227.6	2222.0	2208.0	2219.2
45°	2090.3	2084.7	2090.3	2095.9	2098.7	2104.3	2129.5	2129.5	2121.1	2098.7	2115.5
47.5°	1955.8	1941.8	1955.8	1972.6	1972.6	1981.0	2006.2	2025.8	2011.8	1983.8	1992.2
50°	1812.9	1815.7	1812.9	1824.1	1824.1	1854.9	1874.5	1894.2	1908.2	1874.5	1835.3
52.5°	1672.8	1670.0	1672.8	1681.2	1692.4	1706.4	1740.0	1759.7	1782.1	1762.5	1700.8
55°	1532.7	1538.3	1532.7	1535.5	1541.1	1549.5	1599.9	1619.6	1661.6	1636.4	1571.9
57.5°	1392.6	1384.2	1392.6	1398.2	1401.0	1409.4	1451.4	1487.9	1513.1	1515.9	1437.4
60°	1230.1	1218.9	1230.1	1255.3	1260.9	1266.5	1305.7	1339.4	1361.8	1370.2	1288.9
62.5°	1087.2	1067.6	1087.2	1104.0	1115.2	1129.2	1157.2	1207.7	1227.3	1230.1	1115.2
65°	935.9	927.5	935.9	969.5	972.3	989.1	1019.9	1056.4	1098.4	1092.8	927.5
67.5°	798.6	798.6	798.6	821.0	837.8	846.2	885.4	902.2	955.5	961.1	773.4
70°	672.5	669.7	672.5	689.3	700.5	720.1	756.5	776.2	818.2	832.2	627.6
72.5°	552.0	549.2	552.0	566.0	577.2	594.0	624.8	647.3	683.7	700.5	487.5
75°	445.5	439.9	445.5	456.7	453.9	476.3	501.6	524.0	557.6	568.8	361.5
77.5°	341.8	341.8	341.8	353.1	353.1	375.5	386.7	414.7	434.3	451.1	266.2
80°	255.0	252.2	255.0	257.8	257.8	269.0	288.6	308.2	325.0	325.0	182.1
82.5°	179.3	173.7	179.3	179.3	179.3	184.9	196.1	201.7	213.0	221.4	114.9
85°	112.1	112.1	112.1	114.9	112.1	117.7	120.5	126.1	126.1	120.5	70.0
87.5°	72.9	70.0	72.9	70.0	70.0	67.2	67.2	67.2	64.4	61.6	39.2
90°	10.6	10.6	10.6	10.6	10.6	14.2	19.0	21.3	18.3	12.3	7.8
92.5°	42.8	34.3	42.8	51.2	53.3	75.6	105.3	120.1	105.4	76.1	54.2
95°	148.9	123.2	148.9	174.6	181.0	237.7	313.3	351.1	296.5	187.4	105.5
97.5°	356.8	307.8	356.8	405.6	417.9	453.7	501.5	525.4	434.4	252.4	115.9
100°	514.1	455.8	514.1	572.3	586.8	584.2	580.8	579.0	478.0	276.1	124.6
102.5°	668.7	618.8	668.7	718.5	731.0	685.4	624.6	594.1	491.8	286.9	133.3
105°	865.9	839.1	865.9	892.7	899.4	797.1	660.6	592.4	493.2	295.0	146.2
107.5°	995.2	1001.6	995.2	988.6	987.1	844.2	653.9	558.7	471.3	296.5	165.3
110°	1044.4	1072.3	1044.4	1016.5	1009.5	849.8	637.1	530.7	451.9	294.2	176.0



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1048.8	1091.7	1048.8	1005.9	995.2	831.8	614.1	505.2	434.9	294.3	188.9
115°	1021.0	1080.5	1021.0	961.5	946.6	789.2	579.5	474.6	415.3	297.0	208.3
117.5°	962.0	1028.0	962.0	896.1	879.5	737.6	548.3	453.6	403.2	302.5	227.1
120°	914.5	978.6	914.5	850.4	834.3	704.6	531.5	445.1	399.0	307.0	238.0
122.5°	868.2	931.5	868.2	804.9	789.1	672.3	516.5	438.6	396.9	313.5	250.9
125°	802.1	860.4	802.1	743.9	729.4	630.1	497.7	431.6	395.2	322.2	267.5
127.5°	742.8	791.9	742.8	693.7	681.4	596.2	482.5	425.7	394.1	330.9	283.5
130°	707.9	753.3	707.9	662.5	651.1	575.3	474.1	423.5	394.7	337.3	294.1
132.5°	676.1	716.8	676.1	635.5	625.3	557.4	466.8	421.5	395.2	342.4	302.8
135°	632.6	667.6	632.6	597.6	588.8	531.9	456.1	418.2	394.8	348.0	312.9
137.5°	597.7	626.4	597.7	569.0	561.8	513.7	449.6	417.6	397.2	356.4	325.8
140°	573.8	600.6	573.8	547.0	540.2	498.7	443.3	415.6	397.6	361.6	334.6
142.5°	554.0	577.0	554.0	530.9	525.1	488.6	439.9	415.6	399.0	365.8	341.0
145°	524.2	541.6	524.2	506.7	502.3	472.5	432.7	412.8	399.0	371.5	350.8
147.5°	501.4	515.8	501.4	486.9	483.3	459.8	428.5	412.8	401.8	379.7	363.1
150°	487.0	498.7	487.0	475.2	472.3	452.5	426.1	412.8	403.2	384.0	369.6
152.5°	474.7	483.5	474.7	465.9	463.6	446.7	424.1	412.8	404.1	386.8	373.8
155°	460.6	466.4	460.6	454.8	453.3	439.8	421.8	412.8	406.2	392.9	383.0
157.5°	449.4	453.6	449.4	445.2	444.2	433.7	419.8	412.8	408.3	399.2	392.4
160°	442.7	445.1	442.7	440.3	439.7	430.8	418.8	412.8	409.2	402.0	396.6
162.5°	438.3	440.6	438.3	436.1	435.5	428.0	417.9	412.8	410.2	405.0	401.1
165°	432.1	434.4	432.1	429.6	429.1	423.7	416.5	412.8	411.6	409.3	407.5
167.5°	427.5	428.5	427.5	426.6	426.3	422.7	418.0	415.6	414.6	412.6	411.1
170°	426.3	426.3	426.3	426.3	426.3	422.7	418.0	415.6	415.5	415.4	415.3
172.5°	422.9	422.1	422.9	423.8	424.0	421.2	417.5	415.6	415.6	415.6	415.6
175°	421.0	421.0	421.0	421.0	421.0	419.2	416.8	415.6	416.2	417.3	418.2
177.5°	419.2	418.2	419.2	420.1	420.4	419.0	417.1	416.2	416.7	417.5	418.2
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8
2.5°	3003.8	2987.0	2987.0	2959.0	2947.8	2939.4	2925.4	2883.4	2872.1	2860.9	2877.7
5°	3029.1	2998.2	2975.8	2925.4	2883.4	2866.5	2813.3	2712.4	2645.2	2594.7	2566.7
7.5°	3034.7	2995.4	2953.4	2874.9	2774.1	2729.2	2566.7	2381.7	2331.3	2286.4	2258.4
10°	3029.1	2984.2	2925.4	2807.7	2569.5	2491.1	2328.5	2208.0	2177.2	2168.7	2177.2
12.5°	3009.4	2967.4	2886.2	2690.0	2356.5	2303.2	2208.0	2137.9	2132.3	2146.3	2222.0
15°	2975.8	2936.6	2841.3	2533.1	2238.8	2199.6	2132.3	2107.1	2137.9	2236.0	2463.0
17.5°	2942.2	2897.4	2779.7	2378.9	2149.1	2121.1	2073.5	2123.9	2297.6	2429.3	2505.1
20°	2897.4	2844.1	2709.6	2266.8	2084.7	2059.5	2037.1	2264.0	2395.7	2443.3	2485.5
22.5°	2844.1	2788.1	2614.4	2188.4	2017.4	1997.8	2011.8	2342.5	2395.7	2429.3	2465.8
25°	2774.1	2726.4	2502.3	2126.7	1964.2	1941.8	1995.0	2334.1	2364.9	2373.3	2446.1
27.5°	2709.6	2648.0	2384.5	2070.7	1899.8	1891.4	2009.0	2297.6	2320.1	2328.5	2406.9
30°	2631.2	2538.7	2252.8	2011.8	1832.5	1829.7	2011.8	2252.8	2247.2	2269.6	2348.1
32.5°	2549.9	2376.1	2104.3	1939.0	1768.1	1765.3	1992.2	2185.6	2180.0	2210.8	2269.6
35°	2474.3	2250.0	1902.6	1854.9	1686.8	1689.6	1944.6	2107.1	2109.9	2137.9	2174.4
37.5°	2395.7	2140.7	1681.2	1762.5	1608.3	1608.3	1880.1	2034.3	2028.6	2037.1	2087.5
40°	2303.2	1969.8	1485.1	1642.0	1535.5	1527.1	1801.7	1955.8	1936.2	1933.4	2003.4
42.5°	2205.2	1782.1	1339.4	1482.3	1451.4	1440.2	1706.4	1860.5	1824.1	1832.5	1922.2
45°	2098.7	1731.6	1227.3	1252.5	1364.6	1356.2	1602.7	1751.2	1726.0	1748.4	1840.9
47.5°	1992.2	1630.8	1190.9	1039.5	1272.1	1269.3	1487.9	1644.8	1630.8	1653.2	1751.2
50°	1846.5	1518.7	1188.0	891.0	1168.4	1179.6	1350.6	1541.1	1541.1	1560.7	1664.4
52.5°	1658.8	1381.4	1078.8	807.0	1047.9	1081.6	1230.1	1451.4	1457.0	1476.7	1569.1
55°	1487.9	1238.5	1000.3	742.5	905.0	977.9	1112.4	1359.0	1370.2	1389.8	1473.9
57.5°	1331.0	1031.1	983.5	666.9	773.4	843.4	1008.7	1269.3	1274.9	1291.7	1373.0
60°	1162.8	745.3	902.2	585.6	658.5	711.7	913.5	1162.8	1182.4	1193.7	1263.7
62.5°	972.3	540.8	818.2	529.6	602.4	613.6	835.0	1062.0	1087.2	1095.6	1137.6
65°	692.1	453.9	694.9	481.9	543.6	546.4	750.9	958.3	980.7	994.7	1025.5
67.5°	467.9	369.9	529.6	437.1	498.8	501.6	669.7	837.8	868.6	879.8	899.4
70°	325.0	246.6	392.3	389.5	448.3	453.9	582.8	728.5	756.5	764.9	776.2
72.5°	238.2	198.9	325.0	350.2	395.1	400.7	493.2	605.2	633.3	641.7	647.3
75°	182.1	210.2	263.4	305.4	336.2	339.0	403.5	493.2	512.8	518.4	521.2
77.5°	145.7	196.1	193.3	246.6	274.6	269.0	316.6	381.1	397.9	397.9	397.9
80°	109.3	154.1	145.7	176.5	201.7	196.1	227.0	271.8	277.4	283.0	280.2
82.5°	81.3	98.1	98.1	112.1	134.5	128.9	151.3	176.5	176.5	176.5	182.1
85°	50.4	56.0	44.8	58.8	75.7	72.9	84.1	95.3	98.1	98.1	92.5
87.5°	30.8	25.2	14.0	22.4	33.6	33.6	39.2	42.0	39.2	39.2	39.2
90°	7.3	5.0	2.8	5.0	7.3	7.8	12.3	18.3	21.3	19.0	14.2
92.5°	49.4	30.3	11.2	30.3	49.4	54.2	76.1	105.4	120.1	105.3	75.6
95°	96.8	61.8	26.9	61.8	96.8	105.5	187.4	296.5	351.1	313.3	237.7
97.5°	108.3	77.4	46.6	77.4	108.3	115.9	252.4	434.4	525.4	501.5	453.7
100°	117.6	89.7	61.7	89.7	117.6	124.6	276.1	478.0	579.0	580.8	584.2
102.5°	126.7	100.7	74.6	100.7	126.7	133.3	286.9	491.8	594.1	624.6	685.4
105°	140.7	118.6	96.6	118.6	140.7	146.2	295.0	493.2	592.4	660.6	797.1
107.5°	160.2	139.5	119.0	139.5	160.2	165.3	296.5	471.3	558.7	653.9	844.2
110°	171.3	152.7	134.1	152.7	171.3	176.0	294.2	451.9	530.7	637.1	849.8



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	184.5	166.7	149.1	166.7	184.5	188.9	294.3	434.9	505.2	614.1	831.8
115°	204.2	187.8	171.5	187.8	204.2	208.3	297.0	415.3	474.6	579.5	789.2
117.5°	223.3	208.5	193.6	208.5	223.3	227.1	302.5	403.2	453.6	548.3	737.6
120°	234.5	220.5	206.5	220.5	234.5	238.0	307.0	399.0	445.1	531.5	704.6
122.5°	247.3	233.3	219.2	233.3	247.3	250.9	313.5	396.9	438.6	516.5	672.3
125°	264.3	251.4	238.5	251.4	264.3	267.5	322.2	395.2	431.6	497.7	630.1
127.5°	280.2	267.2	254.2	267.2	280.2	283.5	330.9	394.1	425.7	482.5	596.2
130°	290.7	276.7	262.6	276.7	290.7	294.1	337.3	394.7	423.5	474.1	575.3
132.5°	299.3	285.3	271.4	285.3	299.3	302.8	342.4	395.2	421.5	466.8	557.4
135°	309.7	297.0	284.3	297.0	309.7	312.9	348.0	394.8	418.2	456.1	531.9
137.5°	322.6	310.1	297.5	310.1	322.6	325.8	356.4	397.2	417.6	449.6	513.7
140°	331.7	320.0	308.4	320.0	331.7	334.6	361.6	397.6	415.6	443.3	498.7
142.5°	338.3	327.6	316.8	327.6	338.3	341.0	365.8	399.0	415.6	439.9	488.6
145°	348.5	339.1	329.8	339.1	348.5	350.8	371.5	399.0	412.8	432.7	472.5
147.5°	360.9	351.7	342.7	351.7	360.9	363.1	379.7	401.8	412.8	428.5	459.8
150°	367.5	359.3	351.1	359.3	367.5	369.6	384.0	403.2	412.8	426.1	452.5
152.5°	372.2	366.0	359.8	366.0	372.2	373.8	386.8	404.1	412.8	424.1	446.7
155°	381.9	377.2	372.7	377.2	381.9	383.0	392.9	406.2	412.8	421.8	439.8
157.5°	391.3	386.7	382.2	386.7	391.3	392.4	399.2	408.3	412.8	419.8	433.7
160°	395.7	392.2	388.7	392.2	395.7	396.6	402.0	409.2	412.8	418.8	430.8
162.5°	400.4	397.8	395.2	397.8	400.4	401.1	405.0	410.2	412.8	417.9	428.0
165°	406.9	404.5	402.2	404.5	406.9	407.5	409.3	411.6	412.8	416.5	423.7
167.5°	410.9	409.7	408.6	409.7	410.9	411.1	412.6	414.6	415.6	418.0	422.7
170°	415.1	413.9	412.8	413.9	415.1	415.3	415.4	415.5	415.6	418.0	422.7
172.5°	415.5	415.3	415.1	415.3	415.5	415.6	415.6	415.6	415.6	417.5	421.2
175°	418.2	418.2	418.2	418.2	418.2	418.2	417.3	416.2	415.6	416.8	419.2
177.5°	418.2	418.2	418.2	418.2	418.2	418.2	417.5	416.7	416.2	417.1	419.0
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8	2961.8
2.5°	2858.1	2849.7	2860.9	2830.1	2860.9	2849.7	2858.1	2877.7	2860.9	2872.1	2883.4
5°	2507.9	2493.9	2448.9	2412.5	2448.9	2493.9	2507.9	2566.7	2594.7	2645.2	2712.4
7.5°	2241.6	2230.4	2219.2	2196.8	2219.2	2230.4	2241.6	2258.4	2286.4	2331.3	2381.7
10°	2182.8	2185.6	2202.4	2199.6	2202.4	2185.6	2182.8	2177.2	2168.7	2177.2	2208.0
12.5°	2334.1	2359.3	2451.8	2446.1	2451.8	2359.3	2334.1	2222.0	2146.3	2132.3	2137.9
15°	2507.9	2516.3	2535.9	2538.7	2535.9	2516.3	2507.9	2463.0	2236.0	2137.9	2107.1
17.5°	2524.7	2527.5	2541.5	2541.5	2541.5	2527.5	2524.7	2505.1	2429.3	2297.6	2123.9
20°	2510.7	2516.3	2544.3	2549.9	2544.3	2516.3	2510.7	2485.5	2443.3	2395.7	2264.0
22.5°	2505.1	2516.3	2538.7	2535.9	2538.7	2516.3	2505.1	2465.8	2429.3	2395.7	2342.5
25°	2477.1	2477.1	2479.9	2482.7	2479.9	2477.1	2477.1	2446.1	2373.3	2364.9	2334.1
27.5°	2418.1	2423.7	2440.5	2437.7	2440.5	2423.7	2418.1	2406.9	2328.5	2320.1	2297.6
30°	2364.9	2359.3	2345.3	2334.1	2345.3	2359.3	2364.9	2348.1	2269.6	2247.2	2252.8
32.5°	2275.2	2261.2	2247.2	2238.8	2247.2	2261.2	2275.2	2269.6	2210.8	2180.0	2185.6
35°	2168.7	2171.6	2168.7	2160.3	2168.7	2171.6	2168.7	2174.4	2137.9	2109.9	2107.1
37.5°	2093.1	2098.7	2095.9	2084.7	2095.9	2098.7	2093.1	2087.5	2037.1	2028.6	2034.3
40°	2014.6	2017.4	2014.6	2006.2	2014.6	2017.4	2014.6	2003.4	1933.4	1936.2	1955.8
42.5°	1939.0	1936.2	1927.8	1922.2	1927.8	1936.2	1939.0	1922.2	1832.5	1824.1	1860.5
45°	1852.1	1854.9	1838.1	1829.7	1838.1	1854.9	1852.1	1840.9	1748.4	1726.0	1751.2
47.5°	1765.3	1765.3	1751.2	1742.8	1751.2	1765.3	1765.3	1751.2	1653.2	1630.8	1644.8
50°	1672.8	1670.0	1650.4	1647.6	1650.4	1670.0	1672.8	1664.4	1560.7	1541.1	1541.1
52.5°	1566.3	1566.3	1569.1	1574.7	1569.1	1566.3	1566.3	1569.1	1476.7	1457.0	1451.4
55°	1473.9	1476.7	1496.3	1501.9	1496.3	1476.7	1473.9	1473.9	1389.8	1370.2	1359.0
57.5°	1378.6	1378.6	1392.6	1392.6	1392.6	1378.6	1378.6	1373.0	1291.7	1274.9	1269.3
60°	1269.3	1274.9	1286.1	1283.3	1286.1	1274.9	1269.3	1263.7	1193.7	1182.4	1162.8
62.5°	1154.4	1160.0	1162.8	1157.2	1162.8	1160.0	1154.4	1137.6	1095.6	1087.2	1062.0
65°	1033.9	1039.5	1042.3	1036.7	1042.3	1039.5	1033.9	1025.5	994.7	980.7	958.3
67.5°	910.6	907.8	905.0	916.3	905.0	907.8	910.6	899.4	879.8	868.6	837.8
70°	784.6	784.6	781.8	787.4	781.8	784.6	784.6	776.2	764.9	756.5	728.5
72.5°	650.1	647.3	658.5	650.1	658.5	647.3	650.1	647.3	641.7	633.3	605.2
75°	518.4	524.0	518.4	526.8	518.4	524.0	518.4	521.2	518.4	512.8	493.2
77.5°	395.1	400.7	395.1	395.1	395.1	400.7	395.1	397.9	397.9	397.9	381.1
80°	280.2	277.4	277.4	274.6	277.4	277.4	280.2	280.2	283.0	277.4	271.8
82.5°	179.3	176.5	176.5	182.1	176.5	176.5	179.3	182.1	176.5	176.5	176.5
85°	98.1	100.9	95.3	95.3	95.3	100.9	98.1	92.5	98.1	98.1	95.3
87.5°	36.4	33.6	33.6	33.6	33.6	33.6	36.4	39.2	39.2	39.2	42.0
90°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	14.2	19.0	21.3	18.3
92.5°	53.3	51.2	42.8	34.3	42.8	51.2	53.3	75.6	105.3	120.1	105.4
95°	181.0	174.6	148.9	123.2	148.9	174.6	181.0	237.7	313.3	351.1	296.5
97.5°	417.9	405.6	356.8	307.8	356.8	405.6	417.9	453.7	501.5	525.4	434.4
100°	586.8	572.3	514.1	455.8	514.1	572.3	586.8	584.2	580.8	579.0	478.0
102.5°	731.0	718.5	668.7	618.8	668.7	718.5	731.0	685.4	624.6	594.1	491.8
105°	899.4	892.7	865.9	839.1	865.9	892.7	899.4	797.1	660.6	592.4	493.2
107.5°	987.1	988.6	995.2	1001.6	995.2	988.6	987.1	844.2	653.9	558.7	471.3
110°	1009.5	1016.5	1044.4	1072.3	1044.4	1016.5	1009.5	849.8	637.1	530.7	451.9



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	995.2	1005.9	1048.8	1091.7	1048.8	1005.9	995.2	831.8	614.1	505.2	434.9
115°	946.6	961.5	1021.0	1080.5	1021.0	961.5	946.6	789.2	579.5	474.6	415.3
117.5°	879.5	896.1	962.0	1028.0	962.0	896.1	879.5	737.6	548.3	453.6	403.2
120°	834.3	850.4	914.5	978.6	914.5	850.4	834.3	704.6	531.5	445.1	399.0
122.5°	789.1	804.9	868.2	931.5	868.2	804.9	789.1	672.3	516.5	438.6	396.9
125°	729.4	743.9	802.1	860.4	802.1	743.9	729.4	630.1	497.7	431.6	395.2
127.5°	681.4	693.7	742.8	791.9	742.8	693.7	681.4	596.2	482.5	425.7	394.1
130°	651.1	662.5	707.9	753.3	707.9	662.5	651.1	575.3	474.1	423.5	394.7
132.5°	625.3	635.5	676.1	716.8	676.1	635.5	625.3	557.4	466.8	421.5	395.2
135°	588.8	597.6	632.6	667.6	632.6	597.6	588.8	531.9	456.1	418.2	394.8
137.5°	561.8	569.0	597.7	626.4	597.7	569.0	561.8	513.7	449.6	417.6	397.2
140°	540.2	547.0	573.8	600.6	573.8	547.0	540.2	498.7	443.3	415.6	397.6
142.5°	525.1	530.9	554.0	577.0	554.0	530.9	525.1	488.6	439.9	415.6	399.0
145°	502.3	506.7	524.2	541.6	524.2	506.7	502.3	472.5	432.7	412.8	399.0
147.5°	483.3	486.9	501.4	515.8	501.4	486.9	483.3	459.8	428.5	412.8	401.8
150°	472.3	475.2	487.0	498.7	487.0	475.2	472.3	452.5	426.1	412.8	403.2
152.5°	463.6	465.9	474.7	483.5	474.7	465.9	463.6	446.7	424.1	412.8	404.1
155°	453.3	454.8	460.6	466.4	460.6	454.8	453.3	439.8	421.8	412.8	406.2
157.5°	444.2	445.2	449.4	453.6	449.4	445.2	444.2	433.7	419.8	412.8	408.3
160°	439.7	440.3	442.7	445.1	442.7	440.3	439.7	430.8	418.8	412.8	409.2
162.5°	435.5	436.1	438.3	440.6	438.3	436.1	435.5	428.0	417.9	412.8	410.2
165°	429.1	429.6	432.1	434.4	432.1	429.6	429.1	423.7	416.5	412.8	411.6
167.5°	426.3	426.6	427.5	428.5	427.5	426.6	426.3	422.7	418.0	415.6	414.6
170°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	422.7	418.0	415.6	415.5
172.5°	424.0	423.8	422.9	422.1	422.9	423.8	424.0	421.2	417.5	415.6	415.6
175°	421.0	421.0	421.0	421.0	421.0	421.0	421.0	419.2	416.8	415.6	416.2
177.5°	420.4	420.1	419.2	418.2	419.2	420.1	420.4	419.0	417.1	416.2	416.7
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2961.8	2961.8	2961.8	2961.8	2961.8
2.5°	2925.4	2939.4	2947.8	2959.0	2987.0
5°	2813.3	2866.5	2883.4	2925.4	2975.8
7.5°	2566.7	2729.2	2774.1	2874.9	2953.4
10°	2328.5	2491.1	2569.5	2807.7	2925.4
12.5°	2208.0	2303.2	2356.5	2690.0	2886.2
15°	2132.3	2199.6	2238.8	2533.1	2841.3
17.5°	2073.5	2121.1	2149.1	2378.9	2779.7
20°	2037.1	2059.5	2084.7	2266.8	2709.6
22.5°	2011.8	1997.8	2017.4	2188.4	2614.4
25°	1995.0	1941.8	1964.2	2126.7	2502.3
27.5°	2009.0	1891.4	1899.8	2070.7	2384.5
30°	2011.8	1829.7	1832.5	2011.8	2252.8
32.5°	1992.2	1765.3	1768.1	1939.0	2104.3
35°	1944.6	1689.6	1686.8	1854.9	1902.6
37.5°	1880.1	1608.3	1608.3	1762.5	1681.2
40°	1801.7	1527.1	1535.5	1642.0	1485.1
42.5°	1706.4	1440.2	1451.4	1482.3	1339.4
45°	1602.7	1356.2	1364.6	1252.5	1227.3
47.5°	1487.9	1269.3	1272.1	1039.5	1190.9
50°	1350.6	1179.6	1168.4	891.0	1188.0
52.5°	1230.1	1081.6	1047.9	807.0	1078.8
55°	1112.4	977.9	905.0	742.5	1000.3
57.5°	1008.7	843.4	773.4	666.9	983.5
60°	913.5	711.7	658.5	585.6	902.2
62.5°	835.0	613.6	602.4	529.6	818.2
65°	750.9	546.4	543.6	481.9	694.9
67.5°	669.7	501.6	498.8	437.1	529.6
70°	582.8	453.9	448.3	389.5	392.3
72.5°	493.2	400.7	395.1	350.2	325.0
75°	403.5	339.0	336.2	305.4	263.4
77.5°	316.6	269.0	274.6	246.6	193.3
80°	227.0	196.1	201.7	176.5	145.7
82.5°	151.3	128.9	134.5	112.1	98.1
85°	84.1	72.9	75.7	58.8	44.8
87.5°	39.2	33.6	33.6	22.4	14.0
90°	12.3	7.8	7.3	5.0	2.8
92.5°	76.1	54.2	49.4	30.3	11.2
95°	187.4	105.5	96.8	61.8	26.9
97.5°	252.4	115.9	108.3	77.4	46.6
100°	276.1	124.6	117.6	89.7	61.7
102.5°	286.9	133.3	126.7	100.7	74.6
105°	295.0	146.2	140.7	118.6	96.6
107.5°	296.5	165.3	160.2	139.5	119.0
110°	294.2	176.0	171.3	152.7	134.1



TEST NUMBER: P933981

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	294.3	188.9	184.5	166.7	149.1
115°	297.0	208.3	204.2	187.8	171.5
117.5°	302.5	227.1	223.3	208.5	193.6
120°	307.0	238.0	234.5	220.5	206.5
122.5°	313.5	250.9	247.3	233.3	219.2
125°	322.2	267.5	264.3	251.4	238.5
127.5°	330.9	283.5	280.2	267.2	254.2
130°	337.3	294.1	290.7	276.7	262.6
132.5°	342.4	302.8	299.3	285.3	271.4
135°	348.0	312.9	309.7	297.0	284.3
137.5°	356.4	325.8	322.6	310.1	297.5
140°	361.6	334.6	331.7	320.0	308.4
142.5°	365.8	341.0	338.3	327.6	316.8
145°	371.5	350.8	348.5	339.1	329.8
147.5°	379.7	363.1	360.9	351.7	342.7
150°	384.0	369.6	367.5	359.3	351.1
152.5°	386.8	373.8	372.2	366.0	359.8
155°	392.9	383.0	381.9	377.2	372.7
157.5°	399.2	392.4	391.3	386.7	382.2
160°	402.0	396.6	395.7	392.2	388.7
162.5°	405.0	401.1	400.4	397.8	395.2
165°	409.3	407.5	406.9	404.5	402.2
167.5°	412.6	411.1	410.9	409.7	408.6
170°	415.4	415.3	415.1	413.9	412.8
172.5°	415.6	415.6	415.5	415.3	415.1
175°	417.3	418.2	418.2	418.2	418.2
177.5°	417.5	418.2	418.2	418.2	418.2
180°	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P933981
 CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-STD-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.47	15.60	15.19	16.34	17.22	17.32	18.45	18.04	19.19	20.07
	3H	14.97	15.98	15.70	16.73	17.65	18.70	19.71	19.43	20.46	21.37
	4H	15.17	16.13	15.93	16.89	17.81	19.16	20.11	19.91	20.87	21.80
	6H	15.31	16.19	16.07	16.96	17.90	19.46	20.34	20.23	21.11	22.05
	8H	15.31	16.15	16.09	16.94	17.89	19.55	20.38	20.32	21.17	22.12
	12H	15.29	16.09	16.08	16.88	17.85	19.60	20.40	20.38	21.18	22.15
4H	2H	15.54	16.50	16.30	17.26	18.18	17.76	18.72	18.52	19.48	20.41
	3H	16.59	17.39	17.36	18.19	19.13	19.30	20.10	20.07	20.89	21.84
	4H	16.88	17.60	17.67	18.40	19.37	19.84	20.57	20.63	21.36	22.34
	6H	17.02	17.65	17.82	18.47	19.45	20.23	20.86	21.03	21.68	22.66
	8H	17.03	17.62	17.84	18.43	19.43	20.35	20.93	21.15	21.75	22.74
	12H	17.01	17.54	17.84	18.38	19.37	20.42	20.95	21.25	21.78	22.78
8H	4H	17.36	17.94	18.16	18.76	19.75	19.99	20.57	20.79	21.39	22.38
	6H	17.63	18.12	18.47	18.97	19.97	20.44	20.93	21.28	21.79	22.78
	8H	17.68	18.11	18.52	18.96	19.97	20.60	21.03	21.45	21.89	22.90
	12H	17.67	18.05	18.52	18.90	19.96	20.71	21.09	21.56	21.94	23.01
12H	4H	17.38	17.90	18.20	18.74	19.74	19.97	20.49	20.79	21.33	22.33
	6H	17.70	18.13	18.54	18.98	19.99	20.44	20.87	21.29	21.73	22.74
	8H	17.77	18.15	18.62	19.00	20.07	20.62	21.00	21.47	21.84	22.91