

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934081

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934081
REPORT IS A COMBINATION OF REPORTS P933681 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12858.4 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934081
CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79		
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70	67		
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59	56		
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	47		
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41		
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38	35		
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33	31		
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30	27		
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26	24		
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24	22		
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12104	12104	12104	12104
5°	12199	12218	12199	9607
10°	12121	12036	12121	8604
15°	11994	11775	11994	9832
20°	11748	11466	11748	9852
25°	11239	11015	11239	9643
30°	10580	10641	10580	9186
35°	9437	10168	9437	8682
40°	7867	9611	7867	8301
45°	7034	8959	7034	7863
50°	7479	8182	7479	7424
55°	7043	7344	7043	7170
60°	7270	6237	7270	6567
65°	6601	5156	6601	5763
70°	4582	4109	4582	4831
75°	4033	3037	4033	3637
80°	3274	2008	3274	2186
85°	1918	1063	1918	904

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 10774 cd/sqm



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	353.2	2.7
10°-20°	1002.9	7.8
20°-30°	1550.3	12.1
30°-40°	1850.7	14.4
40°-50°	1861.6	14.5
50°-60°	1619.8	12.6
60°-70°	1148.5	8.9
70°-80°	607.6	4.7
80°-90°	152.9	1.2
90°-100°	203.8	1.6
100°-110°	535.9	4.2
110°-120°	555.7	4.3
120°-130°	445.7	3.5
130°-140°	349.7	2.7
140°-150°	268.4	2.1
150°-160°	193.3	1.5
160°-170°	118.3	0.9
170°-180°	40.0	0.3
0°-30°	2906.5	22.6
0°-40°	4757.2	37.0
0°-60°	8238.6	64.1
0°-90°	10147.6	78.9
90°-120°	1295.4	10.1
90°-150°	2359.2	18.3
90°-180°	2711.0	21.1
0°-180°	12858.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3913	3913	3913	3913	3913	
5°	3932	4054	3932	3188	3932	373
15°	3754	4017	3754	3354	3754	1056
25°	3306	3747	3306	3280	3306	1518
35°	2514	3343	2514	2854	2514	1555
45°	1622	2754	1622	2418	1622	1299
55°	1322	2032	1322	1984	1322	1214
65°	918	1225	918	1370	918	877
75°	348	581	348	696	348	366
85°	59	148	59	126	59	80
90°	3	11	3	11	3	5
95°	27	123	27	123	27	30
105°	97	839	97	839	97	102
115°	172	1080	172	1080	172	169
125°	238	860	238	860	238	212
135°	284	668	284	668	284	220
145°	330	542	330	542	330	207
155°	373	466	373	466	373	171
165°	402	434	402	434	402	114
175°	418	421	418	421	418	40
180°	418	418	418	418	418	



TEST NUMBER: P934081
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1
2.5°	3946.4	3946.4	3968.7	3976.0	3976.0	3964.9	3953.8	3964.9	3998.3	4009.4	4005.6
5°	3931.7	3961.3	4002.0	4009.4	4016.8	4013.1	4005.6	4013.1	4050.1	4057.5	4061.2
7.5°	3902.0	3957.5	4009.4	4020.5	4031.6	4020.5	4016.8	4024.2	4061.2	4068.6	4068.6
10°	3865.0	3942.8	4002.0	4009.4	4020.5	4009.4	4009.4	4024.2	4061.2	4068.6	4072.3
12.5°	3813.1	3920.6	3976.0	3983.5	3998.3	3994.5	3990.9	4005.6	4042.7	4050.1	4050.1
15°	3753.9	3879.8	3931.7	3939.1	3964.9	3957.5	3957.5	3972.4	4013.1	4024.2	4020.5
17.5°	3672.5	3828.0	3887.2	3898.3	3916.8	3913.1	3916.8	3931.7	3968.7	3976.0	3979.8
20°	3579.9	3757.7	3828.0	3839.1	3857.6	3857.6	3857.6	3876.1	3913.1	3927.9	3927.9
22.5°	3454.0	3683.6	3757.7	3765.0	3787.3	3787.3	3794.7	3820.5	3853.9	3857.6	3857.6
25°	3306.0	3602.2	3665.1	3687.3	3709.5	3720.6	3731.7	3746.6	3757.7	3753.9	3757.7
27.5°	3150.5	3498.5	3579.9	3594.8	3624.4	3635.5	3650.3	3654.0	3657.6	3668.8	3661.4
30°	2976.5	3354.1	3476.3	3491.1	3539.2	3546.6	3531.8	3539.2	3557.7	3565.2	3572.6
32.5°	2780.2	3139.4	3368.9	3402.2	3446.6	3424.4	3420.8	3431.9	3461.5	3461.5	3468.9
35°	2513.8	2972.8	3269.0	3298.6	3331.9	3306.0	3320.7	3324.5	3343.0	3354.1	3350.4
37.5°	2221.2	2828.4	3165.3	3187.6	3213.4	3180.1	3202.3	3213.4	3228.3	3220.8	3220.8
40°	1962.1	2602.6	3043.2	3057.9	3080.1	3054.3	3076.4	3083.9	3091.3	3083.9	3080.1
42.5°	1769.6	2354.5	2913.5	2932.1	2917.3	2935.7	2943.1	2958.0	2946.9	2932.1	2932.1
45°	1621.5	2287.9	2772.9	2795.1	2772.9	2802.5	2813.6	2813.6	2780.2	2772.9	2769.2
47.5°	1573.4	2154.6	2632.2	2632.2	2621.1	2658.1	2676.7	2650.7	2617.3	2606.3	2606.3
50°	1569.7	2006.5	2439.7	2424.9	2476.7	2521.1	2502.7	2476.7	2450.8	2410.1	2410.1
52.5°	1425.3	1825.1	2191.6	2247.2	2328.6	2354.5	2324.9	2299.0	2254.6	2236.1	2221.2
55°	1321.6	1636.4	1965.8	2076.8	2162.0	2195.4	2139.8	2113.9	2047.2	2036.1	2028.7
57.5°	1299.5	1362.3	1758.5	1899.2	2002.9	1999.1	1965.8	1917.7	1862.1	1851.1	1847.4
60°	1192.1	984.7	1536.3	1703.0	1810.4	1799.3	1769.6	1725.2	1673.4	1666.0	1658.5
62.5°	1081.0	714.5	1284.6	1473.5	1625.3	1621.5	1595.6	1529.0	1492.0	1473.5	1458.6
65°	918.1	599.7	914.4	1225.4	1443.8	1451.2	1395.7	1347.6	1306.9	1284.6	1280.9
67.5°	699.7	488.7	618.2	1021.8	1269.9	1262.4	1192.1	1169.8	1118.0	1106.9	1084.7
70°	518.3	325.8	429.5	829.3	1099.5	1081.0	1025.4	999.6	951.5	925.5	910.7
72.5°	429.5	262.8	314.7	644.2	925.5	903.3	855.2	825.6	784.8	762.6	747.9
75°	348.0	277.7	240.6	477.6	751.5	736.7	692.3	662.7	629.3	599.7	603.5
77.5°	255.4	259.2	192.5	351.7	596.1	573.8	547.9	510.9	496.0	466.4	466.4
80°	192.5	203.6	144.4	240.6	429.5	429.5	407.2	381.4	355.4	340.6	340.6
82.5°	129.5	129.5	107.3	151.8	292.4	281.3	266.6	259.2	244.3	237.0	237.0
85°	59.2	74.1	66.6	92.6	159.2	166.6	166.6	159.2	155.5	148.0	151.8
87.5°	18.5	33.3	40.7	51.8	81.4	85.2	88.8	88.8	88.8	92.6	92.6
90°	2.8	5.0	7.3	7.8	12.3	18.3	21.3	19.0	14.2	10.6	10.6
92.5°	11.2	30.3	49.4	54.2	76.1	105.4	120.1	105.3	75.6	53.3	51.2
95°	26.9	61.8	96.8	105.5	187.4	296.5	351.1	313.3	237.7	181.0	174.6
97.5°	46.6	77.4	108.3	115.9	252.4	434.4	525.4	501.5	453.7	417.9	405.6
100°	61.7	89.7	117.6	124.6	276.1	478.0	579.0	580.8	584.2	586.8	572.3
102.5°	74.6	100.7	126.7	133.3	286.9	491.8	594.1	624.6	685.4	731.0	718.5
105°	96.6	118.6	140.7	146.2	295.0	493.2	592.4	660.6	797.1	899.4	892.7
107.5°	119.0	139.5	160.2	165.3	296.5	471.3	558.7	653.9	844.2	987.1	988.6
110°	134.1	152.7	171.3	176.0	294.2	451.9	530.7	637.1	849.8	1009.5	1016.5



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	149.1	166.7	184.5	188.9	294.3	434.9	505.2	614.1	831.8	995.2	1005.9
115°	171.5	187.8	204.2	208.3	297.0	415.3	474.6	579.5	789.2	946.6	961.5
117.5°	193.6	208.5	223.3	227.1	302.5	403.2	453.6	548.3	737.6	879.5	896.1
120°	206.5	220.5	234.5	238.0	307.0	399.0	445.1	531.5	704.6	834.3	850.4
122.5°	219.2	233.3	247.3	250.9	313.5	396.9	438.6	516.5	672.3	789.1	804.9
125°	238.5	251.4	264.3	267.5	322.2	395.2	431.6	497.7	630.1	729.4	743.9
127.5°	254.2	267.2	280.2	283.5	330.9	394.1	425.7	482.5	596.2	681.4	693.7
130°	262.6	276.7	290.7	294.1	337.3	394.7	423.5	474.1	575.3	651.1	662.5
132.5°	271.4	285.3	299.3	302.8	342.4	395.2	421.5	466.8	557.4	625.3	635.5
135°	284.3	297.0	309.7	312.9	348.0	394.8	418.2	456.1	531.9	588.8	597.6
137.5°	297.5	310.1	322.6	325.8	356.4	397.2	417.6	449.6	513.7	561.8	569.0
140°	308.4	320.0	331.7	334.6	361.6	397.6	415.6	443.3	498.7	540.2	547.0
142.5°	316.8	327.6	338.3	341.0	365.8	399.0	415.6	439.9	488.6	525.1	530.9
145°	329.8	339.1	348.5	350.8	371.5	399.0	412.8	432.7	472.5	502.3	506.7
147.5°	342.7	351.7	360.9	363.1	379.7	401.8	412.8	428.5	459.8	483.3	486.9
150°	351.1	359.3	367.5	369.6	384.0	403.2	412.8	426.1	452.5	472.3	475.2
152.5°	359.8	366.0	372.2	373.8	386.8	404.1	412.8	424.1	446.7	463.6	465.9
155°	372.7	377.2	381.9	383.0	392.9	406.2	412.8	421.8	439.8	453.3	454.8
157.5°	382.2	386.7	391.3	392.4	399.2	408.3	412.8	419.8	433.7	444.2	445.2
160°	388.7	392.2	395.7	396.6	402.0	409.2	412.8	418.8	430.8	439.7	440.3
162.5°	395.2	397.8	400.4	401.1	405.0	410.2	412.8	417.9	428.0	435.5	436.1
165°	402.2	404.5	406.9	407.5	409.3	411.6	412.8	416.5	423.7	429.1	429.6
167.5°	408.6	409.7	410.9	411.1	412.6	414.6	415.6	418.0	422.7	426.3	426.6
170°	412.8	413.9	415.1	415.3	415.4	415.5	415.6	418.0	422.7	426.3	426.3
172.5°	415.1	415.3	415.5	415.6	415.6	415.6	415.6	417.5	421.2	424.0	423.8
175°	418.2	418.2	418.2	418.2	417.3	416.2	415.6	416.8	419.2	421.0	421.0
177.5°	418.2	418.2	418.2	418.2	417.5	416.7	416.2	417.1	419.0	420.4	420.1
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1
2.5°	4013.1	4002.0	4013.1	4005.6	4009.4	3998.3	3964.9	3953.8	3964.9	3976.0	3976.0
5°	4061.2	4053.8	4061.2	4061.2	4057.5	4050.1	4013.1	4005.6	4013.1	4016.8	4009.4
7.5°	4076.0	4065.0	4076.0	4068.6	4068.6	4061.2	4024.2	4016.8	4020.5	4031.6	4020.5
10°	4076.0	4065.0	4076.0	4072.3	4068.6	4061.2	4024.2	4009.4	4009.4	4020.5	4009.4
12.5°	4057.5	4050.1	4057.5	4050.1	4050.1	4042.7	4005.6	3990.9	3994.5	3998.3	3983.5
15°	4027.9	4016.8	4027.9	4020.5	4024.2	4013.1	3972.4	3957.5	3957.5	3964.9	3939.1
17.5°	3983.5	3968.7	3983.5	3979.8	3976.0	3968.7	3931.7	3916.8	3913.1	3916.8	3898.3
20°	3931.7	3920.6	3931.7	3927.9	3927.9	3913.1	3876.1	3857.6	3857.6	3857.6	3839.1
22.5°	3850.2	3839.1	3850.2	3857.6	3857.6	3853.9	3820.5	3794.7	3787.3	3787.3	3765.0
25°	3757.7	3746.6	3757.7	3757.7	3753.9	3757.7	3746.6	3731.7	3720.6	3709.5	3687.3
27.5°	3668.8	3661.4	3668.8	3661.4	3668.8	3657.6	3654.0	3650.3	3635.5	3624.4	3594.8
30°	3579.9	3572.6	3579.9	3572.6	3565.2	3557.7	3539.2	3531.8	3546.6	3539.2	3491.1
32.5°	3468.9	3461.5	3468.9	3468.9	3461.5	3461.5	3431.9	3420.8	3424.4	3446.6	3402.2
35°	3354.1	3343.0	3354.1	3350.4	3354.1	3343.0	3324.5	3320.7	3306.0	3331.9	3298.6
37.5°	3220.8	3209.7	3220.8	3220.8	3220.8	3228.3	3213.4	3202.3	3180.1	3213.4	3187.6
40°	3083.9	3069.0	3083.9	3080.1	3083.9	3091.3	3083.9	3076.4	3054.3	3080.1	3057.9
42.5°	2928.4	2924.6	2928.4	2932.1	2932.1	2946.9	2958.0	2943.1	2935.7	2917.3	2932.1
45°	2761.7	2754.4	2761.7	2769.2	2772.9	2780.2	2813.6	2813.6	2802.5	2772.9	2795.1
47.5°	2584.1	2565.6	2584.1	2606.3	2606.3	2617.3	2650.7	2676.7	2658.1	2621.1	2632.2
50°	2395.2	2399.0	2395.2	2410.1	2410.1	2450.8	2476.7	2502.7	2521.1	2476.7	2424.9
52.5°	2210.1	2206.5	2210.1	2221.2	2236.1	2254.6	2299.0	2324.9	2354.5	2328.6	2247.2
55°	2025.0	2032.5	2025.0	2028.7	2036.1	2047.2	2113.9	2139.8	2195.4	2162.0	2076.8
57.5°	1840.0	1828.9	1840.0	1847.4	1851.1	1862.1	1917.7	1965.8	1999.1	2002.9	1899.2
60°	1625.3	1610.4	1625.3	1658.5	1666.0	1673.4	1725.2	1769.6	1799.3	1810.4	1703.0
62.5°	1436.4	1410.5	1436.4	1458.6	1473.5	1492.0	1529.0	1595.6	1621.5	1625.3	1473.5
65°	1236.5	1225.4	1236.5	1280.9	1284.6	1306.9	1347.6	1395.7	1451.2	1443.8	1225.4
67.5°	1055.1	1055.1	1055.1	1084.7	1106.9	1118.0	1169.8	1192.1	1262.4	1269.9	1021.8
70°	888.5	884.8	888.5	910.7	925.5	951.5	999.6	1025.4	1081.0	1099.5	829.3
72.5°	729.4	725.6	729.4	747.9	762.6	784.8	825.6	855.2	903.3	925.5	644.2
75°	588.6	581.2	588.6	603.5	599.7	629.3	662.7	692.3	736.7	751.5	477.6
77.5°	451.7	451.7	451.7	466.4	466.4	496.0	510.9	547.9	573.8	596.1	351.7
80°	336.9	333.2	336.9	340.6	340.6	355.4	381.4	407.2	429.5	429.5	240.6
82.5°	237.0	229.5	237.0	237.0	237.0	244.3	259.2	266.6	281.3	292.4	151.8
85°	148.0	148.0	148.0	151.8	148.0	155.5	159.2	166.6	166.6	159.2	92.6
87.5°	96.3	92.6	96.3	92.6	92.6	88.8	88.8	88.8	85.2	81.4	51.8
90°	10.6	10.6	10.6	10.6	10.6	14.2	19.0	21.3	18.3	12.3	7.8
92.5°	42.8	34.3	42.8	51.2	53.3	75.6	105.3	120.1	105.4	76.1	54.2
95°	148.9	123.2	148.9	174.6	181.0	237.7	313.3	351.1	296.5	187.4	105.5
97.5°	356.8	307.8	356.8	405.6	417.9	453.7	501.5	525.4	434.4	252.4	115.9
100°	514.1	455.8	514.1	572.3	586.8	584.2	580.8	579.0	478.0	276.1	124.6
102.5°	668.7	618.8	668.7	718.5	731.0	685.4	624.6	594.1	491.8	286.9	133.3
105°	865.9	839.1	865.9	892.7	899.4	797.1	660.6	592.4	493.2	295.0	146.2
107.5°	995.2	1001.6	995.2	988.6	987.1	844.2	653.9	558.7	471.3	296.5	165.3
110°	1044.4	1072.3	1044.4	1016.5	1009.5	849.8	637.1	530.7	451.9	294.2	176.0



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1048.8	1091.7	1048.8	1005.9	995.2	831.8	614.1	505.2	434.9	294.3	188.9
115°	1021.0	1080.5	1021.0	961.5	946.6	789.2	579.5	474.6	415.3	297.0	208.3
117.5°	962.0	1028.0	962.0	896.1	879.5	737.6	548.3	453.6	403.2	302.5	227.1
120°	914.5	978.6	914.5	850.4	834.3	704.6	531.5	445.1	399.0	307.0	238.0
122.5°	868.2	931.5	868.2	804.9	789.1	672.3	516.5	438.6	396.9	313.5	250.9
125°	802.1	860.4	802.1	743.9	729.4	630.1	497.7	431.6	395.2	322.2	267.5
127.5°	742.8	791.9	742.8	693.7	681.4	596.2	482.5	425.7	394.1	330.9	283.5
130°	707.9	753.3	707.9	662.5	651.1	575.3	474.1	423.5	394.7	337.3	294.1
132.5°	676.1	716.8	676.1	635.5	625.3	557.4	466.8	421.5	395.2	342.4	302.8
135°	632.6	667.6	632.6	597.6	588.8	531.9	456.1	418.2	394.8	348.0	312.9
137.5°	597.7	626.4	597.7	569.0	561.8	513.7	449.6	417.6	397.2	356.4	325.8
140°	573.8	600.6	573.8	547.0	540.2	498.7	443.3	415.6	397.6	361.6	334.6
142.5°	554.0	577.0	554.0	530.9	525.1	488.6	439.9	415.6	399.0	365.8	341.0
145°	524.2	541.6	524.2	506.7	502.3	472.5	432.7	412.8	399.0	371.5	350.8
147.5°	501.4	515.8	501.4	486.9	483.3	459.8	428.5	412.8	401.8	379.7	363.1
150°	487.0	498.7	487.0	475.2	472.3	452.5	426.1	412.8	403.2	384.0	369.6
152.5°	474.7	483.5	474.7	465.9	463.6	446.7	424.1	412.8	404.1	386.8	373.8
155°	460.6	466.4	460.6	454.8	453.3	439.8	421.8	412.8	406.2	392.9	383.0
157.5°	449.4	453.6	449.4	445.2	444.2	433.7	419.8	412.8	408.3	399.2	392.4
160°	442.7	445.1	442.7	440.3	439.7	430.8	418.8	412.8	409.2	402.0	396.6
162.5°	438.3	440.6	438.3	436.1	435.5	428.0	417.9	412.8	410.2	405.0	401.1
165°	432.1	434.4	432.1	429.6	429.1	423.7	416.5	412.8	411.6	409.3	407.5
167.5°	427.5	428.5	427.5	426.6	426.3	422.7	418.0	415.6	414.6	412.6	411.1
170°	426.3	426.3	426.3	426.3	426.3	422.7	418.0	415.6	415.5	415.4	415.3
172.5°	422.9	422.1	422.9	423.8	424.0	421.2	417.5	415.6	415.6	415.6	415.6
175°	421.0	421.0	421.0	421.0	421.0	419.2	416.8	415.6	416.2	417.3	418.2
177.5°	419.2	418.2	419.2	420.1	420.4	419.0	417.1	416.2	416.7	417.5	418.2
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1
2.5°	3968.7	3946.4	3946.4	3909.4	3894.6	3883.5	3865.0	3809.5	3794.7	3779.8	3802.0
5°	4002.0	3961.3	3931.7	3865.0	3809.5	3787.3	3716.9	3583.7	3494.7	3428.2	3391.2
7.5°	4009.4	3957.5	3902.0	3798.4	3665.1	3605.9	3391.2	3146.8	3080.1	3020.9	2983.8
10°	4002.0	3942.8	3865.0	3709.5	3394.8	3291.1	3076.4	2917.3	2876.5	2865.4	2876.5
12.5°	3976.0	3920.6	3813.1	3554.1	3113.5	3043.2	2917.3	2824.7	2817.3	2835.8	2935.7
15°	3931.7	3879.8	3753.9	3346.7	2958.0	2906.1	2817.3	2784.0	2824.7	2954.2	3254.1
17.5°	3887.2	3828.0	3672.5	3143.1	2839.5	2802.5	2739.5	2806.2	3035.7	3209.7	3309.7
20°	3828.0	3757.7	3579.9	2995.0	2754.4	2721.0	2691.4	2991.3	3165.3	3228.3	3283.8
22.5°	3757.7	3683.6	3454.0	2891.4	2665.5	2639.6	2658.1	3095.0	3165.3	3209.7	3257.9
25°	3665.1	3602.2	3306.0	2809.9	2595.2	2565.6	2635.9	3083.9	3124.6	3135.7	3231.9
27.5°	3579.9	3498.5	3150.5	2735.9	2510.0	2498.9	2654.4	3035.7	3065.4	3076.4	3180.1
30°	3476.3	3354.1	2976.5	2658.1	2421.2	2417.5	2658.1	2976.5	2969.1	2998.7	3102.4
32.5°	3368.9	3139.4	2780.2	2561.9	2336.0	2332.3	2632.2	2887.6	2880.3	2921.0	2998.7
35°	3269.0	2972.8	2513.8	2450.8	2228.7	2232.4	2569.2	2784.0	2787.7	2824.7	2872.8
37.5°	3165.3	2828.4	2221.2	2328.6	2125.0	2125.0	2484.1	2687.8	2680.3	2691.4	2758.1
40°	3043.2	2602.6	1962.1	2169.4	2028.7	2017.6	2380.5	2584.1	2558.1	2554.5	2647.0
42.5°	2913.5	2354.5	1769.6	1958.4	1917.7	1902.8	2254.6	2458.2	2410.1	2421.2	2539.6
45°	2772.9	2287.9	1621.5	1654.9	1802.9	1791.8	2117.6	2313.8	2280.5	2310.2	2432.3
47.5°	2632.2	2154.6	1573.4	1373.4	1680.7	1677.1	1965.8	2173.1	2154.6	2184.3	2313.8
50°	2439.7	2006.5	1569.7	1177.3	1543.8	1558.6	1784.4	2036.1	2036.1	2062.1	2199.0
52.5°	2191.6	1825.1	1425.3	1066.2	1384.6	1429.0	1625.3	1917.7	1925.1	1951.0	2073.2
55°	1965.8	1636.4	1321.6	981.1	1195.8	1292.0	1469.7	1795.5	1810.4	1836.2	1947.3
57.5°	1758.5	1362.3	1299.5	881.1	1021.8	1114.4	1332.7	1677.1	1684.5	1706.7	1814.0
60°	1536.3	984.7	1192.1	773.7	870.0	940.4	1206.9	1536.3	1562.3	1577.1	1669.6
62.5°	1284.6	714.5	1081.0	699.7	796.0	810.8	1103.2	1403.1	1436.4	1447.5	1503.1
65°	914.4	599.7	918.1	636.8	718.2	721.9	992.2	1266.1	1295.7	1314.2	1355.0
67.5°	618.2	488.7	699.7	577.5	658.9	662.7	884.8	1106.9	1147.6	1162.5	1188.4
70°	429.5	325.8	518.3	514.6	592.3	599.7	770.1	962.6	999.6	1010.7	1025.4
72.5°	314.7	262.8	429.5	462.8	522.0	529.4	651.6	799.7	836.7	847.8	855.2
75°	240.6	277.7	348.0	403.5	444.2	447.9	533.1	651.6	677.5	684.9	688.5
77.5°	192.5	259.2	255.4	325.8	362.8	355.4	418.3	503.5	525.7	525.7	525.7
80°	144.4	203.6	192.5	233.2	266.6	259.2	299.9	359.1	366.5	373.9	370.2
82.5°	107.3	129.5	129.5	148.0	177.7	170.3	199.9	233.2	233.2	233.2	240.6
85°	66.6	74.1	59.2	77.7	99.9	96.3	111.1	125.9	129.5	129.5	122.2
87.5°	40.7	33.3	18.5	29.6	44.5	44.5	51.8	55.6	51.8	51.8	51.8
90°	7.3	5.0	2.8	5.0	7.3	7.8	12.3	18.3	21.3	19.0	14.2
92.5°	49.4	30.3	11.2	30.3	49.4	54.2	76.1	105.4	120.1	105.3	75.6
95°	96.8	61.8	26.9	61.8	96.8	105.5	187.4	296.5	351.1	313.3	237.7
97.5°	108.3	77.4	46.6	77.4	108.3	115.9	252.4	434.4	525.4	501.5	453.7
100°	117.6	89.7	61.7	89.7	117.6	124.6	276.1	478.0	579.0	580.8	584.2
102.5°	126.7	100.7	74.6	100.7	126.7	133.3	286.9	491.8	594.1	624.6	685.4
105°	140.7	118.6	96.6	118.6	140.7	146.2	295.0	493.2	592.4	660.6	797.1
107.5°	160.2	139.5	119.0	139.5	160.2	165.3	296.5	471.3	558.7	653.9	844.2
110°	171.3	152.7	134.1	152.7	171.3	176.0	294.2	451.9	530.7	637.1	849.8



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	184.5	166.7	149.1	166.7	184.5	188.9	294.3	434.9	505.2	614.1	831.8
115°	204.2	187.8	171.5	187.8	204.2	208.3	297.0	415.3	474.6	579.5	789.2
117.5°	223.3	208.5	193.6	208.5	223.3	227.1	302.5	403.2	453.6	548.3	737.6
120°	234.5	220.5	206.5	220.5	234.5	238.0	307.0	399.0	445.1	531.5	704.6
122.5°	247.3	233.3	219.2	233.3	247.3	250.9	313.5	396.9	438.6	516.5	672.3
125°	264.3	251.4	238.5	251.4	264.3	267.5	322.2	395.2	431.6	497.7	630.1
127.5°	280.2	267.2	254.2	267.2	280.2	283.5	330.9	394.1	425.7	482.5	596.2
130°	290.7	276.7	262.6	276.7	290.7	294.1	337.3	394.7	423.5	474.1	575.3
132.5°	299.3	285.3	271.4	285.3	299.3	302.8	342.4	395.2	421.5	466.8	557.4
135°	309.7	297.0	284.3	297.0	309.7	312.9	348.0	394.8	418.2	456.1	531.9
137.5°	322.6	310.1	297.5	310.1	322.6	325.8	356.4	397.2	417.6	449.6	513.7
140°	331.7	320.0	308.4	320.0	331.7	334.6	361.6	397.6	415.6	443.3	498.7
142.5°	338.3	327.6	316.8	327.6	338.3	341.0	365.8	399.0	415.6	439.9	488.6
145°	348.5	339.1	329.8	339.1	348.5	350.8	371.5	399.0	412.8	432.7	472.5
147.5°	360.9	351.7	342.7	351.7	360.9	363.1	379.7	401.8	412.8	428.5	459.8
150°	367.5	359.3	351.1	359.3	367.5	369.6	384.0	403.2	412.8	426.1	452.5
152.5°	372.2	366.0	359.8	366.0	372.2	373.8	386.8	404.1	412.8	424.1	446.7
155°	381.9	377.2	372.7	377.2	381.9	383.0	392.9	406.2	412.8	421.8	439.8
157.5°	391.3	386.7	382.2	386.7	391.3	392.4	399.2	408.3	412.8	419.8	433.7
160°	395.7	392.2	388.7	392.2	395.7	396.6	402.0	409.2	412.8	418.8	430.8
162.5°	400.4	397.8	395.2	397.8	400.4	401.1	405.0	410.2	412.8	417.9	428.0
165°	406.9	404.5	402.2	404.5	406.9	407.5	409.3	411.6	412.8	416.5	423.7
167.5°	410.9	409.7	408.6	409.7	410.9	411.1	412.6	414.6	415.6	418.0	422.7
170°	415.1	413.9	412.8	413.9	415.1	415.3	415.4	415.5	415.6	418.0	422.7
172.5°	415.5	415.3	415.1	415.3	415.5	415.6	415.6	415.6	415.6	417.5	421.2
175°	418.2	418.2	418.2	418.2	418.2	418.2	417.3	416.2	415.6	416.8	419.2
177.5°	418.2	418.2	418.2	418.2	418.2	418.2	417.5	416.7	416.2	417.1	419.0
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P934081
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1	3913.1
2.5°	3776.2	3765.0	3779.8	3739.1	3779.8	3765.0	3776.2	3802.0	3779.8	3794.7	3809.5
5°	3313.4	3294.9	3235.7	3187.6	3235.7	3294.9	3313.4	3391.2	3428.2	3494.7	3583.7
7.5°	2961.7	2946.9	2932.1	2902.4	2932.1	2946.9	2961.7	2983.8	3020.9	3080.1	3146.8
10°	2883.9	2887.6	2909.9	2906.1	2909.9	2887.6	2883.9	2876.5	2865.4	2876.5	2917.3
12.5°	3083.9	3117.1	3239.3	3231.9	3239.3	3117.1	3083.9	2935.7	2835.8	2817.3	2824.7
15°	3313.4	3324.5	3350.4	3354.1	3350.4	3324.5	3313.4	3254.1	2954.2	2824.7	2784.0
17.5°	3335.6	3339.3	3357.8	3357.8	3357.8	3339.3	3335.6	3309.7	3209.7	3035.7	2806.2
20°	3317.1	3324.5	3361.5	3368.9	3361.5	3324.5	3317.1	3283.8	3228.3	3165.3	2991.3
22.5°	3309.7	3324.5	3354.1	3350.4	3354.1	3324.5	3309.7	3257.9	3209.7	3165.3	3095.0
25°	3272.6	3272.6	3276.4	3280.0	3276.4	3272.6	3272.6	3231.9	3135.7	3124.6	3083.9
27.5°	3194.9	3202.3	3224.5	3220.8	3224.5	3202.3	3194.9	3180.1	3076.4	3065.4	3035.7
30°	3124.6	3117.1	3098.6	3083.9	3098.6	3117.1	3124.6	3102.4	2998.7	2969.1	2976.5
32.5°	3006.1	2987.6	2969.1	2958.0	2969.1	2987.6	3006.1	2998.7	2921.0	2880.3	2887.6
35°	2865.4	2869.2	2865.4	2854.3	2865.4	2869.2	2865.4	2872.8	2824.7	2787.7	2784.0
37.5°	2765.5	2772.9	2769.2	2754.4	2769.2	2772.9	2765.5	2758.1	2691.4	2680.3	2687.8
40°	2661.8	2665.5	2661.8	2650.7	2661.8	2665.5	2661.8	2647.0	2554.5	2558.1	2584.1
42.5°	2561.9	2558.1	2547.0	2539.6	2547.0	2558.1	2561.9	2539.6	2421.2	2410.1	2458.2
45°	2447.1	2450.8	2428.6	2417.5	2428.6	2450.8	2447.1	2432.3	2310.2	2280.5	2313.8
47.5°	2332.3	2332.3	2313.8	2302.7	2313.8	2332.3	2332.3	2313.8	2184.3	2154.6	2173.1
50°	2210.1	2206.5	2180.5	2176.9	2180.5	2206.5	2210.1	2199.0	2062.1	2036.1	2036.1
52.5°	2069.5	2069.5	2073.2	2080.6	2073.2	2069.5	2069.5	2073.2	1951.0	1925.1	1917.7
55°	1947.3	1951.0	1976.9	1984.3	1976.9	1951.0	1947.3	1947.3	1836.2	1810.4	1795.5
57.5°	1821.4	1821.4	1840.0	1840.0	1840.0	1821.4	1821.4	1814.0	1706.7	1684.5	1677.1
60°	1677.1	1684.5	1699.2	1695.6	1699.2	1684.5	1677.1	1669.6	1577.1	1562.3	1536.3
62.5°	1525.2	1532.7	1536.3	1529.0	1536.3	1532.7	1525.2	1503.1	1447.5	1436.4	1403.1
65°	1366.1	1373.4	1377.2	1369.8	1377.2	1373.4	1366.1	1355.0	1314.2	1295.7	1266.1
67.5°	1203.2	1199.4	1195.8	1210.6	1195.8	1199.4	1203.2	1188.4	1162.5	1147.6	1106.9
70°	1036.6	1036.6	1032.9	1040.3	1032.9	1036.6	1036.6	1025.4	1010.7	999.6	962.6
72.5°	858.9	855.2	870.0	858.9	870.0	855.2	858.9	855.2	847.8	836.7	799.7
75°	684.9	692.3	684.9	696.0	684.9	692.3	684.9	688.5	684.9	677.5	651.6
77.5°	522.0	529.4	522.0	522.0	522.0	529.4	522.0	525.7	525.7	525.7	503.5
80°	370.2	366.5	366.5	362.8	366.5	366.5	370.2	370.2	373.9	366.5	359.1
82.5°	237.0	233.2	233.2	240.6	233.2	233.2	237.0	240.6	233.2	233.2	233.2
85°	129.5	133.3	125.9	125.9	125.9	133.3	129.5	122.2	129.5	129.5	125.9
87.5°	48.1	44.5	44.5	44.5	44.5	44.5	48.1	51.8	51.8	51.8	55.6
90°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	14.2	19.0	21.3	18.3
92.5°	53.3	51.2	42.8	34.3	42.8	51.2	53.3	75.6	105.3	120.1	105.4
95°	181.0	174.6	148.9	123.2	148.9	174.6	181.0	237.7	313.3	351.1	296.5
97.5°	417.9	405.6	356.8	307.8	356.8	405.6	417.9	453.7	501.5	525.4	434.4
100°	586.8	572.3	514.1	455.8	514.1	572.3	586.8	584.2	580.8	579.0	478.0
102.5°	731.0	718.5	668.7	618.8	668.7	718.5	731.0	685.4	624.6	594.1	491.8
105°	899.4	892.7	865.9	839.1	865.9	892.7	899.4	797.1	660.6	592.4	493.2
107.5°	987.1	988.6	995.2	1001.6	995.2	988.6	987.1	844.2	653.9	558.7	471.3
110°	1009.5	1016.5	1044.4	1072.3	1044.4	1016.5	1009.5	849.8	637.1	530.7	451.9



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	995.2	1005.9	1048.8	1091.7	1048.8	1005.9	995.2	831.8	614.1	505.2	434.9
115°	946.6	961.5	1021.0	1080.5	1021.0	961.5	946.6	789.2	579.5	474.6	415.3
117.5°	879.5	896.1	962.0	1028.0	962.0	896.1	879.5	737.6	548.3	453.6	403.2
120°	834.3	850.4	914.5	978.6	914.5	850.4	834.3	704.6	531.5	445.1	399.0
122.5°	789.1	804.9	868.2	931.5	868.2	804.9	789.1	672.3	516.5	438.6	396.9
125°	729.4	743.9	802.1	860.4	802.1	743.9	729.4	630.1	497.7	431.6	395.2
127.5°	681.4	693.7	742.8	791.9	742.8	693.7	681.4	596.2	482.5	425.7	394.1
130°	651.1	662.5	707.9	753.3	707.9	662.5	651.1	575.3	474.1	423.5	394.7
132.5°	625.3	635.5	676.1	716.8	676.1	635.5	625.3	557.4	466.8	421.5	395.2
135°	588.8	597.6	632.6	667.6	632.6	597.6	588.8	531.9	456.1	418.2	394.8
137.5°	561.8	569.0	597.7	626.4	597.7	569.0	561.8	513.7	449.6	417.6	397.2
140°	540.2	547.0	573.8	600.6	573.8	547.0	540.2	498.7	443.3	415.6	397.6
142.5°	525.1	530.9	554.0	577.0	554.0	530.9	525.1	488.6	439.9	415.6	399.0
145°	502.3	506.7	524.2	541.6	524.2	506.7	502.3	472.5	432.7	412.8	399.0
147.5°	483.3	486.9	501.4	515.8	501.4	486.9	483.3	459.8	428.5	412.8	401.8
150°	472.3	475.2	487.0	498.7	487.0	475.2	472.3	452.5	426.1	412.8	403.2
152.5°	463.6	465.9	474.7	483.5	474.7	465.9	463.6	446.7	424.1	412.8	404.1
155°	453.3	454.8	460.6	466.4	460.6	454.8	453.3	439.8	421.8	412.8	406.2
157.5°	444.2	445.2	449.4	453.6	449.4	445.2	444.2	433.7	419.8	412.8	408.3
160°	439.7	440.3	442.7	445.1	442.7	440.3	439.7	430.8	418.8	412.8	409.2
162.5°	435.5	436.1	438.3	440.6	438.3	436.1	435.5	428.0	417.9	412.8	410.2
165°	429.1	429.6	432.1	434.4	432.1	429.6	429.1	423.7	416.5	412.8	411.6
167.5°	426.3	426.6	427.5	428.5	427.5	426.6	426.3	422.7	418.0	415.6	414.6
170°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	422.7	418.0	415.6	415.5
172.5°	424.0	423.8	422.9	422.1	422.9	423.8	424.0	421.2	417.5	415.6	415.6
175°	421.0	421.0	421.0	421.0	421.0	421.0	421.0	419.2	416.8	415.6	416.2
177.5°	420.4	420.1	419.2	418.2	419.2	420.1	420.4	419.0	417.1	416.2	416.7
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	3913.1	3913.1	3913.1	3913.1	3913.1
2.5°	3865.0	3883.5	3894.6	3909.4	3946.4
5°	3716.9	3787.3	3809.5	3865.0	3931.7
7.5°	3391.2	3605.9	3665.1	3798.4	3902.0
10°	3076.4	3291.1	3394.8	3709.5	3865.0
12.5°	2917.3	3043.2	3113.5	3554.1	3813.1
15°	2817.3	2906.1	2958.0	3346.7	3753.9
17.5°	2739.5	2802.5	2839.5	3143.1	3672.5
20°	2691.4	2721.0	2754.4	2995.0	3579.9
22.5°	2658.1	2639.6	2665.5	2891.4	3454.0
25°	2635.9	2565.6	2595.2	2809.9	3306.0
27.5°	2654.4	2498.9	2510.0	2735.9	3150.5
30°	2658.1	2417.5	2421.2	2658.1	2976.5
32.5°	2632.2	2332.3	2336.0	2561.9	2780.2
35°	2569.2	2232.4	2228.7	2450.8	2513.8
37.5°	2484.1	2125.0	2125.0	2328.6	2221.2
40°	2380.5	2017.6	2028.7	2169.4	1962.1
42.5°	2254.6	1902.8	1917.7	1958.4	1769.6
45°	2117.6	1791.8	1802.9	1654.9	1621.5
47.5°	1965.8	1677.1	1680.7	1373.4	1573.4
50°	1784.4	1558.6	1543.8	1177.3	1569.7
52.5°	1625.3	1429.0	1384.6	1066.2	1425.3
55°	1469.7	1292.0	1195.8	981.1	1321.6
57.5°	1332.7	1114.4	1021.8	881.1	1299.5
60°	1206.9	940.4	870.0	773.7	1192.1
62.5°	1103.2	810.8	796.0	699.7	1081.0
65°	992.2	721.9	718.2	636.8	918.1
67.5°	884.8	662.7	658.9	577.5	699.7
70°	770.1	599.7	592.3	514.6	518.3
72.5°	651.6	529.4	522.0	462.8	429.5
75°	533.1	447.9	444.2	403.5	348.0
77.5°	418.3	355.4	362.8	325.8	255.4
80°	299.9	259.2	266.6	233.2	192.5
82.5°	199.9	170.3	177.7	148.0	129.5
85°	111.1	96.3	99.9	77.7	59.2
87.5°	51.8	44.5	44.5	29.6	18.5
90°	12.3	7.8	7.3	5.0	2.8
92.5°	76.1	54.2	49.4	30.3	11.2
95°	187.4	105.5	96.8	61.8	26.9
97.5°	252.4	115.9	108.3	77.4	46.6
100°	276.1	124.6	117.6	89.7	61.7
102.5°	286.9	133.3	126.7	100.7	74.6
105°	295.0	146.2	140.7	118.6	96.6
107.5°	296.5	165.3	160.2	139.5	119.0
110°	294.2	176.0	171.3	152.7	134.1



TEST NUMBER: P934081

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	294.3	188.9	184.5	166.7	149.1
115°	297.0	208.3	204.2	187.8	171.5
117.5°	302.5	227.1	223.3	208.5	193.6
120°	307.0	238.0	234.5	220.5	206.5
122.5°	313.5	250.9	247.3	233.3	219.2
125°	322.2	267.5	264.3	251.4	238.5
127.5°	330.9	283.5	280.2	267.2	254.2
130°	337.3	294.1	290.7	276.7	262.6
132.5°	342.4	302.8	299.3	285.3	271.4
135°	348.0	312.9	309.7	297.0	284.3
137.5°	356.4	325.8	322.6	310.1	297.5
140°	361.6	334.6	331.7	320.0	308.4
142.5°	365.8	341.0	338.3	327.6	316.8
145°	371.5	350.8	348.5	339.1	329.8
147.5°	379.7	363.1	360.9	351.7	342.7
150°	384.0	369.6	367.5	359.3	351.1
152.5°	386.8	373.8	372.2	366.0	359.8
155°	392.9	383.0	381.9	377.2	372.7
157.5°	399.2	392.4	391.3	386.7	382.2
160°	402.0	396.6	395.7	392.2	388.7
162.5°	405.0	401.1	400.4	397.8	395.2
165°	409.3	407.5	406.9	404.5	402.2
167.5°	412.6	411.1	410.9	409.7	408.6
170°	415.4	415.3	415.1	413.9	412.8
172.5°	415.6	415.6	415.5	415.3	415.1
175°	417.3	418.2	418.2	418.2	418.2
177.5°	417.5	418.2	418.2	418.2	418.2
180°	418.2	418.2	418.2	418.2	418.2



TEST NUMBER: P934081
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.81	17.01	16.47	17.69	18.47	18.66	19.86	19.32	20.54	21.33
	3H	16.31	17.39	16.99	18.08	18.90	20.04	21.12	20.71	21.80	22.63
	4H	16.52	17.53	17.21	18.23	19.07	20.50	21.52	21.20	22.22	23.05
	6H	16.65	17.59	17.36	18.30	19.15	20.81	21.75	21.52	22.46	23.31
	8H	16.66	17.56	17.38	18.29	19.14	20.90	21.79	21.62	22.52	23.37
	12H	16.65	17.50	17.37	18.22	19.10	20.95	21.80	21.67	22.53	23.41
4H	2H	16.89	17.90	17.58	18.60	19.44	19.11	20.13	19.81	20.82	21.66
	3H	17.95	18.79	18.66	19.53	20.38	20.65	21.50	21.36	22.24	23.09
	4H	18.24	19.00	18.96	19.74	20.63	21.20	21.97	21.93	22.71	23.59
	6H	18.38	19.05	19.13	19.81	20.70	21.59	22.25	22.33	23.02	23.91
	8H	18.39	19.02	19.14	19.78	20.68	21.71	22.33	22.46	23.09	23.99
	12H	18.38	18.94	19.15	19.72	20.63	21.78	22.34	22.55	23.13	24.04
8H	4H	18.72	19.34	19.47	20.10	21.01	21.35	21.97	22.10	22.73	23.64
	6H	18.99	19.51	19.78	20.31	21.22	21.81	22.32	22.59	23.12	24.03
	8H	19.04	19.50	19.83	20.30	21.22	21.96	22.42	22.76	23.23	24.15
	12H	19.04	19.44	19.83	20.24	21.22	22.08	22.49	22.88	23.28	24.26
12H	4H	18.74	19.30	19.51	20.09	20.99	21.33	21.89	22.10	22.67	23.58
	6H	19.06	19.52	19.85	20.32	21.24	21.80	22.27	22.60	23.07	23.99
	8H	19.14	19.55	19.94	20.34	21.32	21.99	22.39	22.78	23.18	24.16