

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936590

Luminaire Tested: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936590
REPORT IS A COMBINATION OF REPORTS P933448 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7218.8 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936590
CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P936590

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	84	84	84	81
1	104	99	94	90	99	95	91	87	87	84	81	80	77	75	73	71	70	70	70	70	66
2	94	85	78	72	89	82	75	70	75	70	66	69	65	61	63	60	57	57	57	57	54
3	85	74	66	59	81	71	64	58	65	59	54	60	55	51	55	51	48	48	48	48	45
4	77	65	56	49	74	63	54	48	58	51	45	53	47	43	49	44	40	40	40	40	37
5	71	58	49	42	67	55	47	41	51	44	39	47	41	36	43	38	34	34	34	34	32
6	65	51	42	36	62	49	41	35	46	39	33	42	36	31	39	34	30	30	30	30	27
7	60	46	37	31	57	45	36	30	41	34	29	38	32	27	35	30	26	26	26	26	24
8	55	42	33	27	53	40	32	27	37	30	25	35	29	24	32	27	23	23	23	23	21
9	52	38	30	24	49	37	29	24	34	27	23	32	26	22	29	24	20	20	20	20	18
10	48	35	27	22	46	34	26	21	31	25	20	29	23	19	27	22	18	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4554	5389	6269
10°	4129	7854	10393
15°	3509	10258	12549
20°	2855	11884	12790
25°	2381	12433	12529
30°	2006	12509	12506
35°	1774	12298	12829
40°	1545	12025	13163
45°	1397	11823	13215
50°	1281	11641	12996
55°	1225	11377	12420
60°	1253	10873	11511
65°	1303	10107	10260
70°	1384	8808	8668
75°	1528	7177	6764
80°	1657	4971	4559
85°	1449	2632	2333

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13215 cd/sqm



TEST NUMBER: P936590

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.5	1.4
10°-20°	432.2	6.0
20°-30°	756.0	10.5
30°-40°	973.2	13.5
40°-50°	1087.0	15.1
50°-60°	1041.1	14.4
60°-70°	825.1	11.4
70°-80°	485.2	6.7
80°-90°	135.6	1.9
90°-100°	104.2	1.4
100°-110°	274.0	3.8
110°-120°	284.1	3.9
120°-130°	227.9	3.2
130°-140°	178.8	2.5
140°-150°	137.2	1.9
150°-160°	98.8	1.4
160°-170°	60.5	0.8
170°-180°	20.4	0.3
0°-30°	1285.7	17.8
0°-40°	2259.0	31.3
0°-60°	4387.1	60.8
0°-90°	5833.0	80.8
90°-120°	662.2	9.2
90°-150°	1206.1	16.7
90°-180°	1386.0	19.2
0°-180°	7218.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	754	754	754	754	754	
5°	734	788	887	1004	1040	68
15°	550	1016	1712	2075	2140	153
25°	352	1151	2039	2128	2131	162
35°	238	1100	1920	2029	2109	148
45°	162	878	1697	1944	2031	126
55°	116	558	1440	1673	1719	106
65°	92	296	1069	1202	1219	91
75°	68	182	587	645	647	71
85°	24	56	145	160	162	26
90°	1	4	11	5	5	3
95°	14	54	179	92	63	15
105°	49	75	303	460	429	52
115°	88	106	243	484	552	87
125°	122	137	221	373	440	108
135°	145	160	214	301	341	112
145°	169	179	211	257	277	106
155°	190	196	211	232	238	88
165°	206	208	211	219	222	58
175°	214	214	212	215	215	20
180°	214	214	214	214	214	



TEST NUMBER: P936590

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	753.9	753.9	753.9	753.9	753.9	753.9	753.9	753.9	753.9	753.9	753.9
2.5°	753.9	753.9	758.7	761.1	766.0	768.5	773.3	778.1	792.6	795.1	800.0
5°	734.5	744.2	775.7	787.9	821.8	867.8	887.2	918.7	984.2	1003.6	1015.7
7.5°	705.5	727.2	804.8	824.2	909.1	1030.3	1081.2	1149.1	1253.2	1304.1	1345.4
10°	659.3	705.5	843.6	889.7	1027.9	1212.1	1306.6	1401.2	1558.8	1629.0	1655.7
12.5°	608.4	683.6	884.8	947.8	1146.6	1415.7	1529.6	1633.8	1813.3	1907.8	1922.3
15°	550.3	652.1	923.6	1015.7	1272.6	1585.4	1711.5	1839.9	2007.2	2075.0	2092.0
17.5°	499.4	627.8	960.0	1056.9	1369.7	1738.1	1866.5	1973.2	2109.0	2155.1	2167.2
20°	436.3	589.0	984.2	1110.3	1471.5	1849.6	1973.2	2055.6	2147.8	2176.8	2181.7
22.5°	390.3	547.9	998.7	1129.7	1539.4	1917.4	2021.7	2087.2	2150.2	2159.9	2162.3
25°	351.5	501.8	996.4	1151.4	1597.5	1958.7	2038.7	2087.2	2123.5	2128.4	2128.4
27.5°	315.2	450.9	986.6	1156.3	1641.2	1968.4	2031.4	2065.4	2082.3	2092.0	2092.0
30°	283.6	402.4	962.4	1146.6	1660.6	1958.7	2009.6	2026.6	2043.5	2058.1	2065.4
32.5°	259.4	356.3	926.0	1127.2	1662.9	1934.4	1970.8	1980.5	2004.7	2038.7	2050.8
35°	237.6	310.3	884.8	1100.5	1648.4	1895.7	1919.9	1929.6	1978.1	2029.0	2046.0
37.5°	215.7	276.4	831.5	1054.5	1626.6	1849.6	1866.5	1883.5	1958.7	2019.3	2038.7
40°	194.0	247.2	768.5	1003.6	1592.7	1793.9	1808.4	1835.0	1934.4	2004.7	2024.1
42.5°	177.0	223.0	700.6	950.2	1549.0	1730.8	1752.6	1791.4	1905.3	1980.5	2002.3
45°	162.4	198.7	627.8	877.5	1493.2	1665.3	1696.8	1750.2	1871.4	1944.2	1963.6
47.5°	147.8	181.8	552.7	802.4	1432.7	1599.9	1641.2	1701.7	1825.4	1895.7	1912.7
50°	135.7	164.8	477.6	722.4	1367.2	1529.6	1578.1	1641.2	1767.2	1832.6	1854.4
52.5°	126.1	150.3	407.2	642.4	1292.0	1456.9	1512.6	1578.1	1696.8	1759.9	1774.5
55°	116.3	138.2	346.7	557.5	1214.5	1379.3	1439.9	1503.0	1619.3	1672.7	1682.3
57.5°	111.5	128.4	295.8	477.6	1132.1	1292.0	1359.9	1418.1	1527.2	1568.4	1578.1
60°	104.2	121.2	257.0	409.7	1042.4	1209.6	1267.9	1326.0	1418.1	1452.1	1459.3
62.5°	96.9	116.3	227.9	344.2	950.2	1112.7	1170.8	1224.2	1301.8	1326.0	1335.7
65°	92.2	111.5	206.1	295.8	855.7	1010.9	1069.0	1115.1	1178.1	1202.3	1207.2
67.5°	87.3	106.7	189.1	254.5	761.1	909.1	952.7	996.4	1044.8	1069.0	1071.5
70°	80.0	101.8	174.6	225.5	664.2	792.6	829.0	875.1	913.9	926.0	933.3
72.5°	75.2	94.5	164.8	203.6	564.8	681.2	715.1	741.7	775.7	787.9	787.9
75°	67.9	84.8	155.2	181.8	463.0	557.5	586.7	613.3	639.9	644.8	637.6
77.5°	60.6	75.2	133.3	152.7	361.2	441.2	465.5	480.0	501.8	506.6	509.1
80°	50.9	65.4	104.2	118.8	261.8	324.8	341.8	353.9	373.3	373.3	378.2
82.5°	38.8	50.9	75.2	84.8	177.0	223.0	237.6	244.9	257.0	257.0	257.0
85°	24.3	31.5	48.5	55.8	106.7	135.7	145.4	147.8	157.6	160.0	160.0
87.5°	12.1	17.0	31.5	33.9	55.8	70.3	70.3	75.2	75.2	72.8	70.3
90°	1.4	2.6	3.7	4.0	6.3	9.4	10.9	9.6	7.3	5.4	5.4
92.5°	5.7	15.5	25.2	27.7	39.0	54.0	61.4	53.8	38.6	27.2	26.2
95°	13.8	31.6	49.5	54.0	95.8	151.6	179.4	160.2	121.5	92.5	89.3
97.5°	23.8	39.5	55.3	59.2	129.0	222.0	268.5	256.3	232.0	213.6	207.4
100°	31.6	45.8	60.2	63.7	141.1	244.4	296.0	296.8	298.6	300.0	292.5
102.5°	38.2	51.6	64.8	68.2	146.7	251.4	303.7	319.3	350.4	373.8	367.4
105°	49.4	60.6	71.9	74.8	150.8	252.1	302.8	337.7	407.5	459.8	456.4
107.5°	60.8	71.3	81.8	84.5	151.6	240.9	285.6	334.3	431.7	504.6	505.5
110°	68.6	78.1	87.6	90.0	150.4	231.0	271.3	325.8	434.5	516.1	519.6



TEST NUMBER: P936590

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	76.2	85.3	94.3	96.6	150.4	222.3	258.2	313.9	425.3	508.7	514.2
115°	87.7	96.1	104.4	106.5	151.8	212.3	242.6	296.2	403.5	483.9	491.5
117.5°	99.0	106.6	114.1	116.0	154.6	206.1	231.9	280.3	377.0	449.6	458.0
120°	105.6	112.8	119.9	121.7	157.0	204.1	227.6	271.8	360.2	426.6	434.8
122.5°	112.0	119.3	126.4	128.3	160.2	202.9	224.2	264.1	343.7	403.5	411.6
125°	122.0	128.5	135.1	136.8	164.7	202.1	220.7	254.5	322.2	372.9	380.4
127.5°	130.0	136.6	143.2	144.9	169.1	201.5	217.6	246.7	304.8	348.4	354.7
130°	134.3	141.4	148.5	150.3	172.4	201.8	216.5	242.4	294.0	332.8	338.6
132.5°	138.8	145.9	153.0	154.8	175.1	202.1	215.5	238.7	285.0	319.6	324.8
135°	145.4	151.8	158.3	160.0	177.9	201.9	213.8	233.2	272.0	301.0	305.5
137.5°	152.1	158.5	164.9	166.6	182.2	203.1	213.5	230.0	262.7	287.3	290.9
140°	157.7	163.6	169.5	171.0	184.9	203.3	212.5	226.6	255.0	276.2	279.6
142.5°	162.0	167.4	173.0	174.3	187.0	204.0	212.5	224.9	249.8	268.5	271.4
145°	168.6	173.3	178.1	179.3	189.9	204.0	211.1	221.2	241.5	256.8	259.0
147.5°	175.1	179.8	184.5	185.7	194.2	205.4	211.1	219.1	235.0	247.1	248.9
150°	179.4	183.6	187.9	189.0	196.3	206.2	211.1	217.8	231.3	241.4	243.0
152.5°	183.9	187.1	190.3	191.1	197.8	206.7	211.1	216.8	228.3	237.0	238.2
155°	190.5	192.9	195.3	195.9	200.9	207.7	211.1	215.6	224.8	231.7	232.4
157.5°	195.4	197.7	200.0	200.5	204.1	208.8	211.1	214.6	221.8	227.1	227.7
160°	198.7	200.5	202.3	202.7	205.5	209.2	211.1	214.1	220.2	224.8	225.1
162.5°	202.0	203.3	204.7	205.0	207.0	209.7	211.1	213.6	218.8	222.7	223.0
165°	205.6	206.8	208.0	208.3	209.2	210.5	211.1	212.9	216.6	219.4	219.6
167.5°	208.9	209.4	210.0	210.2	211.0	212.0	212.5	213.7	216.1	217.9	218.0
170°	211.1	211.6	212.2	212.3	212.4	212.5	212.5	213.7	216.1	217.9	217.9
172.5°	212.2	212.3	212.5	212.5	212.5	212.5	212.5	213.4	215.4	216.8	216.7
175°	213.8	213.8	213.8	213.8	213.3	212.8	212.5	213.1	214.3	215.3	215.3
177.5°	213.8	213.8	213.8	213.8	213.4	213.0	212.8	213.3	214.2	215.0	214.9
180°	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8	213.8



TEST NUMBER: P936590
 CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	753.9	753.9
2.5°	804.8	800.0
5°	1035.1	1040.0
7.5°	1393.9	1391.4
10°	1733.2	1755.1
12.5°	1980.5	1985.3
15°	2130.8	2140.5
17.5°	2189.0	2191.4
20°	2191.4	2186.6
22.5°	2164.7	2159.9
25°	2133.2	2130.8
27.5°	2104.2	2106.5
30°	2092.0	2099.3
32.5°	2092.0	2104.2
35°	2096.9	2109.0
37.5°	2094.4	2109.0
40°	2084.8	2101.7
42.5°	2058.1	2070.2
45°	2016.9	2031.4
47.5°	1963.6	1973.2
50°	1895.7	1905.3
52.5°	1810.8	1813.3
55°	1709.0	1718.7
57.5°	1599.9	1602.3
60°	1478.7	1486.0
62.5°	1350.3	1350.3
65°	1214.5	1219.3
67.5°	1073.9	1086.0
70°	930.8	933.3
72.5°	790.3	790.3
75°	644.8	647.2
77.5°	506.6	506.6
80°	375.7	378.2
82.5°	259.4	264.2
85°	162.4	162.4
87.5°	75.2	67.9
90°	5.4	5.4
92.5°	21.8	17.5
95°	76.1	63.0
97.5°	182.4	157.4
100°	262.8	233.0
102.5°	341.9	316.4
105°	442.7	429.0
107.5°	508.7	512.1
110°	533.9	548.3



TEST NUMBER: P936590

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	536.1	558.1
115°	521.9	552.4
117.5°	491.8	525.5
120°	467.6	500.3
122.5°	443.9	476.2
125°	410.1	439.9
127.5°	379.8	404.9
130°	361.8	385.1
132.5°	345.6	366.4
135°	323.4	341.3
137.5°	305.6	320.2
140°	293.3	307.0
142.5°	283.2	295.0
145°	268.0	277.0
147.5°	256.3	263.7
150°	249.0	255.0
152.5°	242.7	247.2
155°	235.4	238.5
157.5°	229.8	231.9
160°	226.3	227.6
162.5°	224.1	225.3
165°	220.9	222.1
167.5°	218.6	219.1
170°	217.9	217.9
172.5°	216.2	215.8
175°	215.3	215.3
177.5°	214.3	213.8
180°	213.8	213.8



TEST NUMBER: P936590

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-6-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.78	10.08	9.41	10.73	11.48	21.94	23.24	22.57	23.89	24.64
	3H	9.51	10.69	10.16	11.35	12.13	23.81	24.98	24.45	25.64	26.43
	4H	9.83	10.94	10.49	11.62	12.41	24.47	25.58	25.13	26.25	27.05
	6H	10.10	11.13	10.78	11.82	12.63	24.92	25.95	25.59	26.63	27.44
	8H	10.18	11.17	10.87	11.87	12.69	25.05	26.03	25.74	26.74	27.55
	12H	10.22	11.16	10.91	11.86	12.70	25.13	26.07	25.82	26.77	27.61
4H	2H	16.03	17.15	16.70	17.82	18.61	22.27	23.38	22.93	24.05	24.85
	3H	17.64	18.58	18.32	19.29	20.10	24.35	25.28	25.03	25.99	26.81
	4H	17.75	18.61	18.45	19.32	20.16	25.13	25.98	25.83	26.69	27.54
	6H	17.79	18.53	18.51	19.27	20.12	25.69	26.43	26.40	27.17	28.02
	8H	17.78	18.47	18.50	19.21	20.08	25.86	26.55	26.58	27.29	28.16
	12H	17.76	18.38	18.50	19.14	20.02	25.97	26.60	26.72	27.36	28.23
8H	4H	19.23	19.93	19.95	20.66	21.53	25.23	25.92	25.95	26.66	27.52
	6H	19.50	20.07	20.25	20.85	21.72	25.87	26.45	26.62	27.23	28.10
	8H	19.52	20.04	20.28	20.82	21.70	26.10	26.61	26.86	27.39	28.27
	12H	19.51	19.97	20.28	20.74	21.68	26.26	26.71	27.03	27.48	28.43
12H	4H	19.40	20.02	20.14	20.78	21.66	25.20	25.83	25.94	26.59	27.46
	6H	19.76	20.28	20.52	21.06	21.94	25.86	26.38	26.62	27.16	28.04
	8H	19.85	20.31	20.62	21.08	22.02	26.11	26.57	26.88	27.34	28.28