

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937680

Luminaire Tested: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937680
REPORT IS A COMBINATION OF REPORTS P933559 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20624.2 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 174
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937680
CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P937680

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44	44	44	44
1	96	91	87	84	88	84	80	77	69	67	65	56	55	53	44	43	42	36	36	36	36
2	87	79	73	68	79	73	67	63	60	56	53	49	46	43	38	36	34	30	30	30	30
3	79	69	62	56	72	63	57	52	53	48	44	43	39	36	33	31	29	24	24	24	24
4	72	61	53	46	65	56	49	43	46	41	37	38	34	30	29	27	24	20	20	20	20
5	66	54	46	39	60	49	42	37	41	36	31	33	29	26	26	23	21	17	17	17	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	20	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16	13	13	13	13
8	51	39	31	26	47	36	29	24	30	24	20	25	20	17	19	16	14	11	11	11	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10	10	10	10
10	44	32	25	20	41	30	23	19	25	20	16	21	16	14	16	13	11	9	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3641	3641	3641
5°	3559	4210	4894
10°	3229	6138	8114
15°	2745	8021	9798
20°	2236	9297	9985
25°	1866	9731	9782
30°	1574	9795	9764
35°	1392	9635	10016
40°	1214	9426	10277
45°	1100	9274	10317
50°	1010	9138	10147
55°	968	8938	9697
60°	992	8549	8987
65°	1034	7956	8011
70°	1104	6944	6768
75°	1229	5666	5282
80°	1352	3934	3559
85°	1225	2091	1821

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10317 cd/sqm



TEST NUMBER: P937680

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.3	0.7
10°-20°	674.9	3.3
20°-30°	1180.5	5.7
30°-40°	1519.6	7.4
40°-50°	1697.4	8.2
50°-60°	1625.7	7.9
60°-70°	1288.4	6.2
70°-80°	757.6	3.7
80°-90°	217.2	1.1
90°-100°	865.5	4.2
100°-110°	2275.5	11.0
110°-120°	2359.4	11.4
120°-130°	1892.6	9.2
130°-140°	1485.0	7.2
140°-150°	1139.8	5.5
150°-160°	820.8	4.0
160°-170°	502.2	2.4
170°-180°	169.7	0.8
0°-30°	2007.7	9.7
0°-40°	3527.3	17.1
0°-60°	6850.4	33.2
0°-90°	9113.7	44.2
90°-120°	5500.5	26.7
90°-150°	10017.8	48.6
90°-180°	11511.0	55.8
0°-180°	20624.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1177	1177	1177	1177	1177	
5°	1147	1230	1385	1567	1624	106
15°	859	1586	2672	3240	3342	239
25°	549	1798	3183	3323	3327	253
35°	371	1718	2998	3168	3293	232
45°	254	1370	2650	3036	3172	196
55°	182	871	2248	2612	2684	166
65°	144	462	1669	1877	1904	143
75°	106	284	916	1007	1011	111
85°	38	87	227	250	254	40
90°	12	33	90	45	45	12
95°	114	448	1491	769	523	127
105°	410	621	2516	3819	3563	435
115°	728	884	2015	4020	4588	719
125°	1013	1136	1833	3097	3654	899
135°	1207	1329	1776	2500	2835	934
145°	1400	1490	1753	2133	2300	877
155°	1582	1627	1753	1924	1981	727
165°	1708	1730	1753	1822	1845	482
175°	1776	1776	1765	1788	1788	169
180°	1776	1776	1776	1776	1776	



TEST NUMBER: P937680

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1177.2	1177.2	1177.2	1177.2	1177.2	1177.2	1177.2	1177.2	1177.2	1177.2	1177.2
2.5°	1177.2	1177.2	1184.8	1188.6	1196.1	1200.0	1207.5	1215.0	1237.8	1241.6	1249.1
5°	1147.0	1162.0	1211.3	1230.2	1283.2	1355.1	1385.4	1434.6	1536.8	1567.1	1586.0
7.5°	1101.5	1135.6	1256.7	1287.0	1419.4	1608.7	1688.2	1794.2	1957.0	2036.4	2100.8
10°	1029.6	1101.5	1317.2	1389.1	1605.0	1892.6	2040.3	2187.9	2433.9	2543.6	2585.3
12.5°	950.1	1067.4	1381.6	1480.1	1790.4	2210.5	2388.5	2551.3	2831.4	2979.0	3001.7
15°	859.2	1018.2	1442.1	1586.0	1987.3	2475.6	2672.4	2873.0	3134.2	3240.1	3266.7
17.5°	779.8	980.4	1499.0	1650.3	2138.6	2714.0	2914.7	3081.2	3293.1	3365.0	3384.0
20°	681.3	919.9	1536.8	1733.6	2297.6	2888.1	3081.2	3209.9	3353.7	3399.1	3406.7
22.5°	609.4	855.5	1559.5	1763.9	2403.6	2994.1	3156.8	3259.1	3357.5	3372.7	3376.4
25°	548.8	783.6	1555.7	1798.0	2494.5	3058.5	3183.4	3259.1	3315.9	3323.4	3323.4
27.5°	492.1	704.0	1540.6	1805.5	2562.6	3073.6	3172.0	3225.0	3251.5	3266.7	3266.7
30°	442.8	628.4	1502.7	1790.4	2592.9	3058.5	3137.9	3164.5	3190.9	3213.7	3225.0
32.5°	405.0	556.4	1446.0	1760.2	2596.6	3020.7	3077.4	3092.6	3130.4	3183.4	3202.3
35°	370.9	484.5	1381.6	1718.5	2573.9	2960.0	2997.9	3013.0	3088.8	3168.2	3194.8
37.5°	336.9	431.6	1298.3	1646.6	2539.9	2888.1	2914.7	2941.1	3058.5	3153.1	3183.4
40°	302.8	386.1	1200.0	1567.1	2486.9	2801.1	2823.7	2865.4	3020.7	3130.4	3160.7
42.5°	276.3	348.3	1094.0	1483.8	2418.7	2702.6	2736.7	2797.3	2975.2	3092.6	3126.6
45°	253.6	310.4	980.4	1370.2	2331.7	2600.5	2649.6	2732.9	2922.2	3035.8	3066.0
47.5°	230.9	283.9	863.0	1253.0	2237.1	2498.3	2562.6	2657.2	2850.3	2960.0	2986.6
50°	212.0	257.4	745.7	1128.0	2134.9	2388.5	2464.2	2562.6	2759.5	2861.7	2895.8
52.5°	196.8	234.6	635.9	1003.1	2017.5	2274.9	2362.0	2464.2	2649.6	2748.1	2770.8
55°	181.7	215.7	541.3	870.6	1896.4	2153.8	2248.5	2346.8	2528.6	2611.8	2626.9
57.5°	174.1	200.6	461.8	745.7	1767.7	2017.5	2123.5	2214.4	2384.7	2449.0	2464.2
60°	162.7	189.3	401.2	639.7	1627.6	1888.8	1979.7	2070.5	2214.4	2267.4	2278.7
62.5°	151.4	181.7	355.8	537.5	1483.8	1737.4	1828.3	1911.5	2032.7	2070.5	2085.6
65°	143.8	174.1	321.7	461.8	1336.2	1578.4	1669.2	1741.3	1839.6	1877.4	1885.1
67.5°	136.3	166.6	295.3	397.5	1188.6	1419.4	1487.6	1555.7	1631.4	1669.2	1673.1
70°	124.9	159.0	272.6	352.0	1037.1	1237.8	1294.6	1366.5	1427.1	1446.0	1457.3
72.5°	117.4	147.6	257.4	317.9	881.9	1063.7	1116.7	1158.3	1211.3	1230.2	1230.2
75°	106.0	132.5	242.3	283.9	722.9	870.6	916.0	957.7	999.3	1006.9	995.5
77.5°	94.6	117.4	208.2	238.5	564.0	688.9	726.8	749.5	783.6	791.1	794.9
80°	79.5	102.2	162.7	185.5	408.8	507.2	533.7	552.7	582.9	582.9	590.5
82.5°	60.5	79.5	117.4	132.5	276.3	348.3	370.9	382.3	401.2	401.2	401.2
85°	37.8	49.2	75.7	87.1	166.6	212.0	227.1	230.9	246.0	249.8	249.8
87.5°	18.9	26.5	49.2	53.0	87.1	109.7	109.7	117.4	117.4	113.5	109.7
90°	11.9	21.5	30.9	33.3	52.4	77.8	90.5	80.5	60.4	45.3	45.3
92.5°	47.7	128.6	209.7	230.0	323.4	447.8	510.1	447.0	321.0	226.4	217.5
95°	114.4	262.7	411.0	448.1	795.6	1259.1	1490.8	1330.3	1009.3	768.6	741.3
97.5°	197.8	328.6	459.5	492.2	1071.7	1844.4	2230.8	2129.4	1926.5	1774.4	1722.5
100°	262.1	380.8	499.4	529.1	1172.2	2029.7	2458.5	2465.9	2480.7	2491.8	2430.0
102.5°	317.0	427.6	538.3	566.0	1218.3	2088.0	2522.8	2652.0	2910.5	3104.3	3051.3
105°	410.0	503.7	597.4	620.8	1252.5	2094.6	2515.7	2805.4	3384.8	3819.3	3790.9
107.5°	505.3	592.7	680.1	701.9	1258.8	2001.3	2372.6	2776.8	3585.0	4191.1	4198.0
110°	569.7	648.5	727.4	747.2	1249.2	1918.7	2253.4	2705.2	3608.8	4286.4	4316.1



TEST NUMBER: P937680

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	632.8	708.0	783.2	802.0	1249.7	1846.6	2145.0	2607.4	3532.2	4225.7	4271.2
115°	728.1	797.5	866.9	884.2	1261.2	1763.8	2015.1	2460.6	3351.4	4019.5	4082.6
117.5°	822.3	885.3	948.3	964.1	1284.7	1712.0	1925.8	2327.7	3131.7	3734.7	3804.7
120°	877.1	936.4	995.8	1010.6	1303.8	1694.6	1890.0	2257.3	2991.9	3542.9	3611.0
122.5°	930.7	990.6	1050.4	1065.4	1331.2	1685.5	1862.6	2193.3	2854.9	3351.0	3418.1
125°	1013.0	1067.5	1122.0	1135.7	1368.0	1677.9	1832.8	2113.8	2675.7	3097.2	3158.9
127.5°	1079.6	1134.7	1189.8	1203.6	1405.0	1673.5	1807.8	2049.0	2531.5	2893.4	2945.5
130°	1115.4	1174.7	1234.1	1248.9	1432.0	1676.2	1798.3	2013.0	2442.6	2764.7	2813.0
132.5°	1152.4	1211.7	1271.0	1285.8	1453.8	1677.8	1789.9	1982.1	2366.7	2655.1	2698.3
135°	1207.2	1261.2	1315.2	1328.7	1477.7	1676.3	1775.6	1936.6	2258.6	2500.1	2537.3
137.5°	1263.2	1316.7	1370.1	1383.5	1513.4	1686.6	1773.2	1909.3	2181.6	2385.8	2416.2
140°	1309.7	1359.0	1408.1	1420.5	1535.3	1688.3	1764.8	1882.4	2117.6	2294.0	2322.5
142.5°	1345.4	1391.0	1436.5	1447.9	1553.5	1694.4	1764.8	1868.2	2074.7	2229.6	2254.1
145°	1400.2	1439.9	1479.7	1489.6	1577.4	1694.5	1753.0	1837.4	2006.4	2133.1	2151.6
147.5°	1455.0	1493.7	1532.4	1542.0	1612.3	1706.1	1753.0	1819.5	1952.4	2052.1	2067.5
150°	1490.8	1525.7	1560.7	1569.4	1630.7	1712.2	1753.0	1809.2	1921.4	2005.6	2018.0
152.5°	1527.7	1554.2	1580.7	1587.3	1642.5	1716.1	1753.0	1800.9	1896.7	1968.6	1978.0
155°	1582.5	1602.1	1621.8	1626.7	1668.8	1724.9	1753.0	1791.1	1867.3	1924.5	1930.7
157.5°	1623.0	1642.1	1661.2	1666.0	1695.0	1733.7	1753.0	1782.6	1841.9	1886.4	1890.8
160°	1650.4	1665.3	1680.1	1683.9	1706.9	1737.6	1753.0	1778.4	1829.2	1867.3	1869.8
162.5°	1677.8	1688.9	1700.1	1702.9	1719.6	1741.8	1753.0	1774.4	1817.3	1849.5	1851.8
165°	1707.6	1717.7	1727.8	1730.3	1737.8	1747.9	1753.0	1768.4	1799.0	1822.0	1824.5
167.5°	1735.0	1739.8	1744.6	1745.8	1752.1	1760.6	1764.8	1775.0	1795.1	1810.2	1811.3
170°	1753.0	1757.8	1762.5	1763.7	1764.1	1764.6	1764.8	1775.0	1795.1	1810.2	1810.2
172.5°	1762.5	1763.5	1764.6	1764.8	1764.8	1764.8	1764.8	1772.8	1788.7	1800.7	1799.7
175°	1775.6	1775.6	1775.6	1775.6	1772.0	1767.2	1764.8	1769.9	1779.9	1787.5	1787.5
177.5°	1775.6	1775.6	1775.6	1775.6	1772.9	1769.1	1767.2	1771.2	1779.2	1785.1	1784.0
180°	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6



TEST NUMBER: P937680
 CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1177.2	1177.2
2.5°	1256.7	1249.1
5°	1616.3	1623.9
7.5°	2176.5	2172.7
10°	2706.5	2740.5
12.5°	3092.6	3100.1
15°	3327.2	3342.4
17.5°	3418.0	3421.9
20°	3421.9	3414.3
22.5°	3380.2	3372.7
25°	3331.0	3327.2
27.5°	3285.6	3289.4
30°	3266.7	3278.0
32.5°	3266.7	3285.6
35°	3274.2	3293.1
37.5°	3270.4	3293.1
40°	3255.3	3281.8
42.5°	3213.7	3232.6
45°	3149.3	3172.0
47.5°	3066.0	3081.2
50°	2960.0	2975.2
52.5°	2827.6	2831.4
55°	2668.6	2683.7
57.5°	2498.3	2502.0
60°	2309.0	2320.4
62.5°	2108.4	2108.4
65°	1896.4	1904.0
67.5°	1676.9	1695.8
70°	1453.5	1457.3
72.5°	1234.0	1234.0
75°	1006.9	1010.7
77.5°	791.1	791.1
80°	586.8	590.5
82.5°	405.0	412.6
85°	253.6	253.6
87.5°	117.4	106.0
90°	45.3	45.3
92.5°	181.4	145.4
95°	632.2	523.1
97.5°	1514.9	1307.3
100°	2182.7	1935.3
102.5°	2839.5	2627.7
105°	3676.9	3563.1
107.5°	4225.6	4253.1
110°	4434.7	4553.4



TEST NUMBER: P937680
CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4453.5	4635.7
115°	4335.3	4587.9
117.5°	4084.9	4365.1
120°	3883.1	4155.4
122.5°	3686.6	3955.1
125°	3406.3	3653.6
127.5°	3154.3	3362.9
130°	3005.7	3198.5
132.5°	2870.9	3043.6
135°	2686.1	2835.0
137.5°	2538.0	2659.9
140°	2436.4	2550.2
142.5°	2352.1	2450.1
145°	2225.8	2299.9
147.5°	2128.9	2190.3
150°	2067.9	2117.6
152.5°	2015.6	2053.2
155°	1955.6	1980.6
157.5°	1908.3	1925.8
160°	1879.9	1890.0
162.5°	1861.4	1870.9
165°	1834.7	1844.7
167.5°	1815.5	1819.7
170°	1810.2	1810.2
172.5°	1796.0	1792.2
175°	1787.5	1787.5
177.5°	1779.8	1775.6
180°	1775.6	1775.6



TEST NUMBER: P937680
 CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.95	5.79	5.94	6.80	8.15	18.14	18.98	19.13	20.00	21.34
	3H	5.65	6.41	6.66	7.43	8.80	19.98	20.74	20.99	21.76	23.13
	4H	5.95	6.67	6.97	7.69	9.07	20.63	21.35	21.65	22.37	23.75
	6H	6.20	6.86	7.23	7.89	9.28	21.06	21.73	22.09	22.76	24.15
	8H	6.26	6.90	7.30	7.94	9.33	21.19	21.82	22.22	22.86	24.25
	12H	6.28	6.88	7.32	7.92	9.33	21.26	21.86	22.30	22.90	24.31
4H	2H	12.17	12.89	13.19	13.91	15.29	18.41	19.13	19.44	20.15	21.53
	3H	13.73	14.33	14.77	15.39	16.78	20.46	21.06	21.49	22.11	23.50
	4H	13.83	14.38	14.87	15.42	16.84	21.23	21.78	22.27	22.83	24.24
	6H	13.83	14.31	14.89	15.38	16.79	21.77	22.25	22.82	23.32	24.72
	8H	13.81	14.26	14.87	15.32	16.74	21.93	22.38	22.99	23.44	24.87
	12H	13.77	14.17	14.84	15.25	16.67	22.03	22.43	23.10	23.51	24.94
8H	4H	15.27	15.72	16.33	16.78	18.20	21.29	21.73	22.34	22.79	24.22
	6H	15.51	15.88	16.59	16.99	18.41	21.92	22.29	23.00	23.39	24.81
	8H	15.53	15.86	16.62	16.94	18.38	22.14	22.47	23.23	23.55	24.99
	12H	15.50	15.78	16.59	16.87	18.35	22.29	22.57	23.38	23.66	25.14
12H	4H	15.42	15.82	16.49	16.89	18.32	21.24	21.64	22.31	22.72	24.15
	6H	15.77	16.10	16.86	17.18	18.62	21.90	22.23	22.99	23.31	24.75
	8H	15.84	16.13	16.93	17.21	18.69	22.13	22.42	23.22	23.50	24.98