

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938095

Luminaire Tested: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P938095  
REPORT IS A COMBINATION OF REPORTS P933615 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15629.6 lumens  
Efficiency: N/A  
Efficacy: 121.3 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 128.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P938095  
CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P938095

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	90	86	83	86	82	79	76	67	65	62	53	51	50	40	39	38	32
2	86	78	72	67	78	71	66	61	58	54	51	46	43	41	35	33	31	26
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26	21
4	71	60	52	46	64	55	48	42	45	40	35	35	32	29	27	24	22	18
5	65	53	45	39	59	49	41	36	40	34	30	31	27	24	24	21	19	15
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13
7	55	43	35	29	50	39	32	27	32	26	23	25	21	18	19	16	14	11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	26	21	17	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	18	24	19	16	19	15	13	15	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3642	3642	3642
5°	3558	4209	4895
10°	3227	6135	8115
15°	2743	8015	9799
20°	2233	9289	9986
25°	1863	9720	9783
30°	1571	9782	9765
35°	1389	9619	10017
40°	1210	9408	10278
45°	1096	9254	10319
50°	1005	9115	10147
55°	962	8911	9698
60°	985	8519	8988
65°	1025	7925	8012
70°	1092	6911	6768
75°	1211	5634	5282
80°	1322	3907	3559
85°	1174	2074	1822

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 10319 cd/sqm



TEST NUMBER: P938095

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.5	0.6
10°-20°	450.0	2.9
20°-30°	787.1	5.0
30°-40°	1013.2	6.5
40°-50°	1131.7	7.2
50°-60°	1083.9	6.9
60°-70°	859.0	5.5
70°-80°	505.1	3.2
80°-90°	146.0	0.9
90°-100°	718.3	4.6
100°-110°	1888.3	12.1
110°-120°	1958.0	12.5
120°-130°	1570.5	10.0
130°-140°	1232.3	7.9
140°-150°	945.9	6.1
150°-160°	681.2	4.4
160°-170°	416.8	2.7
170°-180°	140.8	0.9
0°-30°	1338.6	8.6
0°-40°	2351.8	15.0
0°-60°	4567.4	29.2
0°-90°	6077.5	38.9
90°-120°	4564.6	29.2
90°-150°	8313.3	53.2
90°-180°	9552.0	61.1
0°-180°	15629.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	785	785	785	785	785	
5°	765	820	924	1045	1083	71
15°	573	1058	1782	2160	2228	159
25°	366	1199	2122	2216	2218	169
35°	247	1146	1999	2112	2196	154
45°	169	914	1767	2024	2115	131
55°	121	580	1499	1741	1789	110
65°	96	308	1113	1252	1270	95
75°	71	189	611	671	674	74
85°	25	58	152	167	169	27
90°	10	28	75	38	38	10
95°	95	372	1237	638	434	105
105°	340	515	2088	3170	2957	361
115°	604	734	1672	3336	3807	597
125°	841	942	1521	2570	3032	746
135°	1002	1103	1474	2075	2353	775
145°	1162	1236	1455	1770	1909	728
155°	1313	1350	1455	1597	1644	603
165°	1417	1436	1455	1512	1531	400
175°	1474	1474	1465	1483	1483	140
180°	1474	1474	1474	1474	1474	



TEST NUMBER: P938095

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9
2.5°	784.9	784.9	790.0	792.5	797.5	800.0	805.1	810.1	825.3	827.8	832.9
5°	764.7	774.8	807.6	820.2	855.6	903.5	923.7	956.5	1024.6	1044.9	1057.5
7.5°	734.4	757.1	837.9	858.1	946.4	1072.6	1125.6	1196.2	1304.8	1357.8	1400.7
10°	686.5	734.4	878.3	926.3	1070.1	1261.8	1360.3	1458.8	1622.7	1696.0	1723.7
12.5°	633.5	711.7	921.2	986.8	1193.8	1473.9	1592.5	1701.0	1887.7	1986.2	2001.3
15°	572.9	678.9	961.6	1057.5	1325.0	1650.5	1781.7	1915.5	2089.6	2160.3	2178.0
17.5°	519.9	653.7	999.4	1100.4	1425.9	1809.5	1943.3	2054.3	2195.6	2243.6	2256.3
20°	454.3	613.3	1024.6	1155.8	1531.9	1925.7	2054.3	2140.2	2236.0	2266.3	2271.4
22.5°	406.4	570.3	1039.8	1176.1	1602.6	1996.3	2104.8	2172.9	2238.6	2248.6	2251.2
25°	366.0	522.4	1037.2	1198.8	1663.1	2039.2	2122.5	2172.9	2210.8	2215.9	2215.9
27.5°	328.0	469.4	1027.2	1203.9	1708.6	2049.3	2114.9	2150.3	2167.9	2178.0	2178.0
30°	295.3	419.0	1001.9	1193.8	1728.7	2039.2	2092.2	2109.9	2127.5	2142.6	2150.3
32.5°	270.1	371.0	964.1	1173.5	1731.3	2014.0	2051.8	2061.9	2087.2	2122.5	2135.1
35°	247.3	323.1	921.2	1145.8	1716.1	1973.6	1998.8	2008.9	2059.4	2112.4	2130.0
37.5°	224.6	287.7	865.6	1097.9	1693.4	1925.7	1943.3	1961.0	2039.2	2102.2	2122.5
40°	201.9	257.5	800.0	1044.9	1658.1	1867.6	1882.7	1910.5	2014.0	2087.2	2107.3
42.5°	184.2	232.2	729.3	989.3	1612.7	1802.0	1824.7	1865.0	1983.6	2061.9	2084.7
45°	169.1	206.9	653.7	913.6	1554.6	1733.8	1766.7	1822.1	1948.3	2024.0	2044.3
47.5°	153.9	189.3	575.4	835.3	1491.5	1665.7	1708.6	1771.7	1900.4	1973.6	1991.3
50°	141.3	171.6	497.2	752.1	1423.4	1592.5	1643.0	1708.6	1839.8	1908.0	1930.6
52.5°	131.2	156.4	424.0	668.8	1345.1	1516.7	1574.8	1643.0	1766.7	1832.3	1847.4
55°	121.1	143.8	360.9	580.4	1264.4	1436.0	1499.1	1564.8	1685.9	1741.3	1751.5
57.5°	116.1	133.8	307.9	497.2	1178.6	1345.1	1415.8	1476.4	1590.0	1632.9	1643.0
60°	108.5	126.2	267.5	426.5	1085.3	1259.4	1319.9	1380.5	1476.4	1511.8	1519.3
62.5°	100.9	121.1	237.2	358.4	989.3	1158.4	1219.0	1274.5	1355.2	1380.5	1390.6
65°	95.9	116.1	214.5	307.9	890.9	1052.4	1113.0	1160.9	1226.5	1251.8	1256.9
67.5°	90.8	111.1	196.8	265.0	792.5	946.4	991.9	1037.2	1087.7	1113.0	1115.5
70°	83.3	106.0	181.7	234.7	691.5	825.3	863.1	911.1	951.5	964.1	971.6
72.5°	78.2	98.5	171.6	212.0	588.0	709.2	744.5	772.3	807.6	820.2	820.2
75°	70.7	88.3	161.5	189.3	482.1	580.4	610.7	638.5	666.3	671.4	663.7
77.5°	63.1	78.2	138.8	159.0	376.1	459.4	484.6	499.7	522.4	527.4	530.0
80°	53.0	68.2	108.5	123.7	272.6	338.2	355.8	368.4	388.7	388.7	393.7
82.5°	40.4	53.0	78.2	88.3	184.2	232.2	247.3	254.9	267.5	267.5	267.5
85°	25.2	32.9	50.5	58.1	111.1	141.3	151.5	153.9	164.1	166.6	166.6
87.5°	12.6	17.7	32.9	35.3	58.1	73.2	73.2	78.2	78.2	75.7	73.2
90°	9.9	17.9	25.7	27.7	43.5	64.7	75.2	66.8	50.0	37.5	37.5
92.5°	39.5	106.8	174.1	190.9	268.4	371.6	423.3	370.9	266.3	187.8	180.4
95°	94.9	218.0	341.1	371.9	660.3	1044.9	1237.1	1104.0	837.6	637.8	615.2
97.5°	164.2	272.7	381.3	408.5	889.4	1530.7	1851.3	1767.1	1598.8	1472.5	1429.4
100°	217.5	316.0	414.5	439.1	972.8	1684.3	2040.2	2046.3	2058.6	2067.9	2016.6
102.5°	263.0	354.9	446.7	469.8	1011.1	1732.8	2093.6	2200.8	2415.3	2576.1	2532.2
105°	340.2	418.0	495.7	515.2	1039.3	1738.2	2087.6	2328.0	2808.8	3169.5	3145.9
107.5°	419.3	491.8	564.3	582.5	1044.6	1660.8	1968.9	2304.3	2975.0	3478.0	3483.7
110°	472.7	538.2	603.8	620.1	1036.7	1592.3	1870.1	2245.0	2994.8	3557.1	3581.7



TEST NUMBER: P938095

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	525.2	587.5	650.0	665.5	1037.0	1532.4	1780.0	2163.7	2931.1	3506.7	3544.5
115°	604.2	661.8	719.3	733.7	1046.6	1463.7	1672.3	2041.9	2781.2	3335.6	3388.1
117.5°	682.3	734.7	786.9	800.0	1066.1	1420.8	1598.1	1931.7	2598.8	3099.3	3157.4
120°	727.8	777.1	826.3	838.6	1081.8	1406.2	1568.4	1873.2	2482.8	2940.1	2996.5
122.5°	772.3	822.0	871.6	884.0	1104.6	1398.6	1545.7	1820.1	2369.2	2780.9	2836.5
125°	840.6	885.9	931.1	942.4	1135.2	1392.4	1520.9	1754.1	2220.5	2570.2	2621.5
127.5°	896.0	941.7	987.4	998.8	1166.0	1388.8	1500.2	1700.4	2100.8	2401.1	2444.3
130°	925.6	974.9	1024.0	1036.4	1188.3	1391.0	1492.3	1670.5	2027.0	2294.3	2334.3
132.5°	956.2	1005.5	1054.7	1067.0	1206.5	1392.4	1485.3	1644.9	1964.0	2203.3	2239.1
135°	1001.8	1046.6	1091.5	1102.6	1226.2	1391.1	1473.5	1607.1	1874.3	2074.7	2105.6
137.5°	1048.2	1092.6	1137.0	1148.1	1255.9	1399.6	1471.5	1584.4	1810.4	1979.8	2005.1
140°	1086.8	1127.7	1168.5	1178.8	1274.1	1401.1	1464.6	1562.2	1757.3	1903.7	1927.3
142.5°	1116.5	1154.3	1192.0	1201.5	1289.2	1406.1	1464.6	1550.3	1721.7	1850.2	1870.6
145°	1161.9	1194.9	1227.9	1236.2	1309.0	1406.1	1454.7	1524.8	1665.0	1770.2	1785.6
147.5°	1207.5	1239.6	1271.7	1279.7	1338.1	1415.8	1454.7	1509.9	1620.2	1703.0	1715.7
150°	1237.1	1266.1	1295.2	1302.4	1353.1	1420.8	1454.7	1501.3	1594.5	1664.4	1674.7
152.5°	1267.8	1289.7	1311.7	1317.2	1363.1	1424.1	1454.7	1494.5	1574.0	1633.7	1641.5
155°	1313.3	1329.6	1345.8	1349.9	1384.8	1431.4	1454.7	1486.4	1549.7	1597.1	1602.3
157.5°	1346.9	1362.7	1378.5	1382.5	1406.5	1438.6	1454.7	1479.3	1528.5	1565.4	1569.1
160°	1369.7	1382.0	1394.3	1397.4	1416.5	1442.0	1454.7	1475.8	1518.0	1549.6	1551.7
162.5°	1392.4	1401.6	1410.8	1413.1	1427.0	1445.4	1454.7	1472.4	1508.0	1534.8	1536.8
165°	1417.1	1425.5	1433.8	1435.9	1442.1	1450.5	1454.7	1467.5	1493.0	1512.1	1514.2
167.5°	1439.9	1443.8	1447.8	1448.7	1454.0	1461.1	1464.6	1472.9	1489.6	1502.1	1503.0
170°	1454.7	1458.7	1462.7	1463.6	1463.9	1464.4	1464.6	1472.9	1489.6	1502.1	1502.1
172.5°	1462.6	1463.4	1464.4	1464.6	1464.6	1464.6	1464.6	1471.2	1484.4	1494.3	1493.5
175°	1473.5	1473.5	1473.5	1473.5	1470.5	1466.6	1464.6	1468.8	1477.1	1483.4	1483.4
177.5°	1473.5	1473.5	1473.5	1473.5	1471.2	1468.1	1466.6	1469.8	1476.4	1481.4	1480.5
180°	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5



TEST NUMBER: P938095

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	784.9	784.9
2.5°	837.9	832.9
5°	1077.6	1082.7
7.5°	1451.1	1448.6
10°	1804.5	1827.2
12.5°	2061.9	2067.0
15°	2218.4	2228.5
17.5°	2278.9	2281.5
20°	2281.5	2276.4
22.5°	2253.7	2248.6
25°	2220.9	2218.4
27.5°	2190.6	2193.2
30°	2178.0	2185.6
32.5°	2178.0	2190.6
35°	2183.0	2195.6
37.5°	2180.6	2195.6
40°	2170.4	2188.1
42.5°	2142.6	2155.2
45°	2099.8	2114.9
47.5°	2044.3	2054.3
50°	1973.6	1983.6
52.5°	1885.3	1887.7
55°	1779.3	1789.4
57.5°	1665.7	1668.2
60°	1539.5	1547.1
62.5°	1405.8	1405.8
65°	1264.4	1269.5
67.5°	1118.0	1130.6
70°	969.1	971.6
72.5°	822.7	822.7
75°	671.4	673.8
77.5°	527.4	527.4
80°	391.2	393.7
82.5°	270.1	275.1
85°	169.1	169.1
87.5°	78.2	70.7
90°	37.5	37.5
92.5°	150.5	120.6
95°	524.7	434.1
97.5°	1257.2	1084.9
100°	1811.3	1606.0
102.5°	2356.4	2180.6
105°	3051.3	2956.9
107.5°	3506.6	3529.4
110°	3680.2	3778.6





TEST NUMBER: P938095

CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	3695.7	3846.8
115°	3597.7	3807.3
117.5°	3389.9	3622.4
120°	3222.5	3448.3
122.5°	3059.4	3282.2
125°	2826.8	3032.0
127.5°	2617.6	2790.7
130°	2494.3	2654.2
132.5°	2382.4	2525.7
135°	2229.2	2352.6
137.5°	2106.2	2207.3
140°	2021.8	2116.3
142.5°	1951.8	2033.2
145°	1847.1	1908.6
147.5°	1766.7	1817.7
150°	1716.0	1757.3
152.5°	1672.7	1703.9
155°	1622.9	1643.6
157.5°	1583.6	1598.1
160°	1560.0	1568.4
162.5°	1544.7	1552.6
165°	1522.5	1530.9
167.5°	1506.5	1510.0
170°	1502.1	1502.1
172.5°	1490.4	1487.3
175°	1483.4	1483.4
177.5°	1477.0	1473.5
180°	1473.5	1473.5



TEST NUMBER: P938095  
 CATALOG NUMBER: SQ4-FB-125U-100D-B2750-1D-UNV-STD-W-8-4000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.39	5.18	5.43	6.23	7.65	17.56	18.36	18.60	19.41	20.83
	3H	5.09	5.80	6.14	6.86	8.30	19.40	20.11	20.45	21.17	22.61
	4H	5.38	6.06	6.44	7.12	8.57	20.04	20.72	21.10	21.78	23.23
	6H	5.63	6.25	6.70	7.32	8.78	20.47	21.09	21.54	22.16	23.62
	8H	5.69	6.29	6.77	7.37	8.82	20.59	21.18	21.66	22.26	23.72
	12H	5.71	6.28	6.79	7.35	8.83	20.65	21.22	21.73	22.29	23.77
4H	2H	11.59	12.27	12.66	13.33	14.78	17.83	18.51	18.90	19.57	21.02
	3H	13.15	13.72	14.23	14.81	16.27	19.87	20.44	20.95	21.53	22.98
	4H	13.25	13.77	14.33	14.85	16.33	20.63	21.16	21.72	22.23	23.71
	6H	13.25	13.70	14.34	14.80	16.28	21.17	21.62	22.26	22.72	24.19
	8H	13.23	13.65	14.32	14.74	16.23	21.33	21.75	22.42	22.84	24.33
	12H	13.18	13.56	14.29	14.67	16.16	21.42	21.80	22.53	22.91	24.40
8H	4H	14.69	15.10	15.78	16.20	17.69	20.69	21.11	21.78	22.20	23.69
	6H	14.92	15.27	16.04	16.41	17.89	21.31	21.66	22.43	22.80	24.28
	8H	14.94	15.25	16.06	16.36	17.87	21.53	21.84	22.65	22.96	24.46
	12H	14.91	15.17	16.03	16.29	17.83	21.68	21.94	22.80	23.06	24.60
12H	4H	14.83	15.21	15.93	16.31	17.81	20.64	21.02	21.75	22.13	23.62
	6H	15.18	15.49	16.30	16.61	18.11	21.30	21.60	22.42	22.72	24.23
	8H	15.25	15.52	16.37	16.63	18.17	21.52	21.79	22.65	22.91	24.45