

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938180

Luminaire Tested: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P938180  
REPORT IS A COMBINATION OF REPORTS P933592 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 26000.8 lumens  
Efficiency: N/A  
Efficacy: 115.3 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 225.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P938180  
CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P938180

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	44	42	37
2	87	79	73	68	79	73	67	63	61	56	53	49	46	44	39	37	35	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	27	23	21	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	23	24	21	18	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	18	16	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4664	4664	4664
5°	4558	5392	6269
10°	4136	7861	10393
15°	3516	10273	12549
20°	2864	11908	12789
25°	2390	12464	12529
30°	2016	12546	12506
35°	1784	12341	12829
40°	1555	12074	13163
45°	1409	11879	13215
50°	1294	11704	12996
55°	1240	11448	12420
60°	1271	10950	11511
65°	1324	10191	10261
70°	1415	8893	8668
75°	1573	7258	6765
80°	1731	5039	4559
85°	1572	2678	2333

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 13215 cd/sqm



TEST NUMBER: P938180

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.0	0.8
10°-20°	864.4	3.3
20°-30°	1512.0	5.8
30°-40°	1946.4	7.5
40°-50°	2174.1	8.4
50°-60°	2082.3	8.0
60°-70°	1650.2	6.3
70°-80°	970.4	3.7
80°-90°	278.0	1.1
90°-100°	1077.4	4.1
100°-110°	2832.5	10.9
110°-120°	2937.0	11.3
120°-130°	2355.8	9.1
130°-140°	1848.5	7.1
140°-150°	1418.8	5.5
150°-160°	1021.8	3.9
160°-170°	625.2	2.4
170°-180°	211.2	0.8
0°-30°	2571.5	9.9
0°-40°	4517.9	17.4
0°-60°	8774.2	33.7
0°-90°	11672.8	44.9
90°-120°	6846.8	26.3
90°-150°	12469.9	48.0
90°-180°	14328.0	55.1
0°-180°	26000.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1508	1508	1508	1508	1508	
5°	1469	1576	1774	2007	2080	136
15°	1100	2031	3423	4150	4281	306
25°	703	2303	4077	4257	4262	324
35°	475	2201	3840	4058	4218	297
45°	325	1755	3394	3888	4063	251
55°	233	1115	2880	3345	3437	212
65°	184	592	2138	2405	2439	183
75°	136	364	1173	1290	1294	142
85°	48	112	291	320	325	51
90°	15	42	113	56	56	16
95°	142	558	1856	957	651	158
105°	510	773	3131	4754	4435	541
115°	906	1101	2508	5003	5711	895
125°	1261	1414	2281	3855	4548	1119
135°	1503	1654	2210	3112	3529	1163
145°	1743	1854	2182	2655	2863	1092
155°	1970	2025	2182	2396	2465	905
165°	2126	2154	2182	2268	2296	600
175°	2210	2210	2197	2225	2225	210
180°	2210	2210	2210	2210	2210	



TEST NUMBER: P938180  
 CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8
2.5°	1507.8	1507.8	1517.5	1522.4	1532.0	1536.9	1546.6	1556.3	1585.4	1590.3	1599.9
5°	1469.0	1488.4	1551.4	1575.7	1643.6	1735.7	1774.5	1837.5	1968.4	2007.2	2031.4
7.5°	1410.8	1454.5	1609.7	1648.4	1818.1	2060.5	2162.3	2298.1	2506.6	2608.4	2690.8
10°	1318.8	1410.8	1687.2	1779.3	2055.6	2424.1	2613.2	2802.3	3117.4	3258.0	3311.4
12.5°	1217.0	1367.2	1769.6	1895.7	2293.2	2831.4	3059.2	3267.7	3626.5	3815.6	3844.6
15°	1100.5	1304.1	1847.2	2031.4	2545.4	3170.8	3422.8	3679.8	4014.3	4150.1	4184.0
17.5°	998.7	1255.7	1919.9	2113.8	2739.2	3476.2	3733.2	3946.4	4217.9	4310.1	4334.4
20°	872.7	1178.1	1968.4	2220.5	2942.9	3699.2	3946.4	4111.3	4295.6	4353.7	4363.4
22.5°	780.5	1095.7	1997.5	2259.2	3078.6	3835.0	4043.5	4174.3	4300.4	4319.8	4324.6
25°	703.0	1003.6	1992.6	2302.9	3195.0	3917.4	4077.4	4174.3	4247.1	4256.7	4256.7
27.5°	630.3	901.8	1973.2	2312.6	3282.2	3936.8	4062.9	4130.7	4164.7	4184.0	4184.0
30°	567.3	804.8	1924.7	2293.2	3321.0	3917.4	4019.2	4053.1	4087.1	4116.1	4130.7
32.5°	518.8	712.7	1852.0	2254.5	3325.9	3868.9	3941.7	3961.1	4009.5	4077.4	4101.6
35°	475.1	620.6	1769.6	2201.1	3296.9	3791.4	3839.8	3859.3	3956.2	4058.0	4091.9
37.5°	431.5	552.7	1662.9	2109.0	3253.2	3699.2	3733.2	3767.1	3917.4	4038.6	4077.4
40°	387.8	494.5	1536.9	2007.2	3185.3	3587.7	3616.8	3670.2	3868.9	4009.5	4048.2
42.5°	353.9	446.1	1401.2	1900.5	3098.0	3461.7	3505.3	3582.9	3810.7	3961.1	4004.7
45°	324.8	397.6	1255.7	1755.1	2986.5	3330.8	3393.8	3500.5	3742.8	3888.3	3927.1
47.5°	295.8	363.7	1105.4	1604.8	2865.3	3199.8	3282.2	3403.4	3650.8	3791.4	3825.3
50°	271.5	329.7	955.1	1444.8	2734.5	3059.2	3156.2	3282.2	3534.4	3665.3	3708.9
52.5°	252.1	300.6	814.5	1284.8	2584.1	2913.8	3025.3	3156.2	3393.8	3519.8	3548.9
55°	232.7	276.4	693.3	1115.1	2428.9	2758.6	2879.9	3006.0	3238.6	3345.3	3364.7
57.5°	223.0	257.0	591.5	955.1	2264.1	2584.1	2719.8	2836.3	3054.4	3136.8	3156.2
60°	208.5	242.4	513.9	819.4	2084.8	2419.3	2535.6	2652.0	2836.3	2904.1	2918.7
62.5°	194.0	232.7	455.7	688.5	1900.5	2225.3	2341.7	2448.3	2603.5	2652.0	2671.4
65°	184.2	223.0	412.1	591.5	1711.5	2021.7	2138.1	2230.2	2356.3	2404.7	2414.4
67.5°	174.6	213.3	378.2	509.1	1522.4	1818.1	1905.3	1992.6	2089.6	2138.1	2142.9
70°	160.0	203.6	349.1	450.9	1328.4	1585.4	1658.1	1750.2	1827.8	1852.0	1866.5
72.5°	150.3	189.1	329.7	407.2	1129.7	1362.4	1430.2	1483.6	1551.4	1575.7	1575.7
75°	135.7	169.7	310.3	363.7	926.0	1115.1	1173.3	1226.6	1279.9	1289.6	1275.1
77.5°	121.2	150.3	266.6	305.4	722.4	882.4	930.8	960.0	1003.6	1013.3	1018.1
80°	101.8	130.9	208.5	237.6	523.6	649.7	683.6	707.8	746.6	746.6	756.4
82.5°	77.5	101.8	150.3	169.7	353.9	446.1	475.1	489.6	513.9	513.9	513.9
85°	48.5	63.0	96.9	111.5	213.3	271.5	290.9	295.8	315.2	320.0	320.0
87.5°	24.3	33.9	63.0	67.9	111.5	140.6	140.6	150.3	150.3	145.4	140.6
90°	14.8	26.6	38.6	41.5	65.2	96.8	112.7	100.2	75.2	56.3	56.3
92.5°	59.3	160.2	261.1	286.3	402.5	557.4	634.9	556.4	399.5	281.8	270.6
95°	142.4	327.0	511.6	557.7	990.3	1567.3	1855.7	1655.9	1256.4	956.8	922.8
97.5°	246.2	409.0	571.9	612.6	1334.0	2295.9	2776.9	2650.6	2398.1	2208.7	2144.1
100°	326.3	474.1	621.7	658.7	1459.1	2526.5	3060.2	3069.5	3087.9	3101.7	3024.8
102.5°	394.6	532.4	670.1	704.6	1516.5	2599.0	3140.3	3301.1	3622.9	3864.2	3798.3
105°	510.3	627.0	743.7	772.9	1559.0	2607.2	3131.3	3492.0	4213.3	4754.2	4718.8
107.5°	629.0	737.7	846.5	873.7	1567.0	2491.3	2953.4	3456.4	4462.4	5217.0	5225.6
110°	709.1	807.3	905.5	930.1	1555.0	2388.4	2805.0	3367.4	4492.1	5335.7	5372.6



TEST NUMBER: P938180

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	787.7	881.3	974.9	998.3	1555.5	2298.6	2670.1	3245.7	4396.7	5260.0	5316.8
115°	906.3	992.6	1079.1	1100.6	1569.9	2195.5	2508.4	3062.9	4171.7	5003.4	5082.0
117.5°	1023.6	1102.0	1180.5	1200.1	1599.1	2131.1	2397.1	2897.6	3898.3	4648.8	4736.0
120°	1091.8	1165.6	1239.5	1257.9	1622.8	2109.4	2352.6	2809.9	3724.3	4410.1	4494.8
122.5°	1158.5	1233.0	1307.5	1326.1	1656.9	2098.0	2318.5	2730.2	3553.7	4171.2	4254.8
125°	1260.9	1328.8	1396.7	1413.7	1703.0	2088.6	2281.4	2631.1	3330.7	3855.2	3932.2
127.5°	1344.0	1412.5	1481.1	1498.2	1748.9	2083.1	2250.3	2550.5	3151.1	3601.6	3666.5
130°	1388.5	1462.3	1536.1	1554.5	1782.5	2086.5	2238.4	2505.7	3040.4	3441.4	3501.4
132.5°	1434.4	1508.2	1582.1	1600.6	1809.7	2088.6	2228.0	2467.3	2946.0	3305.0	3358.7
135°	1502.7	1569.9	1637.2	1654.0	1839.4	2086.7	2210.3	2410.7	2811.5	3112.2	3158.5
137.5°	1572.4	1639.0	1705.5	1722.2	1883.8	2099.5	2207.3	2376.7	2715.5	2969.7	3007.6
140°	1630.2	1691.5	1752.8	1768.2	1911.1	2101.6	2196.9	2343.2	2635.9	2855.4	2890.9
142.5°	1674.7	1731.4	1788.1	1802.3	1933.8	2109.2	2196.9	2325.4	2582.6	2775.4	2805.9
145°	1743.0	1792.4	1841.9	1854.2	1963.5	2109.2	2182.1	2287.2	2497.5	2655.2	2678.3
147.5°	1811.2	1859.3	1907.4	1919.5	2007.0	2123.7	2182.1	2264.8	2430.3	2554.3	2573.4
150°	1855.7	1899.2	1942.8	1953.6	2029.8	2131.3	2182.1	2252.0	2391.7	2496.5	2511.9
152.5°	1901.7	1934.6	1967.7	1975.9	2044.7	2136.2	2182.1	2241.8	2361.0	2450.5	2462.3
155°	1969.9	1994.3	2018.7	2024.8	2077.2	2147.1	2182.1	2229.5	2324.5	2395.6	2403.4
157.5°	2020.4	2044.1	2067.9	2073.8	2109.9	2158.0	2182.1	2218.9	2292.8	2348.2	2353.6
160°	2054.5	2072.9	2091.4	2096.0	2124.7	2163.0	2182.1	2213.7	2277.0	2324.5	2327.6
162.5°	2088.6	2102.4	2116.3	2119.7	2140.5	2168.2	2182.1	2208.8	2262.2	2302.2	2305.2
165°	2125.6	2138.1	2150.7	2153.8	2163.3	2175.8	2182.1	2201.2	2239.4	2268.0	2271.2
167.5°	2159.8	2165.7	2171.7	2173.1	2181.0	2191.6	2196.9	2209.4	2234.4	2253.2	2254.6
170°	2182.1	2188.0	2193.9	2195.4	2195.8	2196.5	2196.9	2209.4	2234.4	2253.2	2253.2
172.5°	2193.9	2195.3	2196.6	2196.9	2196.9	2196.9	2196.9	2206.8	2226.6	2241.4	2240.2
175°	2210.3	2210.3	2210.3	2210.3	2205.8	2199.8	2196.9	2203.2	2215.7	2225.1	2225.1
177.5°	2210.3	2210.3	2210.3	2210.3	2206.8	2202.1	2199.8	2204.8	2214.6	2222.1	2220.8
180°	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3



TEST NUMBER: P938180  
 CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	1507.8	1507.8
2.5°	1609.7	1599.9
5°	2070.2	2079.9
7.5°	2787.7	2782.9
10°	3466.5	3510.1
12.5°	3961.1	3970.7
15°	4261.6	4281.0
17.5°	4378.0	4382.8
20°	4382.8	4373.1
22.5°	4329.5	4319.8
25°	4266.5	4261.6
27.5°	4208.3	4213.2
30°	4184.0	4198.6
32.5°	4184.0	4208.3
35°	4193.7	4217.9
37.5°	4188.9	4217.9
40°	4169.5	4203.4
42.5°	4116.1	4140.4
45°	4033.7	4062.9
47.5°	3927.1	3946.4
50°	3791.4	3810.7
52.5°	3621.6	3626.5
55°	3418.0	3437.4
57.5°	3199.8	3204.7
60°	2957.4	2972.0
62.5°	2700.5	2700.5
65°	2428.9	2438.7
67.5°	2147.8	2172.1
70°	1861.8	1866.5
72.5°	1580.5	1580.5
75°	1289.6	1294.5
77.5°	1013.3	1013.3
80°	751.5	756.4
82.5°	518.8	528.5
85°	324.8	324.8
87.5°	150.3	135.7
90°	56.3	56.3
92.5°	225.8	181.0
95°	787.0	651.2
97.5°	1885.6	1627.2
100°	2716.9	2409.0
102.5°	3534.6	3270.9
105°	4577.0	4435.3
107.5°	5259.9	5294.1
110°	5520.3	5667.9





TEST NUMBER: P938180

CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	5543.5	5770.3
115°	5396.5	5711.0
117.5°	5084.8	5433.6
120°	4833.6	5172.5
122.5°	4589.1	4923.3
125°	4240.1	4548.0
127.5°	3926.3	4186.1
130°	3741.4	3981.4
132.5°	3573.6	3788.5
135°	3343.6	3528.9
137.5°	3159.2	3310.9
140°	3032.7	3174.4
142.5°	2927.8	3049.8
145°	2770.6	2862.9
147.5°	2649.9	2726.4
150°	2574.0	2636.0
152.5°	2509.1	2555.9
155°	2434.4	2465.3
157.5°	2375.4	2397.1
160°	2340.1	2352.6
162.5°	2317.0	2328.9
165°	2283.7	2296.3
167.5°	2259.8	2265.1
170°	2253.2	2253.2
172.5°	2235.6	2231.0
175°	2225.1	2225.1
177.5°	2215.5	2210.3
180°	2210.3	2210.3



TEST NUMBER: P938180  
 CATALOG NUMBER: SQ4-FB-125U-125D-B2750-1D-UNV-STD-W-12-4000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.88	6.73	6.87	7.74	9.07	19.07	19.92	20.06	20.93	22.27
	3H	6.58	7.34	7.58	8.36	9.72	20.91	21.68	21.91	22.69	24.05
	4H	6.88	7.60	7.89	8.62	9.99	21.56	22.28	22.57	23.31	24.67
	6H	7.13	7.80	8.15	8.82	10.20	21.99	22.66	23.02	23.69	25.07
	8H	7.19	7.83	8.23	8.87	10.25	22.12	22.75	23.15	23.80	25.17
	12H	7.21	7.82	8.25	8.85	10.26	22.19	22.79	23.22	23.83	25.23
4H	2H	13.10	13.82	14.12	14.84	16.21	19.34	20.06	20.36	21.09	22.45
	3H	14.66	15.27	15.69	16.32	17.70	21.39	22.00	22.42	23.05	24.43
	4H	14.76	15.31	15.80	16.35	17.76	22.16	22.72	23.20	23.76	25.16
	6H	14.77	15.25	15.82	16.31	17.71	22.70	23.18	23.75	24.25	25.65
	8H	14.74	15.19	15.79	16.25	17.66	22.87	23.31	23.92	24.37	25.79
	12H	14.70	15.11	15.77	16.18	17.60	22.96	23.37	24.03	24.44	25.86
8H	4H	16.20	16.65	17.25	17.71	19.13	22.22	22.67	23.27	23.72	25.14
	6H	16.45	16.82	17.52	17.92	19.33	22.85	23.22	23.93	24.32	25.73
	8H	16.46	16.79	17.55	17.87	19.30	23.07	23.40	24.16	24.48	25.91
	12H	16.43	16.72	17.52	17.80	19.27	23.22	23.51	24.31	24.59	26.06
12H	4H	16.35	16.75	17.42	17.83	19.25	22.17	22.58	23.24	23.65	25.07
	6H	16.71	17.03	17.79	18.12	19.55	22.83	23.16	23.92	24.24	25.68
	8H	16.78	17.06	17.86	18.14	19.61	23.07	23.35	24.15	24.43	25.90