

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934091

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934091
REPORT IS A COMBINATION OF REPORTS P933683 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6428.7 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934091
CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70	67
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59	56
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	47
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38	35
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33	31
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30	27
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26	24
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12103	12103	12103	12103
5°	12188	12217	12188	9606
10°	12103	12034	12103	8603
15°	11966	11773	11966	9831
20°	11712	11465	11712	9852
25°	11194	11014	11194	9643
30°	10528	10640	10528	9185
35°	9382	10167	9382	8681
40°	7813	9610	7813	8301
45°	6976	8958	6976	7862
50°	7405	8180	7405	7423
55°	6961	7343	6961	7169
60°	7167	6236	7167	6566
65°	6488	5155	6488	5763
70°	4481	4108	4481	4831
75°	3915	3037	3915	3637
80°	3131	2008	3131	2186
85°	1765	1064	1765	905

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 10699 cd/sqm



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.6	2.7
10°-20°	501.4	7.8
20°-30°	775.1	12.1
30°-40°	925.3	14.4
40°-50°	930.7	14.5
50°-60°	809.8	12.6
60°-70°	574.2	8.9
70°-80°	303.8	4.7
80°-90°	76.5	1.2
90°-100°	101.9	1.6
100°-110°	267.9	4.2
110°-120°	277.8	4.3
120°-130°	222.9	3.5
130°-140°	174.9	2.7
140°-150°	134.2	2.1
150°-160°	96.7	1.5
160°-170°	59.1	0.9
170°-180°	20.0	0.3
0°-30°	1453.1	22.6
0°-40°	2378.4	37.0
0°-60°	4118.9	64.1
0°-90°	5073.4	78.9
90°-120°	647.6	10.1
90°-150°	1179.6	18.3
90°-180°	1355.0	21.1
0°-180°	6428.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1956	1956	1956	1956	1956	
5°	1966	2027	1966	1594	1966	186
15°	1877	2008	1877	1677	1877	528
25°	1653	1873	1653	1640	1653	759
35°	1257	1671	1257	1427	1257	778
45°	811	1377	811	1209	811	649
55°	661	1016	661	992	661	607
65°	459	613	459	685	459	439
75°	174	291	174	348	174	183
85°	30	74	30	63	30	40
90°	1	5	1	5	1	2
95°	13	62	13	62	13	15
105°	48	420	48	420	48	51
115°	86	540	86	540	86	85
125°	119	430	119	430	119	106
135°	142	334	142	334	142	110
145°	165	271	165	271	165	103
155°	186	233	186	233	186	86
165°	201	217	201	217	201	57
175°	209	210	209	210	209	20
180°	209	209	209	209	209	



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4
2.5°	1973.1	1973.1	1984.2	1987.8	1987.8	1982.3	1976.7	1982.3	1998.9	2004.6	2002.7
5°	1965.6	1980.5	2000.8	2004.6	2008.2	2006.3	2002.7	2006.3	2024.8	2028.6	2030.4
7.5°	1950.8	1978.6	2004.6	2010.1	2015.6	2010.1	2008.2	2011.9	2030.4	2034.2	2034.2
10°	1932.4	1971.2	2000.8	2004.6	2010.1	2004.6	2004.6	2011.9	2030.4	2034.2	2035.9
12.5°	1906.4	1960.1	1987.8	1991.6	1998.9	1997.1	1995.2	2002.7	2021.2	2024.8	2024.8
15°	1876.8	1939.7	1965.6	1969.3	1982.3	1978.6	1978.6	1986.0	2006.3	2011.9	2010.1
17.5°	1836.1	1913.8	1943.5	1949.0	1958.2	1956.4	1958.2	1965.6	1984.2	1987.8	1989.7
20°	1789.8	1878.6	1913.8	1919.4	1928.6	1928.6	1928.6	1937.9	1956.4	1963.8	1963.8
22.5°	1726.9	1841.7	1878.6	1882.4	1893.5	1893.5	1897.1	1910.1	1926.7	1928.6	1928.6
25°	1652.8	1800.9	1832.4	1843.4	1854.6	1860.2	1865.7	1873.1	1878.6	1876.8	1878.6
27.5°	1575.1	1749.1	1789.8	1797.2	1812.1	1817.6	1824.9	1826.8	1828.7	1834.2	1830.5
30°	1488.1	1676.9	1738.0	1745.4	1769.5	1773.1	1765.7	1769.5	1778.7	1782.4	1786.1
32.5°	1390.0	1569.6	1684.3	1701.0	1723.1	1712.0	1710.2	1715.8	1730.6	1730.6	1734.3
35°	1256.8	1486.3	1634.3	1649.2	1665.8	1652.8	1660.3	1662.1	1671.3	1676.9	1675.0
37.5°	1110.5	1414.1	1582.5	1593.6	1606.6	1589.9	1601.0	1606.6	1614.0	1610.3	1610.3
40°	981.0	1301.2	1521.4	1528.9	1540.0	1527.0	1538.1	1541.8	1545.5	1541.8	1540.0
42.5°	884.7	1177.1	1456.7	1465.9	1458.5	1467.8	1471.4	1478.9	1473.3	1465.9	1465.9
45°	810.7	1143.9	1386.3	1397.5	1386.3	1401.1	1406.7	1406.7	1390.0	1386.3	1384.5
47.5°	786.6	1077.2	1316.0	1316.0	1310.4	1328.9	1338.1	1325.3	1308.5	1303.0	1303.0
50°	784.7	1003.2	1219.7	1212.3	1238.2	1260.4	1251.2	1238.2	1225.3	1205.0	1205.0
52.5°	712.5	912.5	1095.7	1123.5	1164.2	1177.1	1162.4	1149.4	1127.2	1117.9	1110.5
55°	660.8	818.1	982.8	1038.3	1080.9	1097.5	1069.8	1056.8	1023.6	1018.0	1014.3
57.5°	649.7	681.2	879.2	949.5	1001.3	999.5	982.8	958.8	931.0	925.4	923.6
60°	596.0	492.3	768.1	851.4	905.0	899.5	884.7	862.5	836.6	832.9	829.2
62.5°	540.4	357.3	642.2	736.6	812.6	810.7	797.7	764.4	745.9	736.6	729.3
65°	459.1	299.8	457.2	612.6	721.9	725.5	697.8	673.7	653.3	642.2	640.4
67.5°	349.8	244.3	309.1	510.8	634.8	631.2	596.0	584.9	559.0	553.4	542.3
70°	259.1	162.9	214.7	414.6	549.8	540.4	512.7	499.8	475.7	462.7	455.3
72.5°	214.7	131.4	157.3	322.0	462.7	451.6	427.6	412.7	392.4	381.3	373.9
75°	174.0	138.8	120.3	238.7	375.7	368.4	346.1	331.3	314.7	299.8	301.7
77.5°	127.7	129.5	96.2	175.9	297.9	286.9	273.9	255.4	248.0	233.2	233.2
80°	96.2	101.8	72.2	120.3	214.7	214.7	203.6	190.6	177.6	170.3	170.3
82.5°	64.8	64.8	53.7	75.8	146.3	140.7	133.3	129.5	122.2	118.4	118.4
85°	29.6	37.0	33.3	46.2	79.6	83.3	83.3	79.6	77.7	74.1	75.8
87.5°	9.2	16.6	20.4	25.9	40.7	42.6	44.5	44.5	44.5	46.2	46.2
90°	1.4	2.5	3.6	3.9	6.2	9.2	10.6	9.4	7.1	5.3	5.3
92.5°	5.6	15.1	24.7	27.1	38.1	52.8	60.1	52.6	37.7	26.6	25.6
95°	13.4	30.9	48.4	52.8	93.7	148.2	175.5	156.6	118.8	90.5	87.3
97.5°	23.3	38.7	54.1	57.9	126.2	217.2	262.6	250.7	226.9	208.9	202.9
100°	30.9	44.8	58.8	62.3	138.0	239.0	289.4	290.3	292.1	293.4	286.1
102.5°	37.4	50.4	63.4	66.7	143.5	245.8	297.0	312.2	342.7	365.6	359.3
105°	48.3	59.3	70.3	73.1	147.5	246.6	296.2	330.3	398.5	449.7	446.4
107.5°	59.5	69.8	80.0	82.7	148.2	235.6	279.4	327.0	422.2	493.5	494.4
110°	67.1	76.4	85.6	88.0	147.1	225.9	265.3	318.6	425.0	504.7	508.2



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	74.5	83.4	92.2	94.4	147.1	217.4	252.6	307.0	415.9	497.5	502.9
115°	85.7	94.0	102.1	104.1	148.5	207.6	237.2	289.7	394.6	473.3	480.7
117.5°	96.9	104.2	111.6	113.5	151.2	201.6	226.8	274.1	368.7	439.7	447.9
120°	103.3	110.3	117.2	119.0	153.5	199.6	222.6	265.8	352.3	417.2	425.3
122.5°	109.6	116.7	123.7	125.4	156.7	198.5	219.3	258.3	336.1	394.6	402.6
125°	119.3	125.7	132.2	133.7	161.1	197.6	215.8	248.9	315.1	364.7	372.0
127.5°	127.1	133.6	140.1	141.7	165.4	197.1	212.9	241.3	298.1	340.7	346.9
130°	131.3	138.3	145.2	147.0	168.6	197.4	211.7	237.0	287.6	325.5	331.2
132.5°	135.7	142.7	149.6	151.4	171.2	197.6	210.8	233.4	278.7	312.6	317.7
135°	142.2	148.5	154.9	156.4	174.0	197.4	209.1	228.1	266.0	294.4	298.8
137.5°	148.8	155.0	161.3	162.9	178.2	198.7	208.8	224.9	256.9	280.9	284.5
140°	154.2	160.0	165.8	167.3	180.8	198.8	207.8	221.6	249.4	270.1	273.5
142.5°	158.4	163.7	169.1	170.5	182.9	199.5	207.8	220.0	244.3	262.5	265.4
145°	164.9	169.5	174.2	175.4	185.8	199.5	206.4	216.3	236.2	251.2	253.3
147.5°	171.3	175.9	180.4	181.6	189.9	200.9	206.4	214.3	229.9	241.6	243.4
150°	175.5	179.6	183.8	184.8	192.0	201.7	206.4	213.0	226.2	236.1	237.6
152.5°	179.9	183.0	186.1	186.9	193.4	202.1	206.4	212.0	223.3	231.8	232.9
155°	186.3	188.7	191.0	191.6	196.5	203.1	206.4	210.9	219.9	226.6	227.3
157.5°	191.1	193.3	195.6	196.1	199.6	204.2	206.4	209.9	216.9	222.1	222.7
160°	194.4	196.1	197.8	198.3	201.0	204.6	206.4	209.4	215.4	219.9	220.1
162.5°	197.5	198.8	200.2	200.5	202.5	205.1	206.4	208.9	214.0	217.8	218.1
165°	201.1	202.2	203.4	203.7	204.6	205.9	206.4	208.2	211.8	214.5	214.8
167.5°	204.3	204.8	205.4	205.6	206.3	207.3	207.8	209.0	211.4	213.1	213.2
170°	206.4	207.0	207.5	207.6	207.7	207.8	207.8	209.0	211.4	213.1	213.1
172.5°	207.5	207.6	207.8	207.8	207.8	207.8	207.8	208.7	210.6	212.0	211.9
175°	209.1	209.1	209.1	209.1	208.7	208.1	207.8	208.4	209.6	210.5	210.5
177.5°	209.1	209.1	209.1	209.1	208.7	208.3	208.1	208.6	209.5	210.2	210.2
180°	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4
2.5°	2006.3	2000.8	2006.3	2002.7	2004.6	1998.9	1982.3	1976.7	1982.3	1987.8	1987.8
5°	2030.4	2026.7	2030.4	2030.4	2028.6	2024.8	2006.3	2002.7	2006.3	2008.2	2004.6
7.5°	2037.8	2032.3	2037.8	2034.2	2034.2	2030.4	2011.9	2008.2	2010.1	2015.6	2010.1
10°	2037.8	2032.3	2037.8	2035.9	2034.2	2030.4	2011.9	2004.6	2004.6	2010.1	2004.6
12.5°	2028.6	2024.8	2028.6	2024.8	2024.8	2021.2	2002.7	1995.2	1997.1	1998.9	1991.6
15°	2013.8	2008.2	2013.8	2010.1	2011.9	2006.3	1986.0	1978.6	1978.6	1982.3	1969.3
17.5°	1991.6	1984.2	1991.6	1989.7	1987.8	1984.2	1965.6	1958.2	1956.4	1958.2	1949.0
20°	1965.6	1960.1	1965.6	1963.8	1963.8	1956.4	1937.9	1928.6	1928.6	1928.6	1919.4
22.5°	1924.9	1919.4	1924.9	1928.6	1928.6	1926.7	1910.1	1897.1	1893.5	1893.5	1882.4
25°	1878.6	1873.1	1878.6	1878.6	1876.8	1878.6	1873.1	1865.7	1860.2	1854.6	1843.4
27.5°	1834.2	1830.5	1834.2	1830.5	1834.2	1828.7	1826.8	1824.9	1817.6	1812.1	1797.2
30°	1789.8	1786.1	1789.8	1786.1	1782.4	1778.7	1769.5	1765.7	1773.1	1769.5	1745.4
32.5°	1734.3	1730.6	1734.3	1734.3	1730.6	1730.6	1715.8	1710.2	1712.0	1723.1	1701.0
35°	1676.9	1671.3	1676.9	1675.0	1676.9	1671.3	1662.1	1660.3	1652.8	1665.8	1649.2
37.5°	1610.3	1604.7	1610.3	1610.3	1610.3	1614.0	1606.6	1601.0	1589.9	1606.6	1593.6
40°	1541.8	1534.4	1541.8	1540.0	1541.8	1545.5	1541.8	1538.1	1527.0	1540.0	1528.9
42.5°	1464.0	1462.2	1464.0	1465.9	1465.9	1473.3	1478.9	1471.4	1467.8	1458.5	1465.9
45°	1380.7	1377.1	1380.7	1384.5	1386.3	1390.0	1406.7	1406.7	1401.1	1386.3	1397.5
47.5°	1291.9	1282.7	1291.9	1303.0	1303.0	1308.5	1325.3	1338.1	1328.9	1310.4	1316.0
50°	1197.5	1199.3	1197.5	1205.0	1205.0	1225.3	1238.2	1251.2	1260.4	1238.2	1212.3
52.5°	1105.0	1103.1	1105.0	1110.5	1117.9	1127.2	1149.4	1162.4	1177.1	1164.2	1123.5
55°	1012.5	1016.1	1012.5	1014.3	1018.0	1023.6	1056.8	1069.8	1097.5	1080.9	1038.3
57.5°	919.9	914.3	919.9	923.6	925.4	931.0	958.8	982.8	999.5	1001.3	949.5
60°	812.6	805.1	812.6	829.2	832.9	836.6	862.5	884.7	899.5	905.0	851.4
62.5°	718.2	705.2	718.2	729.3	736.6	745.9	764.4	797.7	810.7	812.6	736.6
65°	618.2	612.6	618.2	640.4	642.2	653.3	673.7	697.8	725.5	721.9	612.6
67.5°	527.5	527.5	527.5	542.3	553.4	559.0	584.9	596.0	631.2	634.8	510.8
70°	444.2	442.3	444.2	455.3	462.7	475.7	499.8	512.7	540.4	549.8	414.6
72.5°	364.6	362.8	364.6	373.9	381.3	392.4	412.7	427.6	451.6	462.7	322.0
75°	294.3	290.6	294.3	301.7	299.8	314.7	331.3	346.1	368.4	375.7	238.7
77.5°	225.8	225.8	225.8	233.2	233.2	248.0	255.4	273.9	286.9	297.9	175.9
80°	168.4	166.6	168.4	170.3	170.3	177.6	190.6	203.6	214.7	214.7	120.3
82.5°	118.4	114.8	118.4	118.4	118.4	122.2	129.5	133.3	140.7	146.3	75.8
85°	74.1	74.1	74.1	75.8	74.1	77.7	79.6	83.3	83.3	79.6	46.2
87.5°	48.1	46.2	48.1	46.2	46.2	44.5	44.5	44.5	42.6	40.7	25.9
90°	5.3	5.3	5.3	5.3	5.3	7.1	9.4	10.6	9.2	6.2	3.9
92.5°	21.3	17.1	21.3	25.6	26.6	37.7	52.6	60.1	52.8	38.1	27.1
95°	74.4	61.6	74.4	87.3	90.5	118.8	156.6	175.5	148.2	93.7	52.8
97.5°	178.4	153.9	178.4	202.9	208.9	226.9	250.7	262.6	217.2	126.2	57.9
100°	257.0	227.9	257.0	286.1	293.4	292.1	290.3	289.4	239.0	138.0	62.3
102.5°	334.4	309.4	334.4	359.3	365.6	342.7	312.2	297.0	245.8	143.5	66.7
105°	433.0	419.6	433.0	446.4	449.7	398.5	330.3	296.2	246.6	147.5	73.1
107.5°	497.5	500.8	497.5	494.4	493.5	422.2	327.0	279.4	235.6	148.2	82.7
110°	522.2	536.2	522.2	508.2	504.7	425.0	318.6	265.3	225.9	147.1	88.0



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	524.3	545.8	524.3	502.9	497.5	415.9	307.0	252.6	217.4	147.1	94.4
115°	510.4	540.2	510.4	480.7	473.3	394.6	289.7	237.2	207.6	148.5	104.1
117.5°	481.0	514.0	481.0	447.9	439.7	368.7	274.1	226.8	201.6	151.2	113.5
120°	457.3	489.3	457.3	425.3	417.2	352.3	265.8	222.6	199.6	153.5	119.0
122.5°	434.1	465.7	434.1	402.6	394.6	336.1	258.3	219.3	198.5	156.7	125.4
125°	401.1	430.2	401.1	372.0	364.7	315.1	248.9	215.8	197.6	161.1	133.7
127.5°	371.5	396.0	371.5	346.9	340.7	298.1	241.3	212.9	197.1	165.4	141.7
130°	353.9	376.6	353.9	331.2	325.5	287.6	237.0	211.7	197.4	168.6	147.0
132.5°	338.0	358.4	338.0	317.7	312.6	278.7	233.4	210.8	197.6	171.2	151.4
135°	316.3	333.8	316.3	298.8	294.4	266.0	228.1	209.1	197.4	174.0	156.4
137.5°	298.9	313.2	298.9	284.5	280.9	256.9	224.9	208.8	198.7	178.2	162.9
140°	286.8	300.3	286.8	273.5	270.1	249.4	221.6	207.8	198.8	180.8	167.3
142.5°	276.9	288.5	276.9	265.4	262.5	244.3	220.0	207.8	199.5	182.9	170.5
145°	262.1	270.9	262.1	253.3	251.2	236.2	216.3	206.4	199.5	185.8	175.4
147.5°	250.7	257.9	250.7	243.4	241.6	229.9	214.3	206.4	200.9	189.9	181.6
150°	243.5	249.4	243.5	237.6	236.1	226.2	213.0	206.4	201.7	192.0	184.8
152.5°	237.3	241.8	237.3	232.9	231.8	223.3	212.0	206.4	202.1	193.4	186.9
155°	230.2	233.2	230.2	227.3	226.6	219.9	210.9	206.4	203.1	196.5	191.6
157.5°	224.7	226.8	224.7	222.7	222.1	216.9	209.9	206.4	204.2	199.6	196.1
160°	221.4	222.6	221.4	220.1	219.9	215.4	209.4	206.4	204.6	201.0	198.3
162.5°	219.2	220.3	219.2	218.1	217.8	214.0	208.9	206.4	205.1	202.5	200.5
165°	216.0	217.2	216.0	214.8	214.5	211.8	208.2	206.4	205.9	204.6	203.7
167.5°	213.8	214.3	213.8	213.2	213.1	211.4	209.0	207.8	207.3	206.3	205.6
170°	213.1	213.1	213.1	213.1	213.1	211.4	209.0	207.8	207.8	207.7	207.6
172.5°	211.5	211.1	211.5	211.9	212.0	210.6	208.7	207.8	207.8	207.8	207.8
175°	210.5	210.5	210.5	210.5	210.5	209.6	208.4	207.8	208.1	208.7	209.1
177.5°	209.6	209.1	209.6	210.2	210.2	209.5	208.6	208.1	208.3	208.7	209.1
180°	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4
2.5°	1984.2	1973.1	1973.1	1954.5	1947.1	1941.6	1932.4	1904.5	1897.1	1889.8	1900.9
5°	2000.8	1980.5	1965.6	1932.4	1904.5	1893.5	1858.3	1791.7	1747.2	1713.9	1695.4
7.5°	2004.6	1978.6	1950.8	1899.0	1832.4	1802.7	1695.4	1573.2	1540.0	1510.3	1491.8
10°	2000.8	1971.2	1932.4	1854.6	1697.3	1645.4	1538.1	1458.5	1438.2	1432.6	1438.2
12.5°	1987.8	1960.1	1906.4	1776.8	1556.6	1521.4	1458.5	1412.2	1408.6	1417.8	1467.8
15°	1965.6	1939.7	1876.8	1673.2	1478.9	1452.9	1408.6	1391.8	1412.2	1477.0	1626.9
17.5°	1943.5	1913.8	1836.1	1571.4	1419.6	1401.1	1369.6	1403.0	1517.8	1604.7	1654.7
20°	1913.8	1878.6	1789.8	1497.4	1377.1	1360.4	1345.6	1495.5	1582.5	1614.0	1641.7
22.5°	1878.6	1841.7	1726.9	1445.6	1332.6	1319.6	1328.9	1547.4	1582.5	1604.7	1628.8
25°	1832.4	1800.9	1652.8	1404.8	1297.5	1282.7	1317.9	1541.8	1562.1	1567.7	1615.8
27.5°	1789.8	1749.1	1575.1	1367.8	1254.9	1249.3	1327.1	1517.8	1532.5	1538.1	1589.9
30°	1738.0	1676.9	1488.1	1328.9	1210.5	1208.6	1328.9	1488.1	1484.4	1499.3	1551.0
32.5°	1684.3	1569.6	1390.0	1280.8	1167.9	1166.1	1316.0	1443.7	1439.9	1460.3	1499.3
35°	1634.3	1486.3	1256.8	1225.3	1114.3	1116.0	1284.5	1391.8	1393.7	1412.2	1436.3
37.5°	1582.5	1414.1	1110.5	1164.2	1062.4	1062.4	1241.9	1343.7	1340.0	1345.6	1378.9
40°	1521.4	1301.2	981.0	1084.7	1014.3	1008.7	1190.1	1291.9	1278.9	1277.2	1323.4
42.5°	1456.7	1177.1	884.7	979.1	958.8	951.4	1127.2	1229.0	1205.0	1210.5	1269.7
45°	1386.3	1143.9	810.7	827.3	901.4	895.8	1058.7	1156.8	1140.1	1155.0	1216.1
47.5°	1316.0	1077.2	786.6	686.7	840.3	838.5	982.8	1086.4	1077.2	1092.0	1156.8
50°	1219.7	1003.2	784.7	588.6	771.9	779.2	892.2	1018.0	1018.0	1030.9	1099.4
52.5°	1095.7	912.5	712.5	533.0	692.2	714.4	812.6	958.8	962.5	975.4	1036.5
55°	982.8	818.1	660.8	490.4	597.9	646.0	734.8	897.7	905.0	918.0	973.6
57.5°	879.2	681.2	649.7	440.5	510.8	557.1	666.3	838.5	842.2	853.3	906.9
60°	768.1	492.3	596.0	386.9	435.0	470.1	603.4	768.1	781.1	788.5	834.7
62.5°	642.2	357.3	540.4	349.8	398.0	405.4	551.5	701.5	718.2	723.7	751.5
65°	457.2	299.8	459.1	318.3	359.0	360.9	496.0	633.0	647.8	657.1	677.4
67.5°	309.1	244.3	349.8	288.7	329.4	331.3	442.3	553.4	573.8	581.1	594.1
70°	214.7	162.9	259.1	257.3	296.2	299.8	385.0	481.2	499.8	505.3	512.7
72.5°	157.3	131.4	214.7	231.4	261.0	264.7	325.8	399.8	418.3	423.8	427.6
75°	120.3	138.8	174.0	201.7	222.1	224.0	266.6	325.8	338.7	342.4	344.3
77.5°	96.2	129.5	127.7	162.9	181.4	177.6	209.1	251.7	262.8	262.8	262.8
80°	72.2	101.8	96.2	116.6	133.3	129.5	149.9	179.5	183.3	186.9	185.1
82.5°	53.7	64.8	64.8	74.1	88.8	85.2	99.9	116.6	116.6	116.6	120.3
85°	33.3	37.0	29.6	38.9	50.0	48.1	55.6	63.0	64.8	64.8	61.1
87.5°	20.4	16.6	9.2	14.9	22.2	22.2	25.9	27.7	25.9	25.9	25.9
90°	3.6	2.5	1.4	2.5	3.6	3.9	6.2	9.2	10.6	9.4	7.1
92.5°	24.7	15.1	5.6	15.1	24.7	27.1	38.1	52.8	60.1	52.6	37.7
95°	48.4	30.9	13.4	30.9	48.4	52.8	93.7	148.2	175.5	156.6	118.8
97.5°	54.1	38.7	23.3	38.7	54.1	57.9	126.2	217.2	262.6	250.7	226.9
100°	58.8	44.8	30.9	44.8	58.8	62.3	138.0	239.0	289.4	290.3	292.1
102.5°	63.4	50.4	37.4	50.4	63.4	66.7	143.5	245.8	297.0	312.2	342.7
105°	70.3	59.3	48.3	59.3	70.3	73.1	147.5	246.6	296.2	330.3	398.5
107.5°	80.0	69.8	59.5	69.8	80.0	82.7	148.2	235.6	279.4	327.0	422.2
110°	85.6	76.4	67.1	76.4	85.6	88.0	147.1	225.9	265.3	318.6	425.0



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	92.2	83.4	74.5	83.4	92.2	94.4	147.1	217.4	252.6	307.0	415.9
115°	102.1	94.0	85.7	94.0	102.1	104.1	148.5	207.6	237.2	289.7	394.6
117.5°	111.6	104.2	96.9	104.2	111.6	113.5	151.2	201.6	226.8	274.1	368.7
120°	117.2	110.3	103.3	110.3	117.2	119.0	153.5	199.6	222.6	265.8	352.3
122.5°	123.7	116.7	109.6	116.7	123.7	125.4	156.7	198.5	219.3	258.3	336.1
125°	132.2	125.7	119.3	125.7	132.2	133.7	161.1	197.6	215.8	248.9	315.1
127.5°	140.1	133.6	127.1	133.6	140.1	141.7	165.4	197.1	212.9	241.3	298.1
130°	145.2	138.3	131.3	138.3	145.2	147.0	168.6	197.4	211.7	237.0	287.6
132.5°	149.6	142.7	135.7	142.7	149.6	151.4	171.2	197.6	210.8	233.4	278.7
135°	154.9	148.5	142.2	148.5	154.9	156.4	174.0	197.4	209.1	228.1	266.0
137.5°	161.3	155.0	148.8	155.0	161.3	162.9	178.2	198.7	208.8	224.9	256.9
140°	165.8	160.0	154.2	160.0	165.8	167.3	180.8	198.8	207.8	221.6	249.4
142.5°	169.1	163.7	158.4	163.7	169.1	170.5	182.9	199.5	207.8	220.0	244.3
145°	174.2	169.5	164.9	169.5	174.2	175.4	185.8	199.5	206.4	216.3	236.2
147.5°	180.4	175.9	171.3	175.9	180.4	181.6	189.9	200.9	206.4	214.3	229.9
150°	183.8	179.6	175.5	179.6	183.8	184.8	192.0	201.7	206.4	213.0	226.2
152.5°	186.1	183.0	179.9	183.0	186.1	186.9	193.4	202.1	206.4	212.0	223.3
155°	191.0	188.7	186.3	188.7	191.0	191.6	196.5	203.1	206.4	210.9	219.9
157.5°	195.6	193.3	191.1	193.3	195.6	196.1	199.6	204.2	206.4	209.9	216.9
160°	197.8	196.1	194.4	196.1	197.8	198.3	201.0	204.6	206.4	209.4	215.4
162.5°	200.2	198.8	197.5	198.8	200.2	200.5	202.5	205.1	206.4	208.9	214.0
165°	203.4	202.2	201.1	202.2	203.4	203.7	204.6	205.9	206.4	208.2	211.8
167.5°	205.4	204.8	204.3	204.8	205.4	205.6	206.3	207.3	207.8	209.0	211.4
170°	207.5	207.0	206.4	207.0	207.5	207.6	207.7	207.8	207.8	209.0	211.4
172.5°	207.8	207.6	207.5	207.6	207.8	207.8	207.8	207.8	207.8	208.7	210.6
175°	209.1	209.1	209.1	209.1	209.1	209.1	208.7	208.1	207.8	208.4	209.6
177.5°	209.1	209.1	209.1	209.1	209.1	209.1	208.7	208.3	208.1	208.6	209.5
180°	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4	1956.4
2.5°	1887.9	1882.4	1889.8	1869.4	1889.8	1882.4	1887.9	1900.9	1889.8	1897.1	1904.5
5°	1656.5	1647.3	1617.7	1593.6	1617.7	1647.3	1656.5	1695.4	1713.9	1747.2	1791.7
7.5°	1480.7	1473.3	1465.9	1451.1	1465.9	1473.3	1480.7	1491.8	1510.3	1540.0	1573.2
10°	1441.8	1443.7	1454.8	1452.9	1454.8	1443.7	1441.8	1438.2	1432.6	1438.2	1458.5
12.5°	1541.8	1558.5	1619.6	1615.8	1619.6	1558.5	1541.8	1467.8	1417.8	1408.6	1412.2
15°	1656.5	1662.1	1675.0	1676.9	1675.0	1662.1	1656.5	1626.9	1477.0	1412.2	1391.8
17.5°	1667.7	1669.5	1678.8	1678.8	1678.8	1669.5	1667.7	1654.7	1604.7	1517.8	1403.0
20°	1658.4	1662.1	1680.6	1684.3	1680.6	1662.1	1658.4	1641.7	1614.0	1582.5	1495.5
22.5°	1654.7	1662.1	1676.9	1675.0	1676.9	1662.1	1654.7	1628.8	1604.7	1582.5	1547.4
25°	1636.2	1636.2	1638.0	1639.9	1638.0	1636.2	1636.2	1615.8	1567.7	1562.1	1541.8
27.5°	1597.3	1601.0	1612.1	1610.3	1612.1	1601.0	1597.3	1589.9	1538.1	1532.5	1517.8
30°	1562.1	1558.5	1549.2	1541.8	1549.2	1558.5	1562.1	1551.0	1499.3	1484.4	1488.1
32.5°	1502.9	1493.7	1484.4	1478.9	1484.4	1493.7	1502.9	1499.3	1460.3	1439.9	1443.7
35°	1432.6	1434.4	1432.6	1427.1	1432.6	1434.4	1432.6	1436.3	1412.2	1393.7	1391.8
37.5°	1382.6	1386.3	1384.5	1377.1	1384.5	1386.3	1382.6	1378.9	1345.6	1340.0	1343.7
40°	1330.8	1332.6	1330.8	1325.3	1330.8	1332.6	1330.8	1323.4	1277.2	1278.9	1291.9
42.5°	1280.8	1278.9	1273.4	1269.7	1273.4	1278.9	1280.8	1269.7	1210.5	1205.0	1229.0
45°	1223.4	1225.3	1214.2	1208.6	1214.2	1225.3	1223.4	1216.1	1155.0	1140.1	1156.8
47.5°	1166.1	1166.1	1156.8	1151.2	1156.8	1166.1	1166.1	1156.8	1092.0	1077.2	1086.4
50°	1105.0	1103.1	1090.2	1088.3	1090.2	1103.1	1105.0	1099.4	1030.9	1018.0	1018.0
52.5°	1034.7	1034.7	1036.5	1040.2	1036.5	1034.7	1034.7	1036.5	975.4	962.5	958.8
55°	973.6	975.4	988.4	992.1	988.4	975.4	973.6	973.6	918.0	905.0	897.7
57.5°	910.6	910.6	919.9	919.9	919.9	910.6	910.6	906.9	853.3	842.2	838.5
60°	838.5	842.2	849.6	847.7	849.6	842.2	838.5	834.7	788.5	781.1	768.1
62.5°	762.5	766.3	768.1	764.4	768.1	766.3	762.5	751.5	723.7	718.2	701.5
65°	682.9	686.7	688.5	684.8	688.5	686.7	682.9	677.4	657.1	647.8	633.0
67.5°	601.5	599.7	597.9	605.2	597.9	599.7	601.5	594.1	581.1	573.8	553.4
70°	518.3	518.3	516.4	520.1	516.4	518.3	518.3	512.7	505.3	499.8	481.2
72.5°	429.4	427.6	435.0	429.4	435.0	427.6	429.4	427.6	423.8	418.3	399.8
75°	342.4	346.1	342.4	348.0	342.4	346.1	342.4	344.3	342.4	338.7	325.8
77.5°	261.0	264.7	261.0	261.0	261.0	264.7	261.0	262.8	262.8	262.8	251.7
80°	185.1	183.3	183.3	181.4	183.3	183.3	185.1	185.1	186.9	183.3	179.5
82.5°	118.4	116.6	116.6	120.3	116.6	116.6	118.4	120.3	116.6	116.6	116.6
85°	64.8	66.6	63.0	63.0	63.0	66.6	64.8	61.1	64.8	64.8	63.0
87.5°	24.1	22.2	22.2	22.2	22.2	22.2	24.1	25.9	25.9	25.9	27.7
90°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	7.1	9.4	10.6	9.2
92.5°	26.6	25.6	21.3	17.1	21.3	25.6	26.6	37.7	52.6	60.1	52.8
95°	90.5	87.3	74.4	61.6	74.4	87.3	90.5	118.8	156.6	175.5	148.2
97.5°	208.9	202.9	178.4	153.9	178.4	202.9	208.9	226.9	250.7	262.6	217.2
100°	293.4	286.1	257.0	227.9	257.0	286.1	293.4	292.1	290.3	289.4	239.0
102.5°	365.6	359.3	334.4	309.4	334.4	359.3	365.6	342.7	312.2	297.0	245.8
105°	449.7	446.4	433.0	419.6	433.0	446.4	449.7	398.5	330.3	296.2	246.6
107.5°	493.5	494.4	497.5	500.8	497.5	494.4	493.5	422.2	327.0	279.4	235.6
110°	504.7	508.2	522.2	536.2	522.2	508.2	504.7	425.0	318.6	265.3	225.9



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	497.5	502.9	524.3	545.8	524.3	502.9	497.5	415.9	307.0	252.6	217.4
115°	473.3	480.7	510.4	540.2	510.4	480.7	473.3	394.6	289.7	237.2	207.6
117.5°	439.7	447.9	481.0	514.0	481.0	447.9	439.7	368.7	274.1	226.8	201.6
120°	417.2	425.3	457.3	489.3	457.3	425.3	417.2	352.3	265.8	222.6	199.6
122.5°	394.6	402.6	434.1	465.7	434.1	402.6	394.6	336.1	258.3	219.3	198.5
125°	364.7	372.0	401.1	430.2	401.1	372.0	364.7	315.1	248.9	215.8	197.6
127.5°	340.7	346.9	371.5	396.0	371.5	346.9	340.7	298.1	241.3	212.9	197.1
130°	325.5	331.2	353.9	376.6	353.9	331.2	325.5	287.6	237.0	211.7	197.4
132.5°	312.6	317.7	338.0	358.4	338.0	317.7	312.6	278.7	233.4	210.8	197.6
135°	294.4	298.8	316.3	333.8	316.3	298.8	294.4	266.0	228.1	209.1	197.4
137.5°	280.9	284.5	298.9	313.2	298.9	284.5	280.9	256.9	224.9	208.8	198.7
140°	270.1	273.5	286.8	300.3	286.8	273.5	270.1	249.4	221.6	207.8	198.8
142.5°	262.5	265.4	276.9	288.5	276.9	265.4	262.5	244.3	220.0	207.8	199.5
145°	251.2	253.3	262.1	270.9	262.1	253.3	251.2	236.2	216.3	206.4	199.5
147.5°	241.6	243.4	250.7	257.9	250.7	243.4	241.6	229.9	214.3	206.4	200.9
150°	236.1	237.6	243.5	249.4	243.5	237.6	236.1	226.2	213.0	206.4	201.7
152.5°	231.8	232.9	237.3	241.8	237.3	232.9	231.8	223.3	212.0	206.4	202.1
155°	226.6	227.3	230.2	233.2	230.2	227.3	226.6	219.9	210.9	206.4	203.1
157.5°	222.1	222.7	224.7	226.8	224.7	222.7	222.1	216.9	209.9	206.4	204.2
160°	219.9	220.1	221.4	222.6	221.4	220.1	219.9	215.4	209.4	206.4	204.6
162.5°	217.8	218.1	219.2	220.3	219.2	218.1	217.8	214.0	208.9	206.4	205.1
165°	214.5	214.8	216.0	217.2	216.0	214.8	214.5	211.8	208.2	206.4	205.9
167.5°	213.1	213.2	213.8	214.3	213.8	213.2	213.1	211.4	209.0	207.8	207.3
170°	213.1	213.1	213.1	213.1	213.1	213.1	213.1	211.4	209.0	207.8	207.8
172.5°	212.0	211.9	211.5	211.1	211.5	211.9	212.0	210.6	208.7	207.8	207.8
175°	210.5	210.5	210.5	210.5	210.5	210.5	210.5	209.6	208.4	207.8	208.1
177.5°	210.2	210.2	209.6	209.1	209.6	210.2	210.2	209.5	208.6	208.1	208.3
180°	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1956.4	1956.4	1956.4	1956.4	1956.4
2.5°	1932.4	1941.6	1947.1	1954.5	1973.1
5°	1858.3	1893.5	1904.5	1932.4	1965.6
7.5°	1695.4	1802.7	1832.4	1899.0	1950.8
10°	1538.1	1645.4	1697.3	1854.6	1932.4
12.5°	1458.5	1521.4	1556.6	1776.8	1906.4
15°	1408.6	1452.9	1478.9	1673.2	1876.8
17.5°	1369.6	1401.1	1419.6	1571.4	1836.1
20°	1345.6	1360.4	1377.1	1497.4	1789.8
22.5°	1328.9	1319.6	1332.6	1445.6	1726.9
25°	1317.9	1282.7	1297.5	1404.8	1652.8
27.5°	1327.1	1249.3	1254.9	1367.8	1575.1
30°	1328.9	1208.6	1210.5	1328.9	1488.1
32.5°	1316.0	1166.1	1167.9	1280.8	1390.0
35°	1284.5	1116.0	1114.3	1225.3	1256.8
37.5°	1241.9	1062.4	1062.4	1164.2	1110.5
40°	1190.1	1008.7	1014.3	1084.7	981.0
42.5°	1127.2	951.4	958.8	979.1	884.7
45°	1058.7	895.8	901.4	827.3	810.7
47.5°	982.8	838.5	840.3	686.7	786.6
50°	892.2	779.2	771.9	588.6	784.7
52.5°	812.6	714.4	692.2	533.0	712.5
55°	734.8	646.0	597.9	490.4	660.8
57.5°	666.3	557.1	510.8	440.5	649.7
60°	603.4	470.1	435.0	386.9	596.0
62.5°	551.5	405.4	398.0	349.8	540.4
65°	496.0	360.9	359.0	318.3	459.1
67.5°	442.3	331.3	329.4	288.7	349.8
70°	385.0	299.8	296.2	257.3	259.1
72.5°	325.8	264.7	261.0	231.4	214.7
75°	266.6	224.0	222.1	201.7	174.0
77.5°	209.1	177.6	181.4	162.9	127.7
80°	149.9	129.5	133.3	116.6	96.2
82.5°	99.9	85.2	88.8	74.1	64.8
85°	55.6	48.1	50.0	38.9	29.6
87.5°	25.9	22.2	22.2	14.9	9.2
90°	6.2	3.9	3.6	2.5	1.4
92.5°	38.1	27.1	24.7	15.1	5.6
95°	93.7	52.8	48.4	30.9	13.4
97.5°	126.2	57.9	54.1	38.7	23.3
100°	138.0	62.3	58.8	44.8	30.9
102.5°	143.5	66.7	63.4	50.4	37.4
105°	147.5	73.1	70.3	59.3	48.3
107.5°	148.2	82.7	80.0	69.8	59.5
110°	147.1	88.0	85.6	76.4	67.1



TEST NUMBER: P934091

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	147.1	94.4	92.2	83.4	74.5
115°	148.5	104.1	102.1	94.0	85.7
117.5°	151.2	113.5	111.6	104.2	96.9
120°	153.5	119.0	117.2	110.3	103.3
122.5°	156.7	125.4	123.7	116.7	109.6
125°	161.1	133.7	132.2	125.7	119.3
127.5°	165.4	141.7	140.1	133.6	127.1
130°	168.6	147.0	145.2	138.3	131.3
132.5°	171.2	151.4	149.6	142.7	135.7
135°	174.0	156.4	154.9	148.5	142.2
137.5°	178.2	162.9	161.3	155.0	148.8
140°	180.8	167.3	165.8	160.0	154.2
142.5°	182.9	170.5	169.1	163.7	158.4
145°	185.8	175.4	174.2	169.5	164.9
147.5°	189.9	181.6	180.4	175.9	171.3
150°	192.0	184.8	183.8	179.6	175.5
152.5°	193.4	186.9	186.1	183.0	179.9
155°	196.5	191.6	191.0	188.7	186.3
157.5°	199.6	196.1	195.6	193.3	191.1
160°	201.0	198.3	197.8	196.1	194.4
162.5°	202.5	200.5	200.2	198.8	197.5
165°	204.6	203.7	203.4	202.2	201.1
167.5°	206.3	205.6	205.4	204.8	204.3
170°	207.7	207.6	207.5	207.0	206.4
172.5°	207.8	207.8	207.8	207.6	207.5
175°	208.7	209.1	209.1	209.1	209.1
177.5°	208.7	209.1	209.1	209.1	209.1
180°	209.1	209.1	209.1	209.1	209.1



TEST NUMBER: P934091
 CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.80	17.00	16.46	17.68	18.46	18.62	19.82	19.29	20.50	21.29
	3H	16.30	17.38	16.98	18.07	18.89	19.99	21.07	20.67	21.76	22.58
	4H	16.51	17.52	17.20	18.22	19.06	20.45	21.47	21.15	22.17	23.00
	6H	16.64	17.58	17.35	18.29	19.14	20.75	21.69	21.46	22.40	23.25
	8H	16.66	17.55	17.37	18.28	19.13	20.84	21.73	21.55	22.46	23.31
	12H	16.64	17.49	17.36	18.21	19.09	20.88	21.74	21.61	22.46	23.34
4H	2H	16.87	17.89	17.57	18.59	19.42	19.07	20.09	19.77	20.79	21.62
	3H	17.93	18.78	18.64	19.51	20.37	20.61	21.46	21.32	22.19	23.05
	4H	18.22	18.99	18.95	19.73	20.61	21.15	21.92	21.88	22.66	23.54
	6H	18.36	19.03	19.11	19.79	20.69	21.53	22.20	22.28	22.96	23.85
	8H	18.38	19.00	19.13	19.76	20.66	21.65	22.27	22.40	23.03	23.93
	12H	18.36	18.92	19.13	19.70	20.61	21.72	22.28	22.49	23.06	23.97
8H	4H	18.70	19.32	19.45	20.08	20.99	21.30	21.92	22.05	22.68	23.59
	6H	18.97	19.49	19.75	20.29	21.20	21.75	22.27	22.53	23.07	23.97
	8H	19.02	19.48	19.81	20.28	21.20	21.90	22.36	22.70	23.17	24.09
	12H	19.02	19.42	19.81	20.22	21.20	22.02	22.42	22.81	23.21	24.20
12H	4H	18.72	19.28	19.49	20.06	20.97	21.28	21.84	22.05	22.63	23.53
	6H	19.04	19.50	19.83	20.30	21.22	21.75	22.21	22.54	23.01	23.93
	8H	19.12	19.52	19.91	20.32	21.30	21.93	22.33	22.72	23.12	24.10