

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934991

Luminaire Tested: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934991
REPORT IS A COMBINATION OF REPORTS P933719 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10694.3 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 93
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934991
CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	51
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	45	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15501	15501	15501	15501
5°	15611	15647	15611	12304
10°	15501	15414	15501	11019
15°	15326	15079	15326	12591
20°	15000	14684	15000	12618
25°	14338	14107	14338	12351
30°	13484	13628	13484	11764
35°	12016	13022	12016	11118
40°	10006	12308	10006	10631
45°	8935	11474	8935	10070
50°	9486	10478	9486	9508
55°	8915	9405	8915	9182
60°	9180	7988	9180	8411
65°	8310	6603	8310	7381
70°	5740	5262	5740	6187
75°	5016	3890	5016	4658
80°	4013	2571	4013	2800
85°	2260	1362	2260	1158

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 13702 cd/sqm



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.2	2.1
10°-20°	642.2	6.0
20°-30°	992.7	9.3
30°-40°	1185.1	11.1
40°-50°	1192.1	11.1
50°-60°	1037.2	9.7
60°-70°	735.4	6.9
70°-80°	389.1	3.6
80°-90°	99.4	0.9
90°-100°	315.4	2.9
100°-110°	829.3	7.8
110°-120°	859.9	8.0
120°-130°	689.7	6.4
130°-140°	541.2	5.1
140°-150°	415.4	3.9
150°-160°	299.2	2.8
160°-170°	183.0	1.7
170°-180°	61.8	0.6
0°-30°	1861.1	17.4
0°-40°	3046.2	28.5
0°-60°	5275.5	49.3
0°-90°	6499.4	60.8
90°-120°	2004.6	18.7
90°-150°	3650.9	34.1
90°-180°	4195.0	39.2
0°-180°	10694.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2506	2506	2506	2506	2506	
5°	2518	2596	2518	2041	2518	239
15°	2404	2572	2404	2148	2404	676
25°	2117	2399	2117	2100	2117	972
35°	1610	2141	1610	1828	1610	996
45°	1038	1764	1038	1548	1038	832
55°	846	1301	846	1271	846	778
65°	588	785	588	877	588	562
75°	223	372	223	446	223	234
85°	38	95	38	81	38	51
90°	4	16	4	16	4	5
95°	42	191	42	191	42	46
105°	149	1298	149	1298	149	158
115°	265	1672	265	1672	265	262
125°	369	1332	369	1332	369	328
135°	440	1033	440	1033	440	340
145°	510	838	510	838	510	320
155°	577	722	577	722	577	265
165°	622	672	622	672	622	176
175°	647	652	647	652	647	61
180°	647	647	647	647	647	



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7
2.5°	2527.0	2527.0	2541.3	2546.0	2546.0	2538.9	2531.8	2538.9	2560.3	2567.4	2565.0
5°	2517.6	2536.6	2562.6	2567.4	2572.1	2569.7	2565.0	2569.7	2593.4	2598.2	2600.5
7.5°	2498.6	2534.1	2567.4	2574.5	2581.6	2574.5	2572.1	2576.8	2600.5	2605.3	2605.3
10°	2474.9	2524.7	2562.6	2567.4	2574.5	2567.4	2567.4	2576.8	2600.5	2605.3	2607.6
12.5°	2441.8	2510.5	2546.0	2550.8	2560.3	2557.9	2555.5	2565.0	2588.7	2593.4	2593.4
15°	2403.8	2484.3	2517.6	2522.4	2538.9	2534.1	2534.1	2543.7	2569.7	2576.8	2574.5
17.5°	2351.6	2451.2	2489.1	2496.2	2508.1	2505.7	2508.1	2517.6	2541.3	2546.0	2548.4
20°	2292.4	2406.2	2451.2	2458.3	2470.1	2470.1	2470.1	2482.0	2505.7	2515.2	2515.2
22.5°	2211.8	2358.7	2406.2	2410.9	2425.1	2425.1	2429.9	2446.4	2467.8	2470.1	2470.1
25°	2116.9	2306.6	2346.9	2361.2	2375.3	2382.4	2389.5	2399.1	2406.2	2403.8	2406.2
27.5°	2017.3	2240.2	2292.4	2301.8	2320.8	2327.9	2337.4	2339.8	2342.2	2349.3	2344.5
30°	1905.9	2147.7	2226.0	2235.4	2266.3	2271.0	2261.6	2266.3	2278.1	2282.9	2287.6
32.5°	1780.3	2010.2	2157.3	2178.6	2207.0	2192.8	2190.4	2197.5	2216.5	2216.5	2221.2
35°	1609.7	1903.6	2093.3	2112.2	2133.5	2116.9	2126.4	2128.8	2140.6	2147.7	2145.4
37.5°	1422.4	1811.1	2026.9	2041.1	2057.7	2036.3	2050.6	2057.7	2067.1	2062.5	2062.5
40°	1256.4	1666.5	1948.6	1958.1	1972.3	1955.7	1970.0	1974.8	1979.4	1974.8	1972.3
42.5°	1133.1	1507.7	1865.7	1877.5	1868.0	1879.9	1884.6	1894.2	1887.0	1877.5	1877.5
45°	1038.3	1465.1	1775.5	1789.8	1775.5	1794.6	1801.7	1801.7	1780.3	1775.5	1773.2
47.5°	1007.5	1379.7	1685.5	1685.5	1678.4	1702.1	1714.0	1697.4	1676.0	1668.9	1668.9
50°	1005.2	1284.9	1562.2	1552.8	1585.9	1614.4	1602.6	1585.9	1569.3	1543.2	1543.2
52.5°	912.7	1168.7	1403.4	1438.9	1491.1	1507.7	1488.7	1472.2	1443.7	1431.8	1422.4
55°	846.3	1047.8	1258.8	1329.9	1384.5	1405.8	1370.2	1353.6	1311.0	1303.9	1299.1
57.5°	832.1	872.4	1126.0	1216.2	1282.5	1280.1	1258.8	1227.9	1192.4	1185.3	1182.9
60°	763.4	630.5	983.8	1090.4	1159.2	1152.1	1133.1	1104.7	1071.5	1066.8	1062.1
62.5°	692.2	457.6	822.6	943.5	1040.7	1038.3	1021.7	979.0	955.4	943.5	934.0
65°	588.0	384.1	585.5	784.7	924.6	929.2	893.7	862.9	836.9	822.6	820.2
67.5°	448.0	312.9	395.9	654.3	813.1	808.4	763.4	749.1	715.9	708.8	694.6
70°	331.9	208.7	275.0	531.0	704.0	692.2	656.7	640.1	609.2	592.6	583.2
72.5°	275.0	168.3	201.5	412.5	592.6	578.4	547.6	528.6	502.6	488.4	478.9
75°	222.9	177.8	154.1	305.8	481.2	471.8	443.3	424.3	403.0	384.1	386.4
77.5°	163.5	166.0	123.3	225.2	381.6	367.4	350.8	327.2	317.7	298.7	298.7
80°	123.3	130.4	92.5	154.1	275.0	275.0	260.8	244.1	227.6	218.1	218.1
82.5°	82.9	82.9	68.7	97.2	187.3	180.2	170.6	166.0	156.4	151.7	151.7
85°	37.9	47.4	42.7	59.3	101.9	106.7	106.7	101.9	99.6	94.8	97.2
87.5°	11.9	21.3	26.1	33.2	52.1	54.5	56.9	56.9	56.9	59.3	59.3
90°	4.3	7.8	11.3	12.1	19.1	28.3	33.0	29.3	22.0	16.5	16.5
92.5°	17.4	46.9	76.4	83.8	117.8	163.2	185.9	162.9	116.9	82.5	79.2
95°	41.7	95.7	149.7	163.3	289.9	458.9	543.3	484.8	367.8	280.1	270.2
97.5°	72.1	119.7	167.4	179.3	390.6	672.2	813.0	776.1	702.2	646.7	627.7
100°	95.5	138.8	182.0	192.9	427.2	739.7	896.0	898.7	904.1	908.1	885.6
102.5°	115.5	155.9	196.2	206.3	444.0	760.9	919.4	966.5	1060.7	1131.4	1112.0
105°	149.4	183.6	217.8	226.3	456.4	763.4	916.8	1022.4	1233.5	1391.9	1381.6
107.5°	184.2	216.0	247.9	255.8	458.8	729.4	864.7	1012.0	1306.6	1527.5	1530.0
110°	207.6	236.4	265.1	272.3	455.2	699.3	821.3	985.9	1315.3	1562.2	1573.0



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	230.6	258.0	285.4	292.2	455.4	672.9	781.8	950.3	1287.2	1540.0	1556.6
115°	265.3	290.7	315.9	322.2	459.6	642.8	734.4	896.7	1221.4	1464.9	1487.9
117.5°	299.6	322.6	345.6	351.4	468.2	623.9	701.8	848.4	1141.3	1361.1	1386.6
120°	319.6	341.3	362.9	368.3	475.1	617.6	688.8	822.7	1090.4	1291.2	1316.0
122.5°	339.2	361.0	382.8	388.3	485.1	614.3	678.8	799.3	1040.4	1221.2	1245.7
125°	369.1	389.0	408.9	413.9	498.6	611.5	668.0	770.4	975.2	1128.7	1151.2
127.5°	393.5	413.6	433.6	438.6	512.0	609.9	658.8	746.7	922.6	1054.5	1073.5
130°	406.5	428.1	449.7	455.1	521.9	610.9	655.4	733.7	890.2	1007.6	1025.2
132.5°	419.9	441.6	463.2	468.6	529.9	611.5	652.3	722.4	862.5	967.6	983.3
135°	439.9	459.6	479.3	484.3	538.5	610.9	647.1	705.7	823.1	911.1	924.7
137.5°	460.4	479.8	499.3	504.2	551.5	614.7	646.2	695.8	795.0	869.5	880.6
140°	477.3	495.2	513.2	517.7	559.6	615.3	643.2	686.0	771.8	836.0	846.4
142.5°	490.4	507.0	523.6	527.7	566.2	617.5	643.2	680.8	756.1	812.6	821.5
145°	510.3	524.8	539.2	542.8	574.9	617.6	638.9	669.7	731.2	777.4	784.1
147.5°	530.2	544.3	558.4	562.0	587.6	621.8	638.9	663.0	711.5	747.9	753.5
150°	543.3	556.0	568.8	572.0	594.3	624.0	638.9	659.3	700.2	730.9	735.5
152.5°	556.8	566.5	576.1	578.5	598.6	625.4	638.9	656.3	691.3	717.5	721.0
155°	576.7	583.8	591.0	592.8	608.1	628.6	638.9	652.8	680.6	701.4	703.7
157.5°	591.5	598.5	605.4	607.2	617.7	631.9	638.9	649.7	671.3	687.5	689.1
160°	601.5	606.9	612.3	613.6	622.0	633.3	638.9	648.1	666.6	680.5	681.4
162.5°	611.5	615.6	619.6	620.6	626.7	634.8	638.9	646.7	662.3	674.1	674.9
165°	622.3	626.1	629.7	630.6	633.3	637.0	638.9	644.5	655.7	664.1	665.0
167.5°	632.3	634.1	635.8	636.2	638.6	641.7	643.2	646.8	654.2	659.7	660.1
170°	638.9	640.6	642.3	642.8	642.9	643.1	643.2	646.8	654.2	659.7	659.7
172.5°	642.3	642.7	643.1	643.2	643.2	643.2	643.2	646.0	651.8	656.2	655.9
175°	647.1	647.1	647.1	647.1	645.8	644.0	643.2	645.0	648.7	651.5	651.5
177.5°	647.1	647.1	647.1	647.1	646.0	644.7	644.1	645.6	648.5	650.6	650.3
180°	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7
2.5°	2569.7	2562.6	2569.7	2565.0	2567.4	2560.3	2538.9	2531.8	2538.9	2546.0	2546.0
5°	2600.5	2595.8	2600.5	2600.5	2598.2	2593.4	2569.7	2565.0	2569.7	2572.1	2567.4
7.5°	2610.1	2603.0	2610.1	2605.3	2605.3	2600.5	2576.8	2572.1	2574.5	2581.6	2574.5
10°	2610.1	2603.0	2610.1	2607.6	2605.3	2600.5	2576.8	2567.4	2567.4	2574.5	2567.4
12.5°	2598.2	2593.4	2598.2	2593.4	2593.4	2588.7	2565.0	2555.5	2557.9	2560.3	2550.8
15°	2579.2	2572.1	2579.2	2574.5	2576.8	2569.7	2543.7	2534.1	2534.1	2538.9	2522.4
17.5°	2550.8	2541.3	2550.8	2548.4	2546.0	2541.3	2517.6	2508.1	2505.7	2508.1	2496.2
20°	2517.6	2510.5	2517.6	2515.2	2515.2	2505.7	2482.0	2470.1	2470.1	2470.1	2458.3
22.5°	2465.4	2458.3	2465.4	2470.1	2470.1	2467.8	2446.4	2429.9	2425.1	2425.1	2410.9
25°	2406.2	2399.1	2406.2	2406.2	2403.8	2406.2	2399.1	2389.5	2382.4	2375.3	2361.2
27.5°	2349.3	2344.5	2349.3	2344.5	2349.3	2342.2	2339.8	2337.4	2327.9	2320.8	2301.8
30°	2292.4	2287.6	2292.4	2287.6	2282.9	2278.1	2266.3	2261.6	2271.0	2266.3	2235.4
32.5°	2221.2	2216.5	2221.2	2221.2	2216.5	2216.5	2197.5	2190.4	2192.8	2207.0	2178.6
35°	2147.7	2140.6	2147.7	2145.4	2147.7	2140.6	2128.8	2126.4	2116.9	2133.5	2112.2
37.5°	2062.5	2055.3	2062.5	2062.5	2062.5	2067.1	2057.7	2050.6	2036.3	2057.7	2041.1
40°	1974.8	1965.2	1974.8	1972.3	1974.8	1979.4	1974.8	1970.0	1955.7	1972.3	1958.1
42.5°	1875.2	1872.8	1875.2	1877.5	1877.5	1887.0	1894.2	1884.6	1879.9	1868.0	1877.5
45°	1768.4	1763.8	1768.4	1773.2	1775.5	1780.3	1801.7	1801.7	1794.6	1775.5	1789.8
47.5°	1654.7	1642.8	1654.7	1668.9	1668.9	1676.0	1697.4	1714.0	1702.1	1678.4	1685.5
50°	1533.8	1536.1	1533.8	1543.2	1543.2	1569.3	1585.9	1602.6	1614.4	1585.9	1552.8
52.5°	1415.3	1412.9	1415.3	1422.4	1431.8	1443.7	1472.2	1488.7	1507.7	1491.1	1438.9
55°	1296.7	1301.4	1296.7	1299.1	1303.9	1311.0	1353.6	1370.2	1405.8	1384.5	1329.9
57.5°	1178.1	1171.0	1178.1	1182.9	1185.3	1192.4	1227.9	1258.8	1280.1	1282.5	1216.2
60°	1040.7	1031.2	1040.7	1062.1	1066.8	1071.5	1104.7	1133.1	1152.1	1159.2	1090.4
62.5°	919.8	903.2	919.8	934.0	943.5	955.4	979.0	1021.7	1038.3	1040.7	943.5
65°	791.8	784.7	791.8	820.2	822.6	836.9	862.9	893.7	929.2	924.6	784.7
67.5°	675.7	675.7	675.7	694.6	708.8	715.9	749.1	763.4	808.4	813.1	654.3
70°	568.9	566.6	568.9	583.2	592.6	609.2	640.1	656.7	692.2	704.0	531.0
72.5°	467.0	464.7	467.0	478.9	488.4	502.6	528.6	547.6	578.4	592.6	412.5
75°	377.0	372.2	377.0	386.4	384.1	403.0	424.3	443.3	471.8	481.2	305.8
77.5°	289.3	289.3	289.3	298.7	298.7	317.7	327.2	350.8	367.4	381.6	225.2
80°	215.8	213.3	215.8	218.1	218.1	227.6	244.1	260.8	275.0	275.0	154.1
82.5°	151.7	147.0	151.7	151.7	151.7	156.4	166.0	170.6	180.2	187.3	97.2
85°	94.8	94.8	94.8	97.2	94.8	99.6	101.9	106.7	106.7	101.9	59.3
87.5°	61.6	59.3	61.6	59.3	59.3	56.9	56.9	56.9	54.5	52.1	33.2
90°	16.5	16.5	16.5	16.5	16.5	22.0	29.3	33.0	28.3	19.1	12.1
92.5°	66.0	53.0	66.0	79.2	82.5	116.9	162.9	185.9	163.2	117.8	83.8
95°	230.4	190.6	230.4	270.2	280.1	367.8	484.8	543.3	458.9	289.9	163.3
97.5°	552.1	476.4	552.1	627.7	646.7	702.2	776.1	813.0	672.2	390.6	179.3
100°	795.4	705.3	795.4	885.6	908.1	904.1	898.7	896.0	739.7	427.2	192.9
102.5°	1034.9	957.6	1034.9	1112.0	1131.4	1060.7	966.5	919.4	760.9	444.0	206.3
105°	1340.0	1298.5	1340.0	1381.6	1391.9	1233.5	1022.4	916.8	763.4	456.4	226.3
107.5°	1540.0	1550.0	1540.0	1530.0	1527.5	1306.6	1012.0	864.7	729.4	458.8	255.8
110°	1616.2	1659.4	1616.2	1573.0	1562.2	1315.3	985.9	821.3	699.3	455.2	272.3



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1623.0	1689.4	1623.0	1556.6	1540.0	1287.2	950.3	781.8	672.9	455.4	292.2
115°	1580.0	1672.0	1580.0	1487.9	1464.9	1221.4	896.7	734.4	642.8	459.6	322.2
117.5°	1488.7	1590.8	1488.7	1386.6	1361.1	1141.3	848.4	701.8	623.9	468.2	351.4
120°	1415.2	1514.4	1415.2	1316.0	1291.2	1090.4	822.7	688.8	617.6	475.1	368.3
122.5°	1343.6	1441.4	1343.6	1245.7	1221.2	1040.4	799.3	678.8	614.3	485.1	388.3
125°	1241.5	1331.6	1241.5	1151.2	1128.7	975.2	770.4	668.0	611.5	498.6	413.9
127.5°	1149.6	1225.6	1149.6	1073.5	1054.5	922.6	746.7	658.8	609.9	512.0	438.6
130°	1095.4	1165.6	1095.4	1025.2	1007.6	890.2	733.7	655.4	610.9	521.9	455.1
132.5°	1046.3	1109.2	1046.3	983.3	967.6	862.5	722.4	652.3	611.5	529.9	468.6
135°	978.9	1033.2	978.9	924.7	911.1	823.1	705.7	647.1	610.9	538.5	484.3
137.5°	924.9	969.4	924.9	880.6	869.5	795.0	695.8	646.2	614.7	551.5	504.2
140°	888.0	929.4	888.0	846.4	836.0	771.8	686.0	643.2	615.3	559.6	517.7
142.5°	857.2	892.9	857.2	821.5	812.6	756.1	680.8	643.2	617.5	566.2	527.7
145°	811.2	838.2	811.2	784.1	777.4	731.2	669.7	638.9	617.6	574.9	542.8
147.5°	775.8	798.2	775.8	753.5	747.9	711.5	663.0	638.9	621.8	587.6	562.0
150°	753.6	771.8	753.6	735.5	730.9	700.2	659.3	638.9	624.0	594.3	572.0
152.5°	734.6	748.3	734.6	721.0	717.5	691.3	656.3	638.9	625.4	598.6	578.5
155°	712.7	721.8	712.7	703.7	701.4	680.6	652.8	638.9	628.6	608.1	592.8
157.5°	695.5	701.8	695.5	689.1	687.5	671.3	649.7	638.9	631.9	617.7	607.2
160°	685.1	688.8	685.1	681.4	680.5	666.6	648.1	638.9	633.3	622.0	613.6
162.5°	678.4	681.8	678.4	674.9	674.1	662.3	646.7	638.9	634.8	626.7	620.6
165°	668.7	672.3	668.7	665.0	664.1	655.7	644.5	638.9	637.0	633.3	630.6
167.5°	661.6	663.1	661.6	660.1	659.7	654.2	646.8	643.2	641.7	638.6	636.2
170°	659.7	659.7	659.7	659.7	659.7	654.2	646.8	643.2	643.1	642.9	642.8
172.5°	654.5	653.1	654.5	655.9	656.2	651.8	646.0	643.2	643.2	643.2	643.2
175°	651.5	651.5	651.5	651.5	651.5	648.7	645.0	643.2	644.0	645.8	647.1
177.5°	648.7	647.1	648.7	650.3	650.6	648.5	645.6	644.1	644.7	646.0	647.1
180°	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7
2.5°	2541.3	2527.0	2527.0	2503.4	2493.9	2486.8	2474.9	2439.3	2429.9	2420.4	2434.6
5°	2562.6	2536.6	2517.6	2474.9	2439.3	2425.1	2380.1	2294.7	2237.9	2195.2	2171.5
7.5°	2567.4	2534.1	2498.6	2432.2	2346.9	2308.9	2171.5	2015.0	1972.3	1934.4	1910.7
10°	2562.6	2524.7	2474.9	2375.3	2173.9	2107.5	1970.0	1868.0	1841.9	1834.8	1841.9
12.5°	2546.0	2510.5	2441.8	2275.8	1993.7	1948.6	1868.0	1808.8	1804.0	1815.9	1879.9
15°	2517.6	2484.3	2403.8	2143.1	1894.2	1860.9	1804.0	1782.7	1808.8	1891.7	2083.8
17.5°	2489.1	2451.2	2351.6	2012.7	1818.2	1794.6	1754.2	1796.9	1943.9	2055.3	2119.3
20°	2451.2	2406.2	2292.4	1917.8	1763.8	1742.4	1723.4	1915.4	2026.9	2067.1	2102.7
22.5°	2406.2	2358.7	2211.8	1851.5	1706.8	1690.3	1702.1	1981.9	2026.9	2055.3	2086.1
25°	2346.9	2306.6	2116.9	1799.3	1661.8	1642.8	1687.8	1974.8	2000.8	2007.9	2069.6
27.5°	2292.4	2240.2	2017.3	1751.9	1607.2	1600.1	1699.7	1943.9	1962.9	1970.0	2036.3
30°	2226.0	2147.7	1905.9	1702.1	1550.3	1548.0	1702.1	1905.9	1901.3	1920.2	1986.5
32.5°	2157.3	2010.2	1780.3	1640.5	1495.9	1493.5	1685.5	1849.0	1844.4	1870.4	1920.2
35°	2093.3	1903.6	1609.7	1569.3	1427.1	1429.5	1645.2	1782.7	1785.1	1808.8	1839.6
37.5°	2026.9	1811.1	1422.4	1491.1	1360.7	1360.7	1590.7	1721.1	1716.3	1723.4	1766.1
40°	1948.6	1666.5	1256.4	1389.1	1299.1	1292.0	1524.3	1654.7	1638.0	1635.7	1695.0
42.5°	1865.7	1507.7	1133.1	1254.1	1227.9	1218.5	1443.7	1574.1	1543.2	1550.3	1626.2
45°	1775.5	1465.1	1038.3	1059.6	1154.5	1147.3	1356.0	1481.6	1460.3	1479.3	1557.4
47.5°	1685.5	1379.7	1007.5	879.5	1076.2	1073.9	1258.8	1391.6	1379.7	1398.7	1481.6
50°	1562.2	1284.9	1005.2	753.8	988.5	998.0	1142.7	1303.9	1303.9	1320.4	1408.1
52.5°	1403.4	1168.7	912.7	682.8	886.6	915.0	1040.7	1227.9	1232.7	1249.3	1327.5
55°	1258.8	1047.8	846.3	628.2	765.7	827.3	941.1	1149.8	1159.2	1175.8	1246.9
57.5°	1126.0	872.4	832.1	564.2	654.3	713.6	853.4	1073.9	1078.6	1092.9	1161.6
60°	983.8	630.5	763.4	495.5	557.1	602.1	772.8	983.8	1000.4	1009.8	1069.1
62.5°	822.6	457.6	692.2	448.0	509.7	519.1	706.5	898.4	919.8	926.9	962.5
65°	585.5	384.1	588.0	407.8	459.9	462.2	635.3	810.7	829.7	841.5	867.7
67.5°	395.9	312.9	448.0	369.8	422.0	424.3	566.6	708.8	734.9	744.4	760.9
70°	275.0	208.7	331.9	329.5	379.3	384.1	493.1	616.3	640.1	647.2	656.7
72.5°	201.5	168.3	275.0	296.4	334.3	339.0	417.2	512.0	535.7	542.8	547.6
75°	154.1	177.8	222.9	258.4	284.5	286.8	341.4	417.2	433.8	438.6	440.9
77.5°	123.3	166.0	163.5	208.7	232.3	227.6	267.9	322.4	336.6	336.6	336.6
80°	92.5	130.4	123.3	149.3	170.6	166.0	192.0	230.0	234.7	239.4	237.0
82.5°	68.7	82.9	82.9	94.8	113.8	109.1	128.1	149.3	149.3	149.3	154.1
85°	42.7	47.4	37.9	49.8	64.0	61.6	71.1	80.6	82.9	82.9	78.3
87.5°	26.1	21.3	11.9	19.0	28.5	28.5	33.2	35.6	33.2	33.2	33.2
90°	11.3	7.8	4.3	7.8	11.3	12.1	19.1	28.3	33.0	29.3	22.0
92.5°	76.4	46.9	17.4	46.9	76.4	83.8	117.8	163.2	185.9	162.9	116.9
95°	149.7	95.7	41.7	95.7	149.7	163.3	289.9	458.9	543.3	484.8	367.8
97.5°	167.4	119.7	72.1	119.7	167.4	179.3	390.6	672.2	813.0	776.1	702.2
100°	182.0	138.8	95.5	138.8	182.0	192.9	427.2	739.7	896.0	898.7	904.1
102.5°	196.2	155.9	115.5	155.9	196.2	206.3	444.0	760.9	919.4	966.5	1060.7
105°	217.8	183.6	149.4	183.6	217.8	226.3	456.4	763.4	916.8	1022.4	1233.5
107.5°	247.9	216.0	184.2	216.0	247.9	255.8	458.8	729.4	864.7	1012.0	1306.6
110°	265.1	236.4	207.6	236.4	265.1	272.3	455.2	699.3	821.3	985.9	1315.3



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	285.4	258.0	230.6	258.0	285.4	292.2	455.4	672.9	781.8	950.3	1287.2
115°	315.9	290.7	265.3	290.7	315.9	322.2	459.6	642.8	734.4	896.7	1221.4
117.5°	345.6	322.6	299.6	322.6	345.6	351.4	468.2	623.9	701.8	848.4	1141.3
120°	362.9	341.3	319.6	341.3	362.9	368.3	475.1	617.6	688.8	822.7	1090.4
122.5°	382.8	361.0	339.2	361.0	382.8	388.3	485.1	614.3	678.8	799.3	1040.4
125°	408.9	389.0	369.1	389.0	408.9	413.9	498.6	611.5	668.0	770.4	975.2
127.5°	433.6	413.6	393.5	413.6	433.6	438.6	512.0	609.9	658.8	746.7	922.6
130°	449.7	428.1	406.5	428.1	449.7	455.1	521.9	610.9	655.4	733.7	890.2
132.5°	463.2	441.6	419.9	441.6	463.2	468.6	529.9	611.5	652.3	722.4	862.5
135°	479.3	459.6	439.9	459.6	479.3	484.3	538.5	610.9	647.1	705.7	823.1
137.5°	499.3	479.8	460.4	479.8	499.3	504.2	551.5	614.7	646.2	695.8	795.0
140°	513.2	495.2	477.3	495.2	513.2	517.7	559.6	615.3	643.2	686.0	771.8
142.5°	523.6	507.0	490.4	507.0	523.6	527.7	566.2	617.5	643.2	680.8	756.1
145°	539.2	524.8	510.3	524.8	539.2	542.8	574.9	617.6	638.9	669.7	731.2
147.5°	558.4	544.3	530.2	544.3	558.4	562.0	587.6	621.8	638.9	663.0	711.5
150°	568.8	556.0	543.3	556.0	568.8	572.0	594.3	624.0	638.9	659.3	700.2
152.5°	576.1	566.5	556.8	566.5	576.1	578.5	598.6	625.4	638.9	656.3	691.3
155°	591.0	583.8	576.7	583.8	591.0	592.8	608.1	628.6	638.9	652.8	680.6
157.5°	605.4	598.5	591.5	598.5	605.4	607.2	617.7	631.9	638.9	649.7	671.3
160°	612.3	606.9	601.5	606.9	612.3	613.6	622.0	633.3	638.9	648.1	666.6
162.5°	619.6	615.6	611.5	615.6	619.6	620.6	626.7	634.8	638.9	646.7	662.3
165°	629.7	626.1	622.3	626.1	629.7	630.6	633.3	637.0	638.9	644.5	655.7
167.5°	635.8	634.1	632.3	634.1	635.8	636.2	638.6	641.7	643.2	646.8	654.2
170°	642.3	640.6	638.9	640.6	642.3	642.8	642.9	643.1	643.2	646.8	654.2
172.5°	643.1	642.7	642.3	642.7	643.1	643.2	643.2	643.2	643.2	646.0	651.8
175°	647.1	647.1	647.1	647.1	647.1	647.1	645.8	644.0	643.2	645.0	648.7
177.5°	647.1	647.1	647.1	647.1	647.1	647.1	646.0	644.7	644.1	645.6	648.5
180°	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7	2505.7
2.5°	2418.0	2410.9	2420.4	2394.3	2420.4	2410.9	2418.0	2434.6	2420.4	2429.9	2439.3
5°	2121.7	2109.8	2071.9	2041.1	2071.9	2109.8	2121.7	2171.5	2195.2	2237.9	2294.7
7.5°	1896.5	1887.0	1877.5	1858.6	1877.5	1887.0	1896.5	1910.7	1934.4	1972.3	2015.0
10°	1846.7	1849.0	1863.3	1860.9	1863.3	1849.0	1846.7	1841.9	1834.8	1841.9	1868.0
12.5°	1974.8	1996.1	2074.3	2069.6	2074.3	1996.1	1974.8	1879.9	1815.9	1804.0	1808.8
15°	2121.7	2128.8	2145.4	2147.7	2145.4	2128.8	2121.7	2083.8	1891.7	1808.8	1782.7
17.5°	2135.9	2138.3	2150.2	2150.2	2150.2	2138.3	2135.9	2119.3	2055.3	1943.9	1796.9
20°	2124.1	2128.8	2152.5	2157.3	2152.5	2128.8	2124.1	2102.7	2067.1	2026.9	1915.4
22.5°	2119.3	2128.8	2147.7	2145.4	2147.7	2128.8	2119.3	2086.1	2055.3	2026.9	1981.9
25°	2095.6	2095.6	2098.0	2100.4	2098.0	2095.6	2095.6	2069.6	2007.9	2000.8	1974.8
27.5°	2045.8	2050.6	2064.8	2062.5	2064.8	2050.6	2045.8	2036.3	1970.0	1962.9	1943.9
30°	2000.8	1996.1	1984.2	1974.8	1984.2	1996.1	2000.8	1986.5	1920.2	1901.3	1905.9
32.5°	1925.0	1913.1	1901.3	1894.2	1901.3	1913.1	1925.0	1920.2	1870.4	1844.4	1849.0
35°	1834.8	1837.2	1834.8	1827.7	1834.8	1837.2	1834.8	1839.6	1808.8	1785.1	1782.7
37.5°	1770.9	1775.5	1773.2	1763.8	1773.2	1775.5	1770.9	1766.1	1723.4	1716.3	1721.1
40°	1704.5	1706.8	1704.5	1697.4	1704.5	1706.8	1704.5	1695.0	1635.7	1638.0	1654.7
42.5°	1640.5	1638.0	1631.0	1626.2	1631.0	1638.0	1640.5	1626.2	1550.3	1543.2	1574.1
45°	1567.0	1569.3	1555.1	1548.0	1555.1	1569.3	1567.0	1557.4	1479.3	1460.3	1481.6
47.5°	1493.5	1493.5	1481.6	1474.5	1481.6	1493.5	1493.5	1481.6	1398.7	1379.7	1391.6
50°	1415.3	1412.9	1396.3	1393.9	1396.3	1412.9	1415.3	1408.1	1320.4	1303.9	1303.9
52.5°	1325.2	1325.2	1327.5	1332.3	1327.5	1325.2	1325.2	1327.5	1249.3	1232.7	1227.9
55°	1246.9	1249.3	1265.9	1270.6	1265.9	1249.3	1246.9	1246.9	1175.8	1159.2	1149.8
57.5°	1166.4	1166.4	1178.1	1178.1	1178.1	1166.4	1166.4	1161.6	1092.9	1078.6	1073.9
60°	1073.9	1078.6	1088.1	1085.8	1088.1	1078.6	1073.9	1069.1	1009.8	1000.4	983.8
62.5°	976.7	981.4	983.8	979.0	983.8	981.4	976.7	962.5	926.9	919.8	898.4
65°	874.8	879.5	881.9	877.1	881.9	879.5	874.8	867.7	841.5	829.7	810.7
67.5°	770.5	768.0	765.7	775.2	765.7	768.0	770.5	760.9	744.4	734.9	708.8
70°	663.8	663.8	661.4	666.1	661.4	663.8	663.8	656.7	647.2	640.1	616.3
72.5°	549.9	547.6	557.1	549.9	557.1	547.6	549.9	547.6	542.8	535.7	512.0
75°	438.6	443.3	438.6	445.7	438.6	443.3	438.6	440.9	438.6	433.8	417.2
77.5°	334.3	339.0	334.3	334.3	334.3	339.0	334.3	336.6	336.6	336.6	322.4
80°	237.0	234.7	234.7	232.3	234.7	234.7	237.0	237.0	239.4	234.7	230.0
82.5°	151.7	149.3	149.3	154.1	149.3	149.3	151.7	154.1	149.3	149.3	149.3
85°	82.9	85.4	80.6	80.6	80.6	85.4	82.9	78.3	82.9	82.9	80.6
87.5°	30.8	28.5	28.5	28.5	28.5	28.5	30.8	33.2	33.2	33.2	35.6
90°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	22.0	29.3	33.0	28.3
92.5°	82.5	79.2	66.0	53.0	66.0	79.2	82.5	116.9	162.9	185.9	163.2
95°	280.1	270.2	230.4	190.6	230.4	270.2	280.1	367.8	484.8	543.3	458.9
97.5°	646.7	627.7	552.1	476.4	552.1	627.7	646.7	702.2	776.1	813.0	672.2
100°	908.1	885.6	795.4	705.3	795.4	885.6	908.1	904.1	898.7	896.0	739.7
102.5°	1131.4	1112.0	1034.9	957.6	1034.9	1112.0	1131.4	1060.7	966.5	919.4	760.9
105°	1391.9	1381.6	1340.0	1298.5	1340.0	1381.6	1391.9	1233.5	1022.4	916.8	763.4
107.5°	1527.5	1530.0	1540.0	1550.0	1540.0	1530.0	1527.5	1306.6	1012.0	864.7	729.4
110°	1562.2	1573.0	1616.2	1659.4	1616.2	1573.0	1562.2	1315.3	985.9	821.3	699.3



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1540.0	1556.6	1623.0	1689.4	1623.0	1556.6	1540.0	1287.2	950.3	781.8	672.9
115°	1464.9	1487.9	1580.0	1672.0	1580.0	1487.9	1464.9	1221.4	896.7	734.4	642.8
117.5°	1361.1	1386.6	1488.7	1590.8	1488.7	1386.6	1361.1	1141.3	848.4	701.8	623.9
120°	1291.2	1316.0	1415.2	1514.4	1415.2	1316.0	1291.2	1090.4	822.7	688.8	617.6
122.5°	1221.2	1245.7	1343.6	1441.4	1343.6	1245.7	1221.2	1040.4	799.3	678.8	614.3
125°	1128.7	1151.2	1241.5	1331.6	1241.5	1151.2	1128.7	975.2	770.4	668.0	611.5
127.5°	1054.5	1073.5	1149.6	1225.6	1149.6	1073.5	1054.5	922.6	746.7	658.8	609.9
130°	1007.6	1025.2	1095.4	1165.6	1095.4	1025.2	1007.6	890.2	733.7	655.4	610.9
132.5°	967.6	983.3	1046.3	1109.2	1046.3	983.3	967.6	862.5	722.4	652.3	611.5
135°	911.1	924.7	978.9	1033.2	978.9	924.7	911.1	823.1	705.7	647.1	610.9
137.5°	869.5	880.6	924.9	969.4	924.9	880.6	869.5	795.0	695.8	646.2	614.7
140°	836.0	846.4	888.0	929.4	888.0	846.4	836.0	771.8	686.0	643.2	615.3
142.5°	812.6	821.5	857.2	892.9	857.2	821.5	812.6	756.1	680.8	643.2	617.5
145°	777.4	784.1	811.2	838.2	811.2	784.1	777.4	731.2	669.7	638.9	617.6
147.5°	747.9	753.5	775.8	798.2	775.8	753.5	747.9	711.5	663.0	638.9	621.8
150°	730.9	735.5	753.6	771.8	753.6	735.5	730.9	700.2	659.3	638.9	624.0
152.5°	717.5	721.0	734.6	748.3	734.6	721.0	717.5	691.3	656.3	638.9	625.4
155°	701.4	703.7	712.7	721.8	712.7	703.7	701.4	680.6	652.8	638.9	628.6
157.5°	687.5	689.1	695.5	701.8	695.5	689.1	687.5	671.3	649.7	638.9	631.9
160°	680.5	681.4	685.1	688.8	685.1	681.4	680.5	666.6	648.1	638.9	633.3
162.5°	674.1	674.9	678.4	681.8	678.4	674.9	674.1	662.3	646.7	638.9	634.8
165°	664.1	665.0	668.7	672.3	668.7	665.0	664.1	655.7	644.5	638.9	637.0
167.5°	659.7	660.1	661.6	663.1	661.6	660.1	659.7	654.2	646.8	643.2	641.7
170°	659.7	659.7	659.7	659.7	659.7	659.7	659.7	654.2	646.8	643.2	643.1
172.5°	656.2	655.9	654.5	653.1	654.5	655.9	656.2	651.8	646.0	643.2	643.2
175°	651.5	651.5	651.5	651.5	651.5	651.5	651.5	648.7	645.0	643.2	644.0
177.5°	650.6	650.3	648.7	647.1	648.7	650.3	650.6	648.5	645.6	644.1	644.7
180°	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1	647.1



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2505.7	2505.7	2505.7	2505.7	2505.7
2.5°	2474.9	2486.8	2493.9	2503.4	2527.0
5°	2380.1	2425.1	2439.3	2474.9	2517.6
7.5°	2171.5	2308.9	2346.9	2432.2	2498.6
10°	1970.0	2107.5	2173.9	2375.3	2474.9
12.5°	1868.0	1948.6	1993.7	2275.8	2441.8
15°	1804.0	1860.9	1894.2	2143.1	2403.8
17.5°	1754.2	1794.6	1818.2	2012.7	2351.6
20°	1723.4	1742.4	1763.8	1917.8	2292.4
22.5°	1702.1	1690.3	1706.8	1851.5	2211.8
25°	1687.8	1642.8	1661.8	1799.3	2116.9
27.5°	1699.7	1600.1	1607.2	1751.9	2017.3
30°	1702.1	1548.0	1550.3	1702.1	1905.9
32.5°	1685.5	1493.5	1495.9	1640.5	1780.3
35°	1645.2	1429.5	1427.1	1569.3	1609.7
37.5°	1590.7	1360.7	1360.7	1491.1	1422.4
40°	1524.3	1292.0	1299.1	1389.1	1256.4
42.5°	1443.7	1218.5	1227.9	1254.1	1133.1
45°	1356.0	1147.3	1154.5	1059.6	1038.3
47.5°	1258.8	1073.9	1076.2	879.5	1007.5
50°	1142.7	998.0	988.5	753.8	1005.2
52.5°	1040.7	915.0	886.6	682.8	912.7
55°	941.1	827.3	765.7	628.2	846.3
57.5°	853.4	713.6	654.3	564.2	832.1
60°	772.8	602.1	557.1	495.5	763.4
62.5°	706.5	519.1	509.7	448.0	692.2
65°	635.3	462.2	459.9	407.8	588.0
67.5°	566.6	424.3	422.0	369.8	448.0
70°	493.1	384.1	379.3	329.5	331.9
72.5°	417.2	339.0	334.3	296.4	275.0
75°	341.4	286.8	284.5	258.4	222.9
77.5°	267.9	227.6	232.3	208.7	163.5
80°	192.0	166.0	170.6	149.3	123.3
82.5°	128.1	109.1	113.8	94.8	82.9
85°	71.1	61.6	64.0	49.8	37.9
87.5°	33.2	28.5	28.5	19.0	11.9
90°	19.1	12.1	11.3	7.8	4.3
92.5°	117.8	83.8	76.4	46.9	17.4
95°	289.9	163.3	149.7	95.7	41.7
97.5°	390.6	179.3	167.4	119.7	72.1
100°	427.2	192.9	182.0	138.8	95.5
102.5°	444.0	206.3	196.2	155.9	115.5
105°	456.4	226.3	217.8	183.6	149.4
107.5°	458.8	255.8	247.9	216.0	184.2
110°	455.2	272.3	265.1	236.4	207.6



TEST NUMBER: P934991

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	455.4	292.2	285.4	258.0	230.6
115°	459.6	322.2	315.9	290.7	265.3
117.5°	468.2	351.4	345.6	322.6	299.6
120°	475.1	368.3	362.9	341.3	319.6
122.5°	485.1	388.3	382.8	361.0	339.2
125°	498.6	413.9	408.9	389.0	369.1
127.5°	512.0	438.6	433.6	413.6	393.5
130°	521.9	455.1	449.7	428.1	406.5
132.5°	529.9	468.6	463.2	441.6	419.9
135°	538.5	484.3	479.3	459.6	439.9
137.5°	551.5	504.2	499.3	479.8	460.4
140°	559.6	517.7	513.2	495.2	477.3
142.5°	566.2	527.7	523.6	507.0	490.4
145°	574.9	542.8	539.2	524.8	510.3
147.5°	587.6	562.0	558.4	544.3	530.2
150°	594.3	572.0	568.8	556.0	543.3
152.5°	598.6	578.5	576.1	566.5	556.8
155°	608.1	592.8	591.0	583.8	576.7
157.5°	617.7	607.2	605.4	598.5	591.5
160°	622.0	613.6	612.3	606.9	601.5
162.5°	626.7	620.6	619.6	615.6	611.5
165°	633.3	630.6	629.7	626.1	622.3
167.5°	638.6	636.2	635.8	634.1	632.3
170°	642.9	642.8	642.3	640.6	638.9
172.5°	643.2	643.2	643.1	642.7	642.3
175°	645.8	647.1	647.1	647.1	647.1
177.5°	646.0	647.1	647.1	647.1	647.1
180°	647.1	647.1	647.1	647.1	647.1



TEST NUMBER: P934991
 CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-STD-W-6-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.26	16.23	16.12	17.11	18.22	18.09	19.06	18.95	19.94	21.04
	3H	15.75	16.62	16.62	17.51	18.64	19.44	20.31	20.31	21.20	22.33
	4H	15.95	16.77	16.83	17.66	18.81	19.89	20.71	20.78	21.60	22.75
	6H	16.07	16.83	16.97	17.73	18.89	20.18	20.93	21.08	21.84	22.99
	8H	16.07	16.79	16.98	17.71	18.87	20.25	20.97	21.16	21.89	23.05
	12H	16.05	16.73	16.96	17.65	18.83	20.30	20.98	21.21	21.90	23.08
4H	2H	16.31	17.13	17.20	18.02	19.17	18.51	19.33	19.40	20.23	21.37
	3H	17.35	18.03	18.25	18.96	20.12	20.02	20.71	20.93	21.64	22.80
	4H	17.63	18.25	18.54	19.17	20.36	20.56	21.18	21.47	22.10	23.29
	6H	17.76	18.29	18.69	19.24	20.43	20.93	21.46	21.86	22.41	23.60
	8H	17.77	18.27	18.70	19.21	20.41	21.03	21.54	21.97	22.48	23.68
	12H	17.74	18.19	18.69	19.15	20.36	21.10	21.55	22.05	22.51	23.71
8H	4H	18.09	18.59	19.02	19.53	20.73	20.69	21.19	21.62	22.13	23.33
	6H	18.35	18.77	19.31	19.75	20.95	21.13	21.54	22.09	22.53	23.73
	8H	18.40	18.76	19.36	19.74	20.95	21.28	21.65	22.25	22.62	23.84
	12H	18.39	18.71	19.36	19.68	20.94	21.38	21.71	22.35	22.67	23.94
12H	4H	18.10	18.55	19.05	19.51	20.72	20.66	21.11	21.61	22.07	23.28
	6H	18.41	18.78	19.38	19.76	20.97	21.13	21.49	22.09	22.47	23.69
	8H	18.49	18.81	19.46	19.78	21.04	21.29	21.62	22.26	22.58	23.85