

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937486

Luminaire Tested: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K

Issue Date: 12/17/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P937486  
REPORT IS A COMBINATION OF REPORTS P933565 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5262.1 lumens  
Efficiency: N/A  
Efficacy: 127.7 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 41.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937486  
CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P937486

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	88	84	81	83	79	76	73	62	60	58	46	45	44	32	31	30	23
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	28	26	25	19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	18	13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	11
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13	10
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11	8
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10	7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	11	9	7
10	43	31	24	19	38	28	22	18	22	18	14	17	14	11	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1808	1808	1808
5°	1765	2088	2430
10°	1599	3042	4029
15°	1357	3971	4866
20°	1104	4599	4959
25°	920	4809	4858
30°	774	4835	4849
35°	684	4751	4974
40°	596	4644	5103
45°	536	4563	5124
50°	492	4489	5039
55°	470	4384	4815
60°	479	4186	4463
65°	496	3887	3977
70°	523	3383	3362
75°	577	2751	2623
80°	618	1902	1768
85°	522	1004	903

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 5124 cd/sqm



TEST NUMBER: P937486

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.2	0.5
10°-20°	111.7	2.1
20°-30°	195.4	3.7
30°-40°	251.5	4.8
40°-50°	281.0	5.3
50°-60°	269.1	5.1
60°-70°	213.3	4.1
70°-80°	125.4	2.4
80°-90°	37.0	0.7
90°-100°	282.1	5.4
100°-110°	741.8	14.1
110°-120°	769.2	14.6
120°-130°	617.0	11.7
130°-140°	484.1	9.2
140°-150°	371.6	7.1
150°-160°	267.6	5.1
160°-170°	163.7	3.1
170°-180°	55.3	1.1
0°-30°	332.3	6.3
0°-40°	583.9	11.1
0°-60°	1134.0	21.5
0°-90°	1509.7	28.7
90°-120°	1793.2	34.1
90°-150°	3265.8	62.1
90°-180°	3752.0	71.3
0°-180°	5262.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	195	195	195	195	195	
5°	190	204	229	259	269	18
15°	142	262	442	536	553	40
25°	91	298	527	550	551	42
35°	61	284	496	524	545	38
45°	42	227	439	502	525	32
55°	30	144	372	432	444	27
65°	24	76	276	311	315	24
75°	18	47	152	167	167	18
85°	6	14	38	41	42	7
90°	4	11	30	15	15	4
95°	37	146	486	251	170	41
105°	134	202	820	1245	1162	142
115°	237	288	657	1310	1496	234
125°	330	370	598	1010	1191	293
135°	394	433	579	815	924	304
145°	456	486	572	695	750	286
155°	516	530	572	627	646	237
165°	557	564	572	594	601	157
175°	579	579	575	583	583	55
180°	579	579	579	579	579	



TEST NUMBER: P937486

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	194.8	194.8	194.8	194.8	194.8	194.8	194.8	194.8	194.8	194.8	194.8
2.5°	194.8	194.8	196.1	196.7	198.0	198.7	199.9	201.1	204.9	205.5	206.8
5°	189.9	192.4	200.5	203.6	212.4	224.3	229.3	237.5	254.4	259.4	262.5
7.5°	182.3	188.0	208.0	213.0	235.0	266.3	279.5	297.0	323.9	337.1	347.7
10°	170.5	182.3	218.1	230.0	265.6	313.3	337.7	362.2	402.9	421.0	428.0
12.5°	157.3	176.7	228.7	245.0	296.4	365.9	395.4	422.4	468.7	493.2	496.9
15°	142.2	168.6	238.7	262.5	329.0	409.7	442.3	475.6	518.8	536.3	540.7
17.5°	129.1	162.3	248.2	273.2	354.0	449.3	482.5	510.1	545.1	557.0	560.1
20°	112.8	152.2	254.4	287.0	380.3	478.1	510.1	531.4	555.2	562.6	563.9
22.5°	100.9	141.6	258.2	292.0	397.9	495.6	522.6	539.5	555.7	558.3	558.9
25°	90.9	129.7	257.5	297.7	412.9	506.2	527.0	539.5	548.9	550.1	550.1
27.5°	81.4	116.6	255.0	298.9	424.2	508.7	525.1	533.9	538.3	540.7	540.7
30°	73.3	104.0	248.7	296.4	429.2	506.2	519.4	523.8	528.2	532.0	533.9
32.5°	67.1	92.1	239.4	291.3	429.8	500.0	509.4	511.9	518.2	527.0	530.0
35°	61.4	80.2	228.7	284.5	426.1	490.0	496.2	498.8	511.3	524.4	528.8
37.5°	55.8	71.5	214.9	272.5	420.4	478.1	482.5	486.9	506.2	521.9	527.0
40°	50.2	63.9	198.7	259.4	411.7	463.6	467.5	474.3	500.0	518.2	523.2
42.5°	45.8	57.6	181.1	245.6	400.4	447.4	453.0	463.1	492.5	511.9	517.5
45°	41.9	51.4	162.3	226.8	385.9	430.5	438.6	452.4	483.7	502.5	507.5
47.5°	38.2	47.0	142.9	207.4	370.3	413.6	424.2	439.8	471.9	490.0	494.4
50°	35.1	42.6	123.5	186.7	353.4	395.4	407.9	424.2	456.8	473.7	479.3
52.5°	32.6	38.9	105.3	166.1	334.0	376.6	391.0	407.9	438.6	454.9	458.7
55°	30.1	35.7	89.6	144.1	313.9	356.5	372.2	388.5	418.5	432.3	434.9
57.5°	28.9	33.3	76.4	123.5	292.6	334.0	351.5	366.5	394.7	405.4	407.9
60°	26.9	31.3	66.4	105.9	269.5	312.7	327.7	342.8	366.5	375.3	377.2
62.5°	25.0	30.1	58.9	89.0	245.6	287.6	302.6	316.4	336.4	342.8	345.2
65°	23.8	28.9	53.2	76.4	221.2	261.2	276.3	288.2	304.5	310.7	312.0
67.5°	22.6	27.6	48.8	65.8	196.7	235.0	246.2	257.5	270.0	276.3	276.9
70°	20.6	26.3	45.1	58.3	171.7	204.9	214.3	226.2	236.2	239.4	241.3
72.5°	19.4	24.5	42.6	52.7	146.0	176.1	184.8	191.8	200.5	203.6	203.6
75°	17.6	21.9	40.1	47.0	119.6	144.1	151.6	158.5	165.4	166.6	164.8
77.5°	15.7	19.4	34.5	39.5	93.4	114.0	120.3	124.0	129.7	130.9	131.6
80°	13.2	16.9	26.9	30.7	67.7	84.0	88.4	91.4	96.5	96.5	97.8
82.5°	10.0	13.2	19.4	21.9	45.8	57.6	61.4	63.3	66.4	66.4	66.4
85°	6.3	8.1	12.5	14.4	27.6	35.1	37.6	38.2	40.7	41.4	41.4
87.5°	3.2	4.4	8.1	8.8	14.4	18.2	18.2	19.4	19.4	18.8	18.2
90°	3.9	7.0	10.1	10.8	17.1	25.4	29.5	26.2	19.7	14.8	14.8
92.5°	15.5	41.9	68.4	75.0	105.4	146.0	166.3	145.7	104.6	73.8	70.9
95°	37.3	85.6	134.0	146.1	259.4	410.4	486.0	433.7	329.0	250.6	241.7
97.5°	64.4	107.1	149.8	160.5	349.4	601.3	727.2	694.1	628.0	578.4	561.5
100°	85.5	124.1	162.8	172.5	382.2	661.7	801.5	803.9	808.7	812.3	792.1
102.5°	103.3	139.4	175.5	184.6	397.2	680.7	822.5	864.6	948.9	1012.0	994.7
105°	133.7	164.2	194.7	202.4	408.3	682.8	820.1	914.6	1103.4	1245.1	1235.9
107.5°	164.8	193.2	221.7	228.8	410.4	652.4	773.4	905.2	1168.7	1366.3	1368.6
110°	185.7	211.5	237.1	243.6	407.2	625.5	734.6	881.9	1176.5	1397.4	1407.1



TEST NUMBER: P937486

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	206.3	230.8	255.3	261.4	407.4	602.0	699.3	850.0	1151.4	1377.6	1392.4
115°	237.3	259.9	282.5	288.2	411.1	575.1	657.0	802.2	1092.6	1310.4	1331.0
117.5°	268.1	288.6	309.2	314.3	418.8	558.2	627.8	758.9	1021.0	1217.6	1240.4
120°	285.9	305.2	324.6	329.4	425.0	552.5	616.2	735.9	975.4	1155.0	1177.2
122.5°	303.5	323.0	342.5	347.4	433.9	549.5	607.2	715.0	930.6	1092.4	1114.3
125°	330.3	348.0	365.8	370.2	446.0	547.0	597.5	689.1	872.3	1009.7	1029.8
127.5°	351.9	369.9	387.9	392.4	458.0	545.5	589.4	668.0	825.3	943.2	960.2
130°	363.6	382.9	402.3	407.1	466.8	546.5	586.3	656.3	796.3	901.3	917.0
132.5°	375.7	395.0	414.3	419.2	473.9	547.0	583.5	646.1	771.5	865.5	879.6
135°	393.6	411.1	428.8	433.2	481.8	546.5	578.9	631.4	736.3	815.0	827.2
137.5°	411.8	429.3	446.6	451.0	493.3	549.8	578.1	622.4	711.1	777.7	787.6
140°	426.9	443.0	459.1	463.1	500.5	550.4	575.3	613.6	690.3	747.9	757.1
142.5°	438.6	453.5	468.3	472.0	506.5	552.4	575.3	609.0	676.3	726.8	734.9
145°	456.4	469.4	482.3	485.6	514.3	552.5	571.5	599.1	654.1	695.4	701.4
147.5°	474.4	487.0	499.5	502.7	525.7	556.2	571.5	593.2	636.5	669.0	674.1
150°	486.0	497.4	508.7	511.6	531.6	558.3	571.5	589.8	626.3	653.8	657.8
152.5°	498.0	506.6	515.3	517.4	535.5	559.5	571.5	587.1	618.3	641.8	644.8
155°	515.9	522.3	528.7	530.3	544.1	562.4	571.5	583.9	608.8	627.4	629.4
157.5°	529.1	535.4	541.5	543.1	552.6	565.2	571.5	581.1	600.5	614.9	616.3
160°	538.1	542.9	547.7	548.9	556.5	566.5	571.5	579.8	596.4	608.8	609.6
162.5°	547.0	550.6	554.2	555.2	560.6	567.9	571.5	578.5	592.4	602.9	603.6
165°	556.7	559.9	563.2	564.0	566.6	569.8	571.5	576.6	586.6	594.0	594.9
167.5°	565.6	567.2	568.8	569.2	571.2	573.9	575.3	578.6	585.2	590.1	590.5
170°	571.5	573.0	574.6	575.0	575.1	575.3	575.3	578.6	585.2	590.1	590.1
172.5°	574.6	575.0	575.3	575.3	575.3	575.3	575.3	578.0	583.1	587.0	586.7
175°	578.9	578.9	578.9	578.9	577.7	576.1	575.3	577.0	580.3	582.7	582.7
177.5°	578.9	578.9	578.9	578.9	578.0	576.7	576.1	577.4	580.0	582.0	581.6
180°	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9



TEST NUMBER: P937486

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	194.8	194.8
2.5°	208.0	206.8
5°	267.6	268.8
7.5°	360.2	359.7
10°	448.0	453.6
12.5°	511.9	513.1
15°	550.8	553.3
17.5°	565.8	566.5
20°	566.5	565.2
22.5°	559.6	558.3
25°	551.4	550.8
27.5°	543.9	544.5
30°	540.7	542.7
32.5°	540.7	543.9
35°	542.0	545.1
37.5°	541.3	545.1
40°	538.8	543.2
42.5°	532.0	535.1
45°	521.3	525.1
47.5°	507.5	510.1
50°	490.0	492.5
52.5°	468.0	468.7
55°	441.8	444.2
57.5°	413.6	414.1
60°	382.2	384.1
62.5°	349.0	349.0
65°	313.9	315.1
67.5°	277.6	280.7
70°	240.6	241.3
72.5°	204.3	204.3
75°	166.6	167.3
77.5°	130.9	130.9
80°	97.1	97.8
82.5°	67.1	68.3
85°	41.9	41.9
87.5°	19.4	17.6
90°	14.8	14.8
92.5°	59.1	47.4
95°	206.1	170.5
97.5°	493.8	426.2
100°	711.5	630.9
102.5°	925.7	856.7
105°	1198.7	1161.6
107.5°	1377.6	1386.5
110°	1445.7	1484.4





TEST NUMBER: P937486

CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	1451.8	1511.2
115°	1413.3	1495.7
117.5°	1331.7	1423.0
120°	1265.9	1354.7
122.5°	1201.9	1289.4
125°	1110.4	1191.1
127.5°	1028.3	1096.3
130°	979.9	1042.7
132.5°	935.9	992.2
135°	875.6	924.2
137.5°	827.4	867.1
140°	794.3	831.4
142.5°	766.8	798.8
145°	725.6	749.8
147.5°	694.1	714.0
150°	674.1	690.3
152.5°	657.1	669.4
155°	637.5	645.7
157.5°	622.1	627.8
160°	612.9	616.2
162.5°	606.8	609.9
165°	598.1	601.4
167.5°	591.8	593.2
170°	590.1	590.1
172.5°	585.5	584.3
175°	582.7	582.7
177.5°	580.3	578.9
180°	578.9	578.9



TEST NUMBER: P937486  
 CATALOG NUMBER: SQ4-FB-100U-050D-B2750-1D-UNV-STD-W-4-5000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.67	1.39	1.79	2.50	4.05	13.82	14.53	14.93	15.65	17.19
	3H	1.37	2.01	2.49	3.13	4.69	15.63	16.27	16.75	17.39	18.95
	4H	1.66	2.27	2.80	3.40	4.96	16.26	16.87	17.39	17.99	19.56
	6H	1.91	2.47	3.05	3.59	5.17	16.67	17.23	17.81	18.35	19.93
	8H	1.97	2.51	3.11	3.65	5.22	16.78	17.31	17.92	18.45	20.02
	12H	1.98	2.49	3.13	3.63	5.22	16.83	17.34	17.98	18.48	20.07
4H	2H	7.85	8.46	8.99	9.58	11.15	14.07	14.68	15.21	15.81	17.37
	3H	9.41	9.92	10.55	11.06	12.64	16.09	16.60	17.24	17.75	19.33
	4H	9.49	9.96	10.64	11.10	12.70	16.84	17.31	17.99	18.45	20.04
	6H	9.50	9.90	10.65	11.06	12.65	17.36	17.76	18.51	18.92	20.51
	8H	9.47	9.85	10.63	11.00	12.60	17.51	17.89	18.66	19.04	20.64
	12H	9.42	9.76	10.59	10.92	12.53	17.59	17.93	18.76	19.09	20.70
8H	4H	10.92	11.29	12.07	12.44	14.05	16.89	17.27	18.04	18.42	20.02
	6H	11.15	11.46	12.33	12.66	14.26	17.50	17.81	18.67	19.00	20.61
	8H	11.17	11.44	12.35	12.61	14.23	17.71	17.98	18.89	19.15	20.77
	12H	11.13	11.37	12.31	12.54	14.19	17.84	18.08	19.02	19.25	20.90
12H	4H	11.05	11.39	12.22	12.55	14.16	16.83	17.18	18.01	18.34	19.95
	6H	11.40	11.68	12.59	12.85	14.47	17.48	17.75	18.66	18.92	20.55
	8H	11.47	11.71	12.65	12.88	14.53	17.70	17.93	18.88	19.10	20.76