

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936491

Luminaire Tested: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936491
REPORT IS A COMBINATION OF REPORTS P933447 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5809.4 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936491
CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P936491

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77			77
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66	63			63
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55	51			51
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45	42			42
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38	35			35
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33	30			30
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28	26			26
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25	22			22
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22	20			20
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20	17			17
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17	16			16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3561	3561	3561
5°	3478	4114	4787
10°	3153	5997	7935
15°	2679	7833	9582
20°	2180	9075	9766
25°	1818	9494	9567
30°	1532	9552	9549
35°	1354	9390	9796
40°	1179	9181	10051
45°	1067	9028	10090
50°	979	8889	9924
55°	935	8687	9484
60°	957	8302	8789
65°	994	7718	7834
70°	1057	6727	6618
75°	1166	5479	5165
80°	1266	3796	3481
85°	1103	2011	1781

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10090 cd/sqm



TEST NUMBER: P936491

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	1.3
10°-20°	330.0	5.7
20°-30°	577.3	9.9
30°-40°	743.1	12.8
40°-50°	830.0	14.3
50°-60°	795.0	13.7
60°-70°	630.0	10.8
70°-80°	370.5	6.4
80°-90°	103.7	1.8
90°-100°	101.9	1.8
100°-110°	267.9	4.6
110°-120°	277.8	4.8
120°-130°	222.9	3.8
130°-140°	174.9	3.0
140°-150°	134.2	2.3
150°-160°	96.7	1.7
160°-170°	59.1	1.0
170°-180°	20.0	0.3
0°-30°	981.8	16.9
0°-40°	1724.9	29.7
0°-60°	3349.9	57.7
0°-90°	4454.1	76.7
90°-120°	647.6	11.1
90°-150°	1179.6	20.3
90°-180°	1355.0	23.3
0°-180°	5809.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	576	576	576	576	576	
5°	561	602	677	766	794	52
15°	420	776	1307	1584	1634	117
25°	268	879	1557	1625	1627	124
35°	181	840	1466	1549	1610	113
45°	124	670	1296	1484	1551	96
55°	89	426	1100	1277	1312	81
65°	70	226	816	918	931	70
75°	52	139	448	492	494	54
85°	18	43	111	122	124	20
90°	1	4	11	5	5	2
95°	13	53	176	90	62	15
105°	48	73	296	450	420	51
115°	86	104	237	473	540	85
125°	119	134	216	365	430	106
135°	142	156	209	294	334	110
145°	165	175	206	251	271	103
155°	186	192	206	227	233	86
165°	201	204	206	214	217	57
175°	209	209	208	210	210	20
180°	209	209	209	209	209	



TEST NUMBER: P936491

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6
2.5°	575.6	575.6	579.4	581.2	584.9	586.7	590.5	594.2	605.2	607.1	610.8
5°	560.9	568.2	592.3	601.6	627.5	662.7	677.4	701.5	751.5	766.3	775.6
7.5°	538.6	555.3	614.6	629.3	694.1	786.7	825.6	877.4	957.0	995.8	1027.3
10°	503.4	538.6	644.2	679.3	784.8	925.5	997.7	1069.9	1190.2	1243.9	1264.3
12.5°	464.6	522.0	675.7	723.8	875.5	1081.0	1168.0	1247.5	1384.6	1456.8	1467.9
15°	420.2	497.9	705.3	775.6	971.7	1210.6	1306.9	1404.9	1532.6	1584.4	1597.4
17.5°	381.4	479.4	733.0	807.1	1045.8	1327.2	1425.3	1506.7	1610.4	1645.5	1654.8
20°	333.2	449.8	751.5	847.8	1123.6	1412.3	1506.7	1569.7	1640.0	1662.2	1665.9
22.5°	298.0	418.3	762.6	862.5	1175.3	1464.1	1543.7	1593.7	1641.9	1649.3	1651.1
25°	268.4	383.1	760.7	879.3	1219.8	1495.6	1556.7	1593.7	1621.5	1625.2	1625.2
27.5°	240.6	344.3	753.4	882.9	1253.1	1503.0	1551.1	1577.1	1590.0	1597.4	1597.4
30°	216.6	307.3	734.9	875.5	1267.9	1495.6	1534.5	1547.5	1560.4	1571.5	1577.1
32.5°	198.1	272.1	707.0	860.7	1269.8	1477.1	1504.9	1512.2	1530.7	1556.7	1565.9
35°	181.4	237.0	675.7	840.3	1258.7	1447.5	1466.0	1473.4	1510.4	1549.3	1562.2
37.5°	164.8	211.0	634.9	805.2	1242.0	1412.3	1425.3	1438.3	1495.6	1541.8	1556.7
40°	148.0	188.8	586.7	766.3	1216.1	1369.7	1380.8	1401.2	1477.1	1530.7	1545.6
42.5°	135.1	170.3	534.9	725.6	1182.8	1321.6	1338.2	1367.8	1454.9	1512.2	1529.0
45°	124.0	151.8	479.4	670.1	1140.2	1271.6	1295.7	1336.5	1428.9	1484.5	1499.4
47.5°	112.9	138.8	422.1	612.7	1093.9	1221.7	1253.1	1299.4	1393.8	1447.5	1460.4
50°	103.7	125.9	364.6	551.6	1043.9	1168.0	1205.0	1253.1	1349.3	1399.3	1416.0
52.5°	96.3	114.8	310.9	490.5	986.6	1112.5	1155.0	1205.0	1295.7	1343.8	1355.0
55°	88.8	105.5	264.7	425.7	927.4	1053.2	1099.5	1147.6	1236.4	1277.2	1284.6
57.5°	85.2	98.1	225.8	364.6	864.4	986.6	1038.4	1082.9	1166.1	1197.6	1205.0
60°	79.6	92.6	196.2	312.8	796.0	923.6	968.1	1012.5	1082.9	1108.8	1114.3
62.5°	74.1	88.8	174.0	262.8	725.6	849.6	894.0	934.7	994.0	1012.5	1019.9
65°	70.3	85.2	157.4	225.8	653.4	771.9	816.3	851.4	899.6	918.1	921.8
67.5°	66.6	81.4	144.4	194.4	581.2	694.1	727.4	760.7	797.8	816.3	818.2
70°	61.1	77.7	133.3	172.1	507.2	605.2	633.1	668.2	697.8	707.0	712.6
72.5°	57.3	72.2	125.9	155.5	431.3	520.1	546.0	566.4	592.3	601.6	601.6
75°	51.8	64.8	118.4	138.8	353.5	425.7	447.9	468.3	488.7	492.4	486.8
77.5°	46.2	57.3	101.8	116.7	275.8	336.9	355.4	366.5	383.1	386.9	388.7
80°	38.9	50.0	79.6	90.7	199.9	248.1	261.0	270.2	285.1	285.1	288.8
82.5°	29.6	38.9	57.3	64.8	135.1	170.3	181.4	187.0	196.2	196.2	196.2
85°	18.5	24.1	37.0	42.6	81.4	103.7	111.1	112.9	120.3	122.2	122.2
87.5°	9.2	13.0	24.1	25.9	42.6	53.7	53.7	57.3	57.3	55.6	53.7
90°	1.4	2.5	3.6	3.9	6.2	9.2	10.6	9.4	7.1	5.3	5.3
92.5°	5.6	15.1	24.7	27.1	38.1	52.8	60.1	52.6	37.7	26.6	25.6
95°	13.4	30.9	48.4	52.8	93.7	148.2	175.5	156.6	118.8	90.5	87.3
97.5°	23.3	38.7	54.1	57.9	126.2	217.2	262.6	250.7	226.9	208.9	202.9
100°	30.9	44.8	58.8	62.3	138.0	239.0	289.4	290.3	292.1	293.4	286.1
102.5°	37.4	50.4	63.4	66.7	143.5	245.8	297.0	312.2	342.7	365.6	359.3
105°	48.3	59.3	70.3	73.1	147.5	246.6	296.2	330.3	398.5	449.7	446.4
107.5°	59.5	69.8	80.0	82.7	148.2	235.6	279.4	327.0	422.2	493.5	494.4
110°	67.1	76.4	85.6	88.0	147.1	225.9	265.3	318.6	425.0	504.7	508.2



TEST NUMBER: P936491

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	74.5	83.4	92.2	94.4	147.1	217.4	252.6	307.0	415.9	497.5	502.9
115°	85.7	94.0	102.1	104.1	148.5	207.6	237.2	289.7	394.6	473.3	480.7
117.5°	96.9	104.2	111.6	113.5	151.2	201.6	226.8	274.1	368.7	439.7	447.9
120°	103.3	110.3	117.2	119.0	153.5	199.6	222.6	265.8	352.3	417.2	425.3
122.5°	109.6	116.7	123.7	125.4	156.7	198.5	219.3	258.3	336.1	394.6	402.6
125°	119.3	125.7	132.2	133.7	161.1	197.6	215.8	248.9	315.1	364.7	372.0
127.5°	127.1	133.6	140.1	141.7	165.4	197.1	212.9	241.3	298.1	340.7	346.9
130°	131.3	138.3	145.2	147.0	168.6	197.4	211.7	237.0	287.6	325.5	331.2
132.5°	135.7	142.7	149.6	151.4	171.2	197.6	210.8	233.4	278.7	312.6	317.7
135°	142.2	148.5	154.9	156.4	174.0	197.4	209.1	228.1	266.0	294.4	298.8
137.5°	148.8	155.0	161.3	162.9	178.2	198.7	208.8	224.9	256.9	280.9	284.5
140°	154.2	160.0	165.8	167.3	180.8	198.8	207.8	221.6	249.4	270.1	273.5
142.5°	158.4	163.7	169.1	170.5	182.9	199.5	207.8	220.0	244.3	262.5	265.4
145°	164.9	169.5	174.2	175.4	185.8	199.5	206.4	216.3	236.2	251.2	253.3
147.5°	171.3	175.9	180.4	181.6	189.9	200.9	206.4	214.3	229.9	241.6	243.4
150°	175.5	179.6	183.8	184.8	192.0	201.7	206.4	213.0	226.2	236.1	237.6
152.5°	179.9	183.0	186.1	186.9	193.4	202.1	206.4	212.0	223.3	231.8	232.9
155°	186.3	188.7	191.0	191.6	196.5	203.1	206.4	210.9	219.9	226.6	227.3
157.5°	191.1	193.3	195.6	196.1	199.6	204.2	206.4	209.9	216.9	222.1	222.7
160°	194.4	196.1	197.8	198.3	201.0	204.6	206.4	209.4	215.4	219.9	220.1
162.5°	197.5	198.8	200.2	200.5	202.5	205.1	206.4	208.9	214.0	217.8	218.1
165°	201.1	202.2	203.4	203.7	204.6	205.9	206.4	208.2	211.8	214.5	214.8
167.5°	204.3	204.8	205.4	205.6	206.3	207.3	207.8	209.0	211.4	213.1	213.2
170°	206.4	207.0	207.5	207.6	207.7	207.8	207.8	209.0	211.4	213.1	213.1
172.5°	207.5	207.6	207.8	207.8	207.8	207.8	207.8	208.7	210.6	212.0	211.9
175°	209.1	209.1	209.1	209.1	208.7	208.1	207.8	208.4	209.6	210.5	210.5
177.5°	209.1	209.1	209.1	209.1	208.7	208.3	208.1	208.6	209.5	210.2	210.2
180°	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1	209.1



TEST NUMBER: P936491

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	575.6	575.6
2.5°	614.6	610.8
5°	790.4	794.1
7.5°	1064.3	1062.5
10°	1323.5	1340.1
12.5°	1512.2	1516.0
15°	1627.0	1634.4
17.5°	1671.5	1673.3
20°	1673.3	1669.6
22.5°	1652.9	1649.3
25°	1628.9	1627.0
27.5°	1606.7	1608.5
30°	1597.4	1602.9
32.5°	1597.4	1606.7
35°	1601.2	1610.4
37.5°	1599.3	1610.4
40°	1591.8	1604.8
42.5°	1571.5	1580.8
45°	1540.1	1551.1
47.5°	1499.4	1506.7
50°	1447.5	1454.9
52.5°	1382.7	1384.6
55°	1305.0	1312.4
57.5°	1221.7	1223.5
60°	1129.1	1134.6
62.5°	1031.0	1031.0
65°	927.4	931.0
67.5°	820.0	829.2
70°	710.8	712.6
72.5°	603.5	603.5
75°	492.4	494.2
77.5°	386.9	386.9
80°	286.9	288.8
82.5°	198.1	201.7
85°	124.0	124.0
87.5°	57.3	51.8
90°	5.3	5.3
92.5°	21.3	17.1
95°	74.4	61.6
97.5°	178.4	153.9
100°	257.0	227.9
102.5°	334.4	309.4
105°	433.0	419.6
107.5°	497.5	500.8
110°	522.2	536.2



TEST NUMBER: P936491

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	524.3	545.8
115°	510.4	540.2
117.5°	481.0	514.0
120°	457.3	489.3
122.5°	434.1	465.7
125°	401.1	430.2
127.5°	371.5	396.0
130°	353.9	376.6
132.5°	338.0	358.4
135°	316.3	333.8
137.5°	298.9	313.2
140°	286.8	300.3
142.5°	276.9	288.5
145°	262.1	270.9
147.5°	250.7	257.9
150°	243.5	249.4
152.5°	237.3	241.8
155°	230.2	233.2
157.5°	224.7	226.8
160°	221.4	222.6
162.5°	219.2	220.3
165°	216.0	217.2
167.5°	213.8	214.3
170°	213.1	213.1
172.5°	211.5	211.1
175°	210.5	210.5
177.5°	209.6	209.1
180°	209.1	209.1



TEST NUMBER: P936491

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-6-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.54	8.78	8.22	9.48	10.31	20.71	21.94	21.39	22.65	23.48
	3H	8.27	9.39	8.97	10.10	10.97	22.57	23.68	23.26	24.40	25.26
	4H	8.59	9.64	9.30	10.37	11.24	23.23	24.28	23.94	25.01	25.88
	6H	8.86	9.84	9.59	10.57	11.46	23.67	24.65	24.40	25.38	26.27
	8H	8.94	9.87	9.68	10.63	11.52	23.80	24.73	24.54	25.49	26.38
	12H	8.97	9.86	9.71	10.61	11.53	23.88	24.77	24.63	25.52	26.44
4H	2H	14.79	15.85	15.51	16.57	17.45	21.03	22.08	21.74	22.81	23.68
	3H	16.40	17.28	17.13	18.04	18.93	23.10	23.99	23.83	24.75	25.64
	4H	16.51	17.31	17.25	18.08	19.00	23.88	24.69	24.63	25.45	26.37
	6H	16.54	17.24	17.30	18.03	18.96	24.44	25.14	25.20	25.93	26.85
	8H	16.53	17.18	17.29	17.97	18.91	24.61	25.26	25.38	26.05	26.99
	12H	16.50	17.09	17.29	17.90	18.85	24.72	25.31	25.51	26.12	27.06
8H	4H	17.98	18.64	18.75	19.42	20.36	23.97	24.63	24.74	25.41	26.36
	6H	18.24	18.79	19.04	19.61	20.55	24.62	25.16	25.41	25.99	26.93
	8H	18.26	18.75	19.07	19.58	20.53	24.84	25.33	25.65	26.15	27.11
	12H	18.25	18.68	19.06	19.50	20.51	25.00	25.43	25.81	26.24	27.26
12H	4H	18.14	18.73	18.93	19.54	20.49	23.94	24.54	24.73	25.34	26.29
	6H	18.50	18.99	19.31	19.81	20.77	24.60	25.09	25.41	25.92	26.87
	8H	18.59	19.02	19.40	19.84	20.85	24.85	25.28	25.66	26.10	27.11