

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936896

Luminaire Tested: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936896  
REPORT IS A COMBINATION OF REPORTS P933487 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9659.5 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 90.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936896  
CATALOG NUMBER: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P936896

CATALOG NUMBER: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	100	95	91	87	93	89	85	82	78	75	72	67	65	63	58	56	55	50
2	90	82	75	70	84	77	71	66	67	63	59	58	55	52	50	48	45	41
3	82	72	64	57	76	67	60	54	59	53	49	51	47	43	44	40	38	34
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32	28
5	68	56	47	41	63	52	44	39	46	40	35	40	35	31	34	30	27	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	23	21
7	58	45	36	30	54	42	34	29	37	31	26	32	27	23	28	24	21	18
8	53	40	32	26	50	38	30	25	34	27	23	29	24	20	25	21	18	16
9	50	37	29	23	46	35	27	22	31	24	20	27	22	18	23	19	16	14
10	46	33	26	21	43	32	25	20	28	22	18	25	20	16	21	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3562	3562	3562
5°	3479	4116	4787
10°	3156	6000	7936
15°	2682	7839	9583
20°	2184	9084	9767
25°	1822	9506	9568
30°	1536	9567	9551
35°	1358	9408	9797
40°	1183	9201	10052
45°	1072	9050	10092
50°	983	8914	9924
55°	941	8715	9485
60°	964	8332	8790
65°	1003	7750	7836
70°	1068	6759	6620
75°	1183	5511	5166
80°	1292	3822	3481
85°	1150	2028	1782

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 10092 cd/sqm



TEST NUMBER: P936896

CATALOG NUMBER: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.3	1.0
10°-20°	440.1	4.6
20°-30°	769.8	8.0
30°-40°	990.9	10.3
40°-50°	1106.8	11.5
50°-60°	1060.1	11.0
60°-70°	840.1	8.7
70°-80°	494.0	5.1
80°-90°	139.4	1.4
90°-100°	279.6	2.9
100°-110°	735.2	7.6
110°-120°	762.3	7.9
120°-130°	611.4	6.3
130°-140°	479.8	5.0
140°-150°	368.3	3.8
150°-160°	265.2	2.7
160°-170°	162.3	1.7
170°-180°	54.8	0.6
0°-30°	1309.2	13.6
0°-40°	2300.1	23.8
0°-60°	4467.0	46.2
0°-90°	5940.6	61.5
90°-120°	1777.1	18.4
90°-150°	3236.6	33.5
90°-180°	3719.0	38.5
0°-180°	9659.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	768	768	768	768	768	
5°	748	802	903	1022	1059	69
15°	560	1034	1743	2113	2180	156
25°	358	1172	2076	2167	2170	165
35°	242	1121	1955	2066	2147	151
45°	165	894	1728	1980	2068	128
55°	118	568	1466	1703	1750	108
65°	94	301	1088	1224	1242	93
75°	69	185	597	657	659	72
85°	25	57	148	163	165	26
90°	4	11	29	15	15	5
95°	37	145	482	248	169	41
105°	132	201	813	1234	1151	140
115°	235	286	651	1299	1482	232
125°	327	367	592	1001	1180	291
135°	390	429	574	808	916	302
145°	452	481	566	689	743	283
155°	511	526	566	622	640	235
165°	552	559	566	589	596	156
175°	574	574	570	578	578	54
180°	574	574	574	574	574	



TEST NUMBER: P936896

CATALOG NUMBER: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7
2.5°	767.7	767.7	772.6	775.0	780.0	782.4	787.4	792.3	807.2	809.6	814.5
5°	747.9	757.8	789.9	802.2	836.8	883.7	903.4	935.5	1002.1	1021.9	1034.2
7.5°	718.2	740.5	819.5	839.2	925.6	1049.0	1100.8	1169.9	1276.1	1328.0	1369.9
10°	671.4	718.2	859.0	905.9	1046.5	1234.1	1330.4	1426.7	1587.1	1658.7	1685.8
12.5°	619.5	696.0	900.9	965.1	1167.5	1441.4	1557.4	1663.6	1846.2	1942.5	1957.3
15°	560.3	664.0	940.4	1034.2	1295.8	1614.2	1742.6	1873.4	2043.7	2112.8	2130.1
17.5°	508.5	639.3	977.4	1076.2	1394.6	1769.7	1900.6	2009.1	2147.4	2194.2	2206.7
20°	444.3	599.8	1002.1	1130.4	1498.2	1883.3	2009.1	2093.1	2186.9	2216.5	2221.4
22.5°	397.4	557.8	1016.9	1150.2	1567.3	1952.4	2058.5	2125.1	2189.4	2199.2	2201.7
25°	357.9	510.9	1014.4	1172.5	1626.6	1994.4	2075.8	2125.1	2162.2	2167.2	2167.2
27.5°	320.8	459.1	1004.6	1177.4	1671.0	2004.3	2068.4	2103.0	2120.3	2130.1	2130.1
30°	288.8	409.7	979.9	1167.5	1690.7	1994.4	2046.2	2063.5	2080.8	2095.5	2103.0
32.5°	264.1	362.9	942.9	1147.7	1693.2	1969.7	2006.7	2016.6	2041.3	2075.8	2088.1
35°	241.9	316.0	900.9	1120.6	1678.4	1930.2	1954.9	1964.8	2014.1	2065.9	2083.2
37.5°	219.7	281.4	846.6	1073.7	1656.2	1883.3	1900.6	1917.9	1994.4	2056.0	2075.8
40°	197.4	251.8	782.4	1021.9	1621.6	1826.5	1841.3	1868.5	1969.7	2041.3	2061.0
42.5°	180.2	227.1	713.3	967.5	1577.2	1762.4	1784.6	1824.0	1940.0	2016.6	2038.8
45°	165.4	202.4	639.3	893.5	1520.5	1695.7	1727.8	1782.1	1905.5	1979.5	1999.3
47.5°	150.6	185.1	562.7	817.0	1458.7	1629.1	1671.0	1732.8	1858.6	1930.2	1947.5
50°	138.2	167.8	486.2	735.5	1392.1	1557.4	1606.9	1671.0	1799.4	1866.0	1888.2
52.5°	128.3	153.0	414.7	654.1	1315.5	1483.4	1540.2	1606.9	1727.8	1792.0	1806.7
55°	118.4	140.7	353.0	567.7	1236.6	1404.5	1466.1	1530.4	1648.8	1703.1	1713.0
57.5°	113.6	130.9	301.1	486.2	1152.6	1315.5	1384.7	1444.0	1555.0	1597.0	1606.9
60°	106.1	123.4	261.6	417.1	1061.4	1231.7	1290.9	1350.1	1444.0	1478.5	1485.9
62.5°	98.7	118.4	232.0	350.5	967.5	1132.9	1192.2	1246.5	1325.4	1350.1	1360.0
65°	93.8	113.6	209.8	301.1	871.3	1029.3	1088.5	1135.4	1199.5	1224.3	1229.2
67.5°	88.8	108.6	192.5	259.2	775.0	925.6	970.1	1014.4	1063.8	1088.5	1091.0
70°	81.4	103.7	177.7	229.6	676.3	807.2	844.1	891.0	930.5	942.9	950.3
72.5°	76.5	96.3	167.8	207.3	575.1	693.6	728.1	755.3	789.9	802.2	802.2
75°	69.1	86.4	157.9	185.1	471.5	567.7	597.3	624.5	651.7	656.6	649.1
77.5°	61.7	76.5	135.7	155.5	367.8	449.3	473.9	488.7	510.9	515.8	518.4
80°	51.8	66.7	106.1	121.0	266.6	330.7	348.0	360.3	380.1	380.1	385.1
82.5°	39.5	51.8	76.5	86.4	180.2	227.1	241.9	249.3	261.6	261.6	261.6
85°	24.7	32.1	49.4	56.8	108.6	138.2	148.1	150.6	160.5	162.9	162.9
87.5°	12.3	17.3	32.1	34.6	56.8	71.5	71.5	76.5	76.5	74.1	71.5
90°	3.8	6.9	10.0	10.7	16.9	25.1	29.2	26.0	19.5	14.7	14.7
92.5°	15.4	41.6	67.8	74.3	104.5	144.7	164.8	144.4	103.7	73.1	70.2
95°	37.0	84.9	132.8	144.8	257.0	406.8	481.7	429.8	326.2	248.4	239.6
97.5°	63.9	106.1	148.4	159.0	346.2	595.9	720.8	688.0	622.4	573.3	556.5
100°	84.7	123.0	161.3	170.9	378.7	655.8	794.3	796.7	801.5	805.0	785.0
102.5°	102.5	138.2	173.9	182.9	393.6	674.6	815.1	856.9	940.4	1002.9	985.8
105°	132.4	162.7	193.1	200.6	404.7	676.8	812.8	906.4	1093.6	1234.0	1224.8
107.5°	163.3	191.5	219.7	226.8	406.7	646.6	766.5	897.1	1158.3	1354.1	1356.4
110°	184.0	209.5	235.1	241.4	403.7	619.9	728.1	874.0	1165.9	1384.8	1394.5



TEST NUMBER: P936896

CATALOG NUMBER: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	204.5	228.7	253.0	259.1	403.8	596.6	693.0	842.4	1141.2	1365.2	1380.0
115°	235.3	257.7	280.1	285.7	407.5	569.9	651.1	795.0	1082.8	1298.6	1319.0
117.5°	265.6	286.0	306.4	311.5	415.1	553.1	622.1	752.1	1011.8	1206.6	1229.2
120°	283.4	302.5	321.8	326.5	421.2	547.5	610.6	729.3	966.6	1144.6	1166.6
122.5°	300.7	320.0	339.3	344.2	430.0	544.5	601.8	708.6	922.4	1082.7	1104.4
125°	327.3	344.8	362.5	366.9	442.0	542.1	592.2	682.9	864.5	1000.7	1020.7
127.5°	348.8	366.6	384.3	388.8	453.9	540.7	584.0	662.0	817.9	934.8	951.7
130°	360.3	379.5	398.7	403.5	462.6	541.5	580.9	650.3	789.1	893.2	908.8
132.5°	372.3	391.4	410.7	415.4	469.7	542.1	578.3	640.4	764.7	857.8	871.7
135°	390.0	407.5	424.9	429.3	477.4	541.5	573.7	625.7	729.7	807.7	819.8
137.5°	408.2	425.4	442.7	447.0	488.9	544.9	572.9	616.9	704.9	770.8	780.6
140°	423.1	439.1	455.0	459.0	496.0	545.5	570.2	608.2	684.2	741.1	750.3
142.5°	434.7	449.3	464.1	467.7	501.9	547.4	570.2	603.6	670.3	720.4	728.3
145°	452.4	465.2	478.1	481.3	509.7	547.5	566.4	593.7	648.3	689.2	695.2
147.5°	470.1	482.6	495.1	498.2	520.9	551.2	566.4	587.9	630.7	663.0	667.9
150°	481.7	493.0	504.3	507.1	526.9	553.2	566.4	584.5	620.8	648.0	652.0
152.5°	493.6	502.2	510.7	512.9	530.7	554.5	566.4	581.9	612.8	636.1	639.1
155°	511.3	517.6	524.0	525.6	539.2	557.3	566.4	578.7	603.3	621.8	623.8
157.5°	524.3	530.5	536.7	538.3	547.6	560.1	566.4	575.9	595.1	609.4	610.8
160°	533.2	538.1	542.8	544.1	551.5	561.4	566.4	574.6	590.9	603.3	604.1
162.5°	542.1	545.7	549.3	550.2	555.6	562.8	566.4	573.3	587.2	597.6	598.3
165°	551.7	555.0	558.2	559.0	561.4	564.7	566.4	571.3	581.2	588.7	589.5
167.5°	560.6	562.1	563.7	564.0	566.1	568.8	570.2	573.5	580.0	584.9	585.2
170°	566.4	567.9	569.5	569.8	569.9	570.1	570.2	573.5	580.0	584.9	584.9
172.5°	569.5	569.8	570.1	570.2	570.2	570.2	570.2	572.8	578.0	581.8	581.5
175°	573.7	573.7	573.7	573.7	572.5	571.0	570.2	571.8	575.1	577.5	577.5
177.5°	573.7	573.7	573.7	573.7	572.7	571.5	571.0	572.3	574.8	576.7	576.4
180°	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7



TEST NUMBER: P936896

CATALOG NUMBER: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	767.7	767.7
2.5°	819.5	814.5
5°	1053.9	1058.9
7.5°	1419.2	1416.8
10°	1764.8	1787.0
12.5°	2016.6	2021.5
15°	2169.6	2179.5
17.5°	2228.8	2231.3
20°	2231.3	2226.4
22.5°	2204.1	2199.2
25°	2172.1	2169.6
27.5°	2142.4	2144.9
30°	2130.1	2137.6
32.5°	2130.1	2142.4
35°	2135.0	2147.4
37.5°	2132.6	2147.4
40°	2122.7	2140.0
42.5°	2095.5	2107.9
45°	2053.6	2068.4
47.5°	1999.3	2009.1
50°	1930.2	1940.0
52.5°	1843.8	1846.2
55°	1740.1	1750.0
57.5°	1629.1	1631.5
60°	1505.6	1513.1
62.5°	1374.8	1374.8
65°	1236.6	1241.6
67.5°	1093.4	1105.8
70°	947.8	950.3
72.5°	804.6	804.6
75°	656.6	659.0
77.5°	515.8	515.8
80°	382.6	385.1
82.5°	264.1	269.1
85°	165.4	165.4
87.5°	76.5	69.1
90°	14.7	14.7
92.5°	58.6	47.0
95°	204.3	169.1
97.5°	489.4	422.4
100°	705.2	625.2
102.5°	917.4	848.9
105°	1188.0	1151.2
107.5°	1365.2	1374.1
110°	1432.8	1471.1





TEST NUMBER: P936896

CATALOG NUMBER: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	1438.8	1497.7
115°	1400.6	1482.3
117.5°	1319.8	1410.3
120°	1254.5	1342.5
122.5°	1191.1	1277.9
125°	1100.5	1180.5
127.5°	1019.1	1086.5
130°	971.1	1033.4
132.5°	927.6	983.3
135°	867.9	916.0
137.5°	820.1	859.4
140°	787.1	823.9
142.5°	759.9	791.6
145°	719.2	743.1
147.5°	687.8	707.7
150°	668.1	684.2
152.5°	651.3	663.4
155°	631.9	639.9
157.5°	616.5	622.1
160°	607.4	610.6
162.5°	601.4	604.5
165°	592.7	596.0
167.5°	586.6	588.0
170°	584.9	584.9
172.5°	580.3	579.1
175°	577.5	577.5
177.5°	575.1	573.7
180°	573.7	573.7



TEST NUMBER: P936896  
 CATALOG NUMBER: SQ4-FB-050U-100D-B2750-1D-UNV-STD-W-8-5000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.40	7.43	7.24	8.30	9.39	19.58	20.61	20.42	21.48	22.57
	3H	7.12	8.04	7.97	8.92	10.04	21.43	22.36	22.29	23.24	24.36
	4H	7.43	8.30	8.30	9.19	10.32	22.08	22.96	22.96	23.85	24.98
	6H	7.68	8.49	8.57	9.39	10.53	22.52	23.33	23.41	24.23	25.37
	8H	7.76	8.53	8.65	9.44	10.58	22.65	23.42	23.54	24.33	25.48
	12H	7.78	8.51	8.68	9.42	10.59	22.72	23.46	23.62	24.36	25.53
4H	2H	13.64	14.51	14.51	15.40	16.53	19.87	20.75	20.75	21.64	22.77
	3H	15.22	15.95	16.11	16.87	18.02	21.93	22.67	22.82	23.59	24.73
	4H	15.32	15.99	16.22	16.91	18.08	22.71	23.38	23.61	24.29	25.46
	6H	15.34	15.92	16.26	16.86	18.03	23.26	23.84	24.17	24.78	25.95
	8H	15.32	15.87	16.24	16.80	17.99	23.42	23.97	24.34	24.90	26.09
	12H	15.29	15.78	16.23	16.73	17.92	23.53	24.02	24.46	24.97	26.16
8H	4H	16.78	17.32	17.70	18.26	19.44	22.78	23.33	23.70	24.26	25.45
	6H	17.03	17.48	17.97	18.46	19.64	23.42	23.87	24.37	24.85	26.03
	8H	17.05	17.45	18.00	18.41	19.62	23.64	24.04	24.60	25.01	26.21
	12H	17.03	17.38	17.99	18.34	19.59	23.80	24.15	24.75	25.11	26.36
12H	4H	16.93	17.42	17.87	18.37	19.57	22.74	23.23	23.68	24.19	25.38
	6H	17.29	17.69	18.24	18.66	19.86	23.41	23.81	24.36	24.77	25.97
	8H	17.37	17.72	18.33	18.68	19.93	23.64	24.00	24.60	24.95	26.21