

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938381

Luminaire Tested: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938381
REPORT IS A COMBINATION OF REPORTS P933622 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23632.0 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 190.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938381
CATALOG NUMBER: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P938381

CATALOG NUMBER: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	88	84	81	83	79	76	73	62	60	58	46	45	43	32	31	30	23
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	27	26	25	19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	17	13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	11
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13	10
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11	8
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10	7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	10	9	6
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2695	2695	2695
5°	2634	3116	3623
10°	2390	4544	6007
15°	2032	5938	7253
20°	1655	6882	7392
25°	1381	7204	7242
30°	1165	7251	7228
35°	1031	7133	7415
40°	899	6978	7608
45°	814	6866	7638
50°	748	6765	7512
55°	717	6616	7178
60°	735	6329	6653
65°	766	5890	5930
70°	818	5140	5010
75°	910	4195	3909
80°	1000	2913	2634
85°	907	1548	1348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7638 cd/sqm



TEST NUMBER: P938381

CATALOG NUMBER: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	0.5
10°-20°	499.6	2.1
20°-30°	873.9	3.7
30°-40°	1125.0	4.8
40°-50°	1256.5	5.3
50°-60°	1203.5	5.1
60°-70°	953.8	4.0
70°-80°	560.8	2.4
80°-90°	165.7	0.7
90°-100°	1269.3	5.4
100°-110°	3337.1	14.1
110°-120°	3460.2	14.6
120°-130°	2775.5	11.7
130°-140°	2177.8	9.2
140°-150°	1671.5	7.1
150°-160°	1203.8	5.1
160°-170°	736.5	3.1
170°-180°	248.8	1.1
0°-30°	1486.2	6.3
0°-40°	2611.2	11.0
0°-60°	5071.2	21.5
0°-90°	6751.5	28.6
90°-120°	8066.6	34.1
90°-150°	14691.3	62.2
90°-180°	16880.0	71.4
0°-180°	23632.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	871	871	871	871	871	
5°	849	911	1026	1160	1202	78
15°	636	1174	1978	2399	2474	177
25°	406	1331	2357	2460	2463	187
35°	275	1272	2219	2345	2438	171
45°	188	1014	1962	2247	2348	145
55°	134	644	1664	1934	1987	123
65°	106	342	1236	1390	1410	106
75°	78	210	678	745	748	82
85°	28	64	168	185	188	30
90°	18	49	133	66	66	16
95°	168	657	2186	1127	767	186
105°	601	911	3689	5601	5225	637
115°	1068	1297	2955	5895	6728	1055
125°	1486	1666	2688	4542	5358	1319
135°	1770	1949	2604	3666	4158	1370
145°	2054	2184	2571	3128	3373	1286
155°	2321	2386	2571	2822	2905	1066
165°	2504	2538	2571	2672	2705	707
175°	2604	2604	2588	2622	2622	247
180°	2604	2604	2604	2604	2604	



TEST NUMBER: P938381

CATALOG NUMBER: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4
2.5°	871.4	871.4	877.0	879.8	885.4	888.2	893.8	899.4	916.3	919.1	924.7
5°	849.0	860.2	896.6	910.6	949.9	1003.1	1025.5	1062.1	1137.7	1160.1	1174.1
7.5°	815.4	840.6	930.3	952.7	1050.8	1190.9	1249.8	1328.2	1448.7	1507.6	1555.2
10°	762.1	815.4	975.1	1028.3	1188.1	1401.1	1510.4	1619.6	1801.8	1883.0	1913.9
12.5°	703.3	790.2	1022.7	1095.7	1325.4	1636.5	1768.2	1888.6	2096.0	2205.3	2222.1
15°	636.1	753.7	1067.7	1174.1	1471.1	1832.6	1978.3	2126.8	2320.1	2398.6	2418.2
17.5°	577.2	725.7	1109.7	1221.8	1583.2	2009.1	2157.6	2280.9	2437.8	2491.1	2505.1
20°	504.4	680.9	1137.7	1283.4	1700.9	2138.0	2280.9	2376.2	2482.7	2516.3	2521.9
22.5°	451.1	633.3	1154.5	1305.8	1779.4	2216.5	2337.0	2412.6	2485.5	2496.7	2499.5
25°	406.3	580.0	1151.7	1331.0	1846.6	2264.1	2356.6	2412.6	2454.6	2460.2	2460.2
27.5°	364.3	521.2	1140.5	1336.6	1897.0	2275.3	2348.2	2387.4	2407.0	2418.2	2418.2
30°	327.8	465.1	1112.5	1325.4	1919.5	2264.1	2323.0	2342.6	2362.2	2379.0	2387.4
32.5°	299.8	411.9	1070.5	1303.0	1922.3	2236.1	2278.1	2289.3	2317.3	2356.6	2370.6
35°	274.6	358.7	1022.7	1272.2	1905.5	2191.3	2219.3	2230.5	2286.5	2345.4	2365.0
37.5°	249.4	319.4	961.1	1219.0	1880.2	2138.0	2157.6	2177.2	2264.1	2334.2	2356.6
40°	224.2	285.8	888.2	1160.1	1841.0	2073.6	2090.4	2121.2	2236.1	2317.3	2339.8
42.5°	204.5	257.8	809.8	1098.5	1790.6	2000.7	2025.9	2070.8	2202.5	2289.3	2314.5
45°	187.7	229.8	725.7	1014.3	1726.1	1925.1	1961.5	2023.1	2163.2	2247.3	2269.7
47.5°	170.9	210.2	638.9	927.5	1656.1	1849.4	1897.0	1967.1	2110.0	2191.3	2210.9
50°	156.9	190.5	552.0	835.0	1580.4	1768.2	1824.2	1897.0	2042.8	2118.4	2143.6
52.5°	145.7	173.7	470.7	742.5	1493.6	1684.1	1748.5	1824.2	1961.5	2034.3	2051.2
55°	134.5	159.7	400.7	644.5	1403.9	1594.4	1664.5	1737.3	1871.8	1933.5	1944.7
57.5°	128.9	148.5	341.8	552.0	1308.6	1493.6	1572.0	1639.3	1765.4	1813.0	1824.2
60°	120.5	140.1	297.0	473.5	1205.0	1398.3	1465.5	1532.8	1639.3	1678.5	1686.9
62.5°	112.1	134.5	263.4	397.9	1098.5	1286.2	1353.5	1415.1	1504.8	1532.8	1544.0
65°	106.5	128.9	238.2	341.8	989.1	1168.5	1235.8	1289.0	1361.9	1389.9	1395.5
67.5°	100.9	123.3	218.6	294.2	879.8	1050.8	1101.3	1151.7	1207.8	1235.8	1238.6
70°	92.5	117.7	201.7	260.6	767.7	916.3	958.3	1011.5	1056.4	1070.5	1078.9
72.5°	86.9	109.3	190.5	235.4	652.9	787.4	826.6	857.4	896.6	910.6	910.6
75°	78.5	98.1	179.3	210.2	535.2	644.5	678.1	708.9	739.7	745.3	736.9
77.5°	70.0	86.9	154.1	176.5	417.5	510.0	538.0	554.8	580.0	585.6	588.4
80°	58.8	75.7	120.5	137.3	302.6	375.5	395.1	409.1	431.5	431.5	437.1
82.5°	44.8	58.8	86.9	98.1	204.5	257.8	274.6	283.0	297.0	297.0	297.0
85°	28.0	36.4	56.0	64.4	123.3	156.9	168.1	170.9	182.1	184.9	184.9
87.5°	14.0	19.6	36.4	39.2	64.4	81.3	81.3	86.9	86.9	84.1	81.3
90°	17.5	31.5	45.5	48.9	76.9	114.1	132.8	118.1	88.5	66.4	66.4
92.5°	69.9	188.7	307.6	337.3	474.2	656.7	747.9	655.5	470.6	332.0	318.9
95°	167.7	385.2	602.7	657.1	1166.8	1846.5	2186.3	1950.9	1480.3	1127.2	1087.3
97.5°	290.1	481.9	673.8	721.8	1571.7	2705.0	3271.5	3122.8	2825.4	2602.2	2526.1
100°	384.4	558.4	732.4	776.0	1719.1	2976.6	3605.3	3616.2	3637.9	3654.3	3563.6
102.5°	464.9	627.2	789.5	830.1	1786.6	3062.0	3699.8	3889.3	4268.3	4552.6	4474.9
105°	601.2	738.7	876.2	910.6	1836.8	3071.7	3689.2	4114.1	4963.8	5601.1	5559.4
107.5°	741.0	869.2	997.3	1029.4	1846.1	2935.0	3479.5	4072.1	5257.4	6146.4	6156.5
110°	835.4	951.1	1066.8	1095.8	1832.1	2813.9	3304.8	3967.4	5292.4	6286.2	6329.7



TEST NUMBER: P938381

CATALOG NUMBER: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	928.0	1038.3	1148.6	1176.2	1832.7	2708.0	3145.7	3823.8	5180.0	6197.1	6263.9
115°	1067.8	1169.6	1271.4	1296.8	1849.6	2586.7	2955.3	3608.5	4914.9	5894.8	5987.4
117.5°	1205.9	1298.3	1390.7	1413.8	1883.9	2510.7	2824.1	3413.7	4592.8	5477.1	5579.8
120°	1286.2	1373.3	1460.2	1482.0	1911.9	2485.1	2771.7	3310.4	4387.7	5195.7	5295.5
122.5°	1364.9	1452.7	1540.4	1562.4	1952.2	2471.7	2731.6	3216.6	4186.7	4914.3	5012.8
125°	1485.5	1565.5	1645.5	1665.5	2006.3	2460.7	2687.9	3099.9	3924.0	4542.0	4632.7
127.5°	1583.3	1664.1	1744.9	1765.1	2060.4	2454.3	2651.2	3005.0	3712.6	4243.3	4319.8
130°	1635.8	1722.8	1809.7	1831.5	2100.0	2458.1	2637.1	2952.1	3582.1	4054.5	4125.2
132.5°	1690.0	1776.9	1863.9	1885.7	2132.0	2460.6	2624.9	2906.9	3470.8	3893.8	3957.1
135°	1770.3	1849.5	1928.8	1948.6	2167.1	2458.4	2604.0	2840.1	3312.3	3666.5	3721.1
137.5°	1852.5	1931.0	2009.4	2029.0	2219.5	2473.4	2600.4	2800.0	3199.3	3498.8	3543.4
140°	1920.7	1992.9	2065.2	2083.2	2251.5	2475.9	2588.2	2760.6	3105.6	3364.2	3405.9
142.5°	1973.1	2039.9	2106.6	2123.4	2278.3	2484.9	2588.2	2739.7	3042.6	3269.8	3305.8
145°	2053.5	2111.8	2170.0	2184.5	2313.2	2484.9	2570.7	2694.6	2942.4	3128.2	3155.4
147.5°	2133.8	2190.5	2247.2	2261.4	2364.5	2502.0	2570.7	2668.3	2863.2	3009.4	3032.0
150°	2186.3	2237.6	2288.9	2301.7	2391.3	2511.0	2570.7	2653.1	2817.8	2941.3	2959.5
152.5°	2240.5	2279.3	2318.1	2327.8	2408.8	2516.8	2570.7	2641.1	2781.6	2887.1	2900.9
155°	2320.9	2349.7	2378.3	2385.5	2447.3	2529.6	2570.7	2626.7	2738.6	2822.5	2831.6
157.5°	2380.3	2408.2	2436.2	2443.2	2485.7	2542.3	2570.7	2614.3	2701.2	2766.5	2773.0
160°	2420.5	2442.2	2464.0	2469.4	2503.2	2548.2	2570.7	2608.0	2682.5	2738.5	2742.2
162.5°	2460.6	2477.0	2493.2	2497.3	2521.8	2554.4	2570.7	2602.2	2665.2	2712.3	2715.8
165°	2504.3	2519.1	2533.8	2537.6	2548.6	2563.4	2570.7	2593.3	2638.3	2672.1	2675.8
167.5°	2544.6	2551.6	2558.5	2560.3	2569.6	2582.0	2588.2	2603.0	2632.5	2654.6	2656.2
170°	2570.7	2577.7	2584.8	2586.5	2587.1	2587.8	2588.2	2603.0	2632.5	2654.6	2654.6
172.5°	2584.8	2586.2	2587.8	2588.2	2588.2	2588.2	2588.2	2599.9	2623.2	2640.7	2639.3
175°	2604.0	2604.0	2604.0	2604.0	2598.8	2591.8	2588.2	2595.6	2610.3	2621.5	2621.5
177.5°	2604.0	2604.0	2604.0	2604.0	2599.9	2594.5	2591.8	2597.5	2609.2	2617.9	2616.3
180°	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0



TEST NUMBER: P938381

CATALOG NUMBER: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	871.4	871.4
2.5°	930.3	924.7
5°	1196.5	1202.2
7.5°	1611.2	1608.4
10°	2003.5	2028.7
12.5°	2289.3	2294.9
15°	2463.1	2474.3
17.5°	2530.3	2533.1
20°	2533.1	2527.5
22.5°	2502.3	2496.7
25°	2465.9	2463.1
27.5°	2432.2	2435.0
30°	2418.2	2426.6
32.5°	2418.2	2432.2
35°	2423.8	2437.8
37.5°	2421.0	2437.8
40°	2409.8	2429.4
42.5°	2379.0	2393.0
45°	2331.4	2348.2
47.5°	2269.7	2280.9
50°	2191.3	2202.5
52.5°	2093.2	2096.0
55°	1975.5	1986.7
57.5°	1849.4	1852.2
60°	1709.3	1717.7
62.5°	1560.8	1560.8
65°	1403.9	1409.5
67.5°	1241.4	1255.4
70°	1076.1	1078.9
72.5°	913.5	913.5
75°	745.3	748.1
77.5°	585.6	585.6
80°	434.3	437.1
82.5°	299.8	305.4
85°	187.7	187.7
87.5°	86.9	78.5
90°	66.4	66.4
92.5°	266.0	213.2
95°	927.2	767.2
97.5°	2221.6	1917.1
100°	3200.9	2838.1
102.5°	4164.2	3853.5
105°	5392.4	5225.4
107.5°	6196.9	6237.3
110°	6503.7	6677.7



TEST NUMBER: P938381

CATALOG NUMBER: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	6531.1	6798.3
115°	6357.8	6728.3
117.5°	5990.7	6401.5
120°	5694.7	6094.0
122.5°	5406.6	5800.4
125°	4995.5	5358.3
127.5°	4625.8	4931.8
130°	4407.9	4690.6
132.5°	4210.2	4463.4
135°	3939.3	4157.6
137.5°	3722.1	3900.7
140°	3572.9	3739.9
142.5°	3449.4	3593.1
145°	3264.2	3373.0
147.5°	3122.1	3212.1
150°	3032.5	3105.6
152.5°	2956.0	3011.1
155°	2868.0	2904.6
157.5°	2798.5	2824.1
160°	2757.0	2771.7
162.5°	2729.8	2743.8
165°	2690.6	2705.3
167.5°	2662.4	2668.6
170°	2654.6	2654.6
172.5°	2633.9	2628.5
175°	2621.5	2621.5
177.5°	2610.2	2604.0
180°	2604.0	2604.0



TEST NUMBER: P938381
 CATALOG NUMBER: SQ4-FB-150U-075D-B2750-1D-UNV-STD-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.06	2.78	3.18	3.89	5.44	15.26	15.97	16.37	17.09	18.63
	3H	2.76	3.40	3.88	4.52	6.09	17.09	17.73	18.22	18.86	20.42
	4H	3.05	3.66	4.18	4.78	6.35	17.73	18.34	18.87	19.47	21.03
	6H	3.29	3.86	4.44	4.98	6.56	18.16	18.72	19.30	19.85	21.43
	8H	3.36	3.89	4.50	5.03	6.60	18.28	18.81	19.43	19.96	21.53
	12H	3.37	3.88	4.52	5.01	6.61	18.34	18.85	19.50	19.99	21.58
4H	2H	9.27	9.88	10.41	11.00	12.57	15.51	16.12	16.66	17.25	18.81
	3H	10.82	11.33	11.97	12.48	14.06	17.55	18.06	18.70	19.21	20.79
	4H	10.91	11.38	12.06	12.52	14.12	18.31	18.78	19.47	19.92	21.52
	6H	10.91	11.32	12.07	12.48	14.07	18.85	19.25	20.01	20.41	22.00
	8H	10.89	11.26	12.04	12.42	14.02	19.01	19.39	20.17	20.54	22.15
	12H	10.84	11.18	12.01	12.34	13.95	19.10	19.44	20.27	20.60	22.22
8H	4H	12.35	12.72	13.50	13.88	15.48	18.36	18.74	19.52	19.89	21.50
	6H	12.58	12.89	13.76	14.09	15.69	18.99	19.30	20.17	20.49	22.10
	8H	12.60	12.87	13.78	14.04	15.67	19.21	19.48	20.39	20.65	22.28
	12H	12.56	12.80	13.75	13.97	15.62	19.35	19.59	20.54	20.76	22.41
12H	4H	12.49	12.83	13.66	13.99	15.60	18.31	18.65	19.48	19.81	21.42
	6H	12.84	13.11	14.02	14.29	15.91	18.97	19.24	20.15	20.41	22.04
	8H	12.90	13.14	14.09	14.31	15.97	19.20	19.43	20.38	20.60	22.26