

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937081

Luminaire Tested: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937081
REPORT IS A COMBINATION OF REPORTS P933493 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12916.3 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 103.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937081
CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P937081

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	82	85	81	78	75	65	63	61	50	49	47	37	36	35	29
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29	23
3	77	68	61	55	70	62	55	50	49	45	41	38	35	32	28	26	24	19
4	71	60	52	46	63	54	47	42	44	39	35	34	30	27	25	22	20	16
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	14
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15	12
7	55	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13	10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	14	12	9
9	47	35	27	22	42	32	25	20	26	21	17	20	16	14	15	12	10	8
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	14	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1767	2090	2430
10°	1603	3047	4029
15°	1363	3982	4864
20°	1110	4616	4958
25°	926	4831	4857
30°	782	4863	4848
35°	691	4784	4973
40°	603	4680	5103
45°	546	4605	5123
50°	502	4537	5038
55°	481	4437	4814
60°	493	4244	4462
65°	514	3950	3977
70°	548	3448	3360
75°	610	2813	2622
80°	672	1954	1767
85°	609	1038	904

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5123 cd/sqm



TEST NUMBER: P937081

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	0.6
10°-20°	335.1	2.6
20°-30°	586.1	4.5
30°-40°	754.5	5.8
40°-50°	842.7	6.5
50°-60°	807.2	6.2
60°-70°	639.7	5.0
70°-80°	376.1	2.9
80°-90°	109.4	0.8
90°-100°	630.9	4.9
100°-110°	1658.6	12.8
110°-120°	1719.8	13.3
120°-130°	1379.5	10.7
130°-140°	1082.4	8.4
140°-150°	830.8	6.4
150°-160°	598.3	4.6
160°-170°	366.1	2.8
170°-180°	123.7	1.0
0°-30°	996.8	7.7
0°-40°	1751.3	13.6
0°-60°	3401.2	26.3
0°-90°	4526.4	35.0
90°-120°	4009.2	31.0
90°-150°	7301.8	56.5
90°-180°	8390.0	65.0
0°-180°	12916.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	584	584	584	584	584	
5°	570	611	688	778	806	53
15°	427	788	1327	1609	1659	119
25°	272	893	1580	1650	1652	126
35°	184	853	1488	1573	1635	115
45°	126	680	1316	1507	1575	97
55°	90	432	1116	1297	1332	82
65°	72	229	829	932	945	71
75°	53	141	455	500	502	55
85°	19	43	113	124	126	20
90°	9	24	66	33	33	8
95°	83	327	1087	560	381	93
105°	299	452	1834	2784	2597	317
115°	531	644	1469	2930	3344	524
125°	738	828	1336	2258	2663	656
135°	880	968	1294	1822	2066	681
145°	1021	1086	1278	1555	1676	639
155°	1154	1186	1278	1403	1444	530
165°	1245	1261	1278	1328	1345	351
175°	1294	1294	1286	1303	1303	123
180°	1294	1294	1294	1294	1294	



TEST NUMBER: P937081

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	584.5	584.5	584.5	584.5	584.5	584.5	584.5	584.5	584.5	584.5	584.5
2.5°	584.5	584.5	588.2	590.1	593.8	595.7	599.5	603.3	614.6	616.4	620.2
5°	569.5	576.9	601.4	610.7	637.1	672.8	687.8	712.3	763.0	778.0	787.5
7.5°	546.9	563.8	623.9	638.9	704.8	798.8	838.2	890.8	971.6	1011.1	1043.0
10°	511.2	546.9	654.0	689.8	796.8	939.7	1012.9	1086.2	1208.4	1263.0	1283.6
12.5°	471.7	530.0	685.9	734.8	888.9	1097.5	1185.9	1266.7	1405.8	1479.1	1490.3
15°	426.7	505.6	716.0	787.5	986.7	1229.1	1326.8	1426.4	1556.1	1608.7	1621.9
17.5°	387.1	486.7	744.2	819.4	1061.9	1347.5	1447.0	1529.8	1635.1	1670.7	1680.2
20°	338.3	456.7	763.0	860.8	1140.8	1434.0	1529.8	1593.7	1665.1	1687.6	1691.4
22.5°	302.6	424.7	774.3	875.8	1193.4	1486.6	1567.3	1618.2	1667.0	1674.5	1676.3
25°	272.5	389.0	772.4	892.7	1238.5	1518.5	1580.5	1618.2	1646.3	1650.1	1650.1
27.5°	244.3	349.6	764.9	896.5	1272.3	1526.1	1574.9	1601.2	1614.3	1621.9	1621.9
30°	219.9	312.0	746.1	888.9	1287.3	1518.5	1558.0	1571.2	1584.3	1595.6	1601.2
32.5°	201.1	276.3	717.9	873.9	1289.2	1499.7	1527.9	1535.4	1554.2	1580.5	1589.9
35°	184.2	240.6	685.9	853.2	1278.0	1469.6	1488.4	1496.0	1533.5	1573.0	1586.1
37.5°	167.3	214.3	644.6	817.5	1261.0	1434.0	1447.0	1460.2	1518.5	1565.5	1580.5
40°	150.4	191.7	595.7	778.0	1234.7	1390.7	1402.0	1422.7	1499.7	1554.2	1569.2
42.5°	137.2	172.9	543.1	736.7	1200.9	1341.9	1358.8	1388.9	1477.1	1535.4	1552.3
45°	125.9	154.1	486.7	680.3	1157.7	1291.1	1315.5	1356.9	1450.9	1507.2	1522.2
47.5°	114.6	140.9	428.5	622.0	1110.7	1240.4	1272.3	1319.3	1415.1	1469.6	1482.8
50°	105.3	127.8	370.2	560.0	1059.9	1185.9	1223.4	1272.3	1370.1	1420.8	1437.7
52.5°	97.7	116.6	315.7	498.0	1001.7	1129.5	1172.7	1223.4	1315.5	1364.4	1375.7
55°	90.2	107.1	268.7	432.3	941.6	1069.3	1116.3	1165.2	1255.4	1296.8	1304.2
57.5°	86.5	99.6	229.3	370.2	877.7	1001.7	1054.3	1099.4	1183.9	1216.0	1223.4
60°	80.8	94.0	199.2	317.7	808.1	937.8	982.9	1028.0	1099.4	1125.8	1131.4
62.5°	75.2	90.2	176.6	266.8	736.7	862.6	907.8	949.0	1009.2	1028.0	1035.5
65°	71.5	86.5	159.7	229.3	663.4	783.7	828.8	864.5	913.4	932.1	935.9
67.5°	67.6	82.7	146.5	197.4	590.1	704.8	738.6	772.4	810.0	828.8	830.7
70°	62.0	78.9	135.3	174.8	514.9	614.6	642.8	678.5	708.5	717.9	723.6
72.5°	58.3	73.3	127.8	157.8	437.9	528.1	554.4	575.1	601.4	610.7	610.7
75°	52.6	65.8	120.3	140.9	358.9	432.3	454.8	475.5	496.1	499.9	494.3
77.5°	47.0	58.3	103.4	118.4	280.0	342.0	360.8	372.1	389.0	392.7	394.6
80°	39.5	50.7	80.8	92.1	203.0	251.8	265.0	274.4	289.4	289.4	293.2
82.5°	30.1	39.5	58.3	65.8	137.2	172.9	184.2	189.8	199.2	199.2	199.2
85°	18.8	24.5	37.5	43.2	82.7	105.3	112.7	114.6	122.2	124.0	124.0
87.5°	9.4	13.2	24.5	26.3	43.2	54.5	54.5	58.3	58.3	56.4	54.5
90°	8.7	15.6	22.5	24.3	38.2	56.8	66.0	58.7	44.0	33.0	33.0
92.5°	34.7	93.8	152.9	167.7	235.6	326.3	371.7	325.8	234.0	165.0	158.5
95°	83.4	191.5	299.6	326.6	579.9	917.7	1086.6	969.7	735.7	560.2	540.3
97.5°	144.2	239.6	334.9	358.7	781.2	1344.4	1626.0	1552.0	1404.2	1293.3	1255.5
100°	191.1	277.6	364.1	385.6	854.4	1479.4	1791.9	1797.3	1808.1	1816.3	1771.1
102.5°	231.1	311.8	392.4	412.5	888.0	1521.9	1838.9	1933.0	2121.4	2262.7	2224.1
105°	298.8	367.2	435.4	452.5	912.9	1526.7	1833.6	2044.8	2467.2	2783.9	2763.1
107.5°	368.3	432.0	495.7	511.6	917.6	1458.8	1729.4	2024.0	2613.1	3054.8	3059.9
110°	415.2	472.7	530.2	544.6	910.6	1398.6	1642.5	1971.9	2630.4	3124.3	3145.9



TEST NUMBER: P937081

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	461.2	516.0	570.9	584.6	910.9	1346.0	1563.5	1900.5	2574.6	3080.1	3113.2
115°	530.7	581.2	631.9	644.5	919.2	1285.7	1468.8	1793.5	2442.8	2929.8	2975.8
117.5°	599.3	645.3	691.2	702.6	936.3	1247.8	1403.6	1696.6	2282.6	2722.1	2773.2
120°	639.3	682.6	725.7	736.6	950.3	1235.1	1377.6	1645.2	2180.7	2582.3	2631.9
122.5°	678.4	722.0	765.6	776.5	970.2	1228.5	1357.6	1598.6	2080.9	2442.5	2491.4
125°	738.3	778.1	817.9	827.8	997.1	1223.0	1335.9	1540.7	1950.3	2257.5	2302.6
127.5°	787.0	827.2	867.3	877.3	1024.1	1219.8	1317.7	1493.6	1845.2	2109.0	2147.0
130°	813.0	856.3	899.4	910.3	1043.7	1221.7	1310.7	1467.2	1780.3	2015.1	2050.2
132.5°	839.9	883.2	926.3	937.2	1059.6	1223.0	1304.6	1444.7	1725.0	1935.2	1966.7
135°	879.9	919.2	958.7	968.5	1077.1	1221.9	1294.2	1411.6	1646.3	1822.3	1849.4
137.5°	920.7	959.7	998.7	1008.4	1103.1	1229.3	1292.5	1391.7	1590.1	1738.9	1761.2
140°	954.5	990.4	1026.4	1035.3	1119.0	1230.6	1286.4	1372.1	1543.5	1672.0	1692.8
142.5°	980.6	1013.9	1047.0	1055.3	1132.4	1235.0	1286.4	1361.7	1512.2	1625.2	1643.0
145°	1020.6	1049.5	1078.5	1085.8	1149.8	1235.0	1277.7	1339.3	1462.5	1554.8	1568.4
147.5°	1060.6	1088.8	1117.0	1124.0	1175.3	1243.5	1277.7	1326.2	1423.0	1495.7	1506.9
150°	1086.6	1112.1	1137.6	1144.0	1188.5	1248.0	1277.7	1318.6	1400.4	1461.8	1470.9
152.5°	1113.5	1132.8	1152.1	1156.9	1197.2	1250.9	1277.7	1312.6	1382.5	1434.9	1441.7
155°	1153.5	1167.8	1182.1	1185.6	1216.3	1257.3	1277.7	1305.5	1361.1	1402.8	1407.4
157.5°	1183.0	1196.9	1210.8	1214.3	1235.4	1263.6	1277.7	1299.3	1342.5	1374.9	1378.1
160°	1203.0	1213.8	1224.7	1227.4	1244.2	1266.5	1277.7	1296.2	1333.3	1361.1	1363.0
162.5°	1223.0	1231.1	1239.1	1241.2	1253.3	1269.6	1277.7	1293.3	1324.6	1348.0	1349.8
165°	1244.7	1252.0	1259.3	1261.2	1266.7	1274.1	1277.7	1288.9	1311.2	1328.1	1329.9
167.5°	1264.6	1268.1	1271.6	1272.5	1277.2	1283.3	1286.4	1293.7	1308.3	1319.4	1320.1
170°	1277.7	1281.2	1284.7	1285.6	1285.8	1286.2	1286.4	1293.7	1308.3	1319.4	1319.4
172.5°	1284.6	1285.4	1286.2	1286.4	1286.4	1286.4	1286.4	1292.2	1303.8	1312.5	1311.8
175°	1294.2	1294.2	1294.2	1294.2	1291.6	1288.2	1286.4	1290.0	1297.4	1302.9	1302.9
177.5°	1294.2	1294.2	1294.2	1294.2	1292.2	1289.5	1288.2	1291.1	1296.9	1301.2	1300.4
180°	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2



TEST NUMBER: P937081

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	584.5	584.5
2.5°	623.9	620.2
5°	802.5	806.2
7.5°	1080.6	1078.8
10°	1343.7	1360.7
12.5°	1535.4	1539.1
15°	1652.0	1659.4
17.5°	1697.1	1698.9
20°	1698.9	1695.2
22.5°	1678.2	1674.5
25°	1653.8	1652.0
27.5°	1631.2	1633.2
30°	1621.9	1627.5
32.5°	1621.9	1631.2
35°	1625.6	1635.1
37.5°	1623.8	1635.1
40°	1616.2	1629.4
42.5°	1595.6	1605.0
45°	1563.6	1574.9
47.5°	1522.2	1529.8
50°	1469.6	1477.1
52.5°	1403.9	1405.8
55°	1325.0	1332.4
57.5°	1240.4	1242.2
60°	1146.4	1152.0
62.5°	1046.8	1046.8
65°	941.6	945.3
67.5°	832.6	841.9
70°	721.7	723.6
72.5°	612.7	612.7
75°	499.9	501.7
77.5°	392.7	392.7
80°	291.3	293.2
82.5°	201.1	204.8
85°	125.9	125.9
87.5°	58.3	52.6
90°	33.0	33.0
92.5°	132.3	106.0
95°	460.8	381.4
97.5°	1104.2	952.9
100°	1590.9	1410.6
102.5°	2069.7	1915.3
105°	2680.1	2597.1
107.5°	3080.0	3100.0
110°	3232.4	3318.9



TEST NUMBER: P937081

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3246.0	3378.8
115°	3159.9	3344.1
117.5°	2977.4	3181.7
120°	2830.4	3028.8
122.5°	2687.1	2882.9
125°	2482.9	2663.1
127.5°	2299.1	2451.2
130°	2190.8	2331.4
132.5°	2092.5	2218.4
135°	1957.9	2066.4
137.5°	1849.9	1938.7
140°	1775.8	1858.8
142.5°	1714.5	1785.8
145°	1622.4	1676.3
147.5°	1551.7	1596.5
150°	1507.2	1543.5
152.5°	1469.2	1496.5
155°	1425.5	1443.6
157.5°	1390.9	1403.6
160°	1370.3	1377.6
162.5°	1356.7	1363.7
165°	1337.2	1344.6
167.5°	1323.3	1326.4
170°	1319.4	1319.4
172.5°	1309.1	1306.4
175°	1302.9	1302.9
177.5°	1297.3	1294.2
180°	1294.2	1294.2



TEST NUMBER: P937081
 CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-STD-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.52	2.28	2.59	3.36	4.83	14.71	15.47	15.78	16.55	18.02
	3H	2.21	2.90	3.29	3.99	5.47	16.55	17.23	17.62	18.32	19.80
	4H	2.51	3.16	3.60	4.25	5.74	17.19	17.84	18.28	18.93	20.42
	6H	2.75	3.36	3.85	4.44	5.95	17.62	18.22	18.72	19.31	20.81
	8H	2.82	3.39	3.92	4.50	5.99	17.74	18.31	18.84	19.42	20.92
	12H	2.83	3.38	3.94	4.48	6.00	17.81	18.35	18.92	19.45	20.97
4H	2H	8.73	9.38	9.83	10.47	11.96	14.97	15.62	16.07	16.71	18.20
	3H	10.29	10.83	11.39	11.94	13.45	17.01	17.56	18.12	18.67	20.17
	4H	10.38	10.88	11.49	11.98	13.51	17.78	18.28	18.89	19.38	20.91
	6H	10.38	10.81	11.50	11.94	13.45	18.32	18.75	19.43	19.87	21.39
	8H	10.36	10.76	11.47	11.88	13.41	18.48	18.88	19.60	20.00	21.53
	12H	10.31	10.67	11.44	11.80	13.34	18.57	18.94	19.70	20.06	21.60
8H	4H	11.82	12.22	12.93	13.34	14.87	17.83	18.23	18.95	19.35	20.88
	6H	12.05	12.39	13.19	13.55	15.08	18.46	18.79	19.60	19.95	21.48
	8H	12.07	12.36	13.22	13.50	15.05	18.68	18.97	19.83	20.11	21.66
	12H	12.03	12.29	13.18	13.43	15.01	18.82	19.08	19.97	20.22	21.80
12H	4H	11.96	12.32	13.09	13.45	14.99	17.78	18.14	18.91	19.27	20.81
	6H	12.31	12.61	13.46	13.74	15.29	18.44	18.73	19.59	19.87	21.42
	8H	12.38	12.63	13.53	13.77	15.36	18.67	18.93	19.82	20.06	21.65