

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938581

Luminaire Tested: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938581
REPORT IS A COMBINATION OF REPORTS P933624 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 28298.3 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 249.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938581
CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P938581

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39	33
2	86	79	72	67	78	72	66	62	59	55	51	47	44	42	36	34	32	27
3	78	69	61	55	71	63	56	51	51	47	43	41	37	35	31	29	27	22
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23	19
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	22	19	16
6	60	48	39	34	54	44	36	31	36	30	26	29	25	21	22	19	17	14
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15	12
8	51	39	31	25	46	35	28	24	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	27	21	18	21	17	15	17	14	11	9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4561	4561	4561
5°	4458	5273	6131
10°	4045	7688	10164
15°	3439	10047	12273
20°	2801	11646	12508
25°	2337	12190	12254
30°	1972	12270	12231
35°	1745	12069	12547
40°	1521	11808	12874
45°	1378	11618	12924
50°	1265	11447	12710
55°	1213	11196	12147
60°	1243	10709	11257
65°	1296	9966	10035
70°	1383	8698	8477
75°	1538	7098	6616
80°	1694	4929	4458
85°	1536	2620	2282

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12924 cd/sqm



TEST NUMBER: P938581

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.8	0.7
10°-20°	845.4	3.0
20°-30°	1478.8	5.2
30°-40°	1903.6	6.7
40°-50°	2126.3	7.5
50°-60°	2036.5	7.2
60°-70°	1613.9	5.7
70°-80°	949.0	3.4
80°-90°	273.6	1.0
90°-100°	1269.3	4.5
100°-110°	3337.1	11.8
110°-120°	3460.2	12.2
120°-130°	2775.5	9.8
130°-140°	2177.8	7.7
140°-150°	1671.5	5.9
150°-160°	1203.8	4.3
160°-170°	736.5	2.6
170°-180°	248.8	0.9
0°-30°	2514.9	8.9
0°-40°	4418.6	15.6
0°-60°	8581.3	30.3
0°-90°	11417.8	40.3
90°-120°	8066.6	28.5
90°-150°	14691.3	51.9
90°-180°	16880.0	59.7
0°-180°	28298.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1475	1475	1475	1475	1475	
5°	1437	1541	1736	1963	2034	133
15°	1076	1987	3348	4059	4187	300
25°	688	2252	3988	4163	4168	317
35°	465	2153	3755	3969	4125	290
45°	318	1716	3319	3803	3974	246
55°	228	1090	2817	3272	3362	207
65°	180	578	2091	2352	2385	179
75°	133	356	1148	1261	1266	139
85°	47	109	284	313	318	50
90°	18	49	133	66	66	18
95°	168	657	2186	1127	767	186
105°	601	911	3689	5601	5225	637
115°	1068	1297	2955	5895	6728	1055
125°	1486	1666	2688	4542	5358	1319
135°	1770	1949	2604	3666	4158	1370
145°	2054	2184	2571	3128	3373	1286
155°	2321	2386	2571	2822	2905	1066
165°	2504	2538	2571	2672	2705	707
175°	2604	2604	2588	2622	2622	247
180°	2604	2604	2604	2604	2604	



TEST NUMBER: P938581

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7
2.5°	1474.7	1474.7	1484.1	1488.9	1498.3	1503.1	1512.6	1522.0	1550.5	1555.3	1564.7
5°	1436.7	1455.6	1517.3	1541.0	1607.4	1697.5	1735.5	1797.1	1925.1	1963.1	1986.7
7.5°	1379.8	1422.5	1574.3	1612.2	1778.1	2015.2	2114.8	2247.6	2451.5	2551.0	2631.6
10°	1289.8	1379.8	1650.1	1740.1	2010.4	2370.8	2555.7	2740.6	3048.9	3186.3	3238.6
12.5°	1190.2	1337.1	1730.7	1854.0	2242.8	2769.1	2992.0	3195.9	3546.8	3731.7	3760.1
15°	1076.3	1275.5	1806.5	1986.7	2489.4	3101.1	3347.5	3598.9	3926.1	4058.9	4092.0
17.5°	976.8	1228.1	1877.7	2067.3	2679.0	3399.8	3651.1	3859.7	4125.2	4215.3	4239.1
20°	853.5	1152.2	1925.1	2171.6	2878.2	3617.8	3859.7	4020.9	4201.1	4258.0	4267.4
22.5°	763.4	1071.6	1953.6	2209.6	3010.9	3750.7	3954.6	4082.5	4205.8	4224.8	4229.5
25°	687.5	981.5	1948.8	2252.2	3124.7	3831.3	3987.7	4082.5	4153.7	4163.1	4163.1
27.5°	616.4	882.0	1929.8	2261.8	3210.1	3850.2	3973.5	4039.8	4073.1	4092.0	4092.0
30°	554.8	787.1	1882.4	2242.8	3248.0	3831.3	3930.8	3964.0	3997.2	4025.6	4039.8
32.5°	507.3	697.0	1811.3	2204.9	3252.7	3783.8	3855.0	3874.0	3921.3	3987.7	4011.4
35°	464.7	606.9	1730.7	2152.7	3224.4	3708.0	3755.3	3774.4	3869.2	3968.8	4001.9
37.5°	422.0	540.5	1626.4	2062.6	3181.7	3617.8	3651.1	3684.3	3831.3	3949.8	3987.7
40°	379.3	483.6	1503.1	1963.1	3115.3	3508.9	3537.2	3589.5	3783.8	3921.3	3959.2
42.5°	346.1	436.3	1370.4	1858.8	3029.9	3385.6	3428.2	3504.1	3726.9	3874.0	3916.6
45°	317.7	388.8	1228.1	1716.5	2920.8	3257.5	3319.2	3423.5	3660.5	3802.8	3840.7
47.5°	289.3	355.7	1081.1	1569.5	2802.3	3129.5	3210.1	3328.6	3570.5	3708.0	3741.1
50°	265.5	322.4	934.1	1413.0	2674.3	2992.0	3086.8	3210.1	3456.6	3584.7	3627.4
52.5°	246.6	294.0	796.6	1256.5	2527.3	2849.7	2958.8	3086.8	3319.2	3442.4	3470.8
55°	227.6	270.3	678.1	1090.5	2375.5	2698.0	2816.6	2939.9	3167.4	3271.7	3290.7
57.5°	218.1	251.3	578.5	934.1	2214.3	2527.3	2660.0	2773.9	2987.2	3067.8	3086.8
60°	203.9	237.0	502.6	801.4	2038.9	2366.1	2479.9	2593.7	2773.9	2840.2	2854.5
62.5°	189.7	227.6	445.7	673.3	1858.8	2176.4	2290.2	2394.5	2546.3	2593.7	2612.7
65°	180.2	218.1	403.0	578.5	1673.8	1977.3	2091.0	2181.2	2304.5	2351.8	2361.3
67.5°	170.7	208.7	369.9	497.9	1488.9	1778.1	1863.4	1948.8	2043.7	2091.0	2095.8
70°	156.4	199.1	341.4	440.9	1299.2	1550.5	1621.6	1711.7	1787.6	1811.3	1825.5
72.5°	147.0	184.9	322.4	398.3	1104.8	1332.4	1398.8	1451.0	1517.3	1541.0	1541.0
75°	132.7	166.0	303.5	355.7	905.6	1090.5	1147.5	1199.6	1251.7	1261.3	1247.1
77.5°	118.5	147.0	260.8	298.7	706.5	863.0	910.4	938.9	981.5	991.0	995.7
80°	99.6	128.1	203.9	232.4	512.1	635.4	668.6	692.3	730.2	730.2	739.7
82.5°	75.8	99.6	147.0	166.0	346.1	436.3	464.7	478.9	502.6	502.6	502.6
85°	47.4	61.6	94.8	109.1	208.7	265.5	284.5	289.3	308.2	313.0	313.0
87.5°	23.7	33.2	61.6	66.4	109.1	137.5	137.5	147.0	147.0	142.2	137.5
90°	17.5	31.5	45.5	48.9	76.9	114.1	132.8	118.1	88.5	66.4	66.4
92.5°	69.9	188.7	307.6	337.3	474.2	656.7	747.9	655.5	470.6	332.0	318.9
95°	167.7	385.2	602.7	657.1	1166.8	1846.5	2186.3	1950.9	1480.3	1127.2	1087.3
97.5°	290.1	481.9	673.8	721.8	1571.7	2705.0	3271.5	3122.8	2825.4	2602.2	2526.1
100°	384.4	558.4	732.4	776.0	1719.1	2976.6	3605.3	3616.2	3637.9	3654.3	3563.6
102.5°	464.9	627.2	789.5	830.1	1786.6	3062.0	3699.8	3889.3	4268.3	4552.6	4474.9
105°	601.2	738.7	876.2	910.6	1836.8	3071.7	3689.2	4114.1	4963.8	5601.1	5559.4
107.5°	741.0	869.2	997.3	1029.4	1846.1	2935.0	3479.5	4072.1	5257.4	6146.4	6156.5
110°	835.4	951.1	1066.8	1095.8	1832.1	2813.9	3304.8	3967.4	5292.4	6286.2	6329.7



TEST NUMBER: P938581

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	928.0	1038.3	1148.6	1176.2	1832.7	2708.0	3145.7	3823.8	5180.0	6197.1	6263.9
115°	1067.8	1169.6	1271.4	1296.8	1849.6	2586.7	2955.3	3608.5	4914.9	5894.8	5987.4
117.5°	1205.9	1298.3	1390.7	1413.8	1883.9	2510.7	2824.1	3413.7	4592.8	5477.1	5579.8
120°	1286.2	1373.3	1460.2	1482.0	1911.9	2485.1	2771.7	3310.4	4387.7	5195.7	5295.5
122.5°	1364.9	1452.7	1540.4	1562.4	1952.2	2471.7	2731.6	3216.6	4186.7	4914.3	5012.8
125°	1485.5	1565.5	1645.5	1665.5	2006.3	2460.7	2687.9	3099.9	3924.0	4542.0	4632.7
127.5°	1583.3	1664.1	1744.9	1765.1	2060.4	2454.3	2651.2	3005.0	3712.6	4243.3	4319.8
130°	1635.8	1722.8	1809.7	1831.5	2100.0	2458.1	2637.1	2952.1	3582.1	4054.5	4125.2
132.5°	1690.0	1776.9	1863.9	1885.7	2132.0	2460.6	2624.9	2906.9	3470.8	3893.8	3957.1
135°	1770.3	1849.5	1928.8	1948.6	2167.1	2458.4	2604.0	2840.1	3312.3	3666.5	3721.1
137.5°	1852.5	1931.0	2009.4	2029.0	2219.5	2473.4	2600.4	2800.0	3199.3	3498.8	3543.4
140°	1920.7	1992.9	2065.2	2083.2	2251.5	2475.9	2588.2	2760.6	3105.6	3364.2	3405.9
142.5°	1973.1	2039.9	2106.6	2123.4	2278.3	2484.9	2588.2	2739.7	3042.6	3269.8	3305.8
145°	2053.5	2111.8	2170.0	2184.5	2313.2	2484.9	2570.7	2694.6	2942.4	3128.2	3155.4
147.5°	2133.8	2190.5	2247.2	2261.4	2364.5	2502.0	2570.7	2668.3	2863.2	3009.4	3032.0
150°	2186.3	2237.6	2288.9	2301.7	2391.3	2511.0	2570.7	2653.1	2817.8	2941.3	2959.5
152.5°	2240.5	2279.3	2318.1	2327.8	2408.8	2516.8	2570.7	2641.1	2781.6	2887.1	2900.9
155°	2320.9	2349.7	2378.3	2385.5	2447.3	2529.6	2570.7	2626.7	2738.6	2822.5	2831.6
157.5°	2380.3	2408.2	2436.2	2443.2	2485.7	2542.3	2570.7	2614.3	2701.2	2766.5	2773.0
160°	2420.5	2442.2	2464.0	2469.4	2503.2	2548.2	2570.7	2608.0	2682.5	2738.5	2742.2
162.5°	2460.6	2477.0	2493.2	2497.3	2521.8	2554.4	2570.7	2602.2	2665.2	2712.3	2715.8
165°	2504.3	2519.1	2533.8	2537.6	2548.6	2563.4	2570.7	2593.3	2638.3	2672.1	2675.8
167.5°	2544.6	2551.6	2558.5	2560.3	2569.6	2582.0	2588.2	2603.0	2632.5	2654.6	2656.2
170°	2570.7	2577.7	2584.8	2586.5	2587.1	2587.8	2588.2	2603.0	2632.5	2654.6	2654.6
172.5°	2584.8	2586.2	2587.8	2588.2	2588.2	2588.2	2588.2	2599.9	2623.2	2640.7	2639.3
175°	2604.0	2604.0	2604.0	2604.0	2598.8	2591.8	2588.2	2595.6	2610.3	2621.5	2621.5
177.5°	2604.0	2604.0	2604.0	2604.0	2599.9	2594.5	2591.8	2597.5	2609.2	2617.9	2616.3
180°	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0	2604.0



TEST NUMBER: P938581

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1474.7	1474.7
2.5°	1574.3	1564.7
5°	2024.7	2034.2
7.5°	2726.4	2721.7
10°	3390.2	3432.9
12.5°	3874.0	3883.4
15°	4167.9	4186.8
17.5°	4281.7	4286.4
20°	4286.4	4277.0
22.5°	4234.3	4224.8
25°	4172.6	4167.9
27.5°	4115.8	4120.5
30°	4092.0	4106.2
32.5°	4092.0	4115.8
35°	4101.5	4125.2
37.5°	4096.8	4125.2
40°	4077.8	4111.0
42.5°	4025.6	4049.4
45°	3945.0	3973.5
47.5°	3840.7	3859.7
50°	3708.0	3726.9
52.5°	3542.0	3546.8
55°	3342.9	3361.8
57.5°	3129.5	3134.2
60°	2892.4	2906.6
62.5°	2641.1	2641.1
65°	2375.5	2385.1
67.5°	2100.6	2124.3
70°	1820.8	1825.5
72.5°	1545.8	1545.8
75°	1261.3	1266.0
77.5°	991.0	991.0
80°	735.0	739.7
82.5°	507.3	516.9
85°	317.7	317.7
87.5°	147.0	132.7
90°	66.4	66.4
92.5°	266.0	213.2
95°	927.2	767.2
97.5°	2221.6	1917.1
100°	3200.9	2838.1
102.5°	4164.2	3853.5
105°	5392.4	5225.4
107.5°	6196.9	6237.3
110°	6503.7	6677.7



TEST NUMBER: P938581

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	6531.1	6798.3
115°	6357.8	6728.3
117.5°	5990.7	6401.5
120°	5694.7	6094.0
122.5°	5406.6	5800.4
125°	4995.5	5358.3
127.5°	4625.8	4931.8
130°	4407.9	4690.6
132.5°	4210.2	4463.4
135°	3939.3	4157.6
137.5°	3722.1	3900.7
140°	3572.9	3739.9
142.5°	3449.4	3593.1
145°	3264.2	3373.0
147.5°	3122.1	3212.1
150°	3032.5	3105.6
152.5°	2956.0	3011.1
155°	2868.0	2904.6
157.5°	2798.5	2824.1
160°	2757.0	2771.7
162.5°	2729.8	2743.8
165°	2690.6	2705.3
167.5°	2662.4	2668.6
170°	2654.6	2654.6
172.5°	2633.9	2628.5
175°	2621.5	2621.5
177.5°	2610.2	2604.0
180°	2604.0	2604.0



TEST NUMBER: P938581
 CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.33	6.14	6.36	7.18	8.58	18.52	19.33	19.55	20.37	21.77
	3H	6.03	6.76	7.07	7.81	9.23	20.36	21.09	21.40	22.14	23.56
	4H	6.33	7.02	7.38	8.07	9.50	21.01	21.70	22.06	22.75	24.18
	6H	6.58	7.21	7.64	8.27	9.71	21.44	22.08	22.50	23.13	24.57
	8H	6.64	7.25	7.71	8.32	9.75	21.56	22.17	22.63	23.24	24.68
	12H	6.66	7.23	7.73	8.30	9.76	21.63	22.21	22.70	23.28	24.73
4H	2H	12.55	13.24	13.61	14.29	15.72	18.79	19.48	19.85	20.53	21.96
	3H	14.11	14.69	15.18	15.77	17.21	20.84	21.41	21.90	22.49	23.93
	4H	14.20	14.73	15.27	15.80	17.26	21.60	22.13	22.68	23.20	24.67
	6H	14.21	14.67	15.29	15.76	17.21	22.15	22.60	23.23	23.70	25.15
	8H	14.19	14.61	15.27	15.70	17.17	22.31	22.73	23.39	23.82	25.29
	12H	14.14	14.53	15.24	15.62	17.10	22.40	22.79	23.50	23.89	25.36
8H	4H	15.65	16.07	16.73	17.16	18.63	21.66	22.09	22.74	23.17	24.64
	6H	15.89	16.24	16.99	17.37	18.83	22.29	22.64	23.40	23.77	25.24
	8H	15.90	16.21	17.01	17.32	18.81	22.51	22.82	23.62	23.93	25.42
	12H	15.87	16.14	16.98	17.25	18.77	22.66	22.93	23.77	24.04	25.56
12H	4H	15.79	16.17	16.89	17.27	18.75	21.61	22.00	22.71	23.10	24.57
	6H	16.15	16.46	17.26	17.57	19.05	22.27	22.58	23.38	23.69	25.18
	8H	16.21	16.48	17.33	17.59	19.12	22.50	22.78	23.62	23.88	25.41