

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936998

Luminaire Tested: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936998
REPORT IS A COMBINATION OF REPORTS P933472 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5875.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936998
CATALOG NUMBER: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P936998

CATALOG NUMBER: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67	67	67	67
1	101	96	92	88	95	91	87	83	80	78	75	71	69	67	62	61	59	55	55	55	55
2	91	83	76	71	86	78	72	67	70	65	61	61	58	55	54	51	49	45	45	45	45
3	83	72	64	58	77	68	61	55	61	55	50	54	49	45	47	44	41	37	37	37	37
4	75	64	55	48	70	60	52	46	53	47	42	47	42	38	42	38	34	31	31	31	31
5	69	56	47	41	64	53	45	39	47	41	36	42	37	32	37	33	29	26	26	26	26
6	63	50	41	35	59	47	39	34	42	36	31	38	32	28	33	29	25	23	23	23	23
7	58	45	36	30	55	43	35	29	38	32	27	34	29	24	30	26	22	20	20	20	20
8	54	41	32	27	51	39	31	26	35	28	24	31	26	22	27	23	20	17	17	17	17
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17	15	15	15	15
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4731	4731	4731
5°	4617	5465	6360
10°	4183	7960	10544
15°	3552	10392	12732
20°	2889	12034	12976
25°	2407	12584	12713
30°	2027	12653	12689
35°	1789	12434	13016
40°	1557	12151	13355
45°	1407	11940	13407
50°	1288	11749	13186
55°	1229	11471	12601
60°	1254	10954	11678
65°	1298	10172	10410
70°	1373	8854	8795
75°	1505	7200	6863
80°	1610	4976	4625
85°	1358	2626	2368

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13407 cd/sqm



TEST NUMBER: P936998

CATALOG NUMBER: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.0	1.1
10°-20°	292.3	5.0
20°-30°	511.4	8.7
30°-40°	658.3	11.2
40°-50°	735.3	12.5
50°-60°	704.2	12.0
60°-70°	558.1	9.5
70°-80°	328.2	5.6
80°-90°	92.3	1.6
90°-100°	145.0	2.5
100°-110°	381.4	6.5
110°-120°	395.4	6.7
120°-130°	317.2	5.4
130°-140°	248.9	4.2
140°-150°	191.0	3.3
150°-160°	137.6	2.3
160°-170°	84.2	1.4
170°-180°	28.4	0.5
0°-30°	869.7	14.8
0°-40°	1527.9	26.0
0°-60°	2967.4	50.5
0°-90°	3946.0	67.2
90°-120°	921.8	15.7
90°-150°	1678.9	28.6
90°-180°	1929.0	32.8
0°-180°	5875.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	510	510	510	510	510	
5°	497	533	600	679	703	46
15°	372	687	1158	1404	1448	104
25°	238	779	1379	1440	1441	110
35°	161	744	1299	1372	1426	100
45°	110	594	1148	1315	1374	85
55°	79	377	974	1131	1162	72
65°	62	200	723	813	825	62
75°	46	123	397	436	438	48
85°	16	38	98	108	110	17
90°	2	6	15	8	8	3
95°	19	75	250	129	88	21
105°	69	104	422	640	597	73
115°	122	148	338	674	769	120
125°	170	190	307	519	612	151
135°	202	223	298	419	475	157
145°	235	250	294	358	386	147
155°	265	273	294	323	332	122
165°	286	290	294	305	309	81
175°	298	298	296	300	300	28
180°	298	298	298	298	298	



TEST NUMBER: P936998

CATALOG NUMBER: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	509.9	509.9	509.9	509.9	509.9	509.9	509.9	509.9	509.9	509.9	509.9
2.5°	509.9	509.9	513.2	514.8	518.1	519.8	523.1	526.4	536.1	537.8	541.1
5°	496.8	503.4	524.7	532.9	555.8	587.0	600.1	621.4	665.7	678.8	687.0
7.5°	477.1	491.9	544.4	557.5	614.8	696.8	731.3	777.2	847.7	882.1	910.0
10°	445.9	477.1	570.5	601.7	695.2	819.8	883.7	947.7	1054.3	1101.8	1119.9
12.5°	411.5	462.4	598.5	641.1	775.6	957.6	1034.6	1105.1	1226.5	1290.4	1300.2
15°	372.2	441.1	624.7	687.0	860.8	1072.3	1157.6	1244.5	1357.7	1403.5	1415.0
17.5°	337.8	424.7	649.3	714.9	926.4	1175.6	1262.5	1334.7	1426.5	1457.7	1465.8
20°	295.2	398.5	665.7	751.0	995.3	1251.1	1334.7	1390.4	1452.7	1472.4	1475.7
22.5°	264.0	370.5	675.5	764.1	1041.2	1296.9	1367.5	1411.7	1454.4	1461.0	1462.5
25°	237.8	339.4	673.9	778.8	1080.5	1324.8	1379.0	1411.7	1436.3	1439.6	1439.6
27.5°	213.2	304.9	667.4	782.1	1110.0	1331.4	1374.0	1397.0	1408.4	1415.0	1415.0
30°	191.9	272.2	651.0	775.6	1123.2	1324.8	1359.2	1370.7	1382.2	1392.1	1397.0
32.5°	175.5	241.0	626.4	762.4	1124.8	1308.4	1333.1	1339.5	1356.0	1379.0	1387.1
35°	160.7	209.9	598.5	744.4	1114.9	1282.2	1298.6	1305.1	1337.9	1372.4	1383.8
37.5°	145.9	186.9	562.4	713.3	1100.2	1251.1	1262.5	1274.0	1324.8	1365.8	1379.0
40°	131.2	167.2	519.8	678.8	1077.2	1213.3	1223.2	1241.2	1308.4	1356.0	1369.1
42.5°	119.7	150.9	473.8	642.7	1047.7	1170.7	1185.5	1211.7	1288.8	1339.5	1354.4
45°	109.9	134.5	424.7	593.5	1010.0	1126.5	1147.8	1183.8	1265.8	1315.0	1328.1
47.5°	100.0	123.0	373.8	542.7	969.0	1082.2	1110.0	1151.1	1234.6	1282.2	1293.7
50°	91.9	111.5	323.0	488.6	924.7	1034.6	1067.5	1110.0	1195.3	1239.5	1254.4
52.5°	85.3	101.6	275.5	434.5	873.9	985.4	1023.2	1067.5	1147.8	1190.4	1200.2
55°	78.7	93.4	234.5	377.1	821.4	933.0	973.9	1016.6	1095.3	1131.3	1137.9
57.5°	75.4	86.9	200.0	323.0	765.7	873.9	919.9	959.2	1033.0	1060.9	1067.5
60°	70.5	82.0	173.8	277.1	705.0	818.2	857.6	896.9	959.2	982.2	987.0
62.5°	65.6	78.7	154.2	232.9	642.7	752.6	792.0	828.0	880.5	896.9	903.4
65°	62.3	75.4	139.3	200.0	578.8	683.7	723.1	754.3	796.9	813.3	816.6
67.5°	59.0	72.2	127.9	172.2	514.8	614.8	644.4	673.9	706.7	723.1	724.7
70°	54.1	68.9	118.0	152.5	449.2	536.1	560.8	591.9	618.1	626.4	631.3
72.5°	50.9	64.0	111.5	137.7	382.1	460.8	483.7	501.7	524.7	532.9	532.9
75°	45.9	57.4	104.9	123.0	313.2	377.1	396.8	414.8	432.9	436.1	431.2
77.5°	41.0	50.9	90.2	103.3	244.3	298.5	314.8	324.6	339.4	342.6	344.3
80°	34.4	44.3	70.5	80.3	177.0	219.7	231.2	239.3	252.5	252.5	255.8
82.5°	26.3	34.4	50.9	57.4	119.7	150.9	160.7	165.6	173.8	173.8	173.8
85°	16.4	21.3	32.8	37.7	72.2	91.9	98.4	100.0	106.6	108.2	108.2
87.5°	8.2	11.4	21.3	23.0	37.7	47.6	47.6	50.9	50.9	49.2	47.6
90°	2.0	3.6	5.2	5.6	8.8	13.1	15.2	13.5	10.1	7.6	7.6
92.5°	7.9	21.5	35.2	38.6	54.2	75.0	85.5	74.9	53.8	38.0	36.4
95°	19.2	44.0	68.9	75.1	133.3	211.0	249.8	222.9	169.1	128.8	124.2
97.5°	33.1	55.0	76.9	82.5	179.6	309.1	373.8	356.9	322.9	297.4	288.7
100°	43.9	63.8	83.7	88.7	196.4	340.1	412.0	413.3	415.8	417.6	407.3
102.5°	53.1	71.7	90.2	94.9	204.2	349.9	422.8	444.5	487.8	520.3	511.3
105°	68.7	84.4	100.1	104.1	209.9	351.1	421.6	470.2	567.3	640.1	635.4
107.5°	84.7	99.3	114.0	117.6	211.0	335.5	397.7	465.4	600.9	702.4	703.6
110°	95.4	108.6	121.9	125.2	209.4	321.6	377.7	453.4	604.8	718.4	723.4



TEST NUMBER: P936998

CATALOG NUMBER: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	106.0	118.6	131.2	134.4	209.4	309.5	359.5	437.0	592.0	708.2	715.9
115°	122.0	133.6	145.3	148.2	211.3	295.5	337.7	412.3	561.6	673.6	684.2
117.5°	137.8	148.4	158.9	161.5	215.3	286.9	322.8	390.1	524.8	625.9	637.6
120°	147.0	157.0	166.9	169.4	218.5	284.0	316.8	378.3	501.5	593.8	605.2
122.5°	156.0	166.1	176.1	178.6	223.1	282.5	312.1	367.5	478.5	561.6	572.9
125°	169.8	178.9	188.0	190.3	229.3	281.2	307.2	354.3	448.5	519.1	529.5
127.5°	180.9	190.2	199.4	201.7	235.5	280.5	303.0	343.4	424.2	484.9	493.6
130°	186.9	196.9	206.8	209.3	240.0	280.9	301.4	337.4	409.4	463.4	471.4
132.5°	193.1	203.1	213.0	215.5	243.7	281.2	300.0	332.2	396.6	445.0	452.2
135°	202.3	211.3	220.4	222.7	247.7	280.9	297.6	324.5	378.5	419.0	425.2
137.5°	211.7	220.6	229.7	231.9	253.7	282.7	297.2	320.0	365.6	399.8	404.9
140°	219.5	227.7	236.0	238.1	257.3	282.9	295.7	315.5	354.9	384.5	389.2
142.5°	225.5	233.1	240.7	242.6	260.4	283.9	295.7	313.1	347.7	373.6	377.7
145°	234.7	241.3	248.0	249.6	264.3	284.0	293.8	307.9	336.2	357.5	360.6
147.5°	243.9	250.4	256.8	258.4	270.3	286.0	293.8	304.9	327.2	343.9	346.5
150°	249.8	255.6	261.5	263.0	273.3	286.9	293.8	303.2	322.0	336.1	338.3
152.5°	256.0	260.5	264.9	266.0	275.3	287.6	293.8	301.8	317.9	329.9	331.5
155°	265.2	268.5	271.8	272.6	279.7	289.1	293.8	300.2	313.0	322.6	323.6
157.5°	272.0	275.2	278.4	279.2	284.0	290.5	293.8	298.7	308.7	316.2	317.0
160°	276.6	279.1	281.6	282.2	286.0	291.2	293.8	298.1	306.6	313.0	313.4
162.5°	281.2	283.0	284.9	285.4	288.2	292.0	293.8	297.4	304.6	310.0	310.4
165°	286.2	287.9	289.6	290.0	291.3	292.9	293.8	296.3	301.5	305.3	305.7
167.5°	290.8	291.6	292.3	292.5	293.6	295.1	295.7	297.5	300.9	303.4	303.6
170°	293.8	294.6	295.4	295.5	295.6	295.7	295.7	297.5	300.9	303.4	303.4
172.5°	295.4	295.5	295.7	295.7	295.7	295.7	295.7	297.1	299.7	301.7	301.6
175°	297.6	297.6	297.6	297.6	297.0	296.1	295.7	296.6	298.4	299.6	299.6
177.5°	297.6	297.6	297.6	297.6	297.1	296.5	296.2	296.9	298.3	299.2	299.0
180°	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6



TEST NUMBER: P936998

CATALOG NUMBER: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	509.9	509.9
2.5°	544.4	541.1
5°	700.1	703.4
7.5°	942.8	941.2
10°	1172.3	1187.1
12.5°	1339.5	1342.8
15°	1441.3	1447.8
17.5°	1480.6	1482.3
20°	1482.3	1479.0
22.5°	1464.2	1461.0
25°	1442.8	1441.3
27.5°	1423.2	1424.8
30°	1415.0	1420.0
32.5°	1415.0	1423.2
35°	1418.3	1426.5
37.5°	1416.7	1426.5
40°	1410.1	1421.5
42.5°	1392.1	1400.2
45°	1364.2	1374.0
47.5°	1328.1	1334.7
50°	1282.2	1288.8
52.5°	1224.8	1226.5
55°	1155.9	1162.5
57.5°	1082.2	1083.8
60°	1000.2	1005.1
62.5°	913.3	913.3
65°	821.4	824.7
67.5°	726.4	734.6
70°	629.7	631.3
72.5°	534.5	534.5
75°	436.1	437.8
77.5°	342.6	342.6
80°	254.2	255.8
82.5°	175.5	178.7
85°	109.9	109.9
87.5°	50.9	45.9
90°	7.6	7.6
92.5°	30.4	24.3
95°	105.9	87.7
97.5°	253.9	219.1
100°	365.8	324.3
102.5°	475.9	440.4
105°	616.3	597.2
107.5°	708.1	712.8
110°	743.2	763.1



TEST NUMBER: P936998

CATALOG NUMBER: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	746.4	776.9
115°	726.6	768.9
117.5°	684.6	731.6
120°	650.8	696.4
122.5°	617.9	662.9
125°	570.8	612.3
127.5°	528.6	563.6
130°	503.8	536.1
132.5°	481.1	510.1
135°	450.2	475.1
137.5°	425.3	445.7
140°	408.3	427.4
142.5°	394.2	410.7
145°	373.1	385.5
147.5°	356.8	367.1
150°	346.6	354.9
152.5°	337.8	344.1
155°	327.8	332.0
157.5°	319.9	322.8
160°	315.1	316.8
162.5°	312.0	313.6
165°	307.5	309.2
167.5°	304.3	304.9
170°	303.4	303.4
172.5°	301.0	300.4
175°	299.6	299.6
177.5°	298.4	297.6
180°	297.6	297.6



TEST NUMBER: P936998
 CATALOG NUMBER: SQ4-FB-050U-125D-B35-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.82	8.91	8.60	9.73	10.73	20.96	22.05	21.74	22.87	23.87
	3H	8.54	9.53	9.34	10.35	11.38	22.80	23.79	23.60	24.61	25.64
	4H	8.85	9.79	9.67	10.62	11.66	23.44	24.38	24.26	25.21	26.25
	6H	9.11	9.98	9.94	10.82	11.87	23.87	24.74	24.70	25.58	26.63
	8H	9.19	10.02	10.03	10.87	11.93	24.00	24.82	24.83	25.68	26.73
	12H	9.22	10.00	10.06	10.86	11.94	24.07	24.85	24.91	25.71	26.79
4H	2H	15.04	15.97	15.86	16.80	17.84	21.26	22.20	22.08	23.03	24.07
	3H	16.63	17.41	17.46	18.28	19.33	23.31	24.10	24.15	24.96	26.02
	4H	16.73	17.45	17.58	18.31	19.40	24.08	24.80	24.93	25.66	26.74
	6H	16.76	17.38	17.62	18.27	19.35	24.62	25.24	25.48	26.13	27.21
	8H	16.74	17.32	17.61	18.21	19.31	24.78	25.36	25.65	26.25	27.35
	12H	16.71	17.24	17.60	18.14	19.24	24.88	25.40	25.77	26.31	27.41
8H	4H	18.19	18.77	19.05	19.65	20.75	24.16	24.74	25.03	25.63	26.73
	6H	18.44	18.93	19.34	19.85	20.95	24.79	25.27	25.68	26.20	27.30
	8H	18.46	18.89	19.37	19.81	20.93	25.00	25.43	25.91	26.35	27.47
	12H	18.44	18.82	19.35	19.73	20.90	25.15	25.53	26.06	26.44	27.61
12H	4H	18.34	18.87	19.23	19.77	20.87	24.13	24.65	25.01	25.55	26.66
	6H	18.70	19.13	19.60	20.05	21.16	24.78	25.21	25.68	26.12	27.24
	8H	18.78	19.16	19.69	20.07	21.24	25.01	25.39	25.92	26.30	27.47