

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937198

Luminaire Tested: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937198
REPORT IS A COMBINATION OF REPORTS P933502 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5234.5 lumens
Efficiency: N/A
Efficacy: 123.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 42.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937198
CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P937198

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	96	92	88	84	88	84	80	77	70	67	65	57	55	53	44	43	42	37	37	37	37
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	38	36	35	30	30	30	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25	25	25	25
4	72	61	53	47	65	56	49	43	46	41	37	38	34	31	30	27	24	21	21	21	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	17	17	17	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13	13	13	13
8	51	39	31	26	47	36	29	24	30	24	21	25	20	17	20	16	14	11	11	11	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10	10	10	10
10	44	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2797	2797	2797
5°	2729	3230	3759
10°	2473	4704	6232
15°	2099	6142	7524
20°	1707	7112	7668
25°	1422	7437	7513
30°	1198	7478	7499
35°	1058	7348	7692
40°	919	7181	7893
45°	831	7056	7923
50°	761	6943	7792
55°	726	6780	7447
60°	742	6473	6902
65°	767	6011	6152
70°	812	5232	5198
75°	889	4255	4056
80°	950	2940	2734
85°	803	1551	1398

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7923 cd/sqm



TEST NUMBER: P937198

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	0.7
10°-20°	172.8	3.3
20°-30°	302.2	5.8
30°-40°	389.0	7.4
40°-50°	434.5	8.3
50°-60°	416.2	8.0
60°-70°	329.8	6.3
70°-80°	193.9	3.7
80°-90°	55.6	1.1
90°-100°	218.2	4.2
100°-110°	573.6	11.0
110°-120°	594.7	11.4
120°-130°	477.1	9.1
130°-140°	374.3	7.2
140°-150°	287.3	5.5
150°-160°	206.9	4.0
160°-170°	126.6	2.4
170°-180°	42.8	0.8
0°-30°	514.0	9.8
0°-40°	903.0	17.3
0°-60°	1753.7	33.5
0°-90°	2333.0	44.6
90°-120°	1386.5	26.5
90°-150°	2525.2	48.2
90°-180°	2901.0	55.4
0°-180°	5234.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	301	301	301	301	301	
5°	294	315	355	401	416	27
15°	220	406	684	830	856	61
25°	140	460	815	851	852	65
35°	95	440	767	811	843	59
45°	65	351	678	777	812	50
55°	46	223	576	669	687	42
65°	37	118	427	481	487	37
75°	27	73	234	258	259	28
85°	10	22	58	64	65	10
90°	3	8	23	11	11	3
95°	29	113	376	194	132	32
105°	103	156	634	963	898	110
115°	184	223	508	1013	1156	181
125°	255	286	462	781	921	227
135°	304	335	448	630	715	235
145°	353	376	442	538	580	221
155°	399	410	442	485	499	183
165°	430	436	442	459	465	121
175°	448	448	445	451	451	42
180°	448	448	448	448	448	



TEST NUMBER: P937198
 CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4
2.5°	301.4	301.4	303.3	304.3	306.2	307.2	309.1	311.0	316.9	317.8	319.8
5°	293.6	297.5	310.1	314.9	328.5	346.9	354.7	367.3	393.4	401.2	406.0
7.5°	282.0	290.7	321.7	329.5	363.4	411.8	432.2	459.3	501.0	521.3	537.8
10°	263.6	282.0	337.2	355.6	410.9	484.5	522.3	560.1	623.1	651.2	661.8
12.5°	243.2	273.3	353.7	378.9	458.3	565.9	611.4	653.1	724.8	762.6	768.4
15°	220.0	260.7	369.2	406.0	508.7	633.7	684.1	735.5	802.3	829.5	836.2
17.5°	199.6	251.0	383.7	422.5	547.5	694.8	746.1	788.8	843.0	861.4	866.3
20°	174.4	235.5	393.4	443.8	588.2	739.3	788.8	821.7	858.5	870.2	872.1
22.5°	156.0	219.0	399.2	451.6	615.3	766.5	808.1	834.3	859.5	863.4	864.3
25°	140.5	200.6	398.3	460.3	638.6	783.0	814.9	834.3	848.8	850.8	850.8
27.5°	126.0	180.2	394.4	462.2	656.0	786.8	812.0	825.6	832.4	836.2	836.2
30°	113.4	160.9	384.7	458.3	663.8	783.0	803.3	810.1	816.9	822.7	825.6
32.5°	103.7	142.4	370.2	450.6	664.7	773.3	787.8	791.7	801.4	814.9	819.8
35°	95.0	124.0	353.7	439.9	658.9	757.8	767.4	771.3	790.7	811.1	817.8
37.5°	86.2	110.5	332.4	421.5	650.2	739.3	746.1	752.9	783.0	807.2	814.9
40°	77.5	98.8	307.2	401.2	636.6	717.1	722.9	733.5	773.3	801.4	809.1
42.5°	70.7	89.1	280.0	379.8	619.2	691.9	700.6	716.1	761.6	791.7	800.4
45°	64.9	79.5	251.0	350.8	596.9	665.7	678.3	699.6	748.1	777.1	784.9
47.5°	59.1	72.7	220.9	320.7	572.7	639.5	656.0	680.2	729.7	757.8	764.5
50°	54.3	65.9	190.9	288.8	546.5	611.4	630.8	656.0	706.4	732.6	741.3
52.5°	50.4	60.1	162.8	256.8	516.5	582.4	604.7	630.8	678.3	703.5	709.3
55°	46.5	55.2	138.6	222.9	485.5	551.4	575.6	600.8	647.3	668.6	672.5
57.5°	44.6	51.4	118.2	190.9	452.5	516.5	543.6	566.9	610.5	626.9	630.8
60°	41.7	48.4	102.7	163.8	416.7	483.5	506.8	530.0	566.9	580.4	583.3
62.5°	38.8	46.5	91.1	137.6	379.8	444.8	468.0	489.3	520.4	530.0	533.9
65°	36.8	44.6	82.4	118.2	342.1	404.1	427.3	445.7	470.9	480.6	482.6
67.5°	34.9	42.6	75.6	101.7	304.3	363.4	380.8	398.3	417.6	427.3	428.3
70°	32.0	40.7	69.8	90.1	265.5	316.9	331.4	349.8	365.3	370.2	373.1
72.5°	30.0	37.8	65.9	81.4	225.8	272.3	285.9	296.5	310.1	314.9	314.9
75°	27.1	33.9	62.0	72.7	185.1	222.9	234.5	245.2	255.8	257.8	254.8
77.5°	24.2	30.0	53.3	61.0	144.4	176.4	186.0	191.9	200.6	202.5	203.5
80°	20.3	26.2	41.7	47.5	104.7	129.8	136.6	141.5	149.2	149.2	151.2
82.5°	15.5	20.3	30.0	33.9	70.7	89.1	95.0	97.9	102.7	102.7	102.7
85°	9.7	12.6	19.4	22.3	42.6	54.3	58.1	59.1	63.0	64.0	64.0
87.5°	4.8	6.8	12.6	13.6	22.3	28.1	28.1	30.0	30.0	29.1	28.1
90°	3.0	5.4	7.8	8.4	13.3	19.7	22.9	20.3	15.2	11.4	11.4
92.5°	12.0	32.5	52.8	57.9	81.5	112.9	128.6	112.7	80.9	57.1	54.8
95°	28.9	66.3	103.7	113.0	200.6	317.3	375.8	335.3	254.4	193.7	186.8
97.5°	49.9	82.8	115.8	124.0	270.2	464.9	562.3	536.7	485.7	447.3	434.2
100°	66.1	95.9	125.9	133.3	295.4	511.6	619.7	621.5	625.3	628.1	612.5
102.5°	79.9	107.8	135.7	142.6	307.1	526.4	636.0	668.5	733.6	782.5	769.1
105°	103.3	126.9	150.6	156.5	315.7	528.0	634.1	707.2	853.2	962.7	955.5
107.5°	127.3	149.4	171.4	176.9	317.3	504.5	598.1	699.9	903.6	1056.4	1058.1
110°	143.6	163.5	183.4	188.4	314.9	483.6	568.0	681.9	909.6	1080.4	1087.9



TEST NUMBER: P937198

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	159.5	178.5	197.4	202.1	315.0	465.5	540.7	657.3	890.3	1065.1	1076.7
115°	183.5	201.0	218.5	222.9	317.9	444.6	507.9	620.3	844.8	1013.2	1029.1
117.5°	207.3	223.2	239.1	243.0	323.8	431.5	485.4	586.7	789.3	941.4	959.0
120°	221.1	236.0	251.0	254.8	328.6	427.1	476.4	569.0	754.2	893.0	910.2
122.5°	234.6	249.7	264.7	268.5	335.5	424.8	469.5	552.8	719.6	844.7	861.6
125°	255.3	269.1	282.9	286.2	344.9	423.0	462.0	532.9	674.5	780.7	796.3
127.5°	272.2	286.0	299.9	303.4	354.2	421.9	455.7	516.6	638.2	729.4	742.5
130°	281.2	296.1	311.0	314.8	361.0	422.5	453.3	507.5	615.7	696.9	709.0
132.5°	290.5	305.4	320.4	324.1	366.5	423.0	451.2	499.6	596.6	669.3	680.1
135°	304.3	317.8	331.5	334.9	372.5	422.6	447.6	488.2	569.4	630.2	639.6
137.5°	318.4	331.9	345.4	348.7	381.5	425.2	447.0	481.3	549.9	601.4	609.0
140°	330.1	342.5	354.9	358.0	387.0	425.6	444.9	474.5	533.7	578.2	585.4
142.5°	339.2	350.6	362.0	364.9	391.6	427.1	444.9	470.9	523.0	562.0	568.2
145°	352.9	363.0	373.0	375.5	397.6	427.1	441.9	463.2	505.7	537.7	542.3
147.5°	366.8	376.5	386.2	388.7	406.4	430.0	441.9	458.6	492.2	517.3	521.1
150°	375.8	384.6	393.4	395.6	411.0	431.6	441.9	456.0	484.3	505.5	508.6
152.5°	385.1	391.8	398.5	400.1	414.1	432.6	441.9	454.0	478.1	496.2	498.6
155°	398.9	403.9	408.7	410.0	420.6	434.8	441.9	451.5	470.6	485.1	486.6
157.5°	409.1	414.0	418.8	420.0	427.2	437.0	441.9	449.3	464.2	475.5	476.6
160°	416.0	419.8	423.5	424.4	430.2	438.0	441.9	448.3	461.1	470.7	471.3
162.5°	423.0	425.8	428.6	429.3	433.4	439.1	441.9	447.3	458.0	466.2	466.8
165°	430.4	432.9	435.5	436.1	438.1	440.6	441.9	445.7	453.5	459.3	460.0
167.5°	437.3	438.5	439.7	440.0	441.7	443.8	444.9	447.4	452.5	456.3	456.6
170°	441.9	443.0	444.3	444.6	444.7	444.8	444.9	447.4	452.5	456.3	456.3
172.5°	444.3	444.6	444.8	444.9	444.9	444.9	444.9	446.9	450.9	453.9	453.7
175°	447.6	447.6	447.6	447.6	446.7	445.4	444.9	446.1	448.6	450.6	450.6
177.5°	447.6	447.6	447.6	447.6	446.9	445.9	445.4	446.4	448.5	450.0	449.7
180°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6



TEST NUMBER: P937198

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	301.4	301.4
2.5°	321.7	319.8
5°	413.8	415.7
7.5°	557.2	556.2
10°	692.8	701.6
12.5°	791.7	793.6
15°	851.8	855.6
17.5°	875.0	876.0
20°	876.0	874.0
22.5°	865.3	863.4
25°	852.7	851.8
27.5°	841.1	842.1
30°	836.2	839.2
32.5°	836.2	841.1
35°	838.2	843.0
37.5°	837.2	843.0
40°	833.3	840.1
42.5°	822.7	827.5
45°	806.2	812.0
47.5°	784.9	788.8
50°	757.8	761.6
52.5°	723.8	724.8
55°	683.1	687.0
57.5°	639.5	640.5
60°	591.1	594.0
62.5°	539.7	539.7
65°	485.5	487.4
67.5°	429.3	434.1
70°	372.1	373.1
72.5°	315.9	315.9
75°	257.8	258.7
77.5°	202.5	202.5
80°	150.2	151.2
82.5°	103.7	105.6
85°	64.9	64.9
87.5°	30.0	27.1
90°	11.4	11.4
92.5°	45.7	36.6
95°	159.4	131.9
97.5°	381.9	329.6
100°	550.2	487.8
102.5°	715.7	662.3
105°	926.8	898.2
107.5°	1065.1	1072.1
110°	1117.8	1147.8



TEST NUMBER: P937198

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1122.6	1168.5
115°	1092.8	1156.5
117.5°	1029.7	1100.3
120°	978.8	1047.4
122.5°	929.3	997.0
125°	858.6	920.9
127.5°	795.1	847.7
130°	757.7	806.2
132.5°	723.6	767.2
135°	677.1	714.6
137.5°	639.7	670.5
140°	614.2	642.8
142.5°	592.8	617.5
145°	561.1	579.8
147.5°	536.6	552.1
150°	521.2	533.8
152.5°	508.0	517.5
155°	492.9	499.2
157.5°	481.0	485.4
160°	473.8	476.4
162.5°	469.2	471.6
165°	462.5	465.0
167.5°	457.7	458.7
170°	456.3	456.3
172.5°	452.7	451.7
175°	450.6	450.6
177.5°	448.6	447.6
180°	447.6	447.6



TEST NUMBER: P937198
 CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.05	4.89	5.04	5.91	7.25	17.19	18.03	18.18	19.04	20.39
	3H	4.75	5.51	5.76	6.53	7.90	19.01	19.77	20.01	20.79	22.15
	4H	5.05	5.77	6.07	6.79	8.17	19.64	20.37	20.66	21.39	22.76
	6H	5.30	5.96	6.33	6.99	8.38	20.06	20.73	21.09	21.75	23.14
	8H	5.37	6.00	6.40	7.05	8.43	20.17	20.81	21.21	21.85	23.23
	12H	5.38	5.99	6.42	7.03	8.43	20.24	20.84	21.27	21.88	23.28
4H	2H	11.24	11.96	12.26	12.98	14.35	17.46	18.18	18.48	19.21	20.58
	3H	12.80	13.41	13.84	14.46	15.85	19.49	20.09	20.52	21.15	22.53
	4H	12.90	13.45	13.94	14.50	15.90	20.25	20.80	21.29	21.84	23.25
	6H	12.91	13.39	13.96	14.45	15.86	20.77	21.25	21.82	22.32	23.72
	8H	12.89	13.33	13.94	14.39	15.81	20.93	21.37	21.98	22.43	23.85
	12H	12.84	13.25	13.91	14.32	15.74	21.01	21.42	22.08	22.49	23.91
8H	4H	14.33	14.78	15.38	15.84	17.26	20.31	20.75	21.36	21.81	23.23
	6H	14.57	14.94	15.65	16.05	17.46	20.92	21.29	22.00	22.39	23.81
	8H	14.59	14.92	15.68	16.00	17.44	21.13	21.46	22.22	22.54	23.98
	12H	14.56	14.85	15.65	15.93	17.40	21.27	21.56	22.36	22.64	24.11
12H	4H	14.47	14.88	15.54	15.95	17.37	20.26	20.66	21.33	21.74	23.16
	6H	14.83	15.15	15.91	16.24	17.67	20.90	21.23	21.99	22.31	23.75
	8H	14.90	15.18	15.99	16.26	17.74	21.13	21.41	22.21	22.49	23.97