

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937397

Luminaire Tested: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937397
REPORT IS A COMBINATION OF REPORTS P933496 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20544.7 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 186
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937397
CATALOG NUMBER: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P937397

CATALOG NUMBER: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58			58
1	99	94	90	86	92	88	84	81	76	73	71	65	63	61	55	53	52	47			47
2	89	82	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43	38			38
3	81	71	63	57	75	66	59	54	57	52	47	49	45	41	41	38	36	32			32
4	74	62	54	48	68	58	51	45	50	45	40	43	39	35	36	33	30	27			27
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	33	29	26	23			23
6	62	49	41	35	57	46	38	33	40	34	29	34	29	26	29	25	22	19			19
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19	17			17
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17	15			15
9	49	36	28	23	46	34	27	22	30	24	20	26	21	17	22	18	15	13			13
10	46	33	26	21	43	31	24	20	27	22	18	24	19	16	20	16	14	12			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4732	4732	4732
5°	4624	5471	6361
10°	4197	7977	10545
15°	3568	10424	12733
20°	2906	12082	12977
25°	2425	12647	12713
30°	2046	12730	12689
35°	1810	12522	13017
40°	1578	12251	13357
45°	1430	12053	13409
50°	1313	11876	13187
55°	1258	11615	12602
60°	1290	11110	11679
65°	1344	10340	10411
70°	1435	9024	8795
75°	1596	7364	6864
80°	1757	5113	4625
85°	1594	2718	2367

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13409 cd/sqm



TEST NUMBER: P937397

CATALOG NUMBER: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.9	1.0
10°-20°	877.1	4.3
20°-30°	1534.2	7.5
30°-40°	1974.9	9.6
40°-50°	2205.9	10.7
50°-60°	2112.8	10.3
60°-70°	1674.4	8.1
70°-80°	984.6	4.8
80°-90°	278.7	1.4
90°-100°	654.5	3.2
100°-110°	1720.7	8.4
110°-120°	1784.2	8.7
120°-130°	1431.2	7.0
130°-140°	1122.9	5.5
140°-150°	861.9	4.2
150°-160°	620.7	3.0
160°-170°	379.8	1.8
170°-180°	128.3	0.6
0°-30°	2609.2	12.7
0°-40°	4584.1	22.3
0°-60°	8902.9	43.3
0°-90°	11840.5	57.6
90°-120°	4159.4	20.2
90°-150°	7575.4	36.9
90°-180°	8704.0	42.4
0°-180°	20544.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1530	1530	1530	1530	1530	
5°	1490	1599	1800	2037	2110	138
15°	1117	2061	3473	4211	4344	311
25°	713	2337	4137	4319	4324	329
35°	482	2233	3896	4118	4280	301
45°	330	1781	3444	3945	4122	255
55°	236	1131	2922	3394	3488	215
65°	187	600	2169	2440	2474	185
75°	138	369	1190	1308	1314	144
85°	49	113	295	325	330	52
90°	9	25	68	34	34	11
95°	86	339	1127	581	396	96
105°	310	470	1902	2888	2694	329
115°	551	669	1524	3040	3469	544
125°	766	859	1386	2342	2763	680
135°	913	1005	1343	1891	2144	706
145°	1059	1126	1326	1613	1739	663
155°	1197	1230	1326	1455	1498	550
165°	1291	1308	1326	1378	1395	364
175°	1343	1343	1335	1352	1352	127
180°	1343	1343	1343	1343	1343	



TEST NUMBER: P937397

CATALOG NUMBER: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1530.0	1530.0	1539.7	1544.7	1554.5	1559.4	1569.3	1579.1	1608.6	1613.6	1623.4
5°	1490.5	1510.2	1574.1	1598.8	1667.6	1761.2	1800.5	1864.5	1997.2	2036.6	2061.2
7.5°	1431.5	1475.8	1633.2	1672.6	1844.8	2090.7	2194.0	2331.8	2543.3	2646.6	2730.3
10°	1338.1	1431.5	1711.9	1805.3	2085.8	2459.6	2651.5	2843.3	3163.1	3305.7	3359.9
12.5°	1234.8	1387.2	1795.6	1923.5	2326.9	2872.9	3104.1	3315.6	3679.7	3871.5	3901.0
15°	1116.7	1323.3	1874.2	2061.2	2582.7	3217.3	3473.0	3733.8	4073.2	4211.0	4245.4
17.5°	1013.4	1274.1	1948.1	2144.8	2779.4	3527.2	3787.9	4004.3	4279.8	4373.3	4397.9
20°	885.5	1195.4	1997.2	2253.0	2986.1	3753.4	4004.3	4171.5	4358.6	4417.6	4427.4
22.5°	792.0	1111.7	2026.8	2292.4	3123.8	3891.2	4102.7	4235.5	4363.4	4383.1	4388.0
25°	713.3	1018.3	2021.8	2336.6	3241.8	3974.8	4137.1	4235.5	4309.3	4319.1	4319.1
27.5°	639.5	915.0	2002.1	2346.5	3330.4	3994.5	4122.4	4191.2	4225.7	4245.4	4245.4
30°	575.6	816.6	1952.9	2326.9	3369.7	3974.8	4078.1	4112.5	4147.0	4176.5	4191.2
32.5°	526.4	723.2	1879.2	2287.5	3374.6	3925.6	3999.5	4019.1	4068.2	4137.1	4161.8
35°	482.1	629.7	1795.6	2233.4	3345.2	3846.9	3896.1	3915.8	4014.2	4117.5	4151.9
37.5°	437.8	560.8	1687.3	2139.9	3300.9	3753.4	3787.9	3822.3	3974.8	4097.8	4137.1
40°	393.5	501.7	1559.4	2036.6	3232.0	3640.3	3669.8	3724.0	3925.6	4068.2	4107.6
42.5°	359.1	452.6	1421.7	1928.4	3143.4	3512.4	3556.7	3635.4	3866.6	4019.1	4063.4
45°	329.6	403.4	1274.1	1780.8	3030.3	3379.6	3443.5	3551.8	3797.7	3945.3	3984.6
47.5°	300.1	369.0	1121.6	1628.3	2907.3	3246.7	3330.4	3453.3	3704.3	3846.9	3881.3
50°	275.5	334.5	969.1	1466.0	2774.5	3104.1	3202.4	3330.4	3586.2	3719.0	3763.3
52.5°	255.8	305.0	826.5	1303.6	2622.0	2956.5	3069.7	3202.4	3443.5	3571.4	3600.9
55°	236.1	280.4	703.5	1131.4	2464.6	2799.1	2922.1	3050.0	3286.1	3394.3	3414.0
57.5°	226.3	260.8	600.2	969.1	2297.3	2622.0	2759.7	2877.8	3099.2	3182.8	3202.4
60°	211.5	245.9	521.4	831.4	2115.3	2454.8	2572.8	2690.9	2877.8	2946.6	2961.5
62.5°	196.8	236.1	462.4	698.6	1928.4	2258.0	2376.0	2484.2	2641.7	2690.9	2710.6
65°	186.9	226.3	418.1	600.2	1736.5	2051.4	2169.4	2262.9	2390.8	2439.9	2449.8
67.5°	177.1	216.5	383.7	516.6	1544.7	1844.8	1933.3	2021.8	2120.3	2169.4	2174.3
70°	162.3	206.6	354.2	457.5	1347.9	1608.6	1682.4	1775.9	1854.6	1879.2	1893.9
72.5°	152.5	191.9	334.5	413.2	1146.2	1382.4	1451.2	1505.3	1574.1	1598.8	1598.8
75°	137.7	172.2	314.8	369.0	939.5	1131.4	1190.5	1244.6	1298.7	1308.5	1293.8
77.5°	123.0	152.5	270.5	309.9	733.0	895.4	944.5	974.0	1018.3	1028.1	1033.1
80°	103.3	132.8	211.5	241.1	531.3	659.2	693.6	718.2	757.6	757.6	767.4
82.5°	78.7	103.3	152.5	172.2	359.1	452.6	482.1	496.8	521.4	521.4	521.4
85°	49.2	64.0	98.4	113.2	216.5	275.5	295.2	300.1	319.8	324.7	324.7
87.5°	24.6	34.4	64.0	68.9	113.2	142.6	142.6	152.5	152.5	147.6	142.6
90°	9.0	16.2	23.4	25.2	39.6	58.9	68.5	60.9	45.6	34.2	34.2
92.5°	36.0	97.3	158.6	173.9	244.5	338.6	385.7	338.0	242.7	171.2	164.4
95°	86.5	198.6	310.9	338.9	601.7	952.1	1127.3	1006.0	763.3	581.2	560.6
97.5°	149.6	248.5	347.5	372.2	810.5	1394.8	1686.9	1610.2	1456.8	1341.8	1302.5
100°	198.3	288.0	377.7	400.1	886.4	1534.8	1859.0	1864.6	1875.9	1884.3	1837.5
102.5°	239.7	323.5	407.1	428.0	921.2	1578.9	1907.8	2005.4	2200.9	2347.5	2307.5
105°	310.0	380.9	451.7	469.5	947.1	1583.9	1902.3	2121.4	2559.6	2888.2	2866.7
107.5°	382.1	448.2	514.2	530.8	951.9	1513.5	1794.2	2099.8	2711.0	3169.3	3174.5
110°	430.7	490.4	550.1	565.0	944.7	1451.0	1704.1	2045.8	2729.0	3241.4	3263.8



TEST NUMBER: P937397

CATALOG NUMBER: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	478.5	535.4	592.3	606.5	945.1	1396.4	1622.1	1971.7	2671.0	3195.5	3229.9
115°	550.6	603.0	655.5	668.6	953.7	1333.8	1523.8	1860.7	2534.3	3039.6	3087.3
117.5°	621.8	669.5	717.1	729.0	971.4	1294.6	1456.2	1760.2	2368.1	2824.2	2877.2
120°	663.3	708.1	752.9	764.2	985.9	1281.4	1429.2	1706.9	2262.4	2679.1	2730.5
122.5°	703.8	749.0	794.3	805.6	1006.6	1274.5	1408.4	1658.5	2158.8	2534.0	2584.8
125°	766.0	807.3	848.6	858.8	1034.5	1268.8	1386.0	1598.5	2023.4	2342.1	2388.9
127.5°	816.5	858.1	899.8	910.2	1062.5	1265.5	1367.1	1549.5	1914.4	2188.0	2227.4
130°	843.5	888.4	933.1	944.4	1082.9	1267.5	1359.8	1522.2	1847.0	2090.6	2127.1
132.5°	871.4	916.3	961.1	972.3	1099.3	1268.8	1353.5	1498.8	1789.6	2007.8	2040.4
135°	912.9	953.7	994.6	1004.8	1117.5	1267.6	1342.7	1464.4	1708.0	1890.6	1918.7
137.5°	955.2	995.6	1036.2	1046.2	1144.5	1275.4	1340.9	1443.8	1649.7	1804.1	1827.1
140°	990.3	1027.5	1064.8	1074.1	1161.0	1276.8	1334.6	1423.6	1601.4	1734.7	1756.2
142.5°	1017.4	1051.8	1086.2	1094.9	1174.8	1281.3	1334.6	1412.7	1568.9	1686.1	1704.6
145°	1058.8	1088.9	1118.9	1126.5	1192.8	1281.3	1325.6	1389.4	1517.3	1613.1	1627.1
147.5°	1100.3	1129.6	1158.8	1166.1	1219.3	1290.1	1325.6	1375.9	1476.4	1551.8	1563.4
150°	1127.3	1153.8	1180.2	1186.8	1233.1	1294.8	1325.6	1368.0	1452.9	1516.6	1526.0
152.5°	1155.2	1175.3	1195.3	1200.3	1242.1	1297.8	1325.6	1361.8	1434.3	1488.7	1495.7
155°	1196.7	1211.5	1226.4	1230.0	1261.9	1304.4	1325.6	1354.5	1412.1	1455.3	1460.1
157.5°	1227.3	1241.8	1256.2	1259.8	1281.7	1311.0	1325.6	1348.0	1392.8	1426.5	1429.8
160°	1248.1	1259.3	1270.6	1273.4	1290.8	1314.0	1325.6	1344.8	1383.2	1412.1	1414.1
162.5°	1268.8	1277.2	1285.6	1287.7	1300.3	1317.2	1325.6	1341.8	1374.2	1398.6	1400.4
165°	1291.4	1298.9	1306.5	1308.4	1314.2	1321.8	1325.6	1337.2	1360.4	1377.8	1379.8
167.5°	1312.0	1315.6	1319.3	1320.2	1325.0	1331.4	1334.6	1342.2	1357.4	1368.8	1369.6
170°	1325.6	1329.2	1332.9	1333.7	1334.0	1334.4	1334.6	1342.2	1357.4	1368.8	1368.8
172.5°	1332.8	1333.5	1334.4	1334.6	1334.6	1334.6	1334.6	1340.6	1352.6	1361.6	1361.0
175°	1342.7	1342.7	1342.7	1342.7	1340.0	1336.4	1334.6	1338.4	1346.0	1351.8	1351.8
177.5°	1342.7	1342.7	1342.7	1342.7	1340.6	1337.8	1336.4	1339.4	1345.5	1349.9	1349.1
180°	1342.7	1342.7	1342.7	1342.7	1342.7	1342.7	1342.7	1342.7	1342.7	1342.7	1342.7



TEST NUMBER: P937397

CATALOG NUMBER: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1530.0	1530.0
2.5°	1633.2	1623.4
5°	2100.6	2110.4
7.5°	2828.6	2823.7
10°	3517.3	3561.6
12.5°	4019.1	4028.9
15°	4324.1	4343.7
17.5°	4442.2	4447.0
20°	4447.0	4437.2
22.5°	4393.0	4383.1
25°	4329.0	4324.1
27.5°	4270.0	4274.9
30°	4245.4	4260.1
32.5°	4245.4	4270.0
35°	4255.2	4279.8
37.5°	4250.3	4279.8
40°	4230.7	4265.1
42.5°	4176.5	4201.1
45°	4092.9	4122.4
47.5°	3984.6	4004.3
50°	3846.9	3866.6
52.5°	3674.7	3679.7
55°	3468.1	3487.8
57.5°	3246.7	3251.7
60°	3000.8	3015.5
62.5°	2740.0	2740.0
65°	2464.6	2474.4
67.5°	2179.3	2203.9
70°	1889.1	1893.9
72.5°	1603.7	1603.7
75°	1308.5	1313.5
77.5°	1028.1	1028.1
80°	762.5	767.4
82.5°	526.4	536.2
85°	329.6	329.6
87.5°	152.5	137.7
90°	34.2	34.2
92.5°	137.2	110.0
95°	478.1	395.6
97.5°	1145.6	988.6
100°	1650.5	1463.5
102.5°	2147.2	1987.0
105°	2780.5	2694.4
107.5°	3195.4	3216.2
110°	3353.5	3443.2



TEST NUMBER: P937397

CATALOG NUMBER: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3367.7	3505.5
115°	3278.3	3469.4
117.5°	3089.0	3300.9
120°	2936.5	3142.3
122.5°	2787.8	2990.9
125°	2575.9	2762.9
127.5°	2385.3	2543.0
130°	2272.9	2418.7
132.5°	2170.9	2301.6
135°	2031.3	2143.8
137.5°	1919.2	2011.4
140°	1842.4	1928.4
142.5°	1778.7	1852.7
145°	1683.2	1739.2
147.5°	1609.8	1656.3
150°	1563.7	1601.4
152.5°	1524.2	1552.6
155°	1478.9	1497.7
157.5°	1443.0	1456.2
160°	1421.6	1429.2
162.5°	1407.6	1414.8
165°	1387.3	1395.0
167.5°	1372.9	1376.1
170°	1368.8	1368.8
172.5°	1358.2	1355.3
175°	1351.8	1351.8
177.5°	1345.9	1342.7
180°	1342.7	1342.7



TEST NUMBER: P937397
 CATALOG NUMBER: SQ4-FB-075U-125D-B35-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.08	8.06	7.96	8.97	10.12	20.27	21.25	21.15	22.16	23.31
	3H	7.79	8.67	8.68	9.59	10.77	22.12	23.01	23.01	23.92	25.10
	4H	8.10	8.93	9.00	9.85	11.04	22.78	23.61	23.68	24.53	25.72
	6H	8.35	9.12	9.27	10.05	11.25	23.22	23.99	24.14	24.92	26.12
	8H	8.42	9.16	9.35	10.11	11.31	23.35	24.08	24.27	25.03	26.23
	12H	8.45	9.15	9.38	10.09	11.31	23.42	24.12	24.35	25.06	26.29
4H	2H	14.32	15.15	15.23	16.07	17.26	20.56	21.39	21.47	22.31	23.50
	3H	15.89	16.59	16.82	17.55	18.75	22.62	23.32	23.54	24.27	25.48
	4H	15.99	16.63	16.93	17.58	18.81	23.39	24.03	24.33	24.98	26.21
	6H	16.01	16.56	16.96	17.54	18.76	23.95	24.50	24.89	25.47	26.70
	8H	15.99	16.51	16.94	17.47	18.72	24.11	24.63	25.06	25.60	26.84
	12H	15.95	16.42	16.92	17.40	18.65	24.22	24.68	25.19	25.67	26.92
8H	4H	17.45	17.97	18.40	18.93	20.18	23.47	23.98	24.42	24.95	26.19
	6H	17.70	18.13	18.68	19.14	20.38	24.10	24.53	25.08	25.54	26.78
	8H	17.72	18.10	18.71	19.09	20.35	24.33	24.71	25.32	25.70	26.96
	12H	17.69	18.03	18.68	19.02	20.32	24.48	24.82	25.47	25.81	27.11
12H	4H	17.60	18.07	18.57	19.05	20.30	23.42	23.89	24.39	24.87	26.12
	6H	17.96	18.34	18.95	19.34	20.60	24.09	24.47	25.08	25.47	26.73
	8H	18.04	18.37	19.03	19.36	20.67	24.33	24.66	25.32	25.65	26.96