

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937199

Luminaire Tested: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937199
REPORT IS A COMBINATION OF REPORTS P933510 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7851.8 lumens
Efficiency: N/A
Efficacy: 123.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 63.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937199
CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P937199

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	96	92	88	84	88	84	80	77	70	67	65	57	55	53	44	43	42	37	37	37	37
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	38	36	35	30	30	30	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25	25	25	25
4	72	61	53	47	65	56	49	43	46	41	37	38	34	31	30	27	24	21	21	21	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	17	17	17	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13	13	13	13
8	51	39	31	26	47	36	29	24	30	24	21	25	20	17	20	16	14	11	11	11	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10	10	10	10
10	44	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2796	2796	2796
5°	2731	3231	3759
10°	2476	4709	6231
15°	2103	6151	7525
20°	1712	7126	7669
25°	1428	7456	7513
30°	1203	7501	7499
35°	1063	7375	7693
40°	926	7210	7894
45°	838	7089	7924
50°	768	6980	7793
55°	735	6822	7447
60°	752	6519	6902
65°	780	6061	6152
70°	830	5282	5197
75°	916	4302	4056
80°	993	2980	2732
85°	864	1578	1399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7924 cd/sqm



TEST NUMBER: P937199

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.5	0.7
10°-20°	259.2	3.3
20°-30°	453.3	5.8
30°-40°	583.6	7.4
40°-50°	651.8	8.3
50°-60°	624.3	8.0
60°-70°	494.7	6.3
70°-80°	290.9	3.7
80°-90°	83.4	1.1
90°-100°	327.2	4.2
100°-110°	860.4	11.0
110°-120°	892.1	11.4
120°-130°	715.6	9.1
130°-140°	561.5	7.2
140°-150°	431.0	5.5
150°-160°	310.4	4.0
160°-170°	189.9	2.4
170°-180°	64.2	0.8
0°-30°	771.0	9.8
0°-40°	1354.5	17.3
0°-60°	2630.6	33.5
0°-90°	3499.6	44.6
90°-120°	2079.7	26.5
90°-150°	3787.7	48.2
90°-180°	4352.0	55.4
0°-180°	7851.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	452	452	452	452	452	
5°	440	472	532	602	624	41
15°	330	609	1026	1244	1284	92
25°	211	690	1222	1276	1278	97
35°	142	660	1151	1217	1265	89
45°	97	526	1017	1166	1218	75
55°	70	334	863	1003	1030	64
65°	55	177	641	721	731	55
75°	41	109	352	387	388	43
85°	14	33	87	96	97	15
90°	4	13	34	17	17	5
95°	43	169	564	291	198	48
105°	155	235	951	1444	1347	164
115°	275	334	762	1520	1735	272
125°	383	429	693	1171	1382	340
135°	456	502	671	945	1072	353
145°	530	563	663	806	870	332
155°	598	615	663	728	749	275
165°	646	654	663	689	698	182
175°	671	671	667	676	676	64
180°	671	671	671	671	671	



TEST NUMBER: P937199

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0
2.5°	452.0	452.0	454.9	456.4	459.3	460.8	463.7	466.6	475.3	476.7	479.7
5°	440.4	446.2	465.1	472.4	492.7	520.4	532.0	550.9	590.1	601.7	609.0
7.5°	423.0	436.0	482.6	494.2	545.1	617.7	648.3	689.0	751.5	782.0	806.7
10°	395.4	423.0	505.8	533.4	616.3	726.8	783.4	840.1	934.6	976.8	992.7
12.5°	364.8	409.9	530.5	568.3	687.5	848.8	917.2	979.7	1087.2	1144.0	1152.7
15°	329.9	391.0	553.8	609.0	763.1	950.6	1026.2	1103.3	1203.6	1244.3	1254.5
17.5°	299.4	376.5	575.6	633.7	821.2	1042.2	1119.3	1183.2	1264.6	1292.3	1299.5
20°	261.6	353.2	590.1	665.7	882.3	1109.1	1183.2	1232.7	1287.9	1305.3	1308.2
22.5°	234.0	328.5	598.8	677.3	923.0	1149.8	1212.3	1251.6	1289.4	1295.2	1296.6
25°	210.8	300.9	597.4	690.4	957.9	1174.5	1222.5	1251.6	1273.4	1276.3	1276.3
27.5°	189.0	270.4	591.6	693.3	984.0	1180.3	1218.1	1238.5	1248.7	1254.5	1254.5
30°	170.1	241.3	577.0	687.5	995.6	1174.5	1205.0	1215.2	1225.4	1234.1	1238.5
32.5°	155.5	213.7	555.2	675.9	997.1	1160.0	1181.8	1187.6	1202.1	1222.5	1229.8
35°	142.4	186.0	530.5	659.9	988.4	1136.7	1151.3	1157.1	1186.2	1216.7	1226.9
37.5°	129.4	165.7	498.6	632.3	975.3	1109.1	1119.3	1129.5	1174.5	1210.9	1222.5
40°	116.3	148.3	460.8	601.7	954.9	1075.6	1084.3	1100.3	1160.0	1202.1	1213.8
42.5°	106.1	133.7	420.1	569.8	928.8	1037.8	1050.9	1074.1	1142.5	1187.6	1200.7
45°	97.4	119.2	376.5	526.2	895.4	998.6	1017.4	1049.4	1122.2	1165.8	1177.4
47.5°	88.7	109.0	331.4	481.1	859.0	959.3	984.0	1020.4	1094.5	1136.7	1146.9
50°	81.4	98.8	286.3	433.1	819.8	917.2	946.2	984.0	1059.6	1098.8	1112.0
52.5°	75.6	90.1	244.2	385.2	774.7	873.6	907.0	946.2	1017.4	1055.2	1064.0
55°	69.8	82.8	207.9	334.3	728.2	827.0	863.4	901.2	970.9	1002.9	1008.7
57.5°	66.9	77.0	177.3	286.3	678.8	774.7	815.4	850.3	915.7	940.4	946.2
60°	62.5	72.7	154.1	245.6	625.0	725.3	760.2	795.1	850.3	870.6	875.0
62.5°	58.1	69.8	136.6	206.4	569.8	667.2	702.0	734.0	780.5	795.1	800.9
65°	55.2	66.9	123.5	177.3	513.1	606.1	641.0	668.6	706.4	720.9	723.8
67.5°	52.3	64.0	113.4	152.6	456.4	545.1	571.2	597.4	626.5	641.0	642.4
70°	48.0	61.0	104.7	135.2	398.3	475.3	497.1	524.7	548.0	555.2	559.6
72.5°	45.1	56.7	98.8	122.1	338.7	408.4	428.8	444.8	465.1	472.4	472.4
75°	40.7	50.9	93.0	109.0	277.6	334.3	351.7	367.7	383.7	386.6	382.3
77.5°	36.3	45.1	79.9	91.6	216.6	264.5	279.1	287.8	300.9	303.8	305.2
80°	30.5	39.2	62.5	71.2	157.0	194.8	204.9	212.2	223.8	223.8	226.7
82.5°	23.3	30.5	45.1	50.9	106.1	133.7	142.4	146.8	154.1	154.1	154.1
85°	14.5	18.9	29.1	33.4	64.0	81.4	87.2	88.7	94.5	95.9	95.9
87.5°	7.3	10.2	18.9	20.3	33.4	42.2	42.2	45.1	45.1	43.6	42.2
90°	4.5	8.0	11.7	12.6	19.8	29.4	34.2	30.4	22.9	17.2	17.2
92.5°	18.0	48.6	79.3	86.9	122.2	169.3	192.8	169.0	121.3	85.6	82.2
95°	43.2	99.3	155.3	169.4	300.8	476.1	563.7	503.0	381.6	290.6	280.3
97.5°	74.8	124.2	173.6	186.0	405.2	697.4	843.5	805.1	728.5	670.9	651.3
100°	99.1	144.0	188.9	200.1	443.2	767.4	929.6	932.4	938.0	942.2	918.8
102.5°	119.9	161.7	203.6	214.1	460.7	789.4	953.9	1002.7	1100.5	1173.7	1153.7
105°	155.0	190.5	226.0	234.8	473.6	792.0	951.2	1060.7	1279.8	1444.1	1433.3
107.5°	191.1	224.1	257.2	265.4	476.0	756.7	897.1	1049.9	1355.5	1584.7	1587.3
110°	215.4	245.3	275.0	282.5	472.3	725.5	852.0	1022.9	1364.5	1620.7	1632.0



TEST NUMBER: P937199

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	239.2	267.6	296.1	303.2	472.5	698.2	811.1	985.9	1335.5	1597.7	1614.9
115°	275.3	301.6	327.7	334.3	476.8	666.9	761.9	930.3	1267.2	1519.8	1543.6
117.5°	310.9	334.7	358.5	364.5	485.8	647.3	728.1	880.1	1184.1	1412.1	1438.6
120°	331.6	354.1	376.5	382.1	492.9	640.7	714.6	853.5	1131.2	1339.5	1365.3
122.5°	351.9	374.5	397.2	402.8	503.3	637.3	704.3	829.3	1079.4	1267.0	1292.4
125°	382.9	403.6	424.2	429.4	517.3	634.4	693.0	799.2	1011.7	1171.0	1194.4
127.5°	408.2	429.1	449.8	455.0	531.2	632.8	683.5	774.7	957.2	1094.0	1113.8
130°	421.7	444.2	466.6	472.2	541.5	633.8	679.9	761.1	923.6	1045.4	1063.6
132.5°	435.7	458.1	480.5	486.1	549.7	634.4	676.7	749.4	894.9	1003.9	1020.2
135°	456.4	476.8	497.3	502.4	558.7	633.8	671.3	732.2	854.0	945.3	959.3
137.5°	477.6	497.8	518.0	523.1	572.2	637.7	670.5	721.9	824.8	902.0	913.6
140°	495.2	513.8	532.5	537.1	580.5	638.4	667.3	711.7	800.7	867.4	878.1
142.5°	508.7	526.0	543.2	547.5	587.4	640.6	667.3	706.3	784.4	843.0	852.3
145°	529.5	544.5	559.4	563.2	596.4	640.7	662.8	694.8	758.6	806.5	813.5
147.5°	550.1	564.7	579.4	583.0	609.6	645.1	662.8	687.9	738.2	775.9	781.7
150°	563.7	576.8	590.1	593.4	616.6	647.4	662.8	684.0	726.5	758.3	763.1
152.5°	577.6	587.7	597.7	600.2	621.0	648.8	662.8	680.9	717.2	744.4	748.0
155°	598.4	605.7	613.2	615.0	630.9	652.1	662.8	677.2	706.1	727.7	730.0
157.5°	613.7	620.9	628.1	629.9	640.9	655.5	662.8	674.0	696.4	713.3	714.9
160°	624.0	629.7	635.3	636.6	645.4	657.0	662.8	672.4	691.6	706.0	707.0
162.5°	634.4	638.7	642.8	643.9	650.2	658.6	662.8	670.9	687.1	699.3	700.2
165°	645.6	649.5	653.3	654.3	657.1	660.9	662.8	668.6	680.2	689.0	689.9
167.5°	656.0	657.9	659.6	660.1	662.5	665.7	667.3	671.0	678.7	684.4	684.8
170°	662.8	664.6	666.4	666.9	667.0	667.2	667.3	671.0	678.7	684.4	684.4
172.5°	666.4	666.8	667.2	667.3	667.3	667.3	667.3	670.3	676.3	680.8	680.4
175°	671.3	671.3	671.3	671.3	670.0	668.1	667.3	669.2	673.0	675.9	675.9
177.5°	671.3	671.3	671.3	671.3	670.3	668.9	668.2	669.8	672.8	675.0	674.6
180°	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3



TEST NUMBER: P937199

CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	452.0	452.0
2.5°	482.6	479.7
5°	620.6	623.6
7.5°	835.8	834.3
10°	1039.3	1052.3
12.5°	1187.6	1190.5
15°	1277.7	1283.5
17.5°	1312.6	1314.1
20°	1314.1	1311.2
22.5°	1298.1	1295.2
25°	1279.2	1277.7
27.5°	1261.7	1263.2
30°	1254.5	1258.8
32.5°	1254.5	1261.7
35°	1257.4	1264.6
37.5°	1255.9	1264.6
40°	1250.1	1260.3
42.5°	1234.1	1241.4
45°	1209.4	1218.1
47.5°	1177.4	1183.2
50°	1136.7	1142.5
52.5°	1085.8	1087.2
55°	1024.7	1030.5
57.5°	959.3	960.8
60°	886.6	891.0
62.5°	809.6	809.6
65°	728.2	731.1
67.5°	643.9	651.2
70°	558.1	559.6
72.5°	473.8	473.8
75°	386.6	388.1
77.5°	303.8	303.8
80°	225.3	226.7
82.5°	155.5	158.4
85°	97.4	97.4
87.5°	45.1	40.7
90°	17.2	17.2
92.5°	68.5	54.9
95°	239.1	197.8
97.5°	572.8	494.3
100°	825.2	731.7
102.5°	1073.7	993.5
105°	1390.2	1347.2
107.5°	1597.7	1608.1
110°	1676.8	1721.6



TEST NUMBER: P937199
CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1683.8	1752.7
115°	1639.2	1734.7
117.5°	1544.5	1650.4
120°	1468.2	1571.1
122.5°	1393.9	1495.5
125°	1288.0	1381.5
127.5°	1192.6	1271.5
130°	1136.4	1209.3
132.5°	1085.5	1150.8
135°	1015.6	1071.9
137.5°	959.6	1005.7
140°	921.2	964.3
142.5°	889.3	926.4
145°	841.6	869.6
147.5°	804.9	828.1
150°	781.9	800.7
152.5°	762.1	776.4
155°	739.4	748.8
157.5°	721.5	728.1
160°	710.8	714.6
162.5°	703.8	707.4
165°	693.7	697.5
167.5°	686.4	688.0
170°	684.4	684.4
172.5°	679.1	677.6
175°	675.9	675.9
177.5°	673.0	671.3
180°	671.3	671.3



TEST NUMBER: P937199
 CATALOG NUMBER: SQ4-FB-075U-075D-B35-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.06	4.90	5.05	5.91	7.26	17.22	18.07	18.22	19.08	20.42
	3H	4.76	5.52	5.77	6.54	7.91	19.05	19.82	20.06	20.84	22.20
	4H	5.06	5.78	6.08	6.80	8.18	19.70	20.42	20.71	21.44	22.81
	6H	5.31	5.97	6.34	7.00	8.39	20.12	20.79	21.15	21.81	23.20
	8H	5.38	6.01	6.41	7.06	8.44	20.24	20.87	21.27	21.92	23.30
	12H	5.39	6.00	6.43	7.04	8.44	20.30	20.91	21.34	21.95	23.35
4H	2H	11.26	11.98	12.29	13.01	14.38	17.49	18.22	18.52	19.24	20.61
	3H	12.83	13.43	13.86	14.49	15.87	19.53	20.14	20.57	21.19	22.58
	4H	12.92	13.48	13.96	14.52	15.93	20.30	20.85	21.34	21.89	23.30
	6H	12.93	13.41	13.98	14.48	15.88	20.83	21.31	21.88	22.38	23.78
	8H	12.91	13.36	13.96	14.42	15.83	20.99	21.44	22.04	22.50	23.92
	12H	12.87	13.27	13.94	14.34	15.77	21.08	21.48	22.15	22.56	23.98
8H	4H	14.36	14.81	15.42	15.87	17.29	20.36	20.80	21.41	21.86	23.28
	6H	14.60	14.97	15.68	16.08	17.49	20.98	21.35	22.06	22.45	23.87
	8H	14.62	14.95	15.71	16.03	17.47	21.20	21.52	22.28	22.61	24.04
	12H	14.59	14.88	15.68	15.96	17.43	21.34	21.62	22.43	22.70	24.18
12H	4H	14.50	14.91	15.58	15.98	17.41	20.31	20.71	21.38	21.79	23.21
	6H	14.86	15.19	15.95	16.27	17.71	20.96	21.29	22.05	22.37	23.81
	8H	14.93	15.22	16.02	16.30	17.77	21.19	21.48	22.28	22.56	24.03