

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937800

Luminaire Tested: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937800
REPORT IS A COMBINATION OF REPORTS P933584 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15681.4 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 137.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937800
CATALOG NUMBER: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P937800

CATALOG NUMBER: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	56	56	56	50
1	97	93	89	85	90	86	82	79	72	70	67	60	58	57	49	48	47	49	48	47	41
2	88	80	74	68	81	74	69	64	63	59	55	52	49	46	42	40	38	42	40	38	34
3	80	70	62	56	73	65	58	53	55	50	45	46	42	39	37	34	32	37	34	32	28
4	73	62	53	47	67	57	50	44	48	43	38	40	36	32	33	30	27	33	30	27	23
5	67	54	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23	29	26	23	20
6	61	49	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20	26	23	20	17
7	56	44	35	30	52	40	33	28	34	29	24	29	24	21	24	20	17	24	20	17	15
8	52	39	31	26	48	37	29	24	31	25	21	26	22	18	22	18	15	22	18	15	13
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	20	16	14	20	16	14	11
10	45	33	25	20	41	30	24	19	26	21	17	22	18	15	18	15	12	18	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4732	4732	4732
5°	4623	5470	6361
10°	4194	7973	10546
15°	3564	10416	12734
20°	2901	12071	12977
25°	2421	12632	12714
30°	2041	12711	12690
35°	1805	12500	13018
40°	1573	12226	13357
45°	1424	12025	13409
50°	1306	11844	13187
55°	1252	11580	12603
60°	1281	11071	11680
65°	1332	10298	10412
70°	1419	8981	8796
75°	1574	7323	6864
80°	1719	5078	4625
85°	1528	2695	2368

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13409 cd/sqm



TEST NUMBER: P937800

CATALOG NUMBER: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	0.8
10°-20°	584.8	3.7
20°-30°	1022.8	6.5
30°-40°	1316.7	8.4
40°-50°	1470.7	9.4
50°-60°	1408.6	9.0
60°-70°	1116.3	7.1
70°-80°	656.4	4.2
80°-90°	186.9	1.2
90°-100°	585.5	3.7
100°-110°	1539.2	9.8
110°-120°	1596.0	10.2
120°-130°	1280.2	8.2
130°-140°	1004.5	6.4
140°-150°	771.0	4.9
150°-160°	555.2	3.5
160°-170°	339.7	2.2
170°-180°	114.8	0.7
0°-30°	1739.5	11.1
0°-40°	3056.2	19.5
0°-60°	5935.5	37.9
0°-90°	7895.2	50.3
90°-120°	3720.7	23.7
90°-150°	6776.4	43.2
90°-180°	7786.0	49.7
0°-180°	15681.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1020	1020	1020	1020	1020	
5°	994	1066	1200	1358	1407	92
15°	744	1374	2315	2807	2896	207
25°	476	1558	2758	2880	2883	219
35°	321	1489	2598	2745	2853	201
45°	220	1187	2296	2630	2748	170
55°	158	754	1948	2263	2325	143
65°	125	400	1446	1627	1650	123
75°	92	246	794	872	876	96
85°	33	75	197	216	220	35
90°	8	23	61	31	31	9
95°	77	303	1008	520	354	86
105°	277	420	1702	2584	2410	294
115°	492	598	1363	2719	3104	486
125°	685	768	1240	2095	2472	608
135°	817	899	1201	1691	1918	632
145°	947	1008	1186	1443	1556	593
155°	1070	1100	1186	1302	1340	492
165°	1155	1170	1186	1233	1248	326
175°	1201	1201	1194	1209	1209	114
180°	1201	1201	1201	1201	1201	



TEST NUMBER: P937800
 CATALOG NUMBER: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1020.0	1020.0	1020.0	1020.0	1020.0	1020.0	1020.0	1020.0	1020.0	1020.0	1020.0
2.5°	1020.0	1020.0	1026.6	1029.9	1036.3	1039.6	1046.2	1052.8	1072.5	1075.8	1082.3
5°	993.7	1006.9	1049.5	1065.9	1111.8	1174.1	1200.4	1243.0	1331.5	1357.8	1374.1
7.5°	954.4	983.9	1088.9	1115.1	1229.9	1393.9	1462.7	1554.6	1695.6	1764.5	1820.3
10°	892.1	954.4	1141.3	1203.6	1390.6	1639.8	1767.7	1895.7	2108.8	2204.0	2240.0
12.5°	823.2	924.9	1197.1	1282.4	1551.3	1915.3	2069.5	2210.5	2453.2	2581.1	2600.8
15°	744.5	882.3	1249.5	1374.1	1721.8	2144.9	2315.4	2489.3	2715.6	2807.4	2830.4
17.5°	675.6	849.4	1298.8	1430.0	1853.0	2351.6	2525.3	2669.7	2853.3	2915.6	2932.0
20°	590.3	797.0	1331.5	1502.0	1990.8	2502.4	2669.7	2781.1	2905.8	2945.2	2951.7
22.5°	528.0	741.2	1351.3	1528.3	2082.6	2594.2	2735.3	2823.8	2909.0	2922.2	2925.5
25°	475.6	678.9	1348.0	1557.9	2161.4	2650.0	2758.3	2823.8	2873.0	2879.6	2879.6
27.5°	426.4	610.0	1334.8	1564.5	2220.4	2663.1	2748.4	2794.3	2817.3	2830.4	2830.4
30°	383.7	544.4	1302.0	1551.3	2246.6	2650.0	2718.8	2741.8	2764.8	2784.4	2794.3
32.5°	351.0	482.1	1252.8	1525.0	2249.8	2617.2	2666.4	2679.5	2712.3	2758.3	2774.6
35°	321.4	419.8	1197.1	1489.0	2230.2	2564.7	2597.5	2610.6	2676.2	2745.1	2768.0
37.5°	291.9	373.8	1124.9	1426.7	2200.7	2502.4	2525.3	2548.3	2650.0	2732.0	2758.3
40°	262.4	334.5	1039.6	1357.8	2154.8	2427.0	2446.6	2482.7	2617.2	2712.3	2738.5
42.5°	239.4	301.7	947.9	1285.7	2095.8	2341.7	2371.2	2423.7	2577.8	2679.5	2709.0
45°	219.8	268.9	849.4	1187.2	2020.3	2253.1	2295.8	2367.9	2531.9	2630.4	2656.5
47.5°	200.1	245.9	747.8	1085.6	1938.3	2164.6	2220.4	2302.3	2469.6	2564.7	2587.7
50°	183.6	223.1	646.1	977.3	1849.7	2069.5	2135.1	2220.4	2390.9	2479.5	2508.9
52.5°	170.5	203.3	551.0	869.1	1748.1	1971.0	2046.5	2135.1	2295.8	2381.0	2400.7
55°	157.5	186.9	469.0	754.4	1643.1	1866.1	1948.2	2033.4	2190.8	2263.0	2276.1
57.5°	150.9	173.8	400.1	646.1	1531.6	1748.1	1839.9	1918.6	2066.2	2121.9	2135.1
60°	141.0	164.0	347.7	554.3	1410.3	1636.5	1715.2	1794.0	1918.6	1964.6	1974.3
62.5°	131.2	157.5	308.3	465.7	1285.7	1505.3	1584.1	1656.2	1761.2	1794.0	1807.1
65°	124.6	150.9	278.8	400.1	1157.8	1367.6	1446.3	1508.6	1593.9	1626.8	1633.2
67.5°	118.0	144.3	255.8	344.4	1029.9	1229.9	1288.9	1348.0	1413.6	1446.3	1449.6
70°	108.2	137.8	236.1	305.0	898.7	1072.5	1121.6	1183.9	1236.4	1252.8	1262.7
72.5°	101.6	127.9	223.1	275.5	764.2	921.6	967.5	1003.6	1049.5	1065.9	1065.9
75°	91.9	114.8	209.9	245.9	626.5	754.4	793.7	829.8	865.8	872.4	862.6
77.5°	82.0	101.6	180.4	206.6	488.7	596.9	629.7	649.4	678.9	685.5	688.8
80°	68.9	88.6	141.0	160.7	354.2	439.4	462.4	478.9	505.0	505.0	511.6
82.5°	52.5	68.9	101.6	114.8	239.4	301.7	321.4	331.2	347.7	347.7	347.7
85°	32.8	42.6	65.6	75.4	144.3	183.6	196.8	200.1	213.2	216.5	216.5
87.5°	16.4	23.0	42.6	45.9	75.4	95.2	95.2	101.6	101.6	98.4	95.2
90°	8.0	14.5	20.9	22.6	35.5	52.6	61.2	54.5	40.8	30.6	30.6
92.5°	32.3	87.1	142.0	155.6	218.7	302.9	345.0	302.3	217.2	153.2	147.1
95°	77.4	177.7	278.0	303.1	538.2	851.7	1008.4	899.9	682.8	520.0	501.6
97.5°	133.8	222.3	310.9	332.9	725.0	1247.7	1509.0	1440.4	1303.2	1200.3	1165.2
100°	177.3	257.6	337.9	357.9	792.9	1373.0	1663.0	1668.0	1678.0	1685.6	1643.7
102.5°	214.4	289.2	364.2	382.9	824.0	1412.3	1706.5	1793.9	1968.8	2099.9	2064.1
105°	277.3	340.7	404.1	420.0	847.2	1416.9	1701.7	1897.6	2289.6	2583.5	2564.3
107.5°	341.8	400.9	460.0	474.8	851.6	1353.8	1605.0	1878.3	2425.0	2835.0	2839.7
110°	385.3	438.7	492.1	505.4	845.1	1297.9	1524.3	1830.0	2441.1	2899.5	2919.6



TEST NUMBER: P937800

CATALOG NUMBER: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	428.0	478.9	529.8	542.5	845.4	1249.1	1451.0	1763.8	2389.3	2858.5	2889.3
115°	492.5	539.4	586.4	598.2	853.1	1193.1	1363.1	1664.5	2267.1	2719.0	2761.7
117.5°	556.2	598.8	641.5	652.1	869.0	1158.1	1302.6	1574.5	2118.4	2526.3	2573.7
120°	593.3	633.4	673.6	683.5	881.9	1146.3	1278.5	1527.0	2023.9	2396.5	2442.6
122.5°	629.6	670.1	710.6	720.6	900.4	1140.0	1259.9	1483.6	1931.1	2266.8	2312.2
125°	685.2	722.1	759.0	768.2	925.4	1135.0	1239.7	1429.9	1810.0	2095.1	2136.9
127.5°	730.3	767.5	804.9	814.2	950.4	1132.1	1222.9	1386.1	1712.4	1957.2	1992.5
130°	754.5	794.6	834.7	844.8	968.6	1133.8	1216.4	1361.6	1652.2	1870.2	1902.7
132.5°	779.5	819.6	859.7	869.8	983.4	1135.0	1210.8	1340.8	1600.9	1795.9	1825.1
135°	816.6	853.1	889.7	898.8	999.6	1133.9	1201.1	1310.0	1527.8	1691.2	1716.4
137.5°	854.5	890.6	926.8	935.9	1023.7	1140.9	1199.4	1291.5	1475.7	1613.8	1634.4
140°	885.9	919.2	952.5	960.9	1038.5	1142.1	1193.8	1273.4	1432.5	1551.8	1571.0
142.5°	910.1	940.9	971.7	979.4	1050.9	1146.1	1193.8	1263.7	1403.4	1508.2	1524.8
145°	947.2	974.0	1001.0	1007.7	1067.1	1146.2	1185.8	1242.9	1357.2	1442.9	1455.4
147.5°	984.2	1010.4	1036.5	1043.1	1090.7	1154.1	1185.8	1230.7	1320.7	1388.1	1398.5
150°	1008.4	1032.1	1055.7	1061.6	1103.0	1158.1	1185.8	1223.8	1299.7	1356.7	1365.1
152.5°	1033.4	1051.4	1069.3	1073.7	1111.1	1160.9	1185.8	1218.2	1283.1	1331.7	1338.1
155°	1070.5	1083.7	1097.0	1100.3	1128.8	1166.8	1185.8	1211.5	1263.2	1301.9	1306.0
157.5°	1097.9	1110.8	1123.7	1126.9	1146.5	1172.7	1185.8	1205.8	1245.9	1276.1	1279.0
160°	1116.5	1126.6	1136.5	1139.1	1154.7	1175.4	1185.8	1203.0	1237.4	1263.2	1264.9
162.5°	1135.0	1142.5	1150.1	1151.9	1163.2	1178.2	1185.8	1200.3	1229.3	1251.1	1252.7
165°	1155.1	1161.9	1168.7	1170.5	1175.6	1182.4	1185.8	1196.1	1217.0	1232.6	1234.3
167.5°	1173.7	1176.9	1180.1	1180.9	1185.2	1190.9	1193.8	1200.6	1214.3	1224.4	1225.1
170°	1185.8	1189.0	1192.3	1193.0	1193.3	1193.6	1193.8	1200.6	1214.3	1224.4	1224.4
172.5°	1192.3	1192.9	1193.6	1193.8	1193.8	1193.8	1193.8	1199.2	1210.0	1218.0	1217.5
175°	1201.1	1201.1	1201.1	1201.1	1198.7	1195.5	1193.8	1197.2	1204.0	1209.1	1209.1
177.5°	1201.1	1201.1	1201.1	1201.1	1199.2	1196.7	1195.5	1198.2	1203.5	1207.6	1206.9
180°	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1



TEST NUMBER: P937800

CATALOG NUMBER: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1020.0	1020.0
2.5°	1088.9	1082.3
5°	1400.4	1407.0
7.5°	1885.8	1882.6
10°	2345.0	2374.5
12.5°	2679.5	2686.1
15°	2882.9	2896.0
17.5°	2961.6	2964.8
20°	2964.8	2958.3
22.5°	2928.8	2922.2
25°	2886.2	2882.9
27.5°	2846.7	2850.0
30°	2830.4	2840.2
32.5°	2830.4	2846.7
35°	2836.9	2853.3
37.5°	2833.6	2853.3
40°	2820.6	2843.5
42.5°	2784.4	2800.9
45°	2728.7	2748.4
47.5°	2656.5	2669.7
50°	2564.7	2577.8
52.5°	2449.9	2453.2
55°	2312.1	2325.3
57.5°	2164.6	2167.8
60°	2000.6	2010.5
62.5°	1826.8	1826.8
65°	1643.1	1649.7
67.5°	1452.9	1469.3
70°	1259.4	1262.7
72.5°	1069.2	1069.2
75°	872.4	875.7
77.5°	685.5	685.5
80°	508.3	511.6
82.5°	351.0	357.5
85°	219.8	219.8
87.5°	101.6	91.9
90°	30.6	30.6
92.5°	122.8	98.4
95°	427.7	353.9
97.5°	1024.7	884.3
100°	1476.5	1309.1
102.5°	1920.8	1777.4
105°	2487.2	2410.2
107.5°	2858.4	2877.0
110°	2999.8	3080.1



TEST NUMBER: P937800

CATALOG NUMBER: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3012.4	3135.7
115°	2932.6	3103.5
117.5°	2763.2	2952.7
120°	2626.8	2810.9
122.5°	2493.8	2675.4
125°	2304.2	2471.5
127.5°	2133.6	2274.8
130°	2033.2	2163.6
132.5°	1942.0	2058.7
135°	1817.1	1917.7
137.5°	1716.8	1799.2
140°	1648.0	1725.0
142.5°	1591.1	1657.4
145°	1505.6	1555.7
147.5°	1440.0	1481.6
150°	1398.8	1432.5
152.5°	1363.5	1388.9
155°	1322.9	1339.7
157.5°	1290.8	1302.6
160°	1271.7	1278.5
162.5°	1259.1	1265.6
165°	1241.1	1247.9
167.5°	1228.0	1230.9
170°	1224.4	1224.4
172.5°	1214.9	1212.4
175°	1209.1	1209.1
177.5°	1204.0	1201.1
180°	1201.1	1201.1



TEST NUMBER: P937800

CATALOG NUMBER: SQ4-FB-100U-125D-B35-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.44	7.34	7.38	8.31	9.57	19.62	20.52	20.56	21.49	22.75
	3H	7.15	7.96	8.10	8.94	10.22	21.46	22.27	22.42	23.25	24.53
	4H	7.45	8.22	8.42	9.20	10.49	22.11	22.88	23.08	23.86	25.15
	6H	7.70	8.41	8.68	9.40	10.70	22.54	23.25	23.52	24.24	25.54
	8H	7.77	8.45	8.76	9.45	10.75	22.66	23.34	23.65	24.34	25.65
	12H	7.79	8.43	8.78	9.43	10.76	22.73	23.38	23.73	24.37	25.70
4H	2H	13.66	14.43	14.64	15.41	16.70	19.90	20.67	20.87	21.65	22.94
	3H	15.23	15.87	16.22	16.88	18.19	21.95	22.59	22.93	23.60	24.91
	4H	15.33	15.92	16.32	16.92	18.25	22.71	23.30	23.71	24.31	25.64
	6H	15.34	15.85	16.35	16.88	18.20	23.26	23.77	24.26	24.79	26.12
	8H	15.32	15.79	16.33	16.81	18.16	23.42	23.90	24.43	24.92	26.26
	12H	15.28	15.71	16.31	16.74	18.09	23.51	23.95	24.54	24.98	26.33
8H	4H	16.78	17.25	17.78	18.27	19.62	22.78	23.25	23.79	24.27	25.62
	6H	17.02	17.41	18.05	18.48	19.82	23.41	23.80	24.44	24.87	26.21
	8H	17.04	17.39	18.08	18.43	19.79	23.63	23.98	24.67	25.03	26.39
	12H	17.01	17.31	18.05	18.36	19.76	23.78	24.08	24.82	25.13	26.53
12H	4H	16.92	17.35	17.95	18.39	19.74	22.73	23.16	23.76	24.20	25.55
	6H	17.28	17.63	18.32	18.67	20.04	23.39	23.74	24.44	24.79	26.15
	8H	17.35	17.66	18.40	18.70	20.10	23.63	23.93	24.67	24.97	26.38