

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938199

Luminaire Tested: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6

Issue Date: 12/17/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P938199  
REPORT IS A COMBINATION OF REPORTS P933608 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13191.0 lumens  
Efficiency: N/A  
Efficacy: 116.9 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 112.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P938199  
CATALOG NUMBER: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P938199

CATALOG NUMBER: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	44	42	37	37	37	37
2	87	79	73	68	79	73	67	63	61	56	53	49	46	44	39	37	35	30	30	30	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25	25	25	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21	21	21	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	27	23	21	18	18	18	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	23	24	21	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	18	16	13	13	13	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12	12	12	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10	10	10	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9	9	9	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4732	4732	4732
5°	4621	5468	6361
10°	4190	7969	10545
15°	3560	10408	12733
20°	2897	12058	12977
25°	2416	12616	12713
30°	2036	12692	12689
35°	1800	12478	13017
40°	1567	12201	13356
45°	1418	11996	13409
50°	1299	11812	13187
55°	1243	11544	12602
60°	1271	11032	11679
65°	1321	10256	10411
70°	1404	8938	8796
75°	1550	7282	6863
80°	1679	5043	4625
85°	1467	2671	2367

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 13409 cd/sqm



TEST NUMBER: P938199

CATALOG NUMBER: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.0	0.8
10°-20°	438.5	3.3
20°-30°	767.1	5.8
30°-40°	987.5	7.5
40°-50°	1103.0	8.4
50°-60°	1056.4	8.0
60°-70°	837.2	6.3
70°-80°	492.3	3.7
80°-90°	141.0	1.1
90°-100°	546.6	4.1
100°-110°	1437.0	10.9
110°-120°	1490.0	11.3
120°-130°	1195.2	9.1
130°-140°	937.8	7.1
140°-150°	719.8	5.5
150°-160°	518.4	3.9
160°-170°	317.2	2.4
170°-180°	107.2	0.8
0°-30°	1304.6	9.9
0°-40°	2292.1	17.4
0°-60°	4451.4	33.7
0°-90°	5922.0	44.9
90°-120°	3473.6	26.3
90°-150°	6326.3	48.0
90°-180°	7269.0	55.1
0°-180°	13191.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	765	765	765	765	765	
5°	745	799	900	1018	1055	69
15°	558	1031	1736	2105	2172	155
25°	357	1168	2069	2160	2162	164
35°	241	1117	1948	2059	2140	151
45°	165	890	1722	1973	2061	127
55°	118	566	1461	1697	1744	108
65°	94	300	1085	1220	1237	93
75°	69	184	595	654	657	72
85°	25	57	148	162	165	26
90°	8	21	57	29	29	8
95°	72	283	942	485	330	80
105°	259	392	1589	2412	2250	274
115°	460	558	1273	2538	2897	454
125°	640	717	1158	1956	2307	568
135°	762	839	1121	1579	1790	590
145°	884	941	1107	1347	1452	554
155°	999	1027	1107	1215	1251	459
165°	1078	1093	1107	1151	1165	304
175°	1121	1121	1114	1129	1129	106
180°	1121	1121	1121	1121	1121	



TEST NUMBER: P938199

CATALOG NUMBER: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	764.9	764.9	764.9	764.9	764.9	764.9	764.9	764.9	764.9	764.9	764.9
2.5°	764.9	764.9	769.9	772.3	777.2	779.8	784.6	789.5	804.3	806.8	811.7
5°	745.3	755.1	787.1	799.4	833.8	880.5	900.2	932.2	998.7	1018.3	1030.6
7.5°	715.8	737.9	816.6	836.2	922.4	1045.4	1097.0	1165.9	1271.6	1323.3	1365.1
10°	669.0	715.8	855.9	902.7	1042.9	1229.9	1325.8	1421.7	1581.6	1652.9	1680.0
12.5°	617.3	693.6	897.8	961.7	1163.4	1436.4	1552.0	1657.8	1839.8	1935.8	1950.5
15°	558.3	661.6	937.1	1030.6	1291.3	1608.6	1736.5	1866.9	2036.6	2105.4	2122.7
17.5°	506.7	637.0	974.0	1072.4	1389.7	1763.6	1893.9	2002.1	2139.9	2186.6	2199.0
20°	442.7	597.7	998.7	1126.6	1493.0	1876.8	2002.1	2085.8	2179.3	2208.7	2213.7
22.5°	396.0	555.9	1013.4	1146.2	1561.9	1945.6	2051.4	2117.7	2181.7	2191.6	2194.0
25°	356.7	509.1	1011.0	1168.3	1620.9	1987.4	2068.6	2117.7	2154.7	2159.6	2159.6
27.5°	319.8	457.5	1001.1	1173.3	1665.2	1997.2	2061.2	2095.7	2112.8	2122.7	2122.7
30°	287.8	408.3	976.5	1163.4	1684.9	1987.4	2039.1	2056.3	2073.5	2088.3	2095.7
32.5°	263.2	361.5	939.5	1143.7	1687.3	1962.8	1999.7	2009.5	2034.1	2068.6	2080.8
35°	241.1	314.8	897.8	1116.7	1672.6	1923.5	1948.1	1957.9	2007.1	2058.7	2076.0
37.5°	218.9	280.4	843.7	1070.0	1650.4	1876.8	1893.9	1911.2	1987.4	2048.9	2068.6
40°	196.8	250.9	779.8	1018.3	1616.0	1820.2	1834.9	1861.9	1962.8	2034.1	2053.8
42.5°	179.6	226.3	710.9	964.2	1571.7	1756.2	1778.3	1817.7	1933.3	2009.5	2031.7
45°	164.8	201.6	637.0	890.4	1515.1	1689.7	1721.7	1775.9	1898.9	1972.7	1992.4
47.5°	150.0	184.5	560.8	814.2	1453.7	1623.4	1665.2	1726.7	1852.1	1923.5	1940.7
50°	137.7	167.2	484.6	733.0	1387.2	1552.0	1601.3	1665.2	1793.1	1859.5	1881.6
52.5°	127.9	152.5	413.2	651.8	1311.0	1478.2	1534.8	1601.3	1721.7	1785.7	1800.5
55°	118.0	140.2	351.7	565.7	1232.3	1399.5	1461.1	1525.0	1643.0	1697.2	1707.0
57.5°	113.2	130.3	300.1	484.6	1148.7	1311.0	1379.9	1438.9	1549.6	1591.4	1601.3
60°	105.7	123.0	260.8	415.7	1057.7	1227.3	1286.4	1345.5	1438.9	1473.4	1480.7
62.5°	98.4	118.0	231.2	349.2	964.2	1129.0	1188.0	1242.2	1320.8	1345.5	1355.2
65°	93.5	113.2	209.1	300.1	868.2	1025.7	1084.7	1131.4	1195.4	1220.0	1224.9
67.5°	88.6	108.2	191.9	258.2	772.3	922.4	966.7	1011.0	1060.1	1084.7	1087.2
70°	81.2	103.3	177.1	228.8	673.9	804.3	841.2	887.9	927.3	939.5	947.0
72.5°	76.3	95.9	167.2	206.6	573.1	691.2	725.6	752.6	787.1	799.4	799.4
75°	68.9	86.0	157.5	184.5	469.8	565.7	595.3	622.3	649.3	654.3	646.9
77.5°	61.5	76.3	135.3	154.9	366.5	447.7	472.3	487.0	509.1	514.1	516.6
80°	51.6	66.4	105.7	120.5	265.6	329.6	346.8	359.1	378.8	378.8	383.7
82.5°	39.3	51.6	76.3	86.0	179.6	226.3	241.1	248.5	260.8	260.8	260.8
85°	24.6	32.0	49.2	56.6	108.2	137.7	147.6	150.0	159.9	162.3	162.3
87.5°	12.3	17.2	32.0	34.4	56.6	71.3	71.3	76.3	76.3	73.8	71.3
90°	7.6	13.6	19.6	21.0	33.0	49.1	57.2	50.8	38.1	28.6	28.6
92.5°	30.1	81.3	132.5	145.3	204.2	282.8	322.1	282.3	202.7	143.0	137.3
95°	72.3	165.9	259.5	282.9	502.4	795.2	941.5	840.1	637.4	485.4	468.1
97.5°	124.9	207.5	290.1	310.8	676.7	1164.8	1408.8	1344.8	1216.7	1120.6	1087.8
100°	165.6	240.5	315.4	334.1	740.2	1281.8	1552.5	1557.2	1566.6	1573.6	1534.5
102.5°	200.2	270.1	340.0	357.5	769.4	1318.5	1593.1	1674.7	1838.0	1960.4	1927.0
105°	258.9	318.1	377.2	392.1	790.9	1322.8	1588.7	1771.6	2137.5	2411.9	2393.9
107.5°	319.1	374.2	429.5	443.2	795.0	1263.9	1498.4	1753.6	2264.0	2646.7	2651.1
110°	359.7	409.5	459.3	471.8	788.9	1211.6	1423.1	1708.3	2279.0	2707.0	2725.7



TEST NUMBER: P938199

CATALOG NUMBER: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	399.6	447.1	494.6	506.5	789.2	1166.1	1354.6	1646.5	2230.5	2668.5	2697.3
115°	459.8	503.6	547.5	558.4	796.5	1113.9	1272.6	1553.9	2116.5	2538.4	2578.3
117.5°	519.3	559.1	598.8	608.8	811.2	1081.1	1216.1	1470.0	1977.7	2358.5	2402.7
120°	553.9	591.4	628.8	638.2	823.3	1070.1	1193.5	1425.5	1889.4	2237.3	2280.3
122.5°	587.8	625.6	663.4	672.8	840.6	1064.3	1176.3	1385.2	1802.9	2116.2	2158.5
125°	639.6	674.1	708.5	717.2	864.0	1059.6	1157.5	1334.9	1689.7	1955.9	1995.0
127.5°	681.8	716.6	751.4	760.1	887.3	1056.9	1141.7	1294.0	1598.8	1827.2	1860.2
130°	704.4	741.9	779.3	788.7	904.3	1058.4	1135.6	1271.2	1542.5	1745.9	1776.4
132.5°	727.7	765.2	802.6	812.0	918.1	1059.6	1130.3	1251.8	1494.6	1676.7	1703.9
135°	762.3	796.4	830.5	839.1	933.1	1058.6	1121.3	1223.0	1426.4	1578.9	1602.3
137.5°	797.7	831.5	865.3	873.7	955.7	1065.1	1119.8	1205.7	1377.6	1506.6	1525.8
140°	827.0	858.1	889.3	897.0	969.5	1066.2	1114.5	1188.8	1337.3	1448.7	1466.7
142.5°	849.6	878.4	907.2	914.3	981.1	1070.1	1114.5	1179.8	1310.2	1408.1	1423.6
145°	884.2	909.3	934.4	940.7	996.1	1070.1	1107.0	1160.4	1267.1	1347.1	1358.8
147.5°	918.9	943.3	967.7	973.8	1018.2	1077.4	1107.0	1148.9	1233.0	1295.9	1305.6
150°	941.5	963.6	985.6	991.1	1029.8	1081.2	1107.0	1142.5	1213.4	1266.6	1274.4
152.5°	964.7	981.5	998.3	1002.4	1037.3	1083.7	1107.0	1137.2	1197.8	1243.2	1249.1
155°	999.4	1011.8	1024.1	1027.2	1053.8	1089.3	1107.0	1131.1	1179.3	1215.4	1219.4
157.5°	1025.0	1037.0	1049.0	1052.0	1070.4	1094.8	1107.0	1125.7	1163.2	1191.3	1194.0
160°	1042.3	1051.7	1061.1	1063.4	1077.9	1097.3	1107.0	1123.1	1155.1	1179.3	1180.8
162.5°	1059.6	1066.6	1073.7	1075.4	1086.0	1100.0	1107.0	1120.6	1147.6	1167.9	1169.5
165°	1078.4	1084.8	1091.2	1092.7	1097.5	1103.8	1107.0	1116.7	1136.2	1150.7	1152.2
167.5°	1095.7	1098.7	1101.8	1102.5	1106.5	1111.8	1114.5	1120.9	1133.6	1143.1	1143.8
170°	1107.0	1110.0	1113.0	1113.8	1114.1	1114.4	1114.5	1120.9	1133.6	1143.1	1143.1
172.5°	1113.0	1113.7	1114.4	1114.5	1114.5	1114.5	1114.5	1119.6	1129.6	1137.1	1136.5
175°	1121.3	1121.3	1121.3	1121.3	1119.1	1116.1	1114.5	1117.7	1124.1	1128.9	1128.9
177.5°	1121.3	1121.3	1121.3	1121.3	1119.6	1117.2	1116.0	1118.5	1123.6	1127.3	1126.7
180°	1121.3	1121.3	1121.3	1121.3	1121.3	1121.3	1121.3	1121.3	1121.3	1121.3	1121.3



TEST NUMBER: P938199

CATALOG NUMBER: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	764.9	764.9
2.5°	816.6	811.7
5°	1050.3	1055.2
7.5°	1414.4	1411.8
10°	1758.6	1780.8
12.5°	2009.5	2014.5
15°	2162.0	2171.9
17.5°	2221.0	2223.6
20°	2223.6	2218.6
22.5°	2196.4	2191.6
25°	2164.5	2162.0
27.5°	2135.0	2137.4
30°	2122.7	2130.1
32.5°	2122.7	2135.0
35°	2127.6	2139.9
37.5°	2125.1	2139.9
40°	2115.3	2132.5
42.5°	2088.3	2100.6
45°	2046.4	2061.2
47.5°	1992.4	2002.1
50°	1923.5	1933.3
52.5°	1837.3	1839.8
55°	1734.0	1743.9
57.5°	1623.4	1625.8
60°	1500.4	1507.8
62.5°	1370.1	1370.1
65°	1232.3	1237.2
67.5°	1089.6	1101.9
70°	944.5	947.0
72.5°	801.8	801.8
75°	654.3	656.7
77.5°	514.1	514.1
80°	381.2	383.7
82.5°	263.2	268.1
85°	164.8	164.8
87.5°	76.3	68.9
90°	28.6	28.6
92.5°	114.5	91.8
95°	399.2	330.3
97.5°	956.7	825.6
100°	1378.4	1222.2
102.5°	1793.1	1659.4
105°	2322.0	2250.1
107.5°	2668.4	2685.9
110°	2800.6	2875.5





TEST NUMBER: P938199

CATALOG NUMBER: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	2812.3	2927.4
115°	2737.8	2897.3
117.5°	2579.7	2756.6
120°	2452.2	2624.1
122.5°	2328.1	2497.7
125°	2151.2	2307.4
127.5°	1992.0	2123.8
130°	1898.2	2019.9
132.5°	1813.0	1922.0
135°	1696.3	1790.3
137.5°	1602.7	1679.7
140°	1538.6	1610.5
142.5°	1485.4	1547.3
145°	1405.6	1452.4
147.5°	1344.5	1383.2
150°	1305.9	1337.3
152.5°	1272.9	1296.6
155°	1235.1	1250.8
157.5°	1205.0	1216.1
160°	1187.2	1193.5
162.5°	1175.5	1181.5
165°	1158.6	1164.9
167.5°	1146.4	1149.1
170°	1143.1	1143.1
172.5°	1134.2	1131.9
175°	1128.9	1128.9
177.5°	1124.0	1121.3
180°	1121.3	1121.3



TEST NUMBER: P938199  
 CATALOG NUMBER: SQ4-FB-125U-125D-B35-1D-UNV-STD-W-6

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.92	6.77	6.91	7.78	9.12	19.08	19.93	20.07	20.94	22.28
	3H	6.62	7.39	7.62	8.40	9.76	20.91	21.68	21.92	22.70	24.06
	4H	6.92	7.64	7.93	8.66	10.03	21.56	22.28	22.57	23.30	24.67
	6H	7.17	7.84	8.20	8.86	10.24	21.98	22.65	23.01	23.68	25.06
	8H	7.24	7.87	8.27	8.92	10.29	22.10	22.74	23.13	23.78	25.16
	12H	7.25	7.86	8.29	8.90	10.30	22.17	22.77	23.20	23.81	25.21
4H	2H	13.12	13.85	14.14	14.87	16.24	19.35	20.08	20.38	21.10	22.47
	3H	14.69	15.30	15.72	16.35	17.73	21.39	22.00	22.43	23.05	24.43
	4H	14.78	15.34	15.82	16.38	17.78	22.16	22.71	23.20	23.75	25.16
	6H	14.79	15.27	15.84	16.34	17.74	22.69	23.17	23.74	24.24	25.63
	8H	14.77	15.22	15.82	16.28	17.69	22.85	23.30	23.90	24.36	25.77
	12H	14.73	15.13	15.79	16.20	17.62	22.94	23.35	24.01	24.42	25.84
8H	4H	16.22	16.67	17.27	17.73	19.14	22.22	22.67	23.27	23.72	25.14
	6H	16.47	16.84	17.54	17.94	19.35	22.84	23.21	23.92	24.31	25.72
	8H	16.48	16.81	17.56	17.89	19.32	23.06	23.39	24.14	24.47	25.90
	12H	16.45	16.74	17.54	17.82	19.29	23.20	23.49	24.29	24.57	26.04
12H	4H	16.37	16.77	17.43	17.84	19.26	22.17	22.58	23.24	23.65	25.07
	6H	16.72	17.05	17.80	18.13	19.56	22.82	23.15	23.91	24.23	25.67
	8H	16.79	17.08	17.88	18.16	19.63	23.05	23.34	24.14	24.42	25.89