

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938399

Luminaire Tested: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938399
REPORT IS A COMBINATION OF REPORTS P933638 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12258.8 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 95.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938399
CATALOG NUMBER: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P938399

CATALOG NUMBER: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	36	36	36	29
1	93	88	84	81	83	79	76	73	62	60	58	46	45	43	32	31	30	30	30	30	23
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	27	26	25	25	25	25	19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21	21	21	21	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	17	17	17	17	13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	15	15	15	11
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13	13	13	13	10
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11	11	11	11	8
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10	10	10	10	7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	10	9	9	9	9	6
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2796	2796	2796
5°	2731	3231	3759
10°	2476	4709	6231
15°	2103	6151	7525
20°	1712	7126	7669
25°	1428	7456	7513
30°	1203	7501	7499
35°	1063	7375	7693
40°	926	7210	7894
45°	838	7089	7924
50°	768	6980	7793
55°	735	6822	7447
60°	752	6519	6902
65°	780	6061	6152
70°	830	5282	5197
75°	916	4302	4056
80°	993	2980	2732
85°	864	1578	1399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7924 cd/sqm



TEST NUMBER: P938399

CATALOG NUMBER: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.5	0.5
10°-20°	259.2	2.1
20°-30°	453.3	3.7
30°-40°	583.6	4.8
40°-50°	651.8	5.3
50°-60°	624.3	5.1
60°-70°	494.7	4.0
70°-80°	290.9	2.4
80°-90°	86.0	0.7
90°-100°	658.4	5.4
100°-110°	1731.1	14.1
110°-120°	1794.9	14.6
120°-130°	1439.7	11.7
130°-140°	1129.7	9.2
140°-150°	867.1	7.1
150°-160°	624.4	5.1
160°-170°	382.1	3.1
170°-180°	129.1	1.1
0°-30°	771.0	6.3
0°-40°	1354.5	11.0
0°-60°	2630.6	21.5
0°-90°	3502.2	28.6
90°-120°	4184.4	34.1
90°-150°	7621.0	62.2
90°-180°	8757.0	71.4
0°-180°	12258.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	452	452	452	452	452	
5°	440	472	532	602	624	41
15°	330	609	1026	1244	1284	92
25°	211	690	1222	1276	1278	97
35°	142	660	1151	1217	1265	89
45°	97	526	1017	1166	1218	75
55°	70	334	863	1003	1030	64
65°	55	177	641	721	731	55
75°	41	109	352	387	388	43
85°	14	33	87	96	97	15
90°	9	25	69	34	34	8
95°	87	341	1134	585	398	97
105°	312	472	1914	2906	2711	331
115°	554	673	1533	3058	3490	547
125°	770	864	1394	2356	2780	684
135°	918	1011	1351	1902	2157	711
145°	1065	1133	1334	1623	1750	667
155°	1204	1237	1334	1464	1507	553
165°	1299	1316	1334	1386	1403	367
175°	1351	1351	1343	1360	1360	128
180°	1351	1351	1351	1351	1351	



TEST NUMBER: P938399

CATALOG NUMBER: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0
2.5°	452.0	452.0	454.9	456.4	459.3	460.8	463.7	466.6	475.3	476.7	479.7
5°	440.4	446.2	465.1	472.4	492.7	520.4	532.0	550.9	590.1	601.7	609.0
7.5°	423.0	436.0	482.6	494.2	545.1	617.7	648.3	689.0	751.5	782.0	806.7
10°	395.4	423.0	505.8	533.4	616.3	726.8	783.4	840.1	934.6	976.8	992.7
12.5°	364.8	409.9	530.5	568.3	687.5	848.8	917.2	979.7	1087.2	1144.0	1152.7
15°	329.9	391.0	553.8	609.0	763.1	950.6	1026.2	1103.3	1203.6	1244.3	1254.5
17.5°	299.4	376.5	575.6	633.7	821.2	1042.2	1119.3	1183.2	1264.6	1292.3	1299.5
20°	261.6	353.2	590.1	665.7	882.3	1109.1	1183.2	1232.7	1287.9	1305.3	1308.2
22.5°	234.0	328.5	598.8	677.3	923.0	1149.8	1212.3	1251.6	1289.4	1295.2	1296.6
25°	210.8	300.9	597.4	690.4	957.9	1174.5	1222.5	1251.6	1273.4	1276.3	1276.3
27.5°	189.0	270.4	591.6	693.3	984.0	1180.3	1218.1	1238.5	1248.7	1254.5	1254.5
30°	170.1	241.3	577.0	687.5	995.6	1174.5	1205.0	1215.2	1225.4	1234.1	1238.5
32.5°	155.5	213.7	555.2	675.9	997.1	1160.0	1181.8	1187.6	1202.1	1222.5	1229.8
35°	142.4	186.0	530.5	659.9	988.4	1136.7	1151.3	1157.1	1186.2	1216.7	1226.9
37.5°	129.4	165.7	498.6	632.3	975.3	1109.1	1119.3	1129.5	1174.5	1210.9	1222.5
40°	116.3	148.3	460.8	601.7	954.9	1075.6	1084.3	1100.3	1160.0	1202.1	1213.8
42.5°	106.1	133.7	420.1	569.8	928.8	1037.8	1050.9	1074.1	1142.5	1187.6	1200.7
45°	97.4	119.2	376.5	526.2	895.4	998.6	1017.4	1049.4	1122.2	1165.8	1177.4
47.5°	88.7	109.0	331.4	481.1	859.0	959.3	984.0	1020.4	1094.5	1136.7	1146.9
50°	81.4	98.8	286.3	433.1	819.8	917.2	946.2	984.0	1059.6	1098.8	1112.0
52.5°	75.6	90.1	244.2	385.2	774.7	873.6	907.0	946.2	1017.4	1055.2	1064.0
55°	69.8	82.8	207.9	334.3	728.2	827.0	863.4	901.2	970.9	1002.9	1008.7
57.5°	66.9	77.0	177.3	286.3	678.8	774.7	815.4	850.3	915.7	940.4	946.2
60°	62.5	72.7	154.1	245.6	625.0	725.3	760.2	795.1	850.3	870.6	875.0
62.5°	58.1	69.8	136.6	206.4	569.8	667.2	702.0	734.0	780.5	795.1	800.9
65°	55.2	66.9	123.5	177.3	513.1	606.1	641.0	668.6	706.4	720.9	723.8
67.5°	52.3	64.0	113.4	152.6	456.4	545.1	571.2	597.4	626.5	641.0	642.4
70°	48.0	61.0	104.7	135.2	398.3	475.3	497.1	524.7	548.0	555.2	559.6
72.5°	45.1	56.7	98.8	122.1	338.7	408.4	428.8	444.8	465.1	472.4	472.4
75°	40.7	50.9	93.0	109.0	277.6	334.3	351.7	367.7	383.7	386.6	382.3
77.5°	36.3	45.1	79.9	91.6	216.6	264.5	279.1	287.8	300.9	303.8	305.2
80°	30.5	39.2	62.5	71.2	157.0	194.8	204.9	212.2	223.8	223.8	226.7
82.5°	23.3	30.5	45.1	50.9	106.1	133.7	142.4	146.8	154.1	154.1	154.1
85°	14.5	18.9	29.1	33.4	64.0	81.4	87.2	88.7	94.5	95.9	95.9
87.5°	7.3	10.2	18.9	20.3	33.4	42.2	42.2	45.1	45.1	43.6	42.2
90°	9.1	16.4	23.5	25.4	39.9	59.2	68.9	61.2	45.9	34.5	34.5
92.5°	36.2	97.9	159.6	175.0	246.0	340.7	388.0	340.0	244.2	172.3	165.4
95°	87.0	199.8	312.7	340.9	605.3	957.9	1134.1	1012.0	767.8	584.7	564.0
97.5°	150.5	250.0	349.5	374.4	815.3	1403.2	1697.1	1620.0	1465.6	1349.9	1310.4
100°	199.4	289.7	379.9	402.5	891.8	1544.1	1870.3	1875.9	1887.2	1895.7	1848.7
102.5°	241.2	325.4	409.6	430.6	926.8	1588.4	1919.2	2017.5	2214.1	2361.5	2321.2
105°	311.8	383.1	454.5	472.3	952.8	1593.4	1913.8	2134.1	2574.9	2905.5	2883.8
107.5°	384.4	450.9	517.3	533.9	957.6	1522.5	1805.0	2112.4	2727.3	3188.4	3193.6
110°	433.3	493.4	553.4	568.4	950.4	1459.6	1714.3	2058.0	2745.4	3260.9	3283.5



TEST NUMBER: P938399

CATALOG NUMBER: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	481.4	538.6	595.7	610.1	950.7	1404.8	1631.8	1983.5	2687.0	3214.7	3249.3
115°	553.9	606.7	659.5	672.7	959.4	1341.8	1533.0	1871.8	2549.5	3057.8	3105.8
117.5°	625.5	673.5	721.4	733.4	977.3	1302.4	1465.0	1770.8	2382.4	2841.1	2894.4
120°	667.3	712.4	757.6	768.8	991.8	1289.2	1437.8	1717.3	2276.1	2695.2	2746.9
122.5°	708.0	753.6	799.1	810.5	1012.6	1282.2	1417.0	1668.6	2171.8	2549.2	2600.3
125°	770.5	812.0	853.6	864.0	1040.7	1276.5	1394.3	1608.1	2035.5	2356.1	2403.1
127.5°	821.3	863.2	905.1	915.6	1068.8	1273.1	1375.2	1558.7	1925.8	2201.1	2240.8
130°	848.6	893.7	938.9	950.1	1089.4	1275.2	1368.0	1531.4	1858.2	2103.2	2139.8
132.5°	876.7	921.8	967.0	978.2	1106.0	1276.5	1361.6	1507.9	1800.4	2019.8	2052.6
135°	918.3	959.4	1000.6	1010.9	1124.1	1275.2	1350.8	1473.3	1718.2	1902.0	1930.2
137.5°	961.0	1001.7	1042.4	1052.5	1151.4	1283.1	1348.9	1452.5	1659.6	1814.9	1838.1
140°	996.3	1033.8	1071.2	1080.6	1167.9	1284.4	1342.6	1432.1	1611.0	1745.2	1766.8
142.5°	1023.5	1058.1	1092.8	1101.5	1181.9	1289.1	1342.6	1421.2	1578.3	1696.1	1714.7
145°	1065.2	1095.5	1125.7	1133.2	1200.0	1289.1	1333.5	1397.8	1526.4	1622.8	1636.8
147.5°	1106.9	1136.3	1165.7	1173.1	1226.6	1297.9	1333.5	1384.1	1485.2	1561.1	1572.8
150°	1134.1	1160.7	1187.2	1193.9	1240.4	1302.5	1333.5	1376.3	1461.6	1525.7	1535.2
152.5°	1162.2	1182.4	1202.5	1207.6	1249.5	1305.5	1333.5	1370.0	1442.9	1497.6	1504.8
155°	1203.9	1218.8	1233.7	1237.4	1269.5	1312.2	1333.5	1362.5	1420.6	1464.1	1468.8
157.5°	1234.7	1249.2	1263.8	1267.4	1289.4	1318.8	1333.5	1356.1	1401.3	1435.1	1438.4
160°	1255.6	1266.9	1278.1	1280.9	1298.5	1321.8	1333.5	1352.9	1391.6	1420.6	1422.5
162.5°	1276.5	1284.9	1293.3	1295.5	1308.1	1325.1	1333.5	1349.8	1382.5	1407.0	1408.8
165°	1299.1	1306.8	1314.4	1316.3	1322.0	1329.7	1333.5	1345.3	1368.6	1386.2	1388.1
167.5°	1320.0	1323.6	1327.2	1328.1	1333.0	1339.4	1342.6	1350.3	1365.6	1377.0	1377.8
170°	1333.5	1337.1	1340.8	1341.7	1342.0	1342.5	1342.6	1350.3	1365.6	1377.0	1377.0
172.5°	1340.8	1341.6	1342.5	1342.6	1342.6	1342.6	1342.6	1348.7	1360.8	1369.8	1369.1
175°	1350.8	1350.8	1350.8	1350.8	1348.1	1344.5	1342.6	1346.4	1354.1	1359.8	1359.8
177.5°	1350.8	1350.8	1350.8	1350.8	1348.7	1345.8	1344.4	1347.4	1353.5	1358.1	1357.3
180°	1350.8	1350.8	1350.8	1350.8	1350.8	1350.8	1350.8	1350.8	1350.8	1350.8	1350.8



TEST NUMBER: P938399

CATALOG NUMBER: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	452.0	452.0
2.5°	482.6	479.7
5°	620.6	623.6
7.5°	835.8	834.3
10°	1039.3	1052.3
12.5°	1187.6	1190.5
15°	1277.7	1283.5
17.5°	1312.6	1314.1
20°	1314.1	1311.2
22.5°	1298.1	1295.2
25°	1279.2	1277.7
27.5°	1261.7	1263.2
30°	1254.5	1258.8
32.5°	1254.5	1261.7
35°	1257.4	1264.6
37.5°	1255.9	1264.6
40°	1250.1	1260.3
42.5°	1234.1	1241.4
45°	1209.4	1218.1
47.5°	1177.4	1183.2
50°	1136.7	1142.5
52.5°	1085.8	1087.2
55°	1024.7	1030.5
57.5°	959.3	960.8
60°	886.6	891.0
62.5°	809.6	809.6
65°	728.2	731.1
67.5°	643.9	651.2
70°	558.1	559.6
72.5°	473.8	473.8
75°	386.6	388.1
77.5°	303.8	303.8
80°	225.3	226.7
82.5°	155.5	158.4
85°	97.4	97.4
87.5°	45.1	40.7
90°	34.5	34.5
92.5°	138.0	110.6
95°	480.9	398.0
97.5°	1152.4	994.5
100°	1660.5	1472.3
102.5°	2160.1	1999.0
105°	2797.2	2710.6
107.5°	3214.6	3235.5
110°	3373.7	3464.0



TEST NUMBER: P938399
CATALOG NUMBER: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3387.9	3526.5
115°	3298.0	3490.2
117.5°	3107.6	3320.8
120°	2954.1	3161.2
122.5°	2804.6	3008.8
125°	2591.3	2779.5
127.5°	2399.5	2558.4
130°	2286.5	2433.2
132.5°	2183.9	2315.3
135°	2043.5	2156.7
137.5°	1930.8	2023.5
140°	1853.4	1940.0
142.5°	1789.4	1863.9
145°	1693.2	1749.6
147.5°	1619.5	1666.3
150°	1573.1	1611.0
152.5°	1533.3	1562.0
155°	1487.7	1506.7
157.5°	1451.8	1465.0
160°	1430.1	1437.8
162.5°	1416.0	1423.3
165°	1395.7	1403.3
167.5°	1381.1	1384.3
170°	1377.0	1377.0
172.5°	1366.3	1363.5
175°	1359.8	1359.8
177.5°	1354.0	1350.8
180°	1350.8	1350.8



TEST NUMBER: P938399
 CATALOG NUMBER: SQ4-FB-150U-075D-B35-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.18	2.90	3.30	4.01	5.56	15.35	16.06	16.47	17.18	18.72
	3H	2.88	3.52	4.00	4.64	6.20	17.17	17.81	18.30	18.94	20.50
	4H	3.17	3.78	4.30	4.90	6.47	17.81	18.42	18.94	19.54	21.11
	6H	3.41	3.97	4.56	5.10	6.68	18.23	18.79	19.37	19.91	21.49
	8H	3.48	4.01	4.62	5.15	6.72	18.34	18.87	19.49	20.02	21.59
	12H	3.49	4.00	4.64	5.13	6.73	18.40	18.91	19.55	20.04	21.64
4H	2H	9.37	9.98	10.51	11.11	12.67	15.61	16.22	16.75	17.34	18.91
	3H	10.93	11.44	12.08	12.59	14.17	17.63	18.14	18.78	19.29	20.87
	4H	11.02	11.49	12.17	12.62	14.22	18.39	18.86	19.54	20.00	21.60
	6H	11.02	11.42	12.17	12.58	14.17	18.92	19.32	20.07	20.48	22.07
	8H	10.99	11.37	12.15	12.52	14.13	19.07	19.45	20.23	20.60	22.21
	12H	10.94	11.28	12.11	12.45	14.06	19.15	19.50	20.33	20.66	22.27
8H	4H	12.44	12.82	13.60	13.97	15.58	18.44	18.81	19.59	19.97	21.57
	6H	12.68	12.99	13.86	14.19	15.79	19.06	19.37	20.23	20.56	22.16
	8H	12.70	12.97	13.88	14.14	15.76	19.27	19.54	20.45	20.71	22.34
	12H	12.66	12.90	13.84	14.07	15.72	19.40	19.64	20.59	20.81	22.47
12H	4H	12.58	12.92	13.75	14.08	15.70	18.38	18.72	19.56	19.89	21.50
	6H	12.94	13.21	14.12	14.38	16.00	19.04	19.31	20.22	20.48	22.10
	8H	13.00	13.24	14.18	14.41	16.06	19.26	19.50	20.44	20.67	22.32