

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844823

Luminaire Tested: **SQ4P-BB-050U-075D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P844823
REPORT IS A COMBINATION OF REPORTS P700188 AND P700244
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-BB-050U-075D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3504.5 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 38.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844823

CATALOG NUMBER: SQ4P-BB-050U-075D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P844823

CATALOG NUMBER: SQ4P-BB-050U-075D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51								
1	100	96	93	90	92	89	87	84	76	74	73	64	63	62	53	53	52	47								
2	92	86	81	77	86	80	76	72	69	66	63	59	57	55	49	48	47	42								
3	86	78	71	66	79	72	67	63	63	59	55	54	51	49	45	44	42	38								
4	79	70	63	58	74	66	60	55	57	53	49	49	46	43	42	40	38	34								
5	74	63	56	51	68	60	53	49	52	47	44	45	42	39	39	36	34	31								
6	68	58	51	45	64	54	48	43	48	43	39	42	38	35	36	33	31	29								
7	64	53	46	41	59	50	43	39	44	39	35	39	35	32	34	31	29	26								
8	60	49	42	37	56	46	40	35	41	36	32	36	32	29	31	28	26	24								
9	56	45	38	33	52	42	36	32	38	33	29	33	30	27	29	26	24	22								
10	53	42	35	30	49	39	33	29	35	30	27	31	27	25	27	25	23	21								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13873	13873	13873
5°	13650	13616	13718
10°	12770	12942	13303
15°	11611	11979	12646
20°	10307	10842	11792
25°	8975	9686	10835
30°	7689	8533	9928
35°	6374	7243	8831
40°	4897	5792	7525
45°	3542	4385	6055
50°	2411	3267	4804
55°	1568	2363	3732
60°	899	1664	2700
65°	238	1017	1367
70°	119	313	391
75°	53	25	0
80°	37	0	0
85°	0	0	0



TEST NUMBER: P844823

CATALOG NUMBER: SQ4P-BB-050U-075D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	3.9
10°-20°	350.9	10.0
20°-30°	439.3	12.5
30°-40°	405.8	11.6
40°-50°	272.7	7.8
50°-60°	140.8	4.0
60°-70°	44.1	1.3
70°-80°	2.8	0.1
80°-90°	0.7	0.0
90°-100°	104.9	3.0
100°-110°	364.9	10.4
110°-120°	353.5	10.1
120°-130°	277.3	7.9
130°-140°	219.5	6.3
140°-150°	169.4	4.8
150°-160°	121.4	3.5
160°-170°	74.3	2.1
170°-180°	25.1	0.7
0°-30°	927.5	26.5
0°-40°	1333.3	38.0
0°-60°	1746.8	49.8
0°-90°	1794.4	51.2
90°-120°	823.3	23.5
90°-150°	1489.4	42.5
90°-180°	1710.0	48.8
0°-180°	3504.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1504	1504	1504	1504	1504	
5°	1474	1459	1470	1475	1481	137
15°	1216	1211	1254	1296	1324	339
25°	882	889	952	1017	1064	404
35°	566	580	643	719	784	351
45°	272	288	336	402	464	213
55°	98	114	147	189	232	91
65°	11	21	47	56	63	18
75°	2	2	1	0	0	2
85°	0	0	0	0	0	0
90°	4	6	6	4	2	2
95°	18	61	177	45	28	19
105°	61	86	384	647	602	64
115°	106	128	285	602	710	105
125°	144	177	266	448	535	129
135°	173	195	264	374	423	134
145°	203	216	262	322	350	127
155°	230	238	258	287	297	106
165°	252	254	260	271	273	71
175°	264	264	262	266	264	25
180°	264	264	264	264	264	



TEST NUMBER: P844823

CATALOG NUMBER: SQ4P-BB-050U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1503.7	1503.7	1503.7	1503.7	1503.7
2.5°	1507.1	1493.0	1496.6	1496.6	1492.6
5°	1473.8	1458.8	1470.2	1475.4	1481.2
7.5°	1411.6	1399.9	1421.7	1437.8	1449.6
10°	1363.1	1353.3	1381.4	1403.6	1420.0
12.5°	1307.4	1299.6	1333.7	1364.2	1385.1
15°	1215.6	1211.4	1254.1	1296.1	1324.0
17.5°	1117.3	1117.1	1165.9	1218.2	1251.7
20°	1049.8	1052.0	1104.3	1161.9	1201.0
22.5°	982.3	987.2	1043.2	1103.3	1148.1
25°	881.6	888.7	951.5	1016.6	1064.3
27.5°	785.1	795.5	861.5	929.1	987.2
30°	721.7	733.7	801.0	872.1	931.9
32.5°	659.3	673.7	739.1	814.6	875.3
35°	565.9	580.2	643.1	718.8	784.1
37.5°	469.5	483.4	544.8	619.4	690.1
40°	406.6	422.3	480.9	553.1	624.8
42.5°	349.6	365.3	420.3	491.2	559.2
45°	271.5	287.7	336.1	401.5	464.1
47.5°	206.6	224.2	266.7	326.0	382.9
50°	168.0	185.7	227.6	279.8	334.7
52.5°	137.2	154.5	192.2	241.3	291.5
55°	97.5	113.8	146.9	188.8	232.0
57.5°	67.3	81.5	111.2	145.9	180.1
60°	48.7	62.2	90.2	118.4	146.3
62.5°	32.5	44.8	72.1	93.8	112.5
65°	10.9	20.9	46.6	56.2	62.6
67.5°	5.6	6.6	24.4	25.8	28.0
70°	4.4	4.4	11.6	12.3	14.5
72.5°	3.1	3.1	4.6	6.0	6.5
75°	1.5	1.5	0.7	0.0	0.0
77.5°	0.7	0.7	0.7	0.0	0.0
80°	0.7	0.7	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.9	5.9	5.9	3.9	2.0
92.5°	9.8	29.5	27.5	11.8	9.8
95°	17.7	61.0	177.0	45.2	27.5
97.5°	27.5	68.8	353.9	161.3	86.5
100°	37.4	72.8	413.0	387.4	249.7
102.5°	49.1	78.7	411.0	544.7	448.4
105°	61.0	86.5	383.5	646.9	601.7



TEST NUMBER: P844823

CATALOG NUMBER: SQ4P-BB-050U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	94.4	116.1	299.0	650.9	741.4
115°	106.2	127.8	285.2	601.7	709.9
117.5°	118.0	141.6	277.2	556.5	664.6
120°	127.8	153.3	271.4	513.3	619.4
122.5°	135.7	165.2	267.4	477.8	574.2
125°	143.6	177.0	265.5	448.4	534.9
127.5°	151.4	184.9	265.5	426.8	499.5
130°	159.3	188.8	263.5	405.1	470.0
132.5°	167.1	190.7	263.5	389.4	444.5
135°	173.0	194.6	263.5	373.6	422.8
137.5°	180.9	198.6	263.5	359.8	405.1
140°	186.8	204.5	263.5	346.1	385.5
142.5°	194.6	210.4	263.5	332.3	367.7
145°	202.6	216.4	261.6	322.5	350.0
147.5°	210.4	222.2	259.6	312.7	334.3
150°	216.4	228.1	259.6	302.9	320.6
152.5°	224.2	234.0	257.7	293.0	308.7
155°	230.1	238.0	257.7	287.1	296.9
157.5°	235.9	243.9	257.7	281.2	289.1
160°	241.9	247.8	259.6	277.2	283.2
162.5°	247.8	251.7	259.6	273.3	277.2
165°	251.7	253.6	259.6	271.4	273.3
167.5°	255.6	257.7	259.6	269.4	269.4
170°	257.7	259.6	261.6	267.4	267.4
172.5°	261.6	261.6	261.6	265.5	265.5
175°	263.5	263.5	261.6	265.5	263.5
177.5°	263.5	263.5	261.6	265.5	263.5
180°	263.5	263.5	263.5	263.5	263.5



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	72.8	96.4	348.1	692.2	700.1
110°	82.6	106.2	320.6	686.3	743.3



(END OF REPORT)