

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844829

Luminaire Tested: **SQ4P-BB-050U-125D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P844829
REPORT IS A COMBINATION OF REPORTS P700190 AND P700244
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-BB-050U-125D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4659.2 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844829

CATALOG NUMBER: SQ4P-BB-050U-125D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P844829

CATALOG NUMBER: SQ4P-BB-050U-125D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63																			
1	103	99	96	94	97	94	91	89	83	81	79	73	72	70	64	63	62	58																			
2	96	90	85	80	90	85	80	77	75	72	69	67	65	62	59	57	56	52																			
3	89	81	75	70	84	77	71	67	69	65	61	61	58	56	55	52	50	47																			
4	83	73	67	61	78	70	64	59	63	58	54	56	53	50	50	48	46	43																			
5	77	67	60	55	72	64	57	53	58	53	49	52	48	45	47	44	41	39																			
6	72	61	54	49	68	58	52	47	53	48	44	48	44	41	43	40	38	35																			
7	67	56	49	44	63	54	47	43	49	44	40	45	40	37	40	37	35	32																			
8	63	52	45	40	59	50	43	39	45	40	36	41	37	34	38	34	32	30																			
9	59	48	41	36	56	46	40	35	42	37	33	39	34	31	35	32	29	28																			
10	56	44	38	33	53	43	37	33	39	34	31	36	32	29	33	30	27	26																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22804	22804	22804
5°	22437	22382	22548
10°	20992	21274	21868
15°	19085	19691	20787
20°	16942	17821	19382
25°	14753	15920	17809
30°	12638	14025	16318
35°	10477	11906	14517
40°	8050	9521	12370
45°	5821	7209	9954
50°	3964	5370	7896
55°	2578	3885	6135
60°	1478	2738	4436
65°	391	1672	2244
70°	197	518	642
75°	86	39	0
80°	58	0	0
85°	0	0	0



TEST NUMBER: P844829

CATALOG NUMBER: SQ4P-BB-050U-125D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.6	4.8
10°-20°	576.8	12.4
20°-30°	722.1	15.5
30°-40°	667.0	14.3
40°-50°	448.2	9.6
50°-60°	231.5	5.0
60°-70°	72.5	1.6
70°-80°	4.6	0.1
80°-90°	0.7	0.0
90°-100°	104.9	2.3
100°-110°	364.9	7.8
110°-120°	353.5	7.6
120°-130°	277.3	6.0
130°-140°	219.5	4.7
140°-150°	169.4	3.6
150°-160°	121.4	2.6
160°-170°	74.3	1.6
170°-180°	25.1	0.5
0°-30°	1524.5	32.7
0°-40°	2191.6	47.0
0°-60°	2871.3	61.6
0°-90°	2949.0	63.3
90°-120°	823.3	17.7
90°-150°	1489.4	32.0
90°-180°	1710.0	36.7
0°-180°	4659.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2472	2472	2472	2472	2472	
5°	2423	2398	2417	2425	2435	225
15°	1998	1991	2062	2130	2176	557
25°	1449	1461	1564	1671	1749	664
35°	930	954	1057	1181	1289	576
45°	446	473	552	660	763	350
55°	160	187	242	310	381	150
65°	18	34	77	92	103	30
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	4	6	6	4	2	2
95°	18	61	177	45	28	19
105°	61	86	384	647	602	64
115°	106	128	285	602	710	105
125°	144	177	266	448	535	129
135°	173	195	264	374	423	134
145°	203	216	262	322	350	127
155°	230	238	258	287	297	106
165°	252	254	260	271	273	71
175°	264	264	262	266	264	25
180°	264	264	264	264	264	



TEST NUMBER: P844829

CATALOG NUMBER: SQ4P-BB-050U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2471.7	2471.7	2471.7	2471.7	2471.7
2.5°	2477.3	2454.0	2460.0	2460.0	2453.6
5°	2422.6	2398.1	2416.7	2425.1	2434.6
7.5°	2320.4	2301.1	2336.8	2363.3	2382.9
10°	2240.7	2224.5	2270.8	2307.1	2334.2
12.5°	2148.9	2136.2	2192.3	2242.4	2276.7
15°	1998.1	1991.2	2061.5	2130.5	2176.3
17.5°	1836.6	1836.3	1916.4	2002.5	2057.4
20°	1725.6	1729.1	1815.1	1910.0	1974.1
22.5°	1614.5	1622.7	1714.7	1813.6	1887.2
25°	1449.2	1460.8	1563.9	1671.2	1749.4
27.5°	1290.5	1307.6	1416.2	1527.2	1622.7
30°	1186.3	1206.1	1316.5	1433.5	1531.7
32.5°	1083.7	1107.5	1215.0	1339.0	1438.9
35°	930.2	953.7	1057.1	1181.4	1288.9
37.5°	771.8	794.6	895.6	1018.2	1134.4
40°	668.4	694.1	790.5	909.1	1027.1
42.5°	574.7	600.4	690.9	807.5	919.1
45°	446.1	472.9	552.5	660.0	762.9
47.5°	339.5	368.4	438.3	535.8	629.4
50°	276.2	305.4	374.1	459.9	550.1
52.5°	225.5	253.9	315.9	396.6	479.2
55°	160.3	187.1	241.5	310.2	381.4
57.5°	110.7	134.0	182.7	239.8	295.9
60°	80.1	102.4	148.4	194.6	240.4
62.5°	53.3	73.6	118.6	154.3	184.9
65°	17.9	34.3	76.6	92.3	102.8
67.5°	9.2	10.9	40.0	42.5	46.0
70°	7.3	7.3	19.2	20.3	23.8
72.5°	5.2	5.2	7.5	9.8	10.6
75°	2.4	2.4	1.1	0.0	0.0
77.5°	1.1	1.1	1.1	0.0	0.0
80°	1.1	1.1	0.0	0.0	0.0
82.5°	0.3	0.3	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.9	5.9	5.9	3.9	2.0
92.5°	9.8	29.5	27.5	11.8	9.8
95°	17.7	61.0	177.0	45.2	27.5
97.5°	27.5	68.8	353.9	161.3	86.5
100°	37.4	72.8	413.0	387.4	249.7
102.5°	49.1	78.7	411.0	544.7	448.4
105°	61.0	86.5	383.5	646.9	601.7



TEST NUMBER: P844829

CATALOG NUMBER: SQ4P-BB-050U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	94.4	116.1	299.0	650.9	741.4
115°	106.2	127.8	285.2	601.7	709.9
117.5°	118.0	141.6	277.2	556.5	664.6
120°	127.8	153.3	271.4	513.3	619.4
122.5°	135.7	165.2	267.4	477.8	574.2
125°	143.6	177.0	265.5	448.4	534.9
127.5°	151.4	184.9	265.5	426.8	499.5
130°	159.3	188.8	263.5	405.1	470.0
132.5°	167.1	190.7	263.5	389.4	444.5
135°	173.0	194.6	263.5	373.6	422.8
137.5°	180.9	198.6	263.5	359.8	405.1
140°	186.8	204.5	263.5	346.1	385.5
142.5°	194.6	210.4	263.5	332.3	367.7
145°	202.6	216.4	261.6	322.5	350.0
147.5°	210.4	222.2	259.6	312.7	334.3
150°	216.4	228.1	259.6	302.9	320.6
152.5°	224.2	234.0	257.7	293.0	308.7
155°	230.1	238.0	257.7	287.1	296.9
157.5°	235.9	243.9	257.7	281.2	289.1
160°	241.9	247.8	259.6	277.2	283.2
162.5°	247.8	251.7	259.6	273.3	277.2
165°	251.7	253.6	259.6	271.4	273.3
167.5°	255.6	257.7	259.6	269.4	269.4
170°	257.7	259.6	261.6	267.4	267.4
172.5°	261.6	261.6	261.6	265.5	265.5
175°	263.5	263.5	261.6	265.5	263.5
177.5°	263.5	263.5	261.6	265.5	263.5
180°	263.5	263.5	263.5	263.5	263.5



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	72.8	96.4	348.1	692.2	700.1
110°	82.6	106.2	320.6	686.3	743.3



(END OF REPORT)