

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844901

Luminaire Tested: **SQ4P-F-025U-125D-B35-1D-UNV**

Issue Date: 8/14/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P844901  
REPORT IS A COMBINATION OF REPORTS P700166 AND P700243  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-F-025U-125D-B35-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT  
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5580.8 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 52.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844901

CATALOG NUMBER: SQ4P-F-025U-125D-B35-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P844901

CATALOG NUMBER: SQ4P-F-025U-125D-B35-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	115	115	115	115	111	111	111	111	103	103	103	95	95	95	88	88	88	85			
1	106	101	97	93	101	97	94	90	90	87	85	84	81	79	78	76	74	71			
2	96	88	82	76	92	85	79	74	79	74	70	73	70	66	68	65	62	60			
3	88	77	70	63	84	75	68	62	70	64	59	65	60	56	60	56	53	50			
4	80	69	60	54	77	66	58	52	62	55	50	58	52	48	54	49	46	43			
5	74	61	52	46	71	59	51	45	55	49	43	52	46	41	49	44	40	37			
6	68	55	46	40	65	53	45	39	50	43	38	47	41	36	44	39	35	33			
7	63	50	41	35	60	48	40	35	45	38	33	43	37	32	40	35	31	29			
8	59	45	37	31	56	44	36	31	42	35	30	39	33	29	37	32	28	26			
9	55	42	34	28	53	40	33	28	38	32	27	36	30	26	34	29	25	23			
10	51	38	31	26	49	37	30	25	35	29	24	33	28	24	32	26	23	21			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15986	15986	15986
5°	16028	15835	15962
10°	15972	15777	15886
15°	15862	15664	15798
20°	15712	15532	15646
25°	15537	15349	15493
30°	15322	15198	15296
35°	15156	14973	15049
40°	14867	14723	14753
45°	14559	14439	14439
50°	14252	14119	14053
55°	13919	13732	13658
60°	13400	13184	13099
65°	12760	12509	12354
70°	11888	11635	11386
75°	10662	10334	10085
80°	8629	8517	8257
85°	5124	5907	6129



TEST NUMBER: P844901

CATALOG NUMBER: SQ4P-F-025U-125D-B35-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.5	2.9
10°-20°	465.6	8.3
20°-30°	699.3	12.5
30°-40°	834.8	15.0
40°-50°	855.4	15.3
50°-60°	762.9	13.7
60°-70°	568.1	10.2
70°-80°	308.4	5.5
80°-90°	71.7	1.3
90°-100°	52.2	0.9
100°-110°	181.6	3.3
110°-120°	175.9	3.2
120°-130°	138.0	2.5
130°-140°	109.2	2.0
140°-150°	84.3	1.5
150°-160°	60.4	1.1
160°-170°	37.0	0.7
170°-180°	12.5	0.2
0°-30°	1328.4	23.8
0°-40°	2163.2	38.8
0°-60°	3781.5	67.8
0°-90°	4729.7	84.8
90°-120°	409.7	7.3
90°-150°	741.2	13.3
90°-180°	851.0	15.2
0°-180°	5580.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1733	1733	1733	1733	1733	
5°	1731	1728	1710	1726	1724	164
15°	1661	1656	1640	1654	1654	468
25°	1526	1522	1508	1517	1522	703
35°	1346	1341	1329	1329	1336	840
45°	1116	1118	1107	1104	1107	861
55°	865	865	854	847	849	771
65°	584	582	573	566	566	579
75°	299	297	290	285	283	316
85°	48	53	56	58	58	68
90°	2	3	3	2	1	3
95°	9	30	88	22	14	9
105°	30	43	191	322	300	32
115°	53	64	142	300	353	52
125°	71	88	132	223	266	64
135°	86	97	131	186	210	67
145°	101	108	130	160	174	63
155°	114	118	128	143	148	53
165°	125	126	129	135	136	35
175°	131	131	130	132	131	12
180°	131	131	131	131	131	



TEST NUMBER: P844901

CATALOG NUMBER: SQ4P-F-025U-125D-B35-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1738.2	1734.7	1719.8	1732.7	1731.2
5°	1730.6	1728.1	1709.8	1725.7	1723.5
7.5°	1717.9	1713.6	1695.2	1711.1	1708.7
10°	1704.9	1700.3	1684.0	1697.8	1695.7
12.5°	1688.4	1685.7	1667.6	1681.4	1680.8
15°	1660.7	1656.1	1639.9	1654.0	1654.0
17.5°	1624.7	1622.1	1606.1	1619.3	1618.0
20°	1600.3	1596.0	1581.9	1593.6	1593.6
22.5°	1570.9	1568.2	1554.4	1563.8	1565.7
25°	1526.2	1521.9	1507.8	1517.3	1521.9
27.5°	1477.2	1473.7	1462.1	1467.9	1471.3
30°	1438.2	1438.2	1426.6	1429.0	1435.8
32.5°	1403.0	1403.0	1389.5	1391.9	1395.1
35°	1345.6	1341.0	1329.4	1329.4	1336.1
37.5°	1278.5	1276.3	1269.0	1267.6	1269.5
40°	1234.4	1231.9	1222.4	1224.9	1224.9
42.5°	1189.6	1187.2	1177.8	1174.8	1178.3
45°	1115.8	1118.2	1106.6	1104.1	1106.6
47.5°	1043.2	1043.2	1033.8	1027.2	1030.7
50°	992.9	992.9	983.7	979.1	979.1
52.5°	940.9	942.8	931.4	925.1	927.0
55°	865.3	865.3	853.7	846.9	849.1
57.5°	781.7	781.7	770.2	763.3	767.3
60°	726.2	726.2	714.5	707.5	709.9
62.5°	670.4	670.4	659.0	651.9	652.2
65°	584.5	582.3	573.0	565.9	565.9
67.5°	502.0	496.0	489.0	479.8	479.8
70°	440.7	438.3	431.3	422.1	422.1
72.5°	385.0	381.0	373.9	366.6	366.6
75°	299.1	296.7	289.9	285.3	282.9
77.5°	214.4	212.5	212.0	205.5	207.4
80°	162.4	162.4	160.3	155.4	155.4
82.5°	115.9	117.8	113.7	112.6	110.8
85°	48.4	53.0	55.8	57.9	57.9
87.5°	9.5	14.6	13.0	14.9	14.9
90°	2.0	2.9	2.9	2.0	1.0
92.5°	4.9	14.7	13.7	5.9	4.9
95°	8.8	30.3	88.1	22.5	13.7
97.5°	13.7	34.2	176.1	80.2	43.1
100°	18.6	36.2	205.5	192.8	124.3
102.5°	24.5	39.1	204.5	271.1	223.1
105°	30.3	43.1	190.8	322.0	299.5



TEST NUMBER: P844901

CATALOG NUMBER: SQ4P-F-025U-125D-B35-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	47.0	57.7	148.7	324.0	369.0
115°	52.8	63.6	141.9	299.5	353.4
117.5°	58.7	70.5	138.0	276.9	330.9
120°	63.6	76.3	135.0	255.4	308.3
122.5°	67.5	82.2	133.1	237.8	285.8
125°	71.4	88.1	132.1	223.1	266.2
127.5°	75.3	92.0	132.1	212.3	248.6
130°	79.3	93.9	131.1	201.6	233.9
132.5°	83.2	94.9	131.1	193.8	221.2
135°	86.1	96.9	131.1	185.9	210.4
137.5°	90.0	98.8	131.1	179.1	201.6
140°	93.0	101.8	131.1	172.2	191.8
142.5°	96.9	104.7	131.1	165.4	183.0
145°	100.8	107.6	130.1	160.5	174.2
147.5°	104.7	110.6	129.2	155.6	166.4
150°	107.6	113.5	129.2	150.7	159.5
152.5°	111.6	116.4	128.2	145.8	153.6
155°	114.5	118.4	128.2	142.9	147.8
157.5°	117.4	121.3	128.2	139.9	143.8
160°	120.4	123.3	129.2	138.0	140.9
162.5°	123.3	125.3	129.2	136.0	138.0
165°	125.3	126.2	129.2	135.0	136.0
167.5°	127.2	128.2	129.2	134.1	134.1
170°	128.2	129.2	130.1	133.1	133.1
172.5°	130.1	130.1	130.1	132.1	132.1
175°	131.1	131.1	130.1	132.1	131.1
177.5°	131.1	131.1	130.1	132.1	131.1
180°	131.1	131.1	131.1	131.1	131.1



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	36.2	47.9	173.2	344.6	348.5
110°	41.1	52.8	159.5	341.6	370.0



(END OF REPORT)