

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844913

Luminaire Tested: **SQ4P-F-050U-125D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P844913
REPORT IS A COMBINATION OF REPORTS P700194 AND P700244
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-F-050U-125D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6440.2 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844913
CATALOG NUMBER: SQ4P-F-050U-125D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P844913

CATALOG NUMBER: SQ4P-F-050U-125D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78	73				73
1	103	99	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66	62				62
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	58	55	52				52
3	85	76	68	62	81	72	65	59	65	60	55	59	55	51	53	50	47	44				44
4	78	67	59	52	74	64	56	50	58	52	47	53	48	43	48	44	40	37				37
5	72	60	51	45	68	57	49	43	52	45	40	47	42	38	43	38	35	32				32
6	66	54	45	39	63	51	43	38	47	40	35	43	37	33	39	34	31	28				28
7	61	48	40	34	58	46	39	33	42	36	31	39	33	29	35	31	27	25				25
8	57	44	36	30	54	42	35	30	39	32	28	36	30	26	32	28	24	22				22
9	53	40	32	27	50	39	31	26	36	29	25	33	27	23	30	25	22	20				20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18				18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15986	15986	15986
5°	16028	15835	15962
10°	15972	15777	15886
15°	15862	15664	15798
20°	15712	15532	15646
25°	15537	15349	15493
30°	15322	15198	15296
35°	15156	14973	15049
40°	14867	14723	14753
45°	14559	14439	14439
50°	14252	14119	14053
55°	13919	13732	13658
60°	13400	13184	13099
65°	12760	12509	12354
70°	11888	11635	11386
75°	10662	10334	10085
80°	8629	8517	8257
85°	5124	5907	6129



TEST NUMBER: P844913

CATALOG NUMBER: SQ4P-F-050U-125D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.5	2.5
10°-20°	465.6	7.2
20°-30°	699.3	10.9
30°-40°	834.8	13.0
40°-50°	855.4	13.3
50°-60°	762.9	11.8
60°-70°	568.1	8.8
70°-80°	308.4	4.8
80°-90°	72.0	1.1
90°-100°	104.9	1.6
100°-110°	364.9	5.7
110°-120°	353.5	5.5
120°-130°	277.3	4.3
130°-140°	219.5	3.4
140°-150°	169.4	2.6
150°-160°	121.4	1.9
160°-170°	74.3	1.2
170°-180°	25.1	0.4
0°-30°	1328.4	20.6
0°-40°	2163.2	33.6
0°-60°	3781.5	58.7
0°-90°	4730.1	73.4
90°-120°	823.3	12.8
90°-150°	1489.4	23.1
90°-180°	1710.0	26.6
0°-180°	6440.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1733	1733	1733	1733	1733	
5°	1731	1728	1710	1726	1724	164
15°	1661	1656	1640	1654	1654	468
25°	1526	1522	1508	1517	1522	703
35°	1346	1341	1329	1329	1336	840
45°	1116	1118	1107	1104	1107	861
55°	865	865	854	847	849	771
65°	584	582	573	566	566	579
75°	299	297	290	285	283	316
85°	48	53	56	58	58	68
90°	4	6	6	4	2	4
95°	18	61	177	45	28	19
105°	61	86	384	647	602	64
115°	106	128	285	602	710	105
125°	144	177	266	448	535	129
135°	173	195	264	374	423	134
145°	203	216	262	322	350	127
155°	230	238	258	287	297	106
165°	252	254	260	271	273	71
175°	264	264	262	266	264	25
180°	264	264	264	264	264	



TEST NUMBER: P844913

CATALOG NUMBER: SQ4P-F-050U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1738.2	1734.7	1719.8	1732.7	1731.2
5°	1730.6	1728.1	1709.8	1725.7	1723.5
7.5°	1717.9	1713.6	1695.2	1711.1	1708.7
10°	1704.9	1700.3	1684.0	1697.8	1695.7
12.5°	1688.4	1685.7	1667.6	1681.4	1680.8
15°	1660.7	1656.1	1639.9	1654.0	1654.0
17.5°	1624.7	1622.1	1606.1	1619.3	1618.0
20°	1600.3	1596.0	1581.9	1593.6	1593.6
22.5°	1570.9	1568.2	1554.4	1563.8	1565.7
25°	1526.2	1521.9	1507.8	1517.3	1521.9
27.5°	1477.2	1473.7	1462.1	1467.9	1471.3
30°	1438.2	1438.2	1426.6	1429.0	1435.8
32.5°	1403.0	1403.0	1389.5	1391.9	1395.1
35°	1345.6	1341.0	1329.4	1329.4	1336.1
37.5°	1278.5	1276.3	1269.0	1267.6	1269.5
40°	1234.4	1231.9	1222.4	1224.9	1224.9
42.5°	1189.6	1187.2	1177.8	1174.8	1178.3
45°	1115.8	1118.2	1106.6	1104.1	1106.6
47.5°	1043.2	1043.2	1033.8	1027.2	1030.7
50°	992.9	992.9	983.7	979.1	979.1
52.5°	940.9	942.8	931.4	925.1	927.0
55°	865.3	865.3	853.7	846.9	849.1
57.5°	781.7	781.7	770.2	763.3	767.3
60°	726.2	726.2	714.5	707.5	709.9
62.5°	670.4	670.4	659.0	651.9	652.2
65°	584.5	582.3	573.0	565.9	565.9
67.5°	502.0	496.0	489.0	479.8	479.8
70°	440.7	438.3	431.3	422.1	422.1
72.5°	385.0	381.0	373.9	366.6	366.6
75°	299.1	296.7	289.9	285.3	282.9
77.5°	214.4	212.5	212.0	205.5	207.4
80°	162.4	162.4	160.3	155.4	155.4
82.5°	115.9	117.8	113.7	112.6	110.8
85°	48.4	53.0	55.8	57.9	57.9
87.5°	9.5	14.6	13.0	14.9	14.9
90°	3.9	5.9	5.9	3.9	2.0
92.5°	9.8	29.5	27.5	11.8	9.8
95°	17.7	61.0	177.0	45.2	27.5
97.5°	27.5	68.8	353.9	161.3	86.5
100°	37.4	72.8	413.0	387.4	249.7
102.5°	49.1	78.7	411.0	544.7	448.4
105°	61.0	86.5	383.5	646.9	601.7



TEST NUMBER: P844913

CATALOG NUMBER: SQ4P-F-050U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	94.4	116.1	299.0	650.9	741.4
115°	106.2	127.8	285.2	601.7	709.9
117.5°	118.0	141.6	277.2	556.5	664.6
120°	127.8	153.3	271.4	513.3	619.4
122.5°	135.7	165.2	267.4	477.8	574.2
125°	143.6	177.0	265.5	448.4	534.9
127.5°	151.4	184.9	265.5	426.8	499.5
130°	159.3	188.8	263.5	405.1	470.0
132.5°	167.1	190.7	263.5	389.4	444.5
135°	173.0	194.6	263.5	373.6	422.8
137.5°	180.9	198.6	263.5	359.8	405.1
140°	186.8	204.5	263.5	346.1	385.5
142.5°	194.6	210.4	263.5	332.3	367.7
145°	202.6	216.4	261.6	322.5	350.0
147.5°	210.4	222.2	259.6	312.7	334.3
150°	216.4	228.1	259.6	302.9	320.6
152.5°	224.2	234.0	257.7	293.0	308.7
155°	230.1	238.0	257.7	287.1	296.9
157.5°	235.9	243.9	257.7	281.2	289.1
160°	241.9	247.8	259.6	277.2	283.2
162.5°	247.8	251.7	259.6	273.3	277.2
165°	251.7	253.6	259.6	271.4	273.3
167.5°	255.6	257.7	259.6	269.4	269.4
170°	257.7	259.6	261.6	267.4	267.4
172.5°	261.6	261.6	261.6	265.5	265.5
175°	263.5	263.5	261.6	265.5	263.5
177.5°	263.5	263.5	261.6	265.5	263.5
180°	263.5	263.5	263.5	263.5	263.5



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	72.8	96.4	348.1	692.2	700.1
110°	82.6	106.2	320.6	686.3	743.3



(END OF REPORT)