

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844967

Luminaire Tested: **SQ4P-F-150U-075D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P844967
REPORT IS A COMBINATION OF REPORTS P700136 AND P700248
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-F-150U-075D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7846.7 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 68.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844967

CATALOG NUMBER: SQ4P-F-150U-075D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P844967

CATALOG NUMBER: SQ4P-F-150U-075D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				37
1	95	91	87	83	86	82	79	76	66	64	62	52	51	49	39	38	37	31				31
2	86	79	73	68	78	72	67	62	58	55	51	46	43	41	34	32	31	26				26
3	79	69	62	56	71	63	57	52	51	47	43	40	37	35	30	28	26	22				22
4	72	61	53	48	65	56	49	44	45	40	37	36	32	29	27	25	23	19				19
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	22	20	16				16
6	61	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17	14				14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	12				12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11				11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10				10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9728	9728	9728
5°	9753	9636	9713
10°	9720	9601	9667
15°	9654	9532	9614
20°	9562	9452	9522
25°	9455	9340	9428
30°	9324	9248	9308
35°	9223	9112	9158
40°	9046	8959	8978
45°	8858	8786	8786
50°	8672	8592	8552
55°	8471	8356	8311
60°	8154	8023	7971
65°	7765	7612	7519
70°	7235	7081	6930
75°	6488	6288	6135
80°	5249	5186	5021
85°	3123	3599	3726



TEST NUMBER: P844967

CATALOG NUMBER: SQ4P-F-150U-075D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	1.3
10°-20°	283.3	3.6
20°-30°	425.6	5.4
30°-40°	508.0	6.5
40°-50°	520.5	6.6
50°-60°	464.2	5.9
60°-70°	345.7	4.4
70°-80°	187.7	2.4
80°-90°	45.3	0.6
90°-100°	304.6	3.9
100°-110°	1059.8	13.5
110°-120°	1026.6	13.1
120°-130°	805.3	10.3
130°-140°	637.4	8.1
140°-150°	491.9	6.3
150°-160°	352.6	4.5
160°-170°	215.7	2.7
170°-180°	73.0	0.9
0°-30°	808.4	10.3
0°-40°	1316.4	16.8
0°-60°	2301.1	29.3
0°-90°	2879.9	36.7
90°-120°	2391.0	30.5
90°-150°	4325.6	55.1
90°-180°	4967.0	63.3
0°-180°	7846.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1054	1054	1054	1054	1054	
5°	1053	1052	1040	1050	1049	100
15°	1011	1008	998	1006	1006	285
25°	929	926	918	923	926	428
35°	819	816	809	809	813	511
45°	679	680	673	672	673	524
55°	527	527	520	515	517	469
65°	356	354	349	344	344	352
75°	182	180	176	174	172	192
85°	30	32	34	35	35	41
90°	11	17	17	11	6	8
95°	51	177	514	131	80	54
105°	177	251	1114	1879	1748	186
115°	308	371	828	1748	2062	305
125°	417	514	771	1302	1554	373
135°	503	565	765	1085	1228	390
145°	588	628	760	937	1017	368
155°	668	691	748	834	862	308
165°	731	737	754	788	794	206
175°	765	765	760	771	765	72
180°	765	765	765	765	765	



TEST NUMBER: P844967

CATALOG NUMBER: SQ4P-F-150U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1054.4	1054.4	1054.4	1054.4	1054.4
2.5°	1057.7	1055.6	1046.6	1054.4	1053.4
5°	1053.1	1051.7	1040.4	1050.2	1048.8
7.5°	1045.4	1042.8	1031.5	1041.3	1039.8
10°	1037.5	1034.6	1024.8	1033.2	1031.9
12.5°	1027.4	1025.7	1014.8	1023.2	1022.8
15°	1010.7	1007.8	997.9	1006.5	1006.5
17.5°	988.7	987.1	977.3	985.4	984.6
20°	973.9	971.2	962.7	969.8	969.8
22.5°	956.0	954.3	945.9	951.7	952.8
25°	928.8	926.1	917.5	923.3	926.1
27.5°	898.9	896.8	889.7	893.3	895.3
30°	875.2	875.2	868.1	869.6	873.7
32.5°	853.8	853.8	845.6	847.0	849.0
35°	818.9	816.0	809.0	809.0	813.1
37.5°	778.0	776.7	772.2	771.4	772.6
40°	751.1	749.7	743.9	745.4	745.4
42.5°	723.9	722.5	716.7	714.8	717.0
45°	678.9	680.4	673.4	671.9	673.4
47.5°	634.8	634.8	629.0	625.1	627.3
50°	604.2	604.2	598.6	595.8	595.8
52.5°	572.6	573.6	566.8	563.0	564.1
55°	526.6	526.6	519.5	515.3	516.7
57.5°	475.7	475.7	468.7	464.4	466.9
60°	441.9	441.9	434.8	430.5	432.0
62.5°	408.0	408.0	401.0	396.7	396.9
65°	355.7	354.4	348.7	344.4	344.4
67.5°	305.4	301.8	297.6	291.9	291.9
70°	268.2	266.8	262.5	256.9	256.9
72.5°	234.3	231.8	227.5	223.1	223.1
75°	182.0	180.5	176.4	173.7	172.1
77.5°	130.4	129.4	129.0	125.1	126.2
80°	98.8	98.8	97.6	94.5	94.5
82.5°	70.6	71.6	69.2	68.5	67.4
85°	29.5	32.3	34.0	35.2	35.2
87.5°	5.8	8.9	7.9	9.1	9.1
90°	11.4	17.1	17.1	11.4	5.7
92.5°	28.6	85.6	79.9	34.2	28.6
95°	51.4	177.0	514.0	131.3	79.9
97.5°	79.9	199.9	1028.1	468.3	251.3
100°	108.5	211.3	1199.4	1125.2	725.3
102.5°	142.8	228.5	1193.7	1582.0	1302.2
105°	177.0	251.3	1113.7	1879.0	1747.7



TEST NUMBER: P844967

CATALOG NUMBER: SQ4P-F-150U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.1	337.0	868.1	1890.5	2153.1
115°	308.4	371.3	828.2	1747.7	2061.8
117.5°	342.7	411.2	805.3	1616.3	1930.4
120°	371.3	445.4	788.1	1490.6	1799.1
122.5°	394.1	479.8	776.8	1387.9	1667.7
125°	417.0	514.0	771.0	1302.2	1553.5
127.5°	439.8	536.8	771.0	1239.4	1450.7
130°	462.7	548.3	765.3	1176.5	1365.0
132.5°	485.5	554.0	765.3	1130.8	1290.7
135°	502.6	565.4	765.3	1085.1	1227.9
137.5°	525.5	576.9	765.3	1045.2	1176.5
140°	542.6	594.0	765.3	1005.2	1119.4
142.5°	565.4	611.1	765.3	965.3	1068.0
145°	588.3	628.2	759.6	936.7	1016.6
147.5°	611.1	645.4	753.9	908.1	970.9
150°	628.2	662.5	753.9	879.5	930.9
152.5°	651.1	679.6	748.2	851.0	896.7
155°	668.3	691.1	748.2	833.8	862.4
157.5°	685.4	708.2	748.2	816.7	839.6
160°	702.5	719.6	753.9	805.3	822.4
162.5°	719.6	731.1	753.9	793.9	805.3
165°	731.1	736.8	753.9	788.1	793.9
167.5°	742.4	748.2	753.9	782.5	782.5
170°	748.2	753.9	759.6	776.8	776.8
172.5°	759.6	759.6	759.6	771.0	771.0
175°	765.3	765.3	759.6	771.0	765.3
177.5°	765.3	765.3	759.6	771.0	765.3
180°	765.3	765.3	765.3	765.3	765.3



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	211.3	279.9	1011.0	2010.4	2033.3
110°	239.8	308.4	930.9	1993.2	2158.9



(END OF REPORT)