

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845030

Luminaire Tested: **SQ4P-PC3-100U-100D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845030
REPORT IS A COMBINATION OF REPORTS P700085 AND P700246
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PC3-100U-100D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1000 LUMENS PER FOOT
UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7003.9 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845030
CATALOG NUMBER: SQ4P-PC3-100U-100D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845030

CATALOG NUMBER: SQ4P-PC3-100U-100D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53								
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45								
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37								
3	82	72	65	59	75	67	61	56	58	53	49	49	45	42	41	38	36	32								
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	27								
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	23								
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	23	21								
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21	18								
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16								
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15								
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12513	12513	12513
5°	12609	12528	12482
10°	12579	12520	12484
15°	12513	12513	12499
20°	12431	12466	12466
25°	12313	12401	12364
30°	12162	12309	12256
35°	11982	12164	12080
40°	11783	11950	11830
45°	11571	11652	11470
50°	11267	11267	11088
55°	10909	10768	10608
60°	10383	10175	10010
65°	9595	9407	9320
70°	8406	8468	8438
75°	6759	7479	7525
80°	4808	6339	6408
85°	2932	5314	5314



TEST NUMBER: P845030

CATALOG NUMBER: SQ4P-PC3-100U-100D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	1.8
10°-20°	368.4	5.3
20°-30°	557.9	8.0
30°-40°	668.8	9.5
40°-50°	682.0	9.7
50°-60°	595.3	8.5
60°-70°	426.2	6.1
70°-80°	219.5	3.1
80°-90°	56.8	0.8
90°-100°	202.4	2.9
100°-110°	704.3	10.1
110°-120°	682.2	9.7
120°-130°	535.2	7.6
130°-140°	423.6	6.0
140°-150°	326.9	4.7
150°-160°	234.3	3.3
160°-170°	143.3	2.0
170°-180°	48.5	0.7
0°-30°	1054.6	15.1
0°-40°	1723.4	24.6
0°-60°	3000.7	42.8
0°-90°	3703.2	52.9
90°-120°	1588.9	22.7
90°-150°	2874.6	41.0
90°-180°	3301.0	47.1
0°-180°	7003.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1356	1356	1356	1356	1356	
5°	1362	1348	1353	1349	1348	129
15°	1310	1299	1310	1310	1309	369
25°	1210	1201	1218	1214	1214	557
35°	1064	1061	1080	1072	1072	665
45°	887	884	893	882	879	683
55°	678	670	669	660	660	605
65°	440	430	431	427	427	435
75°	190	198	210	211	211	205
85°	28	42	50	52	50	38
90°	8	11	11	8	4	6
95°	34	118	342	87	53	36
105°	118	167	740	1249	1162	124
115°	205	247	550	1162	1370	202
125°	277	342	512	865	1032	248
135°	334	376	509	721	816	259
145°	391	418	505	622	676	245
155°	444	459	497	554	573	205
165°	486	490	501	524	528	137
175°	509	509	505	512	509	48
180°	509	509	509	509	509	



TEST NUMBER: P845030

CATALOG NUMBER: SQ4P-PC3-100U-100D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1356.3	1356.3	1356.3	1356.3	1356.3
2.5°	1364.5	1352.7	1356.3	1353.3	1348.3
5°	1361.5	1347.9	1352.7	1348.8	1347.7
7.5°	1351.6	1338.1	1344.5	1341.8	1340.5
10°	1342.7	1329.0	1336.4	1333.8	1332.5
12.5°	1330.6	1318.0	1326.3	1323.8	1323.4
15°	1310.0	1298.9	1310.0	1310.0	1308.6
17.5°	1284.0	1274.1	1285.7	1286.6	1285.7
20°	1266.1	1255.0	1269.7	1268.4	1269.7
22.5°	1244.0	1234.9	1250.7	1247.4	1248.7
25°	1209.5	1200.9	1218.2	1214.5	1214.5
27.5°	1168.8	1162.5	1181.6	1177.5	1177.5
30°	1141.6	1135.5	1155.4	1150.4	1150.4
32.5°	1111.5	1107.3	1126.4	1120.4	1120.4
35°	1063.8	1061.3	1080.0	1072.5	1072.5
37.5°	1014.5	1012.3	1029.5	1020.4	1017.3
40°	978.3	977.2	992.2	982.2	982.2
42.5°	942.2	940.9	954.1	942.0	942.0
45°	886.8	884.1	893.0	881.6	879.1
47.5°	826.1	823.8	829.1	816.8	815.5
50°	785.0	782.4	785.0	773.6	772.5
52.5°	742.7	738.2	738.6	727.4	727.2
55°	678.2	669.6	669.4	659.5	659.5
57.5°	609.8	598.6	599.7	591.1	589.7
60°	562.7	550.3	551.4	543.8	542.5
62.5°	516.3	502.3	505.0	496.6	496.4
65°	439.5	429.7	430.9	426.9	426.9
67.5°	365.7	356.6	363.2	360.2	360.0
70°	311.6	305.2	313.9	313.9	312.8
72.5°	261.3	261.1	271.6	271.6	272.5
75°	189.6	198.3	209.8	211.1	211.1
77.5°	126.6	141.8	154.6	155.0	154.8
80°	90.5	107.6	119.3	121.9	120.6
82.5°	61.3	79.5	89.1	91.6	90.5
85°	27.7	42.5	50.2	51.6	50.2
87.5°	8.0	16.9	20.2	20.2	18.2
90°	7.6	11.4	11.4	7.6	3.8
92.5°	19.0	57.0	53.1	22.8	19.0
95°	34.2	117.6	341.6	87.3	53.1
97.5°	53.1	132.9	683.2	311.3	167.0
100°	72.1	140.4	797.0	747.7	482.0
102.5°	94.9	151.8	793.2	1051.4	865.3
105°	117.6	167.0	740.1	1248.7	1161.5



TEST NUMBER: P845030

CATALOG NUMBER: SQ4P-PC3-100U-100D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.2	223.9	577.0	1256.3	1431.0
115°	204.9	246.7	550.3	1161.5	1370.2
117.5°	227.7	273.3	535.2	1074.2	1282.9
120°	246.7	296.0	523.8	990.6	1195.6
122.5°	261.9	318.8	516.2	922.3	1108.3
125°	277.0	341.6	512.4	865.3	1032.4
127.5°	292.3	356.8	512.4	823.7	964.1
130°	307.5	364.4	508.6	781.9	907.1
132.5°	322.6	368.1	508.6	751.5	857.8
135°	334.0	375.8	508.6	721.2	816.0
137.5°	349.2	383.3	508.6	694.6	781.9
140°	360.6	394.8	508.6	668.0	743.9
142.5°	375.8	406.1	508.6	641.5	709.8
145°	390.9	417.6	504.8	622.5	675.6
147.5°	406.1	428.9	501.0	603.5	645.3
150°	417.6	440.3	501.0	584.5	618.6
152.5°	432.7	451.7	497.2	565.5	595.9
155°	444.1	459.2	497.2	554.2	573.1
157.5°	455.4	470.7	497.2	542.8	558.0
160°	466.9	478.2	501.0	535.2	546.5
162.5°	478.2	485.9	501.0	527.5	535.2
165°	485.9	489.7	501.0	523.8	527.5
167.5°	493.4	497.2	501.0	520.0	520.0
170°	497.2	501.0	504.8	516.2	516.2
172.5°	504.8	504.8	504.8	512.4	512.4
175°	508.6	508.6	504.8	512.4	508.6
177.5°	508.6	508.6	504.8	512.4	508.6
180°	508.6	508.6	508.6	508.6	508.6



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	140.4	186.0	671.8	1336.0	1351.2
110°	159.4	204.9	618.6	1324.7	1434.7



(END OF REPORT)