

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844991

Luminaire Tested: **SQ4P-PC3-050U-075D-B35-1D-UNV**

Issue Date: 8/14/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P844991  
REPORT IS A COMBINATION OF REPORTS P700196 AND P700244  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PC3-050U-075D-B35-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4528.1 lumens  
Efficiency: N/A  
Efficacy: 117.3 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 38.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844991

CATALOG NUMBER: SQ4P-PC3-050U-075D-B35-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P844991

CATALOG NUMBER: SQ4P-PC3-050U-075D-B35-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62																			
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53																			
2	92	84	78	73	86	79	73	69	69	65	62	61	57	55	53	50	48	44																			
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	43	41	37																			
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32																			
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28																			
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24																			
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21																			
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19																			
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17																			
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	18	16																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9523	9523	9523
5°	9597	9534	9499
10°	9573	9528	9501
15°	9523	9523	9513
20°	9460	9487	9487
25°	9371	9438	9409
30°	9256	9368	9327
35°	9119	9258	9193
40°	8967	9094	9003
45°	8805	8867	8729
50°	8575	8575	8437
55°	8303	8194	8072
60°	7901	7743	7619
65°	7302	7156	7093
70°	6396	6444	6423
75°	5144	5689	5729
80°	3661	4824	4877
85°	2234	4054	4054



TEST NUMBER: P844991

CATALOG NUMBER: SQ4P-PC3-050U-075D-B35-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	97.7	2.2
10°-20°	280.4	6.2
20°-30°	424.6	9.4
30°-40°	509.0	11.2
40°-50°	519.0	11.5
50°-60°	453.0	10.0
60°-70°	324.3	7.2
70°-80°	167.1	3.7
80°-90°	42.9	0.9
90°-100°	104.9	2.3
100°-110°	364.9	8.1
110°-120°	353.5	7.8
120°-130°	277.3	6.1
130°-140°	219.5	4.8
140°-150°	169.4	3.7
150°-160°	121.4	2.7
160°-170°	74.3	1.6
170°-180°	25.1	0.6
0°-30°	802.6	17.7
0°-40°	1311.6	29.0
0°-60°	2283.6	50.4
0°-90°	2817.9	62.2
90°-120°	823.3	18.2
90°-150°	1489.4	32.9
90°-180°	1710.0	37.8
0°-180°	4528.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1032	1032	1032	1032	1032	
5°	1036	1026	1029	1026	1026	98
15°	997	988	997	997	996	281
25°	920	914	927	924	924	424
35°	810	808	822	816	816	506
45°	675	673	680	671	669	519
55°	516	510	509	502	502	460
65°	334	327	328	325	325	331
75°	144	151	160	161	161	156
85°	21	32	38	39	38	29
90°	4	6	6	4	2	3
95°	18	61	177	45	28	19
105°	61	86	384	647	602	64
115°	106	128	285	602	710	105
125°	144	177	266	448	535	129
135°	173	195	264	374	423	134
145°	203	216	262	322	350	127
155°	230	238	258	287	297	106
165°	252	254	260	271	273	71
175°	264	264	262	266	264	25
180°	264	264	264	264	264	



TEST NUMBER: P844991

CATALOG NUMBER: SQ4P-PC3-050U-075D-B35-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1032.2	1032.2	1032.2	1032.2	1032.2
2.5°	1038.5	1029.4	1032.2	1029.9	1026.1
5°	1036.2	1025.7	1029.4	1026.4	1025.6
7.5°	1028.6	1018.4	1023.2	1021.1	1020.2
10°	1021.8	1011.4	1017.0	1015.1	1014.1
12.5°	1012.6	1003.0	1009.3	1007.5	1007.1
15°	997.0	988.5	997.0	997.0	996.0
17.5°	977.2	969.6	978.5	979.2	978.5
20°	963.5	955.1	966.3	965.4	966.3
22.5°	946.7	939.8	951.8	949.3	950.3
25°	920.5	913.9	927.1	924.3	924.3
27.5°	889.5	884.7	899.2	896.1	896.1
30°	868.8	864.2	879.3	875.5	875.5
32.5°	845.9	842.7	857.2	852.6	852.6
35°	809.6	807.6	822.0	816.2	816.2
37.5°	772.1	770.4	783.4	776.5	774.2
40°	744.5	743.7	755.1	747.5	747.5
42.5°	717.0	716.0	726.1	716.9	716.9
45°	674.8	672.9	679.6	670.9	669.0
47.5°	628.7	626.9	631.0	621.6	620.6
50°	597.4	595.5	597.4	588.7	587.8
52.5°	565.3	561.8	562.2	553.6	553.4
55°	516.2	509.6	509.4	501.8	501.8
57.5°	464.1	455.5	456.4	449.7	448.8
60°	428.2	418.8	419.6	413.8	412.9
62.5°	393.0	382.2	384.4	377.9	377.8
65°	334.5	327.0	327.8	324.9	324.9
67.5°	278.3	271.4	276.4	274.2	274.0
70°	237.1	232.3	238.9	238.9	238.1
72.5°	198.8	198.6	206.8	206.8	207.5
75°	144.3	150.9	159.6	160.7	160.7
77.5°	96.4	107.9	117.6	117.9	117.8
80°	68.9	81.9	90.8	92.8	91.8
82.5°	46.6	60.5	67.9	69.7	68.9
85°	21.1	32.3	38.3	39.2	38.3
87.5°	6.1	12.8	15.4	15.4	13.8
90°	3.9	5.9	5.9	3.9	2.0
92.5°	9.8	29.5	27.5	11.8	9.8
95°	17.7	61.0	177.0	45.2	27.5
97.5°	27.5	68.8	353.9	161.3	86.5
100°	37.4	72.8	413.0	387.4	249.7
102.5°	49.1	78.7	411.0	544.7	448.4
105°	61.0	86.5	383.5	646.9	601.7



TEST NUMBER: P844991

CATALOG NUMBER: SQ4P-PC3-050U-075D-B35-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	94.4	116.1	299.0	650.9	741.4
115°	106.2	127.8	285.2	601.7	709.9
117.5°	118.0	141.6	277.2	556.5	664.6
120°	127.8	153.3	271.4	513.3	619.4
122.5°	135.7	165.2	267.4	477.8	574.2
125°	143.6	177.0	265.5	448.4	534.9
127.5°	151.4	184.9	265.5	426.8	499.5
130°	159.3	188.8	263.5	405.1	470.0
132.5°	167.1	190.7	263.5	389.4	444.5
135°	173.0	194.6	263.5	373.6	422.8
137.5°	180.9	198.6	263.5	359.8	405.1
140°	186.8	204.5	263.5	346.1	385.5
142.5°	194.6	210.4	263.5	332.3	367.7
145°	202.6	216.4	261.6	322.5	350.0
147.5°	210.4	222.2	259.6	312.7	334.3
150°	216.4	228.1	259.6	302.9	320.6
152.5°	224.2	234.0	257.7	293.0	308.7
155°	230.1	238.0	257.7	287.1	296.9
157.5°	235.9	243.9	257.7	281.2	289.1
160°	241.9	247.8	259.6	277.2	283.2
162.5°	247.8	251.7	259.6	273.3	277.2
165°	251.7	253.6	259.6	271.4	273.3
167.5°	255.6	257.7	259.6	269.4	269.4
170°	257.7	259.6	261.6	267.4	267.4
172.5°	261.6	261.6	261.6	265.5	265.5
175°	263.5	263.5	261.6	265.5	263.5
177.5°	263.5	263.5	261.6	265.5	263.5
180°	263.5	263.5	263.5	263.5	263.5



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	72.8	96.4	348.1	692.2	700.1
110°	82.6	106.2	320.6	686.3	743.3



(END OF REPORT)