

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845000

Luminaire Tested: **SQ4P-PC3-075U-050D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845000
REPORT IS A COMBINATION OF REPORTS P700223 AND P700245
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PC3-075U-050D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT
UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4354.9 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 35.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845000

CATALOG NUMBER: SQ4P-PC3-075U-050D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845000

CATALOG NUMBER: SQ4P-PC3-075U-050D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				44				
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37				37				
2	88	80	74	69	80	74	69	64	61	57	54	50	47	45	39	37	36	31				31				
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30	26				26				
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22				22				
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19				19				
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20	17				17				
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15				15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				12				
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11				11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6400	6400	6400
5°	6450	6407	6384
10°	6434	6403	6386
15°	6400	6400	6394
20°	6358	6377	6377
25°	6297	6344	6324
30°	6221	6296	6269
35°	6129	6223	6179
40°	6027	6112	6051
45°	5918	5960	5868
50°	5763	5763	5671
55°	5580	5508	5426
60°	5311	5204	5121
65°	4908	4812	4768
70°	4297	4332	4316
75°	3458	3825	3846
80°	2460	3246	3273
85°	1503	2721	2721



TEST NUMBER: P845000

CATALOG NUMBER: SQ4P-PC3-075U-050D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.7	1.5
10°-20°	188.4	4.3
20°-30°	285.4	6.6
30°-40°	342.1	7.9
40°-50°	348.8	8.0
50°-60°	304.5	7.0
60°-70°	218.0	5.0
70°-80°	112.3	2.6
80°-90°	29.3	0.7
90°-100°	150.9	3.5
100°-110°	525.0	12.1
110°-120°	508.6	11.7
120°-130°	398.9	9.2
130°-140°	315.7	7.3
140°-150°	243.7	5.6
150°-160°	174.7	4.0
160°-170°	106.8	2.5
170°-180°	36.1	0.8
0°-30°	539.4	12.4
0°-40°	881.5	20.2
0°-60°	1534.9	35.2
0°-90°	1894.5	43.5
90°-120°	1184.4	27.2
90°-150°	2142.8	49.2
90°-180°	2460.0	56.5
0°-180°	4354.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	696	689	692	690	689	66
15°	670	664	670	670	669	189
25°	619	614	623	621	621	285
35°	544	543	552	549	549	340
45°	454	452	457	451	450	349
55°	347	342	342	337	337	309
65°	225	220	220	218	218	222
75°	97	102	107	108	108	105
85°	14	22	26	26	26	19
90°	6	8	8	6	3	4
95°	25	88	255	65	40	27
105°	88	124	552	931	866	92
115°	153	184	410	866	1021	151
125°	207	255	382	645	770	185
135°	249	280	379	538	608	193
145°	291	311	376	464	504	182
155°	331	342	371	413	427	153
165°	362	365	373	390	393	102
175°	379	379	376	382	379	36
180°	379	379	379	379	379	



TEST NUMBER: P845000

CATALOG NUMBER: SQ4P-PC3-075U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	693.7	693.7	693.7	693.7	693.7
2.5°	697.9	691.8	693.7	692.2	689.7
5°	696.4	689.4	691.8	689.9	689.3
7.5°	691.4	684.4	687.6	686.4	685.7
10°	686.8	679.8	683.5	682.3	681.6
12.5°	680.6	674.1	678.3	677.2	676.9
15°	670.0	664.4	670.0	670.0	669.4
17.5°	656.8	651.6	657.7	658.1	657.7
20°	647.6	641.9	649.5	648.8	649.5
22.5°	636.3	631.7	639.7	638.0	638.7
25°	618.6	614.2	623.2	621.2	621.2
27.5°	597.9	594.7	604.4	602.3	602.3
30°	583.9	580.8	591.0	588.4	588.4
32.5°	568.5	566.4	576.2	573.0	573.0
35°	544.2	542.8	552.5	548.6	548.6
37.5°	518.9	517.8	526.6	521.9	520.3
40°	500.4	499.9	507.5	502.4	502.4
42.5°	481.9	481.3	488.0	481.8	481.8
45°	453.6	452.2	456.8	450.9	449.7
47.5°	422.5	421.4	424.1	417.8	417.2
50°	401.5	400.2	401.5	395.6	395.1
52.5°	380.0	377.6	377.8	372.1	372.0
55°	346.9	342.5	342.4	337.3	337.3
57.5°	312.0	306.2	306.8	302.3	301.6
60°	287.8	281.5	282.0	278.2	277.5
62.5°	264.1	256.9	258.3	254.0	253.9
65°	224.8	219.8	220.4	218.4	218.4
67.5°	187.0	182.4	185.8	184.3	184.2
70°	159.3	156.2	160.6	160.6	160.0
72.5°	133.7	133.6	139.0	139.0	139.4
75°	97.0	101.5	107.3	107.9	107.9
77.5°	64.8	72.5	79.1	79.3	79.2
80°	46.3	55.0	61.1	62.3	61.6
82.5°	31.3	40.6	45.6	46.9	46.3
85°	14.2	21.7	25.7	26.3	25.7
87.5°	4.1	8.6	10.3	10.3	9.3
90°	5.7	8.5	8.5	5.7	2.8
92.5°	14.2	42.5	39.6	16.9	14.2
95°	25.4	87.7	254.6	65.1	39.6
97.5°	39.6	99.0	509.2	232.0	124.5
100°	53.7	104.7	594.1	557.4	359.3
102.5°	70.8	113.1	591.3	783.7	645.1
105°	87.7	124.5	551.7	930.8	865.7



TEST NUMBER: P845000

CATALOG NUMBER: SQ4P-PC3-075U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.8	166.9	430.1	936.5	1066.6
115°	152.8	183.9	410.2	865.7	1021.3
117.5°	169.8	203.7	399.0	800.7	956.3
120°	183.9	220.7	390.4	738.4	891.2
122.5°	195.2	237.7	384.8	687.5	826.1
125°	206.6	254.6	381.9	645.1	769.5
127.5°	217.8	266.0	381.9	614.0	718.7
130°	229.2	271.6	379.1	582.8	676.2
132.5°	240.4	274.4	379.1	560.2	639.4
135°	248.9	280.1	379.1	537.5	608.3
137.5°	260.3	285.7	379.1	517.8	582.8
140°	268.8	294.3	379.1	497.9	554.6
142.5°	280.1	302.8	379.1	478.1	529.0
145°	291.4	311.2	376.3	464.0	503.6
147.5°	302.8	319.7	373.4	449.8	481.0
150°	311.2	328.2	373.4	435.7	461.2
152.5°	322.5	336.6	370.6	421.6	444.2
155°	331.0	342.3	370.6	413.1	427.2
157.5°	339.5	350.8	370.6	404.5	415.9
160°	348.0	356.5	373.4	399.0	407.4
162.5°	356.5	362.2	373.4	393.3	399.0
165°	362.2	365.0	373.4	390.4	393.3
167.5°	367.8	370.6	373.4	387.6	387.6
170°	370.6	373.4	376.3	384.8	384.8
172.5°	376.3	376.3	376.3	381.9	381.9
175°	379.1	379.1	376.3	381.9	379.1
177.5°	379.1	379.1	376.3	381.9	379.1
180°	379.1	379.1	379.1	379.1	379.1



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	104.7	138.7	500.7	995.9	1007.2
110°	118.8	152.8	461.2	987.4	1069.5



(END OF REPORT)