

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845003

Luminaire Tested: **SQ4P-PC3-075U-075D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845003
REPORT IS A COMBINATION OF REPORTS P700224 AND P700245
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PC3-075U-075D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT
UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5278.6 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 44.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845003

CATALOG NUMBER: SQ4P-PC3-075U-075D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845003

CATALOG NUMBER: SQ4P-PC3-075U-075D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53																			
1	99	94	90	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45																			
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38																			
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32																			
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31	27																			
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24																			
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21																			
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21	18																			
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16																			
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	19	17	15																			
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9523	9523	9523
5°	9597	9534	9499
10°	9573	9528	9501
15°	9523	9523	9513
20°	9460	9487	9487
25°	9371	9438	9409
30°	9256	9368	9327
35°	9119	9258	9193
40°	8967	9094	9003
45°	8805	8867	8729
50°	8575	8575	8437
55°	8303	8194	8072
60°	7901	7743	7619
65°	7302	7156	7093
70°	6396	6444	6423
75°	5144	5689	5729
80°	3661	4824	4877
85°	2234	4054	4054



TEST NUMBER: P845003

CATALOG NUMBER: SQ4P-PC3-075U-075D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.7	1.9
10°-20°	280.4	5.3
20°-30°	424.6	8.0
30°-40°	509.0	9.6
40°-50°	519.0	9.8
50°-60°	453.0	8.6
60°-70°	324.3	6.1
70°-80°	167.1	3.2
80°-90°	43.2	0.8
90°-100°	150.9	2.9
100°-110°	525.0	9.9
110°-120°	508.6	9.6
120°-130°	398.9	7.6
130°-140°	315.7	6.0
140°-150°	243.7	4.6
150°-160°	174.7	3.3
160°-170°	106.8	2.0
170°-180°	36.1	0.7
0°-30°	802.6	15.2
0°-40°	1311.6	24.8
0°-60°	2283.6	43.3
0°-90°	2818.2	53.4
90°-120°	1184.4	22.4
90°-150°	2142.8	40.6
90°-180°	2460.0	46.6
0°-180°	5278.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1032	1032	1032	1032	1032	
5°	1036	1026	1029	1026	1026	98
15°	997	988	997	997	996	281
25°	920	914	927	924	924	424
35°	810	808	822	816	816	506
45°	675	673	680	671	669	519
55°	516	510	509	502	502	460
65°	334	327	328	325	325	331
75°	144	151	160	161	161	156
85°	21	32	38	39	38	29
90°	6	8	8	6	3	4
95°	25	88	255	65	40	27
105°	88	124	552	931	866	92
115°	153	184	410	866	1021	151
125°	207	255	382	645	770	185
135°	249	280	379	538	608	193
145°	291	311	376	464	504	182
155°	331	342	371	413	427	153
165°	362	365	373	390	393	102
175°	379	379	376	382	379	36
180°	379	379	379	379	379	



TEST NUMBER: P845003

CATALOG NUMBER: SQ4P-PC3-075U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1032.2	1032.2	1032.2	1032.2	1032.2
2.5°	1038.5	1029.4	1032.2	1029.9	1026.1
5°	1036.2	1025.7	1029.4	1026.4	1025.6
7.5°	1028.6	1018.4	1023.2	1021.1	1020.2
10°	1021.8	1011.4	1017.0	1015.1	1014.1
12.5°	1012.6	1003.0	1009.3	1007.5	1007.1
15°	997.0	988.5	997.0	997.0	996.0
17.5°	977.2	969.6	978.5	979.2	978.5
20°	963.5	955.1	966.3	965.4	966.3
22.5°	946.7	939.8	951.8	949.3	950.3
25°	920.5	913.9	927.1	924.3	924.3
27.5°	889.5	884.7	899.2	896.1	896.1
30°	868.8	864.2	879.3	875.5	875.5
32.5°	845.9	842.7	857.2	852.6	852.6
35°	809.6	807.6	822.0	816.2	816.2
37.5°	772.1	770.4	783.4	776.5	774.2
40°	744.5	743.7	755.1	747.5	747.5
42.5°	717.0	716.0	726.1	716.9	716.9
45°	674.8	672.9	679.6	670.9	669.0
47.5°	628.7	626.9	631.0	621.6	620.6
50°	597.4	595.5	597.4	588.7	587.8
52.5°	565.3	561.8	562.2	553.6	553.4
55°	516.2	509.6	509.4	501.8	501.8
57.5°	464.1	455.5	456.4	449.7	448.8
60°	428.2	418.8	419.6	413.8	412.9
62.5°	393.0	382.2	384.4	377.9	377.8
65°	334.5	327.0	327.8	324.9	324.9
67.5°	278.3	271.4	276.4	274.2	274.0
70°	237.1	232.3	238.9	238.9	238.1
72.5°	198.8	198.6	206.8	206.8	207.5
75°	144.3	150.9	159.6	160.7	160.7
77.5°	96.4	107.9	117.6	117.9	117.8
80°	68.9	81.9	90.8	92.8	91.8
82.5°	46.6	60.5	67.9	69.7	68.9
85°	21.1	32.3	38.3	39.2	38.3
87.5°	6.1	12.8	15.4	15.4	13.8
90°	5.7	8.5	8.5	5.7	2.8
92.5°	14.2	42.5	39.6	16.9	14.2
95°	25.4	87.7	254.6	65.1	39.6
97.5°	39.6	99.0	509.2	232.0	124.5
100°	53.7	104.7	594.1	557.4	359.3
102.5°	70.8	113.1	591.3	783.7	645.1
105°	87.7	124.5	551.7	930.8	865.7



TEST NUMBER: P845003

CATALOG NUMBER: SQ4P-PC3-075U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.8	166.9	430.1	936.5	1066.6
115°	152.8	183.9	410.2	865.7	1021.3
117.5°	169.8	203.7	399.0	800.7	956.3
120°	183.9	220.7	390.4	738.4	891.2
122.5°	195.2	237.7	384.8	687.5	826.1
125°	206.6	254.6	381.9	645.1	769.5
127.5°	217.8	266.0	381.9	614.0	718.7
130°	229.2	271.6	379.1	582.8	676.2
132.5°	240.4	274.4	379.1	560.2	639.4
135°	248.9	280.1	379.1	537.5	608.3
137.5°	260.3	285.7	379.1	517.8	582.8
140°	268.8	294.3	379.1	497.9	554.6
142.5°	280.1	302.8	379.1	478.1	529.0
145°	291.4	311.2	376.3	464.0	503.6
147.5°	302.8	319.7	373.4	449.8	481.0
150°	311.2	328.2	373.4	435.7	461.2
152.5°	322.5	336.6	370.6	421.6	444.2
155°	331.0	342.3	370.6	413.1	427.2
157.5°	339.5	350.8	370.6	404.5	415.9
160°	348.0	356.5	373.4	399.0	407.4
162.5°	356.5	362.2	373.4	393.3	399.0
165°	362.2	365.0	373.4	390.4	393.3
167.5°	367.8	370.6	373.4	387.6	387.6
170°	370.6	373.4	376.3	384.8	384.8
172.5°	376.3	376.3	376.3	381.9	381.9
175°	379.1	379.1	376.3	381.9	379.1
177.5°	379.1	379.1	376.3	381.9	379.1
180°	379.1	379.1	379.1	379.1	379.1



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	104.7	138.7	500.7	995.9	1007.2
110°	118.8	152.8	461.2	987.4	1069.5



(END OF REPORT)